

DATA SHEET

NTC THERMISTOR


HIGH SURGE INRUSH CURRENT LIMITER

NT SERIES

RoHS compliant & Halogen free




Product specification— February 19, 2021 V.0



NTC Thermistor NT series Data Sheet

Features

- Effectively restrain surge
- Low power loss under the stable state
- Over-current wide control range and fast response
- Thermal and electrical characteristics of with stability
- Wide range of electrical specifications
- RoHS& Halogen Free (HF) compliant
- Safety certification-UL / TUV




Applications

- Monitor, Sps, Fax, Telecom, Adaptor etc.
- Power supply, Communications equipment etc.

Part Number Code


NT	E	04	—	010	M	F	TR
Series Code	Nominal Diameter	Max. Steady State Current		R25 (Nominal Resistance at 25°C)	Tolerance of R25	Forming Type (Kink)	Packing
High Surge NTC Thermistor	B: 5mm, D: 8mm, E: 10mm, G: 13mm, J: 15mm, L: 20mm,	01~12: 1A~12A R25: 0.25A		0R7: 0.7Ω , 1R3: 1.3Ω, 2R5: 2.5 Ω, 001~008: 1~8Ω, 010~080: 10~80Ω, 120: 120Ω	L: ±15%, M: ±20%	No suffix: Straight leads O: Outside crimped leads F: Y Kinked leads, V: Wider kink leads,	No suffix: Bulk, TB: Tape & Box, TR: Tape & Reel

Marking



- ① Brightking Logo
- ② Disk Size
- ③ Zero Power Resistance at 25°C
- ④ Internal control code

Dimensions (Unit: mm)




Disc Φ	D (max.)	H (max.)	H1 (max.)	L (Min.)	L1 (Min.)	d (± 0.02)	d1 (± 0.4)	T (max.)	F (± 0.8)	e (± 0.5)	Lead Shape Type			
5(B)	7.5	/	10.5	/	15	0.60	1.4	5.0	5.0	1.6	/	/	/	v
8(D)	11.0	13.5	14.0	20.0	15	0.80	1.4	6.0	5.0	2.0	Straight	O	F	/
10(E)	13.5	16.0	18.0	20.0	15	0.80	1.4	6.0	5.0	2.1	Straight	O	F	/
13(G)	16.0	19.0	22.0	20.0	15	1.00	1.6	6.0	7.5	2.9	Straight	O	F	/
15(J)	18.0	21.0	25.0	20.0	15	1.00	1.6	6.5	7.5	3.1	Straight	O	F	/
20(L)	24.0	28.0	33.0	20.0	15	1.00	1.6	7.5	7.5	3.6	Straight	O	F	/

Remarks: The default lead shape for 8 Φ (NTD) ~20 Φ (NTL) products is Straight lead shape.

"V" type is only for 5 Φ (NTB) products.

Maximum Power Rating



Electrical Characteristics

Nominal Diameter (mm)	Part Number	Zero Power Resistance at 25°C	Maximum Steady State Current at 25°C	Residual Resistance at 25°C I _{max} R _{I_{max}}	Typical value		Recommend Capacitance 240Vac	Maximum Steady Power	Operating Temperature Range	U _L	T _{UV}
					Thermal Time Constant	Thermal Dissipation Constant					
		(Ω)	(A)	(Ω)	(s)	(mW/°C)	(μF)	(W)	(°C)		
5(B)	NTB02-005□	5	2	0.325	35	7	60	1.5	-40~+170	V	V
	NTB02-006□	6	2	0.350	35	7	60	1.5	-40~+170	V	V
	NTB02-007□	7	2	0.375	35	7	60	1.5	-40~+170	V	V
	NTB02-008□	8	2	0.400	35	7	60	1.5	-40~+170	V	V
	NTB02-009□	9	2	0.425	35	7	60	1.5	-40~+170	V	V
	NTB02-010□	10	2	0.450	35	7	60	1.5	-40~+170	V	V
	NTB01-012□	12	1	1.250	35	7	60	1.5	-40~+170	V	V
	NTBR25-045□	45	0.25	7.720	35	7	40	1.5	-40~+170	V	V
8(D)	NTD04-003□	3	4	0.150	48	12	220	2.3	-40~+170	V	V
	NTD04-004□	4	4	0.166	48	12	220	2.3	-40~+170	V	V
	NTD04-005□	5	4	0.182	48	9	220	2.3	-40~+170	V	V
	NTD04-006□	6	4	0.191	48	9	220	2.3	-40~+170	V	V
	NTD03-007□	7	3	0.195	48	9	220	2.3	-40~+170	V	—
	NTD03-008□	8	3	0.278	45	12	220	2.3	-40~+170	V	V
	NTD03-009□	9	3	0.283	45	12	220	2.3	-40~+170	V	V
	NTD03-010□	10	3	0.288	45	12	220	2.3	-40~+170	V	V
10(E)	NTE05-001□	1	5	0.082	59	12	330	2.5	-40~+170	V	V
	NTE05-002□	2	5	0.094	59	12	330	2.5	-40~+170	V	V
	NTE05-003□	3	5	0.098	59	12	330	2.5	-40~+170	V	V
	NTE04-005□	5	4	0.152	59	12	330	2.5	-40~+170	V	V
	NTE04-006□	6	4	0.166	59	12	330	2.5	-40~+170	V	V
	NTE04-007□	7	3	0.180	59	12	330	2.5	-40~+170	V	—
	NTE04-008□	8	4	0.194	59	12	330	2.5	-40~+170	V	V
	NTE04-009□	9	4	0.195	59	12	330	2.5	-40~+170	V	V
	NTE04-010□	10	4	0.196	59	12	330	2.5	-40~+170	V	V
	NTE03-011□	11	3	0.293	58	11	270	2.5	-40~+170	V	V
	NTE03-012□	12	3	0.296	58	11	270	2.5	-40~+170	V	V
	NTE03-013□	13	3	0.299	58	11	270	2.5	-40~+170	V	V
	NTE03-014□	14	3	0.302	58	11	270	2.5	-40~+170	V	V
	NTE03-015□	15	3	0.305	62	11	270	2.5	-40~+170	V	V
	NTE03-016□	16	3	0.308	62	11	270	2.5	-40~+170	V	V
	NTE03-017□	17	3	0.311	62	11	270	2.5	-40~+170	V	V
	NTE03-018□	18	3	0.314	62	11	270	2.5	-40~+170	V	V
	NTE03-019□	19	3	0.317	62	11	270	2.5	-40~+170	V	V
	NTE03-020□	20	3	0.320	62	11	270	2.5	-40~+170	V	V
	NTE03-021□	21	3	0.323	62	11	270	2.5	-40~+170	V	V
	NTE03-022□	22	3	0.326	62	11	270	2.5	-40~+170	V	V

NTC Inrush Current Limiter

NT series



Nominal Diameter (mm)	Part Number	Zero Power Resistance at 25°C	Maximum Steady State Current at 25°C	Residual Resistance at 25°C I _{max} R _{Imax}	Typical value		Recommend Capacitance 240Vac	Maximum Steady Power	Operating Temperature Range	U _L	T _{UV}
					Thermal Time Constant	Thermal Dissipation Constant					
		(Ω)	(A)	(Ω)	(s)	(mW/°C)	(μF)	(W)	(°C)		
13(G)	NTG07-001□	1	7	0.074	85	18	680	3	-40~+200	V	V
	NTG07-002□	2	7	0.074	85	18	680	3	-40~+200	V	V
	NTG07-003□	3	7	0.074	85	18	680	3	-40~+200	V	V
	NTG06-005□	5	6	0.120	93	17	560	3	-40~+200	V	V
	NTG05-006□	6	5	0.163	90	17	560	3	-40~+200	V	V
	NTG05-007□	7	5	0.171	80	19	560	3	-40~+200	V	V
	NTG05-008□	8	5	0.155	91	15	560	3	-40~+200	V	V
	NTG05-009□	9	5	0.163	89	15	560	3	-40~+200	V	V
	NTG05-010□	10	5	0.171	87	14	560	3	-40~+200	V	V
	NTG04-011□	11	4	0.241	87	14	560	3	-40~+200	V	V
	NTG04-012□	12	4	0.243	87	14	560	3	-40~+200	V	V
	NTG04-013□	13	4	0.244	87	14	560	3	-40~+200	V	V
	NTG04-014□	14	4	0.245	87	14	560	3	-40~+200	V	V
	NTG04-015□	15	4	0.247	87	14	560	3	-40~+200	V	V
	NTG04-016□	16	4	0.250	87	15	560	3	-40~+200	V	V
	NTG04-017□	17	4	0.255	87	15	560	3	-40~+200	V	V
	NTG04-018□	18	4	0.260	87	15	560	3	-40~+200	V	V
	NTG04-019□	19	4	0.265	87	15	560	3	-40~+200	V	V
	NTG04-020□	20	4	0.270	87	15	560	3	-40~+200	V	V
15(J)	NTJ09-001□	1	9	0.051	104	20	1000	4	-40~+200	V	V
	NTJ09-002□	2	9	0.056	104	20	820	4	-40~+200	V	V
	NTJ09-2R5□	2.5	9	0.063	104	20	820	4	-40~+200	V	V
	NTJ09-003□	3	9	0.059	106	20	820	4	-40~+200	V	V
	NTJ08-005□	5	8	0.082	110	20	820	4	-40~+200	V	V
	NTJ06-008□	8	6	0.142	99	15	680	4	-40~+200	V	V
	NTJ06-009□	9	6	0.143	99	16	680	4	-40~+200	V	V
	NTJ06-010□	10	6	0.145	99	19	680	4	-40~+200	V	V
	NTJ06-011□	11	6	0.148	99	19	680	4	-40~+200	V	V
	NTJ06-012□	12	6	0.149	99	21	680	4	-40~+200	V	V
	NTJ06-013□	13	6	0.152	99	19	680	4	-40~+200	V	V
	NTJ06-014□	14	6	0.156	99	19	680	4	-40~+200	V	V
	NTJ06-015□	15	6	0.159	99	17	680	4	-40~+200	V	V
	NTJ04-040□	40	4	0.292	101	20	680	4	-40~+200	V	V
20(L)	NTL12-0R7□	0.7	12	0.039	160	28	1200	5	-40~+200	V	V
	NTL12-001□	1	12	0.039	160	28	1200	5	-40~+200	V	V
	NTL12-002□	2	12	0.041	160	28	1200	5	-40~+200	V	V
	NTL12-2R5□	2.5	12	0.046	120	24	1200	5	-40~+200	V	V
	NTL12-003□	3	12	0.050	130	24	1200	5	-40~+200	V	V
	NTL10-005□	5	10	0.068	144	24	1200	5	-40~+200	V	V
	NTL10-006□	6	10	0.072	144	24	1200	5	-40~+200	V	V

Remarks: □ means tolerance of R25 , L: ±15%, M: ±20%,



Reliability Test Requirements

Test items Reference standard	Test conditions			Criterion
High Temperature Storage IEC 60068-2-2	$T_U \pm 5^\circ\text{C}$, 1000 $\pm$ 24hrs			No visible damage $\Delta R_{25}/R_{25}$ $\leq 20\%$
Damp Heat, Steady State IEC 60068-2-78	40 $\pm 2^\circ\text{C}$, 90~95%RH , 1000 $\pm$ 24hrs			No visible damage $\Delta R_{25}/R_{25}$ $\leq 20\%$
Endurance IEC 60539-1	25 $\pm 5^\circ\text{C}$, I _{max} .1000 $\pm$ 24hrs			No visible damage $\Delta R_{25}/R_{25}$ $\leq 20\%$
Rapid Change of Temperature IEC 60068-2-14	Step	Temperature ($^\circ\text{C}$)	Period (min.)	No visible damage $\Delta R_{25}/R_{25}$ $\leq 20\%$
	1	$T_L \pm 5$	30 ± 3	
	2	Room	5 ± 3	
	3	$T_U \pm 5$	30 ± 3	
	4	Room	5 ± 3	
	5 Cycles			
Capacitance test standard specifications	25 $\pm 5^\circ\text{C}$, C _{th} , interval 2mins. , Number of cycles: 1000 , C _{th} =Capacitance at 340 VDC			No visible damage $\Delta R_{25}/R_{25}$ $\leq 20\%$
Cyclic endurance IEC 60539-1	25 $\pm 5^\circ\text{C}$, I _{max} .1min ON/5min OFF*1000cycles;			No visible damage $\Delta R_{25}/R_{25}$ $\leq 20\%$
Insulation Test MIL-STD-202F-Method 302	1000 VDC, 1min			No visible damage
Tensile Strength of Terminals IEC 60068-2-21	Gradually applying the force specified and keeping the unit fixed for 10 ± 1 sec.			No visible damage $\Delta R_{25}/R_{25}$ $\leq 10\%$
	Terminal diameter (mm)		Force (kg)	
	0.5<d $\leq$ 0.8		1.0	
	0.8<d $\leq$ 1.25		2.0	
Bending Strength of Terminals IEC60068-2-21	Follow spec: Hold specimen and apply the force specified below to each lead. Bend the specimen to 90°, then return to the original position. Repeat the procedure in the opposite direction.			No visible damage $\Delta V/V_{1mA}$ $\leq 5\%$
	Terminal diameter (mm)		Force (kg)	
	0.5<d $\leq$ 0.8		0.5	
	0.8<d $\leq$ 1.25		1.0	
	1.25<d		2.0	
Solderability IEC 60068-2-20	245 $\pm$ 3 $^\circ\text{C}$, 3 $\pm$ 0.3 sec			$\geq 95\%$
Resistance to Soldering Heat IEC 60068-2-20	260 $\pm$ 3 $^\circ\text{C}$, 10 $\pm$ 1 sec			$\Delta R/R$ $\leq 5\%$



Resistance–Temperature Characteristic Curves




Resistance–Temperature Characteristic Curves





Resistance–Temperature Characteristic Curves





Resistance–Temperature Characteristic Curves





V-I Characteristic Curves



V-I Characteristic Curves




V-I Characteristic Curves



Soldering Recommendation

Wave Soldering Recommendation









Recommendation Reworking Conditions with Soldering Iron


Item	Conditions
Temperature of Soldering Iron-tip	360°C (max.)
Soldering Time	3 seconds (max.)
Distance from Thermistor	2mm (min.)

Packaging

Taping

Tape & Box 		Tape & Reel 							
 Default Straight		 NTB(5Φ) only :V-type							
 O-type		 F-type							
Dimensions	W	W0	W1	W2	H0	H2	D0	t	l
(Unit: mm)	18.0 ±1.0	12.0 ±1.0	9.0 +0.5/-0	Max 3.0	16.0 ±1.0	20.0 ±2.0	4.0 ±0.2	0.6 ±0.1	Max 2
Disc Φ	P0	P1 (±0.7)	P2 (+1.3/-0)	P (+1.0)	H (±1.0)	B (Max)		SPQ P0: 12.7mm	
								Taping & Box	Taping & Reel
5(B)	12.7±0.3	3.85	6.35	12.7	0±2	32		1500pcs/Box	1500pcs/Box
8(D)	12.7±0.3	3.85	6.35	12.7	0±2	33		1500pcs/Box	1500pcs/Box
10(E)	12.7±0.3	3.85	6.35	25.4	0±2	36		500pcs/Box	600pcs/Box
13(G)	12.7±1.0	8.95	12.7	25.4	0±4	40		500pcs/Box	600pcs/Box
15(J)	12.7±1.0	8.95	12.7	25.4	0±4	42		500pcs/Box	600pcs/Box
20(L)	12.7±1.0	8.95	12.7	25.4	0±4	45		400pcs/Box	400pcs/Box

■ Bulk Packing

Bulk (Unit: mm)	Disc Φ	SPQ (pcs / Bag)	Quantity	
			(Bags / Box)	(pcs / Box)
	Φ5 (NTB)	700	2	1400
	Φ8 (NTD)	500	2	1000
	Φ10 (NTE)	500	2	1000
	Φ13 (NTG)	300	2	600
	Φ15 (NTJ)	125	4	500
	Φ20 (NTL)	75	4	300

Warehouse Storage Conditions

- Storage temperature: -10℃~+40℃.
- Relative humidity: ≤80%RH.
- Keep away from corrosive atmosphere and sunlight.
- Period of Storage: 1 year.

LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non-infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial, automotive, and/or COTS grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.