Radiation-Hardened Quad 2-Input AND Gate

with **cold sparing**

1 GENERAL DESCRIPTION

The **AP54RHC08** is a radiation-hardened by design **quad 2-Input AND gate** that is ideally suited for commerical space and other applications demanding radiation tolerance and high reliability. It is fabricated in a 180 nm CMOS process utilizing proprietary radiation-hardening techniques, delivering high resiliency to single-event effects (SEE) and to a total ionizing dose (TID) to **30 krad (Si) at 5V** and **70 krad (Si) at 3.3V**.

This device is a member of the Apogee Semiconductor AP54RHC logic family operating across a voltage supply range of **1.65 V to 5.5 V**.

Zero-power penalty™ cold sparing is supported, along with Class 1C ESD protection on all inputs and outputs. A proprietary output stage and robust power-on reset (POR) circuit allow the AP54RHC08 to be cold-spared in any redundant configuration with no static power loss on any pad of the device. The redundant output stage also features a high drive capability with low static power loss.

The AP54RHC08 also features a triple-redundant design throughout its entire circuitry, which allows it to be immune to single-event transients (SET) without requiring additional redundant devices.

This device provides four instances of the Boolean logical function **AND** ($Y = A \cdot B$).

Ordering information may be found in Table 9 on Page 13.

1.1 FEATURES

- **1.65 VDC to 5.5 VDC** operation
- Inputs tolerant up to 5.5 VDC at any V_{CC}
- Provides logic-level down translation to V_{CC}
- Extended operating temperature range (-55 °C to +125 °C)
- Proprietary **cold sparing capability** with **zero** static power penalty
- **Built-in triple redundancy** for enhanced reliability
- Internal power-on reset (POR) circuitry ensures reliable power up and power down responses during hot plug and cold sparing operations
- Class 1C ESD protection (1000 V HBM, 500 V CDM)
- TID resilience of **30 krad (Si)** assured at 5V and characterized to **70 krad (Si)** at 3.3V.
- SEL immune to LET of **75 MeV-cm^2/mg**
- Meets NASA's ASTM E595 outgassing specification
- Moisture sensitivity level : MSL 1

1.2 LOGIC DIAGRAM

The AP54RHC08 logic function is shown below:




Figure 1: AP54RHC08 Logic Diagram

COPYRIGHT 2026 APOGEE SEMICONDUCTOR INC.

Downloaded from Arrow.com.

CONTENTS

1 General Description **1**
1.1 Features . . . 1
1.2 Logic Diagram . . . 1
2 Acronyms and Abbreviations **2**
3 Logic Data **3**
3.1 Truth Table . . . 3
4 Pin Configuration **3**
5 Electrical Characteristics **4**
5.1 Absolute Maximum Ratings . . . 4
5.2 Recommended Operating Conditions . . . 5
5.3 Static Characteristics . . . 6
5.4 Dynamic Characteristics . . . 8
5.5 Radiation Resilience . . . 8
5.6 Characteristics Measurement Information . . . 8
6 Detailed Description **9**
7 Applications Information **10**
7.1 Use in Cold-Sparing Configuration . . . 10
7.2 Power Supply Recommendations . . . 10
7.3 Application Tips . . . 10
8 Packaging Information **11**
9 Ordering Information **13**
10 Revision History **15**
11 Legal **16**

LIST OF TABLES

1 Truth Table . . . 3
2 Device Pinout . . . 3
3 Absolute Maximum Ratings . . . 4
4 Recommended Operating Conditions . . . 5
5 Thermal Information . . . 5
6 DC Electrical Characteristics . . . 6
7 AC Electrical Characteristics . . . 8
8 Radiation Resilience Characteristics . . . 8
9 Ordering Information . . . 13

LIST OF FIGURES

1 AP54RHC08 Logic Diagram . . . 1
2 Device Pinout . . . 3
3 Icc vs. Temperature @0krad typ . . . 7
4 Icc vs. Temperature @30krad typ . . . 7
5 Load Circuit . . . 8
6 Propagation Delay . . . 8
7 Input Pin Structure . . . 9
8 Output Pin Structure . . . 9
9 Two-Path Cold-Sparing Configuration . . . 10
10 Package Mechanical Drawing (SnPb) . . . 11
11 Package Mechanical Drawing (NiPdAu) . . . 12
12 Part Number Decoder . . . 14

2 ACRONYMS AND ABBREVIATIONS

ESD	Electrostatic Discharge
POR	Power On Reset
RHA	Radiation Hardness Assurance
SEE	Single Event Effects
SEL	Single Event Latchup
SET	Single Event Transient
TID	Total Ionizing Dose
TMR	Triple Modular Redundancy
CDM	Charged-device Model
HBM	Human-body Model

COPYRIGHT 2026 APOGEE SEMICONDUCTOR INC.

Downloaded from Arrow.com.

3 LOGIC DATA

3.1 TRUTH TABLE

The AP54RHC08 truth table is found in Table 1. **H** indicates HIGH logic level and **L** indicates LOW logic level. Subscript **n** reflects one of the four gates in the device (1 to 4).

Table 1: AP54RHC08 Device Truth Table

Input		Output
A_n	B_n	Y_n
L	L	L
L	H	L
H	L	L
H	H	H

4 PIN CONFIGURATION




Figure 2: AP54RHC08 Device Pinout

Table 2: AP54RHC08 Device Pinout

PIN NAME(S)	PIN NUMBER(S)	DESCRIPTION
A1, B1 A2, B2 A3, B3 A4, B4	1, 2 4, 5 9, 10 12, 13	Logic Inputs
Y1 Y2 Y3 Y4	3 6 8 11	Logic Outputs
V_{CC}	14	Positive Voltage Supply
GND	7	Ground

Downloaded from Arrow.com.

5 ELECTRICAL CHARACTERISTICS

The sign convention for current follows JEDEC standards with negative values representing current sourced from the device and positive values representing current sunk into the device.

5.1 ABSOLUTE MAXIMUM RATINGS

Excursions beyond the values listed in Table 3 may cause permanent damage to the device. Proper function of the device cannot be guaranteed if these values are exceeded, and long-term device reliability may be affected. Functionality of the device at these values, or beyond those listed in Recommended Operating Conditions (Table 4) is not guaranteed.

All parameters are specified across the entire operating temperature range unless otherwise specified.

Table 3: Absolute Maximum Ratings

SYMBOL	PARAMETER		VALUE	UNITS
V_{CC}	Supply Voltage		-0.5 to +5.5	V
V_I	Input voltage range		-0.5 to +5.5	V
V_O	Output voltage range		-0.5 to +5.5	V
I_{IK} (V_I < 0)	Input clamp current		100	mA
I_O	Continuous output current (per pin)		100	mA
I_{CC}	Maximum supply current		100	mA
V_{ESD}	ESD Voltage	HBM	1000	V
		CDM	500	V
T_J	Operating junction temperature range		-55 to +150	°C
T_{STG}	Storage temperature range		-65 to +150	°C

COPYRIGHT 2026 APOGEE SEMICONDUCTOR INC.

Downloaded from Arrow.com.

5.2 RECOMMENDED OPERATING CONDITIONS

All recommended parameters below are specified across the entire operating temperature range unless otherwise specified.

Table 4: Recommended Operating Conditions

SYMBOL	PARAMETER		MIN	MAX	UNITS
V_{CC}	Supply voltage		1.65	5.5	V
V_I	Input voltage range		0	5.5	V
V_O	Output voltage range		0	V_{CC}	V
V_{IH}	HIGH-level input voltage	V_{CC} = 1.65 to 1.95 V	1.4	-	V
		V_{CC} = 2.3 to 2.7 V	1.9	-	
		V_{CC} = 3.0 to 3.6 V	2.5	-	
		V_{CC} = 4.5 to 5.5 V	3.8	-	
V_{IL}	LOW-level input voltage	V_{CC} = 1.65 to 1.95 V	-	0.4	V
		V_{CC} = 2.3 to 2.7 V	-	0.6	
		V_{CC} = 3.0 to 3.6 V	-	0.9	
		V_{CC} = 4.5 to 5.5 V	-	1.35	
I_{OH}	HIGH-level output current	V_{CC} = 1.65 to 1.95 V	-	-4	mA
		V_{CC} = 2.3 to 2.7 V	-	-8	
		V_{CC} = 3.0 to 3.6 V	-	-16	
		V_{CC} = 4.5 to 5.5 V	-	-24	
I_{OL}	LOW-level output current	V_{CC} = 1.65 to 1.95 V	-	4	mA
		V_{CC} = 2.3 to 2.7 V	-	8	
		V_{CC} = 3.0 to 3.6 V	-	16	
		V_{CC} = 4.5 to 5.5 V	-	24	
t_r, t_f	Input rise or fall time (10% - 90%)	V_{CC} = 1.65 to 1.95 V	-	1000	ns
		V_{CC} = 2.3 to 2.7 V	-	600	
		V_{CC} = 3.0 to 3.6 V	-	500	
		V_{CC} = 4.5 to 5.5 V	-	400	

Table 5: Thermal Information

SYMBOL	PARAMETER	MIN	TYP	MAX	UNITS
T_J	Operating junction temperature	-55	-	+125	°C
$R_{\theta JA}$	Junction to ambient thermal resistance	-	100	-	°C/W

COPYRIGHT 2026 APOGEE SEMICONDUCTOR INC.

Downloaded from Arrow.com.

5.3 STATIC CHARACTERISTICS

All parameters are specified across the entire operating temperature range unless otherwise specified.

Table 6: DC Electrical Characteristics

SYMBOL	PARAMETER	CONDITIONS	V_{CC}	MIN	TYP	MAX	UNITS
V_{OL}	LOW-Level Output Voltage	I_O = 100 µA	1.65 to 5.5 V	-	0.02	0.05	V
		I_O = 1 mA	1.65 to 5.5 V	-	0.05	0.15	V
		I_O = 4 mA	1.65 V	-	0.27	0.8	V
			2.3 V	-	0.3	0.6	V
			3.0 V	-	0.2	0.4	V
			4.5 V	-	0.2	0.4	V
		I_O = 8 mA	2.3 V	-	0.6	1.0	V
			3.0 V	-	0.4	0.8	V
			4.5 V	-	0.3	0.6	V
		I_O = 16 mA	3.0 V	-	1.0	1.4	V
			4.5 V	-	1.1	1.2	V
		I_O = 24 mA	4.5 V	-	1.1	1.5	V
V_{OH}	HIGH-Level Output Voltage	I_O = -100 µA	1.65 to 5.5 V	V_{CC} - 0.1	V_{CC} - 0.02	-	V
		I_O = -1 mA	1.65 to 5.5 V	V_{CC} - 0.15	V_{CC} - 0.08	-	V
		I_O = -4 mA	1.65 V	1	1.35	-	V
			2.3 V	1.8	2.0	-	V
			3.0 V	2.6	2.8	-	V
			4.5 V	4.2	4.4	-	V
		I_O = -8 mA	2.3 V	1.4	1.7	-	V
			3.0 V	2.2	2.5	-	V
			4.5 V	3.9	4.1	-	V
		I_O = -16 mA	3.0 V	1.5	2.0	-	V
			4.5 V	3.3	3.8	-	V
		I_O = -24 mA	4.5 V	3.0	3.5	-	V
I_{CC}	Quiescent supply current	V_I = V_{CC} or GND I_O = 0 mA	1.8 V	-	48	85	µA
			3.5 V	-	125	190	µA
			5.5 V	-	247	400	µA
		V_I = V_{CC} or GND I_O = 0 mA T_a = 25°C, Post TID	5.5 V	-	527	564	µA
I_I	Input current	V_I = V_{CC} or GND	1.65 to 5.5 V	-	-	±1	µA
I_{OFF}	Powerdown leakage current(1)	V_I = V_{CC} or GND	OFF(2)	-	-	5	µA

(1) into any input or output port
(2) V_{CC} is at GND potential

Downloaded from Arrow.com.




Figure 3: AP54RHC08 Typical I_{CC} vs. Temperature at 0krad TID(1)




Figure 4: AP54RHC08 Typical I_{CC} vs. Temperature at 30krad TID(1)

(1) based on simulations

Downloaded from Arrow.com.

5.4 DYNAMIC CHARACTERISTICS

All parameters are specified across the entire operating temperature range unless otherwise specified.

Table 7: AC Electrical Characteristics

SYMBOL	PARAMETER	CONDITIONS	V_{CC}	MIN	TYP	MAX	UNITS
t_{pd} [1]	Propagation Delay (Input A_n or B_n to output **Y**)	C_L = 50 pF	4.5 to 5.5 V	-	7.6	11	ns
			3.0 to 3.6 V	-	9	13	ns
			2.3 to 2.7 V	-	11	15	ns
			1.65 to 1.95 V	-	17	25	ns
C_{in}	Input Capacitance[2]	V_I = V_{CC} or GND	1.65 to 5.5 V	-	2	4	pF
C_{pd}	Power Dissipation Capacitance[2]	I_O = 0 mA, f = 1 MHz	5.5 V	-	40	-	pF

[1] equivalent to t_{PLH}, t_{PHL}
[2] guaranteed by design

5.5 RADIATION RESILIENCE

For detailed radiation testing reports, please contact Apogee Semiconductor at sales@apogeesemi.com.

Table 8: Radiation Resilience Characteristics

PARAMETER	CONDITIONS	VALUE	UNITS
Total Ionizing Dose (TID)	Please contact Apogee Semiconductor for test report.	30	krad (Si)
SEL Onset LET Threshold	Please contact Apogee Semiconductor for test report.	≥75	MeV-cm²/mg

5.6 CHARACTERISTICS MEASUREMENT INFORMATION




Figure 5: Load Circuit




Figure 6: Propagation Delay Measurement

Downloaded from Arrow.com.

6 DETAILED DESCRIPTION

The AP54RHC08 is a quad 2-Input AND gate intended to perform the Boolean function **AND** ($Y = A \cdot B$) in positive logic. Designed to operate from a wide supply voltage of 1.65 to 5.5 V, it has fully redundant input and output stages providing for superior resiliency to single event effects.

The output and input stages are constructed with transient-activated clamps (Figure 7, 8) that prevent inadvertent biasing of the V_{CC} power rail through parasitic diodes inherent to conventional input, output, and ESD circuits. The IC also incorporates an internal power-on reset (POR) circuit that prevents the output from driving erroneous results during power-on, and guarantees correct operation at power supply voltages as low as 1.65 V. While the supply is ramping, the POR holds the output buffers in tri-state, a feature that prevents unwanted DC current during cold sparing on input and output pins.

The AP54RHC family's I/O protection circuitry allows for cold sparing configurations as it avoids a leakage current penalty on inputs and outputs while in a power-down state. This can result in considerable power savings in systems where multiple-path redundancy is employed. The ESD clamp circuits for this logic family are designed to support Class 1C ESD levels of 1 kV HBM and 500 V CDM.




Figure 7: Input Pin Structure




Figure 8: Output Pin Structure

Downloaded from Arrow.com.

7 APPLICATIONS INFORMATION

7.1 USE IN COLD-SPARING CONFIGURATION

As the AP54RHC family is radiation-hardened by design and includes internal TMR, it can be utilized in high-reliablity applications without additional supporting circuitry or devices. Nonetheless, some application requirements call for fully-redundant designs, where an “A” and a “B” device are required, often on separate power rails.




Figure 9: Two-Path Cold-Sparing Configuration

With the cold sparing capability of the AP54RHC family, fully redundant “A” and “B” functions may be placed in parallel (as seen in Figure 9) running off redundant power supplies. The inputs and outputs on each one of these functions are assumed to be based on the AP54RHC family, allowing for direct parallel connection without unwanted leakage current paths during cold sparing. In the event of a failure in power supply A or within function A, the system can simply shut power supply A off and switch on power supply B, without requiring additional input or output switching or configuration changes.

7.2 POWER SUPPLY RECOMMENDATIONS

This device can operate at any voltage within the range specified in Table 4 Recommended Operating Conditions.

At a minimum, a 16 VDC (or higher), X7R-rated 0.1 µF ceramic decoupling capacitor should be placed near (within 1 cm) the V_{CC} pin of the device.


7.3 APPLICATION TIPS

Unused **inputs** must **not** be left floating. They may be connected to either a low (GND) or high (V_{CC}) bias to provide a known state at the input of the device. Resistors may be used to tie off unused inputs. In the event of a design change, such resistors can be removed, thereby allowing use of the inputs without having to cut traces on the PCB.

An unused **output** may be left floating. It is suggested that it be routed to a test point or similar accessible structure in case the gate needs to be utilized as part of a design revision.

Downloaded from Arrow.com.

8 PACKAGING INFORMATION




Notes:
1. All linear dimensions are in millimeters. Dimensioning and tolerancing are as per ISO/TS 128-71:2010
2. The part is compliant with JEDEC MO-153 specifications.

* Body width does **not** include interlead flash. Interlead flash shall not exceed 0.25 mm each side.
** Body length does **not** include mold flash, protrusion, or gate burrs. Mold flash, protrusions, and gate burrs shall not exceed 0.15 mm on each side.

Figure 10: 14-LT - Package Mechanical Drawing (SnPb)

Downloaded from Arrow.com.



Notes:
1. All linear dimensions are in millimeters. Dimensioning and tolerancing are as per ISO/TS 128-71:2010
2. The part is compliant with JEDEC MO-153 specifications.

* Body width does **not** include interlead flash. Interlead flash shall not exceed 0.25 mm each side.
** Body length does **not** include mold flash, protrusion, or gate burrs. Mold flash, protrusions, and gate burrs shall not exceed 0.15 mm on each side.

Figure 11: 14-NT - Package Mechanical Drawing (NiPdAu)

Downloaded from Arrow.com.

9 ORDERING INFORMATION

Example part numbers for the AP54RHC08 are listed in Table 9. The full list of options for this part can be found in Figure 12. For a detailed description of product grades, please refer to Product Grades and Quality Flows document. Please contact Apogee Semiconductor sales at sales@apogeesemi.com for further information on sampling, lead time and purchasing on specific part numbers.

Table 9: AP54RHC08 Ordering Information

DEVICE	DESCRIPTION	PACKAGE	LEAD FINISH	PACKAGE DIAGRAM	PACKAGE MASS
AP54RHC08ALT-R	Rad-Hard Quad 2-Input AND Gate (30 krad (Si))	TSSOP-14	SnPb	14-LT	58 mg
AP54RHC08ALT-J(1)	Rad-Hard Quad 2-Input AND Gate (30 krad (Si))	TSSOP-14	SnPb	14-LT	58 mg
AP54RHC08BLT-R	Rad-Hard Quad 2-Input AND Gate (30 krad (Si))	TSSOP-14	SnPb	14-LT	58 mg
AP54RHC08BLT-J(1)	Rad-Hard Quad 2-Input AND Gate (30 krad (Si))	TSSOP-14	SnPb	14-LT	58 mg
AP54RHC08CLT-R	Rad-Hard Quad 2-Input AND Gate (30 krad (Si))	TSSOP-14	SnPb	14-LT	58 mg
AP54RHC08CLT-J(1)	Rad-Hard Quad 2-Input AND Gate (30 krad (Si))	TSSOP-14	SnPb	14-LT	58 mg
AP54RHC08ELT-R	Rad-Hard Quad 2-Input AND Gate (for eval only)	TSSOP-14	SnPb	14-LT	58 mg
AP54RHC08ELT-J(1)	Rad-Hard Quad 2-Input AND Gate (for eval only)	TSSOP-14	SnPb	14-LT	58 mg
AP54RHC08ANT-R	Rad-Hard Quad 2-Input AND Gate (30 krad (Si))	TSSOP-14	NiPdAu	14-NT	58 mg
AP54RHC08ANT-J(1)	Rad-Hard Quad 2-Input AND Gate (30 krad (Si))	TSSOP-14	NiPdAu	14-NT	58 mg
AP54RHC08BNT-R	Rad-Hard Quad 2-Input AND Gate (30 krad (Si))	TSSOP-14	NiPdAu	14-NT	58 mg
AP54RHC08BNT-J(1)	Rad-Hard Quad 2-Input AND Gate (30 krad (Si))	TSSOP-14	NiPdAu	14-NT	58 mg
AP54RHC08CNT-R	Rad-Hard Quad 2-Input AND Gate (30 krad (Si))	TSSOP-14	NiPdAu	14-NT	58 mg
AP54RHC08CNT-J(1)	Rad-Hard Quad 2-Input AND Gate (30 krad (Si))	TSSOP-14	NiPdAu	14-NT	58 mg
AP54RHC08ENT-R	Rad-Hard Quad 2-Input AND Gate (for eval only)	TSSOP-14	NiPdAu	14-NT	58 mg
AP54RHC08ENT-J(1)	Rad-Hard Quad 2-Input AND Gate (for eval only)	TSSOP-14	NiPdAu	14-NT	58 mg

(1) Available through distributors only.

COPYRIGHT 2026 APOGEE SEMICONDUCTOR INC.

Downloaded from Arrow.com.




Figure 12: Part Number Decoder

1. RHA Designation
   - **P** 30 krad (Si)
   - **F** 300 krad (Si)
2. Part Number
   - **_** 08 (Quad 2-Input AND Gate)
3. Pedigree
   - **A** -55 to +125 °C (Burn-in)
   - **B** -55 to +125 °C (No burn-in)
   - **C** 25 °C (No burn-in)
   - **E** 25 °C Functional Test Only (Evaluation)
4. Lead Finish
   - **L** Tin-Lead (SnPb)
   - **N** Nickel-Palladium-Gold (NiPdAu)
5. Package
   - **T** 14-pin Thin Shrink Small Outline Package (TSSOP)
6. Packaging
   - **R** Tape and Reel[1]
   - **J** JEDEC Tray

[1] Contact us for custom reel quantities. Orders less than full reel quantities may be shipped as cut tape.

COPYRIGHT 2026 APOGEE SEMICONDUCTOR INC.

Downloaded from Arrow.com.

10 REVISION HISTORY

REVISION	DESCRIPTION	DATE
C00	Converted to new revision standard for Production datasheets indicated by C##. Updated V_{ESD} HBM value in Absolute Maximum Ratings (Table 3). Update Icc data to accommodate new wafer foundry and include post TID specifications in DC Electrical Characteristics (Table 6). Added figures 3 and 4 for I_{CC} in Static Characteristics. SEL onset threshold was corrected from $\geq$80 MeV-cm^2/mg to $\geq$75 MeV-cm^2/mg. Corrected package mass entries. Updated ordering information. Relaxed Vo Absolute Maximum Rating. Added MSL rating to Features bullets.	2026-02-18
A06	Added package mass. Updated ordering information.	2025-08-15
A05	Updated figures 5 and 6 in Characteristics Measurement Information. Add 4mA row for VCC=1.65 for VOH/VOL. Added NiPdAu lead finish option. Fixed typographical error in Table 8. Added outgassing feature bullet. Added package mass. Initial production release.	2025-01-14
A04	Correct output pin structure diagram	2021-12-06
A03	Revamped static and dynamic characteristics with new test data.	2021-03-01
A02	Update Static and Dynamic characteristics.	2020-08-07
A01	Initial public release.	2020-02-29
A00	Initial internal release.	2019-07-05

For the latest version of this document, please visit https://www.apogeesemi.com.

COPYRIGHT 2026 APOGEE SEMICONDUCTOR INC.

Downloaded from Arrow.com.

11 LEGAL

All product, product specifications and data are subject to change without notice.

Apogee Semiconductor provides technical data (such as datasheets), design resources (including reference designs), reliability data (including performance in radiation environments), application or other design advice, safety information, and other resources **"as is"** and with all faults, and disclaims all warranties, express and implied, including without limitation any implied warranties of merchantability, fitness for a particular purpose or non-infringement of third party intellectual property rights. These resources are intended for skilled engineers with understanding of high reliability and high radiation environments and its complexities.

Apogee Semiconductor is not responsible for: (1) selecting the suitable products for a given application, (2) designing, verifying, validating and testing it, or (3) ensuring that it meets any performance, safety, security, or other requirements. These resources are subject to change without advance notice. The use of these resources is restricted to the development of an application that uses the Apogee Semiconductor products described in them. Other reproduction and display of these resources is prohibited. No license is granted to any other Apogee Semiconductor intellectual property right or to any third-party intellectual property right.

Apogee Semiconductor disclaims responsibility and reserves the right to demand indemnification for any claims, damages, costs, losses, and liabilities arising out of wrongful use of these resources. The products are provided subject to Apogee Semiconductor's Terms of Sale (https://www.apogeesemi.com/terms) or other applicable terms provided in conjunction with applicable products. The provision of these resources does not expand or otherwise alter applicable warranties or warranty disclaimers for Apogee Semiconductor products.

Purchasers of these products acknowledge that they may be subject to and agree to abide by the United States laws and regulations controlling the export of technical data, computer software, electronic hardware and other commodities. The transfer of such items may require a license from the cognizant agency of the U.S. Government.

COPYRIGHT 2026 APOGEE SEMICONDUCTOR INC.

Downloaded from Arrow.com.