
Description

The API782X are high-performance dual-channel digital isolators with 5700V_{RMS} isolation ratings per UL 1577. This family insulation level can fulfill reinforce and basic isolation requirements, according to VDE, UL, CQC, etc. The data rate of API782X is up to 100Mbps. It provides digital channel direction configuration and the default output level. It can also operate under wide supply voltage of 2.5V to 5.5V.

The API782X provide strong electromagnetic immunity and low emissions at low power consumption. This family has a minimum of 150kV/μs common-mode transient immunity (CMTI). The API7820 device has both channels in the same direction while the API7821 device has both channels in the opposite direction. The default output is high for devices without suffix F and low for devices with suffix F. See *Device Functional Modes* section for further details.

Pin Assignments

SO-16WW (Type CJ)



Top View

Features

- 100Mbps Data Rate
- Supply Voltage: 2.5V to 5.5V
- ±150kV/μs Minimum CMTI
- CMOS Threshold Inputs
- Default Output High (API782X) and Low (API782XF) Options
- Low-Power Consumption, Typical 2.1mA per Channel at 1Mbps
- Low Propagation Delay: 11ns Typical
- Safety-Related Certifications:
  – 8000V_{PK} Isolation per DIN VDE 0884-17:2021-10
  – 5700V_{RMS} Isolation for 1 Minute per UL 1577
  – CQC Certification per GB 4943.1-2022
- Packaged in SO-16WW (Type CJ)
- Operation Temperature Range -40 to +125°C
- **Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**
- **For automotive applications requiring specific change control, (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/**

Applications

- Solar inverters
- Motor control
- Industrial automation
- Power in DATA center/telecom equipment
- Grid, electricity meters

Notes:
1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

© 2025 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Typical Applications Circuit

The API782X device can be used with MCU, CAN transceiver, bias power supply, and voltage regulator to create an isolated CAN interface. The following is an example circuit of API7821.




Figure 1. Typical Application Circuit of API782X

Pin Configuration and Descriptions




Figure 2. API782X Pin Configuration

Pin Name	Pin Number		Function
	API7820	API7821	
VCC1	1	1	Power supply, VCC1
INA	5	12	Input of Channel A
INB	6	6	Input of Channel B
GND1	2, 8	2, 8	Ground reference for VCC1 side
GND2	9, 15	9, 15	Ground reference for VCC2 side
OUTB	11	11	Output of Channel B
OUTA	12	5	Output of Channel A
VCC2	16	16	Power supply, VCC2
NC	3, 4, 7, 10, 13, 14	3, 4, 7, 10, 13, 14	Not connected

Table 1. Pin Description

© 2025 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Absolute Maximum Ratings (Note 4)

Symbol	Parameter	Rating	Unit
V_{CC1}, V_{CC2}	Supply Voltage	-0.5 to 6	V
V_{INA}, V_{INB}	Input Signal Voltage	-0.5 to V_{CC} +0.5 (Note 5)	V
V_{OUTA}, V_{OUTB}	Output Signal Voltage	-0.5 to V_{CC} +0.5 (Note 5)	V
I_O	Output Current	-15 to 15	mA
T_J	Operating Junction Temperature Range	-40 to +150	°C
T_{STG}	Storage Temperature Range	-65 to +150	°C
ESD	Human Body Model	8000	V
	Charged Device Model	1600	V
	Contact Discharge per IEC 61000-4-2; Isolation Barrier Withstand Test (Note 6)	8000	V

Notes: 4. Stresses greater than those listed under *Absolute Maximum Ratings* can cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under *Recommended Operating Conditions* is not implied. Exposure to *Absolute Maximum Ratings* for extended periods can affect device reliability.
5. Maximum voltage must not exceed 6V.
6. IEC ESD strike is applied across the barrier with all pins on each side tied together creating a two-terminal device.

Recommended Operating Conditions

Symbol	Parameter	Min	Typ	Max	Unit
V_{CC1}, V_{CC2}	Power-Supply Voltage	2.5	—	5.5	V
V_{IH}	High-Level Input Voltage	0.7 × V_{CCI}	—	V_{CCI}	V
V_{IL}	Low-Level Input Voltage	0	—	0.3 × V_{CCI}	V
DR	Data Rate	—	—	100	Mbps
T_A	Ambient Temperature	-40	—	+125	°C

© 2025 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Package Thermal Information

Symbol	Parameter	Value	Unit
$R_{\theta JA}$	Junction to Ambient Thermal Resistance	59.91	°C/W
$R_{\theta JC(top)}$	Junction to Case Thermal Resistance	25.68	°C/W
$R_{\theta JB}$	Junction-to-Board Thermal Resistance	31.44	°C/W
ψ_{JT}	Junction-to-Top Characterization Parameter	6.90	°C/W
ψ_{JB}	Junction-to-Board Characterization Parameter	30.37	°C/W
$R_{\theta JC(bot)}$	Junction-to-Case (Bottom) Thermal Resistance	35.05	°C/W

Power Ratings

Parameter		Test Conditions	Min	Typ	Max	Unit
API7820						
P_D	Maximum Power Dissipation (Both Sides)	V_{CC1} = V_{CC2} = 5.5V, T_J = +150°C, CL = 15pF, Input 50MHz 50% duty cycle square wave	—	—	154	mW
P_{D1}	Maximum Power Dissipation (Side-1)		—	—	27.5	mW
P_{D2}	Maximum Power Dissipation (Side-2)		—	—	126.5	mW
API7821						
P_D	Maximum Power Dissipation (Both Sides)	V_{CC1} = V_{CC2} = 5.5V, T_J = +150°C, CL = 15pF, Input 50MHz 50% duty cycle square wave	—	—	165	mW
P_{D1}	Maximum Power Dissipation (Side-1)		—	—	82.5	mW
P_{D2}	Maximum Power Dissipation (Side-2)		—	—	82.5	mW

© 2025 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Insulation Specifications

Symbol	Parameter	Condition	Value	Unit
CLR	External Clearance	Shortest terminal-to-terminal distance through air	15	mm
CPG	External Creepage	Shortest terminal-to-terminal distance across the package surface	15	mm
DTI	Distance Through the Insulation	Minimum internal gap (internal clearance)	26	µm
CTI	Comparative Tracking Index	DIN EN 60112 (VDE 0303-11); IEC 60112	> 600	V
—	Material Group	According to IEC 60664-1	I	—
—	For Rated Mains Voltage ≤ 150V_{RMS}	—	I to IV	—
—	For Rated Mains Voltage ≤ 300V_{RMS}	—	I to IV	—
—	For Rated Mains Voltage ≤ 600V_{RMS}	—	I to IV	—
—	For Rated Mains Voltage ≤ 1000V_{RMS}	—	I to III	—
DIN V VDE 0884-11 (VDE V 0884-11): 2017-01				
V_{IORM}	Maximum Repetitive Peak Isolation Voltage	AC voltage	2121	V_{PK}
V_{IOWM}	Maximum Working Isolation Voltage	AC voltage	1500	V_{RMS}
		DC voltage	2121	VDC
V_{IOTM}	Maximum Transient Isolation Voltage	VTEST = VIOTM, t = 60s (qualification) VTEST = 1.2 × VIOTM, t = 1s (100% production)	8000	V_{PK}
V_{IMP}	Maximum Impulse Voltage	Tested in air, 1.2/50µs waveform per IEC 62368-1	8000	V_{PK}
V_{IOSM}	Maximum Surge Isolation Voltage	V_{IOSM} ≥ 1.6 × V_{IMP}; Tested in oil (qualification test), 1.2/50µs waveform, per IEC 62368-1	12800	V_{PK}
Q_{pd}	Apparent Charge	Method a, After I/O safety test subgroup 2/3. Vini = VIOTM, tini = 60s; Vpd(m) = 1.2 × VIORM, tm = 10s	< 5	pC
		Method a, After environmental tests subgroup 1. Vini = VIOTM, tini = 60s; Vpd(m) = 1.6 × VIORM, tm = 10s	< 5	pC
		Method b1; At routine test (100% production) and preconditioning (type test) Vini = 1.2 × VIOTM; tini = 1s; Vpd(m) = 1.875 × VIORM, tm = 1s	< 5	pC
C_{IO}	Barrier Capacitance, Input to Output	VIO = 0.4 sin (2πft), f = 1MHz	~0.5	pF
R_{IO}	Isolation Resistance, Input to Output	VIO = 500V at T_A = +25°C	> 10^{12}	Ω
R_{IO}	Isolation Resistance, Input to Output	VIO = 500V at +100°C ≤ T_A ≤ +125°C	> 10^{11}	
R_{IO}	Isolation Resistance, Input to Output	VIO = 500V at T_S = +150°C	> 10^9	
Pollution Degree	—	—	2	—
Climatic Category	—	—	55/125/21	—
UL1577				
V_{ISO}	Withstand Isolation Voltage	VTEST = VISO, t = 60s (qualification), VTEST = 1.2 × VISO, t = 1s (100% production)	5700	V_{RMS}

© 2025 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Safety-Related Certifications

VDE	UL	CQC
DIN VDE 0884-17:2021-10	UL 1577	GB 4943.1-2022
Maximum transient isolation voltage, 8000V_{PK} Maximum repetitive peak isolation voltage, 2121V_{PK} Maximum surge isolation voltage, 12800V_{PK}	Single protection, 5700V_{RMS}	Reinforced insulation, Altitude ≤ 5000m, tropical climate, 700V_{RMS} maximum working voltage
Certification planned	File Number: E550819	Certification planned

Safety-Limiting Values

Symbol	Parameter	Condition	Value	Unit
I_S	Safety Supply Current	V_{CC} = 5.5V, T_J = +150°C, T_A = +25°C	379	mA
P_S	Safety Supply Power	T_J = +150°C, T_A = +25°C	2086	mW
T_S	Safety Temperature	—	+150	°C

© 2025 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Electrical Characteristics (V_{CC1} = V_{CC2}, T_A = -40°C to +125°C. Unless otherwise noted, typical values are at T_A = +25°C)

Symbol	Parameter	Condition	Min	Typ	Max	Unit
V_{CC} (UVLOP)	UVLO Threshold When Supply Voltage is Rising	—	—	2.2	—	V
V_{CC} (UVLON)	UVLO Threshold When Supply Voltage is Falling	—	—	2.1	—	V
V_{HYS} (UVLO)	Supply Voltage UVLO Hysteresis	—	—	100	—	mV
V_{OH}	High-Level Output Voltage	I_O <= 4mA	V_{CCO} - 0.4	——	—	V
V_{OL}	Low-Level Output Voltage	I_O <= 4mA	—	—	0.4	V
$V_{IT+(IN)}$	Rising Input Threshold Voltage	—	—	0.6 x V_{CCI}	0.7 x V_{CCI}	V
$V_{IT-(IN)}$	Falling Input Threshold Voltage	—	0.3 x V_{CCI}	0.4 x V_{CCI}	—	V
$V_{I(HYS)}$	Input Threshold Voltage Hysteresis	—	0.1 x V_{CCI}	0.2 x V_{CCI}	—	V
I_{IH}	High-Level Input Current	V_{IH} = V_{CCI} at INx	—	—	15	µA
I_{IL}	Low-Level Input Current	V_{IL} = 0 at INx	-15	—	—	µA
CMTI	Common-Mode Transient Immunity (Note 7)	V_I = V_{CCI} or 0, V_{CM} = 1200V	150	—	—	kV/µs

Note: 7. Parameter is not subject to production test - verified by design/characterization.

Supply Current Characteristics – 5V Supply (V_{CC1} = V_{CC2} = 5V ± 10%, T_A = -40°C to +125°C. Unless otherwise noted, Typical values are at T_A = +25°C.)

Symbol	Parameter	Condition	Min	Typ	Max	Unit
API7820, API7820F						
$I_{CC1(0)}$	Supply Current - DC Signal	V_I = V_{CCI} (API7820), V_I = 0 (API7820F)	—	0.80	1.19	mA
$I_{CC2(0)}$			—	1.80	2.88	
$I_{CC1(1)}$		V_I = 0 (API7820), V_I = V_{CCI} (API7820F)	—	3.15	4.55	
$I_{CC2(1)}$			—	1.84	2.85	
$I_{CC1(1M)}$	Supply Current - AC Signal	All channels switching with 1Mbps square wave clock input; CL = 15pF	—	1.96	2.76	
$I_{CC2(1M)}$			—	2.0	3.04	
$I_{CC1(10M)}$		All channels switching with 10Mbps square wave clock input; CL = 15pF	—	1.97	2.86	
$I_{CC2(10M)}$			—	3.49	4.5	
$I_{CC1(100M)}$		All channels switching with 100Mbps square wave clock input; CL = 15pF	—	2.26	4.00	
$I_{CC2(100M)}$			—	16.88	24.08	
API7821, API7821F						
$I_{CC1(0)}$, $I_{CC2(0)}$	Supply Current - DC Signal	V_I = V_{CCI} (API7821) V_I = 0 (API7821F)	—	1.48	1.91	mA
$I_{CC1(1)}$, $I_{CC2(1)}$		V_I = 0 (API7821) V_I = V_{CCI} (API7821F)	—	2.74	3.71	
$I_{CC1(1M)}$, $I_{CC2(1M)}$	Supply Current - AC Signal	All channels switching with 1Mbps square wave clock input; CL = 15pF	—	2.10	2.87	
$I_{CC1(10M)}$, $I_{CC2(10M)}$		All channels switching with 10Mbps square wave clock input; CL = 15pF	—	2.89	3.83	
$I_{CC1(100M)}$, $I_{CC2(100M)}$		All channels switching with 100Mbps square wave clock input; CL = 15pF	—	10.16	12.25	

© 2025 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Supply Current Characteristics – 3.3V Supply (V_{CC1} = V_{CC2} = 3.3V ± 10%, T_A = -40°C to +125°C. Unless otherwise noted, typical values are at T_A = +25°C)

Symbol	Parameter	Condition	Min	Typ	Max	Unit
API7820, API7820F						
$I_{CC1(0)}$	Supply Current - DC Signal	V_I = V_{CCI} (API7820), V_I = 0 (API7820F)	—	0.64	0.91	mA
$I_{CC2(0)}$			—	1.62	2.81	
$I_{CC1(1)}$		V_I = 0 (API7820), V_I = V_{CCI} (API7820F)	—	2.98	4.25	
$I_{CC2(1)}$			—	1.67	2.77	
$I_{CC1(1M)}$	Supply Current - AC Signal	All channels switching with 1Mbps square wave clock input; CL = 15pF	—	1.79	2.62	
$I_{CC2(1M)}$			—	1.75	2.92	
$I_{CC1(10M)}$		All channels switching with 10Mbps square wave clock input; CL = 15pF	—	1.80	2.66	
$I_{CC2(10M)}$			—	2.75	4.26	
$I_{CC1(100M)}$		All channels switching with 100Mbps square wave clock input; CL = 15pF	—	2.17	3.63	
$I_{CC2(100M)}$			—	12.88	16.53	
API7821, API7821F						
$I_{CC1(0)}$, $I_{CC2(0)}$	Supply Current - DC Signal	V_I = V_{CCI} (API7821) V_I = 0 (API7821F)	—	1.32	1.77	mA
$I_{CC1(1)}$, $I_{CC2(1)}$		V_I = 0 (API7821) V_I = V_{CCI} (API7821F)	—	2.56	3.57	
$I_{CC1(1M)}$, $I_{CC2(1M)}$	Supply Current - AC Signal	All channels switching with 1Mbps square wave clock input; CL = 15pF	—	1.95	2.68	
$I_{CC1(10M)}$, $I_{CC2(10M)}$		All channels switching with 10Mbps square wave clock input; CL = 15pF	—	2.47	3.33	
$I_{CC1(100M)}$, $I_{CC2(100M)}$		All channels switching with 100Mbps square wave clock input; CL = 15pF	—	6.77	9.67	

Supply Current Characteristics – 2.5V Supply (V_{CC1} = V_{CC2} = 2.5V ± 10%, T_A = -40°C to +125°C. Unless otherwise noted, typical values are at T_A = +25°C.)

Symbol	Parameter	Condition	Min	Typ	Max	Unit
API7820, API7820F						
$I_{CC1(0)}$	Supply Current - DC Signal	V_I = V_{CCI} (API7820), V_I = 0 (API7820F)	—	0.62	0.89	mA
$I_{CC2(0)}$			—	1.60	2.78	
$I_{CC1(1)}$		V_I = 0 (API7820), V_I = V_{CCI} (API7820F)	—	2.95	4.32	
$I_{CC2(1)}$			—	1.64	2.76	
$I_{CC1(1M)}$	Supply Current - AC Signal	All channels switching with 1Mbps square wave clock input; CL = 15pF	—	1.76	2.58	
$I_{CC2(1M)}$			—	1.70	2.87	
$I_{CC1(10M)}$		All channels switching with 10Mbps square wave clock input; CL = 15pF	—	1.78	2.62	
$I_{CC2(10M)}$			—	2.46	3.96	
$I_{CC1(100M)}$		All channels switching with 100Mbps square wave clock input; CL = 15pF	—	2.15	3.40	
$I_{CC2(100M)}$			—	10.42	13.53	
API7821, API7821F						
$I_{CC1(0)}$, $I_{CC2(0)}$	Supply Current - DC Signal	V_I = V_{CCI} (API7821), V_I = 0 (API7821F)	—	1.30	1.72	mA
$I_{CC1(1)}$, $I_{CC2(1)}$		V_I = 0 (API7821) V_I = V_{CCI} (API7821F)	—	2.54	3.53	
$I_{CC1(1M)}$, $I_{CC2(1M)}$	Supply Current - AC Signal	All channels switching with 1Mbps square wave clock input; CL = 15pF	—	1.97	2.68	
$I_{CC1(10M)}$, $I_{CC2(10M)}$		All channels switching with 10Mbps square wave clock input; CL = 15pF	—	2.36	3.79	
$I_{CC1(100M)}$, $I_{CC2(100M)}$		All channels switching with 100Mbps square wave clock input; CL = 15pF	—	5.73	8.03	

© 2025 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Switching Characteristics – 5V Supply (V_{CC1} = V_{CC2} = 5V ± 10%, T_A = -40°C to +125°C. Unless otherwise noted, typical values are at T_A = +25°C)

Symbol	Parameter	Condition	Min	Typ	Max	Unit
t_{PLH}, t_{PHL}	Propagation Delay Time	—	—	10	17	ns
PWD	Pulse Width Distortion $\|t_{PHL} - t_{PLH}\|$	—	—	0.5	5	ns
$t_{sk(o)}$	Channel-to-Channel Output Skew Time (Note 8)	Same direction channels	—	—	4	ns
$t_{sk(pp)}$	Part-to-Part Skew Time (Note 9)	—	—	—	5	ns
t_r	Output Signal Rise Time	—	—	—	5	ns
t_f	Output Signal Fall Time	—	—	—	5	ns
MPW	Minimum Pulse Width	—	—	—	10	ns
$t_{JIT(PK)}$	Peak Eye Diagram Jitter (Note 10)	—	—	350	—	ps

Switching Characteristics – 3.3V Supply (V_{CC1} = V_{CC2} = 3.3V ± 10%, T_A = -40°C to +125°C. Unless otherwise noted, typical values are at T_A = +25°C.)

Symbol	Parameter	Condition	Min	Typ	Max	Unit
t_{PLH}, t_{PHL}	Propagation Delay Time	—	—	10.5	18.5	ns
PWD	Pulse Width Distortion $\|t_{PHL} - t_{PLH}\|$	—	—	0.5	5	ns
$t_{sk(o)}$	Channel-to-Channel Output Skew Time (Note 8)	Same direction channels	—	—	4	ns
$t_{sk(pp)}$	Part-to-Part Skew Time (Note 9)	—	—	—	5	ns
t_r	Output Signal Rise Time	—	—	—	5	ns
t_f	Output Signal Fall Time	—	—	—	5	ns
MPW	Minimum Pulse Width	—	—	—	10	ns
$t_{JIT(PK)}$	Peak Eye Diagram Jitter (Note 10)	—	—	350	—	ps

Switching Characteristics – 2.5V Supply (V_{CC1} = V_{CC2} = 2.5V ± 10%, T_A = -40°C to +125°C. Unless otherwise noted, typical values are at T_A = +25°C.)

Symbol	Parameter	Condition	Min	Typ	Max	Unit
t_{PLH}, t_{PHL}	Propagation Delay Time	—	—	11	21	ns
PWD	Pulse Width Distortion $\|t_{PHL} - t_{PLH}\|$	—	—	0.5	5	ns
$t_{sk(o)}$	Channel-to-Channel Output Skew Time (Note 8)	Same direction channels	—	—	4	ns
$t_{sk(pp)}$	Part-to-Part Skew Time (Note 9)	—	—	—	5	ns
t_r	Output Signal Rise Time	—	—	—	5	ns
t_f	Output Signal Fall Time	—	—	—	5	ns
MPW	Minimum Pulse Width	—	—	—	10	ns
$t_{JIT(PK)}$	Peak Eye Diagram Jitter (Note 10)	—	—	350	—	ps

Notes:
8. $t_{sk(o)}$ is the skew between outputs of a single device with all inputs connected and outputs switching in the same direction with same loads.
9. $t_{sk(pp)}$ is the magnitude of the difference in propagation delay times between any terminals of different devices switching in the same direction while operating at identical supply voltages, temperature, input signals and loads.
10. Parameter is not subject to production test - verified by design/characterization.

© 2025 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Insulation Characteristics Curves




Figure 3. Thermal Derating Curve for Limiting Current






Figure 4. Thermal Derating Curve for Limiting Power

© 2025 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.


Typical Characteristics




T_A = +25°C CL = 15pF
Figure 5. API7820 Supply Current vs. Data Rate (With 15pF Load)



T_A = +25°C CL = No Load
Figure 6. API7820 Supply Current vs. Data Rate (With No Load)



T_A = +25°C CL = 15pF
Figure 7. API7821 Supply Current vs. Data Rate (With 15pF Load)



T_A = +25°C CL = No Load
Figure 8. API7821 Supply Current vs. Data Rate (With No Load)




Figure 9. High-Level Output Voltage vs. High-level Output Current




Figure 10. Low-Level Output Voltage vs. Low-Level Output Current

© 2025 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Typical Characteristics (continued)




Figure 11. Propagation Delay Time vs. Free-Air Temperature




Figure 12. Propagation Delay Time vs. Free-Air Temperature





Figure 13. Power-Supply Undervoltage Threshold vs. Free-Air Temperature


© 2025 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Parameter Measurement



A. The input pulse is supplied by a generator having the following characteristics: PRR ≤ 50kHz, 50% duty cycle, tr ≤ 3ns, tf ≤ 3ns, ZO = 50Ω. At the input, 50Ω resistor is required to terminate input generator signal. It is not needed in actual application.
B. CL = 15pF and includes instrumentation and fixture capacitance within ±20%.

Figure 14. Switching Characteristics Test Circuit and Voltage Waveforms



A. CL = 15pF and includes instrumentation and fixture capacitance within ±20%.

Figure 15. Common-Mode Transient Immunity Test Circuit

Operation Description

Overview

The API782X/API782XF family of devices is dual-channel isolator based on ON-OFF keying (OOK) modulation scheme to transfer digital data through capacitive isolation barrier. The different state of digital data was modulated with high frequency carrier at the transmitter side and demodulated at receiver side by advanced signal process technique, and the accomplished circuit technique were incorporated to enhance the CMTI performance and minimize the influence of radiated emissions.




Figure 16. API782X Internal Block Diagram

© 2025 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Operation Description (continued)

A concept of OOK modulation scheme works:




Figure 17. ON-OFF Keying (OOK) Modulation Scheme

Device Functional Modes:

Below table lists the functional modes for the API782X devices.

Input	V_{CCI} Status	V_{CCO} Status	Output	Comment
H	Ready	Ready	H	Normal operation.
L	Ready	Ready	L	
AO	Ready	Ready	Default	Default mode: When INx is open, the corresponding channel output goes to the default logic state. The default is high for API7820/21 and low for API7820F/21F.
X	Unready	Ready	Default	Default mode: When V_{CCI} is unpowered, a channel output assumes the logic state based on the selected default option. The default is high for API7820/21 and low for API7820F/21F. When V_{CCI} transitions from unpowered to powered-up, a channel output assumes the logic state of the input. When V_{CCI} transitions from powered-up to unpowered, a channel output assumes the selected default state.
X	X	Unready	Undetermined	When V_{CCO} is unpowered, a channel output is undetermined. When V_{CCO} transitions from unpowered to powered-up, a channel output assumes the logic state of the input.

Note: H = Logic High; L = Logic Low; O = Left Open; X = Irrelevant.


Table 2. API782X Function Table

© 2025 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.


Application and Implementation

Application Curve

The following typical eye diagrams of the API782X family of devices indicate low jitters and wide open eye at the maximum data rate of 100Mbps.



API7820 Eye Diagram at 100Mbps, 5V Supplies and +25°C




API7821 Eye Diagram at 100Mbps, 5V Supplies and +25°C

Figure 18. API7820/21 Eye Diagram

© 2025 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.


Ordering Information (Note 11)



Orderable Part Number	Marking ID	Package	Packing	
			Qty.	Carrier
API7820S16C-13	API7820	SO-16WW (Type CJ)	1000	13'' Tape and Reel
API7821S16C-13	API7821	SO-16WW (Type CJ)	1000	13'' Tape and Reel
API7820FS16C-13	API7820F	SO-16WW (Type CJ)	1000	13'' Tape and Reel
API7821FS16C-13	API7821F	SO-16WW (Type CJ)	1000	13'' Tape and Reel

Note: 11. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information




© 2025 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SO-16WW (Type CJ)




SO-16WW (Type CJ)			
Dim	**Min**	**Max**	**Typ**
A	--	2.650	--
A1	0.100	0.300	--
A2	2.236	2.336	--
b	0.310	0.510	--
c	0.220	0.280	--
D	10.200	10.400	--
E	17.100	17.400	--
E1	13.900	14.100	--
e	1.270 BSC		
L	0.600	1.100	--
L1	1.625 REF		
θ	0°	8°	--
All Dimensions in mm			

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SO-16WW (Type CJ)



Dimensions	Value (in mm)
C	1.270
G	6.800
G1	0.280
X	0.710
X1	9.600
Y	2.075
Y1	17.750

Mechanical Data

- Moisture Sensitivity: Level 3 per J-STD-020
- Terminals: Finish – Matte Tin Plated Leads, Solderable per JESD22-B102 e3
- Weight: 0.468 grams (Approximate)

© 2025 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.
All other trademarks are the property of their respective owners.
© 2025 Diodes Incorporated. All Rights Reserved.

www.diodes.com

© 2025 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.