AURIX™ TC38x variants

About this document

Scope and purpose

This document is an addendum to the TC38x Product Data Sheet and User's Manual, listing all planned product variants, key parameters such as memory size and optional features.

The User's Manual lists functions implemented on the Silicon, but this document counts functions that are pinning dependent; that is functions are counted that are connected to at least one package pin. As pins are overlaid with several functions the pinning needs to be checked (see Product Data Sheet) to determine the number of usable functions in an application.

Naming conventions

Prefix:

- SAK: $T_{ambient}$ Temperature Range from -40°C up to +125°C
- SAL: $T_{ambient}$ Temperature Range from -40°C up to +150°C (packaged device)

Feature Package:

- P: Standard feature
- E: Emulation device with all features of the emulated standard type, additionally full MCDS, overlay functionality for calibration, AGBT as trace interface for development (depending on the package)
- C,V,Z,M: Customer Specific
- A: ADAS ext. Memory
- T: ADAS + emulation
- X: Extended Feature device. These products contain the extended memory (EMEM) of the ADAS subsystem. The ADAS peripherals SPU and RIF are not available
- F: Extended Flash
- G: Additional Connectivity
- H: ADAS Standard feature
- N: Standard feature with AMU

Downloaded from Arrow.com.

Table of contents

About this document . . . 1

Table of contents . . . 2

1 TC38x AE step variants . . . 3

1.1 TC38x AE step (part 1) . . . 3

1.2 TC38x AE step (part 2) . . . 6

2 TC38x AD step variants . . . 9

2.1 TC38x AD step (part 1) . . . 9

2.2 TC38x AD step (part 2) . . . 12

3 Memory maps of TC38x variants . . . 15

Revision history . . . 17

Disclaimer . . . 18

Downloaded from Arrow.com.

1 TC38x AE step variants

The following tables list the TC38x AE step variants.

1.1 TC38x AE step (part 1)

A table listing the TC38x AE step variants.

Table 1 TC38x_AE step (part 1)

SAK-TC389QP-160F300S	SAK-TC387QP-160F300S	SAK-TC387TP-128F300S	SAK-TC387QN-160F300S	SAK-TC389QN-160F300S	SAL-TC389QP-160F300S	SAL-TC387QP-160F300S
Step						
AE	AE	AE	AE	AE	AE	AE
Production Status						
Standard	Standard	Customer Specific	Customer Specific	Customer Specific	Standard	Standard
Package Type						
PG-FBGA-516	PG-LFBGA-292	PG-LFBGA-292	PG-LFBGA-292	PG-FBGA-516	PG-FBGA-516	PG-LFBGA-292
Pinout						
LFBGA 0.8 mm	LFBGA 0.8 mm	LFBGA 0.8 mm	LFBGA 0.8 mm	LFBGA 0.8 mm	LFBGA 0.8 mm	LFBGA 0.8 mm
Reference Silicon						
TC38x	TC38x	TC38x	TC38x	TC38x	TC38x	TC38x
Temperature Range (Ambient)						
SAK	SAK	SAK	SAK	SAK	SAL	SAL
Chip ID ***Attention*: *The value of SCU_CHIPID in the UCODE field contains the default value 0 not the µCode version.***						
0x8C008984	0x8C008784	0xCB008784	0xAC008784	0xAC008984	0x8C008984	0x8C008784
Cores / Checker Cores						
4/2	4/2	3/2	4/2	4/2	4/2	4/2
Max. Freq. (MHz)						
300	300	300	300	300	300	300
Program Flash (MB)						
10	10	8	10	10	10	10
Data Flash0 (single-ended) (KB)						
512	512	512	512	512	512	512
Total SRAM (without EMEM and Cache) (KB)						
1376	1376	1152	1376	1376	1376	1376
EMEM Size (KB)						

(table continues...)

Downloaded from Arrow.com.

1 TC38x AE step variants

Table 1 (continued) TC38x_AE step (part 1)

SAK-TC389QP-160F300S	SAK-TC387QP-160F300S	SAK-TC387TP-128F300S	SAK-TC387QN-160F300S	SAK-TC389QN-160F300S	SAL-TC389QP-160F300S	SAL-TC387QP-160F300S
0	0	0	0	0	0	0
DSPR (KB)						
240 in CPU0&1; 96 other	240 in CPU0&1; 96 other	240 in CPU0&1; 96 other	240 in CPU0&1; 96 other	240 in CPU0&1; 96 other	240 in CPU0&1; 96 other	240 in CPU0&1; 96 other
DLMU (KB)						
64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU
PSPR (KB)						
64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU
LMU (KB)						
128	128	128	128	128	128	128
DAM (KB)						
64	64	64	64	64	64	64
AMU[1)]						
No	No	No	Yes	Yes	No	No
ADC (Primary Groups/Channels)						
8/64	5/40	5/40	5/40	8/64	8/64	5/40
ADC (Secondary Groups/Channels)						
4/60	4/60	4/60	4/60	4/60	4/60	4/60
ADC (Fast Compare Channels)						
4	4	4	4	4	4	4
ADC (EDSADC Channels)						
10	6	6	6	10	10	6
CAN (Modules/Nodes)						
3/3x4	3/3x4	3/3x4	3/3x4	3/3x4	3/3x4	3/3x4
FlexRay (Modules/Channels)						
2/2x2	2/2x2	2/2x2	2/2x2	2/2x2	2/2x2	2/2x2
HSSL Modules						
1	1	1	1	1	1	1
ASCLIN Modules / with ASC & LIN / with 3-wire SPI						
24/24/12	24/24/11	24/24/11	24/24/11	24/24/12	24/24/12	24/24/11

(table continues...)

1 AMU is abbreviated as ASC Modeling Unit. For Additional details about AMU, Contact an Infineon Representative

Downloaded from Arrow.com.

1 TC38x AE step variants

Table 1 (continued) TC38x_AE step (part 1)

SAK-TC389QP-160F300S	SAK-TC387QP-160F300S	SAK-TC387TP-128F300S	SAK-TC387QN-160F300S	SAK-TC389QN-160F300S	SAL-TC389QP-160F300S	SAL-TC387QP-160F300S
QSPI Modules / with LVDS						
5/2	5/2	5/2	5/2	5/2	5/2	5/2
SENT Channels						
25	20	20	20	25	25	20
MSC Modules						
3	2	2	2	3	3	2
PSI5 Channels						
4	4	4	4	4	4	4
PSI5-S Module						
Yes	Yes	Yes	Yes	Yes	Yes	Yes
SDMMC Module						
No	No	No	No	No	No	No
Max. Ethernet Availability: 1GBit/100Mbit/No						
1Gbit/s	1Gbit/s	1Gbit/s	1Gbit/s	1Gbit/s	1Gbit/s	1Gbit/s
MCDS Availability						
miniMCDS	miniMCDS	miniMCDS	miniMCDS	miniMCDS	miniMCDS	miniMCDS
ADAS Cluster Available						
No	No	No	No	No	No	No
CIF						
No	No	No	No	No	No	No
HSM Available						
Yes	Yes	Yes	Yes	Yes	Yes	Yes

Downloaded from Arrow.com.

1.2 TC38x AE step (part 2)

A continuation table listing the TC38x AE step variants.

Table 2 TC38x_AE step (part 2)

SAL-TC387TP-128F300S	SAK-TC387TP-160F300S	SAL-TC387TP-160F300S	SAK-TC387QM-160F300S	SAK-TC389QP-160F400S	SAK-TC387QP-160F400S
Step					
AE	AE	AE	AE	AE	AE
Production Status					
Customer Specific	Customer Specific	Customer Specific	Customer Specific	Standard	Standard
Package Type					
PG-LFBGA-292	PG-LFBGA-292	PG-LFBGA-292	PG-LFBGA-292	PG-FBGA-516	PG-LFBGA-292
Pinout					
LFBGA 0.8 mm	LFBGA 0.8 mm	LFBGA 0.8 mm	LFBGA 0.8 mm	LFBGA 0.8 mm	LFBGA 0.8 mm
Reference Silicon					
TC38x	TC38x	TC38x	TC38x	TC38x	TC38x
Temperature Range (Ambient)					
SAL	SAK	SAL	SAK	SAK	SAK
Chip ID ***Attention*: *The value of SCU_CHIPID in the UCODE field contains the default value 0 not the µCode version.***					
0xCB008784	0xFC008784	0xFC008784	0xDC008784	0x8C008984	0x8C008784
Cores / Checker Cores					
3/2	3/2	3/2	4/2	4/2	4/2
Max. Freq. (MHz)					
300	300	300	300	400	400
Program Flash (MB)					
8	10	10	10	10	10
Data Flash0 (single-ended) (KB)					
512	512	512	512	512	512
Total SRAM (without EMEM and Cache) (KB)					
1152	960	960	1376	1376	1376
EMEM Size (KB)					
0	0	0	0	0	0
DSPR (KB)					

(table continues...)

Downloaded from Arrow.com.

1 TC38x AE step variants

Table 2 (continued) TC38x_AE step (part 2)

SAL-TC387TP-128F300S	SAK-TC387TP-160F300S	SAL-TC387TP-160F300S	SAK-TC387QM-160F300S	SAK-TC389QP-160F400S	SAK-TC387QP-160F400S
240 in CPU0&1; 96 other	160 in CPU0; 128 in CPU1; 96 other	160 in CPU0; 128 in CPU1; 96 other	240 in CPU0&1; 96 other	240 in CPU0&1; 96 other	240 in CPU0&1; 96 other
DLMU (KB)					
64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU
PSPR (KB)					
64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU
LMU (KB)					
128	128	128	128	128	128
DAM (KB)					
64	64	64	64	64	64
AMU[2)]					
No	No	No	No	No	No
ADC (Primary Groups/Channels)					
5/40	5/40	5/40	5/40	8/64	5/40
ADC (Secondary Groups/Channels)					
4/60	4/60	4/60	4/60	4/60	4/60
ADC (Fast Compare Channels)					
4	4	4	4	4	4
ADC (EDSADC Channels)					
6	6	6	6	10	6
CAN (Modules/Nodes)					
3/3x4	3/3x4	3/3x4	3/3x4	3/3x4	3/3x4
FlexRay (Modules/Channels)					
2/2x2	2/2x2	2/2x2	2/2x2	2/2x2	2/2x2
HSSL Modules					
1	1	1	1	1	1
ASCLIN Modules / with ASC & LIN / with 3-wire SPI					
24/24/11	24/24/11	24/24/11	24/24/11	24/24/12	24/24/11
QSPI Modules / with LVDS					
5/2	5/2	5/2	5/2	5/2	5/2

(table continues...)

2 AMU is abbreviated as ASC Modeling Unit. For Additional details about AMU, Contact an Infineon Representative

Downloaded from Arrow.com.

1 TC38x AE step variants

Table 2 (continued) TC38x_AE step (part 2)

SAL-TC387TP-128F300S	SAK-TC387TP-160F300S	SAL-TC387TP-160F300S	SAK-TC387QM-160F300S	SAK-TC389QP-160F400S	SAK-TC387QP-160F400S
SENT Channels					
20	20	20	20	25	20
MSC Modules					
2	2	2	2	3	2
PSI5 Channels					
4	4	4	4	4	4
PSI5-S Module					
Yes	Yes	Yes	Yes	Yes	Yes
SDMMC Module					
No	No	No	No	No	No
Max. Ethernet Availability: 1GBit/100Mbit/No					
1Gbit/s	1Gbit/s	1Gbit/s	1Gbit/s	1Gbit/s	1Gbit/s
MCDS Availability					
miniMCDS	miniMCDS	miniMCDS	miniMCDS	miniMCDS	miniMCDS
ADAS Cluster Available					
No	No	No	No	No	No
CIF					
No	No	No	No	No	No
HSM Available					
Yes	Yes	Yes	Yes	Yes	Yes

Downloaded from Arrow.com.

2 TC38x AD step variants

The following tables list the TC38x AD step variants.

2.1 TC38x AD step (part 1)

A table listing the TC38x AD step variants.

Table 3 TC38x_AD step (part 1)

SAL-TC389QP-160 F300S	SAL-TC387QP-160 F300S	SAK-TC389QP-160 F300S	SAK-TC387QP-160 F300S	SAK-TC387TP-128 F300S	SAL-TC387TP-128 F300S	SAK-TC387TP-160 F300S
Step						
AD	AD	AD	AD	AD	AD	AD
Production Status						
Standard	Standard	Standard	Standard	Customer Specific	Customer Specific	Customer Specific
Package Type						
PG-FBGA-516	PG-LFBGA-292	PG-FBGA-516	PG-LFBGA-292	PG-LFBGA-292	PG-LFBGA-292	PG-LFBGA-292
Pinout						
LFBGA 0.8 mm	LFBGA 0.8 mm	LFBGA 0.8 mm	LFBGA 0.8 mm	LFBGA 0.8 mm	LFBGA 0.8 mm	LFBGA 0.8 mm
Reference Silicon						
TC38x	TC38x	TC38x	TC38x	TC38x	TC38x	TC38x
Temperature Range (Ambient)						
SAL	SAL	SAK	SAK	SAK	SAL	SAK
Chip ID						
Attention*: *The value of SCU_CHIPID in the UCODE field contains the default value 0 not the µCode version.						
0x8C008983	0x8C008783	0x8C008983	0x8C008783	0xCB008783	0xCB008783	0xFC008783
Cores / Checker Cores						
4/2	4/2	4/2	4/2	3/2	3/2	3/2
Max. Freq. (MHz)						
300	300	300	300	300	300	300
Program Flash (MB)						
10	10	10	10	8	8	10
Data Flash0 (single-ended) (KB)						
512	512	512	512	512	512	512
Total SRAM (without EMEM and Cache) (KB)						
1376	1376	1376	1376	1152	1152	960
EMEM Size (KB)						

(table continues...)

Downloaded from Arrow.com.

Table 3 (continued) TC38x_AD step (part 1)

SAL-TC389QP-160F300S	SAL-TC387QP-160F300S	SAK-TC389QP-160F300S	SAK-TC387QP-160F300S	SAK-TC387TP-128F300S	SAL-TC387TP-128F300S	SAK-TC387TP-160F300S
0	0	0	0	0	0	0
DSPR (KB)						
240 in CPU0&1; 96 other	240 in CPU0&1; 96 other	240 in CPU0&1; 96 other	240 in CPU0&1; 96 other	240 in CPU0&1; 96 other	240 in CPU0&1; 96 other	160 in CPU0; 128 in CPU1; 96 other
DLMU (KB)						
64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU
PSPR (KB)						
64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU	64 per CPU
LMU (KB)						
128	128	128	128	128	128	128
DAM (KB)						
64	64	64	64	64	64	64
AMU[3)]						
No	No	No	No	No	No	No
ADC (Primary Groups/Channels)						
8/64	5/40	8/64	5/40	5/40	5/40	5/40
ADC (Secondary Groups/Channels)						
4/60	4/60	4/60	4/60	4/60	4/60	4/60
ADC (Fast Compare Channels)						
4	4	4	4	4	4	4
ADC (EDSADC Channels)						
10	6	10	6	6	6	6
CAN (Modules/Nodes)						
3/3x4	3/3x4	3/3x4	3/3x4	3/3x4	3/3x4	3/3x4
FlexRay (Modules/Channels)						
2/2x2	2/2x2	2/2x2	2/2x2	2/2x2	2/2x2	2/2x2
HSSL Modules						
1	1	1	1	1	1	1
ASCLIN Modules / with ASC & LIN / with 3-wire SPI						
24/24/12	24/24/11	24/24/12	24/24/11	24/24/11	24/24/11	24/24/11

(table continues...)

[3] AMU is abbreviated as ASC Modeling Unit. For Additional details about AMU, Contact an Infineon Representative

Downloaded from Arrow.com.

Table 3 (continued) TC38x_AD step (part 1)

SAL-TC389QP-160F300S	SAL-TC387QP-160F300S	SAK-TC389QP-160F300S	SAK-TC387QP-160F300S	SAK-TC387TP-128F300S	SAL-TC387TP-128F300S	SAK-TC387TP-160F300S
QSPI Modules / with LVDS						
5/2	5/2	5/2	5/2	5/2	5/2	5/2
SENT Channels						
25	20	25	20	20	20	20
MSC Modules						
3	2	3	2	2	2	2
PSI5 Channels						
4	4	4	4	4	4	4
PSI5-S Module						
Yes	Yes	Yes	Yes	Yes	Yes	Yes
SDMMC Module						
No	No	No	No	No	No	No
Max. Ethernet Availability: 1GBit/100Mbit/No						
1Gbit/s	1Gbit/s	1Gbit/s	1Gbit/s	1Gbit/s	1Gbit/s	1Gbit/s
MCDS Availability						
miniMCDS	miniMCDS	miniMCDS	miniMCDS	miniMCDS	miniMCDS	miniMCDS
ADAS Cluster Available						
No	No	No	No	No	No	No
CIF						
No	No	No	No	No	No	No
HSM Available						
Yes	Yes	Yes	Yes	Yes	Yes	Yes

Downloaded from Arrow.com.

2.2 TC38x AD step (part 2)

A continuation table listing the TC38x AD step variants.

Table 4 TC38x_AD step (part 2)

	SAL-TC387TP-160F300S
Step	
	AD
Production Status	
	Customer Specific
Package Type	
	PG-LFBGA-292
Pinout	
	LFBGA 0.8 mm
Reference Silicon	
	TC38x
Temperature Range (Ambient)	
	SAL
Chip ID ***Attention:*** ***The value of SCU_CHIPID in the UCODE field contains the default value 0 not the µCode version.***	
	0xFC008783
Cores / Checker Cores	
	3/2
Max. Freq. (MHz)	
	300
Program Flash (MB)	
	10
Data Flash0 (single-ended) (KB)	
	512
Total SRAM (without EMEM and Cache) (KB)	
	960
EMEM Size (KB)	
	0
DSPR (KB)	
	160 in CPU0; 128 in CPU1; 96 other
DLMU (KB)	
	64 per CPU

(table continues...)

Downloaded from Arrow.com.

Table 4 (continued) TC38x_AD step (part 2)

	SAL-TC387TP-160F300S
PSPR (KB)	
	64 per CPU
LMU (KB)	
	128
DAM (KB)	
	64
AMU[4]	
	No
ADC (Primary Groups/Channels)	
	5/40
ADC (Secondary Groups/Channels)	
	4/60
ADC (Fast Compare Channels)	
	4
ADC (EDSADC Channels)	
	6
CAN (Modules/Nodes)	
	3/3x4
FlexRay (Modules/Channels)	
	2/2x2
HSSL Modules	
	1
ASCLIN Modules / with ASC & LIN / with 3-wire SPI	
	24/24/11
QSPI Modules / with LVDS	
	5/2
SENT Channels	
	20
MSC Modules	
	2
PSI5 Channels	
	4

(table continues...)

[4] AMU is abbreviated as ASC Modeling Unit. For Additional details about AMU, Contact an Infineon Representative

Downloaded from Arrow.com.

Table 4 (continued) TC38x_AD step (part 2)

	SAL-TC387TP-160F300S
PSI5-S Module	
	Yes
SDMMC Module	
	No
Max. Ethernet Availability: 1GBit/100Mbit/No	
	1Gbit/s
MCDS Availability	
	miniMCDS
ADAS Cluster Available	
	No
CIF	
	No
HSM Available	
	Yes

Downloaded from Arrow.com.

3 Memory maps of TC38x variants

This section shows the influence of above feature variants on the memory map.

Program Flash

Variants:

- 10 MB: umbrella (3 x 3 MB, 1 x 1 MB), see User's Manual
- 8 MB: following configurations are available. See Figure below.
  - 3 MB + 1 MB + 3 MB + 1 MB
  - 3 MB + 3 MB + 2 MB




Figure 1 TC38x PFlash variants

Cores/Checker cores

Variants:

- 4/2: umbrella, see User's Manual
- 3/2: not available is CPU3 including its RAMs (DSPR, DCACHE, DTAG, PSPR, PCACHE, PTAG, DLMU)

CPU RAMs

Variants:

- DSPR: 240 KB in CPU0 & CPU1, 96 KB in CPU2 & CPU3: umbrella, see User's Manual
- DSPR: 240 KB in CPU0 & CPU1, 96 KB in CPU2: default for 3/2 Cores/Checker Cores configuration (see Figure below for available DSPR address ranges)
- DSPR: 160 KB in CPU0, 128 KB in CPU1, 96 KB in CPU2: reduced RAM variant of 3/2 Cores/Checker Cores configuration (see Figure below for available DSPR address ranges)

Downloaded from Arrow.com.

3 Memory maps of TC38x variants




Figure 2 DSPR variants

ADC availability

- Limitation on availability of ADC channels are caused by pin limitations. See Data Sheet for the pinning table of the package

Downloaded from Arrow.com.

Revision history

Document version	Date of release	Description of changes
V1.0	2018-06-08	• First release
V1.1	2018-08-06	• Added row "Reference Silicon" (needed e.g. for TC37x) to refer user to User's Manual Appx
V1.2	2019-02-04	• Removed from "Memory Maps" the description for LMU and DAM variations as these are not varied • "Variant Tables": added SAL-TC387TP-128F300S
V1.3	2019-03-01	• "About this document": reduced list of described Feature Package to the used ones • "Memory Maps": added hint to understand ADC device specific differences • "Variant Tables": changed Production Status of several devices • "Variant Tables": clarified Total SRAM value is without cache memories
V1.4	2019-06-12	• Chapter 1: Added the TC38x AE step variants table • Chapter 1 and 2: TC38x Ax step variants table format changed to fit all the contents • Chapter 1 and 2:Added new row in the variant tables called "AMU" with the footnote for additional details • Chapter: About this document: Feature package definitions are updated to consistent with the product naming nomenclature definition
V1.5	2020-01-10	• Chapter 1,2: Total SRAM (without EMEM and Cache) size is corrected for SAK-TC387TP-160F300S and SAL-TC387TP-160F300S • Page 1: About the document:Feature Package 'X' definition is updated to remove CIF • Chapter 1 and 2:Added new row in the variant tables called "CIF" indicating the Camera Interface availability
V1.6	2020-11-18	• Chapter 1,2: Package type name for SAK-TC389QP-160F300S, SAK-TC389QN-160F300S, SAL-TC389QP-160F300S is corrected from PG-LFBGA-516 to PG-FBGA-516 • Chapter 1 and 2:Removed Bare Die Marking variant SAL-TC380QP-160F300
V1.7	2023-03-02	• Chapter 3 : Updated the Program flash variants memory figure
V1.8	2025-08-19	• Chapter 1 : Added new variant: SAK-TC387QM-160F300S
V1.9	2025-12-12	• Chapter 1 : Added new variants: SAK-TC389QP-160F400S, SAK-TC387QP-160F400S

Downloaded from Arrow.com.

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2025-12

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2026 Infineon Technologies AG

All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-ume1559051479610

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Downloaded from Arrow.com.