

# TVS Diode

Transient Voltage Suppressor Diodes

## ESD207-B1-02 Series

Ultra Low Clamping Bi-directional ESD / Transient / Surge Protection Diodes

ESD207-B1-02ELS  
ESD207-B1-02EL

## Data Sheet

Revision 1.3, 2013-12-19  
Final

Power Management & Multimarket

**Revision History: Revision 1.2, 2013-11-15**

| Page or Item | Subjects (major changes since previous revision) |
|--------------|--------------------------------------------------|
|--------------|--------------------------------------------------|

**Revision 1.3, 2013-12-19**

|   |                    |
|---|--------------------|
| 5 | Table 2-2) updated |
|   |                    |
|   |                    |
|   |                    |
|   |                    |
|   |                    |

**Trademarks of Infineon Technologies AG**

AURIX™, BlueMoon™, C166™, CanPAK™, CIPOS™, CIPURSE™, COMNEON™, EconoPACK™, CoolMOS™, CoolSET™, CORECONTROL™, CROSSAVE™, DAVE™, EasyPIM™, EconoBRIDGE™, EconoDUAL™, EconoPIM™, EiceDRIVER™, eupec™, FCOS™, HITFET™, HybridPACK™, I<sup>2</sup>RF™, ISOFACE™, IsoPACK™, MIPAK™, ModSTACK™, my-d™, NovalithIC™, OmniTune™, OptiMOS™, ORIGAT™, PRIMARION™, PrimePACK™, PrimeSTACK™, PRO-SIL™, PROFET™, RASIC™, ReverSave™, SatRIC™, SIEGET™, SINDRION™, SIPMOS™, SMARTi™, SmartLEWIS™, SOLID FLASH™, TEMPFET™, thinQ!™, TRENCHSTOP™, TriCore™, X-GOLD™, X-PMU™, XMM™, XPOSYS™.

**Other Trademarks**

Advance Design System™ (ADS) of Agilent Technologies, AMBA™, ARM™, MULTI-ICE™, KEIL™, PRIMECELL™, REALVIEW™, THUMB™, µVision™ of ARM Limited, UK. AUTOSAR™ is licensed by AUTOSAR development partnership. Bluetooth™ of Bluetooth SIG Inc. CAT-iq™ of DECT Forum. COLOSSUS™, FirstGPS™ of Trimble Navigation Ltd. EMV™ of EMVCo, LLC (Visa Holdings Inc.). EPCOS™ of Epcos AG. FLEXGO™ of Microsoft Corporation. FlexRay™ is licensed by FlexRay Consortium. HYPERTERMINAL™ of Hilgraeve Incorporated. IEC™ of Commission Electrotechnique Internationale. IrDA™ of Infrared Data Association Corporation. ISO™ of INTERNATIONAL ORGANIZATION FOR STANDARDIZATION. MATLAB™ of MathWorks, Inc. MAXIM™ of Maxim Integrated Products, Inc. MICROTEC™, NUCLEUS™ of Mentor Graphics Corporation. Mifare™ of NXP. MIPI™ of MIPI Alliance, Inc. MIPS™ of MIPS Technologies, Inc., USA. muRata™ of MURATA MANUFACTURING CO., MICROWAVE OFFICE™ (MWO) of Applied Wave Research Inc., OmniVision™ of OmniVision Technologies, Inc. Openwave™ Openwave Systems Inc. RED HAT™ Red Hat, Inc. RFMD™ RF Micro Devices, Inc. SIRIUS™ of Sirius Satellite Radio Inc. SOLARIS™ of Sun Microsystems, Inc. SPANSION™ of Spansion LLC Ltd. Symbian™ of Symbian Software Limited. TAIYO YUDEN™ of Taiyo Yuden Co. TEAKLITE™ of CEVA, Inc. TEKTRONIX™ of Tektronix Inc. TOKO™ of TOKO KABUSHIKI KAISHA TA. UNIX™ of X/Open Company Limited. VERILOG™, PALLADIUM™ of Cadence Design Systems, Inc. VLYNQ™ of Texas Instruments Incorporated. VXWORKS™, WIND RIVER™ of WIND RIVER SYSTEMS, INC. ZETEX™ of Diodes Zetex Limited.

Last Trademarks Update 2010-10-26

# 1 Ultra Low Clamping Bi-directional ESD / Transient / Surge Protection Diodes

## 1.1 Features

- ESD / transient / surge protection of one data /  $V_{bus}$  line exceeding standard:
  - IEC61000-4-2 (ESD):  $\pm 30$  kV (air / contact discharge)
  - IEC61000-4-4 (EFT):  $\pm 50$  A (5/50 ns)
  - IEC61000-4-5 (surge):  $\pm 8$  A (8/20  $\mu$ s)
- Bi-directional, symmetrical working voltage up to  $V_{RWM} = \pm 3.3$  V
- Medium capacitance:  $C_L = 14$  pF (typ.)
- Ultra low clamping voltage  $V_{CL} = 7$  V (typ.) @  $I_{PP} = 16$  A (TLP)
- Ultra low dynamic resistance  $R_{DYN} = 0.13 \Omega$  typ.
- Pb-free (RoHS compliant) and halogen free package



## 1.2 Application Examples

- Audio Line, Speaker, Headset, Microphone Protection
- Human Interface Devices (Keyboard, Touchpad, Buttons)

## 1.3 Product Description




Figure 1-1 Pin Configuration and Schematic Diagram

Table 1-1 Ordering Information

| Type            | Package   | Configuration          | Marking code |
|-----------------|-----------|------------------------|--------------|
| ESD207-B1-02ELS | TSSLP-2-3 | 1 line, bi-directional | <u>Y</u>     |
| ESD207-B1-02EL  | TSLP-2-19 | 1 line, bi-directional | A            |

## 2 Characteristics

**Table 2-1 Maximum Ratings** at  $T_A = 25\text{ °C}$ , unless otherwise specified<sup>1)</sup>

| Parameter                                                            | Symbol    | Values |      |      | Unit |
|----------------------------------------------------------------------|-----------|--------|------|------|------|
|                                                                      |           | Min.   | Typ. | Max. |      |
| ESD contact discharge <sup>2)</sup>                                  | $V_{ESD}$ | –      | –    | 30   | kV   |
| Peak pulse current ( $t_p = 8/20\text{ }\mu\text{s}$ ) <sup>3)</sup> | $I_{PP}$  | –      | –    | 8    | A    |
| Peak pulse power ( $t_p = 8/20\text{ }\mu\text{s}$ ) <sup>3)</sup>   | $P_{PK}$  | –      | –    | 65   | W    |
| Operating temperature range                                          | $T_{OP}$  | -40    | –    | 125  | °C   |
| Storage temperature                                                  | $T_{stg}$ | -65    | –    | 150  | °C   |


1) Device is electrically symmetrical

2)  $V_{ESD}$  according to IEC61000-4-2

3)  $I_{PP}$  according to IEC61000-4-5

**Attention: Stresses above the max. values listed here may cause permanent damage to the device. Exposure to absolute maximum rating conditions for extended periods may affect device reliability. Maximum ratings are absolute ratings; exceeding only one of these values may cause irreversible damage to the integrated circuit.**

### 2.1 Electrical Characteristics at $T_A = 25\text{ °C}$ , unless otherwise specified



**Figure 2-1 Definitions of electrical characteristics**

## Characteristics

**Table 2-2 DC Characteristics** at  $T_A = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified<sup>1)</sup>

| Parameter               | Symbol    | Values |      |      | Unit | Note / Test Condition |
|-------------------------|-----------|--------|------|------|------|-----------------------|
|                         |           | Min.   | Typ. | Max. |      |                       |
| Reverse working voltage | $V_{RWM}$ | –      | –    | 3.3  | V    |                       |
| Reverse current         | $I_R$     | –      | –    | 50   | nA   | $V_R = 3.3\text{ V}$  |
| Trigger voltage         | $V_{t1}$  | 3.65   | –    | –    | V    |                       |
| Holding voltage         | $V_h$     | 3.65   | 4.4  | –    | V    | $I_R = 10\text{ mA}$  |

1) Device is electrically symmetrical

**Table 2-3 AC Characteristics** at  $T_A = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified

| Parameter        | Symbol | Values |      |      | Unit | Note / Test Condition                   |
|------------------|--------|--------|------|------|------|-----------------------------------------|
|                  |        | Min.   | Typ. | Max. |      |                                         |
| Line capacitance | $C_L$  | –      | 14   | 20   | pF   | $V_R = 0\text{ V}$ , $f = 1\text{ MHz}$ |

**Table 2-4 ESD and Surge Characteristics** at  $T_A = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified

| Parameter                                   | Symbol           | Values |      |      | Unit | Note / Test Condition   |
|---------------------------------------------|------------------|--------|------|------|------|-------------------------|
|                                             |                  | Min.   | Typ. | Max. |      |                         |
| Clamping voltage <sup>1)</sup> Pin 1 to GND | V <sub>CL</sub>  | —      | 7    | —    | V    | I <sub>TLP</sub> = 16 A |
|                                             |                  | —      | 9    | —    |      | I <sub>TLP</sub> = 30 A |
| Clamping voltage <sup>1)</sup> GND to Pin 1 |                  | —      | 7.5  | —    |      | I <sub>TLP</sub> = 16 A |
|                                             |                  | —      | 9    | —    |      | I <sub>TLP</sub> = 30 A |
| Clamping voltage <sup>2)</sup>              |                  | —      | 4.5  | 5.8  |      | I <sub>PP</sub> = 1 A   |
|                                             |                  | —      | 6.8  | 8.1  |      | I <sub>PP</sub> = 8 A   |
| Dynamic resistance <sup>1)</sup>            | R <sub>DYN</sub> | —      | 0.13 | —    | Ω    |                         |

1) ANSI/ESD STM5.5.1 - Electrostatic Discharge Sensitive Testing using Transmission Line Pulse (TLP) Model. TLP conditions:  $Z_0 = 50\text{ }\Omega$ ,  $t_p = 100\text{ ns}$ ,  $t_r = 0.6\text{ ns}$ ,  $I_{TLP}$  and  $V_{TLP}$  averaging window:  $t_1 = 30\text{ ns}$  to  $t_2 = 60\text{ ns}$ , extraction of dynamic resistance using least squares fit of TLP characteristic between  $I_{TLP1} = 5\text{ A}$  and  $I_{TLP2} = 40\text{ A}$ . Please refer to Application Note AN210 [1]

2)  $I_{PP}$  according to IEC61000-4-5 ( $t_p = 8/20\text{ }\mu\text{s}$ )

## 2.2 Typical Characteristics at $T_A = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified




Figure 2-2 Reverse current:  $I_R = f(V_R)$




Figure 2-3 Reverse current:  $I_R = f(T_A)$ ,  $V_R = 3.3\text{ V}$





Figure 2-4 Line capacitance:  $C_L = f(V_R)$ ,  $f = 1\text{MHz}$



**Figure 2-5 Clamping voltage (TLP):  $I_{TLP} = f(V_{TLP})$  according ANSI/ESD STM5.5.1 - Electrostatic Discharge Sensitivity Testing using Transmission Line Pulse (TLP) Model. TLP conditions:  $Z_0 = 50 \Omega$ ,  $t_p = 100 \text{ ns}$ ,  $t_r = 0.6 \text{ ns}$ ,  $I_{TLP}$  and  $V_{TLP}$  averaging window:  $t_1 = \text{ns}$  to  $t_2 = 60 \text{ ns}$ , extraction of dynamic resistance using squares fit to TLP characteristics between  $I_{TLP1} = 5 \text{ A}$  and  $I_{TLP2} = 40 \text{ A}$ . Please refer to Application Note AN210 [1]**




Figure 2-6 Pulse current (IEC61000-4-5) versus clamping voltage:  $I_{PP} = f(V_{CL})$




Figure 2-7 IEC61000-4-2 :  $V_{CL} = f(t)$ , 8 kV positive pulse from pin 1 to pin 2




Figure 2-8 IEC61000-4-2 :  $V_{CL} = f(t)$ , 8 kV negative pulse from pin 1 to pin 2




Figure 2-9 IEC61000-4-2 :  $V_{CL} = f(t)$ , 15 kV positive pulse from pin 1 to pin 2




Figure 2-10 IEC61000-4-2 :  $V_{CL} = f(t)$ , 15 kV negative pulse from pin 1 to pin 2

### 3 Application Information






Figure 3-1 Single line, bi-directional ESD / Transient protection

## 4 Package Information


### 4.1 TSSLP-2-3




**Figure 4-1** TSSLP-2-3: Package overview (dimension in mm)



**Figure 4-2** TSSLP-2-3: Footprint (dimension in mm)




**Figure 4-3** TSSLP-2-3: Tape information (dimension in mm)




**Figure 4-4** TSSLP-2-3: Marking (example)


## 4.2 TSLP-2-19




**Figure 4-5 TSLP-2-19: Package outline(dimension in mm), proposal**



**Figure 4-6 TSLP-2-19: Footprint (dimension in mm), proposal**



**Figure 4-7 TSLP-2-19: Tape information (dimension in mm), proposal**



**Figure 4-8 TSLP-2-19: Marking (example)**

## References

- [1] Infineon AG - **Application Note AN210**: Effective ESD Protection design at System Level Using VF-TLP Characterization Methodology
- [2] Infineon AG - Recommendations for PCB Assembly of Infineon TSLP and TSSLP Packages

www.infineon.com

Published by Infineon Technologies AG