

MOSFET

TOLL



600V CoolMOS™ CFD7 Power Transistor

CoolMOS™ is a revolutionary technology for high voltage power MOSFETs, designed according to the superjunction (SJ) principle and pioneered by Infineon Technologies. The latest CoolMOS™ CFD7 is the successor to the CoolMOS™ CFD2 series and is an optimized platform tailored to target soft switching applications such as phase-shift full-bridge (ZVS) and LLC. Resulting from reduced gate charge (Q_g), best-in-class reverse recovery charge (Q_{rr}) and improved turn off behavior CoolMOS™ CFD7 offers highest efficiency in resonant topologies. As part of Infineon's fast body diode portfolio, this new product series blends all advantages of a fast switching technology together with superior hard commutation robustness, without sacrificing easy implementation in the design-in process.



*1: Internal body diode

Features

- Ultra-fast body diode
- Low gate charge
- Best-in-class reverse recovery charge (Q_{rr})
- Improved MOSFET reverse diode dv/dt and di_F/dt ruggedness
- Lowest FOM $R_{DS(on)}$*Q_g and $R_{DS(on)}$*E_{oss}
- Best-in-class $R_{DS(on)}$ in SMD and THD packages

Benefits

- Excellent hard commutation ruggedness
- Highest reliability for resonant topologies
- Highest efficiency with outstanding ease-of-use / performance tradeoff
- Enabling increased power density solutions

Potential applications

Suitable for Soft Switching topologies
Optimized for phase-shift full-bridge (ZVS), LLC Applications – Server, Telecom, EV Charging

Product validation

Fully qualified according to JEDEC for Industrial Applications

Please note: The source and sense source pins are not exchangeable. Their exchange might lead to malfunction. For paralleling 4pin MOSFET devices the placement of the gate resistor is generally recommended to be on the Driver Source instead of the Gate.

Table 1 Key performance parameters

Parameter	Value	Unit
V_{DS} @ $T_{j,max}$	650	V
$R_{DS(on),max}$	90	mΩ
$Q_{g,typ}$	42	nC
$I_{D,pulse}$	79	A
E_{oss} @ 400V	4.8	µJ
Body diode di_F/dt	1300	A/µs

Part number	Package	Marking	Related links
IPT60R090CFD7	PG-HSOF-8	60R090F7	see Appendix A

Downloaded from Arrow.com.

Table of contents

Description 1
Maximum ratings 3
Thermal characteristics 4
Electrical characteristics 5
Electrical characteristics diagrams 7
Test circuits 11
Package outlines 12
Appendix A 15
Revision history 16
Trademarks 17
Disclaimer 17

Downloaded from Arrow.com.

1 Maximum ratings

at T_j = 25°C, unless otherwise specified

Table 2 Maximum ratings

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Continuous drain current [1]	I_D	-	-	28	A	T_C=25°C
				18		T_C=100°C
Pulsed drain current [2]	$I_{D,pulse}$	-	-	79	A	T_C=25°C
Avalanche energy, single pulse	E_{AS}	-	-	93	mJ	I_D=4.8A; V_{DD}=50V; see table 10
Avalanche energy, repetitive	E_{AR}			0.47		
Avalanche current, single pulse	I_{AS}	-	-	4.8	A	-
MOSFET dv/dt ruggedness	dv/dt	-	-	120	V/ns	V_{DS}=0...400V
Gate source voltage (static)	V_{GS}	-20	-	20	V	static;
Gate source voltage (dynamic)	V_{GS}	-30	-	30	V	AC (f>1 Hz)
Power dissipation	P_{tot}	-	-	160	W	T_C=25°C
Storage temperature	T_{stg}	-55	-	150	°C	-
Operating junction temperature	T_j	-55		150	°C	
Mounting torque	-	-		n.a.	Ncm	
Continuous diode forward current [1]	I_S	-	-	28	A	T_C=25°C
Diode pulse current [2]	$I_{S,pulse}$			79		
Reverse diode dv/dt [3]	dv/dt	-	-	70	V/ns	V_{DS}=0...400V, I_{SD}≤21A, T_j=25°C see table 8
Maximum diode commutation speed	di_F/dt			1300	A/µs	
Insulation withstand voltage	V_{ISO}	-	-	n.a.	V	V_{rms}, T_C=25°C, t=1min

[1] Limited by $T_{j\,max}$.

[2] Pulse width t_p limited by $T_{j,max}$

[3] Identical low side and high side switch with identical R_G

Downloaded from Arrow.com.

2 Thermal characteristics

Table 3 Thermal characteristics

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case	R_{thJC}	-	-	0.78	°C/W	-
Thermal resistance, junction - ambient	R_{thJA}	-	-	62	°C/W	device on PCB, minimal footprint
Thermal resistance, junction - ambient for SMD version	R_{thJA}	-	35	45	°C/W	Device on 40mm*40mm*1.5mm epoxy PCB FR4 with 6cm² (one layer, 70µm thickness) copper area for drain connection and cooling. PCB is vertical without air stream cooling.
Soldering temperature, wave- & reflow soldering allowed	T_{sold}	-	-	260	°C	reflow MSL1

Downloaded from Arrow.com.

3 Electrical characteristics

at T_j=25°C, unless otherwise specified

Table 4 Static characteristics

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Drain-source breakdown voltage	$V_{(BR)DSS}$	600	-	-	V	V_{GS}=0V, I_D=1mA
Gate threshold voltage	$V_{(GS)th}$	3.5	4	4.5	V	V_{DS}=V_{GS}, I_D=0.47mA
Zero gate voltage drain current	I_{DSS}	-	-	1	µA	V_{DS}=600V, V_{GS}=0V, T_j=25°C
Zero gate voltage drain current [4]	I_{DSS}	-	10	39	µA	V_{DS}=600V, V_{GS}=0V, T_j=125°C
Gate-source leakage current	I_{GSS}	-	-	100	nA	V_{GS}=20V, V_{DS}=0V
Drain-source on-state resistance	$R_{DS(on)}$	-	0.074	0.09	Ω	V_{GS}=10V, I_D=9.3A, T_j=25°C
			0.167	-		V_{GS}=10V, I_D=9.3A, T_j=150°C
Gate resistance	R_G	-	8.2	-	Ω	f=1MHz, open drain

[4] Maximum specification is defined by calculated six sigma upper confidence bound

Table 5 Dynamic characteristics

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Input capacitance	C_{iss}	-	1747	-	pF	V_{GS}=0V, V_{DS}=400V, f=250kHz
Output capacitance	C_{oss}		33			
Effective output capacitance, energy related [5]	$C_{o(er)}$	-	60	-	pF	V_{GS}=0V, V_{DS}=0...400V
Effective output capacitance, time related [6]	$C_{o(tr)}$	-	612	-	pF	I_D=constant, V_{GS}=0V, V_{DS}=0...400V
Turn-on delay time	$t_{d(on)}$	-	24	-	ns	V_{DD}=400V, V_{GS}=10V, I_D=9.6A, R_G=5.3Ω; see table 9
Rise time	t_r		15			
Turn-off delay time	$t_{d(off)}$		88			
Fall time	t_f		5			

[5] $C_{o(er)}$ is a fixed capacitance that gives the same stored energy as C_{oss} while V_{DS} is rising from 0 to 400V

[6] $C_{o(tr)}$ is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to 400V

Downloaded from Arrow.com.

Table 6 Gate charge characteristics

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Gate to source charge	Q_{gs}	-	10	-	nC	V_{DD}=400V, I_D=9.6A, V_{GS}=0 to 10V
Gate to drain charge	Q_{gd}		15		nC	
Gate charge total	Q_g		42		nC	
Gate plateau voltage	$V_{plateau}$		5.7		V	


Table 7 Reverse diode characteristics

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Diode forward voltage	V_{SD}	-	1.0	-	V	V_{GS}=0V, I_F=9.3A, T_j=25°C
Reverse recovery time	t_{rr}	-	103	155	ns	V_R=400V, I_F=9.6A, di_F/dt=100A/µs; see table 8
Reverse recovery charge	Q_{rr}		0.45	0.90	µC	
Peak reverse recovery current	I_{rrm}		7.6	-	A	

Downloaded from Arrow.com.


4 Electrical characteristics diagrams

Diagram 1: Power dissipation




P_{tot}=f(T_C)

Diagram 2: Safe operating area




I_D=f(V_{DS}); T_C=25 °C; D=0; parameter: t_p

Diagram 3: Safe operating area



I_D=f(V_{DS}); T_C=80 °C; D=0; parameter: t_p


Diagram 4: Max. transient thermal impedance



Z_{thJC} =f(t_P); parameter: D=t_p/T


Downloaded from Arrow.com.

Diagram 5: Typ. output characteristics




$I_D=f(V_{DS})$; T_j=25 °C; parameter: V_{GS}

Diagram 6: Typ. output characteristics




$I_D=f(V_{DS})$; T_j=125 °C; parameter: V_{GS}

Diagram 7: Typ. drain-source on-state resistance



$R_{DS(on)}=f(I_D)$; T_j=125 °C; parameter: V_{GS}

Diagram 8: Drain-source on-state resistance



$R_{DS(on)}=f(T_j)$; I_D=9.3 A; V_{GS}=10 V

Downloaded from Arrow.com.






Diagram 9: Typ. transfer characteristics	Diagram 10: Typ. gate charge
	
I_D=f(V_{GS}); V_{DS}=20V; parameter: T_j	V_{GS}=f(Q_{gate}); I_D=9.6 A pulsed; parameter: V_{DD}

Diagram 11: Forward characteristics of reverse diode	Diagram 12: Avalanche energy
	
I_F=f(V_{SD}); parameter: T_j	E_{AS}=f(T_j); I_D=4.8 A; V_{DD}=50 V


Downloaded from Arrow.com.

Diagram 13: Drain-source breakdown voltage




$V_{BR(DSS)}$=f(T_j); I_D=1 mA

Diagram 14: Typ. capacitances



C=f(V_{DS}); V_{GS}=0 V; f=250 kHz

Diagram 15: Typ. Coss stored energy



E_{oss}=f(V_{DS})

Downloaded from Arrow.com.

5 Test circuits

Table 8 Diode characteristics



Test circuit for diode characteristics	Diode recovery waveform
	

Table 9 Switching times (ss)






Switching times test circuit for inductive load	Switching times waveform
	

Table 10 Unclamped inductive load (ss)

Unclamped inductive load test circuit	Unclamped inductive waveform
	

Downloaded from Arrow.com.

6 Package outlines



PACKAGE - GROUP NUMBER:	PG-HSOF-8-U02	
DIMENSIONS	MILLIMETERS	
	MIN.	MAX.
A	2.20	2.40
b	0.70	0.90
b1	9.70	9.90
b2	0.42	0.50
c	0.40	0.60
D	10.28	10.58
D1	3.30	
E	9.70	10.10
E1	7.50	
E2	8.50	
E3	9.46	
e	1.20 (BSC)	
H	11.48	11.88
H1	6.55	6.95
H2	7.15	
H3	3.59	
H4	3.26	
N	8	
K1	4.18	
L	1.40	1.80
L1	0.50	0.90
L2	0.50	0.70
L3	1.00	1.30
L4	2.62	2.81

1) PARTIALLY COVERED WITH MOLD FLASH

Figure 1 Outline PG-HSOF-8, dimensions in mm

Downloaded from Arrow.com.





Figure 2 Footprint drawing PG-HSOF-8, dimensions in mm

Downloaded from Arrow.com.



All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [ ]

Figure 3 Packaging variant PG-HSOF-8, dimensions in mm

Downloaded from Arrow.com.

7 Appendix A

Table 11 Related links

- IFX CoolMOS™ CFD7 Webpage
- IFX CoolMOS™ CFD7 application note
- IFX CoolMOS™ CFD7 simulation model
- IFX Design tools

Downloaded from Arrow.com.

Revision history

IPT60R090CFD7

Revision 2025-02-03, Rev. 2.4

Previous revisions

Revision	Date	Subjects (major changes since last revision)
2.0	2020-04-22	Release of final version
2.1	2020-06-23	Changed diode commutation speed current
2.2	2020-08-28	Changed trr,Qrr and Irrm value
2.3	2020-10-28	Changed diagram 2, 3, 7, 8, 9; Changed typical static and dynamic parameters
2.4	2025-02-03	Implementation of standardized Infineon Umbrella-Templates for package drawings. H1 Extension from 6.75 to 6.95 MAX

Downloaded from Arrow.com.

Trademarks
All referenced product or service names and trademarks are the property of their respective owners.

We Listen to Your Comments Any information within this document that you feel is wrong, unclear or missing at all? Your feedback will help us to continuously improve the quality of this document. Please send your proposal (including a reference to this document) to: **erratum@infineon.com**

Published by
Infineon Technologies AG
81726 München, Germany
© 2025 Infineon Technologies AG
All Rights Reserved.

Important notice
The products which may also include samples and may be comprised of hardware or software or both ("Product") are sold or provided and delivered by Infineon Technologies AG and its affiliates ("Infineon") subject to the terms and conditions of the frame supply contract or other written agreement(s) executed by a customer and Infineon or, in the absence of the foregoing, the applicable Sales Conditions of Infineon. General terms and conditions of a customer or deviations from applicable Sales Conditions of Infineon shall only be binding for Infineon if and to the extent Infineon has given its express written consent.

For the avoidance of doubt, Infineon disclaims all warranties of non-infringement of third-party rights and implied warranties such as warranties of fitness for a specific use/purpose or merchantability.

Infineon shall not be responsible for any information with respect to samples, the application or customer's specific use of any Product or for any examples or typical values given in this document.

The data contained in this document is exclusively intended for technically qualified and skilled customer representatives. It is the responsibility of the customer to evaluate the suitability of the Product for the intended application and the customer's specific use and to verify all relevant technical data contained in this document in the intended application and the customer's specific use. The customer is responsible for properly designing, programming, and testing the functionality and safety of the intended application, as well as complying with any legal requirements related to its use.

Unless otherwise explicitly approved by Infineon, Products may not be used in any application where a failure of the Product or any consequences of the use thereof can reasonably be expected to result in personal injury. However, the foregoing shall not prevent the customer from using any Product in such fields of use that Infineon has explicitly designed and sold it for, provided that the overall responsibility for the application lies with the customer.

If the Product includes security features:
Because no computing device can be absolutely secure, and despite security measures implemented in the Product, Infineon does not guarantee that the Product will be free from intrusion, data theft or loss, or other breaches ("Security Breaches"), and Infineon shall have no liability arising out of any Security Breaches.
If this document includes or references software:
The software is owned by Infineon under the intellectual property laws and treaties of the United States, Germany, and other countries worldwide. All rights reserved. Therefore, you may use the software only as provided in the software license agreement accompanying the software. If no software license agreement applies, Infineon hereby grants you a personal, non-exclusive, non-transferable license (without the right to sublicense) under its intellectual property rights in the software (a) for software provided in source code form, to modify and reproduce the software solely for use with Infineon hardware products, only internally within your organization, and (b) to distribute the software in binary code form externally to end users, solely for use on Infineon hardware products. Any other use, reproduction, modification, translation, or compilation of the software is prohibited.

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

Downloaded from Arrow.com.