



Pushing Performance



People | Power | Partnership

HARTING News 2013

Transforming customer wishes into concrete solutions



The HARTING Technology Group is skilled in the fields of electrical, electronic and optical connection, transmission and networking, as well as in manufacturing, mechatronics and software creation. The Group uses these skills to develop customized solutions and products such as connectors for energy and data transmission applications including, for example, mechanical engineering, rail technology, wind energy plants, factory automation and the telecommunications sector. In addition, HARTING also produces electro-magnetic components for the automobile industry and offers solutions in the field of Enclosures and Shop Systems. The HARTING Group currently comprises 36 subsidiary companies and worldwide distributors employing a total of approximately 3,500 staff.



HARTING Subsidiary company



HARTING Representatives



We aspire to top performance.

Connectors ensure functionality. As core elements of electrical and optical wiring, connection and infrastructure technologies, they are essential in enabling the modular construction of devices, machines and systems across a very wide range of industrial applications. Their reliability is a crucial factor guaranteeing smooth functioning in the manufacturing area, in telecommunications, applications in medical technology – in fact, connectors are at work in virtually every conceivable application area. Thanks to the consistent further development of our technologies, customers enjoy investment security and benefit from durable, long term functionality.

Always at hand, wherever our customers may be.

Increasing industrialization is creating growing markets characterized by widely diverging demands and requirements. The search for perfection, increasingly efficient processes and reliable technologies is a common factor in all sectors across the globe.

HARTING is providing these technologies – in Europe, America and Asia. The **HARTING** professionals at our international subsidiaries engage in close, partnership based interaction with our customers, right from the very early product development phases, in order to realize customer demands and requirements in the best possible manner.

Our people on location form the interface to the centrally coordinated development and production departments. In this way, our customers can rely on consistently high, superior product quality – worldwide.

Our claim: pushing performance.

HARTING provides more than optimally attuned components. In order to serve our customers with the best possible solutions, **HARTING** is able to contribute a great deal more and play a closely integrative role in the value creation process.

From ready assembled cables through to control racks or ready-to-go control desks: Our aim is to generate the maximum benefits for our customers – without compromise!

Quality creates reliability – and warrants trust.

The **HARTING** brand stands for superior quality and reliability – worldwide. The standards we set are the result of consistent, stringent quality management that is subject to regular certifications and audits.

EN ISO 9001, the EU Eco-Audit and ISO 14001:2004 are key elements here. We take a proactive stance to new requirements, which is why **HARTING** ranks among the first companies worldwide to have obtained the new IRIS quality certificate for rail vehicles.



HARTING technology creates added value for customers. Technologies by **HARTING** are at work worldwide. **HARTING's** presence stands for smoothly functioning systems, powered by intelligent connectors, smart infrastructure solutions and mature network systems. In the course of many years of close, trust-based cooperation with its customers, the **HARTING** Technology Group has advanced to one of the worldwide leading specialists for connector technology. Extending beyond the basic functionalities demanded, we offer individual customers specific and innovative solutions. These tailored solutions deliver sustained effects, provide investment security and enable customers to achieve strong added value.

Opting for HARTING opens up an innovative, complex world of concepts and ideas.

In order to develop connectivity and network solutions serving an exceptionally wide range of connector applications and task scopes in a professional and cost optimized manner, **HARTING** not only commands the full array of conventional tools and basic technologies. Over and beyond these capabilities, **HARTING** is constantly harnessing and refining its broad base of knowledge and experience to create new solutions that ensure continuity at the same time. In securing this know-how lead, **HARTING** draws on a wealth of sources from both in-house research and the world of applications alike.

Salient examples of these sources of innovative knowledge include microstructure technologies, 3D design and construction technology, as well as high temperature

or ultrahigh frequency applications that are finding use in telecommunications or automation networks, in the automotive industry, or in industrial sensor and actuator applications, RFID and wireless technologies, in addition to packaging and housing made of plastics, aluminum or stainless steel.

HARTING solutions extend across technology boundaries.

Drawing on the comprehensive resources of the group's technology pool, **HARTING** devises practical solutions for its customers. Whether this involves industrial networks for manufacturing automation, or hybrid interface solutions for wireless telecommunication infrastructures, 3D circuit carriers with microstructures, or cable assemblies for high-temperature applications in the automotive industry – **HARTING** technologies offer far more than components, and represent mature, comprehensive solutions attuned to individual customer requirements and wishes. The range covers ready-to-use cable configurations, completely assembled backplanes and board system carriers, as well as fully wired and tested control panels.


In order to ensure the future proof design of RF- and EMC-compatible interface solutions, the central **HARTING** laboratory (certified to EN 45001) provides simulation tools, as well as experimental, testing and diagnostics facilities all the way through to scanning electron microscopes. In the selection of materials and processes, lifecycle and environmental aspects play a key role, in addition to product and process capability considerations.



HARTING knowledge is practical know-how generating synergy effects.

HARTING commands decades of experience with regard to the applications conditions of connectors in telecommunications, computer and network technologies and medical technologies, as well as industrial automation technologies, such as the mechanical engineering and plant engineering areas, in addition to the power generation industry or the transportation sector. **HARTING** is highly conversant with the specific application areas in all of these technology fields.

The key focus is on applications in every solution approach. In this context, uncompromising, superior quality is our hallmark. Every new solution found will invariably flow back into the **HARTING** technology pool, thereby enriching our resources. And every new solution we go on to create will draw on this wealth of resources in order to optimize each and every individual solution. In this way, **HARTING** is synergy in action.



Contents

Page

Installation Technology

Han® High Temp Connector for high Temperatures.	11
Han® High Temp Size 6 B.	13
Han® High Temp Size 10 B.	15
Han® High Temp Size 16 B.	17
Han® High Temp Size 24 B.	19
 Han® 16 B Hood with M50 cable entry	 21
 Han® B bulkhead mounted housing, IP 67	 23
 Han® HMC Connectors for High Mating Cycles	 26
Han D® HMC / Han DD® HMC	27
Han E® HMC / Han® EEE HMC	37
Han-Modular®	47
Han® HMC Hoods/housings	63
Han® HMC Accessories.	70
 Han-Yellock® Outdoor	 72
 Han-Modular®	
Han-Modular® LC module.	75
Han-Modular® E screw module.	77
Han-Modular® Docking frame.	79
Han-Modular® Module clamp	82
 Han-Port® Frame.	 83
 Han® Q	
Han® Q High Density	86
Han® Q 3/0 Crimp.	89
Han® Q 4/0 Crimp.	91

Contents

Page

Han® HPR

Han® 3 HPR Cover **93**Han® 24 HPR EasyCon Carrier Frame **95**

Han® HC Individual

Han® HC Individual **97**Han® HC Individual Accessories **99**Han® HC Individual Contacts **101**Han® HC Individual Sets **102**Han® HC Individual Assembly and Construction **103**HARTING Hall-Effekt Current Sensors Eco Series **105**

Han® Tools

Crimp tool Han-Fast® Lock **108**Han-Modular® Removal tool **109**Han® Torque Tool Set for high current axial screw contacts **110**Han® Torque Tool Set for power contacts **111**Han® Torque Tool Set for HARTING screw contacts and fixing screws **112**Han® VDE Screw Driver Set **113****Automation IT**Ha-VIS Middleware **115**Ha-VIS RF-R200 Reader **117**Ha-VIS mCon 3000 Next Generation **120**Ha-VIS mCon 3000 Next Generation **122**Ha-VIS mCon 3080-A **125**Ha-VIS mCon 3102-AASFP **126**Ha-VIS Accessories - Memory Cards **127**Ha-VIS SFP Modules **128**

Contents

Page

Device Connectivity

DIN 41612 connectors

Technical characteristics for types 3Q and 3R	131
Male connectors of complementary type 3Q	132
Male connectors of complementary type 3R.	134
Shrouds for type F	136

harmik® series

Hoods for bellows male connectors	137
---	------------

harlink® series

Technical characteristics	138
Male and female connectors.	139

D-Sub series

Turned crimp contacts	140
Technical characteristics for D-Sub SMT with straight solder terminations	141
D-Sub SMT connectors with straight solder terminations	142
D-Sub SMT connectors with straight solder terminations and grounding pins	144

Cables

Flat cables for insulation displacement termination, types SEK and D-Sub.	146
Ha-VIS data bus cables	147
PRORFINET cables	150
Han® SFP fibre optic cables and accessories	152

Ha-VIS preLink®

preLink® Extender and terminal module	154
---	------------

HARTING RJ Industrial®

RJ45 jacks with transformer	155
---------------------------------------	------------

Contents

Page

Circular connectors

har-speed adapter M12 - RJ45 and Gender changer **156**

har-speed with slim design **157**

har-flexicon® series

Pitches 1.27 mm / 2.54 mm

PCB connectors female with IDC termination **158**

PCB terminal blocks with push-in-spring-cage termination . . . **160**

PCB connectors female with push-in-spring-cage termination **162**

PCB connectors male **164**

Pitches 3.50 mm / 3.81 mm

PCB terminal blocks with push-in-spring-cage termination . . . **166**

PCB terminal blocks with screw termination **168**

PCB connectors female with push-in-spring-cage termination **170**

PCB connectors female with screw termination **172**

PCB connectors male **174**

Pitches 5.00 mm / 5.08 mm

PCB terminal blocks with push-in-spring-cage termination . . . **176**

PCB terminal blocks with screw termination **178**

PCB connectors female with push-in-spring-cage termination **182**

PCB connectors female with screw termination **184**

PCB connectors male **186**

HARTING eCatalogue **188**

Addresses **189**

Description

Han® High Temp is a new product series that is based on our well-established Han® B and Han® E series. We used high-quality materials with wide temperature ranges to produce connectors that are uniquely suited for a wide variety of applications.

These connectors can withstand temperatures up to 200 °C – so they can be used directly in machines and facilities that would otherwise require cumbersome and complex constructions.

For our users, this delivers direct advantages:

- The electro-mechanical design process is optimized.
Machine parts which are exposed to high temperatures can be designed modularly.
- The work process is optimized
since lower wiring complexity results in reduced maintenance costs.
- The after-sales phase is optimized
because this more service-friendly approach results in less outages and down times.

Design overview

The basic structure of the Han® High Temp connector consists of a bulkhead mounted housing and a cable-side hood.

Hoods and housings:

The aluminium die-cast hoods and housings feature a highly compressed surface with excellent non-stick properties. It also has a special non-stick coating on the bulkhead-side seal which allows easy handling without significant sticking.

Inserts:

The Han® High Temp series features very rugged contact inserts, which are really the heart of any connector. The LCP injection-moulded insert delivers outstanding temperature resistance coupled with excellent mechanical stability.

Contacts:

Our new temperature resistant contacts, for either screw or crimp terminations, ensure reliable connections with minimal contact resistance even at extreme temperatures.



**Han® High Temp connectors
remain robust and reliable for their entire lifespan!**


Features

- Reliable also at extreme temperatures up to 200 °C
- All piece parts (contacts, insert material, hoods and housings, seals and grounding elements) are designed in a temperature resistant way
- Developed on the basis of the proven Han® E series for 6, 10, 16 or 24 contacts
- Electrical data for 16 A and 400 V

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5



① wire gauge: 2.5 mm²

Technical characteristics

Specifications	DIN EN 60 664-1 DIN EN 61 984
----------------	----------------------------------

Inserts

Number of contacts	6, 10, 16, 24 + PE
Electrical data acc. to EN 61 984	16 A 400 V 6 kV 3
Rated current	16 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	≥ 10 ¹⁰ Ω
Material	LCP
Limiting temperatures	-40 °C ... +200 °C
Flammability acc. to UL 94	V 0
Mechanical working life - mating cycles	≥ 500

Contacts

Material	copper alloy
Contact resistance	≤ 1 mΩ
Crimp termination - min.	0.5 mm²/ AWG 20
Crimp termination - max.	2.5 mm²/ AWG 14
Screw termination - min.	0.5 mm²/ AWG 20
Screw termination - max.	2.5 mm²/ AWG 14
Tightening-/Testing torque	0.5 Nm
Stripping length	7 mm



Hoods/housings


Material	aluminium die cast
Surface	unpainted
Locking element	stainless steel
Hoods/housings seal	FPM, red
Limiting temperatures	-40 °C ... +200 °C
Degree of protection acc. to DIN EN 60 528 for coupled connector	IP 65

Number of contacts

6 +










Available September 2013

Identification		Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Screw termination with wire protection		09 33 806 2601	09 33 806 2701	 1) Distance for contact max. 21 mm	a = 19.7 mm b = 34.7 mm c = 21.0 mm d = 37.0 mm
Crimp termination Crimp contacts order separately		09 33 806 2602	09 33 806 2702		
				 Contact arrangement view from termination side Panel cut out	

Identification		Wire gauge (mm ²)	Part number		Drawing	Dimensions in mm
			Male contact	Female contact		
Han® High Temp contacts						
		0.5	09 33 800 6121	09 33 800 6220		
		0.75	09 33 800 6114	09 33 800 6214		
		1.0	09 33 800 6105	09 33 800 6205		
		1.5	09 33 800 6104	09 33 800 6204		
		2.5	09 33 800 6102	09 33 800 6202		

Wire gauge		Identifica- tion	Stripping length
0.5 mm ²	AWG 20	no groove	7.5 mm
0.75 mm ²	AWG 18	1 groove*	7.5 mm
1.0 mm ²	AWG 18	1 groove	7.5 mm
1.5 mm ²	AWG 16	2 grooves	7.5 mm
2.5 mm ²	AWG 14	3 grooves	7.5 mm



* on the back crimp collar


Identification	Part number		Cable entry metric	Drawing	Dimensions in mm
	Low construction	High construction			
Hood side entry	19 62 806 1540		1 x 20	 	
Hood side entry		19 62 806 0546 19 62 806 0547	1 x 25 1 x 32	 	
Hood top entry	19 62 806 1440		1 x 20	 	
Hood top entry		19 62 806 0446 19 62 806 0447	1 x 25 1 x 32	 	
Identification	Part number		Cable entry metric	Drawing	Dimensions in mm
	Low construction	High construction			
Bulkhead mounted housing	09 62 806 0391			 Panel cut out	






Number of contacts

10 +

Available September 2013

Identification		Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Screw termination with wire protection		09 33 810 2601	09 33 810 2701		a = 19.7 mm b = 34.7 mm c = 21.0 mm d = 37.0 mm
				1) Distance for contact max. 21 mm	
Crimp termination Crimp contacts order separately		09 33 810 2602	09 33 810 2702		Contact arrangement view from termination side Panel cut out



Identification		Wire gauge (mm²)	Part number		Drawing	Dimensions in mm																								
			Male contact	Female contact																										
Han® High Temp contacts		0.5 0.75 1.0 1.5 2.5	09 33 800 6121 09 33 800 6114 09 33 800 6105 09 33 800 6104 09 33 800 6102	09 33 800 6220 09 33 800 6214 09 33 800 6205 09 33 800 6204 09 33 800 6202																										
					<table><tr><th colspan="2">Wire gauge</th><th>Identifica- tion</th><th>Stripping length</th></tr><tr><td>0.5 mm²</td><td>AWG 20</td><td>no groove</td><td>7.5 mm</td></tr><tr><td>0.75 mm²</td><td>AWG 18</td><td>1 groove*</td><td>7.5 mm</td></tr><tr><td>1.0 mm²</td><td>AWG 18</td><td>1 groove</td><td>7.5 mm</td></tr><tr><td>1.5 mm²</td><td>AWG 16</td><td>2 grooves</td><td>7.5 mm</td></tr><tr><td>2.5 mm²</td><td>AWG 14</td><td>3 grooves</td><td>7.5 mm</td></tr></table>	Wire gauge		Identifica- tion	Stripping length	0.5 mm²	AWG 20	no groove	7.5 mm	0.75 mm²	AWG 18	1 groove*	7.5 mm	1.0 mm²	AWG 18	1 groove	7.5 mm	1.5 mm²	AWG 16	2 grooves	7.5 mm	2.5 mm²	AWG 14	3 grooves	7.5 mm	
Wire gauge		Identifica- tion	Stripping length																											
0.5 mm²	AWG 20	no groove	7.5 mm																											
0.75 mm²	AWG 18	1 groove*	7.5 mm																											
1.0 mm²	AWG 18	1 groove	7.5 mm																											
1.5 mm²	AWG 16	2 grooves	7.5 mm																											
2.5 mm²	AWG 14	3 grooves	7.5 mm																											
					* on the back crimp collar																									


Identification	Part number		Cable entry metric	Drawing	Dimensions in mm
	Low construction	High construction			
Hood side entry	19 62 810 1520		1 x 20		
Hood side entry		19 62 810 0526 19 62 810 0527	1 x 25 1 x 32		
Hood top entry	19 62 810 1420 19 62 810 1421		1 x 20 1 x 25		
Hood top entry		19 62 810 0426 19 62 810 0427	1 x 25 1 x 32		
Identification	Part number		Cable entry metric	Drawing	Dimensions in mm
	Low construction	High construction			
Bulkhead mounted housing	09 62 810 0391				






Number of contacts

16 +

Available September 2013

Identification		Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Screw termination with wire protection		09 33 816 2601	09 33 816 2701	 a = 19.7 mm b = 34.7 mm c = 21.0 mm d = 37.0 mm 1) Distance for contact max. 21 mm	
					
Crimp termination Crimp contacts order separately		09 33 816 2602	09 33 816 2702	 Contact arrangement view from termination side Panel cut out	
					



Identification		Wire gauge (mm ²)	Part number		Drawing	Dimensions in mm																								
			Male contact	Female contact																										
Han® High Temp contacts					 Operating contact Identification																									
		0.5 0.75 1.0 1.5 2.5	09 33 800 6121 09 33 800 6114 09 33 800 6105 09 33 800 6104 09 33 800 6102	09 33 800 6220 09 33 800 6214 09 33 800 6205 09 33 800 6204 09 33 800 6202																										
					<table><tr><th colspan="2">Wire gauge</th><th>Identifica- tion</th><th>Stripping length</th></tr><tr><td>0.5 mm²</td><td>AWG 20</td><td>no groove</td><td>7.5 mm</td></tr><tr><td>0.75 mm²</td><td>AWG 18</td><td>1 groove*</td><td>7.5 mm</td></tr><tr><td>1.0 mm²</td><td>AWG 18</td><td>1 groove</td><td>7.5 mm</td></tr><tr><td>1.5 mm²</td><td>AWG 16</td><td>2 grooves</td><td>7.5 mm</td></tr><tr><td>2.5 mm²</td><td>AWG 14</td><td>3 grooves</td><td>7.5 mm</td></tr></table>	Wire gauge		Identifica- tion	Stripping length	0.5 mm ²	AWG 20	no groove	7.5 mm	0.75 mm ²	AWG 18	1 groove*	7.5 mm	1.0 mm ²	AWG 18	1 groove	7.5 mm	1.5 mm ²	AWG 16	2 grooves	7.5 mm	2.5 mm ²	AWG 14	3 grooves	7.5 mm	
Wire gauge		Identifica- tion	Stripping length																											
0.5 mm ²	AWG 20	no groove	7.5 mm																											
0.75 mm ²	AWG 18	1 groove*	7.5 mm																											
1.0 mm ²	AWG 18	1 groove	7.5 mm																											
1.5 mm ²	AWG 16	2 grooves	7.5 mm																											
2.5 mm ²	AWG 14	3 grooves	7.5 mm																											
					* on the back crimp collar																									


Identification	Part number		Cable entry metric	Drawing	Dimensions in mm
	Low construction	High construction			
Hood side entry	19 62 816 1521		1 x 20		
Hood side entry		19 62 816 0527	1 x 32		
Hood top entry	19 62 816 1421		1 x 25		
Hood top entry		19 62 816 0427	1 x 32		
Identification	Part number		Cable entry metric	Drawing	Dimensions in mm
	Low construction	High construction			
Bulkhead mounted housing	09 62 816 0391			 Panel cut out	






Number of contacts

24 +

Available September 2013

Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
Crimp termination with wire protection 	09 33 824 2601	09 33 824 2701	 1) Distance for contact max. 21 mm a = 19.7 mm b = 34.7 mm c = 21.0 mm d = 37.0 mm	
Screw termination Crimp contacts order separately 	09 33 824 2602	09 33 824 2702	 13 ● 1 14 ● 2 15 ● 3 16 ● 4 17 ● 5 18 ● 6 19 ● 7 20 ● 8 21 ● 9 22 ● 10 23 ● 11 24 ● 12 1 ● 13 2 ● 14 3 ● 15 4 ● 16 5 ● 17 6 ● 18 7 ● 19 8 ● 20 9 ● 21 10 ● 22 11 ● 23 12 ● 24 Panel cut out	

Identification		Wire gauge (mm ²)	Part number		Drawing	Dimensions in mm																								
			Male contact	Female contact																										
Han® High Temp contacts																														
		0.5	09 33 800 6121	09 33 800 6220																										
		0.75	09 33 800 6114	09 33 800 6214																										
		1.0	09 33 800 6105	09 33 800 6205																										
		1.5	09 33 800 6104	09 33 800 6204																										
		2.5	09 33 800 6102	09 33 800 6202																										
					<table><tr><th colspan="2">Wire gauge</th><th>Identifica- tion</th><th>Stripping length</th></tr><tr><td>0.5 mm²</td><td>AWG 20</td><td>no groove</td><td>7.5 mm</td></tr><tr><td>0.75 mm²</td><td>AWG 18</td><td>1 groove*</td><td>7.5 mm</td></tr><tr><td>1.0 mm²</td><td>AWG 18</td><td>1 groove</td><td>7.5 mm</td></tr><tr><td>1.5 mm²</td><td>AWG 16</td><td>2 grooves</td><td>7.5 mm</td></tr><tr><td>2.5 mm²</td><td>AWG 14</td><td>3 grooves</td><td>7.5 mm</td></tr></table>	Wire gauge		Identifica- tion	Stripping length	0.5 mm ²	AWG 20	no groove	7.5 mm	0.75 mm ²	AWG 18	1 groove*	7.5 mm	1.0 mm ²	AWG 18	1 groove	7.5 mm	1.5 mm ²	AWG 16	2 grooves	7.5 mm	2.5 mm ²	AWG 14	3 grooves	7.5 mm	
Wire gauge		Identifica- tion	Stripping length																											
0.5 mm ²	AWG 20	no groove	7.5 mm																											
0.75 mm ²	AWG 18	1 groove*	7.5 mm																											
1.0 mm ²	AWG 18	1 groove	7.5 mm																											
1.5 mm ²	AWG 16	2 grooves	7.5 mm																											
2.5 mm ²	AWG 14	3 grooves	7.5 mm																											
					* on the back crimp collar																									

Identification	Part number		Cable entry metric	Drawing	Dimensions in mm
	Low construction	High construction			
Hood side entry	19 62 824 1521		1 x 25		
Hood side entry		19 62 824 0527 19 62 824 0528	1 x 32 1 x 40		
Hood top entry	19 62 824 1422		1 x 32		
Hood top entry		19 62 824 0427	1 x 32		
Identification	Part number		Cable entry metric	Drawing	Dimensions in mm
	Low construction	High construction			
Bulkhead mounted housing	09 62 824 0391				

Features





- High construction
- Large cabling space
- Cable entry with optimised 30° angle
- Compatible to all standard hoods and housings

Technical characteristics

Material hood/housing	aluminium die cast
Colour	RAL 7037 (grey)
Surface	powder coated
Locking lever	Han-Easy Lock®
Material Locking lever	stainless steel
Seal hood/housing	NBR
Limiting temperatures	-40 °C ... +125 °C
Approval acc. to UL 50 in locked position	IP 65



Han® 16 B hood with M50 cable entry

Identification	Part-Number	M	Drawing	Dimensions in mm
Hood side entry M40 with 2 locking levers on the bulkhead mounted housing 	19 30 016 0523	40		
Hood side entry M50 with 2 locking levers on the bulkhead mounted housing 	19 30 016 0529	50		

Available Juli 2013



Features

- Compatible to all standard hoods/housings
- Approved lever locking system with Han-Easy Lock®
- Standard panel cut out
- Degree of protection IP 66 and IP 67
- No sliding off the seal due to the protective flange

Technical Characteristics

Han® Standard Hoods/Housings Metal hoods/housings for industrial applications


Material	aluminium die-cast
Colour	RAL 7037 (grey)
Surface	powder-coated
Locking element	Stainless steel
Lever type	Han-Easy Lock®
Hoods/Housings seal	NBR
Limiting temperatures	-40 °C ... +125 °C
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP 66 and IP 67

Identification	Part-Number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

Housings, bulkhead mounting 6 B




09 30 006 1301



Housings, bulkhead mounting 10 B




09 30 010 1301



Housings, bulkhead mounting 16 B




09 30 016 1301



Housings, bulkhead mounting 24 B



09 30 024 1301




Features

This series Han® HMC (**H**igh **M**ating **C**ycles) is a connector series specifically aiming at industrial applications for 10,000 mating cycles.

Benefits:

- High mechanical robustness
- Simple and easy understandable design
- Optimized concept for signal and power transmission
- Low mating and unmating forces
- High contact density

General Description



Technical characteristics

Hoods/Housings Han B® HMC

Material	aluminium die-cast
Surface	powder coated RAL 7037 (grey)
Locking element	Han-Easy Lock® HMC
Flammability acc. to UL 94	V 0
Hoods/Housings seal	NBR
Limiting temperatures	-40 °C ... +125 °C
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP 65

Selection of hoods housings see page 53

Specifications

DIN EN 175 301-801
DIN EN 60 664-1
DIN EN 61 984

Inserts

Number of contacts	40, 64 + PE
Electrical data acc. to EN 61 984	10 A 250 V 4 kV 3
Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Pollution degree 2 also – for wrap terminal only	10 A 230/400 V 4 kV 2 10 A 250 V 4 kV 2
Rated voltage acc. to UL/CSA	600 V
Insulation resistance	$\geq 10^{10} \Omega$
Material	polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life - mating cycles	$\geq 10,000$

Contacts Han D® HMC

Material	copper alloy
Surface	HMC gold plating
Contact resistance	$\leq 3 \text{ m}\Omega$
Crimp terminal - min	0.14 mm² / AWG 26
Crimp terminal - max	2.5 mm² / AWG 14



Features

- High density contacts / connector
- For requirements up to 250 V / 10 A
- Time saving rapid termination by use of crimping contacts
- Suitable for hoods/housings of series Han® B HMC
- Han D® HMC contacts available with special HMC gold plating for 10,000 mating cycles


Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5



① 0.75 mm²
② 1.5 mm²

Identification	Wire gauge (mm²)	Male contact	Female contact	Drawing	Dimensions in mm																												
Crimp contacts HMC gold plated	0.14-0.37	09 15 200 6124	09 15 200 6224		<table><tr><th colspan="2">Wire gauge</th><th>D</th><th>Stripping length</th></tr><tr><td>0.14-0.37 mm²</td><td>AWG 26-22</td><td>0.9 mm</td><td>8 mm</td></tr><tr><td>0.5 mm²</td><td>AWG 20</td><td>1.1 mm</td><td>8 mm</td></tr><tr><td>0.75 mm²</td><td>AWG 18</td><td>1.3 mm</td><td>8 mm</td></tr><tr><td>1 mm²</td><td>AWG 18</td><td>1.45 mm</td><td>8 mm</td></tr><tr><td>1.5 mm²</td><td>AWG 16</td><td>1.75 mm</td><td>8 mm</td></tr><tr><td>2.5 mm²</td><td>AWG 14</td><td>2.25 mm</td><td>6 mm</td></tr></table>	Wire gauge		D	Stripping length	0.14-0.37 mm²	AWG 26-22	0.9 mm	8 mm	0.5 mm²	AWG 20	1.1 mm	8 mm	0.75 mm²	AWG 18	1.3 mm	8 mm	1 mm²	AWG 18	1.45 mm	8 mm	1.5 mm²	AWG 16	1.75 mm	8 mm	2.5 mm²	AWG 14	2.25 mm	6 mm
	Wire gauge		D			Stripping length																											
	0.14-0.37 mm²	AWG 26-22	0.9 mm			8 mm																											
	0.5 mm²	AWG 20	1.1 mm			8 mm																											
	0.75 mm²	AWG 18	1.3 mm			8 mm																											
	1 mm²	AWG 18	1.45 mm			8 mm																											
	1.5 mm²	AWG 16	1.75 mm			8 mm																											
2.5 mm²	AWG 14	2.25 mm	6 mm																														
0.5	09 15 200 6123	09 15 200 6223																															
0.75	09 15 200 6125	09 15 200 6225																															
1	09 15 200 6122	09 15 200 6222																															
1.5	09 15 200 6121	09 15 200 6221																															
2.5	09 15 200 6126	09 15 200 6226																															

Technical characteristics

Hoods/Housings Han® B HMC

Material	aluminium die-cast
Surface	powder coated RAL 7037 (grey)
Locking element	Han-Easy Lock® · HMC
Flammability acc. to UL 94	V 0
Hoods/Housings seal	NBR
Limiting temperatures	-40 °C / 125 °C
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP 65

Selection of hoods housings see page 53

Specifications

DIN EN 60 664-1
DIN EN 61 984

Inserts

Number of contacts	24, 42, 72, 108, + PE
Electrical data acc. to EN 61 984	10 A 250 V 4 kV 3
Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Pollution degree 2 also	10 A 230/400 V 4 kV 2
Rated voltage acc. to UL/CSA	600 V
Insulation resistance	$\geq 10^{10} \Omega$
Material	polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life - mating cycles	$\geq 10,000$

Contacts Han D® HMC

Material	copper alloy
Surface - hard-gold plated	HMC gold plated
Contact resistance	$\leq 3 \text{ m}\Omega$
Crimp terminal - min	0.14 mm ² / AWG 26
Crimp terminal - max	2.5 mm ² / AWG 14



Features

- High density of crimping contacts, up to 108 contacts/connector
- Time saving rapid termination by use of crimping contacts
- For requirements up to 250 V / 10 A
- Han D® HMC contacts available with special HMC gold plating for 10,000 mating cycles
- Suitable for hoods/housings of series Han® B HMC


Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5




- ① Han® 24 DD HMC
- ② Han® 42 DD HMC
- ③ Han® 72 DD HMC
- ④ Han® 108 DD HMC

Identification	Wire gauge (mm²)	Male contact	Female contact	Drawing	Dimensions in mm																												
Crimp contacts HMC gold plated	0.14-0.37	09 15 200 6124	09 15 200 6224		<table><tr><th colspan="2">Wire gauge</th><th>D</th><th>Stripping length</th></tr><tr><td>0.14-0.37 mm²</td><td>AWG 26-22</td><td>0.9 mm</td><td>8 mm</td></tr><tr><td>0.5 mm²</td><td>AWG 20</td><td>1.1 mm</td><td>8 mm</td></tr><tr><td>0.75 mm²</td><td>AWG 18</td><td>1.3 mm</td><td>8 mm</td></tr><tr><td>1 mm²</td><td>AWG 18</td><td>1.45 mm</td><td>8 mm</td></tr><tr><td>1.5 mm²</td><td>AWG 16</td><td>1.75 mm</td><td>8 mm</td></tr><tr><td>2.5 mm²</td><td>AWG 14</td><td>2.25 mm</td><td>6 mm</td></tr></table>	Wire gauge		D	Stripping length	0.14-0.37 mm²	AWG 26-22	0.9 mm	8 mm	0.5 mm²	AWG 20	1.1 mm	8 mm	0.75 mm²	AWG 18	1.3 mm	8 mm	1 mm²	AWG 18	1.45 mm	8 mm	1.5 mm²	AWG 16	1.75 mm	8 mm	2.5 mm²	AWG 14	2.25 mm	6 mm
	Wire gauge		D			Stripping length																											
	0.14-0.37 mm²	AWG 26-22	0.9 mm			8 mm																											
	0.5 mm²	AWG 20	1.1 mm			8 mm																											
	0.75 mm²	AWG 18	1.3 mm			8 mm																											
	1 mm²	AWG 18	1.45 mm			8 mm																											
	1.5 mm²	AWG 16	1.75 mm			8 mm																											
2.5 mm²	AWG 14	2.25 mm	6 mm																														
0.5	09 15 200 6123	09 15 200 6223																															
0.75	09 15 200 6125	09 15 200 6225																															
1	09 15 200 6122	09 15 200 6222																															
1.5	09 15 200 6121	09 15 200 6221																															
2.5	09 15 200 6126	09 15 200 6226																															




Number of contacts

24 +

Available May 2013




Inserts

Identification	Series	Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately (see Technical characteristics on page 19)  Only with Han Docking Frame (see page 61)	Han DD® HMC	09 16 224 3001	09 16 224 3101	 1) Distance for contact max. 21 mm Contact arrangement view from termination side  Panel cut out for inserts for use without hoods/housings 	
Coding pin 			09 33 000 9915	Coding pin  Use of the coding pin prevents incorrect mating to other connectors of the same type. The male pin should be omitted from the opposing cavity in the male insert.	




Number of contacts

42 + 

Available May 2013




Inserts

Identification	Series	Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately (see Technical characteristics on page 19) 	Han DD® HMC	09 16 242 3001	09 16 242 3101	 1) Distance for contact max. 21 mm Contact arrangement view from termination side  Panel cut out for inserts for use without hoods/housings 	
Coding pin 				Coding pin  Use of the coding pin prevents incorrect mating to other connectors of the same type. The male pin should be omitted from the opposing cavity in the male insert.	





Number of contacts

40 +

Available May 2013



Inserts

Identification	Series	Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately (see Technical characteristics on page 17) 	Han D® HMC	09 21 240 3001	09 21 240 3101	 1) Distance for contact max. 21 mm Contact arrangement view from termination side  Panel cut out for inserts for use without hoods/housings 	
Coding pin 				Coding pin  Use of the coding pin prevents incorrect mating to other connectors of the same type. The male pin should be omitted from the opposing cavity in the male insert.	

Number of contacts

72 +

Available May 2013



Inserts

Identification	Series	Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately (see Technical characteristics on page 19) 	Han DD® HMC	09 16 272 3001	09 16 272 3101	1) Distance for contact max. 21 mm Contact arrangement view from termination side Panel cut out for inserts for use without hoods/housings	
Coding pin 			09 33 000 9915	Coding pin Use of the coding pin prevents incorrect mating to other connectors of the same type. The male pin should be omitted from the opposing cavity in the male insert.	




Number of contacts

64 +

Available May 2013




Inserts

Identification	Series	Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately (see Technical characteristics on page 17) 	Han D® HMC	09 21 264 3001	09 21 264 3101	 1) Distance for contact max. 21 mm Contact arrangement view from termination side  Panel cut out for inserts for use without hoods/housings 	
Coding pin 				Coding pin  Use of the coding pin prevents incorrect mating to other connectors of the same type. The male pin should be omitted from the opposing cavity in the male insert.	

Number of contacts

108 +

Available May 2013



Inserts

Identification	Series	Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately (see Technical characteristics on page 19) 	Han DD® HMC	09 16 208 3001	09 16 208 3101	1) Distance for contact max. 21 mm Contact arrangement view from termination side Panel cut out for inserts for use without hoods/housings	
Coding pin 				Coding pin Use of the coding pin prevents incorrect mating to other connectors of the same type. The male pin should be omitted from the opposing cavity in the male insert.	

Technical characteristics

Hoods/Housings Han[®] B HMC

Material	aluminium die-cast
Surface	powder-coated
Locking element	Han-Easy Lock [®] HMC
Flammability acc. to UL 94	V 0
Hoods/Housings seal	NBR
Limiting temperatures	-40 °C ... +125 °C
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP 65

selection of hoods/housings see page 53

Specifications

DIN EN 60 664-1
DIN EN 61 984

Inserts

Number of contacts	6, 10, 16, 24, + PE
Electrical data acc. to EN 61 984	16 A 500 V 6 kV 3
Rated current	16 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Pollution degree 2 also	16 A 400/690 V 6 kV 2
Rated voltage acc. to UL/CSA	600 V
Insulation resistance	≥ 10 ¹⁰ Ω
Material	polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life - mating cycles	≥ 10,000

Contacts Han E[®] HMC

Material	copper alloy
Surface	HMC gold plated
Contact resistance	≤ 1 mΩ
Crimp terminal - min	0.14 mm ² / AWG 26
Crimp terminal - max	4 mm ² / AWG 12



Features

- Han E[®] HMC contacts with crimp termination
- Suitable for hoods/housings of series Han[®] B HMC
- Han E[®] HMC contacts available with special HMC gold plating for 10,000 mating cycles



Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5



- ① Han® 6 E HMC
- ② Han® 10 E HMC
- ③ Han® 16 E HMC
- ④ Han® 24 E HMC

Identification	Wire gauge (mm²)	Part number		Drawing	Dimensions in mm																																				
		Male contact	Female contact																																						
Crimp contacts HMC gold plated				Operating contact Identification 																																					
	0.14-0.37 0.5 0.75 1 1.5 2.5 4	09 33 200 6117 09 33 200 6122 09 33 200 6115 09 33 200 6118 09 33 200 6116 09 33 200 6123 09 33 200 6119	09 33 200 6217 09 33 200 6222 09 33 200 6215 09 33 200 6218 09 33 200 6216 09 33 200 6223 09 33 200 6221	<table><tr><th>Identification</th><th colspan="2">Wire gauge</th><th>Stripping length</th></tr><tr><td>no groove</td><td>0.14-0.37 mm²</td><td>AWG 26-22</td><td>7.5 mm</td></tr><tr><td>no groove</td><td>0.5 mm²</td><td>AWG 20</td><td>7.5 mm</td></tr><tr><td>1 groove*</td><td>0.75 mm²</td><td>AWG 18</td><td>7.5 mm</td></tr><tr><td>1 groove</td><td>1 mm²</td><td>AWG 18</td><td>7.5 mm</td></tr><tr><td>2 grooves</td><td>1.5 mm²</td><td>AWG 16</td><td>7.5 mm</td></tr><tr><td>3 grooves</td><td>2.5 mm²</td><td>AWG 14</td><td>7.5 mm</td></tr><tr><td>wide groove</td><td>3 mm²</td><td>AWG 12</td><td>7.5 mm</td></tr><tr><td>no groove</td><td>4 mm²</td><td>AWG 12</td><td>7.5 mm</td></tr></table> * on the back crimp collar	Identification	Wire gauge		Stripping length	no groove	0.14-0.37 mm²	AWG 26-22	7.5 mm	no groove	0.5 mm²	AWG 20	7.5 mm	1 groove*	0.75 mm²	AWG 18	7.5 mm	1 groove	1 mm²	AWG 18	7.5 mm	2 grooves	1.5 mm²	AWG 16	7.5 mm	3 grooves	2.5 mm²	AWG 14	7.5 mm	wide groove	3 mm²	AWG 12	7.5 mm	no groove	4 mm²	AWG 12	7.5 mm	
Identification	Wire gauge		Stripping length																																						
no groove	0.14-0.37 mm²	AWG 26-22	7.5 mm																																						
no groove	0.5 mm²	AWG 20	7.5 mm																																						
1 groove*	0.75 mm²	AWG 18	7.5 mm																																						
1 groove	1 mm²	AWG 18	7.5 mm																																						
2 grooves	1.5 mm²	AWG 16	7.5 mm																																						
3 grooves	2.5 mm²	AWG 14	7.5 mm																																						
wide groove	3 mm²	AWG 12	7.5 mm																																						
no groove	4 mm²	AWG 12	7.5 mm																																						
Coding pin for crimp inserts only			09 33 000 9954		Use of the coding pin prevents incorrect mating to other connectors of the same type. The male pin should be omitted from the opposing cavity in the male insert.																																				
																																									

Technical characteristics

Hoods/Housings Han® B HMC

Material	aluminium die-cast
Surface	powder-coated
Locking element	Han-Easy Lock® HMC
Flammability acc. to UL 94	V 0
Hoods/Housings seal	NBR
Limiting temperatures	-40 °C ... +125 °C
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP 65

Selection of hoods/housings see page 53

Specifications

DIN EN 60 664-1
DIN EN 61 984

Inserts

Number of contacts	40, 64 + PE
Electrical data acc. to EN 61 984	16 A 500 V 6 kV 3
Rated current	16 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	$\geq 10^{10} \Omega$
Material	polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life - mating cycles	$\geq 10,000$

Contacts Han® E HMC

Material	copper alloy
Surface	HMC gold plated
Contact resistance	$\leq 1 \text{ m}\Omega$
Crimp terminal - min	0.14 mm ² / AWG 26
Crimp terminal - max	4 mm ² / AWG 12


Features

- Han E® HMC contacts with crimp termination
- Polarised insert
- Suitable for hoods/housings of series Han® B HMC
- Han E® HMC contacts available with special HMC gold plating for 10,000 mating cycles



Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5




- ① Han® 64 EEE HMC / 1.5 mm²
- ② Han® 64 EEE HMC / 2.5 mm²
- ③ Han® 64 EEE HMC / 4.0 mm²
- ④ Han® 40 EEE HMC / 1.5 mm²
- ⑤ Han® 40 EEE HMC / 2.5 mm²

Identification	Wire gauge (mm²)	Male contact	Female contact	Drawing	Dimensions in mm																																				
Crimp contacts HMC gold plated																																									
	0.14-0.37 0.5 0.75 1 1.5 2.5 4	09 33 200 6117 09 33 200 6122 09 33 200 6115 09 33 200 6118 09 33 200 6116 09 33 200 6123 09 33 200 6119	09 33 200 6217 09 33 200 6222 09 33 200 6215 09 33 200 6218 09 33 200 6216 09 33 200 6223 09 33 200 6221	<table><tr><th>Identification</th><th colspan="2">Wire gauge</th><th>Stripping length</th></tr><tr><td>no groove</td><td>0.14-0.37 mm²</td><td>AWG 26-22</td><td>7.5 mm</td></tr><tr><td>no groove</td><td>0.5 mm²</td><td>AWG 20</td><td>7.5 mm</td></tr><tr><td>1 groove*</td><td>0.75 mm²</td><td>AWG 18</td><td>7.5 mm</td></tr><tr><td>1 groove</td><td>1 mm²</td><td>AWG 18</td><td>7.5 mm</td></tr><tr><td>2 grooves</td><td>1.5 mm²</td><td>AWG 16</td><td>7.5 mm</td></tr><tr><td>3 grooves</td><td>2.5 mm²</td><td>AWG 14</td><td>7.5 mm</td></tr><tr><td>wide groove</td><td>3 mm²</td><td>AWG 12</td><td>7.5 mm</td></tr><tr><td>no groove</td><td>4 mm²</td><td>AWG 12</td><td>7.5 mm</td></tr></table> * on the back crimp collar	Identification	Wire gauge		Stripping length	no groove	0.14-0.37 mm²	AWG 26-22	7.5 mm	no groove	0.5 mm²	AWG 20	7.5 mm	1 groove*	0.75 mm²	AWG 18	7.5 mm	1 groove	1 mm²	AWG 18	7.5 mm	2 grooves	1.5 mm²	AWG 16	7.5 mm	3 grooves	2.5 mm²	AWG 14	7.5 mm	wide groove	3 mm²	AWG 12	7.5 mm	no groove	4 mm²	AWG 12	7.5 mm	
Identification	Wire gauge		Stripping length																																						
no groove	0.14-0.37 mm²	AWG 26-22	7.5 mm																																						
no groove	0.5 mm²	AWG 20	7.5 mm																																						
1 groove*	0.75 mm²	AWG 18	7.5 mm																																						
1 groove	1 mm²	AWG 18	7.5 mm																																						
2 grooves	1.5 mm²	AWG 16	7.5 mm																																						
3 grooves	2.5 mm²	AWG 14	7.5 mm																																						
wide groove	3 mm²	AWG 12	7.5 mm																																						
no groove	4 mm²	AWG 12	7.5 mm																																						
Coding pin for crimp inserts only			09 33 000 9954		Use of the coding pin prevents incorrect mating to other connectors of the same type. The male pin should be omitted from the opposing cavity in the male insert.																																				
																																									

Number of contacts

16 +



Inserts

Identification	Series	Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		


Crimp terminal

Order crimp contacts separately (see Technical characteristics on page 27)

Han E®
HMC

09 33 216 2602


09 33 216 2702




1) Distance for contact max. 21 mm

	a	b	c	d
Han E® HMC	19	34	19	36

Contact arrangement
view from termination side



Panel cut out



Number of contacts

40
+




Inserts

Identification	Series	Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Crimp termination Order crimp contacts separately (see Technical characteristics on page 29)	Han® EEE HMC	09 32 240 3001	09 32 240 3101	1) Distance for contact max. 21 mm Contact arrangement view from termination side Panel cut out	

Number of contacts

64
+



Inserts


Identification	Series	Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Crimp termination Order crimp contacts separately (see Technical characteristics on page 29)					

Summary Han-Modular®



Series	Han E® module	Han® EE module	Han E® Protected module	Han® EEE module
Number of contacts	6	8	6	20
Modules	Crimp terminal	Crimp terminal	Crimp terminal	Crimp terminal
				
Rated current	16 A	16 A	16 A	16 A
Rated voltage	500 V	400 V	830 V	500 V
Wire gauge	0.14 ... 4 mm²	0.14 ... 4 mm²	0.14 ... 4 mm²	0.14 ... 4 mm²
Page	36	38	40	42

Series	Han DD® module	Han® DDD module		
Number of contacts	12	17		
Modules	Crimp terminal	Crimp terminal		
				
Rated current	10 A	10 A		
Rated voltage	250 V	160 V		
Wire gauge	0.14 ... 2.5 mm²	0.14 ... 2.5 mm²		
Page	44	46		



Features

- Blind mating connector system for drawer systems
- Direct panel mounting without housing
- Very robust design
- Solid pre-leading guid pins and float bushes
- Can be fixed with standard M4 screws
- Designed for 10,000 mating cycles

Notice:


Due the plastic material used in the docking frame without PE, the panel will need to be grounded separately







Technical characteristics

Specifications	DIN EN 60 664-1 DIN EN 61 984
----------------	----------------------------------


Docking frames






Number of modules	2, 4, 6
Material	
- Docking frames	polycarbonate
- Float washer	zinc die-cast
Floating tolerance	± 2 mm
Aligning tolerance	± 4 mm
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	
- mating cycles	≥ 10,000



Identification		Part number		Drawing	Dimensions in mm
		Marking A ... F ¹⁾	Marking a ... f ²⁾		
Docking frame for 2 modules 		09 14 006 1701		 ① floating tolerance ±2 mm Panel cut out	
Docking frame for 2 modules 			09 14 006 1711	 ① floating tolerance ±2 mm Panel cut out	
Docking frame for 4 modules 		09 14 016 1701		 ① floating tolerance ±2 mm Panel cut out	
Docking frame for 4 modules 			09 14 016 1711	 ① floating tolerance ±2 mm Panel cut out	

1) Float mount
2) Fixed



Identification		Part number		Drawing	Dimensions in mm
Marking A ... F ¹⁾	Marking a ... f ²⁾				
Docking frame for 6 modules 	09 14 024 1701			  ① floating tolerance ±2 mm	
Docking frame for 6 modules 		09 14 024 1711		  Panel cut out	
Float washer to enable the frame to be float mounted using standard M4 fixing screws 	09 14 000 9936				

1) Float mount
2) Fixed

Features

- Suitable for Han E® HMC crimp contacts
- Standard module for power up to 40 A
- Designed for 10,000 mating cycles with Han E® HMC crimp contacts and only with Han-Modular® Docking frame

Technical characteristics

Specifications DIN EN 60 664-1
DIN EN 61 984

Approvals 

Inserts

Number of contacts	6
Electrical data	
acc. to EN 61 984	16 A 500 V 6 kV 3
Rated current	16 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3

Rated voltage	600 V
acc. to UL/CSA	
Insulation resistance	$\geq 10^{10} \Omega$
Material	polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	
- mating cycles	$\geq 10,000$


Contacts Han E® HMC

Material	copper alloy
Surface	HMC gold plated
Contact resistance	$\leq 1 \text{ m}\Omega$
Crimp terminal	
- mm ²	0.14 ... 4 mm ²
- AWG	26 ... 12

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5




① 24 B HMC hoods/housings with 6 modules; wire gauge: 2.5 mm²


② 24 B HMC hoods/housings with 6 modules; wire gauge: 1.5 mm²





Number of contacts

6



Identification		Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately		09 14 006 3001	09 14 006 3101	 Contact arrangement view from termination side	

Identification		Wire gauge (mm²)	Part number		Drawing	Dimensions in mm																																				
			Male contact	Female contact																																						
Crimp contacts HMC gold plated																																										
		0.14-0.37	09 33 200 6117	09 33 200 6217	<table><tr><th>Identification</th><th colspan="2">Wire gauge</th><th>Stripping length</th></tr><tr><td>no groove</td><td>0.14-0.37 mm²</td><td>AWG 26-22</td><td>7.5 mm</td></tr><tr><td>no groove</td><td>0.5 mm²</td><td>AWG 20</td><td>7.5 mm</td></tr><tr><td>1 groove*</td><td>0.75 mm²</td><td>AWG 18</td><td>7.5 mm</td></tr><tr><td>1 groove</td><td>1 mm²</td><td>AWG 18</td><td>7.5 mm</td></tr><tr><td>2 grooves</td><td>1.5 mm²</td><td>AWG 16</td><td>7.5 mm</td></tr><tr><td>3 grooves</td><td>2.5 mm²</td><td>AWG 14</td><td>7.5 mm</td></tr><tr><td>wide groove</td><td>3 mm²</td><td>AWG 12</td><td>7.5 mm</td></tr><tr><td>no groove</td><td>4 mm²</td><td>AWG 12</td><td>7.5 mm</td></tr></table> * on the back crimp collar	Identification	Wire gauge		Stripping length	no groove	0.14-0.37 mm²	AWG 26-22	7.5 mm	no groove	0.5 mm²	AWG 20	7.5 mm	1 groove*	0.75 mm²	AWG 18	7.5 mm	1 groove	1 mm²	AWG 18	7.5 mm	2 grooves	1.5 mm²	AWG 16	7.5 mm	3 grooves	2.5 mm²	AWG 14	7.5 mm	wide groove	3 mm²	AWG 12	7.5 mm	no groove	4 mm²	AWG 12	7.5 mm	
Identification	Wire gauge		Stripping length																																							
no groove	0.14-0.37 mm²	AWG 26-22	7.5 mm																																							
no groove	0.5 mm²	AWG 20	7.5 mm																																							
1 groove*	0.75 mm²	AWG 18	7.5 mm																																							
1 groove	1 mm²	AWG 18	7.5 mm																																							
2 grooves	1.5 mm²	AWG 16	7.5 mm																																							
3 grooves	2.5 mm²	AWG 14	7.5 mm																																							
wide groove	3 mm²	AWG 12	7.5 mm																																							
no groove	4 mm²	AWG 12	7.5 mm																																							
		0.5	09 33 200 6122	09 33 200 6222																																						
		0.75	09 33 200 6115	09 33 200 6215																																						
		1	09 33 200 6118	09 33 200 6218																																						
		1.5	09 33 200 6116	09 33 200 6216																																						
		2.5	09 33 200 6123	09 33 200 6223																																						
		4	09 33 200 6119	09 33 200 6221																																						


Features

- Suitable for Han E® HMC crimp contacts
- High contact density
- Designed for 10,000 mating cycles with Han E® HMC crimp contacts and only with Han-Modular® Docking frame

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5



① 24 B HMC hoods/housings with 6 modules; wire gauge: 2.5 mm²

② 24 B HMC hoods/housings with 6 modules; wire gauge: 1.5 mm²

Technical characteristics

Specifications DIN EN 60 664-1
DIN EN 61 984

Approvals



Inserts

Number of contacts 8
Electrical data acc. to EN 61 984 **16 A 400 V 6 kV 3**
Rated current 16 A
Rated voltage 400 V
Rated impulse voltage 6 kV
Pollution degree 3


Rated voltage acc. to UL 600 V
Insulation resistance $\geq 10^{10} \Omega$
Material polycarbonate
Limiting temperatures -40 °C ... +125 °C
Flammability acc. to UL 94 V 0
Mechanical working life - mating cycles $\geq 10,000$


Contacts Han E® HMC



Material copper alloy
Surface HMC gold plated
Contact resistance $\leq 1 \text{ m}\Omega$
Crimp terminal
- mm² 0.14 ... 4 mm²
- AWG 26 ... 12

Number of contacts

8



Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately	09 14 008 3001	09 14 008 3101		Contact arrangement view from termination side

Identification	Wire gauge (mm²)	Part number		Drawing	Dimensions in mm																																				
		Male contact	Female contact																																						
Crimp contacts HMC gold plated																																									
	0.14-0.37	09 33 200 6117	09 33 200 6217																																						
	0.5	09 33 200 6122	09 33 200 6222																																						
	0.75	09 33 200 6115	09 33 200 6215																																						
	1	09 33 200 6118	09 33 200 6218																																						
	1.5	09 33 200 6116	09 33 200 6216																																						
	2.5	09 33 200 6123	09 33 200 6223																																						
	4	09 33 200 6119	09 33 200 6221																																						
<table><tr><th>Identification</th><th colspan="2">Wire gauge</th><th>Stripping length</th></tr><tr><td>no groove</td><td>0.14-0.37 mm²</td><td>AWG 26-22</td><td>7.5 mm</td></tr><tr><td>no groove</td><td>0.5 mm²</td><td>AWG 20</td><td>7.5 mm</td></tr><tr><td>1 groove*</td><td>0.75 mm²</td><td>AWG 18</td><td>7.5 mm</td></tr><tr><td>1 groove</td><td>1 mm²</td><td>AWG 18</td><td>7.5 mm</td></tr><tr><td>2 grooves</td><td>1.5 mm²</td><td>AWG 16</td><td>7.5 mm</td></tr><tr><td>3 grooves</td><td>2.5 mm²</td><td>AWG 14</td><td>7.5 mm</td></tr><tr><td>wide groove</td><td>3 mm²</td><td>AWG 12</td><td>7.5 mm</td></tr><tr><td>no groove</td><td>4 mm²</td><td>AWG 12</td><td>7.5 mm</td></tr></table>						Identification	Wire gauge		Stripping length	no groove	0.14-0.37 mm²	AWG 26-22	7.5 mm	no groove	0.5 mm²	AWG 20	7.5 mm	1 groove*	0.75 mm²	AWG 18	7.5 mm	1 groove	1 mm²	AWG 18	7.5 mm	2 grooves	1.5 mm²	AWG 16	7.5 mm	3 grooves	2.5 mm²	AWG 14	7.5 mm	wide groove	3 mm²	AWG 12	7.5 mm	no groove	4 mm²	AWG 12	7.5 mm
Identification	Wire gauge		Stripping length																																						
no groove	0.14-0.37 mm²	AWG 26-22	7.5 mm																																						
no groove	0.5 mm²	AWG 20	7.5 mm																																						
1 groove*	0.75 mm²	AWG 18	7.5 mm																																						
1 groove	1 mm²	AWG 18	7.5 mm																																						
2 grooves	1.5 mm²	AWG 16	7.5 mm																																						
3 grooves	2.5 mm²	AWG 14	7.5 mm																																						
wide groove	3 mm²	AWG 12	7.5 mm																																						
no groove	4 mm²	AWG 12	7.5 mm																																						
* on the back crimp collar																																									


Features

- Suitable for Han E® HMC crimp contacts
- designed for a high working voltage up to 830 V
- finger safe male and female contacts
- Designed for 10,000 mating cycles with Han E® HMC crimp contacts and only with Han-Modular® Docking frame

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5



- ① 24 B HMC hoods/housings with 6 modules; wire gauge: 1.5 mm²
 ② 24 B HMC hoods/housings with 6 modules; wire gauge: 2.5 mm²
 ③ 24 B HMC hoods/housings with 6 modules; wire gauge: 4 mm²

Technical characteristics

Specifications DIN EN 60 664-1
DIN EN 61 984

Approvals



Inserts

Number of contacts 6
 Electrical data acc. to EN 61 984 **16 A 830 V 8 kV 3**
 Rated current 16 A
 Rated voltage 830 V
 Rated impulse voltage 8 kV
 Pollution degree 3

Rated voltage acc. to UL 600 V
 Insulation resistance $\geq 10^{10} \Omega$
 Material polycarbonate
 Limiting temperatures -40 °C ... +125 °C
 Flammability acc. to UL 94 V 0
 Mechanical working life - mating cycles $\geq 10,000$


Contacts Han E® HMC

Material copper alloy
 Surface HMC gold plated
 Contact resistance $\leq 1 \text{ m}\Omega$
 Crimp terminal
 - mm² 0.14 ... 4 mm²
 - AWG 26 ... 12



Number of contacts

6



Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately	09 14 006 3041	09 14 006 3141	M F M F Contact arrangement view from termination side	

Identification	Wire gauge (mm²)	Male contact	Part number	Female contact	Drawing	Dimensions in mm																																				
Crimp contacts HMC gold plated																																										
	0.14-0.37	09 33 200 6117	09 33 200 6217																																							
	0.5	09 33 200 6122	09 33 200 6222																																							
	0.75	09 33 200 6115	09 33 200 6215																																							
	1	09 33 200 6118	09 33 200 6218																																							
	1.5	09 33 200 6116	09 33 200 6216																																							
	2.5	09 33 200 6123	09 33 200 6223																																							
	4	09 33 200 6119	09 33 200 6221																																							
					<table><tr><th>Identification</th><th colspan="2">Wire gauge</th><th>Stripping length</th></tr><tr><td>no groove</td><td>0.14-0.37 mm²</td><td>AWG 26-22</td><td>7.5 mm</td></tr><tr><td>no groove</td><td>0.5 mm²</td><td>AWG 20</td><td>7.5 mm</td></tr><tr><td>1 groove*</td><td>0.75 mm²</td><td>AWG 18</td><td>7.5 mm</td></tr><tr><td>1 groove</td><td>1 mm²</td><td>AWG 18</td><td>7.5 mm</td></tr><tr><td>2 grooves</td><td>1.5 mm²</td><td>AWG 16</td><td>7.5 mm</td></tr><tr><td>3 grooves</td><td>2.5 mm²</td><td>AWG 14</td><td>7.5 mm</td></tr><tr><td>wide groove</td><td>3 mm²</td><td>AWG 12</td><td>7.5 mm</td></tr><tr><td>no groove</td><td>4 mm²</td><td>AWG 12</td><td>7.5 mm</td></tr></table>	Identification	Wire gauge		Stripping length	no groove	0.14-0.37 mm²	AWG 26-22	7.5 mm	no groove	0.5 mm²	AWG 20	7.5 mm	1 groove*	0.75 mm²	AWG 18	7.5 mm	1 groove	1 mm²	AWG 18	7.5 mm	2 grooves	1.5 mm²	AWG 16	7.5 mm	3 grooves	2.5 mm²	AWG 14	7.5 mm	wide groove	3 mm²	AWG 12	7.5 mm	no groove	4 mm²	AWG 12	7.5 mm	
Identification	Wire gauge		Stripping length																																							
no groove	0.14-0.37 mm²	AWG 26-22	7.5 mm																																							
no groove	0.5 mm²	AWG 20	7.5 mm																																							
1 groove*	0.75 mm²	AWG 18	7.5 mm																																							
1 groove	1 mm²	AWG 18	7.5 mm																																							
2 grooves	1.5 mm²	AWG 16	7.5 mm																																							
3 grooves	2.5 mm²	AWG 14	7.5 mm																																							
wide groove	3 mm²	AWG 12	7.5 mm																																							
no groove	4 mm²	AWG 12	7.5 mm																																							
					* on the back crimp collar																																					


Features

- Suitable for Han E® HMC crimp contacts
- High contact density
- Up to 16 A per contact
- Also suitable as a reliable signal connector
- Designed for 10,000 mating cycles with Han E® HMC crimp contacts and only with Han-Modular® Docking frame

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5



- ① 24 B HMC hoods/housings with 3 modules; wire gauge: 1.5 mm²
 ② 24 B HMC hoods/housings with 3 modules; wire gauge: 2.5 mm²
 ③ 24 B HMC hoods/housings with 3 modules; wire gauge: 4 mm²

Technical characteristics

Specifications DIN EN 60 664-1
DIN EN 61 984

Approvals



Inserts

Number of contacts 20
 Electrical data acc. to EN 61 984 **16 A 500 V 6 kV 3**
 Rated current 16 A
 Rated voltage 500 V
 Rated impulse voltage 6 kV
 Pollution degree 3

Rated voltage acc. to UL 600 V
 Insulation resistance $\geq 10^{10} \Omega$
 Material polycarbonate
 Limiting temperatures -40 °C ... +125 °C
 Flammability acc. to UL 94 V 0
 Mechanical working life - mating cycles $\geq 10,000$


Contacts Han E® HMC


Material copper alloy
 Surface HMC gold plated
 Contact resistance $\leq 1 \text{ m}\Omega$
 Crimp terminal
 - mm² 0.14 ... 4 mm²
 - AWG 26 ... 12




Number of contacts

20



Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately	09 14 020 3001	09 14 020 3101		Contact arrangement view from termination side

Identification	Wire gauge (mm²)	Male contact	Female contact	Drawing	Dimensions in mm																																				
Crimp contacts HMC gold plated																																									
	0.14-0.37 0.5 0.75 1 1.5 2.5 4	09 33 200 6117 09 33 200 6122 09 33 200 6115 09 33 200 6118 09 33 200 6116 09 33 200 6123 09 33 200 6119	09 33 200 6217 09 33 200 6222 09 33 200 6215 09 33 200 6218 09 33 200 6216 09 33 200 6223 09 33 200 6221	<table><tr><th>Identification</th><th colspan="2">Wire gauge</th><th>Stripping length</th></tr><tr><td>no groove</td><td>0.14-0.37 mm²</td><td>AWG 26-22</td><td>7.5 mm</td></tr><tr><td>no groove</td><td>0.5 mm²</td><td>AWG 20</td><td>7.5 mm</td></tr><tr><td>1 groove*</td><td>0.75 mm²</td><td>AWG 18</td><td>7.5 mm</td></tr><tr><td>1 groove</td><td>1 mm²</td><td>AWG 18</td><td>7.5 mm</td></tr><tr><td>2 grooves</td><td>1.5 mm²</td><td>AWG 16</td><td>7.5 mm</td></tr><tr><td>3 grooves</td><td>2.5 mm²</td><td>AWG 14</td><td>7.5 mm</td></tr><tr><td>wide groove</td><td>3 mm²</td><td>AWG 12</td><td>7.5 mm</td></tr><tr><td>no groove</td><td>4 mm²</td><td>AWG 12</td><td>7.5 mm</td></tr></table> * on the back crimp collar	Identification	Wire gauge		Stripping length	no groove	0.14-0.37 mm²	AWG 26-22	7.5 mm	no groove	0.5 mm²	AWG 20	7.5 mm	1 groove*	0.75 mm²	AWG 18	7.5 mm	1 groove	1 mm²	AWG 18	7.5 mm	2 grooves	1.5 mm²	AWG 16	7.5 mm	3 grooves	2.5 mm²	AWG 14	7.5 mm	wide groove	3 mm²	AWG 12	7.5 mm	no groove	4 mm²	AWG 12	7.5 mm	
Identification	Wire gauge		Stripping length																																						
no groove	0.14-0.37 mm²	AWG 26-22	7.5 mm																																						
no groove	0.5 mm²	AWG 20	7.5 mm																																						
1 groove*	0.75 mm²	AWG 18	7.5 mm																																						
1 groove	1 mm²	AWG 18	7.5 mm																																						
2 grooves	1.5 mm²	AWG 16	7.5 mm																																						
3 grooves	2.5 mm²	AWG 14	7.5 mm																																						
wide groove	3 mm²	AWG 12	7.5 mm																																						
no groove	4 mm²	AWG 12	7.5 mm																																						


Features

- Suitable for Han D[®] HMC crimp contacts
- Standard module for power up to 10 A
- Compatible to Han D[®] module with Quick Lock terminal
- Designed for 10,000 mating cycles with Han D[®] HMC crimp contacts and only with Han-Modular[®] Docking frame

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5



① 24 B HMC hoods/housings with 6 modules; wire gauge: 1.5 mm²

② 24 B HMC hoods/housings with 6 modules; wire gauge: 1.0 mm²

Technical characteristics

Specifications

DIN EN 60 664-1
DIN EN 61 984

Approvals



Inserts

Number of contacts	12
Electrical data acc. to EN 61 984	10 A 250 V 4 kV 3
Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3


Rated voltage acc. to UL/CSA	600 V
Insulation resistance	≥ 10 ¹⁰ Ω
Material	polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life - mating cycles	≥ 10,000


Contacts Han D[®] HMC


Material	copper alloy
Surface	HMC gold plated
Contact resistance	≤ 3 mΩ
Crimp terminal	
- mm ²	0.14 ... 2.5 mm ²
- AWG	26 ... 14

Number of contacts

12



Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately	09 14 012 3001	09 14 012 3101		

Identification	Wire gauge (mm²)	Part number		Male contact	Female contact	Drawing	Dimensions in mm
Crimp contacts							
HMC gold plated							
	0.14-0.37	09 15 200 6124	09 15 200 6224				
	0.5	09 15 200 6123	09 15 200 6223				
	0.75	09 15 200 6125	09 15 200 6225				
	1	09 15 200 6122	09 15 200 6222				
	1.5	09 15 200 6121	09 15 200 6221				
	2.5	09 15 200 6126	09 15 200 6226				

Stock items in bold type

Features

- Suitable for Han D® HMC crimp contacts
- High contact density
- Designed for 10,000 mating cycles with Han® D HMC crimp contacts and only with Han-Modular® Docking frame

Technical characteristics

Specifications DIN EN 60 664-1
DIN EN 61 984

Approvals



Inserts

Number of contacts	17
Electrical data	
acc. to EN 61 984	10 A 160 V 2.5 kV 3
Rated current	10 A
Rated voltage	160 V
Rated impulse voltage	2.5 kV
Pollution degree	3

Rated voltage	250 V
acc. to UL	
Insulation resistance	$\geq 10^{10} \Omega$
Material	polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	
- mating cycles	$\geq 10,000$


Contacts Han D® HMC

Material	copper alloy
Surface	HMC gold plated
Contact resistance	$\leq 3 \text{ m}\Omega$
Crimp terminal	
- mm ²	0.14 ... 2.5 mm ²
- AWG	26 ... 14

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5




① 24 B HMC hoods/housings with 6 modules; wire gauge: 1.5 mm²


② 24 B HMC hoods/housings with 6 modules; wire gauge: 1.0 mm²




Number of contacts

17



Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately	09 14 017 3001	09 14 017 3101		Contact arrangement view from termination side

Identification	Wire gauge (mm²)	Part number		Drawing	Dimensions in mm																												
		Male contact	Female contact																														
Crimp contacts																																	
HMC gold plated																																	
	0,14-0,37 0,5 0,75 1 1,5 2,5	09 15 200 6124 09 15 200 6123 09 15 200 6125 09 15 200 6122 09 15 200 6121 09 15 200 6126	09 15 200 6224 09 15 200 6223 09 15 200 6225 09 15 200 6222 09 15 200 6221 09 15 200 6226		<table><tr><th colspan="2">Wire gauge</th><th>Ø</th><th>Stripping length</th></tr><tr><td>0.14-0.37 mm²</td><td>AWG 26-22</td><td>0.9</td><td>8 mm</td></tr><tr><td>0.5 mm²</td><td>AWG 20</td><td>1.1</td><td>8 mm</td></tr><tr><td>0.75 mm²</td><td>AWG 18</td><td>1.3</td><td>8 mm</td></tr><tr><td>1 mm²</td><td>AWG 18</td><td>1.45</td><td>8 mm</td></tr><tr><td>1.5 mm²</td><td>AWG 16</td><td>1.75</td><td>8 mm</td></tr><tr><td>2.5 mm²</td><td>AWG 14</td><td>2.25</td><td>6 mm</td></tr></table>	Wire gauge		Ø	Stripping length	0.14-0.37 mm²	AWG 26-22	0.9	8 mm	0.5 mm²	AWG 20	1.1	8 mm	0.75 mm²	AWG 18	1.3	8 mm	1 mm²	AWG 18	1.45	8 mm	1.5 mm²	AWG 16	1.75	8 mm	2.5 mm²	AWG 14	2.25	6 mm
Wire gauge		Ø	Stripping length																														
0.14-0.37 mm²	AWG 26-22	0.9	8 mm																														
0.5 mm²	AWG 20	1.1	8 mm																														
0.75 mm²	AWG 18	1.3	8 mm																														
1 mm²	AWG 18	1.45	8 mm																														
1.5 mm²	AWG 16	1.75	8 mm																														
2.5 mm²	AWG 14	2.25	6 mm																														












Technical characteristics

Han® B HMC












Metal hoods/housings for industrial applications

Material	aluminium die-cast
Colour	RAL 7037 (grey)
Surface	powder-coated
Locking element	Stainless steel
Lever type	Han-Easy Lock® HMC
Hoods/Housings seal	NBR
Limiting temperatures	-40 °C ... +125 °C
Approval acc. to UL 50	NEMA Type 4/4X/12
Degree of protection acc. to DIN EN 60 529	
for coupled connector	IP 65
Locking cycles	≥ 10,000





Metal hoods/housings for industrial applications / 1 lever locking system

Identification	Part number		Cable entry metric	Drawing	Dimensions in mm
	Low construction	High construction			
Hoods side entry 	19 30 210 1540 19 30 210 1541		1 x 20 1 x 25		
side entry 		19 30 210 0547	1 x 32		
Hoods top entry 	19 30 210 1440 19 30 210 1441		1 x 20 1 x 25		
top entry 		19 30 210 0447	1 x 32		
Hoods without cable entry 		09 30 210 0803	—		
Housings, bulkhead mounting 	09 30 210 0305				
				Panel cut out	







Metal hoods/housings for industrial applications / 1 lever locking system

Identification	Part number		Cable entry metric	Drawing	Dimensions in mm
	Low construction	High construction			
Hoods side entry 	19 30 216 1541 19 30 216 1542		1 x 25 1 x 32		
side entry 		19 30 216 0547 19 30 216 0548	1 x 32 1 x 40		
Hoods top entry 	19 30 216 1441 19 30 216 1442		1 x 25 1 x 32		
top entry 		19 30 216 0447 19 30 216 0448	1 x 32 1 x 40		
Hoods without cable entry 		09 30 216 0803	—		
Housings, bulkhead mounting 	09 30 216 0307				
				Panel cut out	





Metal hoods/housings for industrial applications / 1 lever locking system

Identification	Part number		Cable entry metric	Drawing	Dimensions in mm
	Low construction	High construction			
Housings, surface mounting side entry 	19 30 216 1251 19 30 216 1291		1 x 25 2 x 25	 Blind way for one cable entry	
side entry 		19 30 216 0252 19 30 216 0291 19 30 216 0292	1 x 32 2 x 25 2 x 32	 Blind way for one cable entry	
Hoods, cable to cable top entry 	19 30 216 1751 19 30 216 1752		1 x 25 1 x 32		
top entry 		19 30 216 0757	1 x 32		

Metal hoods/housings for industrial applications / 1 lever locking system

Identification	Part number		Cable entry metric	Drawing	Dimensions in mm
	Low construction	High construction			
Hoods side entry 	19 30 224 1541 19 30 224 1542		1 x 25 1 x 32		
side entry 		19 30 224 0547 19 30 224 0548	1 x 32 1 x 40		
Hoods top entry 	19 30 224 1442		1 x 32		
top entry 		19 30 224 0447 19 30 224 0448	1 x 32 1 x 40		
Hoods without cable entry 		09 30 224 0803	—		
Housings, bulkhead mounting 	09 30 224 0307			 Panel cut out	

Metal hoods/housings for industrial applications / 1 lever locking system

Identification	Part number		Cable entry metric	Drawing	Dimensions in mm
	Low construction	High construction			
Housings, surface mounting side entry 	19 30 224 1251 19 30 224 1291		1 x 25 2 x 25	 Blind way for one cable entry	
side entry 		19 30 224 0292	2 x 32	 Blind way for one cable entry	
Hoods, cable to cable top entry 	19 30 224 1752		1 x 32		
top entry 		19 30 224 0757	1 x 32		

Features

- Suitable for all inserts of the series Han D® HMC, Han E® HMC, Han® EEE HMC and Han DD® HMC
- Ideal for applications in the field of transportation, as well as in the printing industry
- Due to the floating system of the docking frame the PE connection of the mounting base has to be installed separately
- Inserts are protected against mechanical damage
- Designed for 10,000 mating cycles

Technical characteristics

Material	
Docking frame	stainless steel
Fixing screws	steel, zinc-plated
Pull-in-range	
x-axis	± 1.5 mm
y-axis	± 1.5 mm
Mechanical working life	
- mating cycles	10,000




Identification	Size	Part number	Drawing	Dimensions in mm
----------------	------	-------------	---------	------------------

Han® Docking frame



6 B

09 30 006 1701




Distance for electrical and F.O. contacts max. 27 mm; for pneumatic contacts max. 26.5 mm

10 B

09 30 010 1701

16 B

09 30 016 1701



24 B


09 30 024 1701

Size	a	b	e	f
6 B	86	69	54.5	84
10 B	99	82	67.5	97
16 B	119.5	102.5	88	117.5
24 B	146	129	114.5	144

Range of delivery:
1 frame
4 cheese head shoulder screws to fix
the docking frame

Features

- Suitable for rough environments
- Two-part hoods for easy wiring and testing
- High robustness by means of an internal locking mechanism



- ① Shell with top entry
- ② Thread M25 ... M40
- ③ Carrier hood with push button release
- ④ Housings bulkhead mounting



Technical characteristics

Shells and Housings, surface mounting

Material	aluminium die-cast
Surface	powder coated
Locking element	stainless steel
Limiting temperatures	-40 °C ... +125 °C
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP 65 and IP 67
Tightening torque M4 fixing screw	1.2 Nm ... 2.0 Nm

Carrier hoods and Housings, bulkhead mounting






Number of Han-Yellock® modules	
Han-Yellock® 30	3
Han-Yellock® 60	6
Material	zinc die-cast
Surface	chromated
Colour	RAL 9005 (black)
Locking element	metallised plastic / stainless steel
Hoods/Housings seal	NBR
Limiting temperatures	-40 °C ... +125 °C
Un-/Locking temperatures	-10 °C ... +85 °C
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP 65 and IP 67
Mechanical working life - mating cycles	< 500
PE contact wire gauge	≤ 4 mm ²
Tightening torque M4 fixing screw	1 Nm
panel fastener	2.3 Nm



- ① M4 fixing screw (screw length > 20 mm)
- ② Panel fastener

Available June 2013



Identification	Part number	Cable entry	Drawing	Dimensions in mm
Shell Han-Yellock® 30 top entry  Han-Yellock® 30 side entry  Han-Yellock® 30 angled entry 	11 13 300 1401 11 13 300 1501 11 13 300 1601	M25 M25 M25	  	
Shell Han-Yellock® 60 top entry  Han-Yellock® 60 side entry 	11 13 600 1402 11 13 600 1403 11 13 600 1502	M32 M40 M32	 	

Identification	Part-Number	Drawing	Dimensions in mm
Housings, bulkhead mounting Han-Yellok® 30 Han-Yellok® 60 Set consists of Han-Yellok® bulkhead mounted housing and panel fastener* ¹ Han-Yellok® 30 Han-Yellok® 60	11 13 300 0301 11 13 600 0301 11 13 300 0302 11 13 600 0302		
^{*1} screws for using with panel fastener M4 x 20 or longer			
Carrier hood push button with slot Han-Yellok® 30* ² Han-Yellok® 60 plain push button Han-Yellok® 30* ² Han-Yellok® 60* ²	11 13 300 0110 11 13 600 0110 11 13 300 0100 11 13 600 0100		

*² differing from depiction

Features

- Suitable for HARTING LC contacts
- For GI-Fibre 50 - 62.5 / 125 µm and for single mode fibre
- Using of guiding pins (male and female) is obligatory

Technical characteristics


Inserts



Number of contacts	6
Material	polycarbonate
Limiting temperatures	-40 °C ... +85 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles


Number of contacts

6

Available Nov. 2013



Identification	Part-Number		Drawings	Dimensions in mm
	Male insert (M)	Female insert (F)		
LC module order contacts separately 	09 14 006 4701	09 14 006 4711	 Contact arrangement View termination side	

Identification	Part-Number		Drawings	Dimensions in mm
	Male insert (M)			
LC contact  for multi mode for cable $\varnothing \leq 3$ mm for cable $\varnothing \leq 2$ mm for single mode for cable $\varnothing \leq 3$ mm for cable $\varnothing \leq 2$ mm	20 10 125 8211 20 10 125 8212 20 10 125 8220 20 10 125 8221			

Features

- Screw connection, suitable for all users around the world
- Field assembly without special tools
- For flexible and solid conductors from 0.5 to 2.5 mm²
- Additional protection against voltage and accidental contact by a sliding insulation cover that closes automatically during mating

Technical characteristics

Specifications	DIN EN 60 664-1 DIN EN 61 984
----------------	----------------------------------

Inserts

Number of contacts	5
Electrical data acc. to EN 61 984	16 A 230/400 V 4 kV 3
Rated current	16 A
Rated voltage	230/400 V
Rated impulse voltage	4 kV
Pollution degree	3

Insulation resistance	≥ 10 ¹⁰ Ω
Material	polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life - mating cycles	≥ 500

Contacts


Material	copper alloy
Surface	
- hard-silver plated	3 µm Ag
Contact resistance	≤ 1 mΩ
Quick Lock termination	
- mm ²	0.5 ... 2.5 mm ²
- AWG	20 ... 14



Number of contacts

5

Available September 2013




Identification		Part number		Drawing	Dimensions in mm
		Male insert (M)	Female insert (F)		

Screw termination



09 14 005 26 01

09 14 005 27 01



Features

- Blind mating connector system for drawer systems
- Direct panel mounting without housing
- Very robust design
- Solid pre-leading guide pins and float bushes
- Can be fixed with standard M4 screws

Note:

Due to the plastic material used in the docking frame without PE, the panel will need to be grounded separately.

Technical characteristics

Specifications	DIN EN 60 664-1 DIN EN 61 984
Frames	
Number of modules	2, 3, 4, 6
Material	
Docking Frame	polycarbonate
Float washer	zinc die-cast alloy
Floating tolerance	± 2 mm
Aligning tolerance	± 4 mm
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	≥ 500 mating cycles



Identification	Float mount A ... F	Fixed a ... f	Drawings	Dimensions in mm
Docking frame for 2 modules 	09 14 006 1701			
Docking frame for 2 modules 		09 14 006 1711		
Docking frame for 3 modules 	09 14 010 1701			
Docking frame for 3 modules 		09 14 010 1711		






Identification	Float mount A ... F	Fixed a ... f	Drawings	Dimensions in mm
Docking frame for 4 modules Docking frame for 4 modules	09 14 016 1701		Technical drawing of the 4-module docking frame showing front, side, and cross-section views with dimensions: $\phi 10,7$, 94, 45, 78, 68, 40, 28,8, $\phi 4,2$, 31,7-32,7, 1. ① floating tolerance: ± 2 mm panel cut out	
Docking frame for 6 modules Docking frame for 6 modules	09 14 024 1701		Technical drawing of the 6-module docking frame showing front, side, and cross-section views with dimensions: $\phi 10,7$, 123,4, 45, 107,4, 97,4, 40, 28,8, $\phi 4,2$, 31,7-32,7, 1. ① floating tolerance: ± 2 mm	
Float washer to enable the frame to be float mounted using standard M4 fixing screws	09 14 000 9936		Technical drawing of the float washer showing front and side views with dimensions: 5,8, $\phi 6,5$, $\phi 4,2$, $\phi 12$.	



Features

- Suitable for individual modules of the series Han-Modular® in control cabinets, distribution etc. as cable-to-cable connection
- Strain relief provided by cable ties (max. width: 5 mm)
- Optional fixing due to two drill holes on the strain relief flange
- Easy mounting and removal of the modules (see Han-Modular® removal tool)

Identification	Part-Number	Depiction
Module clamp with strain relief * 	09 14 000 0312	 1 For cable ties with max. 5 mm width
Module clamp for rail * 	09 14 000 0313	 1 G-rail DIN EN 60 715-G32 2 Rail DIN EN 60 715-35 x 7.5 with 1 mm thickness or -35 x 15 with 1.5 mm thickness 3 C-rail DIN EN 60 715-C30

*Delivery comprises one module clamp

Features

- Suitable for rough industrial environments (degree of protection IP 65 with closed cover)
- Optimum locking (3 mm double bit or rotation knob)
- Safe opening (integrated spring, 30 degree opening and locking position in the cover)
- Worldwide use (see approvals)
- High quality plastics

Technical characteristics

Material	
Frame	plastic PBT black
Cover	plastic PC transparent plastic ABS metallic silver
Limiting temperatures	-30 °C ... +70 °C
Locking	3 mm double bit rotation knob
Suitable for wall thickness	1 ... 5 mm
Degree of protection acc. to EN 60 529 with closed cover	IP 65
Dimensions	
single mounting frame (HxWxD)	127 x 66 x 32
double mounting frame (HxWxD)	127 x 131 x 32
Approvals	NEMA 4/4x/12/13 

Han-Port® Mounting Frame

Available September 2013



Plastic mounting frame

Identification	Part-Number	Depiction
Single mounting frames, plastic		
with transparent plastic cover and 3 mm double bit closure	39 50 000 0300	
with transparent plastic cover and rotation knob closure	39 50 000 0310	
with metallic silver plastic cover and 3 mm double bit closure	39 50 000 0320	
with metallic silver plastic cover and rotation knob closure	39 50 000 0330	

Han-Port® Mounting Frame

Available September 2013



Plastic mounting frame

Identification	Part-Number	Depiction
Double mounting frames, plastic		
with transparent plastic cover and 3 mm double bit closure	39 50 000 0400	
with transparent plastic cover and rotation knob closure	39 50 000 0410	
with metallic silver plastic cover and 3 mm double bit closure	39 50 000 0420	
with metallic silver plastic cover and rotation knob closure	39 50 000 0430	


Features

- Heavy duty connector for D-Sub signal contacts
- Suitable for all Han® 3 A hoods/housing types: Standard (metal, plastic), EMC, INOX, M and HPR
- High contact density at small foot print
- Easy handling of signal connectors in industrial environment
- One preleading contact

Current Carrying Capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5



- ① wire gauge: 0.14 mm² stamped contacts
 ② wire gauge: 0.25 mm² stamped contacts
 ③ wire gauge: 0.5 mm² turned contacts

Technical characteristics

Inserts

Number of contacts	21
Electrical data	
acc. to EN 61 984	6.5 A ~50 V / 120 V 0.8 kV 3
Rated current	6.5 A
Rated voltage AC	~50 V
Rated voltage DC	~120 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Insulation resistance	≥ 10 ¹⁰ Ω
Material	polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Mechanical working life	
- mating cycles	according to performance level of used contacts

Contacts

Material	copper alloy
Surface	
- selectively gold plated	according to performance level
Crimp termination	
- mm ²	0.09 mm ² ... 0.56 mm ²
- AWG	28 ... 20

Hoods/Housings

Detailed information and further hood/housing types see catalog "Industrial Connectors Han®", chapter 31

Plastic hoods/housings

Material	polycarbonate
Flammability acc. to UL 94	V 0
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP 67





Metal hoods/housings

Material	zinc die-cast
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP 44
	IP 67 is achieved with seal screw 09 20 000 9918

Number of contacts

21



Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately	09 12 021 3001	09 12 021 3101	M  F 	 

Identification	Part number	Drawing	Dimensions in mm
Insertion / removal tool for D-Sub crimp contacts 	09 99 000 0368		

Contacts



Identification		Wire gauge (mm²)	Part number		Drawing	Dimensions in mm	
			Male contact	Female contact			
Individual contacts, turned	Performance level 1	0.09-0.25 0.13-0.33 0.25-0.52	09 67 000 7576 09 67 000 5576 09 67 000 8576	09 67 000 7476 09 67 000 5476 09 67 000 8476			
Individual contacts, stamped	Performance level 1	0.09-0.25 0.25-0.56	09 67 000 7176 09 67 000 8176	09 67 000 7276 09 67 000 8276			
500 pieces/reel	Performance level 1 Unrolling left	0.09-0.25 0.25-0.56	09 67 000 7166 09 67 000 8166	09 67 000 7266 09 67 000 8266			
10,000 pieces/reel	Performance level 1 Unrolling left	0.09-0.25 0.25-0.56	09 67 000 7156 09 67 000 8156	09 67 000 7256 09 67 000 8256			

*) Ø = max. insulation diameter


Features

- High current inserts designed to fit all hoods/housings size Han® 3 A
- 4 coding options
- Use of standard Han® C crimp contacts
- Finger protected male and female contacts
- Pre-mating PE crimp contact

Current Carrying Capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5



- ① wire gauge: 2.5 mm²
- ② wire gauge: 4 mm²
- ③ wire gauge: 6 mm²
- ④ wire gauge: 10 mm²

Technical characteristics

Inserts

Number of contacts	3 + PE
Electrical data	
acc. to EN 61 984	40 A 400 V 6 kV 3
Rated current	40 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Insulation resistance	$\geq 10^{10} \Omega$
Material	polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life	
- mating cycles	≥ 500

Contacts

Material	copper alloy
Surface	
- hard-silver plated	3 µm Ag
Contact resistance	$\leq 1 \text{ m}\Omega$
Crimp termination	
- mm²	1.5 ... 10 mm²
- AWG	16 ... 8

Tools

see chapter 99
in the main catalogue
„Industrial Connectors Han®“

Hoods/Housings

Detailed information and further hood/housing types see catalogue „Industrial Connectors Han®“, chapter 31

Plastic hoods/housings

Material	polycarbonate
Flammability acc. to UL 94	V 0
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP 67

Metal hoods/housings

Material	zinc die-cast
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP 44
	IP 67 is achieved with seal screw 09 20 000 9918


Number of contacts

3 +

Available July 2013



Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately				
Coding element 20 pieces per frame 	09 12 003 3051	09 12 003 3151		
	09 12 000 9924	09 12 000 9924		

Identification		Wire gauge (mm²)	Part number		Male contact	Female contact	Drawing	Dimensions in mm																															
Crimp contacts																																							
Power contacts																																							
silver plated																																							
																																							
		1,5		09 32 000 6104		09 32 000 6204		<table><tr><th colspan="3">Wire gauge</th><th>Ø</th><th>Stripping length</th></tr><tr><td>1.5</td><td>mm²</td><td>AWG 16</td><td>1.75</td><td>9 mm</td></tr><tr><td>2.5</td><td>mm²</td><td>AWG 14</td><td>2.25</td><td>9 mm</td></tr><tr><td>4</td><td>mm²</td><td>AWG 12</td><td>2.85</td><td>9.6 mm</td></tr><tr><td>6</td><td>mm²</td><td>AWG 10</td><td>3.5</td><td>9.6 mm</td></tr><tr><td>10</td><td>mm²</td><td>AWG 8</td><td>4.3</td><td>12 mm</td></tr></table>		Wire gauge			Ø	Stripping length	1.5	mm²	AWG 16	1.75	9 mm	2.5	mm²	AWG 14	2.25	9 mm	4	mm²	AWG 12	2.85	9.6 mm	6	mm²	AWG 10	3.5	9.6 mm	10	mm²	AWG 8	4.3	12 mm
Wire gauge			Ø	Stripping length																																			
1.5	mm²	AWG 16	1.75	9 mm																																			
2.5	mm²	AWG 14	2.25	9 mm																																			
4	mm²	AWG 12	2.85	9.6 mm																																			
6	mm²	AWG 10	3.5	9.6 mm																																			
10	mm²	AWG 8	4.3	12 mm																																			
		2,5		09 32 000 6105		09 32 000 6205																																	
		4		09 32 000 6107		09 32 000 6207																																	
		6		09 32 000 6108		09 32 000 6208																																	
		10		09 32 000 6109		09 32 000 6209																																	


Features

- High current insert in a compact design, suitable for plastic hoods/housings only in size Han® 3 A
- 4 coding options
- Use of standard Han® C crimp contacts
- Finger protected male and female contacts

Current Carrying Capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5



- ① wire gauge: 2.5 mm²
- ② wire gauge: 4 mm²
- ③ wire gauge: 6 mm²
- ④ wire gauge: 10 mm²

Technical characteristics

Inserts

Number of contacts	4 without PE
Electrical data acc. to EN 61 984	40 A 830 V 8 kV 3
Rated current	40 A
Rated voltage	830 V
Rated impulse voltage	8 kV
Pollution degree	3
Insulation resistance	≥ 10 ¹⁰ Ω
Material	polycarbonate
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to UL 94	V 0
Mechanical working life - mating cycles	≥ 500

Contacts

Material	copper alloy
Surface	
- hard-silver plated	3 µm Ag
Contact resistance	≤ 1 mΩ
Crimp termination	
- mm ²	1.5 ... 10 mm ²
- AWG	16 ... 8

Tools

see chapter 99
in the main catalogue
„Industrial Connectors Han®“

Hoods/Housings

Detailed information and further hood/housing types see catalogue „Industrial Connectors Han®“, chapter 31

Plastic hoods/housings

Material	polycarbonate
Flammability acc. to UL 94	V 0
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP 67


Number of contacts

4

Available July 2013



Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately				
	09 12 004 3051	09 12 004 3151		
Coding element 20 pieces per frame				
	09 12 000 9924	09 12 000 9924		
				Contact arrangement view from termination side

Identification	Wire gauge (mm²)	Male contact	Female contact	Drawing	Dimensions in mm																														
Crimp contacts																																			
Power contacts																																			
silver plated	1,5	09 32 000 6104	09 32 000 6204																																
	2,5	09 32 000 6105	09 32 000 6205																																
	4	09 32 000 6107	09 32 000 6207																																
	6	09 32 000 6108	09 32 000 6208																																
	10	09 32 000 6109	09 32 000 6209																																
				<table><tr><th colspan="3">Wire gauge</th><th>Ø</th><th>Stripping length</th></tr><tr><td>1.5</td><td>mm²</td><td>AWG 16</td><td>1.75</td><td>9 mm</td></tr><tr><td>2.5</td><td>mm²</td><td>AWG 14</td><td>2.25</td><td>9 mm</td></tr><tr><td>4</td><td>mm²</td><td>AWG 12</td><td>2.85</td><td>9.6 mm</td></tr><tr><td>6</td><td>mm²</td><td>AWG 10</td><td>3.5</td><td>9.6 mm</td></tr><tr><td>10</td><td>mm²</td><td>AWG 8</td><td>4.3</td><td>12 mm</td></tr></table>	Wire gauge			Ø	Stripping length	1.5	mm²	AWG 16	1.75	9 mm	2.5	mm²	AWG 14	2.25	9 mm	4	mm²	AWG 12	2.85	9.6 mm	6	mm²	AWG 10	3.5	9.6 mm	10	mm²	AWG 8	4.3	12 mm	
Wire gauge			Ø	Stripping length																															
1.5	mm²	AWG 16	1.75	9 mm																															
2.5	mm²	AWG 14	2.25	9 mm																															
4	mm²	AWG 12	2.85	9.6 mm																															
6	mm²	AWG 10	3.5	9.6 mm																															
10	mm²	AWG 8	4.3	12 mm																															

Features

- Suitable for extreme environmental conditions
- Suitable for sensitive interfaces that have to be protected and shielded
- Robust metal version
- For sizes 6, 10, 16 and 24 with screw and toggle locking
- Captive cover due to fixing cord





Technical characteristics

Material	aluminium die-cast corrosion resistant
Colour	RAL 9005 (black)
Surface	powder-coated
Locking	
Screw locking	M6
- material	stainless steel
- tightening torque	4 Nm
Toggle locking	
- material	stainless steel
Fixing cord	stainless steel
Limiting temperatures	-40 °C ... +125 °C
Corrosion resistance	ASTM B117-09 (500 h)
Degree of protection acc. to EN 60 529 in locked position	IP 68

Available by May 2013



Cover for Han® HPR hood

Identification	Part-Number		Size	Drawing	Dimensions in mm
	Toggle	Screw			
Cover for Han® HPR hood 	09 40 006 5404	09 40 006 5414	6 B		
	09 40 010 5404	09 40 010 5414	10 B		
	09 40 016 5404	09 40 016 5414	16 B		
	09 40 024 5404	09 40 024 5414	24 B		

General description


- Frame for Han® HC Modular 250 contacts suitable for Han® 24 HPR EasyCon

Technical characteristics





Material	Stainless steel
Frame	3 and 4 contacts for Han® HC Modular 250

Han® 24 HPR EasyCon Frames

Available May 2013



Frame for Han® HC Modular 250 contacts

Identification	Part-Number	Drawing		Dimensions in mm
Frames for 3 x Han® HC Modular 250 male  for 3 x Han® HC Modular 250 female 	09 40 024 9901 09 40 024 9902	Male 	Female  Included in kit: 2 x distance bolt (SW 7) 2 x M4 screw 2 x washer SK S4 2 x M4 Countersunk screw	
for 4 x Han® HC Modular 250 male  for 4 x Han® HC Modular 250 female 	09 40 024 9903 09 40 024 9904	Male 	Female  Included in kit: 4 x M4 screw 4 x washer SK S4 4 x washer SK S6 4 x cheese-head screw M6 x 20 4 x cheese-head screw M6 x 25	


Features

- Flexible high-current interface
- Low mating and unmating forces
- Stackable due to modular design
- Suitable for HC 350 crimp contacts
- On-board removal tool

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature.

Measuring and testing techniques according to DIN EN 60 512-5



① wire gauge: 35 mm²

② wire gauge: 95 mm²

HC Individual 3-poles

Technical characteristics

Inserts

Number of contacts	3
Electrical data	
acc. to EN 61 984	350 A 4000 V 18 kV 3
Rated current	350 A
Rated voltage	4000 V
Rated impulse voltage	18 kV
Pollution degree	3
Termination wire gauge	25 mm² ... 120 mm²
Insulation resistance	≥ 10 ¹⁰ Ω
Material	polyamide
Limiting temperatures	-40 °C ... +125 °C
Flammability acc. to	
UL 94	V 0
NFF 16-101/102	I2 / F3
CEN/TS 45545-2:2009	HL 2 / R24 outside HL1 / R23 inside
FprEN 45545-2:2012	HL 2 / R23 outside HL1 / R22 inside
Mechanical working life - mating cycles	500
Degree of protection acc. to DIN EN 60 529 for coupled connector	IP 66 (IP 68 in preparation)
Cable gland thread	M 32

Contacts

Material	copper alloy
Surface	3 µm Ag
Contact resistance	≤ 0.3 mΩ
Crimp terminal	25 mm² ... 120 mm²
Max. insulation diameter	20 mm
Crimp die	DIN 46 235
Pressing force requirement	130 kN


Carrier plate and Locking modules

Material	aluminium
Locking	stainless steel

Mechanical solidness

Vibration test	acc. to DIN EN 60 068-2-6 • 5 Hz ... 9 Hz: 15 mm • 9 Hz ... 150 Hz: 5 g
Shock test	acc. to DIN EN 61 373 • 30 g, 18 ms • 3 axis
Noise	acc. to DIN EN 61 373 • Cat. 2





Coding possibilities with 1 coding element (3-poles set):



Other coding possibilities on request

Available August 2013



Identification		Part Number	Drawings	Dimensions in mm
Han® HC Individual				
Carrier module, male	350 A	19 11 001 3032		
Carrier module, female	350 A	19 11 001 3132		
Carrier plate for 3x 350 A carrier modules		09 11 000 9991		
other lengths		on request		
Locking module, active		09 11 000 9980		
Locking module, passive		09 11 000 9982		
				

Identification

Part Number

Drawings

Dimensions in mm

Cable entry protection
with metric cable entries (IP 68)

metal

**19 00 000 5080**

20

19 00 000 5081

20

19 00 000 5082

20

19 00 000 5084

20

19 00 000 5090

25

19 00 000 5091

25

19 00 000 5092

25

19 00 000 5094

32

19 00 000 5095

32

19 00 000 5096

32

plastic



19 00 000 5180

20

19 00 000 5182

20

19 00 000 5184

20

19 00 000 5190

25

19 00 000 5192

25



19 00 000 5194

32

19 00 000 5196

32

SW	E	Outer cable Ø	Nm
22	24.4	5 ... 9 mm	10
22	24.4	5 ... 9 mm	10
		6 ... 12 mm	
22	24.4	6 ... 12 mm	10
24	26.5	10 ... 14 mm	10
30	33.5	9 ... 16 mm	15
30	33.5	9 ... 16 mm	15
		13 ... 18 mm	
30	33.5	13 ... 18 mm	15
40	44	13 ... 20 mm	15
40	44	13 ... 20 mm	15
		18 ... 25 mm	
40	44	18 ... 25 mm	15



22	26.4	5 ... 9 mm	8
22	26.4	6 ... 12 mm	8
22	29.8	10 ... 14 mm	10
24	33.5	9 ... 16 mm	10
30	36.5	13 ... 18 mm	15
30	46.8	13 ... 20 mm	15
30	46.8	18 ... 25 mm	15

Reducer
for metric cable entries (IP 68)

metal



M32 → M20

19 00 000 5066


32



M32 → M25







19 00 000 5069

32

D
20
25



Identification	Part Number	Drawings	Dimensions in mm
Coding element (set with 2 pieces) 	09 11 000 9987		
Unlocking tool 	09 99 000 0826		
Identification carrier module 	1 - 10 A 09 11 000 9996 1 - 10 B 09 11 000 9997 1 - 10 C 09 11 000 9998 blank 09 11 000 9999		

Identification	Wire gauge mm ²	Part-Number		Drawings	Dimensions in mm																					
		Male contacts (M)	Female contacts (F)																							
Crimp contacts* silver 																										
	25 ¹⁾	09 11 000 6139	09 11 000 6239	1) 	4) 																					
	35 ²⁾	09 11 000 6140	09 11 000 6240	2) 	5) 																					
	50 ³⁾	09 11 000 6141	09 11 000 6241	3) 	6) 																					
	70 ⁴⁾	09 11 000 6142	09 11 000 6242																							
	95 ⁵⁾	09 11 000 6143	09 11 000 6243																							
120 ⁶⁾	09 11 000 6144	09 11 000 6244																								
<table><tr><th>Wire gauge</th><th>Tool identification</th><th>Stripping length</th></tr><tr><td>25 mm²</td><td>10</td><td>26 mm</td></tr><tr><td>35 mm²</td><td>12</td><td>26 mm</td></tr><tr><td>50 mm²</td><td>14</td><td>28 mm</td></tr><tr><td>70 mm²</td><td>16</td><td>28 mm</td></tr><tr><td>95 mm²</td><td>18</td><td>30 mm</td></tr><tr><td>120 mm²</td><td>20</td><td>24 mm</td></tr></table>						Wire gauge	Tool identification	Stripping length	25 mm ²	10	26 mm	35 mm ²	12	26 mm	50 mm ²	14	28 mm	70 mm ²	16	28 mm	95 mm ²	18	30 mm	120 mm ²	20	24 mm
Wire gauge	Tool identification	Stripping length																								
25 mm ²	10	26 mm																								
35 mm ²	12	26 mm																								
50 mm ²	14	28 mm																								
70 mm ²	16	28 mm																								
95 mm ²	18	30 mm																								
120 mm ²	20	24 mm																								
* Crimp zone (①) acc. to DIN EN 46 235																										
* for stranded wire acc. to IEC 60 228 class 5																										



Set, 3-poles


Identification	Part Number	Drawings	Dimensions in mm
----------------	-------------	----------	------------------

Set*, 3-poles, male

- consists of:
- 3x carrier module, male
(19 11 001 3032)
 - 1x carrier plate
(09 11 000 9991)
 - 2x locking module, passive
(09 11 000 9982)



19 11 003 3032




Set*, 3-poles, female

- consists of:
- 3x carrier module, female
(19 11 001 3132)
 - 1x carrier plate
(09 11 000 9991)
 - 2x locking module, active
(09 11 000 9980)



19 11 003 3132






other sets

on request

- * Order separately:
- coding elements
 - unlocking tool
 - cable glands
 - crimp contacts


Assembly and construction






Wire gauge	Tool identification	Stripping length
25 mm ²	10	26 mm
35 mm ²	12	26 mm
50 mm ²	14	28 mm
70 mm ²	16	28 mm
95 mm ²	18	30 mm
120 mm ²	20	24 mm

* for stranded wire acc. to IEC 60 228 class 5

4 Variant 1



④ Variant 2



Features

- Direct hall effect current sensor
- $I_{Pmax} = 300 \text{ A} \dots 1000 \text{ A}$
- Galvanic insulation between primary and secondary current
- Panel mounting
- Housing material and potting mass have a flammability rating UL94 V0
- Standard EN 50 178: Electronic equipment for use in power installations

Advantages

- High accuracy
- Wide measuring range
- High current overload capability
- Very low susceptance to external magnetic fields

Technical characteristics

HCSE 100

I_{PN}	Nominal primary current	100 A
I_P	Measuring range	0 ... $\pm 300 \text{ A}$

HCSE 300

I_{PN}	Nominal primary current	300 A
I_P	Measuring range	0 ... $\pm 900 \text{ A}$

HCSE 500

I_{PN}	Nominal primary current	500 A
I_P	Measuring range	0 ... $\pm 1000 \text{ A}$

HCSE 800

I_{PN}	Nominal primary current	800 A
I_P	Measuring range	0 ... $\pm 1000 \text{ A}$

V_{out}	Output voltage at I_{PN}	4 V
R_L	Load resistance	$> 1 \text{ k}\Omega$
V_C	Nominal power supply ($\pm 5 \%$)	$\pm 15 \text{ V}$

I_C	Supply current @ $V_C = 15 \text{ V}$	$< 25 \text{ mA}$
R_{IN}	Insulation resistance	$> 500 \text{ M}\Omega$

X	Accuracy at I_{PN} $T_A = 25^\circ\text{C}$ without Offset	$\pm 1 \%$
E_L	Linearity	$< 0.5 \%$


V_O	Offset voltage at $I_P = 0$, $T = 25^\circ\text{C}$	$\pm 10 \text{ mV}$
V_{OOL}	Offset after I_{Pmax}	$\pm 10 \text{ mV}$
V_{OT}	Thermal offset drift, $T = -25^\circ\text{C} \dots +85^\circ\text{C}$	$\pm 1 \text{ mV/K}$
V_{outT}	Thermal gain drift, $T = -25^\circ\text{C} \dots +85^\circ\text{C}$	$\pm 0.05 \%/K$
t_r	Delay time of I_{PN}	$< 3 \mu\text{s}$
di/dt	di/dt correctly following	$> 50 \text{ A}/\mu\text{s}$
f	Bandwidth	DC ... 100 kHz

T_A	Operating temperature range	$-25 \dots +85^\circ\text{C}$
T_S	Storage temperature range	$-25 \dots +90^\circ\text{C}$
m	Weight	$\sim 0.2 \text{ kg}$
V_D	Proof stress voltage, effective, 50 Hz, 1 minute	3.5 kV
V_B	Rated voltage ¹⁾	690 V

¹⁾ Safe separation (Overvoltage Category III, pollution degree 2). Value applies for sensors with clamp terminal, for other secondary connections are higher values possible

$$I_{PN} = 100 \text{ A} \dots 800 \text{ A}$$

Measureable currents are AC, DC, pulsed ...



Available September 2013

Identification	Part number	Drawing	Dimensions in mm
HCSE 100 – HCSE 800 Sensor fastening: 2 x M4 Steel screws (recommended fastening torque 3.2 Nm) Tolerances ± 0.5 mm		The drawing consists of three views: a top view, a front view, and a side view. The top view shows a circular sensor with a central hole and two mounting holes. The front view shows the sensor's profile with dimensions: 70 mm width, 15 mm height, 60 mm base width, 15 mm base offset, 4 mm base height, 3.5 mm base offset, and 25 mm total height. The side view shows the sensor's profile with dimensions: 25 mm width, 2.5 mm height, and 70 mm total height. The drawing also includes a detail of the sensor's internal structure showing a 4-pin connector with dimensions: 90 mm width, 7 mm height, 12.5 mm offset, 6 mm base offset, 6 mm base height, 78 mm total width, and 4.6 mm base offset.	
HCSE 100	20 32 010 0101		
HCSE 300	20 32 030 0101		
HCSE 500	20 32 050 0101		
HCSE 800	20 32 080 0101		
Connections: Spring clamp terminal, pluggable Centerline 5.0 mm; 4pins Pin output: 1 +15 V 2 -15 V 3 Signal 4 0 V			

Remarks

- If I_P flows in the direction of the Arrow I_{Sek} is positive
- Over currents ($\gg I_{PN}$) or the missing of the supply voltage can cause an additional remaining magnetic offset
- The temperature of the primary conductor may not exceed 100 °C
- Protection degree of the standard interface is IP 20



- These sensors may only be used in electrical or electronic systems which fulfill the relevant regulations (Standards, EMC Requirements,...)



- Pay attention to protect non-insulated high-voltage current carrying parts against direct contact (e.g. with a protective housing)
- When installing this sensor you must ensure that the safe separation (between primary circuit and secondary circuit) is maintained over the whole circuits and their connections
- The sensor may only be connected to a power supply respecting the SELV/PELV protective regulations acc. to EN 50 178
- Disconnecting the main power must be possible

The Current Sensors support a Safe Separation. The creepage and clearance distances taken as a basis for the rated voltage are the shortest distance between the secondary connection and the transducer window. The actual rated voltage depends on the position of the primary conductor respectively on the actual distance between the primary conductor and the secondary connection



Crimping Tool for Han-Fast® Lock contacts

Features

- Manual crimping tool for Han-Fast® Lock contacts for wire gauges of 4 mm², 6 mm² and 10 mm²
- Integrated locator guarantees precise contact alignment
- Balanced grip force and optimised handle design
- Built in interlock to ensure a complete crimping cycle
- Easy exchange of crimp dies
- High quality crimping

Technical characteristics

Specification	IEC 60 352-2
Dimensions	207.4 mm x 95.2 mm (length x diameter)
Wire gauge	4, 6 and 10 mm² AWG 12, 10 und 8
Wire retention force	4 mm² > 310 N 6 mm² > 360 N 10 mm² > 380 N


Identification

Part-Number

Depiction

Crimping tool Han-Fast® Lock

09 99 000 0831



Identification	Part-Number	Depiction
Removal tool for Han-Modular®		
plastic	09 99 000 0331	
metal	09 99 000 0828	
Suitable for	Part-Number	Depiction
Han-Modular® docking frame	09 14 0xx 1701 09 14 0xx 1711	The removal tool is applicable to the plastic frames and housings for the Han-Modular® series, Han-Yellock® adapter frames and Han-Eco® hoods / housings
Han-Yellock® adapter frame	11 00 x00 0101 11 00 x00 0301	
Han-Eco®	19 41 xxx xxxx	
Modules without plastic latches i.e. Han® GigaBit module Modules with plastic latches i.e. Han® Pneumatic module Double modules i.e. Han® 100 A Axial module		The removal tool can be used for all Han-Modular® modules. It is compatible to modules with and without plastic latches. for double modules please use 4 x 09 99 000 0331 or 2 x 09 99 000 0331 + 1 x 09 99 000 0828

Part-Number: 09 99 000 0833



Han® Torque Tool Set for High Current Axial Screw Contacts

Features

- Numerical, digital display of torque values
- Torque value can be set stepless by means of a torque-setter (included with delivery)
- Comfortable T-handle with soft zones for optimal torque transmission
- Audible click signal when the pre-set torque value has been attained
- Including factory calibration certificate
- Interchangeable blades made of high quality chrome-vanadium-molybdenum steel

Technical characteristics

- Tightening torque is variable between 5 and 14 Nm
- Torque accuracy: $\pm 6\%$
- Specifications: EN ISO 6789, BS EN 26789, ASME B107.14M.
- Dimensions: 273 x 153 mm (Length x Width)

Included with the set

- High quality metal box
- Variable tightening torque tool TorqueVario®-STplus*
- Setting tool: torque-setter
- HARTING optimised interchangeable blades hexagonal SW 4 and SW 5

Suitable for HARTING products

- Han® 200 A Axial module
- Han® 100 A Axial module
- Han® 100 A single module
- Han® K 3/0
- Han® K 3/2
- Han® K 6/6 (power contacts)
- Han® K 8/0 (power contacts)
- Han® HC Modular 350 Axial (up to 95 mm²)

* TorqueVario® is a registered trademark of Wiha Werkzeuge GmbH

Part-Number: 09 99 000 0834



Han® Torque Tool Set for Power Contacts

Features

- Torque value can be set via window scale
- Torque value can be set stepless by means of a torque-setter (included with delivery)
- Ergonomic multi-component handle, particularly light and compact
- Audible click signal when the pre-set torque value has been attained
- Including factory calibration certificate
- Interchangeable blades made of high quality chrome-vanadium-molybdenum steel

Technical characteristics

- Tightening torque is variable between 1 and 5 Nm
- Torque accuracy: $\pm 6\%$
- Specifications: EN ISO 6789, BS EN 26789, ASME B107.14M.
- Dimensions: 273 x 153 mm (Length x Width)

Included with the set

- High quality metal box
- Variable tightening torque tool TorqueVario®-S*
- Setting tool: torque-setter
- HARTING optimised interchangeable blades hexagonal SW 2 and SW 2.5
- Torque bit universal holder
- Bits: SW3, SW4, P 0, PH1, PH2, T10, T15, T20, slot 0.6 x 4.5, slot 0.8 x 4.5

Suitable for HARTING products

- Han® 70 A Axial module
- Han® 40 A Axial module
- Han® C Axial module
- Han® C Axial module
- Han® K 4/4 (power contacts)
- Han® K 6/12 (power contacts)

* TorqueVario® is a registered trademark of Wiha Werkzeuge GmbH

Part-Number: 09 99 000 0835



Han® Torque Tool Set for HARTING Screw Contacts and Fixing Screws

Features

- Precise torque value by means of a fixed torque value pre-set by the manufacturer
- Ergonomic multi-component handle, particularly light and compact
- Audible click signal when the pre-set torque value has been attained
- Including factory calibration certificate
- Interchangeable blades made of high quality chrome-vanadium-molybdenum steel

Technical characteristics

- Fixed torque value: 0.5 and 1.2 Nm
- Torque accuracy: $\pm 6\%$
- Specifications EN ISO 6789, BS EN 26789, ASME B107.14M.
- Dimensions: 273 x 153 mm (Length x Width)

Included with the set

- High quality metal box
- Two pre-set tightening torque screwdrivers TorqueFix®*
- Interchangeable blades PH1, PH2, slot 0.5 x 3.0

Suitable for HARTING products

- Han® 10 A – 32 A
- Han D® AV, Han E® AV,
- Han® K 6/6, K 6/12 (signal)
- Han® E
- Han Hv E®
- Han® HsB
- Han® fixing screws
- Han® PE contact: Han A®, Han E®, Han D®, Han DD®, K 8/24, K 6/6, K 8/0

* TorqueVario® is a registered trademark of Wiha Werkzeuge GmbH

Part-Number: 09 99 000 0836



Han® VDE Screw Driver Set

Features

- Safety when working with loaded equipment up to 1.000 V AC
- Tool complying with IEC security standards
- High quality chrome-vanadium-molybdenum steel, through-hardened, chrome-plated
- Protective insulation moulded directly onto the bit
- Ergonomic SoftFinish®* multi-component handle with roll off protection

Technical characteristics

- Specifications: DIN ISO 2380, DIN ISO 8764, manufactured acc. to IEC 60900:2004



- Dimensions (Tool length x diameter):
 0.4 x 2.5: 179 x 23 mm
 0.5 x 3.0: 204 x 23 mm
 0.6 x 3.5: 204 x 23 mm
 1.0 x 4.5: 236 x 30 mm
 PH1: 191 x 23 mm
 PH2: 218 x 23 mm

Range of delivery

- SoftFinish®* electric slim bit screw driver: 0.4 x 2.5, 0.5 x 3.0, 0.6 x 3.5, 1.0 x 4.5
- SoftFinish®* electric Phillips screw driver: PH1, PH2,

Suitable for HARTING products

- Han® A
- Han Staf®
- Han® D® AV, Han E® AV,
- Han® K 6/6, K 6/12 (signal)
- Han® E, Hv E®, Han® HsB
- Han® fixing screws
- Han® K 4/0 K 4/2 K 4/8 screw contacts
- Han® PE contacts: Han A®, Han E®, Han D®, Han DD®, K 8/24, K 6/6, K 8/0

* SoftFinish® is a registered trademark of Wiha Werkzeuge GmbH



Ha-VIS Middleware

Advantages

- Easy integration of HARTING RFID Reader
- Collecting any kind of tag information
- Filtering, grouping and aggregation based on various tag information
- Application flow triggered by manual, digital IO or scheduled events
- Report of cumulated data in standardized or customized formats
- Central RFID Reader management
- Advanced reading, writing, locking and muting of RFID transponders
- Import of data e. g. passwords from different sources like caches, association table or random values is supported
- Conform to EPCglobal® ALE 1.1.1 standard

General Description

The HARTING Ha-VIS Middleware is the intelligent software bridge between RFID Hardware and your company application. Scalable number of RFID Reader can easily be connected and configured. The connection is done with the connectors. Via configuration the Ha-VIS Middleware can filter, consolidate and group the raw data. The subscribers deliver the customized data to different sources/formats e. g. to files, databases or programmable interfaces. With the interface bidirectional interaction with the TAGs is easily realizable. The Ha-VIS Middleware Management is a client-software developed for configuration and management of the Middleware. For optimal functionality, the Ha-VIS middleware is delivered with service contract and training.

Identification	Part number	Drawing	Dimensions in mm
Ha-VIS Middleware		Connector RF-R500 up to 5 reader up to 15 reader up to 25 reader up to 50 reader	
incl XML subscriber and connector for one Ha-VIS RF-R500 RFID Reader	26 99 210 1110 00	Middleware Middleware including connector for one RF-R500 and XML subscriber	Subscribers XML file MySQL database http
Subscriber (Software side)			
MySQL Subscriber	26 99 220 4110 00		
http Subscriber	26 99 220 5110 00		
Connector (Hardware side)			
Connector for up to 5 RF-R500	26 99 230 1120 00		
Connector for up to 15 RF-R500	26 99 230 1130 00		
Connector for up to 25 RF-R500	26 99 230 1140 00		
Connector for up to 50 RF-R500	26 99 230 1150 00		
Connector for up to 5 RF-R200	26 99 230 3120 00*		
Connector for up to 15 RF-R200	26 99 230 3130 00*		
Connector for up to 25 RF-R200	26 99 230 3140 00*		
Connector for up to 50 RF-R200	26 99 230 3150 00*		
recommendation: Visit our special training			
optional: Installation and configuration service			
		Note Please specify which connector and which subscriber you need (each component has a separate part no.). If you only order the middleware (part no. 26 99 210 1110 00) you receive the middleware, the XML subscriber and a connector for one Ha-VIS RF-R500 RFID reader. For example, you order the middleware and an additional connector for the Ha-VIS RF-R500 with up to 15 reader, you are allowed to use 16 reader in total.	

* available quarter 3/2013

Technical characteristics

Functionality

- Simple connection and integration of HARTING RFID reader
- Data filtering, aggregation and grouping based on various tag data like PC, TID, user memory bank and user defined primary key.
- Easy reporting of new, current and deleted tags.
- Reducing the appearance of tags moving in and out of the reader field. (Tag Smoothing)
- Management of complex reader hierarchies with composite reader and antenna restriction support.
- Supporting read, write, lock and kill operations according to EPC Class-1 Generation-2
- Different ways to trigger report generation
 - On occurrence of digital Input and Output events.
 - On http trigger events.
 - Time controlled like time interval, time period or specific point of time.
 - Tag controlled like no new tags, first tag occurred or specific amount of processed tags.
- Easy management and configuration access with Ha-VIS Middleware Management

System requirements

- Operating System
 - Microsoft® Windows Server 2008 R2 64 Bit (recommended) or Windows 7 64 Bit
 - Software
 - Microsoft® .NET 3.5
 - Minimum hardware
 - Processor: 2 GHz 64 Bit Dual-Core
 - RAM: 4 GB or more
 - Disk space: 64 GB or more
- (Recommended hardware depends on customer application)

Architecture and concept

Middleware:


The middleware is the central data handling unit. Within the middleware, the data delivered from the connectors is filter, aggregated and grouped. The handled data can be consolidated and enriched with additional information.

Connector:

The connector bundles the full communication with the physical device. Changes in the hardware are fully handled by the connector without implications for the middleware. For every type of RFID reader, a different connector is needed.

Subscriber:

The subscriber delivers reports of the data processed by the middleware. There are different subscribers available for different output formats (e.g. XML). If a direct communication with another software is needed the http subscriber can be used.





Ha-VIS RFID RF-R200 Reader

Advantages

- One internal antenna (up to 30 cm)
- One external antenna (SMA)
- Flexible through large external antenna portfolio
- Power over Ethernet
- For distributed identification points
- Small size and DIN rail mounting
- Easy integration in machines or cabinets


General Description

The Ha-VIS RF-R200 is a cost-efficient mid range reader licensed according to ETSI, FCC und IC.

Due to its very compact design, the Ha-VIS RF-R200 is best suited for integration in machines as well as office applications

Characteristics:

- very compact
- can easily be integrated in machines
- internal antenna for applications with limited space
- one external antenna makes numerous application possible
- 0.5 W transmission power
- Power over Ethernet

Identification	Part number	Drawing	Dimensions in mm
Ha-VIS RFID RF-R200-PoE			
EU version	20 91 106 1101		
Ha-VIS RFID RF-R200-USB			
EU version	20 91 106 1102		
Ha-VIS RFID RF-R200-Serial module (no housing)			
EU version	20 91 106 1103		
Optional accessories			
DIN Rail mounting Kit for RF-R200	20 93 102 0202		
Mounting Kit (screwings)	20 93 102 0203		
Power supply	20 93 310 0203		

Technical characteristics

Transponder protocol	EPC class Gen2 (ISO 18000-6-c)
UHF RFID antenna interface	
Antenna connection	1 x SMA connector (50 Ohm); internally multiplexed; one internal antenna 3 x SMA connector (50 Ohm) RF-R200 (module) only
Transmitting Power	max. 0.5 W configurable
Frequency area	860 MHz ... 960 MHz (depending on specific reader)
Interfaces	- RF-R200 (PoE) Ethernet (TCP/IP) 10/100 Mbit/s; Full Spec. 802.3 - RF-R200 (module); RS 323 (serial)
Performance	
Max. Operating Distance	Up to 2 m, depending on transponder & environmental conditions
Protocol Modi	- Host Mode - Notification Mode (Ha-VIS RFID RF-R200-PoE only) - Scan Mode (Ha-VIS RFID RF-R200-USB only) - Buffered read mode
Power Supply	
Power supply	12 V ... 24 V DC
Power consumption	max. 7 W
Design features	
Dimensions (W x H x D)	145 x 85 x 27 mm
Degree of protection acc. to DIN 60 529	IP 30
Installation on DIN rail	DIN rail mounting kit (optional accessories)
Environmental conditions	
Operating temperature	-25 °C ... +45 °C (PoE) -25 °C ... +50 °C (USB)
Storage temperature	-25 °C ... +85 °C
Relative humidity	5 % ... 95 % (non-condensing)
Vibration	EN 60 068-2-6 10 Hz ... 150 Hz: 0.075 mm / 1 g
Shock	EN 60 068-2-27 Acceleration: 30 g

Technical characteristics

Norms & Safety

Radio license

- EN 302 208
- FCC 47 FCR Part 15
- IC RSS-GEN, RSS-210

EMC

EN 301 489

Safety

EN 60 950

RoHS compliant

Extras

- Internal overheating control
- Demo- and configuration software Ha-VIS RFID config

Management functions

Basic Functions

	Store and Forward Switching Mode	IEEE 802.3
	Manual and Dynamic IP Address Assignment	
Port-Settings	Auto-negotiation on / off	
	Port Speed 10 Mbit/s / 100 Mbit/s	
	Half / Full duplex	
	Port disable / enable	
	Link Up/Down Trap disable / enable	
	Flow Control disable / enable	
Network Discovery	Link Layer Discovery Protocol (LLDP)	802.1AB, 2005
Rate Control	Rate Control per port (Broadcast, Multicast, Unicast)	
File Transfer	Firmware import and export via TFTP and HTTP	
	Configuration import and export via TFTP and HTTP	
Time Settings	Manual time setting	
	Simple Network Time Protocol (SNTP)	RFC 1305, RFC 4330
User Management	Admin, Guest and Service Level	
Service	Service Mode via port 1	

PROFINET

	PROFINET IO Device Stack ¹⁾	
--	--	--

Time Synchronization

	Precision Time Protocol ¹⁾	IEEE 1588, 2008
--	---------------------------------------	-----------------

QoS

	Quality of Service (QoS)	IEEE 802.1p
	Differentiated services (DiffServ)	RFC 2474, 2475

VLAN

	Port protocol based VLANs VLAN ID Range: 1 – 4094 Max. Anzahl aktiver VLANs: 256	IEEE 802.1Q Rev D5.0, 2005
--	--	----------------------------

Redundancy

	Spanning Tree (STP)	IEEE 802.1D (2004)
	Rapid Spanning Tree (RSTP)	IEEE 802.1D (2004)
	Media redundancy protocol ^{1) 2)}	DIN EN 62 439-2

Security

	Port-Based Network Access Control Port Based Authentication with EAP	802.1X (2004)
	RADIUS Client	RFC 2138
	IP authorized manager	

Link Aggregation

	Link Aggregation (LACP)	IEEE 802.3ad (2005)
--	-------------------------	---------------------

Multicast

	IGMP Snooping (v1, v2, v3) with support for querier	RFC 1112, 2236, 3376
--	---	----------------------

Management functions

DHCP

	DHCP Client	RFC 2131
	DHCP relay agent	RFC 2131
	DHCP Option 82	RFC 3046

Alarm

	Alarms via E-mail (SMTP) and SNMP Traps	
	Signalling contact for low voltage detection or Link break	

Diagnostic

	Port diagnostic	
	Port Mirroring	
	Switch History	
	MAC Address Table	
	RMON (1,2,3 & 9 groups)	RFC 2819

Management

	Password protected Web-Management interface	
	SNMP (v1, v2c, v3) agent & MIB support	RFC 1155, 1157, 1212, 1213, 1215, 2089, 2578, 3411, 3412, 3413, 3414, 3415, 3416, 3417, 3584
	Command Line Interface (CLI)	
	Pluggable SD card for saving of configuration ¹⁾	
	Multifunction button ¹⁾	

¹⁾ ... Available for Ha-VIS mCon 3000 Next Generation

²⁾ ... Licensing via separately available SD card

Ethernet Switch
Ha-VIS mCon 3000 Next Generation
 Ethernet Switches, managed,
 for mounting onto top-hat mounting rail
 in control cabinets



General Description

The fully Managed Ethernet Switches of the product family Ha-VIS mCon 3000 enable the connection of up to 10 network devices (according to type) over RJ45 ports or SFP modules on lowest area.

Degree of protection, mechanical stability and the comprehensive management software provide for high operation safety and meet highest demands.

The Ha-VIS mCon 3000 Ethernet Switches are designed for an effective, industrial and individual use.

The configuraton via SD card or via the Multifunction button enables an easy and fast commisioning in the field.

Comprehensive possibilities of configuration and diagnostic are provided easy via web interface or standardized via SNMP.

The Ethernet Switches of the Ha-VIS mCon 3000 Next Generation family can be used as PROFINET IO devices.

Features

- Full managed Ethernet Switch acc. to IEEE 802.3
- Up to 10 ports, managed, non-blocking
- Store and Forward Switching Mode
- Gigabit Uplink ports, RJ45 and SFP modules
- Auto-crossing, Auto-negotiation, Auto-polarity
- Temperature range -40 °C ... +70 °C
- PROFINET IO device
- Time synchronization via IEEE 1588v2
- Multifunction button for fast commisioning
- SD card slot for storage of the configuration
- Management functions see pages 120 and 121

Advantages

- Small, robust metal housing
- External SD card for storage of the configuration
- Individual pre-configuration via Multifunction button
- Fast removable Ethernet data links via SFP „Hot-Swap“
- Optimised DIN rail fitting
- EMC, temperature range and mechanical stability meet the highest demands
- Universally applicable: PROFINET, Ethernet/IP or profile neutral

Application fields

- Industrial automation
- Automotive industry
- Wind power, Solar Power
- Maritime

Technical characteristics

Ethernet interface RJ45

Number of ports

Ha-VIS mCon 3080-A	8x 10/100Base-T(X)
Ha-VIS mCon 3102-AASFP	8x 10/100Base-T(X) 2x 10/100/1000Base-T(X) (Combo ports with SFP slot)

Cable types according to IEEE 802.3

Shielded Twisted Pair (STP) or Unshielded Twisted Pair (UTP), Category 5

Data rate

10 Mbit/s, 100 Mbit/s or 1000 Mbit/s (RJ45)

Maximum cable length

100 m (Twisted Pair; with Category 5 cable acc. to DIN EN 50 173-1)

Termination

RJ45 (Twisted Pair)

Diagnostics (via LED)

- Status Link – Green
- Data transfer (Act) – Green flashing
- Data transfer rate (Speed) – 1000 Mbit/s: Green
100 Mbit/s: Yellow
10 Mbit/s: OFF

Topology

Ring, Line, Star or mixed

Ethernet Interface SFP (mini-GBIC) Fibre Optic and copper

Number of ports

Ha-VIS mCon 3102-AASFP	2x 100/1000Base (Combo ports with SFP slot)
------------------------	---

Data rate

100 Mbit/s, 1000 Mbit/s

Termination

SFP modules according to MSA (Multi Source Agreement)
(see catalogue „HARTING Ethernet Network Solutions Automation IT“)

Diagnostics (via LED)

- Status Link – Green
- Data transfer (Act) – Green flashing

Power supply

Nominal input voltage

24/48 V DC ---

Termination

5-pole screw terminal, pluggable
for redundant power supply

Switch

Diagnostics (via LED)

- Device operates without failures – Green
- Power supply in the admissible range – Green
- Low voltage – Red
- Diagnostics failure – Red
- PROFINET failure / diagnosis – Red/Green flashing

Configuration

Slot for SD cards (back side)

- Saving and loading of configuration files
- Licence management for MRP

Multifunction button

Individual pre-configuration of software functions

Technical characteristics

Design features

Housing material	Aluminium, anodized
Dimensions (W x H x D)	44 x 130 x 100 mm (without connectors)
Degree of protection acc. to DIN 60529	IP 30
Mounting	• 35 mm top-hat rail acc. to EN 60715 • Panel mounting, vertical assembly

Environmental conditions

Operating temperature	–40 °C ... +70 °C
Storage temperature	–40 °C ... +85 °C
Relative humidity	10 % ... 95 % (non-condensing)

Management software

Full managed via web interface and SNMP
Range of functions and detailed description see pages 120 and 121

Ethernet Switch Ha-VIS mCon 3080-A

8-port Ethernet Switch, full managed
for mounting onto top-hat mounting rail in control cabinets



Managed

IP 30

PROFINET compatible ☒EtherNet/IP compatible ☒

Number of ports, Copper / Termination 8x 10/100Base-T(X) / RJ45 (Twisted Pair)

Nominal input voltage range 24/48 V DC ---

Permissible range (min/max) 12 V ... 60 V DC ---

Termination 5-pole screw terminal, pluggable redundant power supply

Input current approx. 130 mA (at 24 V ---)

Housing material Aluminium, anodized

Dimensions (W x H x D) 44 x 130 x 100 mm (without connectors)

Weight approx. 0.450 kg

Operating temperature -40 °C ... +70 °C

MTBF 678.372 h

Approvals (in preparation) UL 508; UL 60 950-1; DNV

Management fully Managed via Web interface and SNMP
Functions see pages 120 and 121

Identification

Part number

Drawing

Dimensions in mm

Ha-VIS mCon 3080-A



Ethernet Switch, full managed

8 RJ45 ports

including

Set for assembly on standard rail

20 76 108 4000





Ethernet Switch
Ha-VIS mCon 3102-AASFP

10-port Ethernet Switch with 2 ports Gigabit Ethernet, full managed for mounting onto top-hat mounting rail in control cabinets

Managed	IP 30	PROFINET compatible ☒	EtherNet/IP compatible ☒
Number of ports, Copper / Termination	8x 10/100Base-T(X) / RJ45 (Twisted Pair) 2x 10/100/1000Base-T(X) / RJ45 (Twisted Pair)		
Number of slots SFP / Termination	2x 100/1000Base / Combo ports		
Nominal input voltage range	24/48 V DC ---		
Permissible range (min/max)	12 V ... 60 V DC ---		
Termination	5-pole screw terminal, pluggable redundant power supply		
Input current	approx. 250 mA (at 24 V ---)		
Housing material	Aluminium, eloxiert		
Dimensions (W x H x D)	44 x 130 x 100 mm (incl. cap, without connectors)		
Weight	approx. 0.485 kg		
Operating temperature	-40 °C ... +70 °C		
MTBF	597.974 h		
Approvals (in preparation)	UL 508; UL 60 950-1; DNV		
Management	fully Managed via Web interface and SNMP Functions see pages 120 and 121		

Identification	Part number	Drawing	Dimensions in mm
Ha-VIS mCon 3102-AASFP Ethernet Switch, full managed 8 ports Fast Ethernet RJ45 2 ports Gigabit Ethernet (combo SFP) including Set for assembly on standard rail	20 76 112 4300		



Accessories

Ha-VIS Memory cards

The HARTING SD cards are used for saving the switch configuration. The web interface can be used to save the current configuration to the SD card.

If an SD card is inserted in the back of the switch, the switch will use the configuration saved on the card when it boots.

So it's quite easy when replacing a switch to transfer the entire configuration to the new switch. The old SD card with your current configuration is simply pushed into the new switch which then boots with these settings. No special network expertise is required.

Note: The HARTING Ethernet Switches are not compatible with conventional memory cards.

MRP memory cards allow you to activate the MRP functionality (media redundancy protocol) when using switches from the FTS 3000 and mCon 3000 series (with firmware ver. 3.0.0.1 and later). For example, in order to operate the device as an MRP slave, you need only have the corresponding MRP slave card inserted during operations.

Operating temperature -40 °C ... +70 °C

Memory space 128 MB

SD Memory cards

Configuration memory	20 89 900 1000
MRP Slave	20 89 900 1001
MRP Master	20 89 900 1002



Accessories

Ha-VIS SFP modules

General description

SFPs (Small Form-factor Pluggable) are small standardized modules for network connections.

These modules are a specification for a new generation of modular optical transceivers. The devices are constructed as connecting plugs for extremely quick network connections.

The SFPs are available in a variety of models, depending on the cable type (multi-mode or single-mode), the wave length (850 nm, 1300 nm, 1550 nm or CWDM), data rate or range.

Copper-based SFP are also available.

Features

- Highly flexible
- Easily swapped out in event of malfunction
- Hot swappable
- Variants:

	SM fibre	MM fibre
100 Mbit/s	X	X
1000 Mbit/s	X	X

Advantages

- SFP used as connecting plug for extremely quick network connections
- Standardized modules for network connections

Application fields

- Railway applications
- Industrial automation
- Automotive industry
- Wind power



Accessories

Ha-VIS SFP modules 100 Mbit/s

SFP:

Type	SFP Fast Ethernet Transceiver 155 Mbit/s MM	SFP Fast Ethernet Transceiver 155 Mbit/s SM	SFP Fast Ethernet Transceiver 155 Mbit/s SM	SFP Fast Ethernet Transceiver 155 Mbit/s SM
Wave length	1310 nm	1310 nm	1310 nm	1550 nm
Mode	Multimode	Singlemode	Singlemode	Singlemode
Fiber	50 / 125 µm or 62.5 / 125 µm	9 / 125 µm	9 / 125 µm	9 / 125 µm
Max. cable length*	2 km	15 km	40 km	80 km
Connector	LC connector duplex	LC connector duplex	LC connector duplex	LC connector duplex
Optical budget	min. 8.2 dB	min. 8.2 dB	min. 10 dB	min. 10 dB
Data rate	155 Mbit/s	155 Mbit/s	155 Mbit/s	155 Mbit/s

* Typical cable length depending on attenuation of each specific application.

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

SFP modules

SFP Fast Ethernet Transceiver 155 Mbit/s MM

20 76 000 0300

SFP Fast Ethernet Transceiver 155 Mbit/s SM

20 76 020 0300


SFP Fast Ethernet Transceiver L40 155 Mbit/s SM

20 76 024 0300

SFP Fast Ethernet Transceiver L80 155 Mbit/s SM

20 76 028 0300

other types on request






Accessories

Ha-VIS SFP modules 1000 Mbit/s

SFP:

Type	SFP Gigabit Ethernet Transceiver 1.25 Gbit/s MM	SFP Gigabit Ethernet Transceiver 1.25 Gbit/s SM	SFP Gigabit Ethernet Transceiver 1.25 Gbit/s SM	SFP Gigabit Ethernet Transceiver 1.25 Gbit/s SM
Wave length	850 nm	1310 nm	1310 nm	1310 nm
Mode	Multimode	Singlemode	Singlemode	Singlemode
Fiber	50 / 125 µm or 62.5 / 125 µm	9 / 125 µm	9 / 125 µm	9 / 125 µm
Max. cable length*	550 m (50 / 125) 275 m (62.5 / 125)	10 km	40 km	80 km
Connector	LC connector duplex	LC connector duplex	LC connector duplex	LC connector duplex
Optical budget	min. 9 dB	min. 9 dB	min. 9 dB	min. 9 dB
Data rate	1250 Mbit/s	1250 Mbit/s	1250 Mbit/s	1250 Mbit/s

* Typical cable length depending on attenuation of each specific application.

Identification	Part number	Drawing	Dimensions in mm
SFP modules			
SFP Gigabit Ethernet Transceiver 1,25 Gbit/s MM	20 76 010 0300		
SFP Gigabit Ethernet Transceiver 1,25 Gbit/s SM	20 76 030 0300		
SFP Gigabit Ethernet Transceiver L40 1,25 Gbit/s SM	20 76 034 0300		
SFP Gigabit Ethernet Transceiver L80 1,25 Gbit/s SM	20 76 038 0300		
other types on request			

Number of contacts 20-30

Contact spacing (mm) 2.54

Working current
see current carrying
capacity chart 2 A max.

Clearance ≥ 1.2 mm

Creepage ≥ 1.2 mm

Working voltage
The working voltage also depends
on the clearance and creepage
dimensions of the pcb itself,
and the associated wiring according to the safety regulations
of the equipment

Test voltage $U_{r.m.s.}$ 1 kV

Contact resistance ≤ 20 m Ω

Insulation resistance $\geq 10^{12}$ Ω

Temperature range
The higher temperature limit
includes the local ambient
and heating effects of the
contacts under load
During reflow soldering
– 55 °C ... + 125 °C
– 40 °C ... + 105 °C
for press-in connector
max. + 240 °C for 15 s
for SMC connectors

Electrical termination
Solder pins for pcb connections
 $\varnothing 1.0 \pm 0.1$ mm
according to IEC 60 326-3
wrap posts 0.6 x 0.6 mm
diagonal 0.79-0.86 mm
Compliant press-in
terminations
PCB thickness ≥ 1.6 mm
Recommended PCB holes
for press-in technology in acc. to EN 60 352-5


Insertion and withdrawal force
20way ≤ 20 N
30way ≤ 30 N

Materials
Mouldings Thermoplastic resin,
glass-fibre filled, UL 94-V0
Contacts Copper alloy
Contact surface
Contact zone Selectively plated according to
performance level

Current carrying capacity


The current carrying capacity is limited by maximum temperature of materials for inserts and contacts including terminals. The current capacity curve is valid for continuous, non interrupted current loaded contacts of connectors when simultaneous power on all contacts is given, without exceeding the maximum temperature.

Control and test procedures according to DIN IEC 60512



Number of contacts

20



Male connectors


Identification	Number of contacts	Contact arrangement	Part No. 3	Performance levels according to IEC 60603-2.	
				2	1
Male connector with solder pins 2.5 mm			Performance level 3 on request		Performance level 1 on request
with fixing flange	20			09 75 120 6902	
with fixing flange, SMC	20			09 75 120 6519 ^{d)}	
without fixing flange	20			09 75 120 6592	
without fixing flange, SMC	20			09 75 120 6569 ^{d)}	
Male connector with solder pins 4.0 mm					
with fixing flange	20			09 75 120 6903	
with fixing flange, SMC	20			09 75 120 6520 ^{d)}	
without fixing flange	20			09 75 120 6593	
without fixing flange, SMC	20			09 75 120 6570 ^{d)}	
Male connector with solder pins 13 mm					
with fixing flange	20			09 75 120 6577	
with fixing flange, SMC	20			09 75 120 6521 ^{d)}	
Male connector with wrap posts ¹⁾ 13 mm					
with fixing flange	20			09 75 120 6907	
Male connector with press-in pins 5.0 mm					
with fixing flange	20			09 75 120 6904	
without fixing flange	20			09 75 120 6504	
Male connector with press-in pins 13 mm					
with fixing flange	20			09 75 120 6985 09 75 120 6974•	
without fixing flange	20			09 75 120 6574•	

• Wrap posts for interfacing selectively gold plated (performance level 3)

¹⁾ To be used only for wire wrap termination^{d)} CTI > 400

Number of contacts

20




Male connectors

Identification


Drawing

Dimensions in mm


Dimensions



Panel cut out

Board drillings
Mounting side



	Y
Solder	1 ± 0.1

Cross section
of solder terminations

Cross area (A) of contacts
row a, b, c: A = 0.35 - 0.39 mm²

Other contact arrangements as well with lagging/leading pins on request

Number of contacts

30, 20




Male connectors

Identification	Number of contacts	Contact arrangement	Part No. 3	Performance levels according to IEC 60603-2. 2	1
Male connector with solder pins 2.5 mm	30		Performance level 3 on request	09 29 130 6902	Performance level 1 on request
with fixing flange	20			09 29 120 6902	
with fixing flange, SMC	30			09 29 130 6519 ^{d)}	
without fixing flange	30			09 29 130 6592	
without fixing flange, SMC	30			09 29 130 6569 ^{d)}	
Male connector with solder pins 4.0 mm	30			09 29 130 6903	
with fixing flange	20			09 29 120 6903	
with fixing flange, SMC	30			09 29 130 6520 ^{d)}	
without fixing flange	30			09 29 130 6593	
without fixing flange, SMC	30			09 29 130 6570 ^{d)}	
Male connector with solder pins 13 mm	30			09 29 130 6577	
with fixing flange	20			09 29 120 6577	
with fixing flange, SMC	30			09 29 130 6521 ^{d)}	
Male connector with wrap posts ¹⁾ 13 mm	30			09 29 130 6907	
Male connector with press-in pins 5.0 mm	30			09 29 130 6904	
with fixing flange	20			09 29 120 6904	
without fixing flange	30			09 29 130 6504	
Male connector with press-in pins 13 mm	30			09 29 130 6985 09 29 130 6974•	
with fixing flange	20			09 29 120 6974•	
without fixing flange	30			09 29 130 6574•	

• Wrap posts for interfacing selectively gold plated (performance level 3)

¹⁾ To be used only for wire wrap termination^{d)} CTI > 400

30, 20



Male connectors


135

Downloaded from Arrow.com.

Number of contacts


48

Pin shrouds
for type F “low profile”
with press-in pins 13 mm




Identification	pcb-thickness ± 10 %	Dimension X ± 0.1	Part No.
Pin shrouds			
Ⓘ with locking levers and press-in fixing	1.6 - 2.4	1.6	09 06 002 9902
Ⓘ without locking levers for screw fixing	1.6 - 2.4	1.6	09 06 002 9912
Ⓙ without locking levers with press-in nuts	1.6 - 2.4	1.6	09 06 002 9922
Ⓘ with locking levers and press-in fixing	3.2 - 4.0	0	09 06 002 9901
Ⓘ without locking levers for screw fixing	3.2 - 4.0	0	09 06 002 9911
Ⓙ without locking levers with press-in nuts	3.2 - 4.0	0	09 06 002 9921
Ⓚ Locking lever for female connector type F ¹⁾			09 06 001 9946

Dimensions,
valid for types
with locking lever
and for screw fixing



Dimensions in mm




Top entry hoods


Identification	No. of contacts	Part No.	Drawing	Dimensions in mm																				
Plastic hood with internal screen and knurled screws																								
Colour: Beige	14	60 13 014 0146 351 ¹⁾																						
	26	60 13 026 0146 351 ¹⁾																						
	36	60 13 036 0146 351 ¹⁾																						
Colour: Black	14	60 13 014 0146 110 ¹⁾																						
	26	60 13 026 0146 110 ¹⁾																						
	36	60 13 036 0146 110 ¹⁾																						
			<table border="1"> <thead> <tr> <th></th><th>a</th><th>b</th><th>c</th><th>d</th></tr> </thead> <tbody> <tr> <td>14</td><td>31.40</td><td>37.00</td><td>23.64</td><td>7.2</td></tr> <tr> <td>26</td><td>39.00</td><td>33.00</td><td>31.26</td><td>8.0</td></tr> <tr> <td>36</td><td>45.40</td><td>33.00</td><td>37.61</td><td>9.2</td></tr> </tbody> </table>		a	b	c	d	14	31.40	37.00	23.64	7.2	26	39.00	33.00	31.26	8.0	36	45.40	33.00	37.61	9.2	
	a	b	c	d																				
14	31.40	37.00	23.64	7.2																				
26	39.00	33.00	31.26	8.0																				
36	45.40	33.00	37.61	9.2																				

¹⁾ Temperature range: - 55 °C ... + 85 °C

Number of contacts	10
Approvals	IEC 61 076-4-107 UL recognized: E102079
Contact pitch	2 mm
Connector pitch	6 mm
Working current	1.5 A at 70 °C
Test voltage $U_{r.m.s.}$	750 V
Contact resistance	$\leq 35 \text{ m}\Omega$
Insulation resistance	$\geq 10^{10} \Omega$
Temperature range during reflow soldering	-55 °C ... +125 °C female: max. + 260 °C for 60 s
Mating cycles	250, performance level 2
Terminations	Insulation displacement (male), AWG 28/7 - 30/7, AWG 30 solid Solder buckets (male), AWG 24-30, outer insulation $\varnothing$ $5.33 \pm 0.25 \text{ mm}$ Solder pins for $\varnothing 0.6 \text{ mm}$ min. (female)
Insertion force	10 N max. / module
Withdrawal force	2 N min. / module (without locking levers)
Latching system	Locking levers
Materials	
Mouldings	Male connector: Polyester, UL 94-V0 Female connector: High temperature plastic material, UL 94-V0
Contacts	Copper alloy
Shells	Male connector: Stainless steel Female connector: Silver nickel
Contact surface	
Contact zone	Selectively gold-plated




Male connectors, straight
Female connectors, angled




Identification	No. of contacts	Colour	Part No.
Male connector for insulation displacement with solder buckets	10	Black	27 11 161 8001
	10	Black	27 11 122 2001
Female connector with solder pins	10	Beige (standard)	27 21 121 8000
	10	Red	27 21 121 8002
	10	Yellow	27 21 121 8004
	10	Green	27 21 121 8005
	10	Blue	27 21 121 8006
	10	Black	27 21 121 8010

Male connector
(delivered in piece parts)



Manuals for the *har-link*® cable free connector assemblies are available in our online catalogue *HARKIS*® or on demand at your local HARTING representative.




Female connector



Dimensions [mm]




Turned crimp contacts

Identification		Wire gauge (mm ²)	Part No.															
			Male contacts	Female contacts	High-end female contacts													
			Performance level 1*	Performance level 1*	Performance level 1*													
Individual contacts ¹⁾	AWG 22-18 0.33-0.82		09 67 000 3576	09 67 000 3476	09 67 000 3676													
	AWG 24-20 0.25-0.52		09 67 000 8576	09 67 000 8476	09 67 000 8676													
	AWG 26-22 0.13-0.33		09 67 000 5576	09 67 000 5476	09 67 000 5676													
	AWG 28-24 0.09-0.25		09 67 000 7576	09 67 000 7476	09 67 000 7676													
Male contacts																		
		<table><tr><td></td><td>a</td><td>groove</td></tr><tr><td>AWG 22-18</td><td>1.34</td><td>none</td></tr><tr><td>AWG 24-20</td><td>1.13</td><td>1</td></tr><tr><td>AWG 26-22</td><td>0.88</td><td>2</td></tr><tr><td>AWG 28-24</td><td>0.64</td><td>3</td></tr></table>					a	groove	AWG 22-18	1.34	none	AWG 24-20	1.13	1	AWG 26-22	0.88	2	AWG 28-24
	a	groove																
AWG 22-18	1.34	none																
AWG 24-20	1.13	1																
AWG 26-22	0.88	2																
AWG 28-24	0.64	3																
Female contacts		Standard																
		High-end with groove																

* Performance level 1 as per CECC 75301-802, 500 mating cycles, 10 days 4 mixed gas test – IEC 60512
Use crimp tool with the part no. 09 99 000 0501 and the locator with the part no. 09 99 000 0531.


Number of contacts	9, 15, 25, 37
Working current	5 A
Test voltage $U_{r.m.s.}$	1 kV
Clearance and creepage	≥ 1.0 mm
Contact resistance	< 25 m Ω
Insulation resistance	> 5 G Ω
Temperature range	as per profile JEDEC 020 D
Terminations	Solder pins for P.C.B. pads
Materials	
Mouldings	LCP black UL 94-V0
Contacts	Phosphorus bronze
Grounding die	Zamac
Shell	Steel
Contact surface	
Contact zone	selectively plated acc. to performance level ¹⁾
Grounding die	Pure tin
Shell	Nickel plated
Mating force	
	9 way ≤ 30 N 15 way ≤ 50 N 25 way ≤ 83 N 37 way ≤ 123 N

Contact arrangement View from termination side



M = Male connector
F = Female connector

Mating conditions as per DIN 41 652



¹⁾ Performance level 3, 50 mating cycles, no gas test

Performance level 2 as per CECC 75301-802, 250 mating cycles, 4 days 4 mixed gas test – IEC 60512

Number of contacts

9–37



SMT stamped solder pins, straight without grounding pins

Identification	No. of contacts	Part No.	
Performance levels Other performance levels on request 		Performance level 3	Performance level 2
Male connector metal shell with dimples	9 15 25 37	09 55 129 78 .. 741 09 55 229 78 .. 741 09 55 329 78 .. 741 09 55 429 78 .. 741	09 55 129 68 .. 741 09 55 229 68 .. 741 09 55 329 68 .. 741 09 55 429 68 .. 741
Female connector metal shell	9 15 25 37	09 55 115 76 .. 741 09 55 215 76 .. 741 09 55 315 76 .. 741 09 55 415 76 .. 741	09 55 115 66 .. 741 09 55 215 66 .. 741 09 55 315 66 .. 741 09 55 415 66 .. 741
Please insert digit for flange thread or fitted female screw locks M3 ► 11 4-40 UNC ► 12 fixed screw locks M3 ► 21 fixed screw locks 4-40 UNC ► 22			

Number of contacts

9–37




SMT stamped solder pins, straight without grounding pins

Identification


Drawing

Dimensions in mm


Male connector

M3 or 4-40 UNC non-removable fitted screw
locks M3 or 4-40 UNC

Female connector





pcb layout



	a	b	c	d
9	31.12	25.00	25.0	31.8
15	39.45	33.33	33.3	40.1
25	53.35	47.04	47.0	53.8
37	69.62	63.50	63.5	70.3

Packaging

(1 reel = 140 pieces)
Reel diameter = 380 mm

Number of contacts

9–37



SMT stamped solder pins, straight with grounding pins

Identification	No. of contacts	Part No.	
Performance levels Other performance levels on request 		Performance level 3	Performance level 2
Male connector metal shell with dimples	9 15 25 37	09 55 169 78 .. 741 09 55 269 78 .. 741 09 55 369 78 .. 741 09 55 469 78 .. 741	09 55 169 68 .. 741 09 55 269 68 .. 741 09 55 369 68 .. 741 09 55 469 68 .. 741
Female connector metal shell	9 15 25 37	09 55 155 76 .. 741 09 55 255 76 .. 741 09 55 355 76 .. 741 09 55 455 76 .. 741	09 55 155 66 .. 741 09 55 255 66 .. 741 09 55 355 66 .. 741 09 55 455 66 .. 741
Please insert digit for flange thread or fitted female screw locks M3 ► 11 4-40 UNC ► 12 fixed screw locks M3 ► 21 fixed screw locks 4-40 UNC ► 22			

Number of contacts

9–37

SMT stamped solder pins, straight with grounding pins




Identification


Drawing

Dimensions in mm


Male connector

M3 or 4-40 UNC non-removable fitted screw
locks M3 or 4-40 UNC

Female connector





pcb layout




PCB layout, component side

	a	b	c	d
9	31.12	25.00	25.0	31.8
15	39.45	33.33	33.3	40.1
25	53.35	47.04	47.0	53.8
37	69.62	63.50	63.5	70.3

Packaging

(1 reel = 140 pieces)
Reel diameter = 380 mm

Cables for insulation displacement termination

Identification	No. of contacts	Part No.	Drawing	Dimensions in mm
Flat cable grey non-halogenated UL style 21447 for VW-1				
	6	09 18 006 700 □ 900		
	9	09 18 009 700 □ 900		
	10	09 18 010 700 □ 900		
	14	09 18 014 700 □ 900		
	15	09 18 015 700 □ 900		
	16	09 18 016 700 □ 900		
	18	09 18 018 700 □ 900		
	20	09 18 020 700 □ 900		
	24	09 18 024 700 □ 900		
	25	09 18 025 700 □ 900		
	26	09 18 026 700 □ 900		
	28	09 18 028 700 □ 900		
	34	09 18 034 700 □ 900		
	37	09 18 037 700 □ 900		
	40	09 18 040 700 □ 900		
	50	09 18 050 700 □ 900		
	60	09 18 060 700 □ 900		
	64	09 18 064 700 □ 900		
Length per reel				
30.48 m (100 feet)	1			
			Conductor material _____ Copper tinned Gauge _____ AWG 28/7 0.089 mm ² Voltage rating _____ 300 V _{r.m.s.} Current rating _____ 1.3 A Capacity unbalanced _____ 42.6 pF/m at 1 MHz Impedance unbalanced _____ 100 Ω Inductance _____ 0.56 μH/m Propagation delay _____ 4.8 ns/m Insulation material _____ Non-halogenated flame retardent Polyolefin Temperature rating _____ -40 °C ... +80 °C Insulation resistance _____ 10000 MΩ/km	

Ha-VIS data bus cable
2-wire, elastic



Advantages

- Halogen free
- Electron-beam cross-linked cable
- Improved fire performance
- High resistance to temperature
- Conform to MVB standard according IEC 61375-3-1

Applications

For fixed and moveable installation inside and outside of rail vehicles and buses. For symmetrical signal and data transmission with impedance of 120 Ohm. Suitable for use in MVB (Multifunction Vehicle Bus) as part of the TCN (Train Communication Network). Especially designed for termination with HARTING D-Sub InduCom and Han-Quintax® and other railway-specific Han® connectors and housings.

Identification

Part No.

Ha-VIS data bus cable
2-wire, elastic

Sheath material:

Elastomer, electron-beam cross-linked,
COMP 603

Color: black

Nominal voltage: 300 V

Testing voltage:

conductor/conductor 2 kV AC
conductor/shielding 2 kV AC

Maximum conductor

resistance at 20 °C: < 40.1 mΩ / m

Impedance at

0.75 – 3 MHz: 120 Ω ±12 Ω

Transfer impedance

at 20 MHz: ≤ 20 mΩ / m

Attenuation:

1 MHz: ≤ 12 dB / km

3 MHz: ≤ 17 dB / km

4 MHz: ≤ 22 dB / km

Maximum conductor temperature:

fixed installed -40 °C ... +90 °C

short circuit +160 °C

Minimum bending radius:

fixed installed > 6 x diameter

Cable sheath diameter: (Ø 7.8 ± 0.2) mm


Cable weight: 77 kg / km

100 m ring

500 m drum

09 45 600 0160

09 45 600 0170



1. Pair

Conductor: tinned copper strands according to VDE 0295 / IEC 60228 class 5 construction 16 x 0.20 mm, Ø 0.85 mm

Insulation: Polyethylene (PE), electron-beam cross-linked, Comp 655 Ø 2.85 mm

colors: red, blue

2. Filler

3. Wrapping

Plastic tape

4. Shielding

Tinned fine copper braid, Ø 6.4 mm

5. Jacket

Elastomer electron-beam cross-linked Comp 603, Ø 7.8 mm

Color: black

Ha-VIS data bus cable
2-wire, elastic



Advantages

- Halogen free
- Electron-beam cross-linked cable
- Improved fire performance
- High resistance to temperature
- Conform to UIC 558 standard
- Conform to WTB standard according IEC 61375-2-1

Applications

For fixed and moveable installation inside and outside of rail vehicles and buses. For symmetrical signal and data transmission with impedance of 120 Ohm. Suitable for use in WTB (Wire Train Bus) as part of the TCN (Train Communication Network) according UIC 558.

Especially designed for termination with HARTING D-Sub InduCom and Han-Quintax® and other railway- specific Han® connectors and housings.

Identification

Part No.

Ha-VIS data bus cable
2-wire, elastic

Sheath material:

Elastomer, electron-beam cross-linked,
COMP 603

Color: black

Nominal voltage: 300 V

Testing voltage:

conductor/conductor 2 kV AC

conductor/shielding 2 kV AC

Maximum conductor
resistance at 20 °C: < 26.7 mΩ / m

Capacitance at 1 MHz:

wire/wire: < 65 pF / m

wire/screen: < 120 pF / m

Impedance at
0.75 – 3 MHz: 120 Ω ±12 Ω

Transfer impedance
at 30 MHz: ≤ 30 mΩ / m

Attenuation:

1 MHz: ≤ 10 dB / km

4 MHz: ≤ 14 dB / km

5 MHz: ≤ 18 dB / km

Maximum conductor temperature:

fixed installed -40 °C ... +90 °C

short circuit +160 °C

Minimum bending radius:

fixed installed > 6 x diameter

Cable sheath diameter: (Ø 9.7 ± 0.2) mm


Cable weight: 106 kg / km

500 m drum

1000 m drum

09 45 600 0180

09 45 600 0190



1. Pair

Conductor: tinned copper strands according to VDE 0295 / IEC 60228 class 5 construction 24 x 0.20 mm, Ø 1.1 mm

Insulation: Polyethylene (PE), electron-beam cross-linked, Comp 655 Ø 3.9 mm

colors: black, white

2. Filler

Polyolefine copolymer

3. Wrapping

Plastic tape

4. Shielding

Tinned fine copper braid, Ø 8.5 mm

5. Jacket

Elastomer electron-beam cross-linked Comp 603, Ø 9.7 mm

Color: black

Ha-VIS data bus cable
2-wire FOAM, elastic



Advantages

- Halogen free
- Electron-beam cross-linked cable
- Improved fire performance
- High resistance to temperature
- Reduced outer diameter
- Conform to UIC 558 standard
- Conform to WTB standard according IEC 61375-2-1

Applications

Primary for fixed but also moveable installation inside and outside of rail vehicles and buses. For symmetrical signal and data transmission with impedance of 120 Ohm. Suitable for use in WTB (Wire Train Bus) as part of the TCN (Train Communication Network) according UIC 558. Especially designed for termination with HARTING D-Sub InduCom and Han-Quintax® and other railway-specific Han® connectors and housings.

Identification

Part No.

Ha-VIS data bus cable
2-wire FOAM, elastic

Sheath material:

Elastomer, electron-beam cross-linked,
COMP 603

Color: black

Nominal voltage: 300 V

Testing voltage:

conductor/conductor 1.5 kV AC
conductor/shielding 1.5 kV AC

Maximum conductor
resistance at 20 °C: < 26.7 mΩ / m

Capacitance at 1 MHz:

wire/wire: < 65 pF / m
wire/screen: < 120 pF / m

Impedance at
0.5 – 2 MHz: 120 Ω ±12 Ω

Transfer impedance
at 30 MHz: ≤ 30 mΩ / m

Attenuation:

1 MHz: ≤ 10 dB / km
2 MHz: ≤ 14 dB / km

Maximum conductor temperature:

fixed installed -25 °C ... +90 °C
temperature load
sporadically
temporary +100 °C

Minimum bending radius:


fixed installed > 6 x diameter

Cable sheath diameter: (Ø 8.0 ± 0.2) mm

Cable weight: 79 kg / km

500 m drum
1000 m drum

09 45 600 0181
09 45 600 0191



1. Pair

Conductor: tinned copper strands construction 19 x 0.20 mm, Ø 1.1 mm

Insulation: foam-skin polyolefin Ø 2.7mm

colors: black, white

2. Filler

Polyolefine copolymer

3. Wrapping

Plastic tape


4. Shielding

Tinned fine copper braid, Ø 6.4 mm

5. Jacket

Elastomer electron-beam cross-linked Comp 603, Ø 8.0 mm

Color: black



PROFINET 4TP type A cable 8 wires, Cat. 6_A, PVC

For fixed laying or to build up PROFINET system cables

Technical characteristics

Cable construction:	4 x 2, twisted pair, shielded, PIMF
Conductor construction:	4 x 2 x AWG 23/1, solid copper
Conductor insulation:	PE Ø 1.4 mm
Sheath material:	PVC
Cable diameter:	7.9 mm
Transmission performance:	Category 6 _A / class E _A up to 500 MHz Acc. to ISO/IEC 11 801:2002, EN 50 173-1
Transmission rate:	10/100 Mbit/s, 1/10 Gbit/s
Shielding:	Twisted shielding and additional overall shielding
Temperature range:	-20 °C ... +60 °C
Standard length:	20 m / 50 m / 100 m / 500 m
Colour:	Green
Printing:	HARTING specific printing
Advantages:	• Robust design • PROFINET conform • RoHS conform • Flame retardant

Identification

Part number

Drawing


PROFINET 4TP type A cable
8 wires, Cat. 6_A, PVC, green

20 m	ring
50 m	ring
100 m	ring
500 m	drum

09 45 600 1200
09 45 600 1210
09 45 600 1220
09 45 600 1230



- Conductor: Solid copper AWG 23/1



PROFINET 4TP type B cable
8 wires, Cat. 6_A, PVC

For flexible laying or to build up PROFINET system cables

Technical characteristics

Cable construction:	4 x 2, twisted pair, shielded, PIMF
Conductor construction:	4 x 2 x AWG 23/7, stranded tinned copper braid
Conductor insulation:	PE Ø 1.59 mm
Sheath material:	PVC
Cable diameter:	8.7 mm
Transmission performance:	Category 6 _A / class E _A up to 500 MHz Acc. to ISO/IEC 11 801:2002, EN 50 173-1
Transmission rate:	10/100 Mbit/s, 1/10 Gbit/s
Shielding:	Twisted shielding and additional overall shielding
Temperature range:	-40 °C ... +80 °C
Standard length:	20 m / 50 m / 100 m / 500 m
Colour:	Green
Printing:	HARTING specific printing
Advantages:	• Robust design • PROFINET conform • RoHS conform • Flame retardant

Identification


Part number

Drawing

PROFINET 4TP type B cable
8 wires, Cat. 6_A, PVC, green


20 m	ring
50 m	ring
100 m	ring
500 m	drum

09 45 600 1211
09 45 600 1221
09 45 600 1231
09 45 600 1241



- Conductor: Stranded tinned copper braid
4x2xAWG 23/7



Identification	Part No.	Drawing	Dimensions in mm
Fibre optic cable, double ended, single mode Han® SFP LC duplex to LC duplex Length: a = 1.0 m a = 2.0 m a = 5.0 m a = 10.0 m a = 15.0 m a = 20.0 m	33 54 451 0010 010 33 54 451 0020 010 33 54 451 0050 010 33 54 451 0100 010 33 54 451 0150 010 33 54 451 0200 010	double ended  a = length	
Fibre optic cable, double ended, multi mode 50/125 µm Han® SFP LC duplex to LC duplex Length: a = 1.0 m a = 2.0 m a = 5.0 m a = 10.0 m a = 15.0 m a = 20.0 m	33 54 451 0010 012 33 54 451 0020 012 33 54 451 0050 012 33 54 451 0100 012 33 54 451 0150 012 33 54 451 0200 012		
Fibre optic cable, double ended, multi mode 62.5/125 µm Han® SFP LC duplex to LC duplex Length: a = 1.0 m a = 2.0 m a = 5.0 m a = 10.0 m a = 15.0 m a = 20.0 m	33 54 451 0010 007 33 54 451 0020 007 33 54 451 0050 007 33 54 451 0100 007 33 54 451 0150 007 33 54 451 0200 007		



Advantages

- For blind mating on various optical SFP transceivers
- Direct compensation of largest transceiver tolerances
- Direct connection to SFP transceivers
- Mechanical keying – no mismatching possible

Technical characteristics

Degree of protection	IP 65 / IP 67
Mating face	LC acc. to IEC 61 754-20
Mating cycles	50
Temperature range	-40 °C ... +85 °C
Housing material	Zinc die-cast, powder coating black
Glas optical fibre	Single mode, multi mode 50/125 and multi mode 62.5/125

Identification

Part No.

Drawing

Dimensions in mm


Han® SFP

Receptacle housing
device side

09 57 474 0500 001

Assembly aid

09 57 000 0000 200





preLink® Extender

Application

- Structured cabling for industrial premises
- Extension of cables for data communication
- Connection of cables with different cross-sections
- Linking of fire compartments

Advantages

- preLink® termination
- Simple, fast and reliable connection of data cables
- Flexible in the application
- Future proof, Category 6A, transmission rate up to 10 Gbit/s

Identification

Part No.



Drawing

Dimensions in mm

preLink® Extender

Wire termination: Ha-VIS preLink®
 Number of contacts: 8
 Transmission: Cat. 6A
 Transmission rate: 10 Gbit/s
 Shielding: fully shielded 360°
 flexible shielding termination
 Cable diameter: Ø 5 – 9 mm
 Wire cross-section: AWG22 ... AWG27
 Single wire diameter: Ø 0.8 mm ... 1.6 mm
 depending on termination module
 Degree of protection: IP 20
 Operating temperature range: -40 °C ... +70 °C
 Housing material: zinc die-cast,
 nickel plated

20 82 101 0001




preLink® terminal module

(package with 10 pcs.)
 Contact block with IDC termination

Number of contacts: 8


Wire cross-section: AWG 22/23 (24)
 solid and stranded
 Single wire diameter: Ø 1.3 – 1.6 mm
 Colour: yellow

20 82 000 0001



Wire cross-section: AWG 26/27
 solid and stranded
 Single wire diameter: Ø 0.8 – 1.1 mm
 Colour: white

20 82 000 0003





HARTING RJ Industrial® RJ45 jacks with transformer

Advantages

- Compact design
- Integrated optical fibres
- Excellent EMC behaviour due to integrated transformers and filters for 10/100 Mbit or 1 Gbit Ethernet
- SMC compatible
- Versions from 10/100 Mbit up to 10 Gbit Ethernet and PoE

Technical characteristics

Mating face	RJ45 acc. to IEC 60603-7
Number of contacts	8
Degree of protection	IP 20
Rated voltage	30 V DC
Rated current	8 mA DC
Mating cycles	min. 750
Temperature range	-25 °C ... +70 °C

Identification

Part No.

Drawing


Dimensions in mm

Components device side

RJ45 jack with transformer (low profile)


90° angled, THT
10/100 Mbit Ethernet
10/100 Mbit Ethernet and PoE

Schematic:



90° angled, THT
1 Gbit Ethernet
1 Gbit Ethernet and PoE

Schematic:




90° angled, THT
10 Gbit Ethernet

09 45 551 1130¹⁾
09 45 551 1131¹⁾

09 45 551 1530¹⁾
09 45 551 1531¹⁾

09 45 551 1560¹⁾



Customer specific versions on request

¹⁾ Packaging: Blister à 56 pieces




Identification	Part No.	Drawing	Dimensions in mm
----------------	----------	---------	------------------

har-speed M12
adapter M12-RJ45


straight, Cat. 6A

21 03 381 2800




angled, Cat. 6A

21 03 381 4800



Gender changer, Cat. 6A


21 03 381 6815



Circular connector slim design M12




Identification	Part No.	Drawing	Dimensions in mm
har-speed M12 8 poles, X-coded, Cat. 6A Cable: 4.4 - 8.8 mm outer diameter	21 03 881 1804		
har-speed M12 Crimp 5 poles, A-coded Cable: 4.4 - 8.8 mm outer diameter	21 03 881 1505		
4 poles, D-coded Cable: 4.4 - 8.8 mm outer diameter	21 03 881 1405		



PCB connectors with IDC termination
for SMT reflow soldering
pitch 1.27 mm

Identification	No. of contacts	Part No.	Packaging unit
PCB connectors with IDC termination			
Female	4	14 31 041 0301 000	50
Male	4	14 11 041 0002 000	560




PCB connectors with IDC termination
for SMT reflow soldering
pitch 1.27 mm

Drawing

Dimensions in mm

Dimensions



Technical characteristics

Technical data

Rated current 2 A
Pitch 1.27 mm

Surge voltage category /
pollution degree

Rated voltage
Rated surge voltage

III/3	III/2	II/2
—	—	16 V
—	—	0.5 kV


Conductor data

Connection technology wire IDC termination
Conductor size solid / stranded — / 0.05 - 0.14 mm²
Conductor size AWG 28 - 26
Stripping length 0 mm

Material data


Group of insulation material III a
Type of insulation material LCP
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +125 °C
Contact material Copper alloy
Contact plating Nickel plated

PCB terminal blocks,
vertical/horizontal
with push-in-spring-cage termination
for SMT reflow soldering
pitch 2.54 mm



Identification	No. of contacts	Part No.		Packaging unit
PCB terminal blocks, vertical/horizontal with push-in-spring-cage termination				vertical / horizontal
	2	14 01 021 310		250 / 500
	3	14 01 031 310		250 / 500
	4	14 01 041 310		250 / 500
	5	14 01 051 310		250 / 500
	6	14 01 061 310		250 / 500
	7	14 01 071 310		250 / 500
	8	14 01 081 310		250 / 500
	9	14 01 091 310		250 / 500
	10	14 01 101 310		250 / 500
	11	14 01 111 310		250 / 500
	12	14 01 121 310		250 / 500
Please insert digit for				
vertical ►		1		
horizontal ►		2		


PCB terminal blocks,
vertical/horizontal
with push-in-spring-cage termination
for SMT reflow soldering
pitch 2.54 mm



Drawing

Dimensions in mm

Dimensions



Technical characteristics

Technical data

Rated current 6 A
Pitch 2.54 mm

Surge voltage category /
pollution degree

Rated voltage
Rated surge voltage

III/3	III/2	II/2
32 V	160 V	160 V
2.5 kV	2.5 kV	2.5 kV

Material data

Group of insulation material III a
Type of insulation material LCP
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +125 °C
Contact material copper alloy
Contact plating tin plated

Conductor data

Connection technology wire push-in-spring-cage
termination
Conductor size solid / stranded 0.14 - 0.5 / 0.2 - 0.5 mm²
Conductor size AWG 24 - 20
Stripping length 6 mm

PCB connectors female,
vertical
with push-in-spring-cage termination
pitch 2.54 mm



Identification	No. of contacts	Part No.	Packaging unit
PCB connectors female, vertical with push-in-spring-cage termination			
	2	14 31 021 3101 000	200
	3	14 31 031 3101 000	200
	4	14 31 041 3101 000	200
	5	14 31 051 3101 000	150
	6	14 31 061 3101 000	150
	7	14 31 071 3101 000	150
	8	14 31 081 3101 000	100
	9	14 31 091 3101 000	100
	10	14 31 101 3101 000	100
	11	14 31 111 3101 000	50
	12	14 31 121 3101 000	50


PCB connectors female,
vertical
with push-in-spring-cage termination
pitch 2.54 mm



Drawing

Dimensions in mm

Dimensions



L = pitch x (poles - 1)

Technical characteristics

Technical data

Rated current 6 A
Pitch 2.54 mm

Surge voltage category /
pollution degree

Rated voltage
Rated surge voltage

III/3	III/2	II/2
32 V	160 V	160 V
2.5 kV	2.5 kV	2.5 kV

Material data

Group of insulation material III a
Type of insulation material LCP
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +125 °C
Contact material copper alloy
Contact plating tin plated

Conductor data

Connection technology wire push-in-spring-cage
termination
Conductor size solid / stranded 0.14 - 0.5 / 0.2 - 0.5 mm²
Conductor size AWG 24 - 20
Stripping length 6 mm

PCB connectors male,
vertical/horizontal
for SMT reflow soldering
pitch 2.54 mm



Identification	No. of contacts	Part No.			Packaging unit
PCB connectors male, vertical/horizontal					vertical / horizontal
	2	14 11 021 300			500 / 600
	3	14 11 031 300			500 / 600
	4	14 11 041 300			500 / 600
	5	14 11 051 300			500 / 600
	6	14 11 061 300			500 / 600
	7	14 11 071 300			500 / 600
	8	14 11 081 300			500 / 600
	9	14 11 091 300			500 / 600
	10	14 11 101 300			500 / 600
	11	14 11 111 300			500 / 600
	12	14 11 121 300			500 / 600
Please insert digit for					
vertical ►		1			
horizontal ►		2			


PCB connectors male,
vertical/horizontal
for SMT reflow soldering
pitch 2.54 mm



Drawing

Dimensions in mm

Dimensions



Technical characteristics

Technical data

Rated current 6 A
Pitch 2.54 mm

Surge voltage category /
pollution degree

Rated voltage


Rated surge voltage

III/3	III/2	II/2
32 V	160 V	160 V
2.5 kV	2.5 kV	2.5 kV

Material data

Group of insulation material III a
Type of insulation material LCP
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +125 °C
Contact material copper alloy
Contact plating tin plated

PCB terminal blocks,
vertical with push-in-spring-cage
termination
pitch 3.50 / 3.81 mm



Identification	No. of contacts	Part No.	Packaging unit
----------------	-----------------	----------	----------------


PCB terminal blocks,
vertical with push-in-spring-cage
termination

2	14 02 021 . 101 000	300
3	14 02 031 . 101 000	200
4	14 02 041 . 101 000	150
5	14 02 051 . 101 000	150
6	14 02 061 . 101 000	100
7	14 02 071 . 101 000	100
8	14 02 081 . 101 000	100
9	14 02 091 . 101 000	100
10	14 02 101 . 101 000	100
11	14 02 111 . 101 000	100
12	14 02 121 . 101 000	100
13	14 02 131 . 101 000	50
14	14 02 141 . 101 000	50
15	14 02 151 . 101 000	50
16	14 02 161 . 101 000	50

Please insert digit for

pitch 3.50 mm ► 4
pitch 3.81 mm ► 5


PCB terminal blocks,
vertical with push-in-spring-cage termination
for reflow soldering
pitch 3.50 / 3.81 mm



Drawing

Dimensions in mm

Dimensions



L = pitch x poles
a = pitch x (poles - 1)

Technical characteristics

Technical data

Rated current 10 A
Pitch 3.50 mm / 3.81 mm

Surge voltage category /
pollution degree

Rated voltage
Rated surge voltage

III/3	III/2	II/2
220 V	300 V	600 V
4 kV	4 kV	4 kV

Material data

Group of insulation material I
Type of insulation material PA / PPA
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +110 °C
Contact material copper alloy
Contact plating tin plated

Conductor and solder pin data

Connection technology wire push-in-spring-cage termination
Conductor size solid / stranded 0.14 - 1.5 / 0.14 - 1.5 mm²
Conductor size AWG 30 - 16
Stripping length 9 - 10 mm
Solder pin: drilled hole diameter 1.4 mm



PCB terminal blocks,
horizontal with screw termination
for reflow soldering
pitch 3.50 / 3.81 mm

Identification	No. of contacts	Part No.	Packaging unit
----------------	-----------------	----------	----------------

PCB terminal blocks,
horizontal with screw termination

2	14 02 021 . 402 000	300
3	14 02 031 . 402 000	200
4	14 02 041 . 402 000	150
5	14 02 051 . 402 000	150
6	14 02 061 . 402 000	100
7	14 02 071 . 402 000	100
8	14 02 081 . 402 000	100
9	14 02 091 . 402 000	100
10	14 02 101 . 402 000	100
11	14 02 111 . 402 000	100
12	14 02 121 . 402 000	100

Please insert digit for

pitch 3.50 mm ► 4
pitch 3.81 mm ► 5


PCB terminal blocks,
horizontal with screw termination
for reflow soldering
pitch 3.50 / 3.81 mm



Drawing

Dimensions in mm

Dimensions



L = pitch x poles
a = pitch x (poles - 1)

Technical characteristics

Technical data

Rated current 12 A
Pitch 3.50 mm / 3.81 mm

Surge voltage category /
pollution degree

Rated voltage
Rated surge voltage

III/3	III/2	II/2
150 V	150 V	300 V
2.5 kV	2.5 kV	2.5 kV


Material data

Group of insulation material I
Type of insulation material PA / PPA
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +110 °C
Contact material copper alloy
Contact plating tin plated

Conductor and solder pin data

Connection technology wire screw termination
Conductor size solid / stranded 0.05 - 1.5 / 0.05 - 1 mm²
Conductor size AWG 28 - 16
Screw thread M2
Tightening torque 0.2 - 0.25 Nm
Stripping length 5 - 6 mm
Solder pin: drilled hole diameter 1.1 mm

PCB connectors female,
horizontal
with push-in-spring-cage termination
pitch 3.50 / 3.81 mm



Identification	No. of contacts	Part No.	Packaging unit
----------------	-----------------	----------	----------------


PCB connectors female,
horizontal
with push-in-spring-cage
termination

2	14 31 021 . 102 000	300
3	14 31 031 . 102 000	200
4	14 31 041 . 102 000	150
5	14 31 051 . 102 000	150
6	14 31 061 . 102 000	100
7	14 31 071 . 102 000	100
8	14 31 081 . 102 000	100
9	14 31 091 . 102 000	100
10	14 31 101 . 102 000	100
11	14 31 111 . 102 000	100
12	14 31 121 . 102 000	100
13	14 31 131 . 102 000	50
14	14 31 141 . 102 000	50
15	14 31 151 . 102 000	50
16	14 31 161 . 102 000	50
17	14 31 171 . 102 000	50
18	14 31 181 . 102 000	50
19	14 31 191 . 102 000	50
20	14 31 201 . 102 000	50
21*	14 31 211 . 102 000	25
22*	14 31 221 . 102 000	25
23*	14 31 231 . 102 000	25
24*	14 31 241 . 102 000	25
25*	14 31 251 . 102 000	25

Please insert digit for

pitch 3.50 mm ► 4
pitch 3.81 mm ► 5




PCB connectors female,
horizontal
with push-in-spring-cage termination
pitch 3.50 / 3.81 mm



Drawing

Dimensions in mm

Dimensions



L = pitch x poles
a = pitch x (poles - 1)

Technical characteristics

Technical data

Rated current 11 A
Pitch 3.50 mm / 3.81 mm

Surge voltage category /
pollution degree

Rated voltage
Rated surge voltage

III/3	III/2	II/2
150 V	150 V	300 V
2.5 kV	2.5 kV	2.5 kV


Material data

Group of insulation material I
Type of insulation material PA / PPA
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +110 °C
Contact material copper alloy
Contact plating tin plated

Conductor data

Connection technology wire push-in-spring-cage
termination
Conductor size solid / stranded 0.14 - 1.5 / 0.14 - 1.5 mm²
Conductor size AWG 30 - 14
Stripping length 9 - 10 mm


PCB connectors female,
vertical/horizontal
with screw termination
pitch 3.50 / 3.81 mm



Identification	No. of contacts	Part No.	Packaging unit
PCB connectors female, vertical/horizontal with screw termination			
	2	14 31 021 . 40 . 000	300
	3	14 31 031 . 40 . 000	200
	4	14 31 041 . 40 . 000	150
	5	14 31 051 . 40 . 000	150
	6	14 31 061 . 40 . 000	100
	7	14 31 071 . 40 . 000	100
	8	14 31 081 . 40 . 000	100
	9	14 31 091 . 40 . 000	100
	10	14 31 101 . 40 . 000	100
	11	14 31 111 . 40 . 000	100
	12	14 31 121 . 40 . 000	100
	13	14 31 131 . 40 . 000	50
	14	14 31 141 . 40 . 000	50
	15	14 31 151 . 40 . 000	50
	16	14 31 161 . 40 . 000	50
	17*	14 31 171 . 40 . 000	50
	18*	14 31 181 . 40 . 000	50
	19*	14 31 191 . 40 . 000	50
	20*	14 31 201 . 40 . 000	50
	21*	14 31 211 . 40 . 000	25
	22*	14 31 221 . 40 . 000	25
	23*	14 31 231 . 40 . 000	25
	24*	14 31 241 . 40 . 000	25
	25*	14 31 251 . 40 . 000	25
Please insert digit for			
pitch 3.50 mm ►	4		
pitch 3.81 mm ►	5		
vertical ►	1		
horizontal ►	2		

* Pitch 3.81 mm (vertical) only available with 2-16 contacts


PCB connectors female,
vertical/horizontal
with screw termination
pitch 3.50 / 3.81 mm




Drawing

Dimensions in mm

Dimensions



L = pitch x poles
a = pitch x (poles - 1)



L = pitch x poles
a = pitch x (poles - 1)

Technical characteristics

Technical data

Rated current 10 A
Pitch 3.50 mm / 3.81 mm

Surge voltage category /
pollution degree

Rated voltage
Rated surge voltage

III/3	III/2	II/2
150 V	150 V	300 V
2.5 kV	2.5 kV	2.5 kV


Material data

Group of insulation material I
Type of insulation material PA / PPA
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +110 °C
Contact material copper alloy
Contact plating tin plated

Conductor data

Connection technology wire screw termination
Conductor size solid / stranded 0.05 - 1.5 / 0.05 - 1.5 mm²
Conductor size AWG 30 - 14
Screw thread M2
Tightening torque 0.2 - 0.25 Nm
Stripping length 5.0 - 6.0 mm

PCB connectors male,
vertical/horizontal
for SMT reflow soldering
pitch 3.50 / 3.81 mm



Identification	No. of contacts	Part No.	Packaging unit
----------------	-----------------	----------	----------------

Connectors,
male, vertical/horizontal


2	14 12 021 . 00 . 000	300
3	14 12 031 . 00 . 000	200
4	14 12 041 . 00 . 000	150
5	14 12 051 . 00 . 000	150
6	14 12 061 . 00 . 000	100
7	14 12 071 . 00 . 000	100
8	14 12 081 . 00 . 000	100
9	14 12 091 . 00 . 000	100
10	14 12 101 . 00 . 000	100
11	14 12 111 . 00 . 000	100
12	14 12 121 . 00 . 000	100
13	14 12 131 . 00 . 000	50
14	14 12 141 . 00 . 000	50
15	14 12 151 . 00 . 000	50
16	14 12 161 . 00 . 000	50
17	14 12 171 . 00 . 000	50
18	14 12 181 . 00 . 000	50
19	14 12 191 . 00 . 000	50
20	14 12 201 . 00 . 000	50
21	14 12 211 . 00 . 000	25
22	14 12 221 . 00 . 000	25
23	14 12 231 . 00 . 000	25
24	14 12 241 . 00 . 000	25
25	14 12 251 . 00 . 000	25

Please insert digit for

pitch 3.50 mm ► 4
pitch 3.81 mm ► 5

vertical ► 1
horizontal ► 2


PCB connectors male,
vertical/horizontal
for SMT reflow soldering
pitch 3.50 / 3.81 mm



Drawing

Dimensions in mm

Dimensions



$L = (\text{pitch} \times \text{poles}) + 1$
 $a = \text{pitch} \times (\text{poles} - 1)$

$L = (\text{pitch} \times \text{poles}) + 1$
 $a = \text{pitch} \times (\text{poles} - 1)$

Technical characteristics

Technical data

Rated current 11 A
Pitch 3.50 mm / 3.81 mm

Surge voltage category /
pollution degree
Rated voltage
Rated surge voltage

III/3	III/2	II/2
150 V	150 V	300 V
2.5 kV	2.5 kV	2.5 kV


Material data

Group of insulation material I
Type of insulation material PA / PPA
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +110 °C
Contact material copper alloy
Contact plating tin plated

Solder pin data

Solder pin: drilled hole diameter 1.2 mm

PCB terminal blocks,
vertical with push-in-spring-cage
termination
pitch 5.00 mm



Identification	No. of contacts	Part No.	Packaging unit
----------------	-----------------	----------	----------------

PCB terminal blocks,
vertical with push-in-spring-cage
termination

2

14 03 021 6101 000

300

3

14 03 031 6101 000

200

4

14 03 041 6101 000

150

5

14 03 051 6101 000

150

6

14 03 061 6101 000

100

7

14 03 071 6101 000

100

8

14 03 081 6101 000

100

9

14 03 091 6101 000

100

10

14 03 101 6101 000

100

11

14 03 111 6101 000

100

12

14 03 121 6101 000

100

13

14 03 131 6101 000

50

14

14 03 141 6101 000

50

15

14 03 151 6101 000

50

16

14 03 161 6101 000

50

17

14 03 171 6101 000


50

18

14 03 181 6101 000

50


PCB terminal blocks,
vertical with push-in-spring-cage termination
for wave soldering
pitch 5.00 mm



Drawing

Dimensions in mm

Dimensions



L = pitch x poles
a = pitch x (poles - 1)

Technical characteristics

Technical data

Rated current 12 A
Pitch 5.00 mm

Surge voltage category /
pollution degree

Rated voltage
Rated surge voltage

III/3	III/2	II/2
300 V	300 V	600 V
4 kV	4 kV	4 kV

Material data

Group of insulation material I
Type of insulation material PA
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +110 °C
Contact material copper alloy
Contact plating tin plated

Conductor and solder pin data

Connection technology wire push-in-spring-cage
termination
Conductor size solid / stranded 0.2 - 2.5 / 0.2 - 2.5 mm²
Conductor size AWG 30 - 12
Stripping length 10 mm
Solder pin: drilled hole diameter 1.4 mm



PCB terminal blocks,
horizontal with screw termination
for reflow soldering
pitch 5.00 mm

Identification	No. of contacts	Part No.	Packaging unit
PCB terminal blocks, horizontal with screw termination			
for wire gauge 2.5 mm²	2	14 02 021 6404 000	300
	3	14 02 031 6404 000	200
	4	14 02 041 6404 000	150
	5	14 02 051 6404 000	150
	6	14 02 061 6404 000	100
	7	14 02 071 6404 000	100
	8	14 02 081 6404 000	100


PCB terminal blocks,
horizontal with screw termination
for reflow soldering
pitch 5.00 mm



Drawing

Dimensions in mm

Dimensions



L = pitch x poles
a = pitch x (poles - 1)

Technical characteristics

Technical data

Rated current 17.5 A
Pitch 5.00 mm

Surge voltage category /
pollution degree

Rated voltage
Rated surge voltage

III/3	III/2	II/2
300 V	300 V	600 V
4 kV	4 kV	4 kV

Material data

Group of insulation material I
Type of insulation material PA / PPA
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +110 °C
Contact material copper alloy
Contact plating tin plated

Conductor and solder pin data

Connection technology wire screw termination
Conductor size solid / stranded 0.05 - 2.5 / 0.05 - 2.5 mm²
Conductor size AWG 30 - 12
Screw thread M3
Tightening torque 0.5 - 0.6 Nm
Stripping length 5.5 - 6.5 mm
Solder pin: drilled hole diameter 1.4 mm

PCB terminal blocks,
horizontal with screw termination
for reflow soldering
pitch 5.00 mm



Identification	No. of contacts	Part No.	Packaging unit
PCB terminal blocks, horizontal with screw termination			
for wire gauge 1.5 mm ²	2	14 02 021 6402 000	300
	3	14 03 031 6402 000	200
	4	14 03 041 6402 000	150
	5	14 03 051 6402 000	150
	6	14 03 061 6402 000	100
	7	14 03 071 6402 000	100
	8	14 03 081 6402 000	100
	9	14 03 091 6402 000	100
	10	14 03 101 6402 000	100
	11	14 03 111 6402 000	100
	12	14 03 121 6402 000	100


PCB terminal blocks,
horizontal with screw termination
for reflow soldering
pitch 5.00 mm



Drawing

Dimensions in mm

Dimensions



L = pitch x poles
a = pitch x (poles - 1)

Technical characteristics

Technical data

Rated current 13.5 A
Pitch 5.00 mm

Surge voltage category /
pollution degree

Rated voltage
Rated surge voltage

III/3	III/2	II/2
220 V	300 V	600 V
4 kV	4 kV	4 kV


Material data

Group of insulation material I
Type of insulation material PA / PPA
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +110 °C
Contact material copper alloy
Contact plating tin plated

Conductor and solder pin data

Connection technology wire screw termination
Conductor size solid / stranded 0.05 - 1.5 / 0.05 - 1.5 mm²
Conductor size AWG 30 - 16
Screw thread M3
Tightening torque 0.5 - 0.6 Nm
Stripping length 5.0 - 6.0 mm
Solder pin: drilled hole diameter 1.1 mm

PCB connectors female,
horizontal
with push-in-spring-cage termination
pitch 5.00 / 5.08 mm



Identification	No. of contacts	Part No.	Packaging unit
----------------	-----------------	----------	----------------


PCB connectors female,
horizontal
with push-in-spring-cage
termination

2	14 31 021 . 102 000	300
3	14 31 031 . 102 000	200
4	14 31 041 . 102 000	150
5	14 31 051 . 102 000	150
6	14 31 061 . 102 000	100
7	14 31 071 . 102 000	100
8	14 31 081 . 102 000	100
9	14 31 091 . 102 000	100
10	14 31 101 . 102 000	100
11	14 31 111 . 102 000	100
12	14 31 121 . 102 000	100
13	14 31 131 . 102 000	50
14	14 31 141 . 102 000	50
15	14 31 151 . 102 000	50
16	14 31 161 . 102 000	50
17	14 31 171 . 102 000	50
18	14 31 181 . 102 000	50

Please insert digit for

pitch 5.00 mm ► 6
pitch 5.08 mm ► 7


PCB connectors female,
horizontal
with push-in-spring-cage termination
pitch 5.00 / 5.08 mm



Drawing

Dimensions in mm

Dimensions



L = pitch x poles
a = pitch x (poles - 1)

Technical characteristics

Technical data

Rated current 12 A
Pitch 5.00 mm / 5.08 mm

Surge voltage category /
pollution degree

Rated voltage
Rated surge voltage

III/3	III/2	II/2
250 V	300 V	600 V
4 kV	4 kV	4 kV


Material data

Group of insulation material I
Type of insulation material PA / PPA
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +110 °C
Contact material copper alloy
Contact plating tin plated

Conductor data

Connection technology wire push-in-spring-cage
termination
Conductor size solid / stranded 0.2 - 2.5 / 0.2 - 2.5 mm²
Conductor size AWG 30 - 12
Stripping length 10 mm

PCB connectors female,
horizontal
with screw termination
pitch 5.00 / 5.08 mm



Identification	No. of contacts	Part No.	Packaging unit
----------------	-----------------	----------	----------------


PCB connectors female,
horizontal
with screw termination

2	14 31 021 . 402 000	300
3	14 31 031 . 402 000	200
4	14 31 041 . 402 000	150
5	14 31 051 . 402 000	150
6	14 31 061 . 402 000	100
7	14 31 071 . 402 000	100
8	14 31 081 . 402 000	100
9	14 31 091 . 402 000	100
10	14 31 101 . 402 000	100
11	14 31 111 . 402 000	100
12	14 31 121 . 402 000	100
13	14 31 131 . 402 000	50
14	14 31 141 . 402 000	50
15	14 31 151 . 402 000	50
16	14 31 161 . 402 000	50
17	14 31 171 . 402 000	50
18	14 31 181 . 402 000	50
19	14 31 191 . 402 000	50
20	14 31 201 . 402 000	50
21	14 31 211 . 402 000	25
22	14 31 221 . 402 000	25
23	14 31 231 . 402 000	25
24	14 31 241 . 402 000	25
25	14 31 251 . 402 000	25

Please insert digit for

pitch 5.00 mm ► 6
pitch 5.08 mm ► 7



PCB connectors female,
horizontal
with screw termination
pitch 5.00 / 5.08 mm



Drawing

Dimensions in mm

Dimensions



$L = \text{pitch} \times \text{poles}$
 $a = \text{pitch} \times (\text{poles} - 1)$

Technical characteristics

Technical data

Rated current 15 A
Pitch 5.00 mm / 5.08 mm

Surge voltage category /
pollution degree

Rated voltage
Rated surge voltage

III/3	III/2	II/2
250 V	300 V	600 V
4 kV	4 kV	4 kV


Conductor data

Connection technology wire screw termination
Conductor size solid / stranded 0.05 - 2.5 / 0.05 - 2.5 mm²
Conductor size AWG 30 - 12
Screw thread M3
Tightening torque 0.5 - 0.6 Nm
Stripping length 6.0 - 7.5 mm

Material data

Group of insulation material I
Type of insulation material PA / PPA
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +110 °C
Contact material copper alloy
Contact plating tin plated

PCB connectors male,
vertical/horizontal
for reflow soldering
pitch 5.00 / 5.08 mm



Identification	No. of contacts	Part No.	Packaging unit
----------------	-----------------	----------	----------------

PCB connectors male,
vertical/horizontal


2	14 12 021 . 00 . 000	300
3	14 12 031 . 00 . 000	200
4	14 12 041 . 00 . 000	150
5	14 12 051 . 00 . 000	150
6	14 12 061 . 00 . 000	100
7	14 12 071 . 00 . 000	100
8	14 12 081 . 00 . 000	100
9	14 12 091 . 00 . 000	100
10	14 12 101 . 00 . 000	100
11	14 12 111 . 00 . 000	100
12	14 12 121 . 00 . 000	100
13*	14 12 131 . 00 . 000	50
14*	14 12 141 . 00 . 000	50
15*	14 12 151 . 00 . 000	50
16*	14 12 161 . 00 . 000	50
17*	14 12 171 . 00 . 000	50
18*	14 12 181 . 00 . 000	50
19*	14 12 191 . 00 . 000	50

Please insert digit for

pitch 5.00 mm ► 6
pitch 5.08 mm ► 7

vertical ► 1
horizontal ► 2


PCB connectors male,
vertical/horizontal
for reflow soldering
pitch 5.00 / 5.08 mm



Drawing

Dimensions in mm

Dimensions



Technical characteristics

Technical data

Rated current 15 A
Pitch 5.00 mm / 5.08 mm

Surge voltage category /
pollution degree

Rated voltage
Rated surge voltage

III/3	III/2	II/2
250 V	300 V	600 V
4 kV	4 kV	4 kV


Material data

Group of insulation material I
Type of insulation material PA / PPA
Flammability rating per UL 94 V0
Operating temperature -40 °C ... +110 °C
Contact material copper alloy
Contact plating tin plated

Solder pin data


Solder pin: drilled hole diameter 1.4 mm


You can find the **HARTING eCatalogue** at www.HARTING.com.



The **HARTING eCatalogue** is an electronic catalogue with a product configurator. Here you can choose a connector according to your requirements. Afterwards you are able to send your inquiry directly to a HARTING sales partner. The drawings to every single part are available in PDF format. The parts are downloadable in 2D format (DXF) and 3D format (IGES, STEP). The 3D models can be viewed with a VRML-viewer.

Product configurator





Sales Network – worldwide



Albania

see Eastern Europe

Argentina

Condelectric S.A.
Hipólito Yrigoyen 2591, 1640 - Martínez
Buenos Aires – Argentina
Phone +54 11 4836 1053
Fax +54 11 4836 1053
comercial@condelectric.com.ar

Armenia

see Eastern Europe

Australia

HARTING Pty Ltd
Suite 11 / 2 Enterprise Drive
Bundoora 3083, AUS-Victoria
Phone +61 3 9466 7088
Fax +61 3 9466 7099
au@HARTING.com
www.HARTING.com.au

Austria

HARTING Ges.m.b.H.
Deutschstraße 19, A-1230 Wien
Phone +431 6162121
Fax +431 6162121-21
at@HARTING.com
www.HARTING.at

Azerbaijan

see Eastern Europe

Bahrain

see United Arab Emirates

Belarus

see Eastern Europe

Belgium

HARTING N.V./S.A.
Z.3 Doornveld 23, B-1731 Zellik
Phone +32 2 466 0190
Fax +32 2 466 7855
be@HARTING.com
www.HARTING.be

Bosnia and Herzegovina

see Eastern Europe

Brazil

HARTING Ltda.
Rua Major Paladino 128; Prédio 11
CEP 05307-000 São Paulo
SP – Brazil
Phone +55 11 5035 0073
Fax +55 11 5034 4743
br@HARTING.com
www.HARTING.com.br

Brunei

see Singapore

Bulgaria

see Eastern Europe

Canada

HARTING Canada Inc.
8455 Trans-Canada Hwy., Suite 202
St. Laurent, QC, H4S1Z1, Canada
Phone 855-659-6653
Fax 855-659-6654
info.ca@HARTING.com
www.HARTING.ca

China

HARTING (Zhuhai) Manufacturing Co., Ltd.
Shanghai Branch
Room 3501- 3503,
No. 1, Hong Qiao Road, Grand Gateway I
Xu Hui District, Shanghai 200030, China
Phone +86 21 6386 2200
Fax +86 21 6386 8636
cn@HARTING.com
www.HARTING.com.cn

Croatia

see Eastern Europe

Czech Republic

HARTING s.r.o.
Mlýnská 2, CZ-160 00 Praha 6
Phone +420 220 380 460
Fax +420 220 380 461
cz@HARTING.com
www.HARTING.cz

Denmark

HARTING ApS
Hjulgagervej 4a
DK - 7100 Vejle
Phone +45 70 25 00 32
Fax +45 75 80 64 99
dk@HARTING.com
www.HARTING.com

Eastern Europe

HARTING Eastern Europe GmbH
Bamberger Straße 7
D-01187 Dresden
Phone +49 351 4361 760
Fax +49 351 436 1770
Eastern.Europe@HARTING.com
www.HARTING.com

Estonia

see Eastern Europe

Finland

HARTING Oy
Teknobulevardi 3-5
FI-01530 Vantaa
Phone +358 207 291 510
Fax +358 207 291 511
fi@HARTING.com
www.HARTING.fi

France

HARTING France
181 avenue des Nations, Paris Nord 2
BP 66058 Tremblay en France
F-95972 Roissy Charles de Gaulle
Cédex
Phone +33 1 4938 3400
Fax +33 1 4863 2306
fr@HARTING.com
www.HARTING.fr

Germany

HARTING Deutschland GmbH & Co. KG
P.O. Box 2451, D-32381 Minden
Simeons carré 1, D-32427 Minden
Phone +49 571 8896 0
Fax +49 571 8896 282
de@HARTING.com
www.HARTING.de

Georgia

see Eastern Europe

Great Britain

HARTING Ltd., Caswell Road
Brackmills Industrial Estate
GB-Northampton, NN4 7PW
Phone +44 1604 827 500
Fax +44 1604 706 777
gb@HARTING.com
www.HARTING.co.uk

Hong Kong

HARTING (HK) Limited
Regional Office Asia Pacific
3512 Metroplaza Tower 1
223 Hing Fong Road
Kwai Fong, N. T., Hong Kong
Phone +852 2423 7338
Fax +852 2480 4378
ap@HARTING.com
www.HARTING.com.hk

Hungary

HARTING Magyarország Kft.
Fehérvári út 89-95, H-1119 Budapest
Phone +36 1 205 34 64
Fax +36 1 205 34 65
hu@HARTING.com
www.HARTING.hu

Iceland

Smith & Norland, Nóatún 4
IS – 105 Reykjavík
Phone +354 520 3000
Fax +354 520 3011
olaf@sminor.is, www.sminor.is

India

HARTING India Pvt Ltd
7th Floor (West Wing), Central Square II
Unit No.B-19 Part, B 20&21
TVK Industrial Estate
Guindy, Chennai - 600032
Phone : +91-44-43560415
+91-44-43456262
Fax : +91-44-43560417
in@HARTING.com
http://www.HARTING.in

Indonesia

see Malaysia

Israel

COMTEL
Israel Electronic Solutions Ltd.
Bet Hapamon, 20 Hataas st.
P.O.Box 66
Kefar-Saba 44425
Phone +972-9-7677240
Fax +972-9-7677243
sales@comtel.co.il
www.comtel.co.il

Italy

HARTING SpA
Via Dell' Industria 7
I-20090 Vimodrone (Milano)
Phone +39 02 250801
Fax +39 02 2650 597
it@HARTING.com
www.HARTING.it

Japan

HARTING K. K.
Yusen Shin-Yokohama 1 Chome Bldg., 2F
1-7-9, Shin-Yokohama, Kohoku
Yokohama 222-0033 Japan
Phone +81 45 476 3456
Fax +81 45 476 3466
jp@HARTING.com
www.HARTING.co.jp

Jordan

see United Arab Emirates

Kazakhstan

see Eastern Europe

Kirghizia

see Eastern Europe

Korea (South)

HARTING Korea Limited
#308 Yatap Leaders Building
342-1, Yatap-dong, Bundang-gu
Sungnam-City, Kyunggi-do
463-828, Republic of Korea
Phone +82 31 781 4615
Fax +82 31 781 4616
kr@HARTING.com
www.HARTING.co.kr

Kosovo

see Eastern Europe

Kuwait

see United Arab Emirates

Latvia

see Eastern Europe

Lithuania

see Eastern Europe

Macedonia

see Eastern Europe

Malaysia (Office)

HARTING Singapore Pte Ltd
Malaysia Branch
11-02 Menara Amcorp
Jln. Persiaran Barat
46200 PJ, Sel. D. E., Malaysia
Phone +60 3 / 7955 6173
Fax +60 3 / 7955 5126
sg@HARTING.com

Montenegro

see Eastern Europe

Netherlands

HARTING B.V.
Larenweg 44
NL-5234 KA 's-Hertogenbosch
Postbus 3526
NL-5203 DM 's-Hertogenbosch
Phone +31 736 410 404
Fax +31 736 440 699
nl@HARTING.com
www.HARTINGbv.nl

New Zealand

see Australia

Norway

HARTING A/S
Østensjøveien 36, N-0667 Oslo
Phone +47 22 700 555
Fax +47 22 700 570
no@HARTING.com
www.HARTING.no

Oman

see United Arab Emirates

Pakistan

see United Arab Emirates

Philippines

see Malaysia

Poland

HARTING Polska Sp. z o. o.
ul. Duńska 9
PL- 54-427 Wrocław
Phone +48 71 352 81 71
Fax +48 71 350 42 13
pl@HARTING.com
www.HARTING.pl

Portugal

HARTING Iberia, S. A.
Avda. Josep Tarradellas 20-30 4º 6a
E-08029 Barcelona
Phone +351 219 673 177
Fax +351 219 678 457
es@HARTING.com
www.HARTING.es/pt

Qatar

see United Arab Emirates

Republic of Moldova

see Eastern Europe

Romania

HARTING Romania SCS
Europa Unita str. 21
550018-Sibiu, Romania
Phone +40 369-102 671
Fax +40 369-102 622
ro@HARTING.com
www.HARTING.com

Russia

HARTING ZAO
Maliy Sampsoniyevsky prospect 2A
194044 Saint Petersburg, Russia
Phone +7 812 327 6477
Fax +7 812 327 6478
ru@HARTING.com
www.HARTING.ru

Saudi Arabia

see United Arab Emirates

Serbia

see Eastern Europe

Singapore

HARTING Singapore Pte Ltd.
25 International Business Park
#04-108 German Centre
Singapore 609916
Phone +65 6225 5285
Fax +65 6225 9947
sg@HARTING.com
www.HARTING.sg

Slovakia

HARTING s.r.o.
Sales office Slovakia
J. Simora 5, SK - 940 52 Nové Zámky
Phone +421 356-493 993
Fax +421 356-402 114
sk@HARTING.com
www.HARTING.sk

Slovenia

see Eastern Europe

South Africa

HellermannTyton Pty Ltd.
Private Bag X158 Rivonia 2128
34 Milky Way Avenue
Linbro Business Park 2065
Johannesburg
Phone +27(0)11879-6600
Fax +27(0)11879-6606
sales.jhb@hellermann.co.za

Spain

HARTING Iberia S.A.
Avda. Josep Tarradellas 20-30 4º 6a
E-08029 Barcelona
Phone +34 93 363 84 75
Fax +34 93 419 95 85
es@HARTING.com
www.HARTING.es

Sweden

HARTING AB
Gustavslundsvägen 141 B 4tr
S-167 51 Bromma
Phone +46 8 445 7171
Fax +46 8 445 7170
se@HARTING.com
www.HARTING.se

Switzerland

HARTING AG
Industriestrasse 26
CH-8604 Volketswil
Phone +41 44 908 20 60
Fax +41 44 908 20 69
ch@HARTING.com
www.HARTING.ch

Taiwan

HARTING Taiwan Ltd.
Room 1, 5/F
495 GuangFu South Road
RC-110 Taipei, Taiwan
Phone +886 2 2758 6177
Fax +886 2 2758 7177
tw@HARTING.com
www.HARTING.com.tw

Tajikistan

see Eastern Europe

Thailand

see Malaysia

Turkey

HARTING TURKEI Elektronik Ltd. Şti.
Barbaros Mah. Dereboyu Cad.
Fesleğen Sok.
Uphill Towers, A-1b Kat:8 D:45
34746 Ataşehir, İstanbul
Phone +90 216 688 81 00
Fax +90 216 688 81 01
tr@HARTING.com
www.HARTING.com.tr

Turkmenistan

see Eastern Europe

Ukraine

see Eastern Europe

United Arab Emirates

HARTING Middle East FZ-LLC
Knowledge Village, Block 2A, Office F72
P.O. Box 454372, Dubai
United Arab Emirates
Phone +971 4 453 9737
Fax +971 4 439 0339
uae@HARTING.com
www.HARTING.ae

USA

HARTING Inc. of North America
1370 Bowes Road
USA-Elgin, Illinois 60123
Phone +1 (877) 741-1500 (toll free)
Fax +1 (866) 278-0307 (Inside Sales)
us@HARTING.com
www.HARTING-USA.com

Uzbekistan

see Eastern Europe

Vietnam

see Singapore

Distributors – worldwide



Farnell:
www.farnell.com

RS Components:
www.rs-components.com

Mouser Electronics:
www.mouser.com

Digi-Key Corporation:
www.digikey.com

Other countries and general contact



HARTING Electric GmbH & Co. KG
P.O. Box 1473, D-32328 Espelkamp
Phone +49 5772 47-97100
Fax +49 5772 47-495
electric@HARTING.com
www.HARTING.com

HARTING Electronics GmbH
P.O. Box 1433
32328 Espelkamp - Germany
Phone +49 5772/47-97200
Fax +49 5772/47-777
electronics@HARTING.com
www.HARTING.com



Pushing Performance

HARTING Technology Group

Marienwerderstr. 3, 32339 Espelkamp – Germany

P.O. Box 11 33, 32325 Espelkamp – Germany

Phone +49 5772 47-0, Fax +49 5772 47-400

info@HARTING.com

www.HARTING.com