

Product Facts

- **SOLISTRAND**
Terminals and Splices
- Utilize a brazed seam
- Applied with "W" crimp tooling
- Available in wire sizes
26 AWG–600 MCM
[0.1–304 mm²]
- For terminating solid
& stranded wires
- U.L. Listed
CSA Certified
Military Approved
- **Budget**
Terminals and Splices
- Utilize a butted seam
- Applied with "F" crimp tooling
- Available in wire
sizes 26–10 AWG
[0.1–6.64 mm²]
- For terminating stranded
wire only
- U.L. Listed
- **DIAMOND GRIP**
Terminals and Splices
- Utilize a butted seam
- Metal insulation support
sleeve with "V" notches
- Applied with a "C" crimp
- Available in wire sizes
26–10 AWG (0.1–6.64 mm²)
- For terminating stranded
wire only
- U.L. Listed
CSA Certified



SOLISTRAND and Budget terminals and splices are specially designed to terminate solid and stranded wire, irregular shaped conductors, and combinations of these — retaining the superior performance characteristics of single-purpose terminals and splices.

Corrosion resistance, vibration resistance and tensile strength of these terminals and splices are well within the limits of commercial and military specifications.

The Budget terminal is primarily the same as the SOLISTRAND terminals without the brazed seam in the wire barrel. These

terminals and splices fulfill the need for an economical and electrically superior termination where extreme vibration and tension on the wires are not present.

DIAMOND GRIP utilizes a tin plated copper insulation support sleeve with "V" notches. The sleeve eliminates fraying of the insulation or breaking of the conductor. The "V" notches lock the wire insulation against vibration and pullout.

Need more information?

Call the AMP Technical Support Center:
1-800-522-6752

The Technical Support Center is staffed with specialists well versed in all AMP Products. The Center can provide you with:

- Technical Support
- Catalogs
- Technical Documents
- Product Samples
- AMP Authorized Distributor Locations

© Copyright 1994, 1996 and 2000 by AMP Incorporated, Harrisburg, PA. All Rights Reserved.


AMP, AMPOMATOR, AMP-O-LECTRIC, AMP-TAPETRONIC, CERTI-CRIMP, DIAMOND GRIP, PRO-CRIMPER II, SOLISTRAND, TAPETRONIC and DYNA-CRIMP are trademarks.

Table of Contents

How to Compute Circular Mil Area of Various Wire Shapes	3
Table of SOLISTRAND and Budget Standard Wire Ranges	3
Table listing: Circular Mil Area for common wire sizes	4 – 7
Product Descriptions	8, 9, 10
Stud Hole Sizes	11
SOLISTRAND and Budget	
Ring Tongue Terminals	12–20
26 AWG–600 MCM [0.1–304 mm ²]	
Right Angle Ring Tongue Terminals	21
22 AWG–300 MCM [0.26–152 mm ²]	
Heavy Duty Ring Tongue Terminals	22, 23
16–1/0 AWG [1.04–60.6 mm ²]	
Rectangular Tongue Terminals	24, 25
22–10 AWG [0.26–6.64 mm ²]	
Spade Tongue Terminals	26
26–10 AWG [0.1–6.64 mm ²]	
Short Spring Spade Tongue Terminals	27, 28
26–10 AWG [0.1–6.64 mm ²]	
Long Spring Spade Tongue Terminals	29
26–10 AWG [0.1–6.64 mm ²]	
Flanged Spade Tongue Terminals	30
26–10 AWG [0.1–6.64 mm ²]	
Slotted Ring Tongue Terminals	31
26–10 AWG [0.1–6.64 mm ²]	
Hook Tongue Terminals	32
22–10 AWG [0.26–6.64 mm ²]	
Tab Tongue Terminals	32
22–8 AWG [0.26–10.5 mm ²]	
Flag Ring Tongue Terminals	33, 34
16–4/0 AWG [1.04–117 mm ²]	
Parallel Splices	35
22 AWG–600 MCM [0.26–304 mm ²]	
Butt Splices	36, 37
26 AWG–600 MCM [0.1–304 mm ²]	
DIAMOND GRIP	
Ring Tongue Terminals	38, 39
26–10 AWG [0.1–6.64 mm ²]	
Knife Disconnect Splices	40
22–10 AWG [0.26–6.64 mm ²]	
Slotted Ring Tongue	40
26–16 AWG [0.1–1.65 mm ²]	
Rectangular Tongue Terminals	41
22–16 AWG [0.26–1.65 mm ²]	
Flanged Spade Tongue Terminals	41
26–14 AWG [0.1–2.62 mm ²]	
Spade Tongue Terminals	42
26–16 AWG [0.1–1.65 mm ²]	
Standard “B”	
Knife Disconnect Splices	43
22–8 AWG [0.26–10.5 mm ²]	
Rectangular Tongue Terminals	43
22–14 AWG [0.26–2.62 mm ²]	
Military Approvals, Part Numbers & Requirements	44–48
U.L. Requirements	49, 50
Application Tooling	51–56
Part Number Index	57–59

How to Compute Circular Mil Area of Various Wire Shapes

Square or Rectangular Wire



U.S. Customary Dimensions

Multiply the width of the wire cross section in mils by the thickness of the wire cross section in mils by 1.2732 and subtract the radius factor shown below.


$$\text{CMA} = W \times T \times 1.2732 - \text{radius factor}$$

Metric Dimensions

Multiply the width of the wire cross section in millimetres by the thickness of the wire cross section in millimetres by 1973.525 and subtract the radius factor shown below.

$$\text{CMA} = W \times T \times 1973.525 - \text{radius factor}$$

Round Solid Wire AWG




Multiply the diameter in mils by itself.

$$\text{CMA} = D^2$$

Multiply the diameter in millimetres by itself by 1550.003

$$\text{CMA} = D^2 \times 1550.003$$

Stranded Wire AWG



Multiply the diameter of one strand (in mils) by itself, and then multiply the result by the total number of strands.

$$\text{CMA} = D^2 \times N$$

Multiply the diameter of one strand in millimetres by itself by the number of strands by 1550.003.

$$\text{CMA} = D^2 \times N \times 1550.003$$

Conversion Table

To Convert From	To	Multiply By
CMA	mm ²	.0005067075
CMA	in ²	.0000007854
mm ²	in ²	.001550003
mm ²	CMA	1973.525

Note: Refer to table listing for circular mil area for common wire sizes.

Radius Factor, U.S. Customary

Radius (in.)	Radius Factor To Subtract (CMA)
.010	110
.012	158
.016	280
.020	438
.026	740
.032	1121
.040	1752
.063	4346
.094	9675

Radius must be measured.

Radius Factor, Metric

Radius (mm)	Radius Factor To Subtract (CMA)
0.25	106
0.3	153
0.35	208
0.4	272
0.5	424
0.6	611
0.8	1086
1.2	2444

Radius must be measured.

Table of SOLISTRAND and Budget Standard Wire Ranges

Use to select the proper size terminals or splices.

Terminal Connector Size	CMA Range
26-22	202-810
24-20	320-1,290
22-16	509-3,260
16-14 & 16-14 HD	2,050-5,180
14-12	3,260-8,230
12-10	5,180-13,100
8 & 8 HD	13,100-20,800
6 & 6 HD	20,800-33,100
4 & 4 HD	33,100-52,600

HD-Denotes Heavy Duty Terminal.

Terminal Connector Size	CMA Range
2 & 2 HD	52,600-83,700
1/0 & 1/0 HD	83,700-119,500
2/0	119,500-150,500
3/0	150,500-190,000
4/0	190,000-231,000
250-300 MCM	231,000-300,000
300-350 MCM	300,000-380,000
400 MCM	350,000-478,000
500-600 MCM	478,000-600,000

Table listing: Circular Mil Area for common wire sizes

Wire Sizes in AWG and mm² to CMA

Note: The following tables are applicable to single and multiple strand, round, conductors only.

Computing Circular Mil Area

For best results, the proper AMP terminal or splice must be selected not by the "fit" of wire or wires in the terminal barrel, but by the total circular mil area in cross section of the wires used. For this purpose AMP has prepared convenient tables to assist in the calculation of circular mil areas. When the totals are known, the proper AMP terminal or splice can be determined quickly.

Unusual combinations or special applications should be submitted to AMP engineering department for size recommendation. In any application, the careful selection of terminals by the circular mil area method will insure the highest possible performance, both electrically and mechanically, in your AMP terminations.

Example of multiple wire configurations used in one termination

ALWAYS SELECT TERMINALS BY THE CIRCULAR MIL AREA METHOD. For example, a No. 18 AWG 16-strand conductor (1600 CMA) and a No. 16 AWG 19-strand conductor (2426 CMA) will have a combined total of 4026 CMA. This total CMA is equivalent to a No. 14 AWG conductor.

CMA	Nominal Wire Size		No.	Strands Diameter		Approximate Conductor Diameter	
	AWG	mm ²		Inch	mm	Inch	mm
3.8	44	0.002	1	0.00195	0.050	0.002	0.051
4.0	44	0.002	1	0.002	0.051	0.002	0.051
4.8	43	0.002	1	0.0022	0.056	0.0022	0.056
6.3	42	0.003	1	0.0025	0.064	0.0025	0.064
7.8	41	0.004	1	0.0028	0.071	0.0028	0.071
9.6	40	0.005	1	0.0031	0.079	0.0031	0.079
12.3	39	0.006	1	0.0035	0.089	0.0035	0.089
15.2	38	0.008	1	0.0039	0.099	0.0039	0.099
16.0	38	0.008	1	0.004	0.102	0.004	0.102
20.2	37	0.010	1	0.0045	0.114	0.0045	0.114
25.0	36	0.013	1	0.005	0.127	0.005	0.127
31.4	35	0.016	1	0.0056	0.142	0.0056	0.142
39.7	34	0.020	1	0.0063	0.160	0.0063	0.160
50.0	33	0.025	1	0.00707	0.180	0.0071	0.180
50.4	33	0.026	1	0.0071	0.180	0.0071	0.180
64.0	32	0.032	1	0.008	0.203	0.008	0.203
79.2	31	0.040	1	0.0089	0.226	0.0089	0.226
100.0	30	0.051	1	0.01	0.254	0.01	0.254
104.0	30	0.053	26	0.002	0.051	0.012	0.305
127.7	29	0.064	1	0.0113	0.287	0.011	0.279
152.1	29	0.077	10	0.0039	0.099	0.013	0.330
158.8	29	0.080	1	0.0126	0.320	0.013	0.330
175.0	28	0.089	7	0.005	0.127	0.015	0.381
182.6	28	0.093	19	0.0031	0.079	0.016	0.406
202	27	0.102	1	0.0142	0.361	0.014	0.356
204	27	0.103	51	0.002	0.051	0.016	0.406
238	26	0.121	6	0.0063	0.160	0.018	0.457
250	26	0.127	26	0.0031	0.079	0.018	0.457
250	26	0.127	10	0.005	0.127	0.018	0.457
251	26	0.127	8	0.0056	0.142	0.018	0.457
253	26	0.128	1	0.0159	0.404	0.016	0.406
256	26	0.130	16	0.004	0.102	0.018	0.457
274	26	0.139	18	0.0039	0.099	0.022	0.558
278	26	0.141	7	0.0063	0.160	0.019	0.483
288	26	0.146	72	0.002	0.051	0.022	0.559
300	26	0.152	3	0.01	0.254	0.02	0.508
304	26	0.154	19	0.004	0.102	0.02	0.508
313	25	0.159	1	0.0177	0.450	0.018	0.457
314	25	0.159	10	0.0056	0.142	0.02	0.508
318	25	0.161	8	0.0063	0.160	0.021	0.533
320	25	0.162	1	0.0179	0.455	0.018	0.457
388	24	0.197	1	0.0197	0.500	0.02	0.508
397	24	0.201	10	0.0063	0.160	0.023	0.584
400	24	0.203	16	0.005	0.127	0.023	0.584
400	24	0.203	4	0.01	0.254	0.023	0.584
403	24	0.204	8	0.0071	0.180	0.023	0.584
404	24	0.205	1	0.0201	0.511	0.02	0.508
408	24	0.207	13	0.0056	0.142	0.023	0.584
408	24	0.207	102	0.002	0.051	0.02	0.508
475	24	0.241	19	0.005	0.127	0.023	0.584
634	22	0.321	8	0.0089	0.226	0.029	0.737
635	22	0.322	16	0.0063	0.160	0.029	0.737
640	22	0.324	10	0.008	0.203	0.029	0.737
640	22	0.324	1	0.0253	0.643	0.025	0.635
650	22	0.329	26	0.005	0.127	0.033	0.838
700	22	0.355	7	0.01	0.254	0.03	0.762
754	22	0.382	19	0.0063	0.160	0.033	0.838
812	21	0.411	1	0.0285	0.724	0.029	0.737
992	20	0.503	1	0.0315	0.800	0.032	0.813
1000	20	0.507	10	0.01	0.254	0.038	0.965
1008	20	0.511	20	0.0071	0.180	0.039	0.991
1024	20	0.519	16	0.008	0.203	0.039	0.991
1024	20	0.519	1	0.032	0.813	0.032	0.813
1024	20	0.519	256	0.002	0.051	0.039	0.991
1025	20	0.519	41	0.005	0.127	0.038	0.965
1032	20	0.523	26	0.0063	0.160	0.039	0.991
1111	20	0.563	7	0.0126	0.320	0.039	0.991
1186	20	0.601	19	0.0079	0.201	0.041	1.041
1289	19	0.653	1	0.0359	0.912	0.036	0.914
1492	18.5	0.756	7	0.0146	0.371	0.047	1.194
1512	18.5	0.766	30	0.0071	0.180	0.047	1.194
1536	18.5	0.778	384	0.002	0.051	0.047	1.194
1536	18.5	0.778	24	0.008	0.203	0.047	1.194
1600	18	0.811	16	0.01	0.254	0.049	1.245
1608	18	0.815	19	0.0092	0.234	0.049	1.245

Table listing: Circular Mil Area for common wire sizes (Continued)

**Wire Sizes in AWG
and mm² to CMA**

Note: The following tables are applicable to single and multiple strand, round, conductors only.

CMA	Nominal Wire Size		No.	Strands		Approximate Conductor Diameter	
	AWG	mm ²		Diameter		Inch	mm
				Inch	mm		
1617	18	0.819	7	0.0152	0.386	0.042	1.067
1624	18	0.823	1	0.0403	1.024	0.04	1.016
1625	18	0.823	65	0.005	0.127	0.04	1.016
1627	18	0.824	41	0.0063	.0160	0.049	1.245
1639	18	0.830	7	0.0153	0.389	0.042	1.067
1770	18	0.897	7	0.0159	0.404	0.048	1.219
1900	18	0.963	19	0.01	0.254	0.052	1.321
1980	17	1.003	1	0.0445	1.130	0.045	1.143
1999	17	1.013	7	0.0169	0.429	0.047	1.194
2048	17	1.038	32	0.008	0.203	0.047	1.194
2048	17	1.038	512	0.002	0.051	0.049	1.245
2052	17	1.040	1	0.0453	1.151	0.045	1.143
2426	16	1.229	19	0.0113	0.287	0.061	1.549
2521	16	1.277	50	0.0071	0.180	0.059	1.499
2540	16	1.287	16	0.0126	0.320	0.059	1.499
2580	16	1.307	65	0.0063	0.160	0.059	1.499
2581	16	1.308	1	0.0508	1.290	0.051	1.295
2600	16	1.317	26	0.01	0.254	0.061	1.549
2625	16	1.330	105	0.005	0.127	0.059	1.499
2800	16	1.419	7	0.02	0.508	0.061	1.549
2942	15.5	1.491	7	0.0205	0.521	0.059	1.499
2948	15.5	1.494	1	0.0543	1.379	0.054	1.372
3000	15.5	1.520	30	0.01	0.254	0.059	1.499
3073	15.5	1.557	392	0.0028	0.071	0.061	1.549
3260	15	1.652	1	0.0571	1.450	0.057	1.448
3831	14	1.941	19	0.0142	0.361	0.076	1.930
3899	14	1.976	7	0.0236	0.599	0.071	1.803
4079	14	2.067	37	0.0105	0.267	0.073	1.854
4099	14	2.077	7	0.0242	0.615	0.076	1.930
4100	14	2.077	41	0.01	0.254	0.077	1.956
4106	14	2.081	19	0.0147	0.373	0.076	1.930
4109	14	2.082	1	0.0641	1.628	0.064	1.626
4128	14	2.092	26	0.0126	0.320	0.075	1.905
4167	14	2.111	105	0.0063	0.160	0.073	1.854
4234	14	2.145	84	0.0071	0.180	0.074	1.880
4802	13.5	2.433	50	0.0098	0.249	0.087	2.210
4842	13.5	2.453	7	0.0263	0.668	0.079	2.007
4914	13.5	2.490	1	0.0701	1.781	0.07	1.778
5184	13	2.627	1	0.072	1.829	0.072	1.829
6088	12	3.085	19	0.0179	0.455	0.096	2.438
6343	12	3.214	165	0.0062	0.157	0.095	2.413
6475	12	3.281	259	0.005	0.127	0.105	2.667
6500	12	3.294	65	0.01	0.254	0.096	2.438
6503	12	3.295	19	0.0185	0.470	0.092	2.337
6509	12	3.298	41	0.0126	0.320	0.094	2.388
6512	12	3.300	7	0.0305	0.775	0.086	2.184
6529	12	3.308	1	0.0808	2.052	0.081	2.057
6545	12	3.316	37	0.0133	0.338	0.093	2.362
6654	12	3.372	84	0.0089	0.226	0.094	2.388
6946	11.5	3.520	7	0.0315	0.800	0.094	2.388
7856	11.5	3.981	7	0.0335	0.851	0.1	2.540
7985	11.5	4.046	19	0.0205	0.521	0.101	2.565
8064	11.5	4.086	56	0.012	0.305	0.102	2.591
8226	11	4.168	1	0.0907	2.304	0.091	2.311
9072	10	4.597	7	0.036	0.914	0.096	2.438
9472	10	4.799	37	0.016	0.406	0.109	2.769
10080	10	5.108	1	0.1004	2.550	0.1	2.540
10319	10	5.229	37	0.0167	0.424	0.109	2.769
10319	10	5.229	65	0.0126	0.320	0.118	2.997
10365	10	5.252	41	0.0159	0.404	0.122	3.099
10376	10	5.258	7	0.0385	0.978	0.096	2.438
10384	10	5.262	1	0.1019	2.588	0.102	2.591
10404	10	5.272	19	0.0234	0.594	0.117	2.972
10500	10	5.320	105	0.01	0.254	0.116	2.946
10867	10	5.506	7	0.0394	1.001	0.118	2.997
11696	10	5.926	84	0.0118	0.300	0.13	3.302
11710	10	5.933	7	0.0409	1.039	0.128	3.251
11816	10	5.987	1	0.1087	2.761	0.109	2.769
12066	10	6.114	19	0.0252	0.640	0.126	3.200
13087	9	6.5	1	0.1144	2.91	0.114	2.90
13125	9	7	525	.0050	0.13	0.140	3.56
14175	8	7	7	.0450	1.14	0.146	3.71
14368	8	7.5	19	.0275	0.70	0.145	3.68
15595	8	8	7	.0472	1.20	0.142	3.60
15665	8	8	50	.0177	0.45	0.146	3.70

Table listing: Circular Mil Area for common wire sizes (Continued)

**Wire Sizes in AWG
and mm² to CMA**

Note: The following tables are applicable to single and multiple strand, round, conductors only.

CMA	Nominal Wire Size		No.	Strands		Approximate Conductor Diameter	
	AWG	mm ²		Diameter		Inch	mm
				Inch	mm		
16387	8	8	133	.0111	0.28	0.167	4.24
16473	8	8	37	.0211	0.54	0.150	3.81
16512	8	8	1	.1285	3.26	0.129	3.26
16533	8	8	7	.0486	1.23	0.146	3.71
16535	8	8	19	.0295	0.75	0.148	3.76
16589	8	8	49	.0184	0.47	0.150	3.81
16983	8	8.5	133	.0113	0.29	0.167	4.24
18853	7	10	19	.0315	0.80	0.161	4.10
19719	7	10	80	.0157	0.40	0.165	4.20
19737	7	10	7	.0531	1.35	0.159	4.05
19768	7	10	1	.1406	3.57	0.141	3.57
19796	7	10	49	.0201	0.51	0.161	4.10
26179	6	13	37	.0266	0.68	0.174	4.42
26218	6	13	7	.0612	1.55	0.184	4.67
26244	6	13	1	.1620	4.11	0.162	4.11
26292	6	15	19	.0372	0.94	0.202	5.13
26818	6	14	133	.0142	0.36	0.210	5.33
27783	6	14	7	.0630	1.60	0.189	4.80
31057	5.5	16	126	.0157	0.400	0.209	5.30
31329	5.5	16	7	.0669	1.700	0.197	5.00
31400	5.5	16	1	.1772	4.500	0.177	4.50
32199	5	16	37	.0295	0.750	0.197	5.00
33088	5	15.5	1	.1819	4.620	0.182	4.62
40682	4.5	20	41	.0315	0.800	0.236	6.00
41616	4	21	1	.2040	5.182	0.204	5.18
41718	4	21	7	.0772	1.961	0.232	5.89
41771	4	21	37	.0336	0.853	0.240	6.10
41792	4	21	19	.0469	1.191	0.226	5.74
42615	4	21	133	.0179	0.455	0.272	6.90
43356	3.5	22	7	.0787	2.000	0.236	6.00
48312	3	25	196	.0157	0.400	0.260	6.60
48867	3	25	783	.0079	0.200	0.280	7.10
49745	3	25	7	.0843	2.140	0.253	6.42
50010	3	25	84	.0244	0.620	0.260	6.60
57205	2.5	34	7	.0904	2.296	0.292	7.42
57459	2.5	30	7	.0906	2.300	0.272	6.90
66049	2	34	1	.2570	6.528	0.257	6.53
66139	2	34	19	.0590	1.499	0.332	8.43
66500	2	35	665	.0100	0.254	0.345	8.76
66517	2	34	37	.0424	1.077	0.300	7.62
68031	2	35	276	.0157	0.400	0.307	7.80
68857	2	35	19	.0602	1.530	0.301	7.65
69088	2	35	1107	.0079	0.200	0.335	8.50
73400	1.5	38	7	.1024	2.600	0.307	7.80
81700	1	41	817	.0100	0.254	0.382	9.70
83600	1	42	836	.0100	0.254	0.386	9.80
84341	1	40	85	.0315	0.800	0.339	8.60
95509	0	50	19	.0709	1.800	0.354	9.00
97610	0	50	396	.0157	0.400	0.406	10.30
98409	0	50	702	.0118	0.300	0.370	9.40
104500	0	53	1045	.0100	0.254	0.431	10.95
106400	0	54	1064	.0100	0.254	0.435	11.05
117680	0	60	19	.0787	2.000	0.394	10.00
133000	00	67	1330	.0100	0.254	0.486	12.34
135023	00	70	19	.0843	2.140	0.421	10.70
139101	00	70	999	.0118	0.300	0.488	12.40
139712	00	70	360	.0197	0.500	0.488	12.40
155959	000	80	19	.0906	2.300	0.453	11.50
167200	000	85	1672	.0100	0.254	0.545	13.84
184343	000	95	475	.0197	0.500	0.571	14.50
185468	000	95	1332	.0118	0.300	0.571	14.50
186972	000	95	19	.0992	2.520	0.496	12.60
199229	0000	100	19	.1024	2.600	0.512	13.00
210900	0000	105	2109	.0100	0.254	0.635	16.13
235959	0000	120	608	.0197	0.500	0.630	16.00
236208	0000	120	37	.0799	2.030	0.571	14.50
247791	0000	125	19	.1142	2.900	0.571	14.50
249856	250	127	61	.0640	1.623	0.576	14.63
249864	250	127	91	.0524	1.331	0.576	14.63
249870	250	127	12	.1443	3.665	0.600	15.24
249966	250	127	19	.1147	2.913	0.574	14.58
250003	250	127	37	.0822	2.088	0.575	14.61
299700	300	152	37	.0900	2.29	0.630	16.0
299755	300	152	61	.0701	1.781	0.631	16.03
299823	300	152	91	.0574	1.458	0.631	16.03

Table listing: Circular Mil Area for common wire sizes (Continued)

Wire Sizes in AWG and mm² to CMA

Note: The following tables are applicable to single and multiple strand, round, conductors only.

CMA	Nominal Wire Size		No.	Strands		Approximate Conductor Diameter	
	AWG	mm ²		Diameter		Inch	mm
299947	300	152	12	.1581	4.016	0.657	14.66
300209	300	152	19	.1257	3.193	0.629	15.98
349560	350	177	61	.0757	1.923	0.681	17.3
349804	350	177	91	.0620	1.575	0.682	17.32
349875	350	177	19	.1357	3.447	0.679	17.25
350072	350	177	12	.1708	4.338	0.710	18.03
350290	350	177	37	.0973	2.471	0.681	17.3
400026	400	203	19	.1451	3.686	0.726	18.44
400192	400	203	37	.1040	2.642	0.728	18.49
400221	400	203	61	.0810	2.057	0.729	18.49
400008	400	203	91	.0663	1.684	0.729	18.49
499868	500	253	19	.1622	4.12	0.811	20.6
499590	500	253	37	.1162	2.951	0.813	20.65
499605	500	253	61	.0905	2.299	0.815	20.7
499664	500	253	91	.0741	1.882	0.815	20.7
599401	600	304	127	.0687	1.745	0.893	22.68
599596	600	304	37	.1273	3.233	0.891	22.63
600003	600	304	91	.0812	2.062	0.893	22.68
600279	600	304	61	.0992	2.52	0.893	22.68
699216	700	355	127	.0742	1.885	0.965	24.51
699531	700	355	37	.1375	3.493	0.963	24.46
699695	700	355	61	.1071	2.72	0.964	24.49
699907	700	355	91	.0877	2.228	0.965	24.51
750227	750	405	61	.1109	2.817	0.998	25.35
750262	750	405	91	.0908	2.306	0.999	25.37
750277	750	405	37	.1424	3.617	0.997	25.32
749096	750	405	127	.0768	1.951	0.998	25.35
799533	800	456	37	.1470	3.734	1.029	26.14
799725	800	456	61	.1145	2.908	1.031	26.19
800654	800	456	127	.0794	2.017	1.032	26.21
800658	800	456	91	.0938	2.383	1.032	26.21
999197	1000	507	127	.0887	2.253	1.153	29.29
999424	1000	507	61	.1280	3.251	1.152	29.26
999457	1000	507	91	.1048	2.662	1.153	29.29
1000012	1000	507	37	.1644	4.176	1.151	29.24

Chart 2 (Solid Wire) U.S. Customary Dimensions

Use to convert wire size to inches of diameter and CMA. To read mils direct, move decimal point three places to the right.

AWG	Dia. inches	CMA*
4/0	.460	212,000
3/0	.410	168,000
2/0	.365	133,000
1/0	.325	106,000
1	.289	83,700
2	.258	66,400
3	.229	52,600
4	.204	41,700
5	.182	33,100
6	.162	26,300
7	.144	20,800
8	.128	16,500
9	.114	13,100
10	.102	10,400
11	.091	8,230
12	.081	6,530
13	.072	5,180
14	.064	4,110
15	.057	3,260
16	.051	2,580
17	.045	2,050
18	.040	1,620

AWG	Dia. inches	CMA*
19	.036	1,290
20	.032	1,020
21	.0285	810
22	.0253	642
23	.0226	509
24	.0201	404
25	.0179	320
26	.0159	254
27	.0142	202
28	.0126	160
29	.0113	127
30	.0100	101
31	.0089	79.7
32	.0080	63.2
33	.0071	50.1
34	.0063	39.8
35	.0056	31.5
36	.0050	25.0
37	.0045	19.8
38	.0040	15.7
39	.0035	12.5
40	.0031	9.9

Metric Dimensions

Use to convert wire size to millimeters of diameter and CMA.

mm ²	Dia. mm	CMA*
113.1	12	223,000
78.54	10	155,000
63.62	9	125,000
50.27	8	99,200
38.48	7	75,900
33.18	6.5	65,500
28.27	6	55,800
23.76	5.5	46,900
19.64	5	38,800
15.90	4.5	31,400
12.57	4	24,800
9.621	3.5	19,000
8.042	3.2	15,900
6.605	2.9	13,000
5.309	2.6	10,500
4.155	2.3	8,200
3.142	2	6,200
2.545	1.8	5,020
2.011	1.6	3,970
1.539	1.4	3,040
1.131	1.2	2,230
0.7854	1	1,550

mm ²	Dia. mm	CMA*
0.6362	0.9	1,260
0.5027	0.8	992
0.3848	0.7	759
0.3318	0.65	655
0.2827	0.6	558
0.2376	0.55	469
0.1964	0.5	338
0.159	0.45	314
0.1257	0.4	248
0.09621	0.35	190
0.08042	0.32	159
0.06605	0.29	130
0.05309	0.26	105
0.04155	0.23	82
0.03142	0.2	62
0.02545	0.18	50.2
0.02011	0.16	39.7
0.01539	0.14	30.4
0.01131	0.12	22.3
0.00785	0.1	15.5

*Nominal CMA has been "rounded off" for ease of calculation when using multiple wires in one termination.


The SOLISTRAND Terminal

SOLISTRAND terminals and splices are specially designed to terminate solid and stranded wire, irregular shaped conductors, and combinations of these — still retaining the superior performance characteristics of single-purpose terminals and splices. Because AMP matches the terminal to the tool each termination is uniformly perfect, making quality control easy and performance consistent. Corrosion resistance, vibration resistance and tensile strength of these terminals and splices are well within the limits of commercial and military specifications. The SOLISTRAND line includes parallel and butt splices, and flag, ring, spade, hooked, and flanged tongue terminals in sizes from 26 AWG [0.1 mm²] through 600 MCM [304 mm²].

The Crimp

The “W” Crimp is one of several time-proven crimp types developed by AMP. It is not just a “kink” in a metal barrel; not something pinched over electrical wire ends. The “W” Crimp is actually two longitudinal crimps applied with precisely controlled pressure so that the conductor within the barrel flows together into the dimples or serrations of the terminal barrel creating one homogeneous mass of metal. The two indents also help to center conductors within the barrel for uniform crimping of the barrel around the wire. Furthermore, the “W” Crimp permits the use of a shorter terminal barrel, an excellent feature for confined area termination.

The “W” Crimp creates terminations of optimum electrical properties and is completely reliable, giving long service in punishing environments.



BRAZED SEAM. The barrel is completely closed and seam is brazed for uniform metal strength around the entire barrel area.

BASIC TERMINAL MATERIAL. The basic terminal is constructed of fine grade high conductivity copper per ASTM B-152 and tin-plated per MIL-T-10727. Basic material for Spring Spade Tongue Terminals is phosphor bronze per ASTM B-103 and tin-plated per MIL-T-10727. AMP's special plating process creates durable corrosion resistance to salt spray and most chemical fumes.

BELL MOUTH. Bell shape of barrel entrance makes insertion of wires easier.

DIMPLES OR SERRATIONS. Inner surface either dimpled or serrated for optimum tensile strength and maximum electrical contact area after crimping.

SOLISTRAND Terminals meet or exceed the requirements of MIL-T-7928, Type I, Class 1 and 2.

Temperature Rating: 170°C Max.

AMP SOLISTRAND Terminals and Splices (Use SOLISTRAND Tooling)

AMP Inc. Wire Size	 Listed File No. E13288	 LR 7189 Certified
22–16 Solid or Stranded	22–16 Solid or Stranded	22–16 Solid or Stranded
16–14 Solid or Stranded	16–14 Solid or Stranded	16–14 Solid or Stranded
16–14 Heavy Duty Solid or Stranded	16–14 Heavy Duty Stranded	16–14 Heavy Duty Solid or Stranded
14–12 Solid or Stranded	14–12 Stranded	14–12 Solid or Stranded
12–10 Solid or Stranded	12–10 Stranded	12–10 Solid or Stranded
8 thru 600 MCM Solid or Stranded	8 thru 600 MCM Stranded	8 thru 600 MCM Solid or Stranded

Note: 22-16 terminals and splices are stamped 22-18 in accordance with MIL-T-7928. Commercial wire range is 22-16.

DANGER: Not to be used on aluminum wire — may cause equipment failure leading to serious injury or death.


The Budget Terminal

Budget Terminals and splices are primarily the same as SOLISTRAND products except for the absence of the brazed seam in the wire barrel. This terminal is ideal for applications where extreme vibration and tension on the wire are not present. These terminals and splices fulfill the need for an economical and electrically superior termination through the use of high grade materials, long plating experience and a proven crimp.

One of the most desirable features of this terminal and splice is the "F" Crimp. This proven crimp configuration rolls the open seam barrel into the conductor presenting a large surface to the inside of the terminal barrel assuring optimum electrical performance.

The Budget line includes butt splices, ring, rectangular, flanged spade, hooked, and spring spade tongue terminals in sizes from 26 AWG [0.1 mm²] through 10 AWG [6.64 mm²].

BASIC TERMINAL MATERIAL. The basic terminal is constructed of fine grade high conductivity copper per ASTM B-152 and tin-plated per MIL-T-10727. Basic material for Spring Spade Tongue Terminals is phosphor bronze per ASTM B-103 and tin-plated per MIL-T-10727. AMP's special plating process creates durable corrosion resistance to salt spray and most chemical fumes.



BELL MOUTH. Bell shape of barrel entrance makes insertion of wires easier.

SERRATIONS. Inner surface serrated for optimum tensile strength and maximum electrical contact area after crimping.

Temperature Rating: 170°C Max.

AMP Budget Terminals and Splices (Use Budget Tooling)

Wire Size	 Listed File No. E13288
22-16 Stranded	22-16 Stranded
16-14 Stranded	16-14 Stranded
12-10 Stranded	12-10 Stranded

Note: 22-16 terminals and splices are stamped 22-18 in accordance with MIL-T-7928. Commercial wire range is 22-16.

DIAMOND GRIP Terminal

The DIAMOND GRIP product line of terminals and splices is designed for completely uniform reliability under the most critical conditions of vibration, thermal shock, corrosion, tension and current overload. AMP's mated tool/terminal concept represents a total approach to wire termination and takes into account all the factors of circuit termination.

The uniformity of appearance of AMP terminations is repeated by their uniformity in performance—made possible by designing the terminal and the tooling to match precisely. This promotes fast and easy crimping and assures precise crimping pressure for every wire size, regardless of the skill of the operator. The result is the best circuit termination at the lowest applied cost. And this is true for all terminations from first to last, week after week, month after month.

The Crimp

After the wire is inserted into the barrel, the matching dies in the AMP tool close over the barrel, exerting great pressure. This causes the wire strands to flow into the serrations of the terminal barrel as it is compressed around them, forming a homogenous mass of the strands and terminal barrel. This maximum contact assures optimum conductivity of the termination.

COPPER SLEEVE. The specially designed copper sleeve, fitted over the terminal barrel, provides circumferential insulation support to the wire and allows the wire to be bent in any direction, without fraying the wire's insulation or breaking the conductor.

SERRATIONS. Serrations inside the barrel provide maximum contact and tensile strength after crimping.

BELL MOUTH. Assures easy wire insertion.

BASIC TERMINAL MATERIAL. The basic terminal is constructed of fine grade high conductivity copper per ASTM B-152 and tin-plated per MIL-T-10727. AMP's special plating process creates durable corrosion resistance to salt spray and most chemical fumes.

"V" NOTCHES. These lock the wire insulation against vibration and pullout.

Temperature Rating: 170°C Max.

DIAMOND GRIP Terminals and Splices (Use DIAMOND GRIP Tooling)

AMP Wire Range	 Listed	 LR 7189 Certified
22-16	22-16 Stranded	22-16 Stranded
16-14	16-14 Stranded	16-14 Stranded
16-14 HD	16-14 HD Stranded	—
12-10	12-10 Stranded	12-10 Stranded

Terminal Stud Hole Size

Use to Select Proper Size Terminal

The chart shows sizes and dimensions of various studs and the corresponding terminal stud hole sizes used with AMP devices. For example, with stud #5 (.125 [3.18] Diameter), use AMP device listed for #5 stud (.132 [3.35] Hole Diameter). Terminal stud hole sizes may easily be checked by fitting sample terminal to black circle.

Stud Size		Stud Dia.		Typical Terminal Stud Hole Diameter
U.S. Cust.	Metric			
#0	—	.060 1.52	●	.067 ± .003 1.70 ± 0.08
#1	—	.073 1.85	●	.080 ± .003 2.03 ± 0.08
#2	M2	.086 2.18	●	.093 ± .003 2.36 ± 0.08
#3	—	.099 2.51	●	Not Available
#4	—	.112 2.84	●	.119 ± .003 3.02 ± 0.08
#5	M3	.125 3.18	●	.132 ± .003 3.35 ± 0.08
#6	M3.5	.138 3.51	●	.145 ± .003 3.68 ± 0.08
#8	M4	.164 4.17	●	.171 ± .003 4.34 ± 0.08
#10	—	.190 4.83	●	.197 ± .003 5.00 ± 0.08
#12	—	.216 5.49	●	.223 ± .003 5.66 ± 0.08
#14	—	.242 6.15	●	.250 ± .003 6.35 ± 0.08
1/4"	M6	.250 6.35	●	.265 ± .005 6.73 ± 0.13
5/16"	M8	.312 7.92	●	.328 ± .005 8.33 ± 0.13
3/8"	—	.375 9.53	●	.390 ± .005 9.91 ± 0.13

Stud Size		Stud Dia.		Typical Terminal Stud Hole Diameter
U.S. Cust.	Metric			
7/16"	—	.437 11.10	●	.453 ± .005 11.51 ± 0.13
1/2"	M12	.500 12.70	●	.515 ± .005 13.08 ± 0.13
5/8"	M16	.625 15.88	●	.656 ± .005 16.66 ± 0.13
3/4"	—	.750 19.05	●	.781 ± .005 19.84 ± 0.13
7/8"	M22	.875 22.23	●	.906 ± .005 23.01 ± 0.13
1"	—	1.000 25.40	●	1.031 ± .005 26.19 ± 0.13

Ring Tongue Terminals


Wire Size Range

AWG 26 to 16,
CMA 202 to 3,260
[0.1 to 1.65 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Style	Dimensions				Material Thickness Max.	Wire Barrel I.D. Min.		Part Numbers	
			L Max.	E Max.	C Min.	W		Solistrand	Budget	Solistrand	Budget
26–22 202–810 [0.1–0.41]	0	A	.329 8.36	.256 6.50	.121 3.07	.140 3.56	.020 0.51	—	.035 0.89	—	31423
		A	.329 8.36	.256 6.50	.121 3.07	.140 3.56	.020 0.51	—	.035 0.89	—	31425 2-31425-2
	2 M2	A	.450 11.43	.346 8.79	.211 5.36	.203 5.16	.020 0.51	—	.035 0.89	—	33695
		A	.419 10.64	.346 8.79	.211 5.36	.140 3.56	.020 0.51	.031 0.79	.035 0.89	50334*	322771
	4	A	.450 11.43	.346 8.79	.211 5.36	.203 5.16	.020 0.51	—	.035 0.89	—	31428
		A	.450 11.43	.346 8.79	.211 5.36	.203 5.16	.020 0.51	—	.035 0.89	—	31430
	6 M3.5	A	.544 13.82	.416 10.57	.281 7.14	.250 6.35	.020 0.51	.031 0.79	.035 0.89	331401 1-331401-1	32858
		A	.544 13.82	.416 10.57	.281 7.14	.250 6.35	.020 0.51	—	.035 0.89	—	32859
	10	A	.544 13.82	.416 10.57	.281 7.14	.250 6.35	.020 0.51	—	.035 0.89	—	32860
		A	.544 13.82	.416 10.57	.281 7.14	.250 6.35	.020 0.51	—	.035 0.89	—	32860
22–16 509–3,260 [0.26–1.65]	1	A	.449 11.40	.337 8.56	.156 3.96	.218 5.54	.033 0.84	—	.065 1.65	—	31087
		A	.449 11.40	.337 8.56	.156 3.96	.218 5.54	.033 0.84	.061 1.55	.065 1.65	34103 2-34103-1	31088
	2 M2	A	.446 11.33	.353 8.97	.172 4.37	.182 4.62	.033 0.84	.061 1.55	.065 1.65	322927	320677
		A	.449 11.40	.337 8.56	.156 3.96	.218 5.54	.033 0.84	.061 1.55	.065 1.65	34104* 2-34104-6	31089 3-31089-6
	4	A	.446 11.33	.353 8.97	.172 4.37	.182 4.62	.033 0.84	.061 1.55	.065 1.65	36467*	36189 2-326850-1
		A	.621 15.77	.493 12.52	.312 7.92	.250 6.35	.033 0.84	.061 1.55	.065 1.65	323096 2-323096-2	322418
	5 M3	A	.449 11.40	.337 8.56	.156 3.96	.218 5.54	.033 0.84	—	.065 1.65	—	31090 2-31090-1
		A	.449 11.40	.337 8.56	.156 3.96	.218 5.54	.033 0.84	.061 1.55	.065 1.65	34105* 2-34105-2	31091
	6 M3.5	A	.528 13.41	.416 10.57	.156 3.96	.218 5.54	.033 0.84	.061 1.55	.065 1.65	34194	31101
		A	.574 14.58	.436 11.07	.250 6.35	.281 7.14	.033 0.84	.061 1.55	.065 1.65	34107* 2-34107-2	31264
	8 M4	A	.621 15.77	.462 11.73	.281 7.14	.312 7.92	.033 0.84	.061 1.55	.065 1.65	34110* 2-34110-3	30691* 1-30691-1
		A	.653 16.59	.478 12.14	.297 7.54	.344 8.74	.033 0.84	—	.065 1.65	—	32822
	8 M4	A	.621 15.77	.462 11.73	.281 7.14	.312 7.92	.033 0.84	.061 1.55	.065 1.65	34111* 2-34111-3	30692
		A	.574 14.58	.436 11.07	.250 6.35	.281 7.14	.033 0.84	.061 1.55	.065 1.65	34108* 2-34108-2	31265*
	8 M4	A	.653 16.59	.478 12.14	.297 7.54	.344 8.74	.033 0.84	.061 1.55	.065 1.65	323086	32823
		A	.653 16.59	.478 12.14	.297 7.54	.344 8.74	.033 0.84	.061 1.55	.065 1.65	323086	32823

Note: Part numbers are shown as loose piece over tape mounted product.

*Part numbers are available in small quantity packages.

Ring Tongue Terminals (Continued)


Wire Size Range

AWG 22 to 14,
CMA 509 to 5,180
[0.26 to 2.62 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Style	Dimensions				Material Thickness Max.	Wire Barrel I.D. Min.		Part Numbers	
			L Max.	E Max.	C Min.	W		Solistrand	Budget	Solistrand	Budget
22-16 509-3,260 [0.26-1.65]	10	A	.621 15.77	.462 11.73	.281 7.14	.312 7.92	.033 0.84	.061 1.55	.065 1.65	34112* 2-34112-2	30693* 3-30693-7
		A	.574 14.58	.436 11.07	.250 6.35	.281 7.14	.033 0.84	.061 1.55	.065 1.65	34109* 2-34109-2	31266
		A	.653 16.59	.478 12.14	.297 7.54	.344 8.74	.033 0.84	.061 1.55	.065 1.65	323087*	32824
	12	A	.621 15.77	.462 11.73	.281 7.14	.312 7.92	.033 0.84	—	.065 1.65	—	30694 2-30694-1
	1/4 M6	A	.856 21.74	.618 15.70	.437 11.10	.469 11.91	.033 0.84	.061 1.55	.065 1.65	34113* 2-34113-2	31172
	5/16 M8	A	.856 21.74	.618 15.70	.437 11.10	.469 11.91	.033 0.84	.061 1.55	.065 1.65	34114* 2-34114-2	31173 3-31173-3
		A	.995 25.27	.727 18.47	.546 13.87	.531 13.49	.033 0.84	—	.065 1.65	—	324124
	3/8	A	.995 25.27	.727 18.47	.546 13.87	.531 13.49	.033 0.84	.061 1.55	.065 1.65	34115* 2-34115-2	31498
	1/2 M12	A	1.070 27.18	.711 18.06	.530 13.46	.713 18.11	.033 0.84	.061 1.55	.065 1.65	329966*	328970
		A	.480 12.19	.352 8.94	.171 4.34	.250 6.35	.033 0.84	—	.089 2.26	—	321007
16-14 2,050-5,180 [1.04-2.62]	2 M2	A	.445 11.30	.352 8.94	.171 4.34	.180 4.57	.033 0.84	.085 2.16	.089 2.26	328377	326854
	4	A	.480 12.19	.352 8.94	.171 4.34	.250 6.35	.033 0.84	.085 2.16	.089 2.26	34119* 2-34119-1	32185
		A	.636 16.15	.462 11.73	.281 7.14	.343 8.71	.033 0.84	.085 2.16	.089 2.26	34121* 2-34121-1	30695
	6 M3.5	A	.480 12.19	.352 8.94	.171 4.34	.250 6.35	.033 0.84	.085 2.16	.089 2.26	34120* 2-34120-1	32186*
		A	.590 14.99	.431 10.95	.250 6.35	.312 7.92	.033 0.84	.085 2.16	.089 2.26	321684* 2-321684-1	321683
	8 M4	A	.636 16.15	.462 11.73	.281 7.14	.343 8.71	.033 0.84	.085 2.16	.089 2.26	34122* 2-34122-1	30696*
		A	.590 14.99	.431 10.95	.250 6.35	.312 7.92	.033 0.84	.085 2.16	.089 2.26	324955* 2-324955-1	322235 1-322235-1
		A	.621 15.77	.462 11.73	.281 7.14	.312 7.92	.033 0.84	—	.089 2.26	—	51872-5
	10	A	.636 16.15	.462 11.73	.281 7.14	.343 8.71	.033 0.84	.085 2.16	.089 2.26	34123* 2-34123-1	30697*
		A	.669 16.99	.510 12.95	.250 6.35	.312 7.92	.033 0.84	.085 2.16	.089 2.26	320093 2-320093-1	31049
	12	A	.855 21.72	.618 15.70	.437 11.10	.469 11.91	.033 0.84	—	.089 2.26	—	31163
	14	A	.730 18.54	.493 12.52	.312 7.92	.468 11.89	.033 0.84	—	.089 2.26	—	34896

Note: Part numbers are shown as loose piece over tape mounted product.

*Part numbers are available in small quantity packages.

Ring Tongue Terminals (Continued)


Wire Size Range

AWG 16 to 10,
CMA 2,050 to 13,100
[1.04 to 6.64 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Style	Dimensions				Material Thickness Max.	Wire Barrel I.D. Min.		Part Numbers	
			L Max.	E Max.	C	W		Solistrand	Budget	Solistrand	Budget
16-14 2,050-5,180 [1.04-2.62]	1/4 M6	A	.855 21.72	.618 15.70	.437 11.10	.469 11.91	.033 0.84	.085 2.16	.089 2.26	34124* 2-34124-1	31164
	5/16 M8	A	.855 21.72	.618 15.70	.437 11.10	.469 11.91	.033 0.84	.085 2.16	.089 2.26	34125* 2-34125-6	31165
	3/8	A	.995 25.27	.727 18.47	.546 13.87	.531 13.49	.033 0.84	.085 2.16	.089 2.26	34126* 2-34126-2	31499
	1/2	A	1.070 27.18	.711 18.06	.530 13.46	.713 18.11	.033 0.84	—	.089 2.26	—	328971
	M12	A	1.184 30.07	.806 20.47	.625 15.88	.750 19.05	.033 0.84	.085 2.16	.089 2.26	50981	50982
14-12 3,260-8,230 [1.65-4.17]	8 M4	B	.685 17.40	.526 13.36	.250 6.35	.312 7.92	.042 1.07	.098 2.49	—	321827	—
	10	B	.739 18.77	.526 13.36	.250 6.35	.421 10.69	.042 1.07	.098 2.49	—	34484 1-34484-0	—
		B	.685 17.40	.526 13.36	.250 6.35	.312 7.92	.042 1.07	.098 2.49	—	321828 1-321828-0	—
	1/4 M6	B	.739 18.77	.526 13.36	.250 6.35	.421 10.69	.042 1.07	.098 2.49	—	34487	—
	3/8	B	1.120 28.45	.774 19.66	.437 11.10	.687 17.45	.042 1.07	.098 2.49	—	34486	—
12-10 5,180-13,100 [2.62-6.64]	4	A	.630 16.00	.487 12.37	.219 5.56	.281 7.14	.042 1.07	.129 3.28	.134 3.40	322447	34891
		A	.630 16.00	.487 12.37	.219 5.56	.281 7.14	.042 1.07	.129 3.28	.134 3.40	35476* 2-35476-1	34892
	6 M3.5	A	.729 18.52	.570 14.48	.302 7.67	.312 7.92	.042 1.07	.129 3.28	.134 3.40	324911	324910
		A	.765 19.43	.575 14.61	.302 7.67	.375 9.53	.042 1.07	.129 3.28	.134 3.40	33456 2-33456-1	31112
	8 M4	A	.708 17.98	.549 13.94	.281 7.14	.312 7.92	.042 1.07	.129 3.28	.134 3.40	322454*	34404*
		A	.765 19.43	.575 14.61	.302 7.67	.375 9.53	.042 1.07	.129 3.28	.134 3.40	32994* 2-32994-1	31113
		A	.723 18.36	.549 13.94	.281 7.14	.343 8.71	.042 1.07	.129 3.28	.134 3.40	322455 2-322455-1	32882
		A	.765 19.43	.575 14.61	.302 7.67	.375 9.53	.042 1.07	.129 3.28	.134 3.40	33457* 2-33457-2	31114*
	10	A	.808 20.52	.618 15.70	.343 8.71	.375 9.53	.042 1.07	.129 3.28	.134 3.40	31805	321829
		A	.865 21.97	.612 15.54	.344 8.74	.500 12.70	.042 1.07	.129 3.28	.134 3.40	35771* 2-35771-1	34964
		A	1.004 25.50	.736 18.69	.468 11.89	.531 13.49	.042 1.07	.129 3.28	.134 3.40	36451	31120
	1/4 M6	A	.865 21.97	.612 15.54	.344 8.74	.500 12.70	.042 1.07	.129 3.28	.134 3.40	35772* 2-35772-1	34965
		A	1.004 25.50	.736 18.69	.468 11.89	.531 13.49	.042 1.07	.129 3.28	.134 3.40	33458* 2-33458-3	31122*
	5/16 M8	A	.865 21.97	.612 15.54	.344 8.74	.500 12.70	.042 1.07	—	.134 3.40	—	34966
		A	1.004 25.50	.736 18.69	.468 11.89	.531 13.49	.042 1.07	.129 3.28	.134 3.40	33459* 2-33459-6	31123

Note: Part numbers are shown as loose piece over tape mounted product.

*Part numbers are available in small quantity packages.

Ring Tongue Terminals (Continued)


Wire Size Range

AWG 12 to 8,
CMA 5,180 to 20,800
[2.62 to 10.5 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Style	Dimensions				Material Thickness Max.	Wire Barrel I.D. Min.		Part Numbers	
			L Max.	E Max.	C	W		Solistrand	Budget	Solistrand	Budget
12-10 5,180-13,100 [2.62-6.64]	3/8	A	1.098 27.89	.799 20.29	.531 13.49	.593 15.06	.042 1.07	.129 3.28	.134 3.40	33220* 1-33220-2 ³	30972
		A	1.271 32.28	.893 22.68	.625 15.88	.750 19.05	.042 1.07	.129 3.28	.134 3.40	322242	34833
	1/2 M12	A	1.102 27.99	.742 18.85	.474 12.04	.715 18.16	.042 1.07	—	.134 3.40	—	52269-1
		A	1.271 32.28	.893 22.68	.625 15.88	.750 19.05	.042 1.07	.129 3.28	.134 3.40	35135 2-35135-2 ³	34834
		A	1.896 48.16	1.268 32.21	1.000 25.40	1.250 31.75	.042 1.07	.129 3.28	.134 3.40	320763	320760
		A	1.896 48.16	1.268 32.21	1.000 25.40	1.250 31.75	.042 1.07	.129 3.28	.134 3.40	320764	320761
	5/8 M16	A	1.896 48.16	1.268 32.21	1.000 25.40	1.250 31.75	.042 1.07	.129 3.28	.134 3.40	320765	320762
	3/4	A	1.896 48.16	1.268 32.21	1.000 25.40	1.250 31.75	.042 1.07	.129 3.28	.134 3.40	320765-1	—
	7/8 M22	A	1.896 48.16	1.268 32.21	1.000 25.40	1.250 31.75	.042 1.07	.129 3.28	—	1-320765-0	—
	1	A	1.896 48.16	1.268 32.21	1.000 25.40	1.250 31.75	.042 1.07	.129 3.28	—	1-320765-0	—
13,100-20,800 [6.64-10.5]	8 M4	C	.949 24.10	.743 18.87	.359 9.12	.406 10.31	.051 1.30	.172 4.37	—	324061*	—
		C	.933 23.70	.696 17.68	.359 9.12	.469 11.91	.051 1.30	.172 4.37	—	32996*	—
	10	C	.933 23.70	.696 17.68	.359 9.12	.469 11.91	.051 1.30	.172 4.37	—	33460* 2-33460-2* ¹ 2-33460-3* ²	—
		C	.949 24.10	.743 18.87	.359 9.12	.406 10.31	.051 1.30	.172 4.37	—	31807 2-31807-2* ²	—
	1/4 M6	C	.933 23.70	.696 17.68	.359 9.12	.469 11.91	.051 1.30	.172 4.37	—	33461* 2-33461-2* ¹ 2-33461-3* ²	—
		A	1.168 29.67	.868 22.05	.531 13.49	.594 15.09	.051 1.30	.172 4.37	—	35247*	—
	5/16 M8	A	1.168 29.67	.868 22.05	.531 13.49	.594 15.09	.051 1.30	.172 4.37	—	33462* 2-33462-1 ²	—
		A	1.074 27.28	.790 20.07	.406 10.31	.562 14.27	.051 1.30	.172 4.37	—	31808*	—
		C	.933 23.70	.696 17.68	.359 9.12	.469 11.91	.051 1.30	.172 4.37	—	55991-1 55991-2	—
		A	1.168 29.67	.868 22.05	.531 13.49	.594 15.09	.051 1.30	.172 4.37	—	33463*	—
	3/8	A	1.965 49.91	1.337 33.96	1.000 25.40	1.250 31.75	.051 1.30	.172 4.37	—	36499	—
	1/2 M12	A	1.965 49.91	1.337 33.96	1.000 25.40	1.250 31.75	.051 1.30	.172 4.37	—	35664*	—
	5/8 M16	A	1.965 49.91	1.337 33.96	1.000 25.40	1.250 31.75	.051 1.30	.172 4.37	—	35665	—
	3/4	A	1.965 49.91	1.337 33.96	1.000 25.40	1.250 31.75	.051 1.30	.172 4.37	—	35666	—

Note: Part numbers are shown as loose piece over tape mounted product.

*Part numbers are available in small quantity packages.

¹Requires a 69875 standard TAPETRONIC machine for application.

²Requires a 68250-1 Heavy Duty TAPETRONIC machine for application.

³Requires a 68250-1 Heavy Duty TAPETRONIC and 68242-2 die set for application.

Ring Tongue Terminals (Continued)


Wire Size Range

AWG 6 to 4,
CMA 20,800 to 52,600
[10.5 to 26.7 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Style	Dimensions				Material Thickness Max.	Wire Barrel I.D. Min. Solistrand	Part Numbers Solistrand
			L Max.	E Max.	C	W			
6 20,800–33,100 [10.5–16.8]	10	C	1.181 30.00	.931 23.65	.531 13.49	.406 10.31	.060 1.52	.232 5.89	52197* 52197-1
		C	1.181 30.00	.984 24.99	.584 14.83	.406 10.31	.060 1.52	.232 5.89	53106-1
		C	1.246 31.65	.931 23.65	.531 13.49	.625 15.88	.060 1.52	.232 5.89	33464*
		C	1.168 29.67	.931 23.65	.531 13.49	.468 11.89	.060 1.52	.232 5.89	321298* 2-321298-6
	1/4 M6	C	1.246 31.65	.931 23.65	.531 13.49	.625 15.88	.060 1.52	.232 5.89	33465* 2-33465-1
		C	1.168 29.67	.931 23.65	.531 13.49	.468 11.89	.060 1.52	.232 5.89	321598* 2-321598-3
	5/16 M8	C	1.246 31.65	.931 23.65	.531 13.49	.625 15.88	.060 1.52	.232 5.89	33466* 2-33466-3
		C	1.246 31.65	.931 23.65	.531 13.49	.625 15.88	.060 1.52	.232 5.89	33467* 2-33467-3
	3/8	A	2.033 51.64	1.400 35.56	1.000 25.40	1.250 31.75	.060 1.52	.232 5.89	36807
		C	1.246 31.65	.931 23.65	.531 13.49	.625 15.88	.060 1.52	.232 5.89	320745
	1/2 M12	C	1.840 46.74	1.400 35.56	1.000 25.40	.875 22.23	.060 1.52	.232 5.89	320344*
		A	2.033 51.64	1.400 35.56	1.000 25.40	1.250 31.75	.060 1.52	.232 5.89	36808
	5/8	A	2.033 51.64	1.400 35.56	1.000 25.40	1.250 31.75	.060 1.52	.232 5.89	36809
		A	2.033 51.64	1.400 35.56	1.000 25.40	1.250 31.75	.060 1.52	.232 5.89	36810
4 33,100–52,600 [16.8–26.7]	10	A	1.314 33.38	.978 24.84	.516 13.11	.656 16.66	.073 1.85	.296 7.52	33468*
		C	1.199 30.45	.946 24.03	.437 11.10	.500 12.70	.073 1.85	.280 7.11	33114
	1/4 M6	A	1.314 33.38	.978 24.84	.516 13.11	.656 16.66	.073 1.85	.296 7.52	33469*
		C	1.199 30.45	.946 24.03	.437 11.10	.500 12.70	.073 1.85	.280 7.11	2-31811-4
	5/16 M8	A	1.314 33.38	.978 24.84	.516 13.11	.656 16.66	.073 1.85	.296 7.52	33470*
		C	1.324 33.63	1.009 25.63	.500 12.70	.625 15.88	.073 1.85	.280 7.11	33115
	3/8	A	1.314 33.38	.978 24.84	.516 13.11	.656 16.66	.073 1.85	.296 7.52	33471*
		A	2.090 53.09	1.462 37.13	1.000 25.40	1.250 31.75	.073 1.85	.296 7.52	36815
		C	1.902 48.31	1.462 37.13	1.000 25.40	.875 22.23	.073 1.85	.296 7.52	322704
		C	1.324 33.63	1.009 25.63	.500 12.70	.625 15.88	.073 1.85	.280 7.11	31812

Note: Part numbers are shown as loose piece over tape mounted product.

*Part numbers are available in small quantity packages.
semi-automatic pneumatic crimping system.

Ring Tongue Terminals (Continued)


Wire Size Range

AWG 4 to 1/0,
CMA 33,100 to 119,500
[16.8 to 60.6 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Style	Dimensions				Material Thickness Max.	Wire Barrel I.D. Min. Solistrand	Part Numbers Solistrand
			L Max.	E Max.	C	W			
4 33,100–52,600 [16.8–26.7]	7/16	A**	1.314 33.38	.978 24.84	.516 13.11	.656 16.66	.073 1.85	.296 7.52	320743
	1/2 M12	A**	2.090 53.09	1.462 37.13	1.000 25.40	1.250 31.75	.073 1.85	.296 7.52	35668*
		B	1.902 48.31	1.462 37.13	1.000 25.40	.875 22.23	.073 1.85	.296 7.52	327175*
	5/8 M16	A**	2.090 53.09	1.462 37.13	1.000 25.40	1.250 31.75	.073 1.85	.296 7.52	35669
	3/4	A**	2.090 53.09	1.462 37.13	1.000 25.40	1.250 31.75	.073 1.85	.296 7.52	35670
2 52,600–83,700 [26.7–42.4]	10	B	1.527 38.79	1.212 30.78	.531 13.49	.625 15.88	.073 1.85	.370 9.40	330301
	1/4 M6	B	1.527 38.79	1.212 30.78	.531 13.49	.625 15.88	.073 1.85	.370 9.40	320383*
		D	1.657 42.09	1.212 30.78	.531 13.49	.890 22.61	.073 1.85	.370 9.40	320138
	5/16 M8	D	1.657 42.09	1.212 30.78	.531 13.49	.890 22.61	.073 1.85	.370 9.40	35183
		B	1.527 38.79	1.212 30.78	.531 13.49	.625 15.88	.073 1.85	.370 9.40	322870*
	3/8	B	1.527 38.79	1.212 30.78	.531 13.49	.625 15.88	.073 1.85	.370 9.40	321600*
		D	1.657 42.09	1.212 30.78	.531 13.49	.890 22.61	.073 1.85	.370 9.40	35184
	7/16	D	1.657 42.09	1.212 30.78	.531 13.49	.890 22.61	.073 1.85	.370 9.40	320741
	1/2 M12	D	1.657 42.09	1.212 30.78	.531 13.49	.890 22.61	.073 1.85	.370 9.40	35185*
		D	2.516 63.91	1.888 47.96	1.125 28.58	1.250 31.75	.073 1.85	.370 9.40	323291
	5/8 M16	D	2.516 63.91	1.888 47.96	1.125 28.58	1.250 31.75	.073 1.85	.370 9.40	320754
		D	2.516 63.91	1.888 47.96	1.125 28.58	1.250 31.75	.073 1.85	.370 9.40	320755
	1/4 M6	C	1.956 49.68	1.529 38.84	.625 15.88	.875 22.23	.073 1.85	.444 11.28	36915
		C	1.925 48.90	1.532 38.91	.625 15.88	.807 20.50	.073 1.85	.444 11.28	321866
1/0 83,700–119,500 [42.4–60.6]	5/16 M8	C	1.956 49.68	1.529 38.84	.625 15.88	.875 22.23	.073 1.85	.444 11.28	36916*
		C	1.925 48.90	1.532 38.91	.625 15.88	.807 20.50	.073 1.85	.444 11.28	321867*
	3/8	C	1.956 49.68	1.529 38.84	.625 15.88	.875 22.23	.073 1.85	.444 11.28	36917*
		C	1.925 48.90	1.532 38.91	.625 15.88	.807 20.50	.073 1.85	.444 11.28	321868
	7/16	C	1.956 49.68	1.529 38.84	.625 15.88	.875 22.23	.073 1.85	.444 11.28	36918
		C	1.925 48.90	1.532 38.91	.625 15.88	.807 20.50	.073 1.85	.444 11.28	321868
	1/2	C	1.956 49.68	1.529 38.84	.625 15.88	.875 22.23	.073 1.85	.444 11.28	36918

*Part numbers are available in small quantity packages.

** See style A art on preceding page.

Ring Tongue Terminals (Continued)



Wire Size Range

AWG 1/0 to 3/0,
CMA 83,700 to 190,000
[42.4 to 96.3 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Style	Dimensions				Material Thickness Max.	Wire Barrel I.D. Min. Solistrand	Part Numbers Solistrand
			L Max.	E Max.	C	W			
1/0 83,700–119,500 [42.4–60.6]	1/2 M12	C	1.956 49.68	1.529 38.84	.625 15.88	.875 22.23	.073 1.85	.444 11.28	36919*
		C	2.678 68.02	2.063 52.40	1.125 28.58	1.265 32.13	.073 1.85	.444 11.28	322291
	5/8 M16	C	2.678 68.02	2.063 52.40	1.125 28.58	1.265 32.13	.073 1.85	.444 11.28	320744
		C	2.678 68.02	2.063 52.40	1.125 28.58	1.265 32.13	.073 1.85	.444 11.28	320748
2/0 119,500–150,500 [60.6–76.3]	1/4 M6	C	1.930 49.02	1.550 39.37	.625 15.88	.926 23.52	.083 2.11	.504 12.80	321869
		C	2.000 50.80	1.545 39.24	.625 15.88	.946 24.03	.083 2.11	.504 12.80	36921
	5/16 M8	C	1.930 49.02	1.550 39.37	.625 15.88	.926 23.52	.083 2.11	.504 12.80	321870*
		C	2.000 50.80	1.545 39.24	.625 15.88	.946 24.03	.083 2.11	.504 12.80	36922
	3/8	C	1.930 49.02	1.550 39.37	.625 15.88	.926 23.52	.083 2.11	.504 12.80	321871*
		C	2.000 50.80	1.545 39.24	.625 15.88	.946 24.03	.083 2.11	.504 12.80	36923*
	7/16	C	1.930 49.02	1.550 39.37	.625 15.88	.926 23.52	.083 2.11	.504 12.80	321872
		C	1.930 49.02	1.550 39.37	.625 15.88	.926 23.52	.083 2.11	.504 12.80	321873*
	1/2 M12	C	2.000 50.80	1.545 39.24	.625 15.88	.946 24.03	.083 2.11	.504 12.80	36925*
		C	2.671 67.84	2.056 52.22	1.125 28.58	1.270 32.26	.083 2.11	.504 12.80	322391
	5/8 M16	C	2.671 67.84	2.056 52.22	1.125 28.58	1.270 32.26	.083 2.11	.504 12.80	322224
		C	2.671 67.84	2.056 52.22	1.125 28.58	1.270 32.26	.083 2.11	.504 12.80	322225
	3/4	C	2.671 67.84	2.056 52.22	1.125 28.58	1.270 32.26	.083 2.11	.504 12.80	322225
		C	2.671 67.84	2.056 52.22	1.125 28.58	1.270 32.26	.083 2.11	.504 12.80	322225
3/0 150,500–190,000 [76.3–96.3]	1/4	B	2.112 53.64	1.622 41.20	.625 15.88	1.020 25.91	.094 2.39	.565 14.35	323868
		B	2.112 53.64	1.622 41.20	.625 15.88	1.020 25.91	.094 2.39	.565 14.35	321874
	5/16 M8	B	2.143 54.43	1.643 41.73	.625 15.88	1.082 27.48	.094 2.39	.565 14.35	320266
		B	2.143 54.43	1.643 41.73	.625 15.88	1.082 27.48	.094 2.39	.565 14.35	321875*
	3/8	B	2.112 53.64	1.622 41.20	.625 15.88	1.020 25.91	.094 2.39	.565 14.35	321875*
		B	2.143 54.43	1.643 41.73	.625 15.88	1.082 27.48	.094 2.39	.565 14.35	36927*
	7/16	B	2.112 53.64	1.622 41.20	.625 15.88	1.020 25.91	.094 2.39	.565 14.35	321876
		B	2.112 53.64	1.622 41.20	.625 15.88	1.020 25.91	.094 2.39	.565 14.35	321876

*Part numbers are available in small quantity packages.

Ring Tongue Terminals (Continued)


Wire Size Range

**AWG 3/0 to 300 MCM,
CMA 150,500 to 300,000
[76.3 to 152 mm²]**

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Style	Dimensions				Material Thickness Max.	Wire Barrel I.D. Min. Solistrand	Part Numbers Solistrand
			L Max.	E Max.	C	W			
3/0 150,500–190,000 [76.3–96.3]	1/2 M12	B	2.143 54.43	1.643 41.73	.625 15.88	1.082 27.48	.094 2.39	.565 14.35	36929*
		B	2.112 53.64	1.622 41.20	.625 15.88	1.020 25.91	.094 2.39	.565 14.35	321877*
	5/8 M16	C	2.699 68.55	2.084 52.93	1.125 28.58	1.270 32.26	.094 2.39	.565 14.35	322222
		B	2.143 54.43	1.643 41.73	.625 15.88	1.082 27.48	.094 2.39	.565 14.35	36930
	3/4	C	2.699 68.55	2.084 52.93	1.125 28.58	1.270 32.26	.094 2.39	.565 14.35	322223
4/0 190,000–231,000 [96.3–117]	1/4 M6	B	2.206 56.03	1.644 41.76	.625 15.88	1.150 29.21	.105 2.67	.635 16.13	2-36932-2
	5/16 M8	B	2.537 64.44	1.985 50.42	1.078 27.38	1.150 29.21	.105 2.67	.635 16.13	321271
	3/8	B	2.206 56.03	1.644 41.76	.625 15.88	1.150 29.21	.105 2.67	.635 16.13	36932
		B	2.178 55.32	1.657 42.09	.625 15.88	1.087 27.61	.105 2.67	.635 16.13	321878*
	7/16	B	2.178 55.32	1.657 42.09	.625 15.88	1.087 27.61	.105 2.67	.635 16.13	321879
	1/2 M12	B	2.178 55.32	1.657 42.09	.625 15.88	1.087 27.61	.105 2.67	.635 16.13	321880*
		B	2.206 56.03	1.644 41.76	.625 15.88	1.150 29.21	.105 2.67	.635 16.13	36934*
		B	2.537 64.44	1.985 50.42	1.078 27.38	1.150 29.21	.105 2.67	.635 16.13	321163
		B	2.206 56.03	1.644 41.76	.625 15.88	1.150 29.21	.105 2.67	.635 16.13	36935
	5/8 M16	C	2.732 69.39	2.117 53.77	1.078 27.38	1.275 32.39	.105 2.67	.635 16.13	322227
	3/4	C	2.732 69.39	2.117 53.77	1.078 27.38	1.275 32.39	.105 2.67	.635 16.13	322228
	7/8 M22	C	2.732 69.39	2.117 53.77	1.078 27.38	1.275 32.39	.105 2.67	.635 16.13	321625
250–300 MCM 231,000–300,000 [117–152]	3/8	B	2.602 66.09	1.987 50.47	.625 15.88	1.435 36.45	.130 3.30	.753 19.13	322252
	7/16	B	2.602 66.09	1.987 50.47	.625 15.88	1.435 36.45	.130 3.30	.753 19.13	322253
	1/2 M12	B	2.602 66.09	1.987 50.47	.625 15.88	1.435 36.45	.130 3.30	.753 19.13	322254
	5/8 M16	B	2.602 66.09	1.987 50.47	.625 15.88	1.435 36.45	.130 3.30	.753 19.13	323050
	3/4	B	3.259 82.78	2.566 65.18	1.203 30.56	1.435 36.45	.130 3.30	.753 19.13	323140
	1	B	3.259 82.78	2.566 65.18	1.203 30.56	1.435 36.45	.130 3.30	.753 19.13	323034
			3.259 82.78	2.566 65.18	1.203 30.56	1.435 36.45	.130 3.30	.753 19.13	

*Part numbers are available in small quantity packages.

Ring Tongue Terminals (Continued)


Wire Size Range

**300 to 600 MCM,
CMA 300,000 — 600,000
[152 to 304 mm²]**

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm²]	Stud Size	Style	Dimensions				Material Thickness Max.	Wire Barrel I.D. Min. Solistrand	Part Numbers Solistrand
			L Max.	E Max.	C	W			
300–350 MCM 300,000–380,000 [152–193]	3/8	B	2.671 67.84	2.056 52.22	.625 15.88	1.545 39.24	.140 3.56	.819 20.80	322257
		B	3.422 86.92	2.675 67.95	1.250 31.75	1.545 39.24	.140 3.56	.819 20.80	322763
	7/16	B	2.671 67.84	2.056 52.22	.625 15.88	1.545 39.24	.140 3.56	.819 20.80	322258
		B	2.671 67.84	2.056 52.22	.625 15.88	1.545 39.24	.140 3.56	.819 20.80	322259
	1/2 M12	B	3.422 86.92	2.675 67.95	1.250 31.75	1.545 39.24	.140 3.56	.819 20.80	322764
		B	2.671 67.84	2.065 52.22	.625 15.88	1.545 39.24	.140 3.56	.819 20.80	324105
	5/8	B	3.422 86.92	2.675 67.95	1.250 31.75	1.545 39.24	.140 3.56	.819 20.80	322428
		B	2.790 70.87	2.175 55.25	.625 15.88	1.749 44.42	.158 4.01	.930 23.62	322262
400 MCM 380,000–478,000 [193–242]	3/8	B	2.790 70.87	2.175 55.25	.625 15.88	1.749 44.42	.158 4.01	.930 23.62	322263
		B	2.790 70.87	2.175 55.25	.625 15.88	1.749 44.42	.158 4.01	.930 23.62	322264
	1/2 M12	B	3.644 92.56	2.795 70.99	1.250 31.75	1.749 44.42	.158 4.01	.930 23.62	327882
		B	2.790 70.87	2.175 55.25	.625 15.88	1.749 44.42	.158 4.01	.930 23.62	324202
	5/8 M16	B	3.644 92.56	2.795 70.99	1.250 31.75	1.749 44.42	.158 4.01	.930 23.62	323222
		B	3.644 92.56	2.795 70.99	1.250 31.75	1.749 44.42	.158 4.01	.930 23.62	322939
	3/4	B	3.187 80.95	2.447 62.15	.750 19.05	2.015 51.18	.182 4.62	1.075 27.31	322267
		B	4.176 106.07	3.194 81.13	1.500 38.10	2.015 51.18	.182 4.62	1.075 27.31	322772
500–600 MCM 478,000–600,000 [242–304]	1/2 M12	B	3.187 80.95	2.447 62.15	.750 19.05	2.015 51.18	.182 4.62	1.075 27.31	322269
		B	4.176 106.07	3.194 81.13	1.500 38.10	2.015 51.18	.182 4.62	1.075 27.31	322773
	5/8 M16	B	3.187 80.95	2.447 62.15	.750 19.05	2.015 51.18	.182 4.62	1.075 27.31	322270
		B	4.176 106.07	3.194 81.13	1.500 38.10	2.015 51.18	.182 4.62	1.075 27.31	322271
	3/4	B	4.176 106.07	3.194 81.13	1.500 38.10	2.015 51.18	.182 4.62	1.075 27.31	322273
		B	4.176 106.07	3.194 81.13	1.500 38.10	2.015 51.18	.182 4.62	1.075 27.31	322273

Right Angle Ring Tongue Terminals

Wire Size Range

AWG 22 to 300 MCM,
CMA 509 — 300,000
[0.26 to 152 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions		Material Thickness Max.	Wire Barrel ID Min	Part Numbers
		C Min.	W			
22-16 509-3,260 [0.26-1.65]	6	.171 4.34	.281 7.14	.033 .838	.061 1.55	321262
	10	.187 4.75	.312 7.92	.033 .838	.061 1.55	322768
16-14 2,050-5,180 [1.04-2.62]	8	.185 4.70	.343 8.71	.050 1.27	.105 2.67	184269
	10	.192 4.88	.343 8.71	.033 .838	.085 2.16	322821
8 13,100-20,800 [6.64-10.5]	1/4	.432 10.97	.594 15.09	.051 1.30	.172 4.37	35277
6 20,800-33,100 [10.5-16.8]	1/4	.390 9.91	.625 15.88	.060 1.52	.232 5.89	35678
	5/16	.390 9.91	.625 15.88	.060 1.52	.232 5.89	33466-1
4 33,100-52,600 [16.8-26.7]	1/4	.375 9.53	.656 16.66	.073 1.85	.296 7.52	35625
	5/16	.348 8.84	.625 15.88	.073 1.85	.280 7.11	33115-1
	3/8	.348 8.84	.625 15.88	.073 1.85	.280 7.11	31812-1
2 52,600-83,700 [26.7-42.4]	5/16	.422 10.72	.625 15.88	.073 1.85	.370 9.40	322870-1
1/0 83,700-119,500 [42.4-60.6]	1/4	.437 11.10	.807 20.50	.073 1.85	.444 11.28	322905
	5/16	.531 13.49	.807 20.50	.073 1.85	.444 11.28	321867-1
	3/8	.531 13.49	.807 20.50	.073 1.85	.444 11.28	322906
	1/2	.531 13.49	.875 22.23	.073 1.85	.444 11.28	322909
2/0 119,500-150,500 [60.6-76.3]	5/16	.500 12.70	.946 24.03	.083 2.11	.504 12.80	36922-1
	3/8	.531 13.49	.926 23.52	.083 2.11	.504 12.80	322912
3/0 150,500-190,000 [76.3-96.3]	5/16	.531 13.49	1.020 25.91	.094 2.39	.565 14.35	321874-1
	3/8	.468 11.89	1.082 27.48	.094 2.39	.565 14.35	324035
	1/2	.468 11.89	1.062 26.97	.094 2.39	.565 14.35	36929-1
4/0 190,000-231,000 [96.3-117]	5/16	.750 19.05	1.150 29.21	.105 2.67	.635 16.13	321272
	3/8	.484 12.29	1.140 28.96	.105 2.67	.635 16.13	321265
250-300 MCM 231,000-300,000 [117-152]	1/2	.863 21.92	1.435 36.45	.129 3.28	.753 19.13	324023

Heavy Duty Ring Tongue Terminals


Wire Size Range

AWG 16 to 8,
CMA 2,050 to 20,800
[1.04 to 10.5 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Style	Dimensions				Material Thickness Max.	Wire Barrel I.D. Min.		Part Numbers	
			L Max.	E Max.	C	W		Solistrand	Budget	Solistrand	Budget
16-14 2,050-5,180 [1.04-2.62]	4	A	.630 16.00	.487 12.37	.219 5.56	.281 7.14	.050 1.27	—	.110 2.79	—	33728
	6	A	.630 16.00	.487 12.37	.219 5.56	.281 7.14	.050 1.27	—	.110 2.79	—	33729
	M3.5	A	.723 18.36	.549 13.94	.281 7.14	.343 8.71	.050 1.27	.105 2.67	.110 2.79	322833	33716
	8	A	.723 18.36	.549 13.94	.281 7.14	.343 8.71	.050 1.27	.105 2.67	.110 2.79	35432	33717
	10	A	.723 18.36	.549 13.94	.281 7.14	.343 8.71	.050 1.27	.105 2.67	.110 2.79	34567* 2-34567-1	33718
		A	.865 21.97	.612 15.54	.344 8.74	.500 12.70	.050 1.27	—	.110 2.79	—	34967
		A	.973 24.71	.705 17.91	.437 11.10	.531 13.49	.050 1.27	—	.110 2.79	—	33646
	1/4 M6	A	.865 21.97	.612 15.54	.344 8.74	.500 12.70	.050 1.27	.105 2.67	.110 2.79	35775* 2-35775-1	34968
		A	.973 24.71	.705 17.91	.437 11.10	.531 13.49	.050 1.27	—	.110 2.79	—	33195
	5/16 M8	A	.865 21.97	.612 15.54	.344 8.74	.500 12.70	.050 1.27	.105 2.67	.110 2.79	35776	34969
		A	.973 24.71	.705 17.91	.437 11.10	.531 13.49	.050 1.27	—	.110 2.79	—	33647
	3/8	A	.973 24.71	.705 17.91	.437 11.10	.531 13.49	.050 1.27	.105 2.67	.110 2.79	322832	33648
		A	1.271 32.28	.893 22.68	.625 15.88	.750 19.05	.050 1.27	.105 2.67	.110 2.79	327732	34829
	1/2 M12	A	1.271 32.28	.893 22.68	.625 15.88	.750 19.05	.050 1.27	.105 2.67	.110 2.79	321165*	34830
		A	1.896 48.16	1.268 32.21	1.000 25.40	1.250 31.75	.050 1.27	—	.110 2.79	—	36199
	5/8 M16	A	1.896 48.16	1.268 32.21	1.000 25.40	1.250 31.75	.050 1.27	.105 2.67	.110 2.79	320758	36200
	3/4	A	1.896 48.16	1.268 32.21	1.000 25.40	1.250 31.75	.050 1.27	.105 2.67	.110 2.79	320759	36201
8 13,100-20,800 [6.64-10.5]	10	C	1.273 32.33	.977 24.82	.443 11.25	.587 14.91	.095 2.41	.177 4.50	—	331414	—
	1/4 M6	C	.949 24.10	.696 17.68	.240 6.10	.500 12.70	.095 2.41	.177 4.50	—	330968	—
		C	.933 23.70	.696 17.68	.250 6.35	.468 11.89	.095 2.41	.177 4.50	—	332042	—
	5/16 M8	C	1.273 32.33	.977 24.82	.443 11.25	.587 14.91	.095 2.41	.177 4.50	—	1-331414-1	—

Note: Part numbers are shown as loose piece over tape mounted product.

*Part numbers are available in small quantity packages.

Heavy Duty Ring Tongue Terminals (Continued)


Wire Size Range

AWG 6 to 1/0,
CMA 20,800 to 119,500
[10.5 to 60.6 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Style	Dimensions				Material Thickness Max.	Wire Barrel I.D. Min. Solistrand	Part Numbers Solistrand
			L Max.	E Max.	C	W			
6 20,800–33,100 [10.5–16.8]	10	B	1.184 30.07	.931 23.65	.370 9.40	.500 12.70	.095 2.41	.232 5.89	2-330969-1
	1/4 M6	B	1.184 30.07	.931 23.65	.370 9.40	.500 12.70	.095 2.41	.232 5.89	330969
		C	1.415 35.94	1.100 27.94	.454 11.53	.625 15.88	.095 2.41	.232 5.89	331417
	3/8	C	1.415 35.94	1.100 27.94	.454 11.53	.625 15.88	.095 2.41	.232 5.89	1-331417-1
4 33,100–52,600 [16.8–26.7]	1/4 M6	B	1.230 31.24	.977 24.82	.390 9.91	.500 12.70	.095 2.41	.296 7.52	330970
		C	1.535 38.99	1.193 30.30	.456 11.58	.679 17.25	.095 2.41	.296 7.52	331420
	5/16 M8	C	1.535 38.99	1.193 30.30	.456 11.58	.679 17.25	.095 2.41	.296 7.52	1-331420-0
	3/8	C	1.535 38.99	1.193 30.30	.456 11.58	.679 17.25	.095 2.41	.296 7.52	1-331420-1
2 52,600–83,700 [26.7–42.4]	3/8	C	1.745 44.32	1.315 33.40	.639 16.23	.855 21.72	.095 2.41	.375 9.53	1-331423-0
	1/2 M12	C	1.745 44.32	1.315 33.40	.639 16.23	.855 21.72	.095 2.41	.375 9.53	1-331423-1
1/0 83,700–119,500 [42.4–60.6]	3/8	B	1.928 48.97	1.519 38.58	.691 17.55	.822 20.88	.095 2.41	.439 11.15	1-331880-0
	1/2 M12	B	1.928 48.97	1.519 38.58	.691 17.55	.822 20.88	.095 2.41	.439 11.15	1-331880-1

Rectangular Tongue Terminals


Wire Size Range

AWG 22 to 14,
CMA 509 to 5,180
[0.26 to 2.62 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions					Material Thickness Max.	Wire Barrel I.D. Min.		Part Numbers	
		L Max.	E Max.	C Min.	W	X		Solistrand	Budget	Solistrand	Budget
22-16 509-3,260 [0.26-1.65]	2 M2	.551 14.00	.431 10.95	.250 6.35	.182 4.62	.115 2.92	.033 0.84	—	.065 1.65	—	320870
		.529 13.44	.384 9.75	.203 5.16	.213 5.41	.140 3.56	.033 0.84	—	.065 1.65	—	32579
	4	.670 17.02	.517 13.13	.237 6.02	.237 6.02	.143 3.63	.033 0.84	.061 1.55	.065 1.65	328363	328349
		.551 14.00	.431 10.95	.250 6.35	.182 4.62	.115 2.92	.033 0.84	.061 1.55	.065 1.65	323119	322408
	6 M3.5	.811 20.60	.606 15.39	.404 10.26	.237 6.02	.195 4.95	.033 0.84	—	.065 1.65	—	327955
		.982 24.94	.745 18.92	.465 11.81	.302 7.67	.227 5.77	.033 0.84	.061 1.55	.065 1.65	328353	328339
		.670 17.02	.462 11.73	.281 7.14	.312 7.92	.203 5.16	.033 0.84	.061 1.55	.065 1.65	323112	321691
	8 M4	.982 24.94	.745 18.92	.465 11.81	.302 7.67	.227 5.77	.033 0.84	.061 1.55	.065 1.65	328355	328341
		.748 19.00	.540 13.72	.281 7.14	.312 7.92	.203 5.16	.033 0.84	.061 1.55	—	330539	—
	10	.670 17.02	.462 11.73	.281 7.14	.375 9.53	.203 5.16	.033 0.84	.061 1.55	.065 1.65	323106 2-323106-1	34525
		.546 13.87	.399 10.13	.218 5.54	.344 8.74	.142 3.61	.033 0.84	.061 1.55	.065 1.65	34459	31821
		.576 14.63	.462 11.73	.281 7.14	.215 5.46	.109 2.77	.033 0.84	—	.089 2.26	—	31691
	5 M3	.632 16.05	.479 12.17	.277 7.04	.277 7.04	.143 3.63	.033 0.84	—	.089 2.26	—	327951
		.560 14.22	.368 9.35	.187 4.75	.250 6.35	.187 4.75	.033 0.84	.085 2.16	.089 2.26	320815	320814
	6 M3.5	.529 13.44	.384 9.75	.203 5.16	.296 7.52	.140 3.56	.033 0.84	.085 2.16	.089 2.26	34266 2-34266-1	31813
		.633 16.08	.493 12.52	.312 7.92	.244 6.20	.125 3.18	.033 0.84	—	.089 2.26	—	35278
	8 M4	.982 24.94	.745 18.92	.465 11.81	.302 7.67	.227 5.77	.033 0.84	.085 2.16	.089 2.26	328356	328342
		.717 18.21	.462 11.73	.281 7.14	.312 7.92	.250 6.35	.033 0.84	.085 2.16	.089 2.26	320819	320818
	12	.951 24.16	.618 15.70	.437 11.10	.375 9.53	.328 8.33	.033 0.84	—	.089 2.26	—	320820

Note: Part numbers are shown as loose piece over tape mounted product.

Rectangular Tongue Terminals (Continued)


Wire Size Range

AWG 12 to 10,
CMA 5,180 to 13,100
[2.62 to 6.64 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions					Material Thickness Max.	Wire Barrel I.D. Min.		Part Numbers	
		L Max.	E Max.	C Min.	W	X		Solistrand	Budget	Solistrand	Budget
12-10 5,180-13,100 [2.62-6.64]	4	.679 17.25	.526 13.36	.237 6.02	.237 6.02	.143 3.63	.042 1.07	.129 3.28	.134 3.40	328050	327971
	5 M3	.719 18.26	.566 14.38	.277 7.04	.277 7.04	.143 3.63	.042 1.07	—	.134 3.40	—	327953
	6 M3.5	.631 16.03	.486 12.34	.218 5.54	.290 7.37	.140 3.56	.042 1.07	.129 3.28	.134 3.40	321499 2-321499-1	33426
		.898 22.81	.693 17.60	.404 10.26	.237 6.02	.195 4.95	.042 1.07	—	.134 3.40	—	327959
		1.006 25.55	.736 18.69	.468 11.89	.296 7.52	.265 6.73	.042 1.07	.129 3.28	.134 3.40	322946	322945
		.924 23.47	.754 19.15	.465 11.81	.302 7.67	.160 4.06	.042 1.07	—	.134 3.40	—	331269
	10	.843 21.41	.588 14.94	.320 8.13	.312 7.92	.250 6.35	.042 1.07	.129 3.28	.134 3.40	321558	321557
	1/4 M6	1.069 27.15	.736 18.69	.468 11.89	.469 11.91	.328 8.33	.042 1.07	.129 3.28	.134 3.40	320823	320822

Note: Part numbers are shown as loose piece over tape mounted product.

Spade Tongue Terminals


Wire Size Range

**AWG 26 to 10,
CMA 202 to 13,100
[0.1 to 6.64 mm²]**

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions					Material Thickness Max.	Wire Barrel I.D. Min.		Part Numbers	
		L Max.	E Max.	C Min.	W	X		Solistrand	Budget	Solistrand	Budget
26–22 202–810 [0.1–0.41]	0	.280 7.11	.213 5.41	.078 1.98	.125 3.18	.062 1.57	.020 0.51	—	.035 0.89	—	32501
	4	.431 10.95	.346 8.79	.211 5.36	.203 5.16	.076 1.93	.020 0.51	—	.035 0.89	—	34247
22–16 509–3,260 [0.26–1.65]	2 M2	.504 12.80	.384 9.75	.203 5.16	.182 4.62	.115 2.92	.033 0.84	.061 1.55	.065 1.65	53555-1* 53555-2	328395
	4	.451 11.46	.337 8.56	.156 3.96	.218 5.54	.109 2.77	.033 0.84	.061 1.55	.065 1.65	321463 2-321463-1	323834
		.685 17.40	.493 12.52	.312 7.92	.375 9.53	.187 4.75	.033 0.84	—	.065 1.65	—	31634
	6 M3.5	.530 13.46	.384 9.75	.203 5.16	.297 7.54	.141 3.58	.033 0.84	.061 1.55	.065 1.65	36195* 2-36195-3	33765
		.623 15.82	.493 12.52	.312 7.92	.250 6.35	.125 3.18	.033 0.84	.061 1.55	.065 1.65	323127*	34518*
	8 M4	.685 17.40	.493 12.52	.312 7.92	.375 9.53	.187 4.75	.033 0.84	.061 1.55	.065 1.65	34117* 2-34117-2	31635*
		.653 16.59	.477 12.12	.296 7.52	.343 8.71	.171 4.34	.033 0.84	—	.065 1.65	—	323823
	10	.733 18.62	.572 14.53	.312 7.92	.344 8.74	.156 3.96	.033 0.84	.061 1.55	—	34583	34582
		.685 17.40	.493 12.52	.312 7.92	.375 9.53	.187 4.75	.033 0.84	.061 1.55	.065 1.65	34118* 2-34118-2	31636*
	6 M3.5	.685 17.40	.493 12.52	.312 7.92	.385 9.78	.187 4.75	.033 0.84	—	.089 2.26	—	31704
		.530 13.46	.384 9.75	.203 5.16	.297 7.54	.141 3.58	.033 0.84	.085 2.16	.089 2.26	322996* 2-322996-1	33202*
		.623 15.82	.493 12.52	.312 7.92	.244 6.20	.125 3.18	.033 0.84	.085 2.16	.089 2.26	330827	33221
	8 M4	.685 17.40	.493 12.52	.312 7.92	.385 9.78	.187 4.75	.033 0.84	.085 2.16	.089 2.26	34128* 2-36880-1	31705*
		.530 13.46	.384 9.75	.203 5.16	.297 7.54	.141 3.58	.033 0.84	.085 2.16	.089 2.26	36880 2-36880-1	35116
16–14 2,050–5,180 [1.04–2.62]	10	.764 19.41	.572 14.53	.312 7.92	.385 9.78	.187 4.75	.033 0.84	.085 2.16	.089 2.26	33219* 34129*	31442 31706
		.685 17.40	.493 12.52	.312 7.92	.385 9.78	.187 4.75	.033 0.84	.085 2.16	.089 2.26	—	—
		.733 18.62	.572 14.53	.312 7.92	.344 8.74	.156 3.96	.033 0.84	.085 2.16	—	324521	—
	6 M3.5	.772 19.61	.564 14.33	.296 7.52	.406 10.31	.203 5.16	.042 1.07	—	.134 3.40	—	31587
		.631 16.03	.486 12.34	.218 5.54	.282 7.16	.140 3.56	.042 1.07	.129 3.28	.134 3.40	322451*	34384
		.772 19.61	.564 14.33	.296 7.52	.312 7.92	.203 5.16	.042 1.07	—	.134 3.40	—	35493
	8 M4	.991 25.17	.757 19.23	.468 11.89	.312 7.92	.250 6.35	.042 1.07	.129 3.28	.134 3.40	325196	325195
		.772 19.61	.564 14.33	.296 7.52	.406 10.31	.203 5.16	.042 1.07	.129 3.28	.134 3.40	32995*	31588*
	10	.772 19.61	.564 14.33	.296 7.52	.406 10.31	.203 5.16	.042 1.07	.129 3.28	.134 3.40	33479* 2-33479-1	31589
		.772 19.61	.564 14.33	.296 7.52	.375 9.53	.203 5.16	.042 1.07	.129 3.28	.134 3.40	35495* 2-35495-2	35494*

Note: Part numbers are shown as loose piece over tape mounted product.

*Part numbers are available in small quantity packages.

Short Spring Spade Tongue Terminals


Wire Size Range

AWG 26 to 16,
CMA 202 to 3,260
[0.1 to 1.65 mm²]

Material

Terminal Body — Phosphor Bronze
per ASTM B-103

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions					Material Thickness Max.	Wire Barrel I.D. Min.		Part Numbers	
		L Max.	E Max.	C Min.	W	X		Solistrand	Budget	Solistrand	Budget
26–22 202–810 [0.1–0.41]	2 M2	.455 11.56	.341 8.66	.206 5.23	.171 4.34	.109 2.77	.020 0.51	—	.034 0.86	—	53000-1
	4	.499 12.67	.354 8.99	.219 5.56	.203 5.16	.140 3.56	.020 0.51	—	.034 0.86	—	53001-1
	5 M3	.483 12.27	.338 8.59	.203 5.16	.250 6.35	.140 3.56	.020 0.51	—	.034 0.86	—	53002-1
	6 M3.5	.483 12.27	.338 8.59	.203 5.16	.250 6.35	.140 3.56	.020 0.51	—	.034 0.86	—	53003-1
	8 M4	.591 15.01	.416 10.57	.281 7.14	.375 9.53	.170 4.32	.020 0.51	—	.034 0.86	—	53004-1
	4	.576 14.63	.431 10.95	.250 6.35	.203 5.16	.140 3.56	.033 0.84	.061 1.55	.065 1.65	53175-1*	53150-2
22–16 509–3,260 [0.26–1.65]	5 M3	.576 14.63	.431 10.95	.250 6.35	.250 6.35	.140 3.56	.033 0.84	—	.065 1.65	—	53005-1
	6 M3.5	.576 14.63	.431 10.95	.250 6.35	.250 6.35	.140 3.56	.033 0.84	.061 1.55	.065 1.65	53120-1* 53120-2	53006-1
		.576 14.63	.431 10.95	.250 6.35	.234 5.94	.140 3.56	.033 0.84	.061 1.55	.065 1.65	53830-1 53830-2	53266-2
	8 M4	.637 16.18	.462 11.73	.281 7.14	.375 9.53	.170 4.32	.033 0.84	.061 1.55	.065 1.65	53121-1	53007-1
		.637 16.18	.462 11.73	.281 7.14	.244 6.20	.170 4.32	.033 0.84	.061 1.55	.065 1.65	53831-1* 53831-2	53267-2
	10	.685 17.40	.462 11.73	.281 7.14	.294 7.47	.218 5.54	.033 0.84	.061 1.55	.065 1.65	53832-1 53832-2	53268-2
	1/4-28 UNF M6	.810 20.57	.524 13.31	.343 8.71	.625 15.88	.281 7.14	.033 0.84	—	.065 1.65	—	53235-2

Note: Part numbers are shown as loose piece over tape mounted product.

*Part numbers are available in small quantity packages.

Short Spring Spade Tongue Terminals (Continued)


Wire Size Range

AWG 16 to 10,
CMA 2,050 to 13,100
[1.04 to 6.64 mm²]

Material

Terminal Body — Phosphor Bronze
per ASTM B-103

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm²]	Stud Size	Dimensions					Material Thickness Max.	Wire Barrel I.D. Min.		Part Numbers		
		L Max.	E Max.	C Min.	W	X		Solistrand	Budget	Solistrand	Budget	
16-14 2,050-5,180 [1.04-2.62]	5 M3	.576 14.63	.431 10.95	.250 6.35	.250 6.35	.140 3.56	.033 0.84	.085 2.16	.089 2.26	53177-1	53009-1	
	6 M3.5	.576 14.63	.431 10.95	.250 6.35	.250 6.35	.140 3.56	.033 0.84	.085 2.16	.089 2.26	53123-1* 53123-2	53010-1	
	8 M4	.637 16.18	.462 11.73	.281 7.14	.375 9.53	.170 4.32	.033 0.84	.085 2.16	.089 2.26	53124-1* 53124-2	53011-1	
		.637 16.18	.462 11.73	.281 7.14	.244 6.20	.170 4.32	.033 0.84	.085 2.16	.089 2.26	53833-1 53833-2	53270-2	
	10	.685 17.40	.462 11.73	.281 7.14	.406 10.31	.218 5.54	.033 0.84	.085 2.16	.089 2.26	53125-1* 53125-2	53012-1	
		.685 17.40	.462 11.73	.281 7.14	.294 7.47	.218 5.54	.033 0.84	.085 2.16	.089 2.26	53834-1 53834-2	53271-2	
	1/4-28 UNF M6	.810 20.57	.524 13.31	.343 8.71	.625 15.88	.281 7.14	.033 0.84	— —	.089 2.26	— —	53032-1	
	12-10 5,180-13,100 [2.62-6.64]	5 M3	.636 16.15	.447 11.35	.169 4.29	.250 6.35	.184 4.67	.042 1.07	— —	.134 3.40	— —	53013-1
		6 M3.5	.636 16.15	.452 11.48	.174 4.42	.250 6.35	.179 4.55	.042 1.07	.129 3.28	.134 3.40	53126-1* 53126-2	53014-1
		8 M4	.729 18.52	.554 14.07	.276 7.01	.375 9.53	.170 4.32	.042 1.07	.129 3.28	.134 3.40	53127-1* 53127-2	53015-1
.729 18.52			.554 14.07	.276 7.01	.312 7.92	.170 4.32	.042 1.07	.129 3.28	.134 3.40	53835-1 53835-2	53273-2	
10		.777 19.74	.554 14.07	.276 7.01	.406 10.31	.218 5.54	.042 1.07	.129 3.28	.134 3.40	53128-1* 53128-2	53016-1	
		.777 19.74	.554 14.07	.276 7.01	.312 7.92	.218 5.54	.042 1.07	.129 3.28	.134 3.40	53836-1 53836-2	53274-2	
1/4-28 UNF M6		.902 22.91	.616 15.65	.338 8.59	.375 9.53	.281 7.14	.042 1.07	— —	.134 3.40	— —	53226-2	

Note: Part numbers are shown as loose piece over tape mounted product.

*Part numbers are available in small quantity packages.

Long Spring Spade Tongue Terminals


Wire Size Range

AWG 26 to 10,
CMA 202 to 13,100
[0.1 to 6.64 mm²]

Material

Terminal Body — Phosphor Bronze
per ASTM B-103

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions					Material Thickness Max.	Wire Barrel I.D. Min.		Part Numbers	
		L Max.	E Max.	C Min.	W	X		Solistrand	Budget	Solistrand	Budget
26–22 202–810 [0.1–0.41]	4	.637 16.18	.341 8.66	.206 5.23	.203 5.16	.276 7.01	.020 0.51	—	.034 0.86	—	52733-1
	6 M3.5	.666 16.92	.370 9.40	.235 5.97	.250 6.35	.276 7.01	.020 0.51	—	.034 0.86	—	52734-1
	8 M4	.696 17.68	.400 10.16	.265 6.73	.281 7.14	.290 7.37	.020 0.51	—	.034 0.86	—	52735-1
22–16 509–3,260 [0.26–1.65]	4	.673 17.09	.392 9.96	.201 5.11	.203 5.16	.276 7.01	.033 0.84	—	.065 1.65	—	53047
	6 M3.5	.709 18.01	.429 10.90	.238 6.05	.250 6.35	.276 7.01	.033 0.84	.061 1.55	.065 1.65	52709-1	52700-1
	8 M4	.756 19.20	.461 11.71	.270 6.86	.281 7.14	.290 7.37	.033 0.84	.061 1.55	.065 1.65	52710-1* 52710-2	52701-1
	10	.782 19.86	.474 12.04	.283 7.19	.343 8.71	.303 7.70	.033 0.84	—	.065 1.65	—	52702-1
	1/4-28 UNF M6	.879 22.33	.536 13.61	.340 8.64	.437 11.10	.333 8.46	.033 0.84	—	.065 1.65	—	53111-2
16–14 2,050–5,180 [1.04–2.62]	6 M3.5	.709 18.01	.429 10.90	.238 6.05	.250 6.35	.276 7.01	.033 0.84	.085 2.16	.089 2.26	52712-1*	52703-1
	8 M4	.756 19.20	.461 11.71	.270 6.86	.281 7.14	.290 7.37	.033 0.84	.085 2.16	.089 2.26	52713-1* 52713-2	52704-1 52704-3
	10	.782 19.86	.474 12.04	.283 7.19	.343 8.71	.303 7.70	.033 0.84	.085 2.16	.089 2.26	52714-1*	52705-1
	1/4-28 UNF M6	.879 22.33	.536 13.61	.345 8.76	.437 11.10	.338 8.59	.033 0.84	—	.089 2.26	—	53033-1
	6 M3.5	.808 20.52	.520 13.21	.242 6.15	.312 7.92	.283 7.19	.042 1.07	.129 3.28	.134 3.40	52715-1	52706-1
12–10 5,180–13,100 [2.62–6.64]	8 M4	.851 21.62	.551 14.00	.273 6.93	.375 9.53	.295 7.49	.042 1.07	.129 3.28	.134 3.40	52716-1 52716-2	52707-1 52707-3
	10	.896 22.76	.583 14.81	.305 7.75	.375 9.53	.308 7.82	.042 1.07	.129 3.28	.134 3.40	52717-1 52717-2	52708-1
	1/4-28 UNF M6	.966 24.54	.623 15.82	.345 8.76	.437 11.10	.338 8.59	.042 1.07	—	.134 3.40	—	52772-1

Note: Part numbers are shown as loose piece over tape mounted product.

*Part numbers are available in small quantity packages.

Flanged Spade Tongue Terminals


Wire Size Range

**AWG 26 to 10,
CMA 202 to 13,100
[0.1 to 6.64 mm²]**

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions						Material Thickness Max.	Wire Barrel I.D. Min.		Part Numbers	
		L Max.	E Max.	C Min.	W	X	H Min.		Solistrand	Budget	Solistrand	Budget
26-22 202-810 [0.1-0.41]	2 M2	.453 11.51	.338 8.59	.203 5.16	.182 4.62	.110 2.79	.026 0.66	.020 0.51	—	.035 0.89	—	324599
	4	.453 11.51	.338 8.59	.203 5.16	.193 4.90	.110 2.79	.026 0.66	.020 0.51	—	.035 0.89	—	52512-1
	6 M3.5	.453 11.51	.338 8.59	.203 5.16	.250 6.35	.110 2.79	.026 0.66	.020 0.51	—	.035 0.89	—	51875-1
22-16 509-3,260 [0.26-1.65]	2 M2	.504 12.80	.384 9.75	.203 5.16	.182 4.62	.115 2.92	.041 1.04	.033 0.84	.061 1.55	.065 1.65	324605*	324604
	6 M3.5	.514 13.06	.384 9.75	.203 5.16	.296 7.52	.125 3.18	.045 1.14	.033 0.84	.061 1.55	.065 1.65	320749*	32418
		.514 13.06	.384 9.75	.203 5.16	.250 6.35	.125 3.18	.045 1.14	.033 0.84	.061 1.55	.065 1.65	323136*	322776
	8 M4	.607 15.42	.431 10.95	.250 6.35	.416 10.57	.171 4.34	.062 1.57	.033 0.84	.061 1.55	.065 1.65	323124*	32494
		.514 13.06	.384 9.75	.203 5.16	.296 7.52	.125 3.18	.045 1.14	.033 0.84	.061 1.55	.065 1.65	52730*	1-32418-2 1-32418-4
	10	.514 13.06	.384 9.75	.203 5.16	.296 7.52	.125 3.18	.045 1.14	.033 0.84	—	.065 1.65	—	328522
	6 M3.5	.514 13.06	.384 9.75	.203 5.16	.294 7.47	.125 3.18	.047 1.19	.033 0.84	.085 2.16	.089 2.26	320855*	320852
16-14 2,050-5,180 [1.04-2.62]	8 M4	.514 13.06	.384 9.75	.203 5.16	.294 7.47	.125 3.18	.047 1.19	.033 0.84	.085 2.16	.089 2.26	320856*	320853
	10	.514 13.06	.384 9.75	.203 5.16	.294 7.47	.125 3.18	.047 1.19	.033 0.84	.085 2.16	.089 2.26	320857*	320854
	6 M3.5	.694 17.63	.518 13.16	.250 6.35	.296 7.52	.171 4.34	.052 1.32	.042 1.07	.129 3.28	.134 3.40	324578 1-324578-0	324579
12-10 5,180-13,100 [2.62-6.64]	8 M4	.694 17.63	.518 13.16	.250 6.35	.416 10.57	.171 4.34	.052 1.32	.042 1.07	.129 3.28	.134 3.40	323143	32416
	10	.694 17.63	.518 13.16	.250 6.35	.416 10.57	.171 4.34	.052 1.32	.042 1.07	.129 3.28	.134 3.40	323144 2-323144-1	322725

Note: Part numbers are shown as loose piece over tape mounted product.

*Part numbers are available in small quantity packages.

Slotted Ring Tongue Terminals


Wire Size Range

AWG 26 to 10,
CMA 202 to 13,100
[0.1 to 6.64 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions				Material Thickness Max.	Wire Barrel I.D. Min.		Part Numbers	
		L Max.	E Max.	C Min.	W		Solistrand	Budget	Solistrand	Budget
26-22 202-810 [0.1-0.41]	6 M3.5	.523 13.28	.416 10.57	.281 7.14	.250 6.35	.020 0.51	—	.035 0.89	—	322211
22-16 509-3,260 [0.26-1.65]	4	.425 10.80	.353 8.97	.172 4.37	.182 4.62	.033 0.84	.061 1.55	.065 1.65	321288*	323838
	6 M3.5	.423 10.74	.337 8.56	.156 3.96	.218 5.54	.033 0.84	.061 1.55	.065 1.65	321289 2-321289-1	323835
	8	.547 13.89	.431 10.95	.250 6.35	.281 7.14	.033 0.84	.061 1.55	.065 1.65	323129	36953
	10	.588 14.94	.462 11.73	.281 7.14	.312 7.92	.033 0.84	—	.065 1.65	—	323832
	1/4	.816 20.73	.618 15.70	.437 11.10	.469 11.91	.033 0.84	.061 1.55	.065 1.65	321809 2-321809-1	323837
16-14 2,050-5,180 [1.04-2.62]	6 M3.5	.459 11.66	.352 8.94	.171 4.34	.250 6.35	.033 0.84	.085 2.16	.089 2.26	322514	35555
	8 M4	.616 15.65	.462 11.73	.281 7.14	.344 8.74	.033 0.84	—	.089 2.26	—	34520
	10	.604 15.34	.462 11.73	.281 7.14	.343 8.71	.033 0.84	—	.089 2.26	—	328872
	1/4 M6	.816 20.73	.618 15.70	.437 11.10	.469 11.91	.033 0.84	—	.089 2.26	—	36216
12-10 5,180-13,100 [2.62-6.64]	1/4 M6	.952 24.18	.736 18.69	.468 11.89	.531 13.49	.042 1.07	.129 3.28	.134 3.40	35680*	55812-2

Note: Part numbers are shown as loose piece over tape mounted product.

*Part numbers are available in small quantity packages.

Hook Tongue Terminals


Wire Size Range

AWG 22 to 10,
CMA 509 to 13,100
[0.26 to 6.64 mm²]

Material

Terminal Body—Copper per
ASTM B-152

Plating—Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions				Material Thickness Max.	Wire Barrel I.D. Min.		Part Numbers	
		L Max.	E Max.	C Min.	W		Solistrand	Budget	Solistrand	Budget
22-16 509-3,260 [0.26-1.65]	6	.530	.384	.203	.281	.033	—	.065	—	34261
	M3.5	13.46	9.75	5.16	7.14	0.84	—	1.65	—	
	8	.656	.482	.296	.343	.033	—	.065	—	31628
	M4	16.66	12.24	7.52	8.71	0.84	—	1.65	—	
16-14 2,050-5,180 [1.04-2.62]	6	.636	.462	.281	.343	.033	—	.089	—	35212
	M3.5	16.15	11.73	7.14	8.71	0.84	—	2.26	—	
	8	.636	.462	.281	.343	.033	—	.089	—	32503
	M4	16.15	11.73	7.14	8.71	0.84	—	2.26	—	
12-10 5,180-13,100 [2.62-6.64]	10	.636	.462	.281	.343	.033	—	.089	—	33437
		16.15	11.73	7.14	8.71	0.84	—	2.26	—	
	10	.760	.570	.302	.375	.042	.129	.134	324209	327902
	1/4	19.30	14.48	7.67	9.53	1.07	3.28	3.40	2-324209-1	
	M6	1.004	.736	.468	.531	.042	.129	.134	321632	327905
		25.50	18.69	11.89	13.49	1.07	3.28	3.40	2-321632-1	

Note: Part numbers are shown as loose piece over tape mounted product.

Tab Tongue Terminals


Wire Size Range

AWG 22 to 8,
CMA 509 to 20,800
[0.26 to 10.5 mm²]

Material

Terminal Body—Copper per
ASTM B-152

Plating—Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Style	Dimensions			Material Thickness Max.	Wire Barrel I.D. Min. Solistrand	Part Numbers Solistrand
		L Max.	E Max.	W			
22-16 509-3,260 [0.26-1.65]	A	.681	.500	.125	.033	.061	323135
		17.30	12.70	3.18	0.84	1.55	
16-14 HD ¹ 2,050-5,180 [1.04-2.62]	B	.863	.615	.125	.050	.105	322441
		21.92	15.62	3.18	1.27	2.67	
12-10 5,180-13,100 [2.62-6.64]	B	.863	.613	.125	.042	.129	322443
		21.92	15.57	3.18	1.07	3.28	
8 13,100-20,800 [6.64-10.5]	B	.937	.625	.221	.051	.177	322445
		23.80	15.88	5.61	1.30	4.50	

¹Heavy Duty for extra mechanical strength.

Flag Ring Tongue Terminals


Wire Size Range

AWG 16 to 2,
CMA 2,050 to 83,700
[1.04 to 42.4 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Style	Dimensions			Material Thickness Max.	Wire Barrel I.D. Min. Solistrand	Part Numbers Solistrand
			L Max.	C Min.	W			
16-14 2,050-5,180 [1.04-2.62]	8 M4	A	.579 14.71	.250 6.35	.312 7.92	.033 0.84	.085 2.16	325069
	10	A	.579 14.71	.250 6.35	.312 7.92	.033 .084	.085 2.16	322819
12-10 5,180-13,100 [2.62-6.64]	6 M3.5	A	.702 17.83	.281 7.14	.375 9.53	.042 1.07	.129 3.28	36269
	8 M4	A	.702 17.83	.281 7.14	.375 9.53	.042 1.07	.129 3.28	36270
	10	A	.702 17.83	.281 7.14	.375 9.53	.042 1.07	.129 3.28	36271*
	1/4 M6	A	.702 17.83	.281 7.14	.375 9.53	.042 1.07	.129 3.28	36272
8 13,100-20,800 [6.64-10.5]	10	B	.791 20.09	.250 6.35	.500 12.70	.043 1.09	.180 4.57	321051
		B	.918 23.32	.378 9.60	.500 12.70	.043 1.09	.180 4.57	321441
	1/4 M6	B	1.130 28.70	.525 13.34	.609 15.47	.043 1.09	.180 4.57	322727
6 20,800-33,100 [10.5-16.8]	10	A	.841 21.36	.250 6.35	.500 12.70	.048 1.22	.224 5.69	323196
	1/4 M6	A	.960 24.38	.371 9.42	.500 12.70	.048 1.22	.224 5.69	321576
	5/16 M8	B	1.200 30.48	.528 13.41	.625 15.88	.048 1.22	.224 5.69	321056
	3/8	B	1.200 30.48	.528 13.41	.625 15.88	.048 1.22	.224 5.69	322204
4 33,100-52,600 [16.8-26.7]	10	A	1.048 26.62	.368 9.35	.546 13.87	.051 1.30	.280 7.11	321059
	1/4 M6	A	1.048 26.62	.368 9.35	.546 13.87	.051 1.30	.280 7.11	321275
	5/16 M8	B	1.278 32.46	.530 13.46	.682 17.32	.051 1.30	.280 7.11	321060
	3/8	B	1.278 32.46	.530 13.46	.682 17.32	.051 1.30	.280 7.11	321121
2 52,600-83,700 [26.7-42.4]	10	B	1.437 36.50	.534 13.56	.713 18.11	.060 1.52	.357 9.07	321063
	1/4 M6	B	1.437 36.50	.534 13.56	.713 18.11	.060 1.52	.357 9.07	321201
	5/16 M8	B	1.437 36.50	.534 13.56	.713 18.11	.060 1.52	.357 9.07	321064
	3/8	B	1.437 36.50	.534 13.56	.713 18.11	.060 1.52	.357 9.07	321253
	10 mm	B	1.437 36.50	.534 13.56	.713 18.11	.060 1.52	.357 9.07	184147-1

*Part numbers are available in small quantity packages.

Flag Ring Tongue Terminals (Continued)


Wire Size Range

AWG 1/0 to 4/0,
CMA 83,700 to 231,000
[42.4 to 117 mm²]

Material

Terminal Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Style	Dimensions			Material Thickness Max.	Wire Barrel I.D. Min. Solistrand	Part Numbers Solistrand
			L Max.	C Min.	W			
1/0 83,700–119,500 [42.4–60.6]	1/4 M6	A	1.733 44.02	.666 16.92	.875 22.23	.073 1.85	.444 11.28	322215
	5/16 M8	A	1.733 44.02	.666 16.92	.875 22.23	.073 1.85	.444 11.28	321580
	3/8	A	1.733 44.02	.666 16.92	.875 22.23	.073 1.85	.444 11.28	321066
	1/2 M12	A	1.733 44.02	.666 16.92	.875 22.23	.073 1.85	.444 11.28	321123
2/0 119,500–150,500 [60.6–76.3]	5/16 M8	A	1.848 46.94	.671 17.04	.920 23.37	.083 2.11	.504 12.80	321582
	3/8	A	1.848 46.94	.671 17.04	.920 23.37	.083 2.11	.504 12.80	321584
3/0 150,500–190,000 [76.3–96.3]	3/8	A	2.001 50.83	.676 17.17	1.056 26.82	.094 2.39	.565 14.35	327887
4/0 190,000–231,000 [96.3–117]	5/16 M8	A	2.131 54.13	.681 17.30	1.115 28.32	.105 2.67	.635 16.13	321277
	3/8	A	2.131 54.13	.681 17.30	1.115 28.32	.105 2.67	.635 16.13	321277-1
	1/2 M12	A	2.131 54.13	.681 17.30	1.115 28.32	.105 2.67	.635 16.13	321259

Parallel Splices

Wire Size Range

**AWG 22 to 600 MCM,
CMA 509 to 600,000
[0.26 to 304 mm²]**

Material

Splice Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils ¹ [mm ²]	Dimensions			Material Thickness Max.	Part Numbers Solistrand
	L Max.	I.D. Min.	O.D. Max.		
22-16 509-3,260 [0.26-1.65]	.301 7.65	.061 1.55	.141 3.58	.033 0.84	34130*
16-14 2,050-5,180 [1.04-2.62]	.301 7.65	.085 2.16	.165 4.19	.033 0.84	34137*
12-10 5,180-13,100 [2.62-6.64]	.343 8.71	.129 3.28	.226 5.74	.042 1.07	34138*
8 13,100-20,800 [6.64-10.5]	.375 9.53	.172 4.37	.296 7.52	.051 1.30	34318*
6 20,800-33,100 [10.5-16.8]	.437 11.10	.232 5.89	.369 9.37	.060 1.52	34319*
4 33,100-52,600 [16.8-26.7]	.531 13.49	.296 7.52	.463 11.76	.073 1.85	34320*
2 52,600-83,700 [26.7-42.4]	.640 16.26	.370 9.40	.539 13.69	.073 1.85	35187*
1/0 83,700-119,500 [42.4-60.6]	.734 18.64	.444 11.28	.613 15.57	.073 1.85	36946*
2/0 119,500-150,500 [60.6-76.3]	.734 18.64	.504 12.80	.703 17.86	.083 2.11	36948*
3/0 150,500-190,000 [76.3-96.3]	.749 19.02	.565 14.35	.775 19.69	.094 2.39	36909
4/0 190,000-231,000 [96.3-117]	.765 19.43	.635 16.13	.869 22.07	.105 2.67	36951*
250-300 MCM 231,000-300,000 [117-152]	1.062 26.97	.753 19.13	1.054 26.77	.130 3.30	322275
300-350 MCM 300,000-380,000 [152-193]	1.124 28.55	.819 20.80	1.137 28.88	.140 3.56	322276
400 MCM 380,000-478,000 [193-242]	1.249 31.72	.925 23.50	1.287 32.69	.158 4.01	322277
500-600 MCM 478,000-600,000 [242-304]	1.421 36.09	1.070 27.18	1.483 37.67	.182 4.62	322278

*Part numbers are available in small quantity packages.

¹When terminating two or more wires in a parallel splice, the combined cross sectional area must be within the listed circular mil area range (CMA).

Butt Splices


Wire Size Range

**AWG 26 to 2,
CMA 202 to 83,700
[0.1 to 42.4 mm²]**

Material

Splice Body—Copper per
ASTM B-152

Plating—Tin per MIL-T-10727



Wire Size Circular Mils ¹ [mm ²]	Style	Solistrand Dimensions			Budget Dimensions			Material Thickness Max.	Part Numbers	
		L Max.	I.D. Min.	O.D. Max.	L Max.	I.D. Min.	O.D. Max.		Solistrand	Budget
26–22 202–810 [0.1–0.41]	Strap	.385 9.78	.031 0.79	.082 2.08	.385 9.78	.034 0.86	.077 1.96	.020 0.51	321198*	321024
24–20 320–1,290 [0.16–0.65]	Strap	.490 12.45	.043 1.09	.105 2.67	—	—	—	.025 0.64	324001*	—
22–16 509–3,260 [0.26–1.65]	Strap	.591 15.01	.061 1.55	.141 3.58	.591 15.01	.065 1.65	.136 3.45	.033 0.84	2-321801-3 2-321801-4	32463
	Standard	.578 14.68	.061 1.55	.141 3.58	.578 14.68	.065 1.65	.136 3.45	.033 0.84	31818* 2-31818-1	34226*
	Sight Hole	.578 14.68	.061 1.55	.141 3.58	—	—	—	.033 0.84	330367*	—
16–14 2,050–5,180 [1.04–2.62]	Strap	.591 15.01	.085 2.16	.165 4.19	.591 15.01	.089 2.26	.160 4.06	.033 0.84	322459	32464
	Standard	.567 14.40	.085 2.16	.165 4.19	.567 14.40	.089 2.26	.160 4.06	.033 0.84	31819* 2-31819-1	34227*
	Strap	.591 15.01	.085 2.16	.165 4.19	—	—	—	.033 0.84	327025* (No Wire Stop)	—
	Sight Hole	.567 14.40	.085 2.16	.165 4.19	—	—	—	.033 0.84	330368*	—
14–12 3,260–8,230 [1.65–4.17]	Sight Hole	.690 17.53	.098 2.49	.178 4.52	—	—	—	.033 0.84	321280	—
12–10 5,180–13,100 [2.62–6.64]	Strap	—	—	—	.703 17.86	.134 3.40	.221 5.61	.042 1.07	—	30953
	Sight Hole	.567 14.40	.129 3.28	.226 5.74	—	—	—	.042 1.07	330369*	—
	Standard	.565 14.35	.129 3.28	.226 5.74	.565 14.35	.134 3.40	.221 5.61	.042 1.07	32151*	34228*
	Strap	.765 19.43	.129 3.28	.226 5.74	.765 19.43	.134 3.40	.221 5.61	.042 1.07	324893	1-324898-0
8 13,100–20,800 [6.64–10.5]	Standard	.827 21.01	.172 4.37	.296 7.52	—	—	—	.051 1.30	34321*	—
	Sight Hole	.827 21.01	.172 4.37	.296 7.52	—	—	—	.051 1.30	36906*	—
6 20,800–33,100 [10.5–16.8]	Standard	1.015 25.78	.232 5.89	.369 9.37	—	—	—	.060 1.52	34322*	—
	Sight Hole	1.015 25.78	.232 5.89	.369 9.37	—	—	—	.060 1.52	36886*	—
4 33,100–52,600 [16.8–26.7]	Standard	1.140 28.96	.296 7.52	.463 11.76	—	—	—	.073 1.85	34323*	—
	Sight Hole	1.140 28.96	.296 7.52	.463 11.76	—	—	—	.073 1.85	320238	—
2 52,600–83,700 [26.7–42.4]	Standard	1.265 32.13	.370 9.40	.539 13.69	—	—	—	.073 1.85	35189*	—
	Sight Hole	1.265 32.13	.370 9.40	.539 13.69	—	—	—	.073 1.85	322246	—

Note: Part numbers are shown as loose piece over tape mounted product.

*Part numbers are available in small quantity packages.

¹When terminating two or more wires in either end of a butt splice, the combined cross sectional area must be within the listed circular mil area range (CMA).

Butt Splices (Continued)


Wire Size Range

**AWG 1/0 to 600 MCM,
CMA 83,700 to 600,000
[42.4 to 304 mm²]**

Material

Splice Body — Copper per
ASTM B-152

Plating — Tin per MIL-T-10727



Wire Circular Mils ¹ [mm ²]	Style	Solistrand Dimensions			Material Thickness Max.	Part Numbers Solistrand
		L Max.	I.D. Min.	O.D. Max.		
1/0 83,700–119,500 [42.4–60.6]	A	1.412 35.86	.444 11.28	.613 15.57	.073 1.85	36957*
2/0 119,500–150,500 [60.6–76.3]	A	1.437 36.50	.504 12.80	.693 17.60	.083 2.11	36958*
3/0 150,500–190,000 [76.3–96.3]	A	1.480 37.60	.565 14.35	.775 19.69	.094 2.39	36959*
4/0 190,000–231,000 [96.3–117]	A	1.484 37.69	.635 16.13	.869 22.07	.105 2.67	36960*
250–300 MCM 231,000–300,000 [117–152]	A	2.093 53.16	.753 19.13	1.054 26.77	.130 3.30	322279
300–350 MCM 300,000–380,000 [152–193]	A	2.217 56.31	.819 20.80	1.137 28.88	.140 3.56	322280
400 MCM 380,000–478,000 [193–242]	A	2.467 62.66	.925 23.50	1.287 32.69	.158 4.01	322281
500–600 MCM 478,000–600,000 [242–304]	A	2.811 71.40	1.070 27.18	1.483 37.67	.182 4.62	322282

*Part numbers are available in small quantity packages.

¹When terminating two or more wires in either end of a butt splice, the combined cross sectional area must be within the listed circular mil area range (CMA).

Ring Tongue Terminals


Wire Size Range

AWG 26 to 16,
CMA 202 to 3,260
[0.1 to 1.65 mm²]

Material

Terminal Body and Sleeve —
Copper per ASTM B-152

Plating —Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions				Material Thickness Max.	Wire Insulation Dia. Max.	Part Numbers	
		L Max.	E Max.	C Min.	W			Loose Piece	Tape Mounted
26–22 202–810 [0.1–0.41]	0	.464 11.79	.391 9.93	.121 3.07	.140 3.56	.020 0.51	.082 2.08	31516	—
	2	.464 11.79	.391 9.93	.121 3.07	.140 3.56	.020 0.51	.082 2.08	31518	2-31518-1
	M2	.564 14.33	.481 12.22	.211 5.36	.165 4.19	.020 0.51	.082 2.08	321621 ¹	1-321621-0 ¹
	4	.585 14.86	.481 12.22	.211 5.36	.203 5.16	.020 0.51	.082 2.08	31679	2-31679-1
	6	.585 14.86	.481 12.22	.211 5.36	.203 5.16	.020 0.51	.082 2.08	31681	2-31681-2
	M3.5	.679 17.25	.551 14.00	.281 7.14	.250 6.35	.020 0.51	.082 2.08	32861	2-32861-2
	8	.679 17.25	.551 14.00	.281 7.14	.250 6.35	.020 0.51	.082 2.08	32862	2-32862-1
	M4	.600 15.24	.507 12.88	.172 4.37	.182 4.62	.033 0.84	.125 3.18	320678	—
	4	.603 15.32	.491 12.47	.156 3.96	.218 5.54	.033 0.84	.125 3.18	31094	—
	6	.775 19.69	.616 15.65	.281 7.14	.312 7.92	.033 0.84	.125 3.18	30995	—
	M3.5	.603 15.32	.491 12.47	.156 3.96	.218 5.54	.033 0.84	.125 3.18	31096	2-31096-1
	6	.775 19.69	.616 15.65	.281 7.14	.312 7.92	.033 0.84	.140 3.56	31159	2-31159-1
22–16 509–3,260 [0.26–1.65]	M3.5	.728 18.49	.585 14.86	.250 6.35	.281 7.14	.033 0.84	.125 3.18	31269	2-31269-1
	6	.603 15.32	.491 12.47	.156 3.96	.218 5.54	.033 0.84	.140 3.56	31393	—
	M3.5	.728 18.49	.585 14.86	.250 6.35	.281 7.14	.033 0.84	.140 3.56	31396	2-31396-2
	6	.775 19.69	.616 15.65	.281 7.14	.312 7.92	.033 0.84	.125 3.18	30996	2-30996-1
	M4	.775 19.69	.616 15.65	.281 7.14	.312 7.92	.033 0.84	.140 3.56	31160	2-31160-1
	6	.728 18.49	.585 14.86	.250 6.35	.281 7.14	.033 0.84	.125 3.18	31270	2-31270-1
	M4	.728 18.49	.585 14.86	.250 6.35	.281 7.14	.033 0.84	.140 3.56	31397	2-31397-1
	10	.775 19.69	.616 15.65	.281 7.14	.312 7.92	.033 0.84	.125 3.18	30997	2-30997-1
	6	.775 19.69	.616 15.65	.281 7.14	.312 7.92	.033 0.84	.140 3.56	31161	2-31161-1
	M3.5	.728 18.49	.585 14.86	.250 6.35	.281 7.14	.033 0.84	.140 3.56	31398	2-31398-1
	1/4	1.009 25.63	.772 19.61	.437 11.10	.469 11.91	.033 0.84	.140 3.56	31176	2-31176-1
	M6	1.009 25.63	.772 19.61	.437 11.10	.469 11.91	.033 0.84	.125 3.18	31251	2-31251-1

Note: "C" dimension applies from edge of metal wire barrel to center of stud hole.

¹Slightly unusual tongue shape.

Ring Tongue Terminals (Continued)

Wire Size Range


AWG 16 to 10,
CMA 2,050 to 13,100
[1.04 to 6.64 mm²]

Material

Terminal Body and Sleeve —

Copper per ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions				Material Thickness Max.	Wire Insulation Dia. Max.	Part Numbers	
		L Max.	E Max.	C Min.	W			Loose Piece	Tape Mounted
16–14 2,050–5,180 [1.04–2.62]	4	.634	.506	.171	.250	.033	.150	32187	—
		16.10	12.85	4.34	6.35	0.84	3.81		
		.634	.506	.171	.250	.033	.170	32189	—
		16.10	12.85	4.34	6.35	0.84	4.32		
	6	.790	.616	.281	.343	.033	.170	30926	—
		20.07	15.65	7.14	8.71	0.84	4.32		
	M3.5	.634	.506	.171	.250	.033	.150	32188	—
		16.10	12.85	4.34	6.35	0.84	3.81		
		.634	.506	.171	.250	.033	.170	32190	2-32190-1
		16.10	12.85	4.34	6.35	0.84	4.32		
	8	.790	.616	.281	.343	.033	.170	30927	2-30927-1
		20.07	15.65	7.14	8.71	0.84	4.32		
16–14HD ¹ 2,050–5,180 [1.04–2.62]	10	.790	.616	.281	.343	.033	.170	30928	2-30928-1
		20.07	15.65	7.14	8.71	0.84	4.32		
		.790	.616	.281	.343	.033	.150	30993	2-30993-1
		20.07	15.65	7.14	8.71	0.84	3.81		
	1/4	1.009	.772	.437	.469	.033	.150	31256	—
		25.63	19.61	11.10	11.91	0.84	3.81		
	M6	1.009	.772	.437	.469	.033	.170	31169	2-31169-1
		25.63	19.61	11.10	11.91	0.84	4.32		
	10	.970	.796	.281	.343	.050	.230	33722	2-33722-1
		24.64	20.22	7.14	8.71	1.27	5.84		
	1/4	1.220	.952	.437	.531	.050	.230	33639	—
		30.99	24.18	11.10	13.49	1.27	5.84		
12–10 5,180–13,100 [2.62–6.64]	1/4	1.282	1.014	.437	.531	.050	.300	322296	—
		32.56	25.76	11.10	13.49	1.27	7.62		
	6	1.007	.817	.302	.375	.042	.230	31825	—
		25.58	20.75	7.67	9.53	1.07	5.84		
	M3.5	.877	.734	.219	.281	.042	.230	321501	2-321501-1
		22.28	18.64	5.56	7.14	1.07	5.84		
		.976	.817	.302	.312	.042	.230	326889	—
		24.79	20.75	7.67	7.92	1.07	5.84		
	8	.955	.796	.281	.312	.042	.230	324523	—
		24.26	20.22	7.14	7.92	1.07	5.84		
	10	1.007	.817	.302	.375	.042	.230	31771	2-31771-1
		25.58	20.75	7.67	9.53	1.07	5.84		
	1/4	1.251	.983	.468	.531	.042	.230	31772	2-31772-1
		31.78	24.97	11.89	13.49	1.07	5.84		
	3/8	1.345	1.046	.531	.593	.042	.230	31828	—
		34.16	26.57	13.49	15.06	1.07	5.84		

Note: "C" dimension applies from edge of metal wire barrel to center of stud hole.

¹Heavy Duty for extra mechanical strength.

Knife Disconnect Splices


Wire Size Range

AWG 22 to 10,
CMA 509 to 13,100
[0.26 to 6.64 mm²]

Material

Splice Body and Sleeve — Copper
per ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Dimensions		Wire Insulation Dia. Max.	Part Numbers	
	L Max.	W		Loose Piece	Tape Mounted
22–16 509–3,260 [0.26–1.65]	.794 20.17	.203 5.16	.125 3.18	31770	—
	.794 20.17	.203 5.16	.140 3.56	31777	2-31777-1
16–14 2,050–5,180 [1.04–2.62]	.794 20.17	.203 5.16	.150 3.81	31943	—
	.794 20.17	.203 5.16	.170 4.32	31944	—
12–10 5,180–13,100 [2.62–6.64]	1.176 29.87	.281 7.14	.230 5.84	31942	2-31942-1

Slotted Ring Tongue Terminals


Wire Size Range

AWG 26 to 16,
CMA 202 to 3,260
[0.1 to 1.65 mm²]

Material

Terminal Body and Sleeve —
Copper per ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions				Material Thickness Max.	Wire Insulation Dia. Max.	Part Numbers	
		L Max.	E Max.	C Min.	W			Loose Piece	Tape Mounted
26–22 202–810 [0.1–0.41]	6 M3.5	.658 16.71	.551 14.00	.281 7.14	.250 6.35	.020 0.51	.082 2.08	322210	—
22–16 509–3,260 [0.26–1.65]	6 M3.5	.710 18.03	.585 14.86	.250 6.35	.281 7.14	.033 0.84	.125 3.18	34101	—
	8 M4	.701 17.81	.585 14.86	.250 6.35	.281 7.14	.033 0.84	.140 3.56	321543	—

Note: “C” dimension applies from edge of metal wire barrel to center of stud hole.

Rectangular Tongue Terminals


Wire Size Range

AWG 22 to 16,
CMA 509 to 3,260
[0.26 to 1.65 mm²]

Material

Terminal Body and Sleeve —
Copper per ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions				Material Thickness Max.	Wire Insulation Dia. Max.	Part Numbers	
		L Max.	E Max.	C Min.	W			Loose Piece	Tape Mounted
22-16 509-3,260 [0.26-1.65]	5 M3	.786 19.96	.633 16.08	.277 7.04	.277 7.04	.033 0.84	.140 3.56	328500	—

Note: "C" dimension applies from edge of metal wire barrel to center of stud hole.

Flanged Spade Tongue Terminals


Wire Size Range

AWG 26 to 14,
CMA 202 to 5,180
[0.1 to 2.62 mm²]

Material

Terminal Body and Sleeve —
Copper per ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions						Material Thickness Max.	Wire Insulation Dia. Max.	Part Numbers	
		L Max.	E Max.	C Min.	W	X	H			Loose Piece	Tape Mounted
26-22 202-810 [0.1-0.41]	2 M2	.588 14.94	.473 12.01	.203 5.16	.182 4.62	.110 2.79	.031 0.79	.020 0.51	.082 2.08	324598	2-324598-1
22-16 509-3,260 [0.26-1.65]	6 M3.5	.668 16.97	.538 13.67	.203 5.16	.296 7.52	.125 3.18	.046 1.17	.033 0.84	.125 3.18	32419	2-32419-1
	8 M4	.761 19.33	.585 14.86	.250 6.35	.416 10.57	.171 4.34	.062 1.57	.033 0.84	.125 3.18	32495	—
	16-14 2,050-5,180 [1.04-2.62]	.685 17.40	.555 14.10	.203 5.16	.294 7.47	.125 3.18	.052 1.32	.033 0.84	.170 4.32	320859	—

Note: "C" dimension applies from edge of metal wire barrel to center of stud hole.

Spade Tongue Terminals

Wire Size Range


**AWG 26 to 16,
CMA 202 to 3,260
[0.1 to 1.65 mm²]**

Material

Terminal Body and Sleeve —

Copper per ASTM B-152

Plating —Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Stud Size	Dimensions					Material Thickness Max.	Wire Insulation Dia. Max.	Part Numbers	
		L Max.	E Max.	C Min.	W	X			Loose Piece	Tape Mounted
26–22 202–810 [0.1–0.41]	0	.415 10.54	.348 8.84	.078 1.98	.125 3.18	.062 1.57	.020 0.51	.082 2.08	32502	—
	4	.558 14.17	.481 12.22	.211 5.36	.203 5.16	.072 1.83	.020 0.51	.082 2.08	34248	—
22–16 509–3,260 [0.26–1.65]	6	.684 17.37	.538 13.67	.203 5.16	.297 7.54	.141 3.58	.033 0.84	.125 3.18	33766	—
	M3.5	.684 17.37	.538 13.67	.203 5.16	.297 7.54	.141 3.58	.033 0.84	.125 3.18	33766	—
	6	.684 17.37	.538 13.67	.203 5.16	.297 7.54	.141 3.58	.033 0.84	.140 3.56	33799	—
	M3.5	.684 17.37	.538 13.67	.203 5.16	.297 7.54	.141 3.58	.033 0.84	.140 3.56	33799	—
	10	.807 20.50	.631 16.03	.296 7.52	.343 8.71	.171 4.34	.033 0.84	.125 3.18	320379	—

Note: "C" dimension applies from edge of metal wire barrel to center of stud hole.

Knife Disconnect Splices

Wire Size Range

AWG 22 to 8,
CMA 509 to 20,800
[0.26 to 10.5 mm²]

Material

Splice Body and Sleeve — Copper
per ASTM B-152

Plating — Tin per MIL-T-10727



Wire Size Circular Mils [mm ²]	Dimensions		Part Numbers Loose Piece
	L Max.	W	
22–16 509–3,260 [0.26–1.65]	.745 18.92	.203 5.16	31762
16–14 2,050–5,180 [1.04–2.62]	.750 19.05	.203 5.16	31763
12–10 5,180–13,100 [2.62–6.64]	.940 23.88	.281 7.14	31945
8 13,100–20,800 [6.64–10.5]	1.225 31.12	.390 9.91	32161

Rectangular Tongue Terminals


Wire Size Range

AWG 22 to 14,
CMA 509 to 5,180
[0.26 to 2.62 mm²]

Material

Terminal Body and Sleeve —
Copper per ASTM B-152

Plating — Tin per MIL-T-10727



Style A
with Side Flange

Style B
with Bossed Hole

Wire Size Circular Mils [mm ²]	Stud Size	Style	Dimensions						Material Thickness Max.	Part Numbers Loose Piece
			L Max.	E Max.	C Min.	W	X	H		
22–16 509–3,260 [0.26–1.65]	6 M3.5	B	.733 18.62	.541 13.74	.250 6.35	.250 6.35	.187 4.75	.047 1.19	.033 0.84	320671
16–14 2,050–5,180 [1.04–2.62]	8 M4	A	.647 16.43	.484 12.29	.219 5.56	.344 8.74	.156 3.96	.094 2.39	.033 0.84	31674

Note: "C" dimension applies from edge of metal wire barrel to center of stud hole.

SOLISTRAND Military Approved Terminals

Military Specification	SOLISTRAND Approval	Approved Wire Range
MS 20659	Class 1 & 2	12-10
MS 20659	Class 2 Only	8-4/0
M7928/7	Class 2 Only*	22-14

SOLISTRAND Class 1 and Class 2 military approved terminals meet the performance requirements outlined in specification Mil-T-7928G.

*320093 also class 1 approved.

Class 1 and Class 2 Military Approvals

Approval	Dimensional Requirement	Application Tooling	Use	Performance Requirement
Class 1	Terminals must comply with the dimensional requirements specified by the military.	Hand application tool which must conform to the military's dimensional and performance specification.	For procurement by government agencies for maintenance and repair.	Per Military Specification Mil-T-7928G
Class 2	Dimensional requirements are maintained by the terminal manufacturers. For field repair purposes Class 2 terminals must be capable of being replaced by Class 1 Terminals	The terminal manufacturers recommended application tooling. Note: Several tape mounted SOLISTRAND part numbers are currently Class 2 approved.	For procurement by contractors and manufacturers for high volume production, modification, and repair.	

Note: Where class 2 approval exists all similar (form, fit and function) parts in that product line are approved.

Cross Reference Military to AMP Part Number

Military Specification M7928/7

Wire Size Range AWG 22 to 14

AWG	M7928/7 Dash Numbers	SOLISTRAND Part Numbers	Class	Stud Size
22-18	1	34103 2-34103-1	2	2
	2	34104 2-34104-6	2	4
	3	34110 2-34110-3	2	6
	4	34112 2-34112-2	2	10
	5	34114 2-34114-2	2	5/6
	6	34115 2-34115-2	2	3/8
16-14	7	321684 2-321684-1	2	6
	8	320093 2-320093-1	1 & 2	10
	9	34125 2-34125-6	2	5/16
	10	34126 2-34126-2	2	3/8
	11	34119 2-34119-1	2	4

Note: Part numbers are shown as loose piece over tape mounted product.

Cross Reference Military to AMP Part Number

Military Specification MS 20659


Wire Size Range AWG 12 to 4/0

AWG	MS20659 Dash Numbers	SOLISTRAND Part Numbers	Class	Stud Size
12-10	105	33457	1&2	10
		2-33457-2	2	
	106	33459	1&2	5/16
		2-33459-6	2	
8	107	31807	2	10
		2-31807-2		
	108	31808	2	5/16
		321598		
6	109	33467	2	3/8
		31811		
4	110	31812	2	3/8
		320383		
2	111	321600	2	3/8
		321866		
1/0	112	321868	2	3/8
		321870		
2/0	113	321871	2	3/8
		321875		
3/0	114	321877	2	1/2
		321878		
4/0	115	321880	2	1/2
		33220		
12-10	116	33463	2	3/8
		321298		
8	117	33466	2	10
		2-33466-3		
6	118	33115	2	5/16
		36919		
4	119	321873	2	1/2
		321625		
2	120	324061	2	8
		33461		
1/0	121	2-33461-2	2	1/4
		320344		
2/0	122	33114	2	10
		327175		
3/0	123	330301	2	10
		322870		
4/0	124	320741	2	7/16
		321867		
12-10	125	321869	2	5/16
		36918		
8	126	321872	2	7/16
		321874		
6	127	321876	2	7/16
		321271		
4	128	321879	2	7/16
		36935		
2	129	322228	2	3/4
		35476		
1/0	130	2-35476-1	2	6
		35135		

Note: Part numbers are shown as loose piece over tape mounted product.

Description of MIL-T-7928G Test Procedures and Requirements for Terminals

Test Group	Test Sequence	Test Type	Test Description
1	A	Current Cycling	Samples subjected to 50 cycles, each cycle consisting of 30 minutes at 125% of the current listed on page 48 followed by 15 minutes with no load.
	B	Voltage Drop	See test method and requirements on page 48.
2	A	Vibration	See test method on page 46.
	B	Voltage Drop	See test method and requirements on page 48.
	C	Tensile	See test method and requirements on page 47.
3	A	Salt Spray/Corrosion	Samples subjected to a salt spray/fog for 48 hours. Salt concentration to be 5%, temperature to be 35° C (95° F, relative humidity to be 95-98%.
	B	Voltage Drop	See test method and requirements on page 48.
	C	Tensile	See test method and requirements on page 47.
4	A	Heat Age	Samples subjected to 193° C for 120 hours then cooled to 23° C within one hour.
	B	Salt Spray/Corrosion	Samples subjected to a salt spray/fog for 48 hours. Salt concentration to be 5%, temperature to be 35° C (95° F, relative humidity to be 95-98%.
	C	Voltage Drop	See test method and requirements on page 48.
	D	Tensile	See test method and requirements on page 47.

Procedure for Vibration Testing of Terminals per MIL-T-7928G

Wire Size	"D" Dimension	Duration of Test
#12 AWG and larger or terminals with insulation support	12 inches	18 hours each on horizontal and vertical axis.
#14 AWG and smaller with no insulation support	17 inches	2 hours each on horizontal and vertical axis.

Vibration to be a simple harmonic motion with an amplitude of 0.03 inches (0.06 total excursion). Frequency to vary uniformly from 10–55 Hz and back to 10 Hz. Frequency to be traversed in approximately one minute.


Military Tensile Test Results

Tensile Requirements Per MIL-T-7928G


Wire Size AWG	Minimum Tensile Strength (Lbs)
22	15
20	19
18	38
16	50
14	70
12	110
10	150
8	225
6	300
4	400
2	550
1/0	700
2/0	750
3/0	825
4/0	875

Note: 1. Samples tensile tested to destruction at a rate of one inch/minute using military approved wire.


SOLISTRAND Tensile Test Results Wire Sizes 22 – 10



SOLISTRAND Tensile Test Results Wire Sizes 8 – 2



SOLISTRAND Tensile Test Results Wire Sizes 1/0 – 4/0




Tensile after
Vibration

Tensile after
Salt Spray

MIL-T-7928
Requirement

Illustration of Millivolt Drop Measurement Procedure

Military Specification MIL-T-7928G





Wire Size AWG	Test Current (Amperes)	Maximum Crimp MVD = EWL Measurement + Value Listed Below	
		Initial Terminal	Final Terminal
22	9		
20	11		
18	16		
16	22		
14	32		
12	41	1	3
10	55		
8	73		
6	101		
4	135		
2	181		
1/0	245		
2/0	283	2	4
3/0	328		
4/0	380		

Military Millivolt Drop Test Results

SOLISTRAND Millivolt Drop Results Per MIL-T-7928G

Using Military
Approved Wire



Description of UL 486A Test Procedures and Requirements for Terminals

Wire Size Range

AWG 22 to 600 MCM

Test Sequences

Test Group 1

Mechanical Sequence

1. Secureness
2. Pullout

Test Group 2

Mechanical Sequence

1. Secureness
2. Static Heat
3. Pullout

Pullout Test Requirements

Terminal must not be separate from wire when subjected to the listed load for one minute.

Wire Size AWG	Pullout Force (lbs.)
22	8
20	13
18	20
16	30
14	50
12	70
10	80
8	90
6	100
4	140
2	180
1/0	250
2/0	300
3/0	350
4/0	450
250	500
300	550
350	600
400	650
500	800
600	900

Note: Testing conducted on non-plated copper wire with UL approved insulation.

Static Heat Test Requirements


Wire Size AWG	Test Current (Amperes)
22	9
20	12
18	17
16	18
14	30
12	35
10	50
8	70
6	95
4	125
2	170
1/0	230
2/0	265
3/0	310
4/0	360
250	405
300	445
350	505
400	545
500	620
600	690

Requirement:

Connector temperatures must not exceed the ambient temperature plus 50°C [90°F] after stability is attained.

Stability:

A test sample is considered to have attained a stable temperature when three readings taken at not less than 10 minute intervals show no more than a 2°C [3.6°F] variation between any two readings.



Secureness Test Requirements

Wire Size AWG	Bushing Dia.	Height	Weight (lbs.)
18-16	1/4	10 1/4	2
14	3/8	11	3
12-10	3/8	11	5
8	3/8	11	8
6	1/2	11 3/4	18
4	1/2	11 3/4	30
2	9/16	12 1/2	30
1/0	5/8	13 1/2	50
2/0	3/4	14 1/2	50
3/0	3/4	14 1/2	60
4/0	3/4	14 1/2	60
250	7/8	16	60
300	7/8	16	80
350-400	1	17	80
500-600	1 1/8	18 1/4	100

Note: Test Duration = 30 Minutes



Description of UL 486A & C Test Procedures and Requirements for Butt and Parallel Type Splices

UL 486 C Wire Size AWG 22 to 6

UL 486 A Wire Size AWG 4 to 600 MCM

Test Sequences

Test Group 1

Mechanical Sequence

1. Secureness
2. Pullout

Test Group 2

Mechanical Sequence

1. Secureness
2. Static Heat
3. Pullout

Pullout Test Requirements

Splices must not be separate from wire when subjected to the listed load for one minute.

Wire Size AWG	Pullout Force (lbs.)
22	8
20	10
18	10
16	15
14	25
12	35
10	40
8	45
6	50
4	140
2	180
1/0	250
2/0	300
3/0	350
4/0	450
250	500
300	550
350	600
400	650
500	800
600	900

Note: Testing conducted on non-plated copper wire with UL approved insulation.

Static Heat Test Requirements


Wire Size AWG	Test Current (Amperes)
22	9
20	12
18	17
16	18
14	30
12	35
10	50
8	70
6	95
4	125
2	170
1/0	230
2/0	265
3/0	310
4/0	360
250	405
300	445
350	505
400	545
500	620
600	690

Requirement:

Connector temperatures must not exceed the ambient temperature plus 50°C [90°F] after stability is attained.

Stability:

A test sample is considered to have attained a stable temperature when three readings taken at not less than 10 minute intervals show no more than a 2°C [3.6°F] variation between any two readings.



Secureness Test Requirements

Wire Size AWG	Bushing Dia.	Height	Weight (lbs.)
18-16	1/4	10 1/4	2
14	3/8	11	3
12-10	3/8	11	5
8	3/8	11	8
6	1/2	11 3/4	18
4	1/2	11 3/4	30

Note: Test Duration=30 Minutes

Application Tooling Information for SOLISTRAND, Budget and DIAMOND GRIP Products

Wire Size Range AWG 26 to 6

Product Type	AMP Wire Size	Hand Tools	Pneumatic Tooling		Dies for 6-26, Tool 189721-1 Requires Straight Action Adapter 217200-1 or 318161-1 Dies Also Fit 69710-1 Hand Tool	Tooling For Tape Mounted Products
			Crimping Heads for 6-26, Tool 189721-1			Dies for 69875 AMP-TAPETRONIC AMP-O-LECTRIC [®] Requires Applicator
						AMPOMATOR CLS IV Requires Applicators
			Single Wire Range	Multiple Wire Range		
All SOLISTRAND terminals and splices except for Flag Tongue terminals	26-22	69363 ²	—	—	—	—
	24-20					
	22-16	49935 ²	314516-1	679301-1	47812	68240-1
	16-14		314517-1	679301-1	47813	68241-1
	12-10 & 16-14 HD	58546-1 ³	—	679301-1	47814 ¹	68242-1
	14-12	49592 ²	314518-1	—	—	90566-1
	8	—	679302-1	—	—	68243-1
	6	—	679303-1	—	—	—
Flag Tongue terminals only	16-14	49975 ²	217204-1	—	—	Flag terminals not available in tape mounted form
	12-10	49965 ²	217203-1			
Budget terminals and splices	26-22	69363 ²	—	—	—	—
	22-16	58508-1 ⁴				68259-1
	16-14	58508-1 ⁴				68094
	12-10 & 16-14 HD	49656, 58508-1 ⁴				68260-1
DIAMOND GRIP terminals and splices	26-22	48070	—	—	—	69902
	24-20	—	—	—	—	—
	22-16	49512	—	—	—	69903
	16-14	49513	—	—	46251-2	69904
	12-10 & 16-14 HD	59054	—	—	—	—
Standard "B" terminals	26-22	—	—	—	—	—
	22-16	48364	—	—	—	—
	16-14	—	—	—	—	—
	12-10	49736	—	—	—	—
	8	49737	—	—	—	—

¹For standard wire only.

²CERTI-CRIMPHand Tool.

³Contains die set 58545-1. PRO-CRIMPER II commercial tool not approved for UL applications.

⁴Contains die set 58509-1. PRO-CRIMPER II commercial tool not approved for UL applications. Not approved for use with Budget Spring Spade terminals.

⁵With locator, for terminals only.

⁶Call Tooling Assistance Center for Machine & Applicator part numbers.

Chart lists common AMP Application Tooling. For additional information call the Tooling Assistance Center 1-800-722-1111.

Application Tooling Information for SOLISTRAND Terminals and Splices

Wire Size Range
AWG 8 to 600 MCM

			Pneumatic Tooling	Hydraulic Tools With Self-Contained Dies			Hydraulic and Battery Powered Tools With Interchangeable Dies					Tooling For Tape Mounted Product			
Product Type	AMP Wire Size	Hand Tool	69015	Hand Tool	Latch Head	59973-1 Hand Tool, 69065 ¹ & 69067 ¹ Latch Heads		69097 ² "C" Head		59445-1 ² Latch Head	69062 "C" Head	69099 ² "C" Head	Dies for 69875 AMP-TAPETRONIC	Dies for 69250-1 HD AMP-TAPETRONIC	
						Nest	Indent	Nest	Indent						
Standard Terminals and Splice	8	69065 ¹	49956			48126	48355	46146	46145			69216	69243-1	69312-1	
	6	59083 No CERTI-CRIMP	48172	59975-1	69069 ²	48128		46134				69217		69313-1	
	4	59131	48173			48129	48127	46135	46133			69218			
	2		48174			48130		46136				45433			
	1/0		48183			48132		46138	46137			45436			
	2/0					48133						45439			
	3/0					48134	48131					45442			
	4/0					900490						45445			
	250-300 MCM									48816	69911				
	300-350 MCM									48817	69912				
	400 MCM									48818	69913				
	500-600 MCM									48819	69914				
	Heavy Duty Terminals	8 HD					48128-1								
		6 HD					48129-1	48127-1							
4 HD				—		48130-1									
2 HD						48132-1	48131-1								
1/0 HD						48133-1									
Tooling for Flag Terminals only	8		48412			Only the 69067 head can be used for Flag terminals									
						48506	48505								
	6		48413			48508									
	4		48414		—	48509	48507		—						
	2		48415			48510									
	1/0	— ¹	48416			48552									
	2/0					48805									
3/0			— ¹		48806	48511									
4/0					48807										

¹CERTI-CRIMP Hand Tool.

²These crimping heads are recommended for use only with AMP Hydraulic Hand Pump 314979-1, DYNA-CRIMP Hydraulic Power Units 69120-1 (115 VAC) and 69120-2 (230 VAC), and with DYNA-CRIMP II Battery Operated Hydraulic Power Unit 122271-1. See pages 55 & 56.

Chart lists common AMP Application Tooling. For additional information call the Tooling Assistance Center 1-800-722-1111.

Application Tooling

Loose Form Terminal and Splice Tooling

CERTI-CRIMP Hand Tools



Double Action
Hand Tool



Heavy Head Hand Tool
Part No. 69355



"C" Head Straight
Action Hand Tool
Part No. 69710-1




PRO-CRIMPER II
Hand Tool
Part No. 58546-1 SOLISTRAND
58508-1 Budget

Pneumatic Tools



6-26 Pneumatic Tool
Part No. 189721-1



Part No. 69015

Hydraulic Hand Tools



Part No. 59975-1
(Self Contained Dies)




Part No. 59973-1
(Dies Required)


For additional tooling information, call 1-800-722-1111.

Application Tooling (Continued)


Tape Mounted



AMP-TAPETRONIC Machine
69875, 68250-1
(Requires Dies)



AMP-O-LECTRIC, Model "G" Machine
(Requires Applicator and Dies)



AMPOMATOR CLS IV Machine 217500-1
(Requires Applicators and Dies)



Entry Level Terminator
(Requires Applicators and Dies)

For additional tooling information, call 1-800-722-1111.

Application Tooling (Continued)

Latch Heads and Dies



Part No.
69065



Part No.
58445-1




Part No.
69067



Part No. 69069
(Self Contained Dies)



Part No.
69099



Part No.
69082



Part No.
69097

For additional tooling information, call 1-800-722-1111.


Application Tooling (Continued)

DYNA-CRIMP II Battery Operated Hydraulic Power Unit



Part No. 122271-1⁴

Hand Operated Power Unit




314979-1² (Hose, head and dies not included)
Refer to the table below for accessories.

DYNA-CRIMP Electric Hydraulic Power Unit




Power Unit Only
(Includes Pressure Release)
115 Volts (60 Hz) — 69120-1³
230 Volts (60 Hz) — 69120-2³


AMP application tools are designed to produce a carefully controlled uniform pressure crimp, regardless of how they are powered. All tools shown are specially designed for AMP products and are precision machined from hard tool steel.




Handle
Control



Hose
Assembly



Foot
Control



Multidirectional
Valve

Power Units Accessories

For Use With Power Unit No.	Accessory Description	Accessory Part No.	Remarks
69120-1 ³ 69120-2 ³ 314979-1 ² 122271-1 ⁴	7' Handle Control Assembly—Hose & Cord	59907-7	
	15' Handle Control Assembly—Hose & Cord	1-59907-5	
	21' Handle Control Assembly—Hose & Cord	2-59907-1	
	28' Handle Control Assembly—Hose & Cord	2-59907-8	
	15' Foot Switch Assembly	68284-1	Need Hose Assembly
	3' Hose Assembly	59909-3	68284-1 Foot Switch Assembly needed with these Hose Assemblies and 69120
	7' Hose Assembly	59909-7	
	15' Hose Assembly	1-59909-5	
	21' Hose Assembly	2-59909-1	
	2' Hose Assembly (1/4" I.D.)	314990-1	More Flexible, Lighter Weight. Recommended for use with DYNA-CRIMP II Battery Operated Hydraulic Power Unit
	3' Hose Assembly (1/4" I.D.)	314990-2	
	7' Hose Assembly (1/4" I.D.)	314990-3	
	15' Hose Assembly (1/4" I.D.)	314990-4	
69120-1 ³	3-Way Multi-Directional Valve	59220 ¹	For use with Foot Switch only
69120-2 ³	3-Way Multi-Directional Valve (Elec.Ctl)	59220-2 ¹	

¹ Contact AMP Incorporated for usage recommendations.

² Also see AMP Customer Manual 409-5860.

³ Also see AMP Customer Manual 409-1950.

⁴ Also see AMP Customer Manual 409-5869.

Note: All Hoses and Handle Control Assemblies have a 3/8" high flow male coupler (311470-1) on each end.
All Power Units and Heads have a 3/8" high flow female coupler (311471-1).

For additional tooling information, call 1-800-722-1111.

Part Number Index

Note: This numerical index lists all cataloged parts by base no. only. Complete part nos. (with prefixes and/or suffixes) are shown on the page(s) indicated.

Part No.	Page
30691	12
30692	12
30693	13
30694	13
30695	13
30696	13
30697	13
30926	39
30927	39
30928	39
30953	36
30972	15
30993	39
30995	38
30996	38
30997	38
31049	13
31087	12
31088	12
31089	12
31090	12
31091	12
31094	38
31096	38
31101	12
31112	14
31113	14
31114	14
31120	14
31122	14
31123	14
31159	38
31160	38
31161	38
31163	13
31164	14
31165	14
31169	39
31172	13
31173	13
31176	38
31251	38
31256	39
31264	12
31265	12
31266	13
31269	38
31270	38
31393	38
31396	38
31397	38
31398	38
31423	12
31425	12
31428	12
31430	12
31442	26
31498	13

Part No.	Page
31499	14
31516	38
31518	38
31587	26
31588	26
31589	26
31628	32
31634	26
31635	26
31636	26
31674	43
31679	38
31681	38
31691	24
31704	26
31705	26
31706	26
31762	43
31763	43
31770	40
31771	39
31772	39
31777	40
31805	14
31807	15
31808	15
31811	16
31812	16, 21
31813	24
31818	36
31819	36
31821	24
31825	39
31828	39
31942	40
31943	40
31944	40
31945	43
32151	36
32161	43
32185	13
32186	13
32187	39
32188	39
32189	39
32190	39
32416	30
32418	30
32419	41
32463	36
32464	36
32494	30
32495	41
32501	26
32502	42
32503	32
32579	24
32822	12
32823	12
32824	13
32858	12
32859	12

Part No.	Page
32860	12
32861	38
32862	38
32882	14
32994	14
32995	26
32996	15
33114	16
33115	16, 21
33195	22
33202	26
33219	26
33220	15
33221	26
33426	25
33437	32
33456	14
33457	14
33458	14
33459	14
33460	15
33461	15
33462	15
33463	15
33464	16
33465	16
33466	16, 21
33467	16
33468	16
33469	16
33470	16
33471	16
33479	26
33639	39
33646	22
33647	22
33648	22
33695	12
33716	22
33717	22
33718	22
33722	39
33728	22
33729	22
33765	26
33766	42
33799	42
34101	40
34103	12
34104	12
34105	12
34107	12
34108	12
34109	13
34110	12
34111	12
34112	13
34113	13
34114	13
34115	13
34117	26
34118	26

Part No.	Page
34119	13
34120	13
34121	13
34122	13
34123	13
34124	14
34125	14
34126	14
34128	26
34129	26
34130	35
34137	35
34138	35
34194	12
34226	36
34227	36
34228	36
34247	26
34248	42
34261	32
34266	24
34318	35
34319	35
34320	35
34321	36
34322	36
34323	36
34384	26
34404	14
34459	24
34484	14
34486	14
34487	14
34518	26
34520	31
34525	24
34567	22
34582	26
34583	26
34829	22
34830	22
34833	15
34834	15
34891	14
34892	14
34896	13
34964	14
34965	14
34966	14
34967	22
34968	22
34969	22
35116	26
35135	15
35183	17
35184	17
35185	17
35187	35
35189	36
35212	32
35247	15
35277	21

Part Number Index (Continued)

Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page
35278	24	36958	37	53150	27	320857	30
35432	22	36959	37	53175	27	320859	41
35476	14	36960	37	53177	28	320870	24
35493	26	50334	12	53226	28	321007	13
35494	26	50981	14	53235	27	321024	36
35495	26	50982	14	53266	27	321051	33
35555	31	51872	13	53267	27	321056	33
35625	21	51875	30	53268	27	321059	33
35664	15	52197	16	53270	28	321060	33
35665	15	52269	15	53271	28	321063	33
35666	15	52512	30	53273	28	321064	33
35668	17	52700	29	53274	28	321066	34
35669	17	52701	29	53555	26	321121	33
35670	17	52702	29	53830	27	321123	34
35678	21	52703	29	53831	27	321163	19
35680	31	52704	29	53832	27	321165	22
35771	14	52705	29	53833	28	321198	36
35772	14	52706	29	53834	28	321201	33
35775	22	52707	29	53835	28	321253	33
35776	22	52708	29	53836	28	321259	34
36189	12	52709	29	55812	31	321262	21
36195	26	52710	29	55991	15	321265	21
36199	22	52712	29	184147	33	321271	19
36200	22	52713	29	184269	21	321272	21
36201	22	52714	29	320093	13	321275	33
36216	31	52715	29	320138	17	321277	34
36269	33	52716	29	320238	36	321280	36
36270	33	52717	29	320266	18	321288	31
36271	33	52730	30	320344	16	321289	31
36272	33	52733	29	320379	42	321298	16
36451	14	52734	29	320383	17	321441	33
36467	12	52735	29	320671	43	321463	26
36499	15	52772	29	320677	12	321499	25
36807	16	53000	27	320678	38	321501	39
36808	16	53001	27	320741	17	321543	40
36809	16	53002	27	320743	17	321557	25
36810	16	53003	27	320744	18	321558	25
36815	16	53004	27	320745	16	321576	33
36880	26	53005	27	320748	18	321580	34
36886	36	53006	27	320749	30	321582	34
36906	36	53007	27	320754	17	321584	34
36909	35	53009	28	320755	17	321598	16
36915	17	53010	28	320758	22	321600	17
36916	17	53011	28	320759	22	321621	38
36917	17	53012	28	320760	15	321625	19
36918	17	53013	28	320761	15	321632	32
36919	18	53014	28	320762	15	321683	13
36921	18	53015	28	320763	15	321684	13
36922	18, 21	53016	28	320764	15	321691	24
36923	18	53032	28	320765	15	321801	36
36925	18	53033	29	320814	24	321809	31
36927	18	53047	29	320815	24	321827	14
36929	19, 21	53106	16	320818	24	321828	14
36930	19	53111	29	320819	24	321829	14
36932	19	53120	27	320820	24	321866	17
36934	19	53121	27	320822	25	321867	17, 21
36935	19	53123	28	320823	25	321868	17
36946	35	53124	28	320852	30	321869	18
36948	35	53125	28	320853	30	321870	18
36951	35	53126	28	320854	30	321871	18
36953	31	53127	28	320855	30	321872	18
36957	37	53128	28	320856	30	321873	18

Part Number Index (Continued)

Part No.	Page
321874	18, 21
321875	18
321876	18
321877	19
321878	19
321879	19
321880	19
322204	33
322210	40
322211	31
322215	34
322222	19
322223	19
322224	18
322225	18
322227	19
322228	19
322235	13
322242	15
322246	36
322252	19
322253	19
322254	19
322257	20
322258	20
322259	20
322262	20
322263	20
322264	20
322267	20
322269	20
322270	20
322271	20
322273	20
322275	35
322276	35
322277	35
322278	35
322279	37
322280	37
322281	37
322282	37
322291	18
322296	39
322391	18

Part No.	Page
322408	24
322418	12
322428	20
322441	32
322443	32
322445	32
322447	14
322451	26
322454	14
322455	14
322459	36
322514	31
322704	16
322725	30
322727	33
322763	20
322764	20
322768	21
322771	12
322772	20
322773	20
322776	30
322819	33
322821	21
322832	22
322833	22
322870	17, 21
322905	21
322906	21
322909	21
322912	21
322927	12
322939	20
322945	25
322946	25
322996	26
323034	19
323050	19
323086	12
323087	13
323096	12
323106	24
323112	24
323119	24
323124	30

Part No.	Page
323127	26
323129	31
323135	32
323136	30
323140	19
323143	30
323144	30
323196	33
323222	20
323291	17
323823	26
323832	31
323834	26
323835	31
323837	31
323838	31
323868	18
324001	36
324023	21
324035	21
324061	15
324105	20
324124	13
324202	20
324209	32
324521	26
324523	39
324578	30
324579	30
324598	41
324599	30
324604	30
324605	30
324893	36
324898	36
324910	14
324911	14
324955	13
325069	33
325195	26
325196	26
326850	12
326854	13
326889	39
327025	36

Part No.	Page
327175	17
327732	22
327882	20
327887	34
327902	32
327905	32
327951	24
327953	25
327955	24
327959	25
327971	25
328050	25
328339	24
328341	24
328342	24
328349	24
328353	24
328355	24
328356	24
328363	24
328377	13
328395	26
328500	41
328522	30
328872	31
328970	13
328971	14
329966	13
330301	17
330367	36
330368	36
330369	36
330539	24
330827	26
330968	22
330969	23
330970	23
331269	25
331401	12
331414	22
331417	23
331420	23
331423	23
331880	23
332042	22

Americas

Argentina – Buenos Aires
Phone: + 54-1-733-2000
Fax: + 54-1-717-0988

Brazil – Sao Paulo
Phone: + 55-11-861-1311
Fax: + 55-11-861-0397

Canada – Toronto
Phone: + 1-905-475-6222
Fax: + 1-905-474-5520

Chile – Santiago
Phone: + 56-2-739-1230
Fax: + 56-2-739-1227

Colombia – Bogota
Phone: + 57-1-231-9398
Fax: + 57-1-240-3769

Mexico – Mexico City
Phone: + 52-5-729-0400
Fax: + 52-5-361-8545

United States – Harrisburg, PA
Phone: + 1-717-564-0100
Fax: + 1-717-986-7575

Venezuela – Caracas
Phone: + 58-2-986-7774
Fax: + 58-2-986-9739

**For Latin/South American
Countries not shown**
Phone: +54-11-4733-2015
Fax: +54-11-4733-2083

Asia/Pacific

Australia – Sydney
Phone: + 61-2-9840-8200
Fax: + 61-2-9899-5649

India – Bangalore
Phone: + 91-80-841-0200
Fax: + 91-80-841-0210

Indonesia – Jakarta
Phone: + 6221-526-7852
Fax: + 6221-526-7856

Japan – Tokyo
Phone: + 81-44-844-8111
Fax: + 81-44-812-3207

Korea – Seoul
Phone: + 82-2-3274-0535
Fax: + 82-2-3274-0524/0531

Malaysia – Selangor
Phone: + 60-3-7053055
Fax: + 60-3-7053066

New Zealand – Auckland
Phone: + 64-9-634-4580
Fax: 64-9-634-4586

People's Republic of China
Hong Kong
Phone: + 852-2735-1628
Fax: + 852-2735-0243
Shanghai
Phone: + 86-21-6485-0602
Fax: + 86-21-6485-0728
Shunde
Phone: + 86-765-7751368
Fax: + 86-765-7752823

Philippines – Makati City
Phone: + 632-867-8641
Fax: + 632-867-8661

Singapore – Singapore
Phone: + 65-482-0311
Fax: + 65-482-1012

Taiwan – Taipei
Phone: + 886-2-2325-0391
Fax: + 886-2-2325-0398

Thailand – Bangkok
Phone: + 66-2-955-0500
Fax: + 66-2-955-0505

Vietnam – Ho Chi Minh City
Phone: + 84-8-8232-546/7
Fax: + 84-8-8221-443

Europe/Middle East/Africa

Austria – Vienna
Inside: Phone: + 0222-277-97-0
Fax: + 0222-277-97-333

Outside: Phone: + 43-1-277-97-0
Fax: + 43-1-277-97-333

Belgium – Kessel - Lo
Phone: + 32-16-35-23-00
Fax: + 32-16-35-23-52

Bulgaria – Sofia
Phone: + 359-2-971-2152
Fax: + 359-2-971-2153

Czech Republic – Kurim
Phone: + 420-5-41-162-111
Fax: + 420-5-41-162-223

Denmark – Viby
Phone: + 45-86-295-055
Fax: + 45-86-295-133

Egypt – Cairo
Phone: + 202-417-76-47
Fax: + 202-419-23-34

Estonia – Haabneeme
Phone: + 372-6205-900
Fax: + 372-6205-980

Finland – Helsinki
Phone: + 358-9-512-34210
Fax: + 358-9-512-34250

France – Cergy - Pontoise
Phone: + 33-1-3420-8888
Fax: + 33-1-3420-8600

Germany – Bensheim
Phone: + 49-6251-133-0
Fax: + 49-6251-133-600

Germany – Neunkirchen - HTS Div.
Phone: + 49-2247-305-0
Fax: + 49-2247-305-122

Great Britain – London
Phone: + 44-208-954-2356
Fax: + 44-208-954-6234

Greece – Athens
Phone: + 30-1-9370-396/7
Fax: + 30-1-9370-655

Holland – 's-Hertogenbosch
Phone: + 31-73-624-62-46
Fax: + 31-73-621-23-65

Hungary – Budapest
Phone: + 36-1-350-8633
Fax: + 36-1-350-8634

Ireland – Dublin
Phone: + 353-1-820-3000
Fax: + 353-1-820-9790

Israel – Tel Aviv
Phone: + 972-3-649-1482
Fax: + 972-3-648-4041

Italy – Torino
Phone: + 39-011-4012-111
Fax: + 39-011-4031-116

Lithuania – Vilnius
Phone: + 370-2-231-402
Fax: + 370-2-231-403

Norway – Nesbru
Phone: + 47-66-77-8899
Fax: + 47-66-77-8855

Poland – Warsaw
Phone: + 48-22-611-59-30
Fax: + 48-22-672-47-88

Portugal – Lisbon
Phone: + 351-1-387-70-16
Fax: + 351-1-387-71-72

Romania – Bucharest
Phone: + 40-1-311-3479/3596
Fax: + 40-1-312-0574

Russia - Moscow
Phone: + 7-095-926-5506/07/08/09
Fax: + 7-095-926-5505

Russia - St. Petersburg
Phone: + 7-812-325-30-83
Fax: + 7-812-325-32-88

Slovakia – Banska Bystrica
Phone: + 421-88-415-20-11/12
Fax: + 421-88-415-20-13

Slovenia – Ljubljana
Phone: + 386-61-161-3270
Fax: + 386-61-161-3240

South Africa – Midrand
Phone: + 27-11-314-10-89
Fax: + 27-11-314-19-10

Spain – Barcelona
Phone: + 34-93-291-0330
Fax: + 34-93-201-7879

Sweden – Upplands Vasby
Phone: + 46-8-50-72-50-00
Fax: + 46-8-50-72-50-01

Switzerland – Steinach
Phone: + 41-71-447-0447
Fax: + 41-71-447-0444

Turkey – Istanbul
Phone: + 90-212-281-8181/2/3
Fax: + 90-212-281-8184

Ukraine – Kiev
Phone: + 38-044-246-5501
Fax: + 38-044-246-5501

**For Middle East/African
Countries not shown**
Phone: +33-1-34-20-83-83
Fax: +33-1-34-20-86-09
