OSRAM KW HJL531.TE

Datasheet

Published by ams-OSRAM AG
Tobelbader Strasse 30, 8141 Premstaetten, Austria
Phone +43 3136 500-0
ams-osram.com
© All rights reserved

Downloaded from Arrow.com.

OSRAM

OSLON® Black Flat S

KW HJL531.TE



OSLON Black Flat S is able to meet a wide range of requirements. The SMT device is very stable, durable and can be used with standard processes. A new solder pad layout allows for high reliability and improved thermal management. The compact chips not only deliver high light output, they are also individually addressable with an ensured chip-to-chip contrast which makes this LED an ideal solution for Adaptive Driving Beam (ADB).



Applications

- Static Forward Lighting

Features

- Package: SMD epoxy package
- Chip technology: UX:3
- Typ. Radiation: 120° (Lambertian emitter)
- Color: Cx = 0.322, Cy = 0.334 acc. to CIE 1931 (● ultra white)
- Corrosion Robustness Class: 3B
- Qualifications: AEC-Q102 Qualified with RV-level 1
- ESD: 8 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 3B)

Downloaded from Arrow.com.

Ordering Information

Type	Luminous Flux [1] I_F = 1000 mA Φ_V	Ordering Code
KW HJL531.TE-T0T8-ebvFfcbB46-DFYF	980 ... 1375 lm	Q65112A8332

Downloaded from Arrow.com.

Maximum Ratings

Parameter	Symbol		Values
Operating Temperature	T_{op}	min. max.	-40 °C 125 °C
Storage Temperature	T_{stg}	min. max.	-40 °C 125 °C
Junction Temperature	T_j	max.	150 °C
Junction Temperature for short time applications*	T_j	max.	175 °C
Forward current T_S = 25 °C	I_F	min. max.	50 mA 1500 mA
Surge current t ≤ 10 µs; D = 0.005 ; T_S = 25 °C	I_{FS}	max.	3000 mA
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 3B)	V_{ESD}		8 kV
Reverse current [2)]	I_R	max.	200 mA

* The median lifetime (L70/B50) for Tj = 175°C is 100h.

Downloaded from Arrow.com.

Characteristics

I_F = 1000 mA; T_S = 25 °C

Parameter	Symbol		Values
Chromaticity Coordinate [3]	Cx	typ.	0.322
	Cy	typ.	0.334
Viewing angle at 50% I_V	2φ	typ.	120 °
Radiating surface	A_{color}	typ.	3,3 mm²
Forward Voltage [4] I_F = 1000 mA	V_F	min. typ. max.	8.15 V 9.05 V 11.15 V
Reverse voltage (ESD device)	$V_{R\ ESD}$	min.	45 V
Reverse voltage [2] I_R = 20 mA	V_R	max.	1.2 V
Chip to Chip Contrast	-	typ.	1:200
Real thermal resistance junction/solderpoint [5]	$R_{thJS\ real}$	typ. max.	1.30 K / W 1.60 K / W
Electrical thermal resistance junction/solderpoint [5] with efficiency η_e = 37 %	$R_{thJS\ elec.}$	typ. max.	0.82 K / W 1.01 K / W

Downloaded from Arrow.com.

Brightness Groups


Group	Luminous Flux [1] I_F = 1000 mA min. Φ_V	Luminous Flux [1] I_F = 1000 mA max. Φ_V	Luminous Intensity [6] I_F = 1000 mA typ. I_v
T0	980 lm	1020 lm	330 cd
T1	1020 lm	1060 lm	340 cd
T2	1060 lm	1100 lm	360 cd
T3	1100 lm	1140 lm	370 cd
T4	1140 lm	1185 lm	380 cd
T5	1185 lm	1230 lm	400 cd
T6	1230 lm	1275 lm	410 cd
T7	1275 lm	1325 lm	430 cd
T8	1325 lm	1375 lm	450 cd

Forward Voltage Groups

Group	Forward Voltage [4] I_F = 1000 mA min. V_F	Forward Voltage [4] I_F = 1000 mA max. V_F
DF	8.15 V	8.90 V
UF	8.90 V	9.65 V
GF	9.65 V	10.40 V
YF	10.40 V	11.15 V

Downloaded from Arrow.com.

Chromaticity Coordinate Groups [3)]



Chromaticity Coordinate Groups [3)]

Group	Cx	Cy	Group	Cx	Cy
ebvF46	0.3104	0.3234	ebzB46	0.3190	0.3430
	0.3199	0.3325		0.3298	0.3526
	0.3212	0.3175		0.3299	0.3361
	0.3127	0.3093		0.3203	0.3274
ebxD46	0.3145	0.3330	fcbB46	0.3241	0.3534
	0.3246	0.3424		0.3355	0.3633
	0.3253	0.3266		0.3350	0.3460
	0.3163	0.3181		0.3248	0.3370

Downloaded from Arrow.com.

Group Name on Label


Example: T0-ebvF46-DF

Brightness	Color Chromaticity	Forward Voltage
T0	ebvF46	DF

Downloaded from Arrow.com.

Relative Spectral Emission [6)]


$\Phi_{rel} = f(\lambda)$; I_F = 1000 mA; T_S = 25 °C



Note: Percentage of red: >5% acc. to ECE regulation
Percentage of UV: <10^{-5}W/lm acc. to ECE regulation

Radiation Characteristics [6)]


$I_{rel} = f(\phi)$; T_S = 25 °C



Downloaded from Arrow.com.


Forward current 6), 7)

$I_F = f(V_F)$; T_S = 25 °C




Relative Luminous Flux 6), 7)

$\Phi_v/\Phi_v(1000\ mA) = f(I_F)$; T_S = 25 °C



Chromaticity Coordinate Shift 6)


$\Delta Cx, \Delta Cy = f(I_F)$; T_S = 25 °C



Downloaded from Arrow.com.


Forward Voltage [6)]

$\Delta V_F = V_F - V_F(25\ °C) = f(T_j);\ I_F = 1000\ mA$




Relative Luminous Flux [6)]

$\Phi_v/\Phi_v(25\ °C) = f(T_j);\ I_F = 1000\ mA$



Chromaticity Coordinate Shift [6)]


$\Delta Cx, \Delta Cy = f(T_j);\ I_F = 1000\ mA$



Downloaded from Arrow.com.


Max. Permissible Forward Current [5)]

I_F = f (T); 0.7 * $\Phi_{V\ min.}$ of bin T0; $R_{th\ real\ max.}$




Permissible Pulse Handling Capability

I_F = f(t_p); D: Duty cycle



Downloaded from Arrow.com.

Dimensional Drawing [8)]



general tolerance ±0.1
Lead finish Au

C63062-A4297-A1-02

Further Information:


Approximate Weight: 35.0 mg

Corrosion test: Class: 3B
Test condition: 40°C / 90 % RH / 15 ppm H_2S / 14 days (stricter than IEC 60068-2-43)


ESD advice: The device is protected by ESD device which is connected in parallel to the Chip.

Downloaded from Arrow.com.

Electrical Internal Circuit



Recommended Solder Pad [8)]




E062.3010.203 -03

For superior solder joint connectivity results we recommend soldering under standard nitrogen atmosphere. Package not suitable for ultra sonic cleaning. To ensure a high solder joint reliability and to minimize the risk of solder joint cracks, the customer is responsible to evaluate the combination of PCB board and solder paste material for his application.

Downloaded from Arrow.com.

Reflow Soldering Profile

Product complies to MSL Level 2 acc. to JEDEC J-STD-020E




Profile Feature	Symbol	Pb-Free (SnAgCu) Assembly			Unit
		Minimum	Recommendation	Maximum	
Ramp-up rate to preheat*) 25 °C to 150 °C			2	3	K/s
Time t_S T_{Smin} to T_{Smax}	t_S	60	100	120	s
Ramp-up rate to peak*) T_{Smax} to T_P			2	3	K/s
Liquidus temperature	T_L		217		°C
Time above liquidus temperature	t_L		80	100	s
Peak temperature	T_P		245	260	°C
Time within 5 °C of the specified peak temperature T_P - 5 K	t_P	10	20	30	s
Ramp-down rate* T_P to 100 °C			3	6	K/s
Time 25 °C to T_P				480	s

All temperatures refer to the center of the package, measured on the top of the component
* slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range

Downloaded from Arrow.com.


Taping [8)]



C67062-A4297-B11-03

Downloaded from Arrow.com.

Tape and Reel [9)]




Leader: min. 400mm*
Trailer: min. 160mm*
*)Dimensions acc. to IEC 60286-3; EIA 481-E

Reel Dimensions


A	W	N_{min}	W_1	$W_{2\,max}$	Pieces per PU
180 mm	12 + 0.3 / - 0.1 mm	60 mm	12.4 + 2 mm	18.4 mm	2000

Downloaded from Arrow.com.

Barcode-Product-Label (BPL)




Dry Packing Process and Materials [8)]



Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.

Downloaded from Arrow.com.

Type Designation System



Downloaded from Arrow.com.

Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet fall into the class **moderate risk (exposure time 0.25 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit https://ams-osram.com/support/application-notes

Downloaded from Arrow.com.

Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics.
Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.
For information on the types in question please contact our Sales Organization.
If printed or downloaded, please find the latest version on our website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.
Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/ applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.

Downloaded from Arrow.com.

Glossary

1) **Brightness:** Brightness values are measured during a current pulse of typically 25 ms, with an internal reproducibility of ±8 % and an expanded uncertainty of ±11 % (acc. to GUM with a coverage factor of k = 3).

2) **Reverse Operation:** This product is intended to be operated applying a forward current within the specified range. Applying any continuous reverse bias or forward bias below the voltage range of light emission shall be avoided because it may cause migration which can change the electro-optical characteristics or damage the LED.

3) **Chromaticity coordinate groups:** Chromaticity coordinates are measured during a current pulse of typically 25 ms, with an internal reproducibility of ±0.005 and an expanded uncertainty of ±0.01 (acc. to GUM with a coverage factor of k = 3).

4) **Forward Voltage:** The forward voltage is measured during a current pulse of typically 8 ms, with an internal reproducibility of ±0.05 V and an expanded uncertainty of ±0.1 V (acc. to GUM with a coverage factor of k = 3).

5) **Thermal Resistance:** Rth max is based on statistic values (6σ) used for Derating.

6) **Typical Values:** Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.

7) **Characteristic curve:** In the range where the line of the graph is broken, you must expect higher differences between single devices within one packing unit.

8) **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.

9) **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.

Downloaded from Arrow.com.

Revision History

Version	Date	Change
1.3	2019-02-12	Ordering Information Brightness Groups Derating (Diagrams) Type Designation System Notes Disclaimer
1.4	2019-08-22	Ordering Information Characteristics Brightness Groups Group Name on Label Derating (Diagrams) Recommended Solder Pad Notes Disclaimer
1.5	2020-01-30	Features Dry Packing Process and Materials Dimensions of Transportation Box
1.6	2020-10-13	Further Information Recommended Solder Pad Glossary
1.7	2023-11-28	Applications New Layout

Downloaded from Arrow.com.

EU RoHS and China RoHS compliant product
此产品符合欧盟 RoHS 指令的要求；
按照中国的相关法规和标准，
不含有毒有害物质或元素。

Published by ams-OSRAM AG
Tobelbader Strasse 30, 8141 Premstaetten, Austria
Phone +43 3136 500-0
ams-osram.com
© All rights reserved

Downloaded from Arrow.com.