

A

В

E

F

G

Н

K

ľ

High Performance Connector Contacts, Wire and Cable



Glenair brings a new perspective to the supply of high-performance Mil-Spec and commercial contacts, wire and cable: High Availability! Whether you need a standard duty socket contact for a MIL-DTL-28840 connector or an extended duty pin for MIL-DTL-38999 Series III, we have you covered with products that are always in stock—with no dollar or quantity minimums. In addition to the broadest selection and availability, Glenair also delivers outstanding interconnection compatibility. Glenair QPL SAE-AS39029 as well as our proprietary contact series are guaranteed to mate properly and perform at the upper limits of application requirements.





For more information contact Glenair at **818-247-6000** or visit our website at **www.glenair.com** U.S. CAGE code 06324

SAE-AS39029 **Crimp Contact Selection Guide**



Military Part Number	Glenair Part Number	Contact Size	Wire Accommodation	Pin / Socket	C	BIN olor Stripir	ng
M39029/56-348	850-001-22-348	22	22-28 AWG	Socket	Orange	Yellow	Grey
M39029/56-351	850-001-20-351	20	20-24 AWG	Socket	Orange	Green	Brown
M39029/56-352	850-001-16-352	16	16-20 AWG	Socket	Orange	Green	Red
M39029/56-353	850-001-12-353	12	12-14 AWG	Socket	Orange	Green	Orange
M39029/56-527	850-001-10-527	10	10 AWG	Socket	Green	Red	Violet
M39029/57-354	850-003-22-354	22	22-28 AWG	Socket	Orange	Green	Yellow
M39029/57-357	850-003-20-357	20	20-24 AWG	Socket	Orange	Green	Violet
M39029/57-358	850-003-16-358	16	16-20 AWG	Socket	Orange	Green	Grey
M39029/57-359	850-003-12-359	12	12-14 AWG	Socket	Orange	Green	White
M39029/58-360	850-002-22-360	22	22-28 AWG	Pin	Orange	Blue	Black
M39029/58-363	850-002-20-363	20	20-24 AWG	Pin	Orange	Blue	Orange
M39029/58-364	850-002-16-364	16	16-20 AWG	Pin	Orange	Blue	Yellow
M39029/58-365	850-002-12-365	12	12-14 AWG	Pin	Orange	Blue	Green
M39029/58-528	850-002-10-528	10	10 AWG	Pin	Green	Red	Grey
M39029/63-368	850-021-20-368	20	20-24 AWG	Socket	Orange	Blue	Grey
M39029/64-369	850-022-20-369	20	20-24 AWG	Pin	Orange	Blue	White
			BIN Color Coding				

M39029/107-624		850-007-10-62	24 10	
				BIN Col
0 BLACK	1 BROWN	2 RED	3 ORANGE	4 YELLOW

	Military Part Number	Glenair Part Number	Contact Size	Wire Accommodation	Pin / Socket	C	BIN olor Stripir	ng
	M39029/83-450	850-004-20-450	20	22-26 AWG	Pin	Yellow	Green	Black
_	M39029/83-451	850-004-20-451	20	28-32 AWG	Pin	Yellow	Green	Brown
	M39029/83-508	850-004-20-508	20	20-24 AWG	Pin	Green	Black	Grey
	M39029/84-452	850-005-20-452	20	22-26 AWG	Socket	Yellow	Green	Red
	M39029/84-453	850-005-20-453	20	28-32 AWG	Socket	Yellow	Green	Orange
	M39029/84-509	850-005-20-509	20	20-24 AWG	Socket	Green	Black	White
	M39029/106-614	850-006-22-614	22	22-28 AWG	Socket	Blue	Brown	Yellow
	M39029/106-615	850-006-20-615	20	20-24 AWG	Socket	Blue	Brown	Green
	M39029/106-616	850-006-16-616	16	16-20 AWG	Socket	Blue	Brown	Blue
	M39029/106-617	850-006-12-617	12	12-14 AWG	Socket	Blue	Brown	Violet
	M39029/106-618	850-006-10-618	10	10 AWG	Socket	Blue	Brown	Grey
	M39029/107-620	850-007-22-620	22	22-28 AWG	Pin	Blue	Red	Black
	M39029/107-621	850-007-20-621	20	20-24 AWG	Pin	Blue	Black	Brown
	M39029/107-622	850-007-16-622	16	16-20 AWG	Pin	Blue	Red	Red
	M39029/107-623	850-007-12-623	12	12-14 AWG	Pin	Blue	Red	Orange
_	M39029/107-624	850-007-10-624	10	10 AWG	Pin	Blue	Red	Yellow
				BIN Color Coding				
	0 1	2	3	4 5	6	7	8	9

BLUE

VIOLET

GREY

WHITE

YELLOW

GREEN

BLUE

VIOLET

GREY

WHITE

ORANGE

BLACK

BROWN

RED

High-Performance Shielded Contacts Selection guide



High-Performance Shielded Contacts Selection guide



Λ	
A	

Military Part Number	Glenair Part Number	Contact Size	Pin / Socket	Туре	C	BIN Olor Stripin	ıg
M39029/27-210	852-001-12-210	12	Socket	Coaxial	Red	Brown	Black
M39029/27-402	852-001-12-402	12	Socket	Coaxial	Yellow	Black	Red
M39029/27-403	852-001-12-403	12	Socket	Coaxial	Yellow	Black	Orange
M39029/27-404	852-001-12-404	12	Socket	Coaxial	Yellow	Black	Yellow
M39029/27-405	852-001-12-405	12	Socket	Coaxial	Yellow	Black	Green
M39029/27-406	852-001-12-406	12	Socket	Coaxial	Yellow	Black	Blue
M39029/27-407	852-001-12-407	12	Socket	Coaxial	Yellow	Black	Violet
M39029/27-408	852-001-12-408	12	Socket	Coaxial	Yellow	Black	Gray
M39029/28-211	852-002-12-211	12	Pin	Coaxial	Red	Brown	Brown
M39029/28-409	852-002-12-409	12	Pin	Coaxial	Yellow	Black	White
M39029/28-410	852-002-12-410	12	Pin	Coaxial	Yellow	Brown	Black
M39029/28-411	852-002-12-411	12	Pin	Coaxial	Yellow	Brown	Brown
M39029/28-412	852-002-12-412	12	Pin	Coaxial	Yellow	Brown	Red
M39029/28-413	852-002-12-413	12	Pin	Coaxial	Yellow	Brown	Orange
M39029/28-414	852-002-12-414	12	Pin	Coaxial	Yellow	Brown	Yellow
M39029/28-415	852-002-12-415	12	Pin	Coaxial	Yellow	Brown	Green
M39029/59-366	852-006-08-366	08	Socket	Coaxial	Orange	Blue	Blue
M39029/60-367	852-007-08-367	08	Pin	Coaxial	Orange	Blue	Violet
M39029/75-416	852-003-12-416	12	Socket	Coaxial	Yellow	Brown	Blue
M39029/75-417	852-003-12-417	12	Socket	Coaxial	Yellow	Brown	Violet
M39029/75-418	852-003-12-418	12	Socket	Coaxial	Yellow	Brown	Gray
M39029/75-419	852-003-12-419	12	Socket	Coaxial	Yellow	Brown	White
M39029/75-420	852-003-12-420	12	Socket	Coaxial	Yellow	Red	Black
M39029/75-421	852-003-12-421	12	Socket	Coaxial	Yellow	Red	Brown
M39029/75-422	852-003-12-422	12	Socket	Coaxial	Yellow	Red	Red
M39029/75-423	852-003-12-423	12	Socket	Coaxial	Yellow	Red	Orange
M39029/76-424	852-008-16-424	16	Pin	Coaxial	Yellow	Red	Yellow
M39029/76-425	852-008-16-425	16	Pin	Coaxial	Yellow	Red	Green

BIN Color Coding									
0	1	2	3	4	5	6	7	8	9
BLACK	BROWN	RED	ORANGE	YELLOW	GREEN	BLUE	VIOLET	GREY	WHITE

Military Part Number	Glenair Part Number	Contact Size	Pin / Socket	Туре	C	BIN Color Stripin	g
M39029/76-426	852-008-16-426	16	Pin	Coaxial	Yellow	Red	Blue
M39029/76-427	852-008-16-427	16	Pin	Coaxial	Yellow	Red	Violet
M39029/77-428	852-009-16-428	16	Socket	Coaxial	Yellow	Red	Gray
M39029/77-429	852-009-16-429	16	Socket	Coaxial	Yellow	Red	White
M39029/77-430	852-009-16-430	16	Socket	Coaxial	Yellow	Orange	Black
M39029/77-431	852-009-16-431	16	Socket	Coaxial	Yellow	Orange	Brown
M39029/78-432	852-010-16-432	16	Socket	Coaxial	Yellow	Orange	Red
M39029/78-433	852-010-16-433	16	Socket	Coaxial	Yellow	Orange	Orange
M39029/78-434	852-010-16-434	16	Socket	Coaxial	Yellow	Orange	Yellow
M39029/78-435	852-010-16-435	16	Socket	Coaxial	Yellow	Orange	Green
M39029/90-529	853-001-08-529	8	Pin	Concentric Twinax	Green	Red	White
M39029/91-530	853-002-08-530	8	Socket	Concentric Twinax	Green	Orange	Black
M39029/102-558	852-004-12-558	12	Pin	Coaxial	Green	Green	Gray
M39029/103-559	852-005-12-559	12	Socket	Coaxial	Green	Green	White
M39029/113-625	853-003-08-625	8	Pin	Concentric Twinax	Blue	Red	Green
M39029/113-626	853-003-08-626	8	Pin	Concentric Twinax	Blue	Red	Blue
M39029/114-628	853-004-08-628	8	Socket	Concentric Twinax	Blue	Red	Gray
M39029/114-629	853-004-08-629	8	Socket	Concentric Twinax	Blue	Red	White
N/A	854-001-01	8	Pin	Quadrax		N/A	
N/A	854-001-02	8	Pin	Quadrax		N/A	
N/A	854-001-03	8	Pin	Quadrax		N/A	
N/A	854-001-04	8	Pin	Quadrax		N/A	
N/A	854-001-05	8	Pin	Quadrax		N/A	
N/A	854-002-01	8	Socket	Quadrax		N/A	
N/A	854-002-02	8	Socket	Quadrax		N/A	
N/A	854-002-03	8	Socket	Quadrax		N/A	
N/A	854-002-04	8	Socket	Quadrax		N/A	
N/A	854-002-05	8	Socket	Quadrax		N/A	

	BIN Color Coding								
0	1	2	3	4	5	6	7	8	9
BLACK	BROWN	RED	ORANGE	YELLOW	GREEN	BLUE	VIOLET	GREY	WHITE

Special Purpose Contacts Selected Examples

Size #12 Differential Twinax Contacts for Multi-Gigabit Data Rate Applications

Glenair Part No.	Cable	Impedence	Frequency Range	VSWR	Insertion Loss
Socket = 853-015-01 Pin = 853-016-01	859-041 963-001	100-Ohms Nominal	DC to 10 GHz	1.1 + (.03 * F GHz)	1.3 *F GHz



050-301 Size #8 Contact Cavity Optoelectronic Insert Transmitter and Receiver

- ARINC 664, 801, 803, 804, and 818 standard compliant
- Data rates from 125Mbps to 3.8 Gbps for transmitter, 125Mbps to 4.25Gbps for receiver
- Supports fast and Gigabit Ethernet, AFDX, 1x/2x Fibre Channel, DVI, HDMI, SFPDP, Serial Rapid I/O (sRIO).
- ARINC 801 1.25mm/2.5mm ceramic fiber ferrule, or expanded beam



Thermocouple Contacts to Fit D38999 Series I, II, III and IV Connectors



Glenair Part No.	Military Part No.	AWG Wire Size			
Pin = 850-023	Pin = AS39029/87				
Series I, III, IV Socket = 850-024	Series I, III, IV Socket = AS39029/88	16–28			
Series II Socket = 850-025	Series II Socket = AS39029/89				
Custom PCB and crimp termination thermocouples available in type K, E, J, N and more.					

Wire-to-Contact Expansion and Reducer Adapters

Glenair Part No.	Finish	Wire Accommodation	Contact Wire Barrel Size
687-348	Z2 - Gold Plate	6, 8, 10, 12, 14, 16, 18, 20, 22, 24, 0-4	4, 8, 12, 16, 20, 22
859-015	Z3 - Silver Plate Z4 - Tin Plate	10, 12, 14, 16, 18, 20, 22, 24, 26, 28	10, 12, 16, 20, 22



PCB Contacts to Fit MIL-DTL-38999/20 and /24 Rear-Release Connectors

Mating End Size	Glenair Part Number	
22	850-010-22	
20	850-010-20	
16	850-010-16	
12	850-010-12	



	Mating End Size	Glenair Part Number
	22	850-011-22
	20	850-011-20
-	16	850-011-16
	12	850-011-12

© 2012 Glenair, Inc. U.S. CAGE Code 06324 Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912 www.glenair.com A-6 E-Mail: sales@glenair.com

Special Purpose Contacts Selected Examples



High-Power and LouverBand Contacts



	High-Power Cont	acts
Contact Wire Accommodation		Glenair Part Number
8	8 AWG	850-013 (Socket) 850-014 (Pin)



High ampacity LouverBand contacts for use in Glenair Series 970 PowerTrip™ 850-026 (pin) 850-027 (skt)

High-Pressure Assemblies for Pure Gas Pneumatic/Hydraulic Applications



831-001 #12 Gas Tube Assembly for MIL-DTL-38999 Series I, III, and IV



Size #12 Pneumatic Contacts

Con land	Contact Type	For Use In	Part Number
11	Socket	D38999 Type Series I, III, IV	830-005
	Socket	D38999 Series II, Series 79 and Series 80	830-004 ¹
1	A CONTRACTOR OF THE PARTY OF TH		


3	Contact Type	For Use In	Part Number
13	Pin	D38999 Type, All Series , Series 80 and Series 79	830-003 ²
1	B	1. 830-004 supersedes 857-010 2. 830-003 supersedes 857-010	

Grommet Sealing Plugs



Fig.	Size	Color	Part Number	Military Part Number
1	#23	Black	809-155	(None)
2	#20	Red	859-012	MS27488-20-2
3	#16	Green	859-013	MS27488-16-2
4	#12	Orange	859-014	MS27488-12-2

All sizes available and in Same-Day stock. **Consult factory for more information**



Crimp Tool And Positioner For #12, #16 and #20 Power Contacts, Crimp Adapters



Crimp tool for use with size #20, #16 and #12 power pins. 9.75 inches OAL, 1.25 pounds. Use with M39029/57 and /58 contacts and 809-093

7 Positioner for use with 809-093 adapters.

> Positioner for use with size #20, #12 and #16 Power contacts.

Glenair offers a complete line of crimp tools in Same-Day stock.

Figure	Part Number	Military Part Number	Daniels Part Number
1	809-136	M22520/1-01	AF8
2	809-137	M22520/1-04	TH163
3	809-138	(none)	TH653

© 2012 Glenair, Inc. U.S. CAGE Code 06324 Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912 A-7 www.glenair.com E-Mail: sales@glenair.com

El Ochito™: The Ultimate Ethernet Contact "The Little Eight": Eight miniaturized contacts in a

"The Little Eight": Eight miniaturized contacts in a standard size #8 shielded module—10G Ethernet ready, with dramatic size and weight reduction compared to all other available solutions

- One full Ethernet channel per standard size #8 cavity
- Fast and easy crimp termination of wires to contacts—PC Tails available
- 100% drop-in solution to installed connectors—no redesign or reinstallation of interfaces
- Supplied as crimp contacts, wire pigtails, or in PC tail configurations in the connector of your choice—up to 8 Ochito modules in a size 25 D38999
- Integral spline and short termination maximizes interconnect/cable performance and minimizes crosstalk
- El Ochito™ delivers the highest density contact system available twice the density of Quadrax, split Quadrax, or other shielded contact solutions
- Tested, qualified, and in-stock for immediate shipment



El Ochito™ is a drop-in solution for Series 80 Mighty Mouse, as well as D38999 Series III, EN4165, EN3645, and other ARINC standards and is ideally suited for Ethernet, high-definition video, high-speed data loading, and other 1Gb/sec and 10Gb/sec applications.

El Ochito™ exploded view: High mating durability, lightweight

contact system with 100 Ohm

shielded performance. Note wire

twist maintained to contact pair to

minimize characteristic

impedance mismatch. Also, Conductive isolation shield

dramatically reduces crosstalk

El Ochito™: The Ultimate Ethernet Contact

Ochito






El Ochito™ utilizes Stinger™ contact technology. These small, durable, low mating force contacts provide El Ochito™ with optimized performance.

Pin Interface	So	ocket Interface	
Green/White	Brown/Whate Blue/White	hite Brown Green	
Orange/White Orange	C	Orange Orange/White	

Contact Perforn	nance Specifications
Temperature Range	-55°C to +175°C
Environmental Sealing	IAW connector specification
Corrosion Resistance	48 hours salt spray
Fire, Smoke and Toxicity	IAW FAR 25
EMI Shielding	360° shielding for each pair
Nominal Current	1 Amp
Contact Resistance	Max 60 milliohms
Wire	IAW TIA/EIA Cat 6A and ISO EA
Mating Cycles	> 500
DWV	500 VAC RMS sea level

Recommended wire-to-contact assignments



-40 -50 0 100 200 300 400

Near End Crosstalk · Cat 6a · 500 MHz

Return Loss · Cat 6a · 500 MHz


AEROSPACE-GRADE CAT 6a CABLE FOR OCHITO CONTACTS 963-003-26

CABLE PHYSICAL DATA


- Conductors: 26AWG stranded SPC
- Shield coverage: 80% (braid)
- Temperature: -55°C to +200°C
- Outer diameter: 0.220" (5.6mm)
- Minimum bend radius: 1.13" (28.7mm)
- Weight (lbs/100 ft): 3.05 (4.54 kg/100m)

CABLE CONSTRUCTION

- 1. White PTFE laser-printable jacket
- 2. Silver-plated copper shield
- 3. Fluoropolymer tape
- 4. PFA insulation
- 5. Fluoropolymer spline
- 6. Silver-plated copper conductors



A-9 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324



High-Performance Bulk Cable for Interconnect Applications

Rugged high-performance environmental and EMC interconnect cable designs—from chemically-resistant jacketed solutions to high-flexibility power transmission cable



Glenair is pleased to offer our customers custom bulk cable for onsite termination. Glenair cables are designed and manufactured for optimal performance in mission-critical applications such as soldier systems, medical equipment, aerospace, geophysical and other military and commercial environments that rely on guaranteed signal integrity and cable durability. Cable jacketing, braiding and shielding

technologies are specified according to application type, and the unique requirements of inner conductors including non-impedance-controlled signal wire, shielded multi-conductor cables, Coaxial, Quadrax, flexible power, fiber optic, and so on. Glenair cables are designed to optimize flexibility, weight reduction, ruggedness, and insulator quality. Our protocolspecific cables are offered with guidance as to shielding properties, impedance performance, attenuation, temperature rating, bend radius, weight, and maximum practical distance.



Coiled cable configurations for radio and comms applications are a Glenair specialty

SERIES 96

High-Performance Custom Bulk Cable for Interconnect Applications





Rugged environmental jacketing in a broad range of material types and colors

- **■** Extruded, blown-on and heat shrink iacketing for harsh application environments
- General purpose polyurethane
- **■** Low-smoke, zero halogen Duralectric[™]
- Chemically-resistant Viton®
- Industry standard neoprene
- Selected materials CBRN tested

High-performance cable and jacketing materials for every application requirement: Immersion, chemical or caustic fluid exposure, temperature extremes, and UV radiation.



	Custom Capabilities
TurboFlex	Highly flexible interconnect conductors and cables for power distribution applications
Duralectric	High-performance, flexible jacket material with outstanding resistance to environmental stress factors including heat, UV radiation and caustic chemicals
Multiconductor cables	Custom cables for unique applications such as robotics, defense electronics, and soldier systems
Overbraiding	Extensive range of conductive and non-conductive wire and fabric braid materials, including ultra-lightweight composites and micro-filaments



TurboFlex™ power distribution cables are constructed from highly flexible conductors and high-performance insulation to produce cables ideally suited for applications where flexibility, durability, and weight reduction are required. Amazingly durable and flexible especially in cold weather—the 16 AWG to 450 MCM TurboFlex cable features high strand count rope lay inner conductors made with copper-, tin-, nickel- and silver-plated copper. TurboFlex is jacketed with Glenair's unique Duralectric™

compound that provides outstanding flexibility Available in a broad range of gages, 16 AWG to 450 MCM

and resistance to environmental and caustic chemical exposure. Duralectric is also halogen-free, flame resistant and has a low smoke index, appropriate for interior applications. Long life and performance are critical in power distribution applications. TurboFlex, with its flexible conductors and durable jacket delivers both.



Glenair's vertically integrated connector, hardware and cable facilities are perfectly positioned to supply catalog and custom short cable runs for the broad range of interconnect applications.



In-stock and available for immediate, same-day shipment. No minimums!

A-10 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

© 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324



- One-stop shopping for general-purpose, high-speed, and protocol-specific/ specialty wire and cable
- No minimum orders. Glenair wire and cable part numbers are in stock and ready for immediate, same-day shipment
- M22759 single-ended data transmission wire, high-speed Quadrax cable, 50 and 75 Ohm Coaxial cable, as well as unique protocol-specific wire solutions
- Custom marking available

High availability, high-speed wire and cable for digital and RF applications—No minimum orders or minimum cable runs

Wire Type	Application	Commonly Used With
M22759 Single-Ended Data Transmission Wire	Non-impedance controlled signal applications	Non-shielded 39029 contacts
Quadrax Cable	10/100/1000BASE-T Ethernet applications	854-001/854-002 Quadrax contacts
Coaxial Cable	50 Ohm/75 Ohm RF transmission	Size #16, #12, #8 Coaxial pin and socket contacts
Protocol Specific Cables	Commercial digital data device connections including Ethernet, USB, SATA/eSATA, Spacewire, LVDS/CML	High Speed Mighty Mouse Mighty Mouse with Ultra-Twinax Differential Twinax contacts SuperSeal USB/RJ45

M22759 Hookup Wire
M22759/11 Silver Coated Copper Wire with Extruded PTFE Insulation
W22759/16 Fin Coated Copper Wire with Extruded ETFE Insulation
W22759/18 Tin Coated Copper Wire with Thin-Wall Extruded ETFE Insulation
W22759/32 Fin Coated Copper Wire with Crosslinked, Modified ETFE Insulation
M22759/33 Silver Coated Copper Wire with Crosslinked, Modified ETFE Insulation
M22759/34 Fin Coated Copper Wire with Overall Braid and Extruded ETFE Insulation
M22759/44 Silver Coated Copper Wire with Crosslinked, Extruded ETFE Insulation
W22759/45 Nickel Coated Copper Wire with Crosslinked, Extruded ETFE Insulation
M22759/46 Nickel Coated High Strength Copper Wire with Crosslinked, Extruded ETFE Insulation
M22759/90 Nickel Coated High Strength Copper Wire with Double Layer Tape Wrap Insulation


963-019
100 Ohm Ethernet Cable with 22 AWG Conductors, FEP Jacket


963-020
100 Ohm Ethernet Cable with 24 AWG Conductors , FEP Jacket

963-021
100 Ohm Ethernet Cable with 26 AWG Conductors , FEP Jacket

963-022
100 Ohm Ethernet Cable with 24 AWG Conductors, FEP Jacket, Without PTFE Binder

963-023
100 Ohm Ethernet Cable with 24 AWG Conductors, ETFE Jacket









Series 80 Mighty Mouse SuperSeal USB

Series 88 SuperFly™

Series 80 Mighty Mouse

HiPer 55116 Audio Frequency Connectors

Series 811 Mighty Mouse HD

Series 15 "CB" Audio Connectors

Glenair.

For more information contact Glenair at **818-247-6000** or visit our website at www.glenair.com U.S. CAGE code 06324

© 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

Mighty Mouse Connectors and Cables





Series 80 Mighty Mouse: Half the size and weight of MIL-DTL-38999 with comparable ratings, features, and performance

The Series 80 Mighty Mouse Connector is designed for use in high-reliability, mission-critical applications—from commercial aerospace to soldier systems—that require robust environmental and EMC performance as well as reduced size and weight. The Series 80 Mighty Mouse connector offers comparable performance to MIL-DTL-38999 interconnects with up to 71% weight and 52% size savings for similar contact layouts. The industry-standard Mighty Mouse is a mature connector series with a proven range of catalog and custom configurations.

- 67 contact arrangements ranging from 1 – 130 contacts
- MIL-DTL-38999 caliber environmental, mechanical, and electrical performance
- Ultraminiature #23 contacts set on .076" centers
- Size #20, #20HD, #16, #12, #8 signal, power, fiber optic and shielded contacts
- Discrete connectors and turnkey cable assemblies



EMI/EMP filter-class connectors also available in every Mighty Mouse series

	Series	80 Mighty Mouse E	<i>nvironmental</i> Conn	ectors	
Series 800	Series 801	Series 802	Series 803	Series 804	Series 805
Light-Duty UNF Thread	Rugged Double-Start ACME Thread	3500 PSI AquaMouse	Fast-Mate Bayonet Coupling	Quick-Disconnect Push-Pull	Ratcheted Triple-Start

Series 80 Mighty Mouse <i>Hermetic</i> Receptacles								
Series 800	Series 801	Series 802	Series 803	Series 804	Series 805			
	A CONTRACTOR OF THE PARTY OF TH			acus de la constant d				
 Vitreous glass sealing 		•Solder-cup and PC tai		•Alloy 52 iron alloy contacts				
•1X10 ⁻⁷ cc/sec maximum	n helium leak rate	 304L stainless steel sh 	ells	 Solder-mount, square flange or jam nut 				

				Series	80 Mig	hty N	louse	Con	tact Arran	gements				
				C	ontact Q	uantit	у				Contact Arı	angement [,]	÷	
Co	ntact Size and C	urrent Rating	#23	#20	#20HD	#16	#12	#8	Series 800	Series 801	Series 802	Series 803	Series 804	Series 805
		et 5/20 und current nating							5-3	5-3	5-3	5-3	5-3	N/A
			4						6-4	6-4	6-4	6-4	6-4	8-4
			6 7						6-6 6-7	6-6 6-7	6-6 6-7	6-6	6-6 6-7	8-6 8-7
Cizo	#23 Contacts		10						7-10	7-10	7-10	6-7 7-10	7-10	9-10
			13						8-13	8-13	8-13	8-13	8-13	10-13
	p Max. Current 2-#28 AWG		19						9-19	9-19	9-19	9-19	9-19	11-19
#2	.Z-#20 AVVU		26						10-26	10-26	10-26	10-26	10-26	12-26
			31						N/A	11-31	N/A	N/A	11-31	13-31
75	0 VAC DWV		37 55						12-37 N/A	13-37 16-55	12-37 14-55	12-37 14-55	12-37 14-55	15-37 18-55
			85						N/A	17-85	15-85	N/A	N/A	19-85
			100						N/A	19-100	N/A	N/A	N/A	21-100
			130						N/A	21-130	21-130	N/A	N/A	23-130
		~			3				6-23	6-23	6-23	6-23	6-23	8-23
Size #	20HD Contacts				5 8				7-25 8-28	7-25 8-28	7-25 8-28	7-25 8-28	7-25 8-28	9-25 10-28
	np Max.Current				10				9-210	9-210	9-210	9-210	9-210	11-210
	:0-#24 AWG				20				12-220	13-220	12-220	12-220	12-220	15-220
"2					35				N/A	16-235	14-235	14-235	14-235	18-235
100	00 VAC DWV				41				N/A	17-241	15-241	N/A	N/A	19-241
10	OO VAC DWV				55				N/A	19-255	N/A	N/A	N/A	21-255
					69	1			N/A 6-1	21-269 6-1	21-269 6-1	N/A 6-1	N/A 6-1	23-269 8-1
						2			8-2	8-2	8-2	8-2	8-2	10-2
	#16 Contacts					4			9-4	9-4	9-4	9-4	9-4	11-4
	np Max. Current					5			10-5	10-5	10-5	10-5	10-5	12-5
#1	6-#20 AWG					7			12-7	13-7	12-7	12-7	12-7	15-7
						12			N/A	16-12	14-12	14-12	14-12	18-12
18	00 VAC DWV	0				14 19			N/A N/A	17-14 19-19	15-14 N/A	N/A N/A	N/A N/A	19-14 21-19
						22			N/A	21-22	21-22	N/A	N/A	23-22
۲٠.	#12 C						1		7-1	7-1	7-1	7-1	7-1	9-1
	#12 Contacts						2		10-2	10-2	10-2	10-2	10-2	12-2
	np Max. Current						2		12-2	13-2	12-2	12-2	12-2	15-2
#	12-#14 AWG						3 5		12-3 N/A	13-3 16-5	12-3 14-5	12-3 14-5	12-3 14-5	15-3 18-5
							7		N/A	17-7	15-7	N/A	N/A	19-7
18	00 VAC DWV						12		N/A	21-12	21-12	N/A	N/A	23-12
Size	#8 Contacts							1	N/A	8-1	N/A	N/A	N/A	10-1
	np Max. Current							2	N/A	16-2	N/A	N/A	N/A	18-2
107111	#8 AWG							3	N/A	17-3	N/A	N/A	N/A	19-3
19	00 VAC DWV							4 5	N/A N/A	19-4 21-5	N/A N/A	N/A N/A	N/A N/A	21-4 23-5
	OU VAC DVV V	1	12				1)	10-200	10-200	10-200	10-200	10-200	12-200
en	Ci=0 #22	d #12 Cantacta	4				2		10-201	10-201	10-201	10-201	10-201	12-201
ngements : DWV	312e #23 an	d #12 Contacts	6				2		12-200	13-200	12-200	12-200	12-200	15-200
			10			_	2		12-201	13-201	12-201	12-201	12-201	15-201
Combo Arraı 750 VAC	Size #23 an	d #16 Contacts	8			2			9-200 10-202	9-200 10-202	9-200 10-202	9-200 10-202	9-200 10-202	11-200 12-202
age 55			4	2					8-200	8-200	8-200	8-200	8-200	10-200
<u> </u>	Size #23 an	d #20 Contacts	8	2					9-201	9-201	9-201	9-201	9-201	11-201
			20			2			12-202	13-202	12-202	12-202	12-202	15-202
	<u> </u>	1.114.6.6.1.1	12			4			12-203	13-203	12-203	12-203	12-203	15-203
	Size #23 an	d #16 Contacts	40			2			N/A	16-204	14-204	14-204	14-204	18-204
£ t			32 40			4			N/A N/A	16-205 17-203	14-205 15-203	14-205 N/A	14-205 N/A	18-205 19-203
Je Z			12			7	2		12-204	13-204	12-204	12-204	12-204	15-204
e de la composition della comp			4				4		12-205	13-205	12-205	12-205	12-205	15-205
Combo Arrangements 1300 VAC DWV	Size #23 an	d #12 Contacts	34				2		N/A	16-206	14-206	14-206	14-206	18-206
300 A			20				4		N/A	16-207	14-207	14-207	14-207	18-207
₩ (F)			28 32				4	1	N/A N/A	17-204 16-208	15-204 N/A	15-204 N/A	15-204 N/A	19-204 18-208
3			40					1	N/A N/A	17-205	N/A N/A	N/A N/A	N/A N/A	19-205
	Size #23 ar	nd #8 Contacts	44					2	N/A	19-201	N/A	N/A	N/A	21-201
			12 28					4	N/A	19-202	N/A	N/A	N/A	21-202
								4	N/A	21-200	N/A	N/A	N/A	23-200

^{*} DWV rating is applicable to contact arrangements shown.

SERIES 80

and Cables

Mighty Mouse Connectors

DWV rating is applicable to contact arrangements snow



LOCKING PUSH-PULL CONNECTORS

ntroducing the new Mighty Mouse Series 824 Locking Push-Pull Connector: all the familiar size, weight and performance advantages of the industry-standard Mighty Mouse 804 pushpull connector with a revolutionary low-profile locking coupling mechanism. Glenair's primary design goal in the development of the locking 824 was to bring mil-spec caliber connector performance to locking push-pull applications. The Series 824 Locking Push-Pull provides superior sealing, excellent EMI protection, low-profile ergonomic mating and demating, and easy crimp contact termination. The locking push-pull mechanism delivers visual, tactile, and audible mating confirmation under even the most extreme field conditions. Built for longterm durability and reduced size and weight, the high-density Series 824 Locking Push-Pull connector far surpasses commercial caliber push-pull connectors.

Specifications					
Current Rating	#23 5 AMPS, #16 13 A., #12 23 A.				
Dielectric Withstanding Voltage	#23 500 VAC RMS, #12 and #16 1800 VAC RMS				
Insulation Resistance	5000 megohms minimum				
Operating Temperature	-65° C to +150° C				
Shock / Vibration	100 g / 16 g				
Shell-to-Shell Resistance, Nickel Plated	2 milliohms maximum				
Durability	500 mating cycles				
Breakaway Force	50 pounds minimum				

Gold plated crimp contacts for #12 to #30 AWG wire





For more information contact Glenair at 818-247-6000 or visit our website at www.glenair.com

• Fast mating, quick-release

coupling mechanism

31 insert arrangements


Integrated cable shield

termination platform

SERIES 824

Mighty Mouse

LOCKING PUSH-PULL CONNECTORS




	How To Order Series 824 Locking Pu	sh-Pull Receptacle					
Sample Part Number		824-003	-01	M	8-1	P	
Product Series	3 /	824-003 Mighty Mouse Locking Push-Pull cable eceptacle with integrated shield termination platform					
Shell Style	-01 - In-Line -07 - Rear-Panel Jam Nut Mount -00 - Front-Panel Jam Nut Mount						
Shell Material/Finish	See Table II						
Shell Size/Contact Arrangement	See Table I	See Table I					
Contact Type	Connector supplied with contacts: P - Pin S - Socket Connector supplied without contact A - Pin B - Socket					cts:	
Shell Key Position	Omit for single polarizing key. A (norma	Omit for single polarizing key. A (normal), B, C, D, E, F polarizing options per Table I					

Position A° B°							
Α	150°	210°					
В	45°	210°					
С	230°						
D	315°						
E	315°						
B° A° 315°							

Table III: Alternate Key Positions

Ta	ble II: Material and Finish					
М	Aluminum/Electroless Nickel RoHS Compliant					
NF	Aluminum/Cadmium with Olive Drab Chromate					
ZR	Aluminum/Zinc-Nickel with Non-Reflective Black Chromate RoHS Compliant					
МТ	Aluminum/Nickel-PTFE RoHS Compliant					
Z 1	Stainless Steel/Passivated RoHS Compliant					



MATERIAL/FINISH

Barrel: Copper Alloy Shell/Release Sleeve: Aluminum Alloy or CRES Insulators: Liquid Crystal Polymer Interfacial Seal, O-Ring, Grommet: Fluorosilicone Contacts: Copper Alloy/Gold over Nickel Plating Spring: CRES/Gold Plated



2

6

12-200

For more information contact Glenair at **818-247-6000** or visit our website at www.glenair.com



Innovative shielded low profile right angle connector plug and backshell assemblies reduce clearance requirements without compromising ruggedness or shielding performance. Available in Series 801 double-start, Series 804 QDC push-pull, and Series 805 triple-start, Cobra assemblies provide optimal low-profile cable routing and legendary Mighty Mouse connector performance in a single package. Each Cobra assembly is equipped with a removable rear cover and gasket for easy crimp or solder contact termination of the connector. Integrated low-profile backshell is equipped with an EMI/RFI shield termination platform and a shrink boot lip. The ultra-lightweight assembly may be clocked in eight different angle orientations for additional flexibility in cable routing. Connectors are equipped with polarization keying to prevent mismating. Glenair Mighty Mouse Cobra mates with available square flange and jam nut receptacles from each respective connector series. Fourteen contact arrangements are available, all with Size #23 contacts from shell size 5 to shell size 21 with 3-130 contacts respectively. Connector shells are aluminum alloy or stainless steel.

SPECIFICATIONS

- Current Rating: #23 5 Amps
- Test Voltage (DWV) #23: 500 VAC Sea Level
- Insulation Resistance: 5000 megohms minimum
- Contact Resistance: 73 millivolt drop at 5 Amp test current
- Mating Cycles Series 801 and 804: 2000; Series 805: 500
- Operating Temperature: -55° C to +150° C
- Shielding Effectiveness: 50 dB min from 100MHz to 1000MHz.
- Magnetic Permeability: 2.0µ
- Vibration: 37g / Shock: 300g
- Immersion, mated: 1meter water immersion for 1 hour

- Space-saving design features one-piece machined and brazed connector shell and right angle backshell for minimum height and optimal EMI performance.
- Master key clocking enables easy cable entry/ exit routing in eight angles
- Removable rear cover and gasket provides easy access to end of connector for crimp or solder contact termination

MIGHTY MOUSE Low-Profile Cobra Plug Connectors



How To Order Mighty Mouse Cobra Plug Connector and Backshell Assemblies								
Sample Part Number	801-069-26	801-069-26 ZNU			Α	1	05	
Connector Series and	801-069-26 Double-Start self-locking plug with ratchet mechanism (the clicker)							
Mighty Mouse Cobra	804-066-06 QDC Push-Pull plug							
Basic Part Number	805-061-16 Triple-Start plug with ratcheting anti-decoupling mechanism							
Material/Finish	M = Aluminum / Electroless Nickel RoHS Compliant NF = Aluminum / Cadmium with Olive Drab Chromate ZNU = Aluminum / Zinc-Nickel with Black Chromate MT = Aluminum / Nickel-PTFE RoHS Compliant Z1 = Stainless Steel / Passivated RoHS Compliant							
Shell Size - Contact Arrangement	See Table V - A: 801-069 B: 804-066 C: 805-061							
Contact Style	A = Pin, Solder B = Socket, Solder P = Pin, Crimp S = Socket, Crimp							
Polarization Key Position	A, B, C, D, E, F - See Table II							
Cable Exit Direction	1, 2, 3, 4, 5, 6, 7, 8 - See Table I							
Cable Entry Size	See Table VI						-	

	ØC J

Table I: Cable Exit Direction							
Cable Exit		C°-≠					
Direction	C°	Master					
Code		Key					
1	0°	\\(\tau\)					
2	45°						
3	90°						
4	135°						
5	180°						
6	225°						
7	270°	Cable Exit Direction					
8	315°	(Direction 2 Shown)					

MATERIALS/FINISH

- Contacts: Copper alloy, gold plated
- Backshell Housing, Connector Shell, Coupling Nut and Lid: Aluminum or Stainless Steel
- Backshell Sealing Gasket and Interfacial Seal: Fluorosilicone
- Screws: 300 Series Stainless Steel
- Insulator: LCP

	Table II: Key Positions								
	Α°	В°							
Α	150°	210°							
В	75°	210°							
C	95°	230°	B° A° (((()						
D	140°	275°							
E	75°	275°							
F	95°	210°							

		MINICE EITH				
Code	Entry Size	Code	Entry Size			
02	.125	10	.625			
03	.188 11	.688				
04	.250	12	.750			
05	.313	13*	.813			
06	.375	14*	.875			
07	.438	15*	.938			
08	.500	16*	1.000			
09	.563	17*	1.063			
* Entry codes 13-17 not available for Series 804 Cobra						

Table VI - Cable Entry

Table V - Shell Size/Contact Arrangements								
	A: 801-069			B: 804-066	: 804-066 C: 805-061			
Shell Size	Contact Arr.	Max Entry	Shell Size	Contact Arr.	Max Entry	Shell Size	Contact Arr.	Max Entry
5	5-3	03	5	5-3	03	8	8-4, 8-6, 8-7	04
6	6-4, 6-6, 6-7	04	6	6-4, 6-6, 6-7	04	9	9-10	05
7	7-10	05	7	7-10	05	10	10-13	06
8	8-13	06	8	8-13	06	11	11-19	07
9	9-19	07	9	9-19	07	12	12-26	08
10	10-26	08	10	10-26	08	13	13-31	09
11	11-31	09	12	12-37	10	15	15-37	10
13	13-37	10	14	14-55	12	18	18-55	12
16	16-55	12				19	19-85	13
17	17-85	13				21	21-100	15
19	19-100	15				23	23-130	17
21	21-130	17						

NOTES

- Rear insulator grommet not supplied.
- Cobra plugs mate with respective series receptacles with same layout, polarization and opposite contact gender.
- Hand crimp tool: P/N 809-015.
 Positioner for hand tool: P/N 809-005.
 Insertion/extraction tool P/N 809-088.
- Crimp barrel accommodates 22, 24, 26 and 28 gage wire.
- All Cobra plugs equipped with Size #23 contacts.

l-6 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

Fluropolymer PFA Insulators • Ultra-Twinax Size #8 Quadrax/Twinax • Size #8 El Ochito®

Mighty Mouse High-Speed and Ultra-Twinax connectors: rugged environmental sealing and high-speed matched impedance electrical performance in an ultraminiature package



Combine Mighty Mouse with—or even eliminate—low-performance commercial high-speed connectors Glenair Series 80 Mighty Mouse connectors are the new industry standard for highperformance ultraminiature connectors. Now Glenair expands the Mighty Mouse line to include connectors optimized for high-speed matched impedance performance. The Mighty Mouse High-Speed product line features Fluoropolymer insulators for superior electrical performance in protocol-specific applications such as eSATA and USB 2.0/3.0.

Mighty Mouse Ultra-Twinax connectors utilize size #12 Twinax contacts for ultra-high speed differential pair applications such as LVDS and CML.

MIGHTY MOUSE HIGH-SPEED



Series 80 Mighty Mouse High Speed **Connectors with Fluoropolymer PFA** Insulators

- For high-speed protocols: eSATA, 10GBASE-T, USB 2.0 / 3.0
- Fluoropolymer PFA insulators for superior insertion loss and balanced impedance
- Series 801 double-start ACME thread and Series 804 push-pull quick disconnect connectors available
- Discrete components or overmolded cordsets

MIGHTY MOUSE ULTRA-TWINAX



Series 80 Mighty Mouse Ultra-Twinax Connectors with Size #12 Twinax contacts

- For ultra high-speed differential pair applications: LVDS, CML
- Size #12 Twinax and hybrid contact arrangements
- Series 801 double-start ACME thread connectors
- Discrete components or overmolded cordsets
- **■** Frequency range from DC to 10GHz

MIGHTY MOUSE WITH SIZE #8 QUADRAX, EL OCHITO® AND DIFFERENTIAL TWINAX CONTACTS



Series 805 Mighty Mouse plug with size 8 Quadrax contacts

- Differential Twinax contacts for 100 Ohm serial data transmission
- Quadrax contacts for 100BASE-T Ethernet
- Arrangements for 1, 2, 3, 4 or 5 snap-in, rear-release contacts
- Lightweight, low profile
- Comprehensive range of assembly tooling
- Available for Series 801 (double-start) and 805 (triple-start) Mighty Mouse connectors
- El Ochito®: the ultimate ethernet contact


SERIES 80

High-Speed Mighty Mouse Connectors and Cables



Fluoropolymer PFA Insulators • Ultra-Twinax Size #8 Quadrax/Twinax • Size #8 El Ochito®

This table compares contact and wire spacing and bandwidth performance in miniaturized interconnect applications. As contact density increases, the performance of the interconnect improves. Note the position of the High-Speed and Size #8 Mighty Mouse compared to standard Mighty Mouse, and the position of the Ultra-Twinax Mighty Mouse with performance up to 10 GHz. The density of the Ultra-Twinax contacts is measured between the two components in each contact—so although the #12 contact is larger overall, the effective contact density is higher.







Shell Size 6

4 Size #23 Contacts


Shell Size 7 10 Size #23 Contacts

Shell Size 9

19 Size #23 Contacts

Shell Size 10 26 Size #23 Contacts

Mighty Mouse Ultra Twinax Size #12 Differential Twinax Contact Arrangements (Mating Face/Pin Connector)



Shell Size 7 1 Size #12 Twinax Contact

Mating Face

Series 801

Series 805

Shell Size 10 2 Size #12 Twinax

Shell Size 16

5 Size #12 Twinax

Shell Size 6

7 Size #23 Contacts

Shell Size 17 7 Size #12 Twinax

Shell Size 21 12 Size #12 Twinax Contacts

Shell Size 10 2 Size #12 Twinax

1 Size #12 Twinax 4 Size #23 Contacts 12 Size #23 Contacts

Shell Size 10

Mighty Mouse #8 Quadrax / Differential Twinax, and El Ochito® Contact Arrangements

Shell Size 8 1 Size # 8 Contact Shell Size 10

Shell Size 10 2 Size #8 Contacts Shell Size 18 2 Size #8 Contacts

Shell Size 17 3 Size #8 Contacts Shell Size 19 3 Size #8 Contacts



Shell Size 19 4 Size #8 Contacts Shell Size 21 4 Size #8 Contacts



Shell Size 21 5 Size #8 Contacts Shell Size 23 5 Size #8 Contacts

© 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

SERIES 811 Mighty Mouse High Density (HD) **Connectors and Cables**






■ High Density Micro TwistPin Contacts set on .050" centers deliver over twice the density of standard Series 80 **Mighty Mouse**


- 7 to 42 Contacts
- Water Resistant to 1 meter
- Double-start ACME threaded coupling


High Performance TwistPin Contacts

811-001-06ME9-42SA Series 811 Plug



Mighty Mouse high density (HD) connector delivers twice the size and weight savings compared to standard Mighty Mouse





The 811 HD Difference: Micro TwistPin Contacts

Widely used for radars, missiles, avionics, and space vehicles, the Micro TwistPin is a spring pin composed of helically wound strands of copper alloy wire, welded into a bundle, then "bulged" and crimped to a copper alloy sleeve. These gold over nickel plated pins and sockets offer low, stable contact resistance even when subjected to temperature extremes and vibration. Designers of soldier systems and other military electronics, medical and highend industrial equipment have all turned to the TwistPin contact in order to reduce the size and weight of high-performance systems.

	Specifications
Current Rating	3 AMPS
Dielectric Withstanding Voltage	600 VAC sea level, 150 VAC at 70,000 ft.
Insulation Resistance	5000 megohms minimum
Operating Temperature	-65° C. to +150° C.
Contact Resistance	8 milliohms maximum
Water Immersion, Mated	MIL-STD-810G, Method 512.5 1 meter for 1 hour
Water Ingress, Mated	Ingress protection 67
Shock	300 g's (MIL-DTL-38999 para. 4.5.21.1)
Vibration, Sine	60 g's (MIL-DTL-38999 para. 4.5.23.2.1)
Vibration, Random	23 g's (MIL-DTL-38999 para. 4.4.23.1)
Altitude-Low Temperature	EIA-364-105
Durability	2000 cycles of mating
Magnetic Permeability	2 μ maximum
Shielding Effectiveness	55 dB minimum from 100MHz to 1000MHz.

TwistPin Contact



TwistPin



Socket

Protective Covers



SERIES 811 MIGHTY MOUSE HD: PRE-WIRED CONNECTORS







In-Line Receptacles 811-003-01



Square-Flange Receptacles 811-003-02 with banding porch 811-004-02 low-profile



Jam Nut Receptacles 811-003-07 with banding porch 811-004-07 low-profile

SERIES 811 MIGHTY MOUSE HD: PC TAIL CONNECTORS



Square Flange Receptacles 811-005-02 splash-proof 811-006-02 immersion-proof



Jam Nut Receptacles 811-005-07 splash-proof 811-006-07 immersion-proof



Also Available: **Overmolded Cordsets**

ULTRAMINIATURE SERIES 80 USB SuperSeal[™] Small **Form-Factor Connectors**











Crimp contact micro-USB connectors with outstanding environmental performance and EMI/RFI grounding. Smallest form-factor highperformance solution for integration of the commercial USB interface

- Significant size and weight reduction compared to MIL-DTL-38999 type USB/ **RJ45 solutions**
- Rear-release crimp contact termination as well as USB/RJ45 jumper accommodation
- Superior sealing, IP67, in unmated condition compared to other available environmental circulars
- Superior grounding for electrostatic discharge and EMC
- Superior cable shield termination with integrated banding platform
- Optional spring-loaded protective covers for environmental protection of junction boxes and switches
- Wide range of high speed Ethernet/ network protocols supported, including **USB 2.0**

Test Description	Mighty Mouse USB Performance Requirements/Specifications	Procedure Per MIL-DTL-38999 or Other Standard
Dielectric withstanding voltage	Maximum leakage current = 2 milliamperes No evidence of electric breakdown or flashover	4.5.11.1 or 4.5.11.2 IAW EIA-364-20, Method A
Insulation resistance	At ambient temperature: >5000 megohms between any pair of contacts and between any contact and the shell. after altitude immersion = 1000 megohms min. after humidity = 100 megohms min. At elevated temperature: >1000 megohms	
Contact resistance	Terminal-to-terminal resistance of vd connector contacts shall not exceed 0.050 ohms.	4.5.14
Mating durability	500-1000 cycles depending on plating, with no mechanical damage. Dielectric, contact resistance and air pressure requirements as described above shall be met after 500-1000 mating cycles.	4.5.8
Contact retention	Individual contacts capable of withstanding at least 10 pounds axial load applied uniformly at one pound per second.	IAW EIA-364-29
Vibration and Shock	37 g's random vibration, 300 g's shock. No electrical discontinuity, no disengagement of mated connectors, backing off of the coupling mechanism, or evidence of cracking, breaking, or loosening.	4.5.23
Temperature cycling	-65°C to 175°C or 200°, depending on finish. No blistering, peeling or separation of plating or other damage detrimental to the operation of the connector.	4.5.4 EIA364-32, Test cond. A
Salt spray	5% solution, 34°–36°C. 48–1000 hours, depending on finish. Unmated connectors show no lifting of plated coating or exposure of basis material under 3X magnification which adversely affects performance.	4.5.13 EIA-364-26
Humidity	Cycle wired, mated connectors between 25 °C at 80 % and 65 °C at 50 %. Ramp time = 0.5 hour, dwell = 1.0 hour. 24 cycles.	4.5.26 EIA364-31, Method IV
Water immersion	1 Meter for 1 Hour, mated.	MIL-STD-810 Method 512
EMI Shielding	Series 801: Good • Series 804: Very Good • Series 805: Excellent	4.5.28 EIA-364-66

ULTRAMINIATURE SERIES 80 USB SuperSeal[™] Small Form-Factor Connectors



SUPERSEAL™ MIGHTY MOUSE MICRO-B USB CONNECTOR SELECTOR



Series 801 Plug Connector with Micro-B USB



Series 801 In-Line Receptacle



Square Flange Mount Receptacle



Series 801 Rear Panel Jam Nut Mount Receptacle



Series 804 Plug Connector with Micro-B USB



Series 804 In-Line Receptacle



Series 804 **Rear Panel Jam Nut Mount** Receptacle



Series 804 Front Panel Jam Nut Mount Receptacle




Plug-and-Play Micro-USB Plug and Receptacle

Plug-and-Play Micro-USB **Booted Cordset**



Spring-Loaded cover for Series 804 Jam Nut Receptacles

Crimp Contact Pin Layout



Pin Number	USB Designation	Typical Wiring Assignment
1	VBUS	Red
2	D-	White
3	D+	Green
4	ID	RA_PLUG_ID
5	GND	Black
Shell	SHIELD	DRAIN WIRE

MATERIAL AND FINISHES

- Shell/coupling: High strength aluminum alloy
- Plating: Cadmium olive drab over electroless nickel; Nickel PTFE; Electroless
- · Contacts: Copper alloy, gold plated
- USB insulator: LCP
- Seals: Silicon-based elastomer
- Stainless steel and other materials and finishes available. Please consult factory.

MICRO USB ELECTRICAL SPECIFICATIONS

- Voltage Rating: 30 VAC (rms)
- Current Rating: Signal pins 1.0A, Power pins 1.8A
- D.W.V.: 600 VAC
- · Shield Continuity: Continous through coupler or continous coupler to shell



The ultimate high-performance connector series: ready for the toughest (and smallest!) applications you've got

Glenair Series 88 SuperFly® represents a perfect storm of high-performance contacts, shells, wires, termination and mating technologies. SuperFly® is the only connector series in existence that combines the weight-saving and performance advantages of nanominiature, microminiature and AS39029 type (size #23) contacts in a precision package made to order for battlefield and other high-performance applications. Available in factory-terminated cordsets, single-ended pigtails, and discrete PCB termination receptacles for complete flexibility in cable and box configurations. SuperFly cordsets ship with ultra-flexible, highspeed GhostWire[™] cabling, your choice of threaded or quick disconnect coupling and a widerange of contact arrangements from 3-44 contacts. PCB receptacles are available in straight and right-angle configurations.



Rear-panel mount push-pull and threaded PCB receptacles now available

SUPPORTED CONTACTS



#23 AS39029 Type 5 Amp Crimp Contact



#24 Micro-D 3 Amp TwistPin




#30 Nano-D Amp TwistPin Contact

SERIES 88 SuperFly® Ultraminiature Connectors and Cordsets



ULTRAMINIATURE SUPERFLY® CORDSETS AND PIGTAILS





- IP67 immersion rated
- High-reliability contacts: 5 Amp, 3 Amp, and 1 Amp
- High shock and vibration
- Robust EMI shielding
- Designed for high speed data applications





Threaded pigtail plug and receptacle





Quick-disconnect pigtail plug and jam nut receptacle

- Pre-wired, epoxy-sealed cordsets
- Straight and right-angle PC tail receptacles
- 21 Contact arrangements
- Front or rear panel mounting
- Aluminum or stainless steel
- Accepts #22 to #32 AWG wire

SuperFly® Layouts Arranged by Protocol						
Layout	Protocol(s)	Layout	Protocol(s)	Layout	Protocol(s)	
B-7N	eSATA/SATA	E-4M4N	Ethernet PoE	H-6W14N	HDMI (3 extra)	
C-10N	USB 3.0 (low power) Ethernet	F-22N	HDMI (3 extra) DisplayPort (2 extra)	J-44N		
C-2M2N	USB	F-4W4N	Ethernet PoE	J-7W19N	HDMI (7 extra) Camera Link	
D-3M		G-7W	eSATA/SATA	K-19M	HDMI	
D-2W2N	USB	G-10M	USB 3.0 Ethernet (2 extra)	K-13M19N	HDMI (13 extra)	
E-3W		H-10W	USB 3.0 Ethernet (2 extra)	L-22M	HDMI (3 extra) DisplayPort (2 extra)	
E-19N	HDMI	H-37N				

	Contact Arrangements									
5 A	MP	COM 5 AMP 8	MBO & 1AMP	3 A	MP		ИВО & 1 AMP		1 AMP	
	000	00	0000	0		00				0000
E3W (3) 5A	G7W (7) 5A	D2W2N (2) 5A, (2) 1A	F4W4N (4) 5A, (4) 1A	D3M (3) 3A	G10M (10) 3A	C2M2N (2) 3A, (2) 1A	E4M4N (4) 3A, (4) 1A	B7N (7) 1A	C10N (10) 1A	E19N (19) 1A
				••••	••••				00000	000000
	0W) 5A	H6W14N (6) 5A, (14) 1A	J7W19N (7) 5A, (19) 1A	K19M (19) 3A	L22M (22) 3A	G6M10N (6) 3A, (10) 1A	K13M19N (13) 3A, (19) 1A	F22N (22) 1A	H37N (37) 1A	J44N (44) 1A



SERIES 152 • MIL-DTL-55116 TYPE

HiPer 55116 Audio Frequency Connectors

Series 152 HiPer 55116 connectors offer significant performance advantages for modern soldier communication systems



Fully intermateable and interoperable with

- Intermateable and interoperable with standard MIL-DTL-55116 connectors
- Low contact resistance: less than 10 milliohms
- Integrated EMI ground spring provides improved 2.5 milliohm shell-to-shell conductivity performance
- IP68 rated sealing in mated and unmated condition, prevents water ingress into radio equipment
- 1,000 hour+ salt spray corrosion resistance
- Integrated cable shield termination band porch
- Superior 100 pound cable pull test rating

SERIES 152 HIGH PERFORMANCE
MIL-DTL-55116 Type High-Performance
Audio Frequency Connectors



	S	Series 152 HiPer 55116	Selection Guide	
Part Description		Glenair P/N	Equivalent Mil P/N, "U" designator	Mates with
	Audio plug, field serviceable, with wire strain relief and rigid contacts	152-001	M55116/1 – /4 type	152-003 HiPer 55116 type jam nut receptacle 152-004 HiPer 55116 type in-line receptacle
	Overmolded audio plug cordset with wire strain relief	152-006	U-229	151-003 standard 55116 type jam nut receptacle 151-004 standard 55116 type in-line receptacle any M55116 receptacle
	Audio plug with shield termination porch, overmolding adapter and rigid contacts	152-002	M55116/5 – /8 type	152-003 HiPer 55116 type jam nut receptacle 152-004 HiPer 55116 type in-line receptacle
	Overmolded audio plug cordset	152-005	U-229	151-003 standard 55116 type jam nut receptacle 151-004 standard 55116 type in-line receptacle any M55116 receptacle
	In-line receptacle with shield termination porch, overmolding adapter, and non-rigid spring contacts	152-004	M55116/5 – /8 type	152-003 HiPer 55116 type jam nut receptacle 152-004 HiPer 55116 type in-line receptacle 151-003 standard 55116 type jam nut receptacle
	Overmolded in-line receptacle cordset	152-007	U-229	151-004 standard 55116 type in-line receptacle any M55116 receptacle
	Radio-mount jam nut receptacle with non- rigid spring contacts	152-003	M55116/9 – /10 type U-183	152-001 HiPer 55116 type plug 152-002 HiPer 55116 type plug 151-001 standard 55116 type plug 151-002 standard 55116 type plug any M55116 plug

Series 152 HiPer 55116 Performance Specifications					
Complies with all MIL-DTL-55116 specifications and exceeds the following performance criteria:					
Shell-to-shell conductivity	152-001 and -002 Plugs: 2.5 milliohms max. 152-003 receptacle: 2.5 milliohms max when mated to Glenair HiPer 55116 plug 152-001 or -002				
Cable shield-to-shell conductivity 2.5 milliohms max.					
Contact resistance (mated)	15 milliohms max. average; 20 milliohms max.				
Water immersion (mated & un-mated)	152-002 plug, 152-003 receptacle: IP68 (10 meters of standing water for 1 hour)				
Air Pressure	15 psi				
Salt spray	1,000 hours (MIL-STD-202, Method 101E)				
Cable pull-out force (unmated) 152-001 and -002 plugs: 100 lbs. (Cable shield strength dependent)					
All other performance characteristics of Serie	es 152 HiPer 55116 connectors are compliant with MIL-DTL-55116 (see table on Page 11 for specifications)				

B-16 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

MIL-DTL-55116 Type **Audio Frequency Connectors**





High reliability performance for mission-critical communication systems

The MIL-DTL-55116 audio frequency connector has been used in tactical radio systems for generations. Now, this reliable, field-cleanable interconnect has been specified for use in the Joint Tactical Radio System—the next generation voice and data radio for U.S. military field operations, ensuring its continued use and service to soldiers, sailors and airmen. The Glenair MIL-DTL-55116 Type connector is manufactured in our Glendale, California factory with materials and processes guaranteed to result in the best performing and most reliable connector system available. Best of all, these products—from crimp and solder termination cable plugs, to ruggedized and sealed receptacles are in-stock and available for immediate, same-day shipment.

Series 151 standard version offers performance IAW MIL-DTL-55116							
Test Description	Procedure Per MIL-DTL-55116	Test Description	Procedure Per MIL-DTL-55116 Or Other Standard				
Dielectric withstanding voltage	4.7.1	Pull test	4.8.7				
Insulation resistance	4.7.2	Bounce	4.9.1				
Contact resistance	4.7.3	Vibration	4.9.2 and MIL-STD-202G, method 201A				
Contact depression	4.8.1	Drop	4.9.3				
Air pressure	4.8.2	Temperature cycling	MIL-STD-202, method 107, test condition A				
Mating durability	4.8.3	Salt spray	MIL-STD-202, method 101E, test condition B				
Contact retention	4.8.4	Humidity	4.9.6 and EIA-364-31, method IV (step 7a not required)				
Compression	4.8.6	Water immersion	4.9.7				

4.8.6	Water immersion	4.9.7			
151 Standard MIL-DTL-551	16 Type Audio Connectors -	Product Selection Guide			
151-001 Standard MIL-DTL-55116 type audio plug, field-servicable with wire strain relief and rigid contacts					
151-002 Standard MIL-DTL-55116 type audio plug with overmold adapter and rigid contacts					
151-003 Standard MIL-DTL-55116 type radio-mount Jam Nut receptacle with non-rigid spring contacts					
151-004 Standard MIL-DTL-55116 type in-line receptacle with wire strain relief and non-rigid spring contacts					
667-374 Protective Cover for 151 Series Plugs					
667-355 Protective Cover for 151 Series Receptacles					
	151-001 Standard M strain relief and rigid 151-002 Standard M rigid contacts 151-003 Standard M non-rigid spring cor 151-004 Standard M wire strain relief and	strain relief and rigid contacts 151-002 Standard MIL-DTL-55116 type aurigid contacts 151-003 Standard MIL-DTL-55116 type race non-rigid spring contacts 151-004 Standard MIL-DTL-55116 type inwire strain relief and non-rigid spring contacts 667-374 Protective Cover for 151 Series PI			



Series CB

Cable Plug

SERIES 15

CB Series Pogo Pin

Audio Connectors



Series CB Jam Nut Receptacle


- Qualified to VG95351 (seven pole) and VG96934 (ten pole)
- Ultraminiature version of U.S. standard 55116 audio frequency connectors
- Robust environmental, mechanical and EMI performance
- High durability—5000 mating cycles


The compact audio frequency bayonet connector with spring-loaded contacts— VG qualified!

CB Series Specifications				
Current rating	2.5 Amps per contact maximum			
Voltage rating (DWV)	500 VAC			
Insulation resistance	5000 ΜΩ			
Durability	5000 cycles of mating, minimum			
Contact resistance	5 mΩ			
Water ingress protection	IP68			
Water immersion	2 meters, 48 hours			
Air pressure	0.4 bar			
Operating temperature	-55° C to +85° C			
Shielding effectiveness	50 dB attenuation up to 100 MHz			
Corrosion resistance (salt spray)	48 hours			
Maximum wire size	1mm maximum diameter			



Self-Cleaning "Wiping" Contacts






Mil-Aero Circular Connectors

Environmental, hermetic, and filter class







Mil-Aero Circular Connectors Selection Guide



SuperNine® High-Performance MIL-DTL-38999 Series III Type Crimp, PC Tail, High-Speed and Hermetic Connectors



MIL-DTL-38999 Type Specials Glass-Sealed Hermetic Connectors



EMI/EMP Filter Connectors


USB and RJ45 SuperSeal™ Connectors



Sav-Con® Connector Savers and Adapters

MIL-DTL-28840 Connectors

rom satellites to ruggedized shipboard and aerospace applications, Glenair supplies virtually every power, signal, or high-speed cylindrical connector configuration currently in active use. From our QPL'd MIL-DTL-38999 hermetic connectors to our revolutionary SuperNine® family of high-performance D38999 Series III type connectors, Glenair is at the forefront in the manufacture and supply of mission critical mil/aero circulars.





For more information contact Glenair at **818-247-6000** or visit our website at **www.glenair.com** U.S. CAGE code 06324



SuperNine® is the industry's most complete and advanced D38999 Series III type connector family. From standard environmental-class connectors with improved durability and ease-of-use, to EMI/EMP filter connectors with innovative flange and PC tail termination configurations, SuperNine® offers military, commercial aerospace and other customers that have standardized on Series III technology the opportunity to improve interconnect system performance and resolve a wide range of persistent electrical, environmental, and mechanical performance problems —all with catalog connector solutions backed by Glenair's high-availability business model.

SuperNine® offers improved durability, sealing, cost-of-ownership, ease of shield termination, a broader range of PC tail configurations, environmental and hermetic bulkhead feed-throughs, connector savers, off-the-shelf EMI/EMP filter connectors and more—all supported with Glenair's well-established reputation for service, support, and fast turnaround.



THE SUPERNINE® TECHNOLOGY PROMISE

- Across-the-board improvements in matingcycle and contact durability
- Advanced ease-of-use features such as integrated shield-termination band porches and threaded PC-**Tail standoffs**
- High-performance improvements in every connector class—from filters to fiber optics

Glenair SuperNine® connectors in action: in this example, a pair of our advanced fiber optic interconnects cabled-up in a turnkey, environmentally sealed point-to-point jumper

BETTER THAN QPL **SuperNine®**



Advanced performance MIL-DTL-38999 Series III Type Connectors

SuperNine™ Environmental I/O and Cable Connectors



- Plug connectors with integrated ground springs and banding porch
- Complete range of crimp connectors with high-durability contacts
- Five different designs of printed circuit board connectors and standoffs
- Standard MIL-STD-1560 as well as high-density insert arrangements
- High-durability/advanced vibration and shock ratcheted coupling

SuperNine™ High-Speed Connectors



- Full range of hybrid insert arrangements incorporating size #22 signal contacts, plus size #12 and #8 keyed shielded contacts
- El Ochito®: One full 1G/10G Ethernet channel per standard size #8 cavity
- Supported applications: 10/100/1G/10G BASE-T Ethernet, analog/digital video, 1553 databus and general RF or differential data transmission
- Turnkey Quadrax and El Ochito® solutions—from crimp and PCB contacts to connectors

SuperNine™ High-Pressure Hermetic Connectors



- Glass-to-metal seal pin/socket hermetics with sealing up to 1x10⁻¹⁰cc/sec
- DSCC qualified and derivative solutions with advanced mounting features
- Pressure resistance to 32,000+ psi
- Stainless steel, titanium, Kovar® and Inconel® shell material options
- Bulkhead feed-through and hull penetrator versions

SuperNine™ Ruggedized RJ45 and USB Connectors



- Insert-to-shell grounding for superior EMC continuity and shielding
- Superior environmental sealing, IP67 unmated compared to COTS solutions
- Advanced vibration and mechanical shock tolerance
- Full range of offerings for Cat6a Ethernet: Jacks, Plugs, PC tail and crimp
- High-temperature rated -40° to +125°C

SuperNine™ EMI/EMP Filter Connectors



- Planar, multilayer ceramic capacative filters with and without TVS diodes
- C, L-C, C-L, and Pi filter electrical configurations
- Special high operating temperature solutions
- Industry's broadest range of pF capacitance: from 10 to 1,000,000 pF
- Fast and reliable in-house manufacturing of all filter elements and processes

SuperNine™ Fiber Optic Connectors



- Ultralightweight composite thermoplastic connector solution
- Qualified size #16 MIL-PRF-29504 pin-socket precision ceramic termini
- Ultra tight tolerance shell and cavity dimensions for precise axial alignment
- Ultra low insertion loss values for both singlemode and multimode
- Insert arrangements from 2 to 37 ways

MIL-DTL-38999 DERIVATIVES AND OTHER **Environmental Connector Specials**



INNOVATIVE TERMINATION TECHNOLOGIES









Flex and **Rigid Flex**

Compliant (Press-Fit)

Insertable **Solder Cups**

Variable-Length **PC Tails**

Ground Plane Inserts

INNOVATIVE SHELL PACKAGE MODIFICATIONS









Mounting Flange Modifications

Bulkhead Penetrators

Integrated/Housed Electronics

Integrated Band/Boot Porch

NON-STANDARD CONTACT LAYOUTS









Hybrid Power Contact Arrangement

Sealed Coax Insert Arrangement

Hybrid Shielded Contact / Signal Contact Insert Arrangement

Ground Plane Metallic Insert for Shielded Contacts

INNOVATIVE MATING TECHNOLOGIES











Space-grade zero extraction force connector for satellite payload deployment

MILITARY/AEROSPACE

Environmental

Problem-solving mil-aero cylindrical

Connector Specials

connectors from the most accommodating

engineering and manufacturing team in the

interconnect industry—we say yes to specials!



High-density contact arrangement with size #23



Unique coupling nut castellations and coverings

Special-purpose connector

ENGINEERED SOLUTIONS AND EXOTIC DERIVATIVES

High-density, push-pull, lanyard release, high temperature, ground plane, compliant pin,

zero extraction force, thru-bulkhead, space-

modified flange, or any other modification

needed to solve a complex interconnect

Liberal policies on NRE costs, minimum order quantities and delivery

challenge

schedules

grade, gender changers,

go-betweens and buffers Center Jackpost and **Guide Pin Integration**

QDC Quick-Disconnect **Push-Pull Mating**

Quick-Disconnect Lanyard-Release Assemblies



Glass-sealed Hermetic **Connectors**

sealed hermetic connectors






Resolve gas, moisture and particle ingress

problems with advanced-performance glass-

VITREOUS GLASS TECHNOLOGY ADVANTAGES



- Higher resistance to extreme operating temperatures to 260°+ C
- Superior mechanical strength
- No material breakdown or aging over time
- Helium leak rate <1X10⁻⁷ cc/sec to 1X10⁻¹⁰

Glass-Sealed Hermetic Connectors

MIL-DTL-38999 AND OTHER



GEOPHYSICAL AND OFFSHORE CONFIGURATIONS











GeoMarine® doublestart hermetic connector

Hermetic power connector

Single-way tool joint hermetic connector

Hermetic probe connector

Hermetic bulkhead penetrator

HIGH-SPEED/SHIELDED DESIGNS











Triax hermetic

Hybrid coax/signal hermetic

Ouadrax hermetic

MT ribbon fiber optic hermetic

Hybrid coax/signal hermetic

RECTANGULAR PACKAGES











MIL-DTL-24308 **QPL** hermetic

Series 79 Micro-Crimp hermetic

MIL-DTL-83513 type micro-D hermetics

Sealed panel-mount micro-D hermetic

MIL-DTL-38999 QPL PIN AND SOCKET HERMETICS






3 Point Bayonet Coupling



Series II Low-profile 3 Point Bayonet Coupling



Series III Scoop-proof Triple Start, Self-Locking



Series IV Scoop-proof **Breech Lock**





MIL-DTL-26482



MIL-DTL-83723






MIL-DTL-5015



Series 80 Mighty Mouse

© 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

MIL-DTL-38999 (QPL)




Glenair manufactures a full range of filter connectors for use in EMC/EMP management of electronic systems and interconnect cabling. All connectors are designed in accordance with applicable connector specifications, and are designed to mate with plugs with the same insert configuration and opposite contact gender. Planar filter arrays and TVS diodes may be integrated into both standard catalog as well as build-to-order configurations. Glenair's stateof-the-art diode burn-in process tests leaded and surface mount diodes with leakage current monitored throughout the entire test procedure ensuring field reliability.

	Table I: Capacitor Array Code / Capacitance Range					
Class	Pi - Circuit (pF)	C - Circuit (pF)				
X	160,000 - 240,000	80,000 - 120,000				
Υ	80,000 - 120,000	40,000 - 60,000				
Z	60,000 - 90,000	30,000 - 45,000				
Α	38,000 - 56,000	19,000 - 28,000				
В	32,000 - 45,000	16,000 - 22,500				
С	18,000 - 33,000	9,000 - 16,500				
D	8,000 - 12,000	4,000 - 6,000				
E	3,300 - 5,000	1,650 - 2,500				
F	800 - 1,300	400 - 650				
G	400 - 600	200 - 300				
J	70-120	35-60				



- Planar, multilayer ceramic capacitive filters, with and without transient voltage suppression diodes
- C and Pi electrical configurations
- PC tail, crimp or solder cup termination
- 35 240,000 pF capacitance
- Fast and reliable diode burn-in and test services
- Turnkey in-house manufacturing of all filter connector elements and processes

SERIES 240 **EMI/EMP Filter connectors** Fast, reliable in-house manufacturing



UNIQUE AND SPECIAL PURPOSE EMI/EMP FILTER CONNECTORS



Extended-shell PC-tail cylindrical with threaded standoff



Special-purpose filter connector cable adapter



Series 80 Mighty Mouse PC-tail filter receptacle



MIL-STD-1760 filtered umbilical connector



Filter plug with crimp contacts

RECTANGULAR PACKAGING



MIL-DTL-83513 type micro-D filter connector



MIL-DTL-24308 type D-sub filter connector



Series 79 Micro-Crimp filter connector



ARINC 600 rack and panel filter connector

EMP TRANSIENT VOLTAGE SUPRESSION DIODE-EQUIPPED



EMP Diode-Equipped Connector MIL-DTL-38999 series III type with Oversized Shell



EMP connector



Reduced-package-size **EMI/EMP** cylindrical



MIL-DTL-38999 series III type EMP with rectangular housing

TTL

Analog Sensors

Thermocouple Wires

USB

Ethernet

Line Types:

THE INDUSTRY'S MOST COMPREHENSIVE AND COMPLIANT FILTER SERVICE

Requirement Compliance:
MIL-STD-449D: RF Spectrum
MIL-STD-461E: EMI Susceptibility
MIL-STD-1310G: Shipboard EMC
MIL-STD-1512: Electroexplosive Subsystems
MIL-STD-1541A: EMC for Space Systems
MIL-STD-1795A: Aerospace Lightning Protection
MIL-STD-1857: Grounding, Bonding and Shielding
MIL-STD-1542B: EMC and Grounding for Space Systems
EN 61000-4-2, 3, 4, 5, 6, 8: EM, RF and Power
RTCA/DO-160 Sec 22: Pin/Cable Level and Waveform

Connector Series:				
38999	83513			
Series I, II, III, IV	5015			
26482	Sr. 80 Mighty Mouse			
83723	Sr. 79 Micro-Crimp			
28840	Sr. ITS Reverse-Bayonet			
24308	Sr. 28 HiPer-D			
ARINC 600	Sr. 970 PowerTrip			

	С	
nce		_
ve		
	-	

CAN BUS

ARINC 429

RS 232

RS 422

RS 485

Pi	
<u></u>	Ţ

© 2014 Glenair Inc	1211 Air Way, Glendale, CA	91201 • 818-247-6000 • wy	ww.glenair.com • U.S	CAGE code 06324
o zorr dichan, mc	izii i ii vay, diciiaaic, ci	1 1201 010 2 17 0000 11	www.greman.com o.s	C/ IGE COGC OOSE I

Filter Types

SUPERSEAL Glenair.

Ruggedized RJ45 and USB Connectors for Aerospace, Defense and Other Applications

Triple-start mating MIL-DTL-38999 type connectors with IP68 sealing (mated condition), robust insert-to-shell grounding, and a complete range of wire, cable, and circuit board terminations



MIL-DTL-38999 Series III

with sealed RJ45



MIL-DTL-38999 Series III with USB jack and jumper



High-capacity, high-speed USB data stick

- Superior sealing—IP67 unmated—for complete system protection against water, sand and dust
- Highly durable RJ45 design, including enhanced operating temperature, increased life-cycle, and rugged vibration and shock performance
- Shielded/grounded coupler designs in both receptacle and plug connectors
- Crimp, solder-cup,
 PC tail, and Quadrax
 contact/wire termination
 options
- RJ45 plug and/or jack interface options available in Cat 5e or Cat 6a
- Intermateable with other MIL-DTL-38999 type RJ45 field-duty connectors

SUPERSEAL MIL-DTL-38999 SERIES III TYPE **RJ45 and USB Aerospace/Defense Connectors**



Product Selection Guide



233-300

SuperSeal™ MIL-DTL-38999 Series III Type Connector/ Adapter with RJ45 Jack/Jack or Plug/Jack Couplers



233-301

SuperSeal™ MIL-DTL-38999 Series III Type Connectors with RJ45 Jack or Plug to Rear Crimp Contact Termination



233-302

SuperSeal™ MIL-DTL-38999 Series III Type Connectors with RJ45 Jack to PC Tail Termination



233-303

SuperSeal™ MIL-DTL-38999 Series III Type Connectors with RJ45 Jack to Rear Solder Cup Termination



233-304

SuperSeal™ MIL-DTL-38999 Series III Type Connectors with Pin or Socket Contacts to RJ45 Jack or Plug Interface



233-305

SuperSeal™ MIL-DTL-38999 Series III Type Connectors with Pin or Socket Quadrax to RJ45 Jack or Plug



233-330

SuperSeal™ MIL-DTL-38999 Series III Type Feedthrough Receptacle with RJ45 Jack to Jack Coupler



MIL-DTL-38999 Series IV*

*Mil-Spec qualification pending

Time-tested, industry standard breech-lock connector

From vertical launch fire-control, tracking, and multi-target missile systems to rugged industrial applications such as mining/gas-pressure blasting, the Glenair MIL-DTL-38999 Series IV type connector is the ultimate solution for positive and reliable breech-locking connector performance. Built IAW MIL-DTL-38999 Series IV, Glenair series 234-105 plug and receptacle connectors are available in shell sizes 11-25, with all MIL-STD 1560 insert arrangements as well as high-density and hybrid shielded contact arrangements. The heart of the 234-105 connector is its revolutionary coupling nut/locking technology which provides familiar breech-lock mating augmented with both primary and secondary locking mechanisms. Environmentally sealed, EMI grounded, and outfitted with pin-to-pin mating protection to prevent circuit shorts and mechanical damage, the Glenair 234-105 delivers unsurpassed reliability and anti-demating performance.

- IAW MIL-DTL-38999 **Series IV**
- Optimized for SWAMP area applications
- Quick-disconnect 90° breech coupling mechanism
- Visual, audible and tactile full-mate indicators
- Integrated EMI grounding fingers
- -65°C to 200°C operating temperature range



Series IV solutions are available in environmental, filter, and hermetic class configurations in shell sizes from 11-25 supporting the full range of MIL-STD-1560 insert arrangements



Glenair's complete Series IV solution includes protective covers and dummy stowage receptacles—available in all sizes, materials, and plating configurations.

SERIES 234-105

MIL-DTL-38999 Series IV

Industry standard breech-lock connector Super fast turnaround on quotes and orders



SERIES 234-105 PLUG AND RECEPTACLE, LOCKING, HIGH-VIBRATION



NOTES

1. Materials and finish

Contacts: IAW AS39029

Seals: Fluorosilicone blend

2. Blue color band indicates rear

release contact retention system

3. Connector supplied with contacts

removal tools and sealing plugs

(including spares), insertion/

4. Glenair 234-105 connectors are

designed to mate with any QPL

manufacturer's MIL-DTL-38999

Series IV connectors with the

same insert arrangement and

polarization. Mil-spec qualification

IAW MIL-DTL-38999

pending.

		How To Order						
Sample Part Number		234-105 -44 NF 11 -				-35	Р	N
D38999 Series IV Type Connectors	234-105 = Er	234-105 = Environmental Class*						
Connector Style	See Table I	See Table I						
Material/Finish	See Table II							
Shell Size	11, 13, 15, 17, 19, 21, 23, 25							
Contact Arrangement	Per MIL-DTL-1560							
Contact Designator	P = Pin A = Pin Gender, Less Contacts S = Socket B = Socket Gender, Less Contacts							
Polarization	N (Normal), A, B, C, D, K, L, M, R, & U				-			

		Table I: Connector Style
NOTES	40	Square-flange wall mount receptacle
. Materials and finish	42	Box-mount square flange receptacle
Insulator: High grade rigid	44	Jam nut receptacle
dielectric	46	Plug with EMI grounding spring
O-ring: Silicone	47	Plug without EMI grounding spring
Contacts: IAW AS39029	49	In-line cable receptacle

Glenair also supplies a full line of qualified MIL-DTL-38999 Series IV pin and socket contact hermetic receptacles—most popular part numbers in stock and ready for immediate shipment


Table II: Material / Finish				
Symbol	bol Material Finish			
ME		Electroless Nickel		
NF	Aluminum	Cad O.D. over Electroless Nickel		
G2		Anodize, Hardcoat		
ZR		Zinc Nickel, Black		
MT		Nickel-PTFE		
Z1*	Chaimlean Chaol	Passivate		
ZL*	Stainless Steel	Electro-Deposited Nickel		
*Available in receptacle only. Not firewall rated.				



A complete range of application tooling is available, including adjustable crimp tools, contact insertion and removal tools, Band-Master™ EMI shield termination system tools and others—all available for immediate, same-day shipment



contact Glenair at 818-247-6000 or visit our website at www.glenair.com U.S. CAGE code 06324



Connector Savers and Bulkhead Feed-Thrus

The smart solution for preventing contact damage and extending the service life of cable assemblies and box and panel-mount receptacles


> Series changers and gender changers available in both Sav-Con® and bulkhead feedthru configurations



Sav-Con° Lock Ring prevents accidental disengagement of bayonet coupled connectors

Locking a Sav-Con® Connector Saver to a receptacle can prevent accidental or unauthorized unmating. This can ensure that the equipment receptacle remains in its unused condition prior to delivery.

- Sav-Con®s for every **Military Standard** connector
- Bulkhead feed-thrus for environmental, filter and hermetic applications
- Pin/pin, pin/socket, and socket/socket versions
- Traditional plugreceptacle savers, as well as in-line versions and gender changers
- Available EMI/EMP filter savers and adapters
- Optional locking mechanism



HIGH-PERFORMANCE CONNECTOR GO-BETWEENS

Sav-Con® Connector Savers and **Bulkhead Feed-Thrus**



Each Glenair Sav-Con* Connector Saver meets the military specification performance requirements of its mating connector. Glenair manufactures and supplies a Sav-Con* connector saver for every military standard connector currently in use including:

- MIL-DTL-26482 Series I and II
- MIL-DTL-28840
- MIL-DTL-38999 Series I, II and III
- MIL-DTL-83723

- LN 29729 (SJT)
- PATT 105 and PATT 602
- MIL-DTL-5015
- Series 801 and 805 **Mighty Mouse**
- M24308 D-Subminiature
- MIL-DTL-83513 Micro-D **Subminiature**
- Series 28 HiPer-D M24308 intermateable
- Series 79 Micro-Crimp

Comprehensive materials, plating, and polarization options available

TRADITIONAL PLUG-RECEPTACLE SAV-CON® CONNECTOR SAVERS



MIL-DTL-38999 series III type



MIL-DTL-5015 threaded and/or reverse-bayonet



MIL-DTL-38999 series II bayonet-coupling saver



Series 80 Mighty Mouse Sav-Con®

BULKHEAD FEED-THRUS



MIL-DTL-38999 series III type jam nut and square-flange bulkhead feed-thrus



MIL-DTL-5015 bulkhead feed-thru



Special shielded contact bulkhead feed-thru

SPECIAL-PURPOSE ADAPTERS AND SAVERS



EMI/RFI filter Sav-Con® adapter



MIL-DTL-83513 type micro-D filter connector



receptacle-to-receptacle feed-thru



connector saver







MIL-DTL-28840 qualified connectors in-stock and ready for immediate, same-day shipment

- High density, scoop proof contact arrangements
- Flange mount, box mount, jam-nut and in-line
- Straight, 45° and 90° strain reliefs and backshell assemblies
- Sav-Con® connector savers
- MIL-DTL-28840 qualified
- Additional glenair commercial part numbers with features not available in the mil-spec

Qualified military standard electrical connectors and accessories for shipboard—and all rugged environmental applications

Performance Specifications			
Current Rating (Maximum)	Size #20 Contact with 20AWG wire=7.5Amps, with 22AWG wire=5.0Amps		
Test Voltage (DWV)	1000 VAC RMS at sea level. Test per EIA-364-20		
Insulation Resistance	5000 megohms minimum (at ambient temperature) per EIA-364-21		
Contact Resistance	Per SAE-AS39029		
Operating Temperature	-55° C to +200° C		
Immersion	per test method EIA-364-09		
Shock	in accordance with MIL-S-901 grade A		
Vibration	per EIA-364-28 test procedure		
Magnetic Permeability	2.0 μ (Aluminum), 5.0 μ (Stainless Steel) maximum; ASTM-A342/A342M		







Splined MIL-DTL-28840 connector-tobackshell interface is ideally suited for heavy backshells and cables

AVAILABLE CONTACT ARRANGEMENTS











Shell Size 15





Shell Size 17 31 Contacts




Shell Size 19

Shell Size 11

Shell Size 23


64 Contacts


Shell Size 13




Shell Size 25

92 Contacts







Shell Size 29 121 Contacts

Shell Size 33 155 Contacts

STANDARD PIN CRIMP CONTACT FOR MIL-DTL-28840 CONNECTORS



MIL-DTL-28840

Connectors and Accessories

QUALIFIED

Mating End Size	Wire Accomodation	Military Part Number	Glenair Part Number
20	28-32 AWG	M39029/83-451	850-004-20-451
20	22-26 AWG	M39029/83-450	850-004-20-450
20	20-24 AWG	M39029/83-508	850-004-20-508

STANDARD SOCKET CRIMP CONTACT FOR MIL-DTL-28840 CONNECTORS



Mating End Size	Wire Accomodation	Military Part Number	Glenair Part Number
20	28-32 AWG	M39029/84-453	850-005-20-453
20	22-26 AWG	M39029/84-452	850-005-20-452
20	20-24 AWG	M39029/84-509	850-005-20-509



M22520/34-01 Basic Crimp Tool M22520/34-02 Positioner M22520/35 Gage



M81969/33-01 Straight Insertion Tool M81969/33-02 Offset Insertion Tool

M81969/34-01 Removal Tool



M39029/83 Standard Duty **Electrical Pin Contact**



Socket Contact

M39029/84 Standard Duty **Electrical Socket Contact**



Backshells



EMI/RFI Environmental Backshells

M28840/6 A Straight M28840/8 A 90° M28840/9 A 45°



Connector Sockets



M28840/23



Non-Self-Locking

Non-Self-Locking

Strain

M28840/1 Straight M28840/3 45° M28840/2 90°



M28840/9 B 45°

M28840/8 B 90°

Dummy Stowage Receptacles

M28840/7

Plug Covers

M28840/15

M28840/13

Protective Receptacle Covers

C-17 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

Jam Nuts

MS3186

Mounting Flanges and Gaskets

M28840/24

MIL-PRF-24758A **Conduit Fittings** M24758-14 Straight

(M24758/14 Straight.) M28840/5 Straight • M28840/25 90° • M28840/27 45° • M28840/30 Coupling

C-16 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324






600G005

Gasket

VG QUALIFIED AND COMMERCIAL

Industrial-Strength Power and Signal Connectors







Industrial-Strength Power and Signal Connectors









Series ITS and Derivative Industrial/Rail Power and Signal Connectors



Series IRT/ITS/UJ High-Current/High-Voltage Power Connectors for Rail and Industrial Applications



PowerTrip™ Extreme Environment Power Connectors

Ruggedized High-Speed Ethernet Connectors



Series 22 Geo-Marine® High-Pressure Harsh-Environment Connectors and Cordsets

Glenair offers a "no gap" family of ruggedized power and signal interconnect solutions for industrial, rail, geophysical and power industry applications. No other interconnect manufacturer in the world supplies such a broad range of connectors, backshells, wire protection conduit, shrink boots, tools and more to meet harsh-environment industrial requirements. All our solutions are backed with our high availability customer service model, which includes in-stock inventory for thousands of critical part numbers, no dollar or quantity minimum orders, free samples upon request, free engineering and application development and more. Contact the factory or our industrial/rail product team for application engineering assistance.



For more information contact Glenair at 818-247-6000 or visit our website at www.glenair.com U.S. CAGE code 06324



Circular industrial power and signal connectors for from mining equipment to military vehicles

Circular Reverse-Bayonet and Threaded Coupling Connectors

Series ITS - Reverse-Bayonet Power and Signal

Series ITS-RG - RadGrip™ Rubber Coupling Nut Circular

Series FRITS - Flame-Resistant Insert for Rail Applications

Series IT - Threaded Coupling Power and Signal

Series ITH - Rigid Insert / Mechanical Contact Retention

Series ITK - High-Temperature Ceramic

Series ITZ - Triple-Start Thread Power and Signal

Series IFO - Reverse-Bayonet Fiber Optic

Series IGE - High Currrent, Low Voltage Single Pole

Series 901- High Current Medium Voltage Circular

Series 500 - Reverse-Bayonet Single-Pole High Voltage

Series IPT - Standard Bayonet Power and Signal

Series IPT-SE - Standard Bayonet Crimp Contact

- Dozens of proven connector technologies for harsh application environments
- Hundreds of power and signal contact arrangements (crimp and solder)
- Threaded, reverse bayonet, and innovative latch-and-lock coupling technologies
- Flame-resistant, caustic substance-free material choices for RoHS and other compliance standards





Series IT, ITS and derivative connector families are available with three plug coupling nut designs: Standard, Arctic, and rubbercovered RadGrip™

INDUSTRY STANDARD AND GLENAIR INNOVATIONS **Industrial/Rail Power and Signal Connectors**



CIRCULAR INDUSTRIAL/RAIL POWER AND SIGNAL CONNECTORS: 5015 TYPE DERIVATIVES









Series ITS Reverse-Bayonet

Series ITH Riaid Insert

Multi-Pin High Voltage

Series IT Threaded Coupling

Series ITZ Triple-Start Coupling

Series ITK **High-Temperature Ceramic**



Seacrow

Marine Bronze









Series IGE Single-Pole High Power



Series ITS Bayonet with Wing Locks

HIGH-SPEED / RUGGEDIZED CONNECTORS FOR INDUSTRIAL AND RAIL APPLICATIONS



SuperSeal™ with RJ45 Ethernet



Series CX **High-Speed Coaxial**



Octobyte™ **Ethernet Contact**



Series IFO **High-Speed Fiber Optic**

SERIES ITS-RG RADGRIP™ REINFORCED RUBBER COUPLING NUT CONNECTORS



ITS-RG

(Basic Black)



ITS-RG (Fiber Optic Blue)



(Safety Red)

D-2 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

(Semper Tan



Rugged high current/high voltage power connectors for rail and industrial applications

Connection of power cables in rolling stock is a critical application. Beyond specific parameters like voltage, current, or watertight sealing, other application requirements must be considered: environment and operating conditions, robustness, handling, and other specifications.

The IRT connector series is one of the most popular connection systems used around the world, and is able to satisfy all of the common parameters from different railway authorities. Glenair is able to develop customized connectors for specific applications, certifying the products according to unique customer requirements.



SERIES IRT RECTANGULAR MULTIPOLE HIGH VOLTAGE TRACTION MOTOR CONNECTORS



The Glenair IRT series is a rectangular power connector for harsh environmental conditions. Available with three, four and six contacts, typical for traction motor applications. Suitable for single cables AWG 4 – 373MCM (35 to 185 mmq). Working voltage up to 3000 Vcc.

Two mating systems offered:

- Screws, for light weight and reduced dimensions
- Lever system with secondary lock, easy to use in difficult positions.

The IRT Series is suitable for separated power cables, with or without shielding, ground body available with a copper plait.

Available with three different cable backend styles:

- Metallic gland
- Clamp with strain relief
- EMC shield and gland



SERIES IRT • ITS • UJ

High Current/High Voltage Power Connectors



for rail and industrial applications

ITS 901 SERIES REVERSE BAYONET MULTI-POLE MEDIUM VOLTAGE JUMPER CONNECTORS



ITS 901 Series is the extension of the ITS Reverse Bayonet connector family, for power cables over AWG 1/0.

Suitable for harsh environmental conditions, 901 Series Connectors accept cable from AWG 4 to 262 MCM (35 - 120 mmq), for current up to 450 Amp.

Working voltage: 800 - 1000 Vac.

Available for single wires and multipole jacketed cables, with cable clamp or conduit. Male contacts with Finger Test Protection, Load Side (Receptacle or Plug).

Long bayonet ramps, three polarization keys and rubber recovered coupling facilitate mating and unmating operations.

901 Series meet the most important rail requirements and specifications:

- Salt Spray Test Corrosion: 500 hours;
- 500 Mating Cycles;
- Shock and Vibrations for Under-Car and Car-To-Car Applications;
- IP67 Sealing (Coupled Connectors);
- Fire Resistant and RoHS Compliant Materials.

ITS 500 SERIES REVERSE BAYONET SINGLE-POLE HIGH VOLTAGE JUMPER CONNECTORS



ITS 500 Series derives from an important Military Specification for Power Connectors: VG96929. Suitable for harsh environmental conditions, ITS 500 accepts cable gauges AWG 3/0 to 444MCM (95-240 mmq), for current up to 750 Amp. Special insulator drawing allows high working voltage, up to 3000 Vcc.

Suitable for jacketed cables, with or without conduit protection.

Receptacle with finger protection (Load side).

ITS 500 meets the most important rail requirements and specifications:

- 500 Mating Cycles;
- Salt Spray Test Corrosion: 500 hours;
- Shock and Vibrations for Under-Car and Car-To-Car Applications;
- IP67 Sealing (Coupled Connectors);
- Fire Resistant and RoHS Compliant Materials.

UJ SERIES POWER JOINT CONNECTOR SYSTEM

Receptacle

Connector



Offers the possibility to connect medium and high power cables without the need for bulky junction boxes. The UJ Power Joint System offers the same environmental protection with substantial size and




	UJ Series	Junction Box
Dimensions	Small	Regular / Big
Veight	Light	Heavy
Protective Varnish	No	Yes
Modularity	Yes	No
Environmental	Yes	Yes
Electrical Performance	Yes	Yes
Cost Reduction	Yes	No
Temperature Range	High	Standard

D-4 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.qlenair.com • U.S. CAGE code 06324

weight savings.

G lenair. PowerTrip[™] Reduced size and weight power connectors





Keyed receptacle with superior sealing and EMI shielding

- Fast, easy mating with triple-start ACME thread: 360° turn for full mating
- Reduced size and weight compared to 5015/VG95234 solutions
- LouverBand sockets for improved current ratings and longer life, up to 2000 mating
- Splined backshell interface for improved backshell attachment and EMI shielding
- Ratcheting coupling nut for secure mating
- Operating temperature -65° C to +200° C
- Hermetic and filter options available

The Series 970 PowerTrip™ offers improved performance compared to standard 5015 type power connectors: higher density and lighter weight packaging, rapid mating and demating triple-start threaded coupling, and extremely rugged splined and threaded backshell attachment interface



The power connector for extreme environments



SERIES 970 POWERTRIP™ CONNECTOR STYLES











Plug 970-001


Receptacles 970-003

Jam Nut Receptacles 970-004

Cable Receptacles 970-005


970-006

Hermetic Feed-Thru **Bulkhead** 970-007



Series 970 PowerTrip™ Specifications Current Rating Up to 225 A. Dielectric Withstanding Voltage 2000 VAC Insulation Resistance 5000 megohms minimum **Operating Temperature** -65° C. to +200° C. Shock 300 g. Vibration Shielding Effectiveness 65 dB minimum from 1GHz to 10GHz. Durability 2000 mating cycles

CONTACT RESISTANCE AFTER 1000 MATING CYCLES



ABOUT THE POWERTRIP CONTACT SYSTEM

Series 970 contacts are precision-machined using high conductivity copper alloy. A stamped and formed spring ("LouverBand") is installed into the socket contact. The spring is made from 6 mil copper alloy. Testing has demonstrated that this contact system outperforms conventional aerospacegrade contact systems. The LouverBand spring provides many points of electrical contact with the mating pin, as opposed to a few "high spots" on a conventional four-finger contact as shown in the figure below. The size #8 Powertrip socket contact has a total of 18 louvers. The #4 has 27 louvers, and the #1/0 has 42 louvers. The LouverBand design offers lower voltage drop for reduced joule heating. In addition to its electrical advantages, the LouverBand also is mechanically superior to four-finger contacts. The LouverBand spring has consistent, stable normal force, even when subjected to thousands of mating cycles and temperature extremes.



LouverBand socket

Conventional contact on the left, LouverBand contact on the right

contact cutaway

D-6 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324



Ruggedized bayonet and reverse-bayonet RJ45 and USB connectors for industrial/rail applications

Glenair offers the world's most comprehensive line of ruggedized RJ45 Ethernet and USB connectors in 5015 and 26482 type connector packaging. The Series ITS reverse-bayonet and IPT bayonet RJ45/USB SuperSeal™ lines offer fast mating and demating, resistance to vibration and shock, as well as superior sealing for complete protection against water, sand and dust in harsh environment applications. High-performance RJ45 and USB inserts feature integrated shielding and grounding in both plug and receptacle connectors plus crimp, solder-cup, PC tail and Quadrax contact/wire termination options.



- Proven reverse-bayonet mating for vibration and shock resistance
- Superior sealing—IP67 in unmated condition—compared to other available environmental circulars
- Rear-release crimp contact termination and USB/RJ45 jumper accommodation
- Superior grounding for electrostatic discharge and EMC
- Superior cable shield termination with integrated banding platform
- Optional spring-loaded protective covers for environmental protection of junction boxes and switches
- Wide range of high speed Ethernet/ network protocols supported, including USB 2.0 and RJ45

In addition to ITS series (5015 type)
reverse-bayonet solutions, low-profile
series IPT bayonet RJ45 SuperSeal™
connectors and integrated box
assemblies are also available

USB AND RJ45

SuperSeal[™] Ruggedized Bayonet and Reverse-Bayonet Connectors



Product Selection Guide



SuperSeal™ 5015 Reverse Bayonet Plug with Cat 5e RJ45 Plug and Rear Crimp Contact Termination



SuperSeal™ 5015 Reverse Bayonet Plug with Cat 5e RJ45 Plug and Pre-Terminated Pigtail



SuperSeal[™] 5015 Reverse Bayonet Receptacle with Cat 5e RJ45 Jack and Pre-Terminated Pigtail



SuperSeal[™] 5015 Reverse Bayonet Receptacle with Cat 5e RJ45 Jack and PCB Termination



SuperSeal™ 5015 Reverse Bayonet Receptacles with Cat 5e RJ45 Jack/Jack Couplers



SuperSeal™ Reverse Bayonet RJ45 Connectors Cable Clamps, Cable Glands, and Backshells

PRODUCT SPECIFICATIONS

MATERIAL AND FINISHES:

Shell/coupling – High strength Aluminum alloy Plating – Electroless Nickel, Cad O.D., Black Zinc Cobalt or Std. black electrodeposited paint

Bronze, stainless steel and other materials and finishes available. Please consult factory.

SHELL TYPE AND SIZES:

Shell Type – D5015 Reverse-Bayonet Type Sizes – Shell size 18

CONNECTOR STYLES:

Receptacle – MIL-DTL-5015 type in shell size 18 with integrated RJ45 jack/jack or jack/PCB coupler available in Cat 5e

Plug – MIL-DTL-5015 type plug in shell size 18 with integrated RJ45 plug/jack coupler available in Cat 5e

Available in square flange front or rear wall mount with slotted or round holes, jam nut front or rear wall mount, in-line, and feedthrough configurations.

TECHNICAL CHARACTERISTICS:

Category – Cat 5e Connection – 10BASE-T, 100BASE-TX, 1000BASE-T Max Current Rating –1.5 Amps at 20° C Dielectrc Withstanding Voltage – 1000 volts Working Temperature – -40° to +85° C Environmental Rating – IP67 unmated

TERMINATION OPTIONS:

Crimp contact and PCB termination, pre-terminated pigtails; jack/jack and jack/plug RJ45 configurations

D-8 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

for industrial Ethernet data applications

Glenair series ITH connector with Octobyte[™] contacts is available with fully dedicated Ethernet protocol or in a combo version where a mix of signal-power and Ethernet is required. RoHS compliant, IP67 (IP68 on request) exceeds performance expectations typical in harsh environmental applications found throughout rail and industrial markets.

OCTOBYTE™ contacts are vibration resistant and designed to work with Ethernet cables from CAT 5 to CAT 7A, MVB-WTB, RG58 Coax.

ITH connectors with Octobyte™ contacts are easy and fast to assemble, making them the best solution for harsh-environment applications where signal reliability is a must.



Tested for compliance according to EN50173-1 standards set for CAT5E and CAT7. Testing was conducted using 12 jumpers, each 7.5 meters in length for a total of 90 meters.



- Commuter rail
- Passenger information systems (audio/video/ digital displays)
- Monitoring and control (braking/doors/lighting/ data)
- Heavy industry
- Data control
- Safety systems
- Tested in accordance with: ISO FO STP: CAT 7A EN50173-1 F600-STP: CAT 7 **EN50173-1 D STP: CAT 5E**

OCTOBYTE

The faster 4/8 pole industrial Ethernet interconnect system



ETHERNET CAT 7A CONTACTS



B . T	Ethernet CAT 6A
Data Transmission Ethernet Contacts for	Ethernet CAT 7
Contacts for	Ethernet CAT 7A
	Internal crimpable contacts
Footuring	Inspectable contact
Featuring	Integrated cable clamp
	Low mating force
Technical Characteristics	Current rating 5A max
recrifical Characteristics	Voltage drop (at 5A and 25°C) 70mV max
Materials and Finish	Copper alloy and gold plating
Incerts	Thermonlastic resin

ETHERNET CAT 5 CONTACTS



	Data Transmission Contacts for	Ethernet CAT 5
		Ethernet CAT 5E
Data Transmission Co	Data Transmission Contacts for	Ethernet CAT 6
	Featuring	Ethernet CAT 6A
		Internal crimpable contacts
		Inspectable contact
		Integrated cable clamp
		Low mating force
	Technical Characteristics	Current rating 5A max
		Voltage drop (at 5A and 25°C) 70mV max
	Materials and Finish	Copper alloy and gold plating
	Inserts	Thermoplastic resin—UL94V0-NFF 16-102 12F3 Exigence 3

COAX CONTACTS



Data Transmission Contacts for	RG58
	Internal crimpable contacts
Featuring	Inspectable contact
	Integrated cable clamp
	Low mating force
To about and Chaus at a visting	Current rating 5A max
Technical Characteristics	Voltage drop (at 5A and 25°C) 70mV max
Materials and Finish	Copper alloy and gold plating
Inserts	PTFE

ETHERNET MVB - WBT CONTACTS



Data Transmission Contacts for	MVB - Multifunctional Vehicle Bus
Data Transmission Contacts for	WTB - Wired Train Bus
	Internal crimpable contacts
Featuring	Inspectable contact
	Integrated cable clamp
	Low mating force
Technical Characteristics	Current rating 5A max
rechnical Characteristics	Voltage drop (at 5A and 25°C) 70mV max
Materials and Finish	Copper alloy and gold plating
Inserts	Thermoplastic resin—UL94V0-NFF 16-102 12F3 Exigence 3

D-10 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324



and overmolded cables for towed array and other high-pressure/submersible applications

Designed for use in oceanographic, geophysical and other severe industrial environments, Glenair Series 22 Geo-Marine® Connectors and Cables are the ultimate harsh-environment power and signal connector solution. Built to withstand hydrostatic pressures up to 5,000 PSI and exposure to extreme temperatures and corrosives, the Series 22 Geo-Marine® is ideally suited for applications such as US Navy towed array sonar systems, military land vehicles, submersibles and ROV's, offshore-oil drilling equipment, seabed exploration, pipeline inspection systems, well monitoring equipment, and digital seismic streamers.



Geo-Marine® plugs are equipped with arctic coupling nuts—made from marine-grade naval bronze with easy-to-grip castellated knurling and a powerful ratcheted anti-decoupling mechanism which quarantees reliable mating and demating performance in even the harshest environments. Supplied as discrete connectors or more typically in build-to-print overmolded cable assemblies.

Geo-Marine®

- Marine Grade 316 stainless steel machined shells and **Naval Bronze coupling rings**
- High-pressure environmental and hermetically sealed receptacles for field applications
- Power and signal contact arrangements from 2 to 128 contacts
- Anti-vibration ratcheted coupling nuts with castellated knurling
- Available Viton® overmolded cable assemblies

SERIES 22 **Geo-Marine® Connectors**

High-pressure environmental and hermetic connectors





photo: Seismometer, geophysical observatory, Neumayer Station, Antarctica by Dr. Hannes Grobe



Anti-Galling Arctic Coupling Nuts

One of the most valuable features of the Series 22 Geo-Marine® from the user's perspective is the speciallydesigned castellated and knurled coupling nut which facilitates rapid mating and demating in field applications. Single-start, stub Acme threads reduce thread fouling and binding, and are supplied with an anti-vibration/anti-decoupling device which prevents accidental loosening or decoupling. Plugs contribute to high-pressure sealing, up to 5,000 PSI in the mated condition, by means of rugged and durable interfacial and peripheral seals.

Range of Offerings

Series 22 Geo-Marine® connectors are supplied with either fused-glass ("H" hermetic class) or high grade thermoplastic ("E" environmental class) insulators. Both classes of connectors are supplied with rugged, corrosion-resistant materials. Low-profile and scoop-proof cable plugs and receptacles, as well as bulkhead feed-throughs are available. Specially-designed cable sealing backshells as well as EMI/RFI shield termination backshells and environmentally-sealed protective covers complete the range of discrete product offerings. 35 insert arrangements (contact sizes #12, #16, #20 and #22) are tooled and fully available.

Receptacle Configurations: High-pressure environmental ("E") and hermetic ("H") class receptacles are available for cable as well as box applications. Rugged o-ring piston seals located inside the receptacle barrel contribute to reliable high-pressure sealing in the mated condition. Glenair is able to supply Geo-Marine® customers with a wide range of receptacle configurations for unique requirements including low-profile and scoop-proof designs, pin and socket contact designs, solder cup and printed circuit board termination, unique flange shapes and mounting configurations, in-line cable receptacles, connector savers and gender changers.

HIGH-PRESSURE ENVIRONMENTAL AND HERMETIC RECEPTACLE CONFIGURATIONS











Square Flange

Solder-Mount **Bulkhead Feed-Through**

D-13 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324



harsh-environment applications

Glenair manufactures connectors qualified to VG96929, VG95234 and VG95328 standards. These connectors are mostly used in harsh-environment military applications for ground vehicles and ground systems. Our new Marine Bronze version increases the level of robustness of these connectors to be succesfully used in all severe environment navy installations, as well as offshore platforms, sea ports, geological and oceanographic applications.



- Marine bronze alloy for superior corrosion resistance in seawater and other harsh environments
- Ideal for shipboard and offshore drilling applications
- Available in Series ITS (5015 reverse-bayonet), Series IPT (26482), Series IGE (Single-pole high-power VG95234) and Series IT (5015 threaded)
- IP67 environmental sealing in mated condition; IP68 available
- Hundreds of available contact arrangements for both power and signal as well as hybrid applications

HARSH ENVIRONMENT **Seacrow Marine Bronze Connectors Superior corrosion resistance**



ITS-MB REVERSE-BAYONET CONNECTORS



VG95234 Compliant Marine Bronze Series

ITS-MB connectors are compliant with VG95234, using all the same insert arrangements available in the standard ITS Reverse Bayonet Connectors catalogue. Typically they are used for power and signal transmission, with wires from 26 AWG to 4/0. A wide variety of backshells allow the ITS-MB to accept jacketed cables, single or multi-poles, with or without RFI/EMI shielding, conduits with PG or metric thread. IP67 protection is the standard performance. IP68 on request.

IPT-MB MIL-DTL-26482 HIGH DENSITY CONNECTORS



VG95328 Compliant Marine Bronze Series

IPT-MB connectors are the choice for reliability when 20-16 AWG signal cables are used. The insert arrangements as well as the electrical characteristics are detailed in the IPT IPT-SE Catalogue. Backshells suitable for EMI shield terminations and heat shrink boots are also available.

The receptacle is also available with PCB contacts. IP67 protection is the standard performance. IP68 on request.

IGE-MB REVERSE-BAYONET SINGLE-POLE CONNECTORS



VG96929 Compliant Marine Bronze Series

IGE-MB High Power Single Pole Connectors are used with cables from 16 to 240 mmg. These connectors achieve high-performance working current and peak current, and are ideal for engines, power supplies, and power distribution boxes. Several backshells are available, either straight or 90° elbows for the most reliable cable accomodation. See the VG96929 Catalogue for detailed electrical characteristics. IP67 protection is the standard performance. IP68 on request.

IT-MB MIL-C-5015G THREADED CONNECTORS



Marine Bronze Series

IT-MB is a threaded connector compliant with the MIL-DTL-5015 standard. All the electrical characteristics are available in the IT standard catalogue. IT-MB family is a threaded version mostly used for power and signal, with IP67 standard performance sealing.

Rectangular Connectors

From nano and micro to D-subminiature the industry's best performance and availability



Glenair manufactures all of the popular industry-standard rectangular connectors used in military and aerospace applications, including special high-performance versions of the M24308 D-Sub and our revolutionary Series 79 Micro-Crimp connector. We offer a small form factor rectangular connector for virtually every I/O and wire-to-board requirement including MIL-DTL-83513 Micro-D subminiatures and MIL-DTL-32139 Nanominiature. All of our rectangular connector products are available in filter and hermetic versions, as well as with flex circuit terminations. Point-to-point cordsets, pigtails, and build-to-print harnesses are Glenair specialties.

Rectangular Connector Selection Guide








AlphaLink® Board-Level Connectors and Flex Jumpers

Series 89 MIL-DTL-32139 Nanominiature Connectors



Micro-D (MIL-DTL-83513) Connectors and Cable Assemblies

MasterLatch® Quick-Disconnect Micro-D







Well-Master™ 260° High-Temperature Micro-D

Series 79 Micro-Crimp Connectors








SuperTwin™ Lightweight Composite Modular Connectors

Series 28 HiPer-D 24308 Compatible Connectors




For more information contact Glenair at 818-247-6000 or visit our website at www.glenair.com U.S. CAGE code 06324

© 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324



AlphaLink SL is a high-performance, solderless board-level connector technology developed by Glenair that significantly expands board-level interconnection options for users of milspec caliber connectors. Precision-machined and EMI shielded, these ultra lightweight PC tail, solder cup, and/or pigtail equipped connectors are designed for high-reliability applications that require avionic system levels of vibration and shock tolerance. Ultra low-profile and high-density, AlphaLink SL connectors are equipped with 2–3 Amp spring-loaded contacts and may be ordered either as discrete connectors or in turnkey flex jumpers with Glenair high-reliability I/O connectors. Glenair is perfectly positioned to provide the entire solution with in-house manufacturing for every component part—from contacts and connectors to rugged polyimide-based flex. AlphaLink SL flex jumpers are available with Series 80 Mighty Mouse and Series 88 SuperFly ultraminiature and nanominiature circular connectors, as well as Micro-D subminiature, Series 79 Micro-Crimp, and nanominiature rectangular connectors. A wide range of insert arrangements, from 4–40 contacts is available.






Flex offers many advantages over conventional wire, including reduced size, weight, and complexity.

- Spring-loaded, solderless board-level connector
- PC tail and solder cup versions offer easy termination to flex or wire
- Turnkey I/O-to-board flex and pigtail wire jumpers
- Lightweight and lowprofile—up to 40% space savings compared to 2mm pitch solutions
- High-density .050" centerto-center contact footprint
- Fast PC board integration with reduced board preparation and masking
- Withstands temperature, vibration and shock extremes


SERIES 171 ALPHALINK SL Spring-loaded contact board-level connector Fast and easy PC board integration








171-134-01 Solder Cup Termination




171-134-03 Wire Pigtail Termination



AlphaLink SL spring-loaded contact PC board connectors deliver up to 50% footprint savings versus conventional 2mm pitch solutions. PC tail equipped connectors, the 171-134-02, are supplied with an EMI shroud / shield for improved EMC compared to low-cost plastic board connectors. All connector styles incorporate a high-reliability spring-loaded contact that delivers a virtually unlimited number of mating cycles. Connectors are typically mated to the PC board using conductive pads or via's. Stainless steel mounting hardware provides a robust, vibration-resistant attachment solution compared to stamped-and-formed retention barbs.


171-134-02 PC Tail Termination



AlphaLink SL flex jumpers: Compact interconnect assemblies that combine circuit board technology and cabling into a lightweight, integrated package. These turnkey jumper assemblies reduce system size and weight and are ideally suited for prototype applications and new product development efforts.



For more information contact Glenair at 818-247-6000 or visit our website at www.glenair.com U.S. CAGE code 06324



Nanominiature Connectors

MIL-DTL-32139 qualified connectors for mission-critical board-to-wire applications simply the smallest and lightest mil-spec connector in the business


- .025 Inch (0.635 mm) contact spacing
- #30 And #32 gage wire accommodation
- Single and double row
- Metal shell, aluminum, titanium or stainless steel
- TwistPin contact system
- Gold alloy contact, unplated

Nanominiature sized circular connectors in threaded and pushpull styles are also now available

from Glenair

Thru-hole and surfacemount PCB versions

THE NANO TWISTPIN ADVANTAGE



Transverse cross-section of a TwistPin contact crimped to solid wire



- Gas-Tight Crimp Joint
- Better Shock and Vibration **Performance**
- Corrosion Proof Contact Alloy

SERIES 89

Nanominiature Connectors



The smallest and lightest mil-spec connector

Pre-Wired Single Row

Connectors

Pre-Wired

Connectors

Pre-Wired

Double Row

Connectors

Double Row

Connectors

PCB

Series 89 Nanominiature Connector Performance Contact Spacing **Contact Centers** #30-#32 AWG Accommodation Current Rating 1 AMP Max 250 VAC RMS Sea Insulation 5000 Megohms Resistance Minimum Operating -55° C. to +125° C. **Temperature** Contact 71 Millivolt Drop Maximum Resistance Shock, Vibration 100g's, 20 g's Durability 200 Mating Cycles 48 Hours Salt Spray Resistance 5 Ounce Max, 0.4 Mating Force Ounce Min







on 0.025 Inch Spacing

SERIES 89 NANOMINIATURE PRODUCT SELECTION GUIDE







Thru-Hole Vertical

Insulated Wire

Thru-Hole Vertical



SMT Straddlei

Back-to-Back Cables

Pre-Wired MIL-DTL-32139 Connectors







Double Row, Insulated Wire

NANOMINIATURE CONTACT ARRANGEMENTS

Double Row Mating Face of Pin (Plug) Connector



Single Row Mating Face of Pin (Plug) Connector



© 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

SERIES MWDM **High-performance** Micro TwistPin contacts

Micro-D Connectors







EMI Filter

TwistPin equipped MIL-DTL-83513 Micro-D connectors offer outstanding mating performance, durability and minimal contact resistance



- High density Micro TwistPin contacts set on .050 centers
- 9 to 130 contact arrangements
- Pigtail, PCB, solder cup, and flex terminations
- Single row, multirow, low profile and high density insert arrangements
- QPL and commercial versions
- Same-day availability on all part numbers



MasterLatch™



Surface Mount



Rear Panel Mount



Flex Circuit

MIL-DTL-83513 AND COMMERCIAL **Micro-D Connectors** Mission-critical mating performance



METAL SHELL MICRO-D FOR HARNESSING APPLICATIONS



Assembly

GRPM Solder Cup



Insulated Wire



MWDM Solder Cup Uninsulated Wire





Insulated Wire



MWDM Back-To-Backs



Environmental



GSWM SpaceWire



GMLM MasterLatch

MICRO-D FOR PRINTED CIRCUIT BOARD

MWDM

Uninsulated Wire





Insulated Wire




MWDM-BS



MWDM-BR



MWDM-CBR



MWDM-CBS



90° Surface Mount



GMR7580



WellMaster™ 260



GMR7580C



GMR7590C



Right Angle Filter




Sav-Con®



Latching MicroStrip



Low Profile



Reduced Cost of Ownership, Easy Integration, and High-Performance for Flight and Lab Grade Cable Assemblies.

The success of any space mission begins with reliable data transmission and Glenair Spacewire cables, built to meet the strict standards set forth by ECSS-E-ST-50-12C, make this a reality. Our Spacewire cables offer bidirectional, high speed data transmission rates up to 400 Mbits/s while significantly reducing cross talk, skew, and signal attenuation. By incorporating a serial, point-to-point cable, with low voltage differential signaling (LVDS) reduced costs are realized through an easily integrated data transmission cable. These features allow Spacewire cables to be incorporated across various satellite programs without the expense of costly design customization.

Spacewire: The Space Industry Data Transmission Standard

Glenair Spacewire assemblies begin with a high performance cable built with expanded polytetraflouroethylene (ePTFE) insulation. This material allows for low-loss transmission of LVDS signals maximizing data-rates while allowing for the implementation of standard hardware protocols, thus eliminating the need for design customization and long lead time cable projects.

TYPICAL USES INCLUDE

- EGSE applications
- · Radar sensor systems
- Hi-resolution camera equipment
- Sensor, mass-memory unit, and telemetry subsystem interconnections

APPROVED FOR USE BY:

- ESA
- NASA
- JAXA
- RKA

- Laboratory and Space Grade **Versions Available**
- Qualified MIL-DTL-83513 **Micro-D Connector**
- Gold Plated Copper Alloy TwistPin Contacts
- Basic Cable, 4 Twisted Pair Cables and a Ground
- Epoxy Resin Potting
- EMI Banding Backshell

PERFORMANCE

- 3 Amps
- Temperature Tolerance -200°C to +180°C
- 100 Ω Impedance Shielded Signal Pair
- Very Low Skew, Signal Attenuation and Cross Talk
- 65dB Minimum Attenuation **Shielding Effectiveness**
- Low Magnetic Permeability IAW EIA-364-54

Spacewire

Technical specifications • How-to-order



NOTES:

- 1. Flight grade (cable Type F) assemblies to be screened IAW NASA EEE-INST-002, Table 2. Level 1 with 100% thermal vacuum outgassing (24 hours/+125°C/10⁻⁶ torr). Reference Glenair Mod Code 429C.
- 2. Operating temperature 200°C to +180°C. Reference Glenair Mod Code 428.
- 3. Electrical performance: Dielectric withstanding voltage: 600 VAC. Insulation resistance: 5000 megohms @500 VDC.
- 4. Assembly to be identified with Glenair's name, Part Number, Cage Code and Date Code or ESCC Component Part Marking Standards.


MATERIALS/FINISH:


- Shells/backshells aluminum alloy/electroless
- · Insulators high grade rigid dielectric/N.A.
- · Contacts copper alloy, gold plated.
- Hardware stainless steel/passivated.


Back To Back Wiring Diagram (GP)




Single Ended Wiring Diagram (P)









How To Order Spacewire*											
Sample Part Number		GSWM	2	L	-9	GP	-6	F	В	-16	S
Product Series	GSWM–Glenair Spacewire Micro-D										
Shell Plating	2–Electroless Nickel 5–Gold	2-Electroless Nickel 5-Gold									
Insulator Material	L -LCP	-LCP									
Shell Size	9										
Connector Type	P-Single Ended Pin (Plug) GP-Pin (Plug) Connector Both Ends										
Wire Gauge	-6 –26 AWG -8 –28 AWG -0 –30 AWG (30 AWG–Lab Only)										
Cable Type	F–Flight Grade L–Lab Grade										
Termination Option	B –Backshell										
Cable Length In Inches	-16 = 16 inches (12 inches minimum)										
Hardware	S–Male Slotted Jackscrew P–Female Jackpost	-Male Slotted Jackscrew P-Female Jackpost									


^{*}Use Mod Code 428 for high-temp version and Mod Code 429C for NASA thermal outgassing

^{© 2014} Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324



MasterLatch (GMLM) Quick-release locking Micro-D connector pairs are equipped with a precision latching and locking mechanism. The single thumb latch on the plug side actuates a pair of locking latches that mate quickly and reliably to GMLM receptacles. These TwistPin equipped, low-insertion-force connectors meet all the standard performance requirements of MIL-DTL-83513 including vibration, shock, and mating durability. Choose from 6 different insert arrangements, with 9 to 37 contacts. The unique ergonomic latching mechanism can be easily activated with a thumb and forefinger grip even when wearing gloves, or when difficult access to connector pairs makes the use of jacking hardware and tools impossible.

Face view pin connector - Micro-D contact arrangements





SERIES GMLM

MasterLatch®



Quick-disconnect Micro-D





MasterLatch™ GMLM connectors are sold as prewired pigtails only, with 18 inch wire leads. Contact factory for alternative lengths.

MATERIAL AND FINISH

- Insulator: Liquid crystal polymer or PPS
- Wire: M22759/11 600 Vrms
 Fluoropolyer (TFE) or M22759/33
 600 Vrms Modified Cross-Linked
 Fluoroplastic (ETFE)
- Pin Contacts: Gold-plated beryllium copper alloy
- Socket Contacts: Gold-plated phosphor bronze allov
- Shell: Aluminum alloy with choice of cadmium plate, electroless nickel, black anodize, gold, or chem film
- · Latching mechanism: Stainless steel



www.glenair.com U.S. CAGE code 06324

E-10 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

Precision latch meets

vibration and shock

latching mechanism

Low insertion force

TwistPin contacts

■ Easy-to-activate

MIL-DTL-83513



The Micro-D connector for serious. high-temperature applications

Standard Micro-D connectors are rated for +125°C. Glenair's MWDM Micro-D can withstand +150°C continuous operating temperature and can be upgraded to +200°C if assembled with special high temperature epoxies. But oil, gas and geothermal wells can subject electronic instruments to temperatures as high as +260°C. The GHTM Series Micro-D meets the need for a high density, high performance connector capable of handling this temperature. The GHTM features contacts made from a special alloy that resists softening when exposed to temperatures up to +260°C (500° F). Rugged passivated stainless steel shells and hardware, high temperature liquid crystal polymer (LCP) insulators allow these connectors to survive the most demanding environments. Unique angled mounting ears allow the Well-Master™ 260° to fit in confined spaces.

- +260°C Operating Temperature
- Angled Mounting Ears to Fit in Small Diameter Instruments
- High Reliability TwistPin **Contact System with Special High Temperature Alloy**
- .050" Pitch Contact Spacing for Reduced Size
- Solder Cup, Pre-Wired or








+260°C PCB Header


+260°C Cable Connector

HIGH TEMPERATURE Well-Master[™] 260° **GHTM Micro-D connectors**



In addition to extreme high temperature tolerance, and demating resistance to vibration and shock, the Glenair Well-Master™ 260° Micro-D connector features unique shell packaging designed to conform with the cylindrical shape of instrument housings. Special angled mounting ears facilitate incorporation of the connector into available space, and the Micro-D's overall reduced size compared to other rectangular connector solutions allows for more efficient utilization.








High Temperature Backto-Back Micro-D



High Temperature PCB Header



GHTM HIGH TEMPERATURE CONTACT ARRANGEMENTS



Mating face of pin connector. Socket connector contact numbers are reversed.

Materials and Finishes		
Contacts	Proprietary nickel alloy, gold plated	
Insulators	Liquid crystal polymer (LCP)	
Shell	Stainless steel, passivated	
Mounting Hardware	Stainless Steel	
Insulated Wire	Nickel-coated copper, PTFE insulation per M22759/87 (260°C)	


Specifications				
Current Rating	3 Amps			
Contact Resistance	8 milliohms maximum			
Dielectric Withstanding Voltage	600 Vac sea level			
Insulation Resistance	5000 megohms minimum			
Operating Temperature	-55° C. to +260° C.			
Shock	50 g.			
Vibration	20 g.			



Micro-Crimp

The ultraminiature crimp contact rectangular with advanced environmental and EMC performance

- Crimp, PCB, fiber optic, coax, power and pitot
- Precision machined aluminum shells sealed to IP67
- High-density #23 contact arrangements set on .076 centers
- Blind mating for rack and panel applications
- **■** Environmental, hermetic and filter versions
- Integrated ground spring for improved EMI shielding



SERIES 79
Micro-Crimp

MICRCCRIMP®

High-reliability crimp contact performance

SERIES 79 MICRO-CRIMP PRODUCT SELECTION GUIDE







Crimp Terminated Panel Mount Connectors

Blind Mate Guide Pins and Sockets



Straight PCB Panel Mount and Free-Standing Connectors



Right Angle PCB Panel Mount and Free-Standing Connectors



Backshells and Accessories, EMI Adapters and Protective Covers

Selected Contact Types







Standard Signal

ınal l

Coaxial







0 11



Fiber Optic

Pitot Tube

Shell	Contact	Cont	Contact Quantity			
Size	Arrangement	#23	#16	#12		
Α	A-5	5	_	_		
В	B-2P2	_	2	_		
D	B-9	9	_	_		
C	C-13	13	_	_		
D	D-15	15	_	_		
	D-3P3	_	3	_		
	D-7P2	5	2	_		
	E-11P2	9	2			
E	E-19	19		_		
	E-7P3	4	3			

Connector may be supplied with

stainless steel non-removable

guide pins.

_					
	Shell	Contact	Cont	act Qua	ntity
	Size	Arrangement	#23	#16	#12
		F-15P2	13	2	_
	F	F-23	23	_	_
		F-5P5	_	5	_
	G	G-33	33	_	
		H-10P4	6	_	4
		H-29P7	22	7	_
	1	H-36P2	34	_	2
	Н	H-54P2	52	2	_
		H-5P5	_	_	5
		H-66	66	_	_

	Shell			act Qua	ntity
	Size	Arrangement	#23	#16	#12
		J-17P4	13	4	_
		J-25P2	23	2	_
	J	J-33	33	_	_
		J-7P7	_	7	_
	K	K-27P4	23	4	_
		K-35P2	33	2	_
		K-43	43	_	_
		K-9P9	_	9	_
	1	L-6P6	_	_	6
	ı	L-78	78		
	M	M-102	102		

	Performance Specifications			
renormance specifications				
Current rating	Contact size #23 5 Amps, size #16 13 Amps, size #12 23 Amps maximum			
Voltage rating (DWV)	Contact size #23 500 VAC rms. size #16 and #12 1800 VAC rms. Sea level.			
Insulation resistance	5000 megohms minimum			
Operating temperature	-65° C. to +150° C.			
Contact resistance	5 milliohms maximum			
Water ingress protection	IP67			
Shielding effectiveness	>75 dB attenuation from 100 MHz to 1000MHz, >60dB 1GHz to 4GHz, >40dB 4GHz to 10GHz.			

Connector may be supplied with

stainless steel non-removable

bushings.



contact Glenair at
818-247-6000 or
visit our website at
www.glenair.com
U.S. CAGE code 06324



Lightweight Composite Modular Connectors

Drop-in replacements for legacy modular rectangular connectors save weight, space, and assembly time

Today's high-performance commercial aircraft are looking for revolutionary materials and product designs that can reduce weight and improve reliability and performance. The Glenair Series 20 Super-Twin™ lightweight modular connector is a drop-in replacement for legacy cable and panel connectors that no longer meet these performance specifications—especially for ease of assembly, electromagnetic compatibility and size, weight and power optimization.

The Glenair Series 20 Super-Twin[™] can accommodate a broad range of contact sizes and types from #23 to #8 signal, Quadrax, El Ochito®, power, and fiber. Modular inserts offer fast and flexible assembly and repair. Peripheral and grommet seals provide

> outstanding environmental protection. Keyed inserts and shells provide versatile polarization and protection against mis-mating. The innovative clamshell and banding porch design brings modern, state-of-the-art connector capabilities to modular cable and panel

- For reduced size and weight cable and panel applications
- **■** Lightweight composite shell with integral strain relief/banding porch
- Modular inserts support a wide range of contact sizes and types up to #8
- Polarization both shell and inserts
- Center jackscrew with self-locking hardware




SERIES 20 Super-Twin™ **Lightweight Composite Modular Connectors**



SUPER-TWIN™ SHELLS AND INSERTS ARE ORDERED SEPARATELY


How To Order - Shells						
Sample Part Number	200-013	Р	2	-XM	31	K
Series 20 Modular Connector	200-013 Plug Shell 200-014 Receptacle Shell					
Plug/Receptacle	P = Plug Shell, R = Receptacle Shell					
Size	Size 2					
Finish	XM = Electroless Nickel XB = No plating, black					
Polarization Code	2 digits: First digit 1 – 4 (factory installed) Second digit 1 – 4 (factory installed) Blank = keys supplied as kit					
MicroBand Option	K = MicroBand supplied. Blank = no MicroBand					

How To Order - Inserts						
Sample Part Number	200-005	P	2	-60	Α	
Series 20 Modular Connector	200-005 Pin Insert 200-006 Socket Insert					
Pin/Socket Insert	P = Pin Insert, S = Socket Insert					
Size	Size 2					
Insert Pattern	60 = 60X #23 contacts					
Polarization	A, B, C, D, E, F, G, H (must match with shell polarization)					





PATTERN 48 DWV@50 000 ft = 800 VAC




000000



PATTERN 21 21 X Size 20 Contact DWV= 1500 VAC





PATTERN 10

Weight Study, Typical **Regional Jet Airframe**

Series 20 SuperTwin™ Mated Pair: 67g Weight/Plane: 7,661g

Legacy rectangular: aluminum Mated Pair: 192g Weight/Plane: 22,103g

Legacy rectangular: composite Mated Pair: 141a Weight/Plane: 16,123g

Summary:

Using Series 20 composite instead of legacy aluminum connector saves 14,442 grams (31.8 lbs) per plane.

Using Series 20 composite instead of legacy composite connector saves **8,482 grams** (18.6 lbs) per plane

Series 20 Super-Twin™ **Performance**

DWV	1500 Vac; 750 VAC (#23 contacts)
Shell-to-Shell	2.5 mΩ
Temp Range	-65°C / +125 °C
Shock*	50 g, half sine, 18x
Vibration*	Random, 8 hrs/ axis, Type VI, cond. G (27.8 g)
Altitude Immersion*	12.1 kPa (15000 m / 49000 ft)
Lightning Indirect Effects	3 kA min

*Test by similarity, Series 79 Micro-Crimp



Keyed, snap-in-place insert modules are currently available in six tooled layouts, accommodating size #23, #20, #16, #12 and keyed size #8 contacts (for use with Quadrax or El Ochito™ contacts).





SERIES 28

HiPer-D Connectors


High-performance M24308 intermateable

The HiPer-D connector is a M24308-type D-Subminiature connector with superior design features. Unlike standard M24308 connectors with stamped steel shells, the HiPer-D connector features a one-piece machined shell, and is rated for 200°C continuous operating temperature. Aerospace grade fluorosilicone grommets and face seals provide environmental protection. The HiPer-D is intermateable, intermountable and interchangeable with standard M24308 D-Sub connectors. A ground spring offers enhanced EMI/RFI protection. New Combo-D insert arrangements for Coax, Quadrax, fiber and El Ochito® contacts now available.

- 11 standard and 20 combo insert arrangements
- High temperature epoxy insulators
- Watertight sealing
- Rugged machined one-piece shell



STANDARD AND HIGH DENSITY CONTACT ARRANGEMENTS (face view of pin connector)



SERIES 28 M24308 INTERMATEABLE HiPer-D[®] Connectors



Enhanced Panel Mount Technology



Combo HiPer-D Contact Arrangements



Ground Spring for Improved EMC




Advanced Board

Modern EMI backshells



COMBO-D CONTACT ARRANGEMENTS (face view of pin connector)








SERIES 240 **ARINC 600 Filter connectors**

Fast, reliable in-house manufacturing







Insert 24 20 #20

Insert 04

4 #12

3 #16


4 #8 Twinax

000000 00000 00000

Insert 16

24 #20

Insert 02 150 #22



Insert 17 60 #20



6 #8 Twinax (Grounded)

Insert 15 110 #22



Also available: ARINC 404 and build-to-order

> **ARINC filter** utions. Consult factory for more

(for cavity C)








Insert 12 10 #8 Twinax (grounded)



2 #8 (Twinax)








00000 0000


Insert 22



Insert blank (for cavity

ARINC 600 SIZE 1 INSERT ARRANGEMENTS







Insert 03

1 #12

2 #16


2 #5 Coax






Insert 19

40 #22







Insert 21

Capa	citor Array Code / Ca	pacitance Range
Class	Pi - Circuit (pF)	C - Circuit (pF)
Х	160,000 - 240,000	80,000 - 120,000
Υ	80,000 - 120,000	40,000 - 60,000
Z	60,000 - 90,000	30,000 - 45,000
Α	38,000 - 56,000	19,000 - 28,000
В	32,000 - 45,000	16,000 - 22,500
С	18,000 - 33,000	9,000 - 16,500
D	8,000 - 12,000	4,000 - 6,000
E	3,300 - 5,000	1,650 - 2,500
F	800 - 1,300	400 - 650
G	400 - 600	200 - 300

70-120

the entire test procedure ensuring field reliability.

SERIES 240

ARINC 600

Filter Connectors

Glenair manufactures a full range of ARINC 600 filter connectors for use in EMC/EMP management

the ARINC 600 specification, and are designed to mate with ARINC 600 plugs with the same insert

configuration and opposite contact gender. Planar filter arrays and TVS diodes may be integrated

into both standard catalog as well as build-to-order configurations. Glenair's state-of-the-art diode burn-in process tests leaded and surface mount diodes with leakage current monitored throughout

of electronic systems and interconnect cabling. All connectors are designed in accordance with

applications.

ARINC 600 size 2 filter connector. Glenair also manufactures narrowprofile size 1 and double-wide size 3. All configurations are environmentally sealed for rugged airframe

- Planar, multilayer ceramic capacitive filters, with and without transient voltage suppression diodes
- C and Pi electrical configurations
- PC tail or solder cup wire termination
- 36 240,000 pF capacitance
- Insert arrangements IAW **ARINC 600**
- Fast and reliable diode burn-in and test services
- **■** Turnkey in-house manufacturing of all filter connector elements and processes

35-60

QPL AND COMMERCIAL

Fiber Optic and **Opto-Electronic** Interconnect Solutions

For land, sea, air, space, and C4ISR applications

Glenair.

FIBER OPTIC









MIL-DTL-38999 Type Fiber Optic

GHD High Density Fiber Optic

Series 80 Mighty Mouse Fiber Optic







MIL-PRF-28876 Fiber Optic

GFOCA M83526 Compliant Fiber Optic

Eye-Beam[™] Expanded Beam Fiber Optic

Opto-Electronic Interconnect Solutions







Size 8 Cavity Opto-Electronic Contacts

PCB-Mount Opto-Electronic Transceivers

Harsh-Environment Opto-Electronic Connectors









Signal Aggregation Media Converters

Glenair Fiber Optic and Opto-Electronic interconnect technologies deliver high data rate and bandwidth, reduced size and weight, EMI immunity, enhanced security, and spark/arc immunity. Our broad offering of fiber optic systems includes qualified MIL-PRF-28876 connectors and termini for shipboard applications, MIL-DTL-38999 Series III type fiber optic connectors and termini for aerospace applications, as well as our revolutionary Eye-Beam™ Expanded Beam termini. Small form-factor Opto-Electronic solutions are offered for harsh-environment Ethernet, video, high-speed data, and signal aggregation.

OPTO-ELECTRONIC INTERCONNECT SOLUTIONS

© 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324



Now Available: Glenair Series 185-002 Hi-Beam™ MIL-DTL-83526/20 and /21 compliant and intermateable hermaphroditic expanded beam comnnectors



For more information contact Glenair at 818-247-6000 or visit our website at www.glenair.com U.S. CAGE code 06324

TIGHT-TOLERANCE MIL-DTL-38999 Series III type plug and square flange wall-mount receptacle

MIL-DTL-38999 **Series III Type**

Fiber optic connection system

The high perfomance fiber optic interconnect system successfully deployed in hundreds of commercial and military aerospace

and other applications-from F-16 upgrade systems to the revolutionary F-35 **Joint Strike Fighter**



Terminated and tested point-to-point and multibranch D38999 type fiber optic cable assemblies

- MIL-DTL-38999 type tight tolerance fiber optic connectors
- Composite, aluminum and stainless steel shells available
- Qualified size #16 MIL-PRF-29504 precision ceramic termini
- Singlemode and multimode fiber, from 9/125 to 1000 microns
- Ultra-low insertion loss values, <.50dB typical
- From 2 to 37 Termini
- Plug and In-Line, Jam **Nut and Square Flange** Receptacles
- Patented MIL-DTL-38999 fiber optic test probes and adapters

TIGHT-TOLERANCE

MIL-DTL-38999 Series III Type

Advanced fiber optic connection system





MIL-DTL-38999 type fiber optic connection system termination, inspection, test, and cleaning tools are available now from Glenair. We also offer comprehensive F/O training services for assembly and maintenance technicians.



Glenair optical fiber test probes and connector adapters provide accurate and repeatable testing of MIL-DTL-38999 F/O assemblies

Glenair M29504/4 and /5 QPL termini are in stock and ready for immediate, same-day shipment





A complete range of metal and composite backshells and protective covers is available

MIL-PRF-29504/04 and /05 Fiber Optic Termini Performance Data				
Test Type	Performance Requirement			
Operating Temperature	-55°C to +165°C (dependent on epoxy and cable)			
Temperature Cycling	-65°C to +175°C			
Thermal Shock	-55°C to +150°C, 5 cycles			
Temperature Life	+150°C for 1,000 hours			
Random Vibration	20-2,000 Hz, 42.2 g's			
Shock (Half-sine Pulse)	300 g Peak Load			
Mechanical Shock	MIL-S-901, Grade A, Type B, Class I			
Mating Durability	500 cycles (cleaning after 100 matings)			
Salt Spray	48 hours (Terminus only)			
Cable Retention Force	22.0 lbs (dependent on cable construction)			

D38999 Type Fiber Optic Connector Part Numbers		
Glenair Dwg. Number*	Product Description	
181-001	#16 Socket Terminus	
181-002	#16 Pin Terminus	
181-048	#16 Dummy Terminus	
180-091 (05)	In-Line Receptacle Connector	
180-091 (06)	Plug Connector	
180-091 (08)	Jam Nut Mount Receptacle Connector	
180-091 (H7)	Square Flange Wall Mount Receptacle with Round Holes	
180-091 (S7)	Square Flange Wall Mount Receptacle with Slotted Holes	
180-091 (T7)	Square Flange Wall Mount Receptacle with Tapped Holes	
* See fiber optic catalog for complete part number information		

INSERT ARRANGEMENTS





4 x 16 Ga



Shell Size 15










Shell Size 21







Shell Size 25

Per MIL-STD-1560. Mating face of pin insert shown.



Density (GHD)

Fiber optic connection system

The system of choice for military and commercial air, space and other applications: **Outstanding optical and environmental** performance with nearly double the density of standard mil-spec designs







with alignment sleeve retainer, and square flange receptacle. Termini available in keyed and nonkeyed styles

- Innovative #18 (1.25mm ferrule) front-release genderless termini accommodate 900µ to 2.0mm jacketed fiber
- M85045/16 cable accommodation
- Composite, aluminum and stainless steel shells available
- Single keying for APC polish available
- Better optical performance than D38999 with nearly double the density
- Precision alignment sleeve retainer with integrated guide pins
- Piston o-ring sealing submersible design

SIZE- AND WEIGHT-SAVING **Glenair High Density (GHD)** Fiber optic connection system



Glenair High Density (GHD) Insert arrangements Alignment Pin, Alignment Pin, Arrangement 6 Shell Size 19 Plug face marking with removable alignment sleeve retainer (ASR) shown. Receptacle face - opposite.

ASR includes two guide pins and a threaded center jackscrew

Fiber Optic Pin Termini Specifications			
Assembly Dash Number		Fiber Size Core/Cladding	A Dia. [microns]
Keyed 181-047-1255C	Non-Keyed 181-056-1255C	9/125 (Singlemode)	125.5
181-047-1260C	181-056-1260C	9/125, 50/125, 62.5/125	126.0
181-047-1270C	181-056-1270C	50/125, 62.5/125	127.0
181-047-1420C	181-056-1420C	100/140	142.0
181-047-1450C	181-056-1450C	100/140	145.0
181-047-1560C	181-056-1560C	62.5/125/155 (Polyimide)	156.0
181-047-1570C	181-056-1570C	62.5/125/155 (Polyimide)	157.0
181-047-1730C	181-056-1730C	100/140/172 (Polyimide)	173.0
181-047-1750C	181-056-1750C	100/140/172 (Polyimide)	175.0
181-047-2360C	181-056-2360C	200/233	236.0
181-047-2860C	181-056-2860C	200/280	286.0
Crimp Sleeve is supplied with Terminus Assembly, and may be ordered separately. For terminus less crimp sleeve, omit C from end of part number (e.g. 181-056-1260)			


terminus iess crimp sieeve, omit C from end	or part number (e.g. 181-056-1260)
Glenair High Densit	y (GHD) Features
Alignment Sleeve Retainer Alignment Pin	O-Ring Seal
D38999 Series III S	tyle Coupling
Five Alternate Key Positions:	A, B, C, D, E (N = Normal)

GHD Fiber Optic Part Number Reference		
Glenair Dwg. Number	Product Description	
181-047	#18 Pin Terminus, Keyed for APC Polish	
181-056	#18 Pin Terminus (non-keyed)	
181-058	#18 Dummy Terminus	
180-122 (05)	In-Line Receptacle Connector	
180-122 (06) Plug Connector with Alignment Sleeve Retain		
180-122 (08) Jam Nut Mount Receptacle Connector		
180-122 (H7) Square Flange Receptacle with Round Holes		
180-122 (S7) Square Flange Receptacle with Slotted Holes		
* See fiber optic catalog for complete part number information		

Pin Density Comparison: Glenair High Density Versus D38999 and M28876 11 13 15 17 19 21 23 25 Connector Style / Size D38999 Cavity Count 2 | 4 | 5 | 8 | 11 | 16 | 21 | 29/37 2 | 4 | 8 | N/A | N/A | N/A | 31 | N/A M28876 Cavity Count **GHD Cavity Count** 4 6 16 20 30 40 52 70









with 181-075 socket termini

- Three snap-in, rear release fiber optic termini sizes: #23, #20HD, and #16 for use in any Series 80 Mighty Mouse connector
- The smallest mil-aero caliber fiber optic connection system available
- Singlemode and multimode
- Precision ceramic ferrules
- <0.5 dB typical attenuation</p>
- 1 to 130 channels



The perfect marriage of high bandwidth fiber optics with ultra-miniature packaging—half the size of D38999

SIZE #16 FIBER OPTIC TERMINI



Termini	Optical Fiber	Part Number	Α	Fiber Size
Type	Type	Part Number	Ferrule I.D.	Core/Cladding
Pin	Multi Mode	181-057-126	126.0 microns	50/125, 62.5/125
PIN	Single Mode	181-057-125	125.5 microns	9/125
Caaliat	Multi Mode	181-075-126	126.0 microns	50/125, 62.5/125
Socket	Single Mode	181-075-125	125.5 microns	9/125

^{*}Consult factory for additional sizes

Series 801 9-4 with size #16 fiber optic termini vs. equivalent functionality

Shell size 9, 4 channel 6 Grams (less termini)



Shell size 13, 4 channel 27 Grams (less termini)

SIZE #20HD FIBER OPTIC TERMINI

181-085 Socket 181-084 Pin Terminus

Termini Type	Optical Fiber Type	Part Number	A Ferrule I.D.*	Fiber Size Core/Cladding
Pin	Multi Mode	181-084-126	126.0 microns	50/125, 62.5/125
PIII	Single Mode	181-084-1255	125.5 microns	9/125
Socket	Multi Mode	181-085-126	126.0 microns	50/125, 62.5/125
	Single Mode	181-085-1255	125.5 microns	9/125

^{*}Consult factory for additional sizes

Series 801 8-8 with size #20 HD fiber optic termini vs. equivalent functionali



Shell size 8, 8 channel 8 Grams (less termini)



D38999 Series III Shell size 17, 8 channel 40 Grams (less termini)

SIZE #23 FIBER OPTIC TERMINI

181-063 Pin Terminus

181-064 Socket

Termini Type	Optical Fiber Type	Part Number	A Ferrule I.D.	Fiber Size Core/Cladding*
Pin	Multi Mode	181-063-126	126.0 microns	50/125, 62.5/125
PIN	Single Mode	181-063-1255	125.5 microns	9/125
Socket	Multi Mode	181-064-126	126.0 microns	50/125, 62.5/125
Socket	Single Mode	181-064-1255	125.5 microns	9/125
*Consult factory for additional sizes				

Series 801 6-4 with size #23 fiber optic termini vs. equivalent functionalit





Shell size 6, 4 channel 5 Grams (less termini)


Shell size 13, 4 channel 21 Grams (less termini)

ULTRAMINIATURE Series 80 Mighty Mouse

Fiber optic connection system







Series 801/802 designator (*Series 805 designator) (†Series 802 designator)

See Series 80 Mighty Mouse catalog for connector ordering information. Order connectors less contacts and order fiber optic termini separately. Cavity numbers are mating face view of pin connectors.

^{© 2014} Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324



QPL AND COMMERCIAL

MIL-PRF-28876

Fiber optic connection system

Qualified MIL-PRF-28876 fiber optic connectors and MIL-PRF-29504 termini—Navy approved, in stock, and ready for immediate shipment



- Connectors qualified to the complete requirements of **MIL-PRF-28876 including** plugs, wall-mount receptacles, iam-nut mount receptacles and in-line receptacles
- Multiple shell sizes and insert arrangements, including 2, 4, 6, 8, 18 and 31 channel layouts
- Backshells in straight, 45° and 90° configurations
- Corrosion-resistant and environmentally sealed
- Qualified MIL-PRF-29504/14 and /15 pin and socket termini and /3 dummy terminus
- Connectors, backshells and protective covers available for immediate, same-day shipment

QPL AND COMMERCIAL MIL-PRF-28876



Fiber optic connection system

Connector/Backshell Types				
Connector Type	Backshell Type	MIL-Spec	Commercial Connector Type Code	
	None	M28876/1	03	
Wall Mount	Straight	M28876/2	13	
Receptacle	45°	M28876/3	23	
	90°	M28876/4	33	
In-Line Receptacle	Straight	M28876/5	15	
	None	M28876/6	06	
Dleas	Straight	M28876/7	16	
Plug	45°	M28876/8	26	
	90°	M28876/9	36	
	None	M28876/11	04	
Jam Nut	Straight	M28876/12	14	
Receptacle	45°	M28876/13	24	
	90°	M28876/14	34	


Con.	ied QPL-29504 d socket termini
Test Description	Performance Spec
Optical Insertion Loss, Multimode	-0.3 dB Typical (62.5/
Optical Insertion Loss, Singlemode	-0.3 dB Typical (9/125
	Rotter than -40 dB -

Optical Insertion Loss, Multimode	-0.3 dB Typical (62.5/125)	
Optical Insertion Loss, Singlemode	-0.3 dB Typical (9/125)	
Optical Back Reflection, Singlemode	Better than -40 dB - PC Polish • Better than -50 dB - Enhanced PC Polish	
Operating Temperature	-28°C to +65°C (MIL-Spec Epoxy and Cable) -55°C to +125°C (alternative Epoxy and Cable)	
Temperature (Thermal) Shock	-40°C to +70°C, 5 Cycles	
Temperature Cycling	-28°C to +65°C, 5 Cycles	
Temperature/Humidity Cycling	-10°C to +65°C, 10 Cycles, 240 hours, 98% RH	
Temperature Life Aging	+110°C, 240 hours, Dry Air	
Mating Durability	500 cycles	
Vibration - Sinusoidal	10 g Peak, 5-500 Hz sin./ 10.2 g RMS, 50-2000 Hz random	
Impact	8 Drops from 8 feet	
Crush Resistance	281 lbs, 7 Cycles	
Cable Pull Out Force - Termini	Termini: 22 lbs min for 1 minute Connector: 162 lbs min for 10 minutes	
Fluid Immersion	Turbine Fuel, Isopropyl Alcohol, Hydraulic Fluid, Lubricating Oil, Coolant, Tap- and seawater, 24 hrs	
Water Pressure	32 feet for 48 hours at +10°C to +35°C	
Mechanical Shock (High Impact)	MIL-S-901, Grade A, Type B, Class I	
Corrosion Resistance (Salt Spray)	500 hours	
Sand and Dust	12 hours	
Flammability	0.75 inch flame for 10 sec. mated, 1.50 inch flame for 60 sec. unmated	
*Performance Specifications/Requirements based on the use of MIL-PRF-24792 Epoxy and MIL-PRF-85045 Simplex and Breakout Shipboard Optical Fiber.		

Qualified Fiber Optic Termini				
Type	Military Part Number	A Dia (Microns)	Typical Fiber Type	
	M29504/14-4131C	126.0	Multi Mode	
Pin Termini	M29504/14-4132C	127.0	Multi Mode	
	M29504/14-4135C	142.0	Multi Mode	
	M29504/15-4171C	126.0	Multi Mode	
Socket Termini	M29504/15-4172C	127.0	Multi Mode	
	M29504/15-4175C	142.0	Multi Mode	
Dummy Terminus	M29504/3-4038			

Crimp sleeve is supplied with terminus assembly and may be ordered separately (see Table II). For terminus less crimp sleeve, omit **C** from end of part number. Consult factory for additional sizes.

> Terminated and tested MIL-PRF-28876 fiber optic cable assembly



© 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

Requirements/



M83526 COMPLIANT

GFOCA

Fiber optic connection system

F-10 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

GFOCA: the genderless, ruggedized, environmentally-sealed solution ideal for fiber optic battlefield communications— **TFOCA-II**® intermateable!



Turnkey point-to-point and pigtail **GFOCA** cable assembly



Factory Terminated Fiber Optic Cable Spool

- 4 channel singlemode and multimode configurations
- Designed IAW MIL-PRF-29504/16 and MIL-DTL-83526/16 and /17 drafts
- Discrete components or complete cable-on-reel solutions available
- Rugged field deployable system
- Corrosion resistant and environmentally sealed
- Low insertion loss 2.5mm diameter genderless butt joint termini
- Designed for both low speed analog and highspeed digital data

TFOCA-II® is a registered trademark of Amphenol Fiber Systems International

M83526 COMPLIANT **GFOCA**



Fiber optic connection system

GFOCA COMPONENTS AND CABLE-ON-REEL SOLUTIONS



GFOCA jam nut mount receptacle connector with lanyard-attached dust cover





GFOCA Performance Specifications			
Insertion Loss <.50 dB Typical			
Cable Pull Resistance	400 pounds minimium, 1 hour; applies to plug and strain relief receptacles		
Mating Durability	2000 Cycles		
Operating Temperature	-46° C to +71° C		
Storage Temperature	-55° C to +85° C		
Cable Diameter Accommodation	.190" Minimum to .379" Maximum		



Glenair GFOCA M83526 Compliant fiber optic connection system termination, inspection, test, and cleaning tools are available now from Glenair. We also offer comprehensive F/O training services for assembly and maintenance technicians.



Available Insert Cap	Key Configurations
Key 1	Key 2
2x·137 (3.5) 4x Cavity Marking 4x Cavity Marking 043 (1.1) 002 (0.1) Key Polarization	.082 (2.1) .084 (2.1) .162 (4.1) .162 (4.1) .157 (4.0) .159 (4.0)
Key 3	Key "U" (Universal)
.160 (4.1) .162 (4.1) .084 (2.1) .084 (2.1)	2x 160 (4.1)

GFOCA Part Number Reference				
Drawing Number	Product Description			
181-050	Pin Terminus			
180-050-S	Alignment Sleeve, Split, Ceramic			
181-059	Dummy Terminus			
180-145	Plug Connector, Hermaphroditic, 4 Channel			
180-146	Jam Nut Receptacle, 4 Channel			
180-147	Square Flange Receptacle, 4 Channel			
180-148	Jam Nut Receptacle, 4 Ch, Internal Mount			
180-149	Jam Nut Receptacle, 4 Channel, Internal Mount with Accessory Threads			
180-150	Jam Nut Receptacle, 4 Channel, Panel Mount with Accessory Threads			
180-153	Jam Nut Receptacle, 4 Channel, Internal Mount with Strain Relief			
180-137	Plug Connector, Hermaphroditic, 90°, 4 Channel			

GFOCA Genderless Termini Part Numbers						
Dash Number	Ø A (Microns)	Fiber Type (Typ)				
181-050-1255C	125.5	SM				
181-050-1260C	126.0	SM and MM				
SM: Singlemode MM: Multimode						
Consult Factory for Add	itional Sizes					



Eye-Beam[™]

Fiber optic connection system

Innovative expanded beam termini and factory-terminated jumpers deliver optimal performance in harsh environments



Eye-Beam[™] Expanded Beam fiber optic termini integrated into a tight-tolerance D38999 Series III type jam-nut receptacle connector

Factory terminated GRIN lens pin termini and GRIN lens socket termini on pigtail fibers allow for easy fusion splicing in the



- All the benefits of an expanded beam connection system built into a discrete, removable F/O terminus
- Factory-terminated F/O Eye-Beam™ termini easily integrated into any connector package
- Innovative expanded beam GRIN lens terminus expands signal 27X from a standard 9.3 micron fiber core
- Revolutionary design delivers low dB loss (1.5 dB multimode, 2.0 dB singlemode) performance while reducing maintenance, inspection and test costs
- Ultra-high precision ceramic sleeves and custom designed terminus bodies ensure perfect axial alignment

EXPANDED-BEAM

Eye-Beam™










	Table I: Eye-Beam [™] Termini								
Designator	Description	Connector Series							
Α	M29504/04 Style Pin (181-070)	MIL-DTL-38999 Series III							
A	Mighty Mouse Size 16 Pin (181-070)	Series 80 Mighty Mouse							
В	M29504/05 Style Socket, Springless (181-077)	MIL-DTL-38999 Series III							
C	M29504/14 Style Pin (181-095)	MIL-PRF-28876							
D	M29504/15 Style Socket (181-096)	MIL-PRF-28876							
F	Mighty Mouse Size 16 Socket (181-083)	Series 80 Mighty Mouse							
G	GFR Pin (181-082)	Glenair GFR System							
Н	GFR Socket (181-081)	Glenair GFR System							
J	GFOCA Termini (181-067)	GFOCA (hermaphroditic)							







Eye-Beam termini and factory-terminated jumpers may be integrated into a broad range of circular and rectangular connector packaging



F-12 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324



Industry standard ball lens expanded beam solution

In accordance with MIL-DTL-83526 /20 and /21 hermaphroditic

Commercial and military customers, such as those engaged in geo-physical exploration, mass-transit and tactical warfare now depend on optical interconnect technology due to its many advantages over electrical transmission systems. Sealed expanded beam interconnect technology prevents water, mud, dust, oil and other chemicals from contaminating the optical path and deteriorating system performance. Connector housings are available in a variety of material and finish choices, including cadmium-free and RoHS-compliant options. Boots, grips, and seals are available in a range of materials as well.

- Ball lens expanded beam IAW MIL-DTL-83526 /20 and /21
- Beam expansion dramatically reduces loss due to contamination
- Large ball lens facilitates easy cleaning
- Fully intermateable with all MIL-DTL-83526 /20 and /21 compliant connectors
- 2 and 4-channel insert arrangements
- Expanded beam lens insert also available in D38999 type packaging

SERIES 185-002 HI-BEAM™

MIL-DTL-83526 / 20 & / 21 compliant and

intermateable hermaphroditic expanded beam connectors

SERIES 185-002 HI-BEAM™ CONNECTORS AND CABLES



M83526/20 type Hermaphroditic Cable Plug Configuration

M83526/21 type
Panel-Mount Configuration

The Glenair 185-002 Hi-Beam™ connector series is a miniaturized connector suited for a vast array of applications. The innovative design ensures its ability for deployment in the toughest environments where high performance, total reliability and reduced package size are critical. Benefiting from low insertion loss expanded beam technology, the precision optical alignment system is tolerant of water, mud, dust and other contaminants. Hermaphroditic coupling eliminates the need for adapters and male and female mating halves. The 185-002 Hi-Beam™ is ideally suited for environmental extremes where low maintenance and rapid deployment are necessary. Connectors and cable assemblies are field installable and repairable.

Expanded Beam vs. Physical Contact Connectors

Physical Contact



Physical contact fiber optic connectors utilize butt-joint type contacts called termini. Mating pairs of termini may be integrated into virtually any connector shell design. The polished mating faces provide extremely low-loss transmission of optical signals but are best suited to clean and controlled environmental applications.

Expanded Beam



Expanded Beam connectors utilize a sealed lens to expand the emitting beam of light from the fiber media. The expanded beam is then refocused back into the fiber of the mating half. These sealed assemblies are ideally suited for environmental applications where optical connectors are subjected to repeated mating/unmating cycles.

Series 185-002 Hi-Beam™ Performance Specifications				
Insertion Loss	Multimode: 1.0 dB at 850/1300nm Singlemode: 1.5 dB at 1310/1550nm			
Return Loss	Singlemode: Better than 34 dB unmated			
Operating Temperature	-46°C to +71°C			
Storage Temperature	-57°C to +85°C			
Mating Durability	3000 mating cycles minimum			
Cable Retention	1500N (cable dependent)			
Bump	4000 bumps at 40g acceleration			
Impact	8 drops from 0.9m per TIA/EIA-455-2, Method C, Service Class: Severe			
Drop (Free Fall)	500 falls onto concrete from 1.2m			
Vibration - Sinusoidal	10g Peak per TIA/EIA-455-11, Test Condition III			
Vibration - Random	9g RMS per TIA/EIA-455-11, Test Condition VI-C, for 1.5 hours			
Physical Shock (Half-sine Pulse)	50g Peak, 5 shocks per axis (30 shocks total) per TIA-455-14, Test Condition A			
Water Immersion	Depth of 15m for 24 hours per TIA-455-74			

HARSH-ENVIRONMENT Technology can be **Opto-Electronic** integrated into milstandard connectors or ruggedized packaging to suit any application **Interconnect Solutions**

Unlock the huge bandwidth of optical fiber and dramatically reduce the size and weight of interconnect systems

Glenair leverages its extensive portfolio of military and aerospace interconnect products to bring you ruggedized opto-electronic solutions, converting signals between the electrical domain and the fiber domain. These opto-electronic products are designed for harsh military/aerospace system and subsystem environments and will operate reliably over very wide temperature ranges and high shock and vibration conditions; they have been optimized to minimize size, weight and power and offer electrical-to-fiber conversion for Ethernet, video, signal aggregation and high-speed digital signals.

Glenair also offers integration of electronics or opto-electronics into rugged connector packages and cable assemblies per specific customer requirements. We offer

rapid response in-house electrical/PCB design, and mechanical connector/backshell engineering from our vertically intergrated factory. Our product portfolio is constantly evolving. Please contact Glenair for the latest developments, or custom solutions.

ADVANTAGES OF GLENAIR OPTO-ELECTRONICS

- Reduced size, weight, and power consumption
- Leverages the virtues of fiber optics: EMI immunity, network security, increased transmission distance and high bandwidth
- High shock and vibration to support mil/aero applications
- Wide operating temperature range: -40°C to +85°C and beyond
- Designed IAW military and aviation requirements: MIL-STD-883, MIL-STD-461, DO-160 and others

SERIES 050 OVERVIEW

Harsh-Environment, Small Form-Factor Opto-Electronic Interconnect Solutions







10Gbps at -65°C




10Gbps at +100°C




PROVEN-PERFORMANCE OPTO-ELECTRONIC INTERCONNECT SOLUTIONS

- Military, industry-standard and custom connector integration
- Custom aggregation media converters
- Integration of active components into cable assemblies
- Link testing and qualification

Laboratory link test and qualification data for harsh-environment opto-electronic solutions are available—just contact the factory




SMPTE 3G – SDI at -40°C Pathological Case 3



SMPTE 3G – SDI at +90°C Pathological Case 3










Opto-Electronic Contacts

Size 8 Opto-electronic contacts transmit and receive differential CML or LVPECL electrical signals over Multimode fiber optic cable. Transmitters consist of a laser driver or LED driver with a temperature compensation circuit to maintain optical power over the entire operating temperature range, and a 850nm VCSEL laser or a 1300nm LED. Receivers consist of a PIN Photo Detector, a Transimpedance Amplifier with automatic gain control circuit, and a Limiting Amplifier. Differential output data signals are LVPECL or CML compatible. The transmitter has a Tx Disable pin to turn off transmitter output.



- Transmit (Tx) and Receive (Rx) Opto-Electronic contacts for use in **ARINC 600 and other** size #8 cavity equipped connectors
- Current offerings include 1.25mm ARINC 801 and 2.5mm ELIO® solutions



4.25 Gbps / +25°C

- Fast and Gigabit Ethernet, **DVI, HDMI video capable** transmitter and receiverequipped contacts
- ARINC 664, 801, 803, 804 and 818 standard compliant
- Link distances up to 500 meters, multimode
- Single, 3.3 V power supply
- Wave-solderable termination with RoHScompliant solders



Evaluation Test Boards Available

Size 8 Opto-Electronic Transmitter and Receiver Contacts for Ethernet, Video and **High-Speed Data**



PRODUCT SELECTION GUIDE


visit **glenair.com** for detailed product datasheets

TRANSMITTER AND RECEIVER CONTACTS, 850nm LASER, ARINC 801 1.25mm TERMINUS



Size 8 Opto-electronic contacts transmit and receive differential CML electrical signals over Multimode fiber optic cable. Transmitters consist of a laser driver with a temperature compensation circuit to maintain optical power over the entire operating temperature range, and a 850nm VCSEL laser. Receivers consist of an

850nm PIN Photo Detector, a Transimpedance Amplifier with automatic gain control circuit, and a Limiting Amplifier. Differential output data signals are CML compatible. The transmitter has a Tx Disable pin to turn off transmitter output and a Tx Fault pin to signal a fault condition. Receiver includes a CMOS compatible Loss of Signal Indicator to prevent invalid data.




TRANSMITTER AND RECEIVER CONTACTS, 850nm LASER, ELIO® 2.5mm TERMINUS



050-307

Size 8 Opto-electronic contacts transmit and receive differential CML electrical signals over Multimode fiber optic cable. Transmitters consist of a laser driver with a temperature compensation circuit to maintain optical power over the entire operating temperature range, and a 850nm VCSEL laser. Receivers consist of an 850nm PIN Photo Detector, a Transimpedance Amplifier with

automatic gain control circuit, and a Limiting Amplifier. Differential output data signals are CML compatible. The transmitter has a Tx Disable pin to turn off transmitter output and a Tx Fault pin to signal a fault condition. Receiver includes a CMOS compatible Loss of Signal Indicator to prevent invalid data.




TRANSMITTER AND RECEIVER CONTACTS, 1300 nm LED, ARINC 801 1.25mm TERMINUS



Size 8 Opto-electronic contacts transmit and receive differential LVPECL electrical signals over Multimode fiber optic cable. Transmitters consist of an LED driver with a temperature compensation circuit to maintain optical power over the entire operating temperature range, and a 1300nm LED. Receivers consist of a PIN Photo Detector, a

Transimpedance Amplifier with automatic gain control circuit, and a Limiting Amplifier. Differential output data signals are LVPECL. The transmitter has a Tx Disable pin to turn off transmitter output.



OPTO-ELECTRONIC CONTACT EVALUATION BOARD



The evaluation board is designed as an interface to allow evaluation of the size 8 transmitters or receivers. Devices are powered through the 3.3V and GND connections. For the transmitter fault pin can be monitored and the transmitter disable can be controlled via an external voltage supply. For

the receiver, loss of signal (LOS) state can be monitored.

Test configuration options:

- Transmitter only
- Receiver only, and
- Both transmitter and receiver either in a single link or two separate links.

F-18 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324



PCB-Mount Opto-Electronics

Connectorized, high-density, board-mount transceivers built for rugged vibration and shock applications up to 10Gbps

Glenair PCB mount transceivers are ruggedized harsh-environment equivalents to SFP transceivers but with mechanical design suited to the harsh temperature and vibration environments found in Military, Aerospace and Other applications. PCB mount optical transceivers support optional Digital Monitoring Interface (DMI) features in accordance with SFF 8472. The Transceiver is comprised of a transmitter section and a receiver section that reside on a common package and interface with a host board through a high-speed electrical connector.

- Smallest footprint available
- Passed jet fighter and space launch shock and vibration testing
- No soldering required
- CML 100 Ohm differential input and output
- -40°C to +85°C operating temperature range extended temperature ranges available



GC fiber optic connector retained with mounting screws to withstand high vibration and shock



PCB-mount opto-electronics feature Samtec high-speed surface-mount connectors



Dual-transceiver, Quad-Transmitter and Quad-Receiver form factor with ARINC 801 contacts



Evaluation boards for all PCB mount transceiver configurations are available

Harsh-Environment PCB-Mount Transceivers, Transmitters and Receivers



PRODUCT SELECTION GUIDE

visit **glenair.com** for detailed product datasheets

General Purpose Applications:

High-Speed Digital balanced signals (i.e. 4B/5B, 8B/10B, 62B/64B etc)
Fast Ethernet, Gigabit Ethernet, 10G Ethernet Fiber Channel (1X, 2X, 4X, 8X), ARINC 818, AFDX, SFPDP, Serial Rapid I/O (sRIO)

Video Applications

DVI, ARINC 818, SMPTE (SDI, HD-SDI, 3G-SDI)

Patte	40 Manual October 10 Manual Oc	Ó	Pop Rate (Glos)	(wu) How)	W. Ser.	John John	Mumber Trans	Number of Receivers	Fiber	N. General Poles	M / (U) 00/1	1000 SV APINS	0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0
050-315	PCB Mount OE Transceiver 5G, MMF	0.1–5	850	VCSEL	1	1	2	MMF	Υ	Υ	N	N	1m-500m
050-316	PCB Mount OE Dual-Transmitter 5G, MMF	0.1–5	850	VCSEL	2	0	2	MMF	Υ	Υ	N	N	1m-500m
050-317	PCB Mount OE Dual-Receiver 5G, MMF	0.1–5	850	N/A	0	2	2	MMF	Υ	Υ	N	N	1m-500m
050-318	PCB Mount OE Transceiver, 4G, SMF	0.1–4.25	1310	FP	1	1	2	SMF	Υ	Υ	N	N	1m-10km
050-319	PCB Mount OE Dual Transmitter, 1310nm FP, 4G, SMF	0.1–4.25	1310	FP	2	0	2	SMF	Υ	Υ	N	N	1m-10km
050-320	PCB Mount OE Dual Receiver, 1310nm, 4G, SMF	0.1-4.25	1310	N/A	0	2	2	SMF	Υ	Υ	N	N	1m-10km
050-321	PCB Mount OE Transceiver, 1300nm LED, 200M, MMF	0.052	1300	LED	1	1	2	MMF	Υ	N	N	N	2km
050-322	PCB mount 10Gbps XVR, 1310nm FP, 2km, SMF	5–10.5	1310	FP	1	1	2	SMF	Υ	Υ	N	N	1m-2km
050-324	PCB Mount OE Transceiver, 1310nm DFB, 4G, SMF	0.1-4.25	1310	DFB	1	1	2	SMF	Υ	Υ	N	N	1m-40km
050-325	PCB Mount OE Dual Transmitter, 1310nm DFB, 4G, SMF	0.1-4.25	1310	DFB	2	0	2	SMF	Υ	Υ	N	N	1m-40km
050-326	PCB Mount OE Dual Receiver, 1310nm DFB, 4G, SMF	0.1-4.25	1310	N/A	0	2	2	SMF	Υ	Υ	N	N	1m-40km
050-327	PCB mount 10Gbps SR Serial XVR, 850nm, MMF	5–10.5	850	VCSEL	1	1	2	MMF	Υ	Υ	N	N	1m-400m
050-328	PCB mount 10Gbps XVR, 1310nm DFB, 10km	5–10.5	1310	DFB	1	1	2	SMF	Υ	Υ	N	N	1m-10km
050-331	PCB Mount OE Dual-Transmitter SMPTE 3G-SDI	2.97	850	VCSEL	2	0	2	MMF	Ν	N	Υ	Υ	1m-1km
050-332	PCB Mount OE Dual-Receiver SMPTE 3G-SDI	2.97	850	N/A	0	2	2	MMF	N	N	Υ	Υ	1m-1km
050-333	PCB Mount OE Dual-Transceiver 5G MMF, ARINC 801	0.1–5	850	VCSEL	2	2	4	MMF	Υ	Υ	N	N	1m-500m
050-336	PCB Mount OE Quad-Transmitter 5G MMF, ARINC 801	0.1–5	850	VCSEL	4	0	4	MMF	Υ	Υ	N	N	1m-500m
050-337	PCB Mount OE Quad-Receiver 5G MMF, ARINC 801	0.1–5	850	N/A	0	4	4	MMF	Υ	Υ	N	N	1m-500m
050-339	PCB Mount OE Dual-Transceiver, 10G MMF, ARINC 801	0.1–5	850	VCSEL	2	2	4	MMF	Υ	Υ	N	N	1m-400m
050-340	SINGLE FIBER Bidirectional Transceiver, 2.5G, SMF	0.1–2.5	1310/1550	FP/FP	1	1	1	SMF	Υ	Υ	N	N	1m-2km
050-341	SINGLE FIBER Bidirectional Transceiver, 10G, SMF	5–10.5	1310/1550	DFB/DFB	1	1	1	SMF	Υ	Υ	N	N	1m-10km
050-342	CWDM Transceiver, 2.5G, SMF	0.1–2.5	CWDM	DFB	1	1	2	SMF	Υ	Υ	N	N	1m-20km
050-343	CWDM Transceiver, 10G, SMF	5–10.5	CWDM	DFB	1	1	2	SMF	Υ	Υ	N	N	1m-10km

	Evaluation Boards						
Part No.	Description	for testing Part Number(s)					
050-329	EVALUATION BOARD supporting Board Mount Transceivers, 1-10Gbps	050-315, 050-318, 050-321, 050-324					
050-330	EVALUATION BOARD supporting Board Mount Dual Transmitters and Board Mount dual Receivers	050-316, 050-317, 050-319, 050-320, 050-325, 050-326, 050-331, 050-332					
050-334	EVALUATION BOARD supporting PCB Mount Dual-Transceiver 050-333+	050-333					
050-338	EVALUATION BOARD	050-336, 050-337					
050-344	FMC Connectivity Card	All Glenair PCB Mount Components					

	Accessories					
Part No.	Description	Details				
FA02454	Fiber Optic jumper cable, GC	Singlemode or multimode connects transceiver to mil/aero connector				
FA03286	Fiber Optic jumper cable, ARINC 801	Singlemode or multimode connects transceiver to mil/aero connector				
059-0007	PCB Threaded Insert	Simplifies installation of PCB transceivers				



Opto-Electronic Connectors

Environmentally sealed, D38999 type triple-start connectors housing turnkey copper-to-fiber transceiver technology

Glenair is able to offer our Opto-Electronic solutions customers turnkey multichannel receptacle connectors housing integrated transceiver technology for fast/gigabit Ethernet, DVI and HDMI video, as well as various high-speed data transfer protocols. The two available connector designs incorporate Glenair small form-factor ARINC 801 type opto-electronic contacts (050-301) or an ELIO® equipped configuration that intermates with the standard ELIO®2.5mm fiber optic terminus (050-307). Receptacles are populated with factory-tested size #8 contacts, and are ready for immediate use as fiber-optic-to-electrical circuit board I/O connectors. Special size #8 cavity adapters are also available to enable construction of compatible plug connectors on the cable side.



Special size #8 cavity adapters facilitate construction of standard fiber optic plug connectors that intermate with the size #8 opto-electronic transceiver contacts



- Catalog solutions include:
 2.5mm ELIO® solution for multimode Ethernet, video, and high-speed data applications
 1.25mm ARINC 801 multimode fiber optic termini solution for Ethernet, video, and high-
- Made-to-order configurations with a wide range of connector packages including Glenair Series 80 Mighty Mouse

speed data

Opto-electronic receptacle connectors are populated with size #8 contacts, and ready for immediate assembly in I/O to circuit board applications

ELIO® is a registered trademark of SOURIAU


Opto-Electronic Connectors for Ethernet, Video, and High-Speed Data Applications



PRODUCT SELECTION GUIDE

visit **glenair.com** for detailed product datasheets

	Part No.	Description
	050-304	O50-304 MIL-DTL-38999 Series III Type Receptacle Connectors with Size 8 Opto-Electronic Contacts The 050-304 series of Active Opto-electronic sealed panel mount connectors offers customers the power to convert from electrical to fiber optic signals within a D38999 connector to support high speed fiber optic transmission in harsh environments. The 050-304 incorporates size 8 active contacts in one of three standard configurations to enable optical Transmitters, optical Receivers or Optical Transceivers, or custom configurations.
	059-0001	059-0001 Size 8 cavity adapter kit for 1.25mm ARINC 801 terminus Size 8 cavity adapter will convert D38999 size 8 cavities (Twinax, Coax, Quadrax or power) into ARINC 801 fiber optic cavities. Kit includes the adapter and an ARINC 801 terminus.
	059-0002	059-0002 Size 8 cavity adapter for ELIO® 2.5mm terminus Size 8 cavity adapter will convert D38999 size 8 cavities (Twinax, Coax, Quadrax or power) into ELIO® fiber optic cavities per EN4531.
(patent pending)	050-313	050-313 Opto-Electronic Transceiver, MIL-DTL-38999 Type 2.5mm ELIO® Compatible, 100Mbps – 4.25Gbps Glenair 050-313 is a D38999 Type 11-02 receptacle connector incorporating an opto-electronic transceiver operating from 100Mbps to convert electrical signals to multimode fiber. The Glenair optical transceiver is ideal for harsh-environment, extreme shock, vibration and temperature avionics and military applications where copper cable link distance, bandwidth, weight or bulk make the use of twisted pair, Twinax or Quadrax copper conductors unacceptable.
	050-303	050-303 Opto-Electronic Receiver with Mighty Mouse connectors, 100Mbps – 2.5 Gbps Glenair 050-303 optical transceiver, connectorized with Series 805 Mighty Mouse connectors, employs state-of-the-art opto-electro-mechanical technology to provide effective harsh environment fiber-optic interconnect solutions for high-speed digital data.



Copper-to-Fiber **Media Converters**

Reduced form-factors for harshenvironment applications

Glenair offers turnkey harsh-environment media converters for in-line and select panel mount applications. The devices facilitate conversion of 10/100/1000BASE-SX/LX fiber optic gigabit Ethernet data streams to electrical signals servicing switches, routers, and other peripherals.

Designed for use in ruggedized applications such as geophysical, naval, commercial and military aerospace, these reduced form-factor

electrical-to-optical transceivers deliver proven performance with significant size and weight savings compared to conventional form-factor technologies. Available for a wide range of fiber optic formats, including 1.25mm, 1.6mm, 2.0mm, and 2.5mm ferrules, in both singlemode and multimode, Glenair's complete range of media converters meets virtually every fiber-optic-to-copper application requirement.

- Reduced form-factor devices for in-line conversion of electrical and optical signals
- Active cable versions that reduce the risk of damage to fiber optic interfaces
- Weight-saving technology that incorporates power and signal conversion functions
- Auto-negotiation 10/100/1000BASE-T to **100BASE-FX, 1000BASE-SX** and 1000BASE-LX
- Advanced monitor & control functions via serial interface to facilitate network management and BIT

Copper-to-Fiber Media Converters for Ethernet Applications PRODUCT SELECTION GUIDE



visit glenair.com for detailed product datasheets

EXAMPLE FUNCTIONAL BLOCK DIAGRAM FOR GLENAIR 050-105 ETHERNET MEDIA CONVERTER



050-105 10/100/1000BASE-T to 1000BASE-SX/LX Media Converter


1000BASE-SX

1000BASE-LX10

Code

-SX

-LX10



	Part No.	Description	Part No.	Description
	050-101	1000BASE-T to 1000BASE-SX/ LX Media Converter	050-112	10/100/1000BASE-T to SX, LX10, or FX Fiber Optic Ethernet, GFOCA Fiber Optic interface
	050-103	10/100/1000BASE-T to 1000BASE-SX/LX Media Converter with Mighty Mouse Connectors	050-113	10/100/1000BASE-T to SX, LX10, or FX Fiber Optic Ethernet, MIL-DTL-1560 interface
	050-104	10/100/1000BASE-T to 1000BASE-SX/LX Active Cable with Mighty Mouse Connectors	050-115	10/100/1000BASE-T to 1000BASE CWDM Media Converter
	050-110	10/100/1000BASE-T to 1000BASE-SX/LX, GFOCA, 38999 Quadrax (signal and BIT), 38999 (Power)	050-117	LRU Media Converter, Single or Dual Channel, 10/100/1000BASE-T to SX/LX Lightning Strike Protection DO160 level 3





Copper-to-Fiber **Media Converters**

Reduced form factor media converters for harsh-environment video applications

Glenair Copper-to-Fiber-Optic Video Media Converters enable extended link distances, improved EMI and security in harsh environments and provide solutions for both MMF and SMF applications. These media converters support ruggedized military systems applications and are tailored to support a variety of Video protocols including DVI, HDMI, SMPTE (SDI, HD-SDI and 3G-SDI), ARINC 818 and more. Many options for mil-spec and military-grade electrical and fiber optic connectors are available. Contact Glenair for custom configurations, application-specific designs and engineering




- Fiber Link 500m with MMF
- Fiber Link 10km with SMF
- 38999 with MIL-STD-1560 and custom contact arrangements—including quadrax and coaxial contact options
- Mighty Mouse electrical and fiber optic connectors
- **■** Fiber Optic connectors including D38999, M28876, GHD, NGCON (M64266), HMA (M83526), and GFOCA
- Power supply functions with wide input-voltage
- DVI, HDMI, SMPTE, **ARINC 818**
- Advanced monitor & control functions via serial interface to facilitate network management and BIT

Copper-to-Fiber Media Converters for Video Applications PRODUCT SELECTION GUIDE



visit glenair.com for detailed product datasheets

MIL-DTL-38999 SERIES III TYPE DVI VIDEO MEDIA CONVERTER




Video Media Converter Selection Guide				
	050-201	DVI Copper-to-Fiber Media Converter		
	050-203	DVI Copper-to-4-Fiber, VCSEL, DO160 Lightning Strike level 3 and "dirty" 28V power		
	050-206	4 Channel SMPTE HD-SDI & 3G-SDI Transmitter or Receiver		
	050-204	4 Channel 3G-SDI MMF TX and 3G-SDI MMF RX, GHD Fiber, Mighty Mouse (Coax and Power).		
	050-205	DVI Copper-to-Fiber Media Converter, Inline		

ENVIRONMENTAL PERFORMANCE



- -40°C to +85°C operating temperature range
- Meets MIL-STD-810 **Mechanical Shock and Vibration**
- Meets MIL-STD-1344 immersion resistance

VIDEO MEDIA CONVERTER FUNCTIONAL BLOCK DIAGRAM



F-26 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324



Copper-to-Fiber Media Converters

Combine multiple electrical signals into a high-speed fiber data stream

Glenair signal aggregation media converters integrate a set of compact opto-electronic modules to digitize and/or aggregate multiple common signal types, and combine them onto high-data-rate serial optical fiber channels. Silicon field-programmable gate array (FPGA) technology provides a flexible way to accommodate many signal I/O types.

	Signal Aggregation Media Converter Selection Guide						
050-501	12-Channel RS422 Copper-to-Fiber Media Converter						
050-502	6x RS-422 and 6x ARINC 429 Copper-to-Fiber Media Converter						
050-503	DVI/HDMI (Dual fiber) + USB(HID) interface (KVM) Copper-to-Fiber Media Converter						
050-504	CAN Bus "bridge" (ARINC 825), ARINC 429, ARINC 664 (AFDX ethernet) DO-160 compliant Copper-to-Fiber Media Covnerter						
050-505	2x Ethernet, 2xRS-422 or 2xRS-232 (422 & 232 not simultaneously) Copper-to-Fiber Media Converter						

- Dramatically reduce size, weight, wire count, and shielding of copper cables
- Leverage the high bandwidth of optical fiber by multiplexing many lowerdata-rate signals onto a few fibers
- One high-speed optoelectronic interface can serve practically all signal types
- Ideal solution to enable optical rotary joints
- -40°C to +85°C operating temperature range
- Meets MIL-STD-810 Mechanical Shock and Vibration
- Meets MIL-STD-1344 immersion resistance
- Advanced monitor & control functions via serial interface to facilitate network management and BIT


Copper-to-Fiber Media Converters Multiplexing Signal Aggregator PRODUCT SELECTION GUIDE





visit **glenair.com** for detailed product datasheets

SIGNAL AGGREGATOR FUNCTIONAL DIAGRAMS


- One compact LRU digitizes or aggregates multiple electrical signals on copper using an FPGA
- FPGA digitizes and serializes the signals onto a high-speed data stream
- Opto-electronic converters get the serialized signals on and off the optical fiber







FPGA MAIN BOARD AND DAUGHTER CARD ARCHITECTURE CAN HANDLE MANY SIGNAL TYPES



F-28 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

An en on head SMALL FORM-FACTOR

Ethernet Switches and Breakout **Cables**

Glenair unmanaged Ethernet switches are layer 2 switches with Auto negotiation and Auto MDI / MDIX circuitry that enables port expansion with IEEE-802.3U 10/100/1000Base-T

Ethernet ports. Developed for use in harsh environment applications, the electronics are incorporated into a panel-mountable housing that is sealed against liquid and solid contaminants and designed for shock and vibration resistance. Standard connector interfaces include high-performance size- and weight-saving Glenair Series 805 Mighty Mouse jam nut receptacles and M28876 type fiber-optic connectors.



- Unmanaged—plug and play operation—no configuration required
- Jumbo frame support in all speeds (10/100/1000 Mbps)
- Operating temperature range: -40°C to +85°C
- Standard ultraminiature **Mighty Mouse electrical** and M28876 type fiber optic connector interfaces
- Experienced optoelectronic engineering services available for special connector and form-factor configurations
- Breakout cables with industry-standard connector interfaces available

Small Form-Factor Ethernet Switches and Breakout Cables



PRODUCT SELECTION GUIDE

visit glenair.com for detailed product datasheets

052-101 7-PORT UNMANAGED ETHERNET SWITCH



Form 3 (heat sink)





Form 2 (with flanges)

■ 7 copper (10/100/1000 Mbps) Ethernet ports per IEEE 802.3:2005

- Non-Blocking switch fabric allows 1000 Mbps data rate on all 7 ports simultaneously
- Cable link distances up to 100 Meters (EIA/TIA Cat-5E)
- Full duplex flow control per IEEE Std 802.3X and half duplex back pressure, symmetric and asymmetric
- Shock, vibration and immersion resistant per MIL-STD-810F
- Auto sensing of half or full duplex operation
- Mighty Mouse Series 805 shell is water-tight to MIL-STD-810 when mated
- 3 form-factors available


050-118 5-PORT UNMANAGED ETHERNET SWITCH



- 1 PORT: 10/100/1000 BASE-T consistent with IEEE 802.3
- 4 PORTS: 1000BASE-LX (IEEE 802.3)
- Non-blocking switch fabric allows 1000 Mbps on all ports
- Material/Plating: Aluminum with Cadmium Olive Drab over electroless Nickel (500 hours salt spray plating)
- 6 Status LEDs to Denote: (Power, Ethernet activity with one LED for each of the 5 ports)
- 4 M28876 type fiber-optic connectors
- Mighty Mouse ultraminiature electrical connector interface
- IP67 in mated condition

BREAKOUT CABLES FOR 7-PORT ETHERNET SWITCH





F-30 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

Shrink Boots, Jackets, and Braided Shielding

for extreme environmental and EMI/RFI protection



Shrink Boots, Jackets, and Braided Shielding Product Selection Guide





Series 77 Full Nelson Environmental Heat Shrink Boots

Piggyback Boot Connector Adapters






Duralectric[™], Viton[®] and other Cable and Conduit Jacketing

AmberStrand[®] Lightweight Composite EMI/RFI Shielding





ArmorLite[™] Lightweight Stainless Steel EMI/RFI Shielding

EMI/RFI Metal Braided Shielding and Fabric Braided Sleeving





MIL-DTL-24749 Type IV Qualified Ground Straps

Lightweight ArmorLite™ Microfilament Ground Straps

Cable assemblies, exposed to harsh environmental, mechanical and Celectromagnetic stress are routinely equipped with boots, shields, and jackets designed to protect critical circuits from damage. Glenair offers a complete, turnkey solution to cable and conduit protection that includes innovative lightweight braided EMI/RFI shielding, revolutionary Duralectric™ jacketing, and our full spectrum Series 77 Full Nelson environmental heat shrink boot product family.

Glenai

For more information contact Glenair at **818-247-6000** or visit our website at **www.glenair.com** U.S. CAGE code 06324

Full Nelson

SERIES 77

Full Nelson

Environmental Shrink Boots

Environmental Shrink Boots



or Lipless Boots





Transitions

Convoluted **Boots**




Mechanical and environmental protection/ strain relief for connectorto-cable transitions

- Standard, short, long and 90° lipped and lipless boots
- Choice of six boot materials and a complete range of highperformance adhesive types
- A wide range of colors including desert tan
- The industry's largest selection of metal and composite shrink boot adapters
- All popular part numbers in stock and ready for same-day shipment

The industry's broadest selection of heat shrink products



Material Color Options for Type 1 High Performance Elastomer Boots and Transitions									
Mod Code	Color	Similar to (Reference)	Mod Code	Color	Similar to (Reference)				
632 B	Blue	PANTONE 3005U	632 R	Red	PANTONE 1797U				
632 E	Grey	FED-STD-595; #36270	632 T	Tan	FED-STD-595; #33446				
632 G	Green	PANTONE 355U	632 W	White	FED-STD-595; #37875				
632 P	Purple	FED-STD-595; #37100	632 Y	Yellow	PANTONE YELLOW U				
632 O	Orange	FED-STD-595; #32300	Standard	Black	FED-STD-595; #37038				



Shrink Boot Typical Material Properties Type 1 Type 2 Type 5 Type 7 Type 3 Type 6 Zero Halogen **General Purpose High Performance Flexible** Performance Polyolefin Polyolefin Fluoroelastome **Elastomer Alloy** Polyolefin Elastomer Blend **Property** Flexibility Semi-rigid Semi-flexible Flexible Flexible Flexible Highly Flexible **Operating Temperature** -75°C to +150°C -30°C to +135°C -55°C to +135°C -55°C to +150°C -55°C to +135°C -55°C to +135℃ Range Shrink Temperature (min.) 135℃ 135℃ 120℃ 135℃ 135℃ 135℃ 1400 1700 1100 2200 1500 1400 Tensile Strength (psi) Elongation (% min.) 250 400 300 250 3000 hrs, 135℃ 168 hrs, 175°C 168 hrs, 150°C 168 hrs, 150°C 168 hrs, 175°C Long Term Heat Aging 3000 hrs, 150℃ **Heat Shock** 4 hrs, 215℃ 4 hrs, 215℃ 4 hrs, 225℃ 4 hrs, 225℃ 4 hrs, 220℃ 4 hrs, 250℃ 168 hrs, 160℃ 168 hrs, 160℃ 168 hrs, 175℃ 168 hrs, 150℃ 168 hrs, 150℃ 168 hrs, 175℃ Heat Aging Dielectric Strength (V/mil) 250 200 300 200 300 Volume Resistivity (ohms-10¹² 10¹² 10¹⁰ 10¹⁰ 10¹² Water Absorption (%) 0.5 0.5 0.5 0.5 0.5 Burn Time <15 Burn Time <15 Burn Time <90 Burn Time <120 sec Burn Time <120 sec Burn Time <120 sec Flammability Burn Length Burn Length Burn Length Burn Length Burn Length Burn Length <25mm <25mm <25mm <25mm <25mm <25mm **RoHS Compliant** Yes Yes Yes Yes Yes Oxygen Index (% min.) 30 250 Temperature Index (℃) Smoke Index (max.) 20

Glenair's complete vertical integration ensures high-availability heat-shrink boots for all connector types



3

SHRINK BOOT ADAPTERS SELECTION GUIDE



Series 310

Shrink Boot

Toxicity Index (max.)





Series 319

Shield Sock/Boot

Adapters



Series 440

Band/Boot

Adapters





SAE-AS85049 QPL **Shrink Boot** Adapters

Composite Thermoplastic **Band/Boot Adapters**

Thread/Boot Adapters © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

EMI/RFI Lamp-Base

G



Glenair Environmental Shrink Boots Now TACOM Approved, In-Stock and Ready for Immediate Shipment

High-performance Series 77 "Full Nelson" environmental shrink boots manufactured by Glenair in Glendale, California are now approved by the US Army Tank-Automotive Command (TACOM). Manufactured from high-temperature crosslinked elastomeric polymer material and/or caustic chemical-resistant Viton polymer, Glenair straight and right angle long-tail shrink boots, Y and T transitions, convoluted strain-relief boots and heat-shrinkable adapter shims have been added to the following source control documentation:

		Glenair Ser	ies 77 "Full N	Nelson" TAC	0
Description	Military Part Number	Glenair Part Number	Raychem Part Number	Hellermann Part Number	
	12273148-1**	770-009Y*05	381A301-**	492H412-*	Г
Heat Shrinkable	12273148-2**	770-009Y*06	381A302-**	492H413-*	
Low Profile	12273148-3**	770-009Y*07-01	381A303-*01	492H414-*01	
3-Entry	12273148-4**	770-009Y*08-01	381A304-*01	492H415-*01	١.
"Y" Transition	12273148-5**	770-009Y*07	381A303-**	_	[
Heat Shrinkable	12273162-1**	770-012T*01	301A511-**	412H622-*	2
Low Profile	12273162-2**	770-012T*02	301A512-**	412H623-*	l
3-Entry	12273162-3**	770-012T*03	301A513-**	412H624-*	Γ
"T" Transition	12273162-4**	770-012T*04	301A514-**	412H625-*	
Heat Shrinkable	12273163-1**	770-014*09	462A421-**	573H532-*	l
Low Profile	12273163-2**	770-014*10	462A422-**	573H533-*	١.
4-Entry	12273163-3**	770-014*11	462A423-**	573H534-*	ا
3:1 Transition	12273163-4**	770-014*12	462A424-**	573H535-*	2
	12273164-1**	770-019SB*01	202E334-**	313E445-*	ŀ
Heat Shrinkable	12273164-2**	770-019SB*02	202E344-**	313E455-*	Γ
Adapter	12273164-3**	770-019SB*03	202E336-**	313E447-*	
Shim Boot	12273164-4**	770-019SB*04	202E346-**	313E457-*	ĺ
	12273242-1**	770-022C*01	202C611-**	313C722-9	1
	12273242-2**	770-022C*02	202C621-**	313C732-9	
	12273242-3**	770-022C*03	202C632-**	313C743-9	ĺ
	12273242-4**	770-022C*04	202C642-**	313C753-9	
	12273242-5**	770-022C*05	202C653-**	313C764-9	
	12273242-6**		202G621-**	_	ĺ
Heat Shrinkable Convoluted	12273242-7**		202G632-**	_	ĺ
Strain Relief	12273242-8**		202C642-**	_	
2-Entry Boot	12273242-9**	_	202C653-**	_	ĺ
					4

lumber	Description	Part Number	Part Number	Part Number	Part Number
H412-*		12273147-1**	770-020S*02	202F211-**	313F322-*
H413-*		12273147-2**	770-020S*03	202F221-**	313F332-*
14-*01		12273147-3**	770-020S*04	202F232-**	313F343-*
15-*01	Heat Shrinkable	12273147-4**	770-020S*05	202F242-**	313F353-*
_	Straight Lipped	12273147-5**	770-020S*06	202F253-**	313F364-*
H622-*	2-Entry	12273147-6**	770-020S*07	202F263-**	313F374-*
H623-*	Long Tail Boot	12273147-7**	770-020S*08	202F274-**	313F385-*
H624-*		12273176-1**	770-021A*02	222F211-**	333F322-*
1625-*		12273176-2**	770-021A*03	222F221-**	333F332-*
H532-*		12273176-3**	770-021A*04	222F232-**	333F343-*
H533-*	Heat Shrinkable	12273176-4**	770-021A*05	222F242-**	333F353-*
H534-*	90° Lipped	12273176-5**	770-021A*06	222F253-**	333F364-*
H535-*	2-Entry	12273176-6**	770-021A*07	222F263-**	333F374-*
E445-*	Long Tail Boot	12273176-7**	770-021A*08	222F274-**	333F385-*
EAFE *			-	•	•

VG QUALIFIED SHRINK BOOTS AND ADHESIVES



M APPROVED Shrink Boots



VG Standards are established by the Deutsches Institut für Normung (DIN) and are widely used in European defense programs. Glenair Type 2 shrink boots are qualified to VG95343 Part 28, and our adhesives are qualified to VG95343 Part 18. Consult Glenair UK for price and delivery.

SERIES 77

TACOM-Approved Environmental Shrink Boots

TACOM #	GLENAIR#	TACOM #	GLENAIR#	TACOM #	GLENAIR#
12273147-120	770-020S602	12273162-110	770-012T601	12273176-120	770-021A602
12273147-220	770-0205603	12273162-210	770-012T602	12273176-220	770-021A603
12273147-320	770-020\$604	12273162-310	770-012T603	12273176-320	770-021A604
12273147-420	770-020S605	12273162-410	770-012T604	12273176-420	770-021A605
12273147-520	770-020\$606	12273162-120	770-012T501	12273176-520	770-021A606
12273147-620	770-020S607	12273162-220	770-012T502	12273176-620	770-021A607
12273147-720	770-020S608	12273162-320	770-012T503	12273176-720	770-021A608
12273147-130	770-020S502	12273162-420	770-012T504	12273176-130	770-021A502
12273147-230	770-020S503	12273163-110	770-014609	12273176-230	770-021A503
12273147-330	770-020S504	12273163-310	770-014611	12273176-330	770-021A504
12273147-430	770-020\$505	12273163-410	770-014612	12273176-430	770-021A505
12273147-530	770-0205506	12273163-120	770-014509	12273176-530	770-021A506
12273147-630	770-020\$507	12273163-220	770-014510	12273176-630	770-021A507
12273147-730	770-020S508	12273163-320	770-014511	12273176-730	770-021A508
12273148-110	770-009Y605	12273163-420	770-014512	12273242-110	770-022C601
12273148-210	770-009Y606	12273164-110	770-019SB601	12273242-210	770-022C602
12273148-310	770-009Y607-01	12273164-210	770-019SB602	12273242-310	770-022C603
12273148-410	770-009Y608-01	12273164-310	770-019SB603	12273242-410	770-022C604
12273148-510	770-009Y607	12273164-410	770-019SB604	12273242-510	770-022C605
12273148-120	770-009Y505	12273164-120	770-019SB501	12273242-120	770-022C501
12273148-220	770-009Y506	12273164-220	770-019SB502	12273242-220	770-022C502
12273148-320	770-009Y507-01	12273164-320	770-019SB503	12273242-320	770-022C503
12273148-420	770-009Y508-01	12273164-420	770-019SB504	12273242-320	770-022C503
12273148-520	770-009Y507			12273242-420	770-022C504
		_		12273242-520	770-022C505

TACOM Approved Shrink Boot Material Properties								
Property	Viton® Fluoroelastomer Blend (SPEC-01417-SC-X15111)	High Performance Elastomer Blend (SPEC-01417-SC-X15112)						
Flexibility	Flexible	Flexible						
Operating Temperature Range	-55°C to +150°C	-55°C to +135°C						
Shrink Temperature (min.)	135°C	135°C						
Tensile Strength (psi)	2200	1500						
Elongation (% min.)	400	300						
Heat Shock	4 hrs, 225°C	4 hrs, 220°C						
Heat Aging	168 hrs, 150°C	168 hrs, 150°C						
Dielectric Strength (V/mil)	200	200						
Volume Resistivity (ohms-cm)	1010	1010						
Water Absorption (%)	0.5	0.5						
Flammability	Burn Time <120 sec Burn Length <25mm	Burn Time <120 sec Burn Length <25mm						
RoHS Compliant	Yes	Yes						

Approval:

Project Manager, Heavy Brigade Combat Team (PM-HBCT),

US Army Tank-Automotive Command (TACOM)



Partially recovered for quick and easy assembly

COMPOSITE

Piggyback boot backshell adapters



Partially recovered for quick and easy assembly

310-048 ENVIRONMENTAL PIGGYBACK BOOT ADAPTER

Pre-positioned and partially recovered shrink-boot/adapter unit is ready for fast and reliable final recovery of the boot. Provides durable environmental sealing and strain-relief to the cable-tobackshell junction. Adapter is lightweight composite thermoplastic.

How To Order								
Sample Part Number	310 F S 048 XB 16 -							
Piggyback Boot Adapter	Environmental							
Connector Designator	A = MIL-DTL-83723, Sr. III; MIL-DTL-5015; MIL-DTL-264							
	$\mathbf{F} = \text{MIL-DTL-38999}, \text{ Sr. I & II} \mathbf{H} = \text{MIL-DTL-38999}, \text{ Sr. I}$	II & IV						
Angular Function	S = Straight							
Basic Number								
Finish	XB = no plating, black composite							
Shell Size	08, 10, 12, 14, 16, 18, 20, 22, 24							
Boot Material Type	1 = High-Performance Semi-Rigid Elastomer 2 = Ze 3 = General Purpose Flexible Polyolefin	ro-Halo	ogen Se	emi-Rig	gid Pol	yolefin	1	

317-102 EMI/RFI ENVIRONMENTAL PIGGYBACK BOOT ADAPTER WITH DROP-IN BANDING PORCH

This Piggyback boot features a unique drop-in conductive banding porch. The pre-positioned and partially recovered shrink boot is ready for final recovery after the cable shield is band terminated to the drop-in accessory. Adapter is lightweight composite thermoplastic.

How To Order								
Sample Part Number	317	F	S	102	XB	16	-2	
Piggyback Boot Adapter	EMI/RFI Environmental with drop-in banding porch	MI/RFI Environmental with drop-in banding porch						
Connector Designator	A = MIL-DTL-83723, Sr. III; MIL-DTL-5015; MIL-DTL-264 F = MIL-DTL-38999, Sr. I & II							
Angular Function	S = Straight							
Basic Number				-				
Finish	XB = electroless nickel XMT = Ni-PTFE, Nickel-Fluo XN = Selective plating, Nickel & Cad O.D.	rocarbo	on Poly	mer				
Shell Size	08, 10, 12, 14, 16, 18, 20, 22, 24							
Boot Material Type	1 = High-Performance Semi-Rigid Elastomer 2 = Ze 3 = General Purpose Flexible Polyolefin	ero-Hal	ogen S	emi-Ri	gid Po	lyolefi	n	
Pre-Coiled Band	K = Pre-Coiled Band, Omit if not required							

635-005 ENVIRONMENTAL PIGGYBACK BOOT CABLE FEED-THROUGH

This composite feed-through is supplied with a pre-positioned and partially recoverd shrinkboot—ready for fast and reliable final recovery of the boot. Provides durable environmental sealing and strain-relief to the feed-through-to-box junction. Adapter is lightweight composite thermoplastic.

How To Order							
Sample Part Number	635 005 XB 01 -2						
Piggyback Boot Adapter	Environmental Cable Feed-Through						
Basic Number							
Finish	XB = no plating, black composite						
Dash No.	01 , 02 , 03 , 04 , 05 , 06 , 07 (consult factory)						
Boot Material Type	1 = High-Performance Semi-Rigid Flastomer 2 = Zero-Hal Semi-Rigid Polyolefin						
Length	in $1/8$ inch increments, $5/8$ " minimum, e.g. $5 = .625$ in.						

319-183 EMI/RFI ENVIRONMENTAL PIGGYBACK BOOT ADAPTER WITH INTEGRATED SHIELD SOCK

This integrated EMI/RFI shield sock, with its partially recovered shrink-boot and composite connector backshell delivers speed, convenience, and performance. Simply couple in place, terminate the supplied shield to the cable and complete the recovery of the boot.

How To Order								
Sample Part Number	ample Part Number 319 H S 183 XM 19							-2
Piggyback Boot Adapter	EMI/RFI Environmental with integrated shield sock							
Connector Designator	A = MIL-DTL-83723, Series III; MIL-DTL-5015; MIL-DTL- F = MIL-DTL-38999, Series I & II	· · · · · · · · · · · · · · · · · · ·						
Angular Function	S = Straight $\mathbf{T} = 45^{\circ}$ Elbow $\mathbf{W} = 90^{\circ}$ Elbow	= Straight T = 45° Elbow W = 90° Elbow						
Basic Number								
Finish	XM = Electroless Nickel XMT = Ni-PTFE, Nickel-Fluorocarbon Polymer XW = Cad/O.D.over electroless nickel							
Shell Size	08, 10, 12, 14, 16, 18, 20, 22, 24	08, 10, 12, 14, 16, 18, 20, 22, 24						
Optional Braid Material	A = 100% AmberStrand® B = 75%/25% AmberStrand® Blend - = Nickel-Copper 34AWG T = Tin/Copper 34AWG L = ArmorLite™							
Boot Material Type	See Table IV							

443-033 EMI/RFI ENVIRONMENTAL BAND-IN-A-CAN PIGGYBACK BOOT AND **COMPOSITE BACKSHELL**

This composite, two-piece band-in-a-can adapter comes equipped with a partially recovered shrink boot attached to the nut. After the cable shield is terminated to the band porch, simply screw the nut and boot into place and complete the boot recovery process.

	How To Order									
Sample Part Number	443	Н	S	033	XM	19	20	K	S	-2
Piggyback Boot Adapter	EMI/RFI Environmental Band-in-a-Can boot/backshell									
Connector Designator	A = MIL-DTL-83723, Series III; MIL-DTL-5015; MIL-DTL-2 F = MIL-DTL-38999, Series I & II	· · · · · · · · · · · · · · · · · · ·								
Angular Function	S = Straight W = 90° Elbow									
Basic Number										
Finish	XM = Electroless Nickel XMT = Ni-PTFE, Nickel-Fluorocarbon Polymer XW = Cad/O.D.over electroless nickel									
Shell Size	08, 10, 12, 14, 16, 18, 20, 22, 24, 28					•				
Entry Dia.	Codes 10–32 for diameters .236" – .394" after shrinkage	e, consi	ult facto	ory			_			
Pre-Coiled Band	K = Pre-Coiled Band, Omit if not required									
Slot Option	= Pigtail Slot, Omit for none									
Boot Material	See Table IV	ee Table IV								



Ultra-fast recovery for

reduced assembly time

Pre-installed, pre-tinned

braid version available

Mil-qualified 81824/1

High availability: all

Glenair HSTs made in

in-line-splices

For fast and reliable termination of EMI cable shielding to ground


Reliable termination of EMI/RFI shielding (to ground) in wire harness applications is universally accomplished with AS83519/1 and /2 type heat shrink termination (HST) sleeves. These devices, supplied in five different sizes—with or without pre-installed ground lead wires—provide environmental encapsulation and insulation of the shield termination site. Lead wire-equipped versions allow for easy and reliable grounding to connector shells, backshells, or ground posts. Transparent heat shrink tubing allows for easy inspection and supplies additional strength and strain-relief. The preflux solder preform delivers a fast and controlled solder joint each and every time.

USA and in-stock for immediate, same day shipment Transparent, heat-shrinkable Thermoplastic sealing ring thermoplastic sleeve Optional preinstalled lead wire


AS83519 TYPE • 81824/1 QUALIFIED **Heat Shrink Termination Sleeves** and Mil-Qualified In-Line Splices




AS83519/1 TYPE HEAT SHRINK TERMINATION (HST) SLEEVES, NO LEAD WIRE Size Basic




AS83519/2 TYPE HEAT SHRINK TERMINATION (HST) SLEEVES, PRE-INSTALLED LEAD WIRE









© 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

Fluxed solder preform

Outstanding durability and insulation performance



Rugged high-temperature, environmental Duralectric™ jacketing is available in a broad range of and colors inculding safety orange

Duralectric[™] is the high-performance jacketing material perfectly suited for immersion, chemical or caustic fluid exposure, temperature extremes, UV radiation and more

Glenair *Duralectric*™ weatherproof jacketing is halogen free, flame resistant, and functional to 260°C. Duralectric™ far surpasses the accelerated solar weathering standards under IEC 60068-2-5, and is tested to 56 accelerated days, equivalent to 53 years of solar exposure. Glenair can supply the material in a variety of formats, including blown jacketing, as an extrusion over wire and cable, as an overmolding compound and as a self-vulcanizing repair

	ap c.							
	Jacketing Options							
0	Black	Weatherproof, halogen free, flame resistant, functional to 260°C						
1	Desert Tan	Fed Std #33446 Desert Tan color						
2	Red	Pantone® 1797 U						
3	Orange	OSHA Safety Orange to mark energized electrical cables						
4	Yellow	Pantone® Yellow U						
5	Green	Pantone® 355 U						
6	Blue	Pantone® 3005 U						
7	Violet	Fed Std 595; #37100						
8	Gray	Qualified to US Navy MIL-PRF-24758A, Fed Std 595B #26270 Haze Gray color						
9	White	Fed Std 595; #37875						

Glenair Duralectric™ Material Specifications					
Temperature rating: -60°C to +260°C (with excursions to 290°C)					
Halogen free per IEC 60614-1. Less than 5mg of hcl p	per 1 gm of product tested.				
Accelerated Weathering (Solar) per IEC 60068-2-5; 5	6 days exposure				
Flame Resistant per IEC 60614-1; Material does not sof flame is removed.	sustain combustion when the source				
Low Smoke Index per NES 711 (11.75); Minimum stand This makes the material acceptable for interior appl					
Smoke Density Class F1 Per NF F 16-101 IAW DIN EN 6	50695-2-11:2001				
Toxicity Index per NES 713 (1.9); Minimum standard i	s 5. The Glenair tested level is 1.9.				
This makes the material acceptable for interior appl	ications as well as topside.				
Colorable to Fed Std 595B					
Markable IAW MIL-PRF-24758A					
Oxygen Limiting Index = 45.1 Per EN ISO 4589-2:1999	9; Minimum is 28.				
ASTME E 595 vacuum outgassing-post bake results:	:TML .06%, CVCM .006%, WVR .02%				
Fungus resistance testing (rating of 0) per MIL-STD-	810F, method 508.5				
ASTM D624 DIE B tear test: 150 KN/M					
12 Sec Vertical Burn: (Pass) Per 14CFR Part	25.853(a) amdt 25-116 App F Part 1 (a)(1)(ii)				
Fluids Per MIL STD 810F, Method 504	Cleaner (MIL-C-85570): CALLA-855				
Fuel (MIL-T-83133): JPG	Solvent (Isopropyl Alcohol): TT-I-735				
	i e e e e e e e e e e e e e e e e e e e				

De Icer (AMS-1432): E36 Runway Deicer

Fire Extinguishant Foam: AMEREX AFFF

Coolant (MIL-C-87252): Coolanol 25R

HIGH-PERFORMANCE

Neoprene • Hypalon® • EPDM • Viton




- Extruded, blown-on and heat shrink jacketing for harsh application environments
- General purpose polyurethane
- Chemically-resistant Viton®
- Industry standard neoprene
- Selected materials CBRN tested

Cable and conduit jacketing materials purpose-designed for every application requirement: Immersion, chemical or caustic fluid exposure, temperature extremes, UV radiation and more

	Jacketing Options							
N	Neoprene	Tough, durable polychloroprene for mechanical and environmental protection						
Н	Hypalon®	Light weight with broad temperature range						
E	EPDM	Better resistance to Ketones						
V	Viton®	Heaviest material with best resistance to oil and gasoline						

	Jacketing Material Properties and Chemical Resistance									
Material Property	EPDM (Ethylene Propylene Diene Monomer)	Hypalon (Chlorosulfonated Polyethylene)	Neoprene (Polychloroprene)	Viton® (Fluoroelastomer)						
Temperature Range	-60°F to +300°F (-51°C to +149°C)	-60°F to +300°F (-51°C to +149°C)	-60°F to +250°F (-51°C to +121°C)	-40°F to +392°F (-40°C to +200°C)						
Specific Gravity	1.26	1.18	1.25	1.80						
Weight: Lbs./Cubic Inch	.045	.043	.045	.055						
Abrasion Resistance	Excellent	Excellent	Excellent	Excellent						
Wear Resistance	Good	Good	Good	Good						
Flame Resistance	Good	Good	Good	Good						
Sunlight Resistance	Good	Excellent	Excellent	Excellent						
		Chemical Resistance								
Aliphatic Hydrocarbons	Good	Good	Good	Excellent						
Aromatic Hydrocarbons	Good	Fair	Fair	Excellent						
Ketones, Etc.	Good	Poor	Poor	Poor						
Oil & Gasoline	Good	Good	Good	Excellent						



Material Property Duralectric™ Temperature Range -60°C to +260°C **Specific Gravity** 1.22 Weight: .045 Lbs./Cubic Inch Abrasion Resistance Good **Wear Resistance** Good Excellent

Flame Resistance **Sunlight Resistance**

Jacketing Material Properties

Chemical Resistance Aliphatic Excellent Hydrocarbons Excellent Hydrocarbons Ketones, Etc. Excellent Oil & Gasoline Excellent

Excellent

Fuel (MIL-T-83133): JPG

Hydraulic Fluid (MIL H 5606): ROYCO 756

Lube Oil (MIL-L-23699): ROYCO-500



AmberStrand®



Composite metal-clad

EMI/RFI braided shielding






- Metal-clad EMI/RFI Shielding with a lightweight composite thermoplastic base material
- Highly conductive surface plating
- Reduce shielding weight up to 80% and more
- Reduce operation costs by permanently reducing launch and aircraft all-up weights
- Superior high frequency shielding compared to tinned and/or nickel plated copper
- Exceptional tensile strength: 590,000 psi (min)


Will Not Melt

AmberStrand®:The smart way to reduce launch and flight weights in aerospace systems



Glenair can also offer AmberStrand® users direct factory overbraiding services for both point-to-point as well as multibranch interconnect assemblies.

Composite strainrelief backshell with integrated AmberStrand® lightweight composite metal-clad braid shield sock.



75%/25% AmberStrand® Blend

103 - 027

Diameter Dash Number

	How does Amberstrand® compare, in terms of mechanical performance, to other materials?											
Material Type	AmberStrand° Thermoplastic	PEEK (Monofil)	Fluoropolymer (Yarn)	Kevlar (Yarn)	Dacron (Yarn)	Halar (Monofil)	Fluoropolymer FEP (Monofil)	Nomex (Yarn)	Polyester Type FR (Monofil)	Ryton Type R-7 (Monofil)	PTFE-Glass (Yarn)	
Glenair P/N	103-026 103-027	102-051	102-061	102-071	102-073	102-023	102-060	103-013	102-001 102-002	102-080	100-022	
Temperature Range	-65°C to +200°C	-65°C to +260°C	-55°C to +200°C	-73°C to +175°C	-62°C to +150°C	-65°C to +200°C	-55°C to +260°C	-55°C to +125°C	-55°C to +200°C	-65°C to +200°C	-75°C to +525°C	
Tensile Strength (PSI) Yield	590,000	780,000	40,000	400,000	160,000	35,000	14,000	90,000	50,000	19,000	450,000	
Elongation Percentage	2.5%	38%	19%	3.6%	12%	15%	50%	25%	20%	35%	5%	
Chemical Resistance	Excellent	Excellent	Excellent	Excellent	Good	Excellent	Excellent	Excellent	Good	Excellent	Excellent	
Abrasion Resistance	Good	Excellent	Good	Good	Excellent	Excellent	Good	Good	Good	Excellent	Excellent	
Specific Gravity	1.45	1.30	2.10	1.44	1.38	1.68	2.17	1.58	1.38	1.25	2.50	

LIGHTWEIGHT

Composite metal-clad EMI/RFI braided shielding

Aircraft Utilization Analysis

Comparison of AmberStrand® Composite EMI/RFI braid to 36 AWG A-A-59569 Ni/Cu Braid results in 60+ pounds weight savings in a typical commercial carrier

	Where is all the EMI/RFI braid deployed in a typical commercial aircraft?											
Diameter (in)	L Wing	R Wing	Fwd Belly	Aft Belly	HYD Bay	Aft Barrel	Tail	V/H Stab	Totals (in)			
0 - 0.25	1852.2	1852.2	0	2811.4	168.2	2015.2	2480.6	1385	12564.8			
0.25 - 0.5	434.8	434.8	511.6	1034.6	257.4	506.2	958.2	1121.7	5259.3			
0.5 - 0.75	0	0	260.9	223	0	184.2	392.4	152.1	1212.6			
0.75 - 1.0	0	0	77.2	0	0	1198	162.2	0	1437.4			
1.0 - 1.5	0	0	0	0	0	446	21	0	467			

How much w	ould all this bi 36 AWG A-A-		was made of
Diameter (in)	Weight (Lb/ft)	Length (in)	Weight (Lb)
0 - 0.25	0.02	12564.8	21.08
0.25 - 0.5	0.05	5259.3	21.17
0.5 - 0.75	0.07	1212.6	7.12
0.75 - 1.0	0.14	1437.4	16.88
1.0 - 1.5	0.18	467	7.05
		Total weight	73.30 lbs

How much would all this braid weigh if it was made of lightweight composite AmberStrand®?									
Diameter (in)	Diameter (in) Weight (Lb/ft) Length (in) Weight (Lb)								
0 - 0.25	0.003	12564.8	4.16						
0.25 - 0.5	0.008	5259.3	3.58						
0.5 - 0.75	0.011	1212.6	1.16						
0.75 - 1.0	0.018	1437.4	2.11						
1.0 - 1.5	0.034	467	1.30						
		Total weight	12.31 lbs						

Braid	d in percentages, how AmberStrand® 100%	Tinned Copper	% Weight	AmberStrand° 75/25% NiCu	Tinned Copper	% Weight Savings/
Diameter	103-026	100-001	Savings/Foot	103-027	100-001	Foot
.062	.6	1.9	68%	.9	1.9	52%
.125	1.0	4.8	79%	1.5	4.8	68%
.250	1.8	16.1	88%	2.4	16.1	85%
.375	2.3	18.5	87%	3.9	18.5	79%
.500	3.7	22.3	83%	5.4	22.3	76%
.625	4.4	27.7	84%	6.4	27.7	77%
.750	5.2	34.3	85%	7.2	34.3	79%
1.000	8.0	35.0	77%	11.0	35.0	69%

Will Not Burn | Will Not Melt | Flammable | Flammable



Microfilament nickel-clad stainless steel EMI/RFI braided shielding





- Ultra-lightweight EMI/RFI braiding for high-temperature applications -80°C to +260°C
- Microfilament stainless steel: 70% lighter than NiCu A-A-59569
- Outstanding EMI/RFI shielding and conductivity
- Reduce shielding weight up to 70% and more
- Superior flexibility and "windowing" resistance: 90 to 95% optical coverage
- 220,000 psi (min) tensile strength
- Best performing metallic braid during lightning tests (Run to ANSI/EIA-364-75-1997 Waveform 5B)

Save weight and money every time you fly! Aircraft All-Up-Weight (AUW) has met its match: ArmorLite[™] microfilament stainless steel braid saves pounds compared to standard QQ-B-575/ A-A-59569 EMI/RFI shielding.








Choose user-installable microfilament tubular braid in twelve standard diameters. Assemble per standard multi-branch cable shielding processes, as above.



Glenair can also offer ArmorLite[™] users direct factory overbraiding services for both point-to-point as well as multibranch assemblies.





A single layer of ArmorLite™ Shields from 40dB to 80dB in Frequency Ranges from 30kHz to 2.5GHz

LIGHTWEIGHT ArmorLite™



Microfilament nickel-clad stainless steel EMI/RFI braided shielding

Aircraft Utilization Analysis

Comparison of ArmorLite[™] nickel clad stainless steel braid to A-A-59569 Ni/Cu braid

	Where is all the EMI/RFI braid deployed in a typical commercial aircraft?											
Diameter (in)	L Wing	R Wing	Fwd Belly	Aft Belly	HYD Bay	Aft Barrel	Tail	V/H Stab	Totals (in)			
0 - 0.25	1852.2	1852.2	0	2811.4	168.2	2015.2	2480.6	1385	12564.8			
0.25 - 0.5	434.8	434.8	511.6	1034.6	257.4	506.2	958.2	1121.7	5259.3			
0.5 - 0.75	0	0	260.9	223	0	184.2	392.4	152.1	1212.6			
0.75 - 1.0	0	0	77.2	0	0	1198	162.2	0	1437.4			
1.0 - 1.5	0	0	0	0	0	446	21	0	467			

How much would all this braid weigh if it was made of 36 AWG A-A-59569 NiCu?								
Diameter (in) Weight (Lb/ft) Length (in) Weight (Lb)								
0 - 0.25	0.02	12564.8	21.08					
0.25 - 0.5	0.05	5259.3	21.17					
0.5 - 0.75	0.07	1212.6	7.12					
0.75 - 1.0	0.14	1437.4	16.88					
1.0 - 1.5	0.18	467	7.05					
		Total weight	73.30 Lbs					

ArmorLite™	¹ Micro Stainle:	ss Steel Braide	d Shielding?
Diameter (in)	Weight (Lb/ft)	Length (in)	Weight (Lb)
0 - 0.25	.00507	12564.8	5.309
0.25 - 0.5	.0097	5259.3	4.251
0.5 - 0.75	.0178	1212.6	1.737
0.75 - 1.0	.0256	1437.4	3.063
1.0 - 1.5	.0368	467	1.434
		Total weight	15.794 Lbs

How much would all this braid weigh if it was made of








Shielding Effectiveness

For EMI/RFI Braiding Solutions - 0 MHz to 2500 MHz Range



■ 70+% Lighter than NiCu QQ-B-575/A-A-59569


Enhanced EMI/RFI Electrical Performance (DC resistance 1 Ohm/ft).

■ Thermal Cycling: No Adverse Effects

■ Flame: Self Extinguishing ■ Flex Test: 50,000 Cycles ■ Salt Spray: 500 Hours

Surface Transfer Impedance

For EMI/RFI Braiding Solutions - 0 MHz to 2500 MHz Range



G-14 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

EMI/RFI metal braided shielding and fabric braided sleeving



INDUSTRY-STANDARD

EMI/RFI metal braided shielding and fabric braided sleeving





- Complete range of QQ-B-575B/A-A and ASTM B conductive braided shielding solutions
- Tubular, tapered tubular, and overbraided application options
- Every size from 1/32" to 33/4"
- High performance tubular fabric braided sleeving for every mechanical and wire-protection application requirement



World's largest selection of metal and fabric cable shields

100-001 TUBULAR METAL BRAID QQ-B-575B/A-A-59569 ASTM B298 TIN COATED COPPER



	How To Order			
Sample Part Number	100-001	A	XXX	L
Tubular Metal Braid	Tin Coated Copper Braid			
Wire Gauge	A = 36 AWG B = 34 AWG			
Size	Consult Factory			
Lanyard Option	L = Lanyard Omit for none			

100-002 TUBULAR METAL BRAID QQ-B-575B/A-A-59569 ASTM B298 SILVER COATED COPPER



How To Order								
Sample Part Number	100-002	A	XXX	L				
Tubular Metal Braid	Silver Coated Copper Braid							
Wire Gauge	A = 36 AWG B = 34 AWG							
Size	Consult Factory							
Lanyard Option	L = Lanyard Omit for none		_					

100-003 TUBULAR METAL BRAID ASTM B355 CLASS 4 OFHC NICKEL PLATED COPPER



How To Order							
Sample Part Number	100-003	A	XXX	L			
Tubular Metal Braid	Nickel Plated Copper Braid						
Wire Gauge	A = 36 AWG B = 34 AWG						
Size	Consult Factory						
Lanyard Option	L = Lanyard Omit for none						

100-041 TAPERED TUBULAR METAL BRAID



How To Order								
Sample Part Number	100-041	-06	Т	10	Α			
Tubular Metal Braid	Tapered Braid							
Dash No.	Diameters .15 – 1.38, Consult Factory							
Material	A = 100% AmberStrand* N = Nickel/Coppe B = 75%/25% AmberStrand* S = Silver/Copper L = 100% ArmorLite* T = Tin/Copper	r						
Length	In 1 inch increments			-				
Wire Gauge	A = 36 AWG, Omit for std. 34 AWG (applies to N, S, T	materia	ls only.					

FABRIC BRAIDED SLEEVING FOR NON-ENVIRONMENTAL WIRE AND CABLE PROTECTION



Non-Environmental Fabric Braided Sleeving Types				
Series No.	Туре			
100-022	PTFE glass tubular braided sleeving			
102-001 and -002	Polyethelene expandable fabric tubular braided sleeving; black, green, red, white, and yellow			
102-020, -021, -022 and -023	Halar expandable fabric tubular braided sleeving, white or black, with and without tracers			
102-073	Dacron tubular braid, black			
103-013	Nomex tubular braid; black, white, red, green, gray, and desert tan			
102-051	PEEK tubular braid, black			
102-061	Fluoropolymer tubular braid, clear and natural			
102-071	Kevlar tubular braid, natural			
102-072	Nylon tubular braid, black			

SERIES 100-022 HIGH-TEMPERATURE PTFE-GLASS TUBULAR BRAIDED SLEEVING



Highly flexible PTFE-glass tubular braided sleeving with outstanding high- and low-temperature resistance (-240°C to +525°C)

How To Order							
Sample Part Number	100-022	XXX	GN				
Tubular Metal Braid	PTFE-Glass Braided Sleeving						
Size	Consult Factory	_					
Color Option	GN = Green/Olive Drab (Omit for Natural)						

FACTORY OVERBRAIDING SERVICES FOR MULTI-BRANCH CABLE ASSEMBLIES





G-16 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

G



for Navy shipboard applications

Ground straps utilized in shipboard applications are subject to grueling environmental conditions: wet, cold, salt water spray, and caustic hydraulic fluids. Conventional copper braid/copper lug ground straps corrode, and become a source of electrical resistance problems in these harsh environments.

Glenair MIL-DTL-24749 Rev B Type IV ground straps solve these corrosion and electrical resistance problems with a unique 50% Stainless Steel 316L / 50% Nickel 200 36AWG blend braid, and passivated Stainless Steel lugs. These US Navy-approved ground straps are qualified to the rigorous standards of M24749, and are tested beyond the mil-spec to survive 1000 hours salt spray. Allowed usages for Type IV straps can be found in MIL-STD-1310H.




Glenair MIL-DTL-24749 Rev. B Type IV Stainless Steel/Nickel Ground Straps: US Navy qualified and tested to survive extreme environments


- Meets the rigorous specifications of MIL-DTL-24749 Rev. B
- Tested to survive 1000 hours salt spray
- Unique Stainless Steel/ Nickel hybrid braid
- Available in six standard configurations, with non-standard length/ lug size configurations available



MIL-DTL-24749 REV B TYPE IV **Stainless Steel/Nickel Ground Straps**









NOTES

- 1. Lugs are ink stamped or electro-etched per M24749 Rev B. Minimum character height shall be .06 (1.52)
- 2. Metric dimensions (mm) indicated in parentheses
- 3. Codes A F are standard lengths. To order non-standard straps, omit Standard Size Code and enter length (in inches) in part number.

MATERIAL/FINISH

Lugs - 316L Stainless Steel/Passivate

Braid - 316L Stainless Steel 36 AWG, 50%; 200 Nickel 36 AWG, 50%



Straps—for Aircraft ESD, Lightning Strike and Other Applications

Lightning interaction mechanisms and protection techniques are well known disciplines in aircraft design. But innovations are still required, particularly in support of efforts to reduce the size, weight and assembly complexity of aircraft electrical systems. Lightweight Glenair technologies for spot grounding are broadly utilized for:

- Grounding airframe sections
- Dissipating static build-up in composite structures
- Dissipating lightning strike energy
- Grounding individual moving parts in complex equipment such as landing gear

ArmorLite™ microfilament braid offers 70+% weight savings over standard NiCu braid—plus advantages in virtually every category due to Glenair's ability to fine-tune the makeup of the material cross-section (core, cladding and protective plating) to the exact requirements of each application. Glenair ArmorLite™ lightweight microfilament braids, and hybrid ArmorLite™ and nickel braids are now approved for use by every major airframe and equipment manufacturer.

CUSTOM CONFIGURATIONS AVAILABLE







ARNOR! ITE



GLENAIR BONDING ENGINEERS ARE EXPERTS IN GROUND STRAP OPTIMIZATION FOR:

- Weight and conductivity
- Electrical resistance and high operating temperature (200°C)
- Rapid heat distribution
- Bend cycle durability up to 250,000 cycles per EN4199-001
- Material aging and corrosion resistance

Comprehensive test reports available

LIGHT-DUTY, LOW PROFILE ArmorLite™ Single-Layer ESD Grounding Strap



LOW-PROFILE ESD GROUNDING STRAPS, LIGHT AND MEDIUM DUTY

107-098




	Table II: Mechanical/Electrical Parameters for ArmorLite Material											
Width Code	A ± .03	C	R	D	E	Ţ	Nom. Resistance m0hm/m* (AWG Equiv.)	Lug Junction Resistance mOhm	Weight gr/m*	Inductance nH/m (Ref. Only)	Test Current Amps**	Tensile Strength Lbf
12	.290 (7.37)	.150 (3.81)	.145 (3.68)	.042 (1.06)	.480 (12.19)	.016 (.41)	48 (22)	0.129	9.0	1277	37	130
20	.480 (12.19)	.200 (5.08)	.240 (6.10)	.042 (1.06)	.690 (17.53)	.016 (.41)	26 (19)	0.111	13.4	1170	52	216
24	.590 (14.99)	.260 (6.60)	.295 (7.49)	.042 (1.06)	.790 (20.06)	.016 (.41)	23 (18)	0.097	17.9	1116	62	219
32	.820 (2.83)	.390 (9.91)	.375 (9.53)	.052 (1.32)	.950 (24.13)	.021 (.53)	13 (16)	0.089	35.8	1047	127	483
40	.870 (22.10)	.390 (9.91)	.375 (9.53)	.052 (1.32)	.950 (24.13)	.021 (.53)	11 (15)	0.061	40.3	1034	141	524
48	1.080 (27.43)	.390 (9.91)	.375 (9.53)	.052 (1.32)	.950 (24.13)	.021 (.53)	8 (14)	0.054	53.8	983	162	590
64	1.330 (33.78)	.390 (9.91)	.375 (9.53)	.052 (1.32)	.950 (24.13)	.021 (.53)	6 (12)	0.047	71.7	936	208	723
	for 107-098 double-layer straps											
48	1.080 (27.43)	.390 (9.91)	.375 (9.53)	.080 (2.03)	1.15 (29.21)	.042 (1.06)	4 (11)	0.054	107.6	976	500	590
64	1.330 (33.78)	.390 (9.91)	.375 (9.53)	.080 (2.03)	1.15 (29.21)	.042 (1.06)	3 (10)	0.047	143.4	930	650	723
* Braid	only, figures	exclude term	nination lugs	. **Test cur	rent is define	ed as the cu	rrent required t	o reach 200°	C at ambi	ent temperati	ure	

GROUND CONTROL EARTH BOND SYSTEM



	How To Order			
600-120	Hydraulic Setting Tool for 1/4" Earth Bonds			
600-123	Hydraulic Setting Tool for 3/8" Earth Bonds			
600-124	Hydraulic Setting Tool for M6 Earth Bonds			
600-125	Hydraulic Setting Tool for M10 Earth Bonds			
The tools feature one hand operation and ram retract mechanism actuated by release trigger.				

Consult factory for control gauges and earth bond part numbers for each material type and size.



Annular Polymer-Core Conduit Systems









- Lightweight, flexible polymer-core materials and easy to install fittings, transitions and adapters
- Choice of three tubing material choices: Kynar, PVDF and **G-FLEX Siltem**
- A wide range of colors including desert tan
- Choice of turnkey, factory-terminated assemblies or user-installable configurations
- All popular part numbers in stock and ready for same-day shipment

High-performance annular convoluted tubing provides an economical, lightweight and durable enclosure for interconnect wiring

Part Number 120-144

For non-environmental and non-EMI/RFI applications

Strong, abrasion resistant annular conduit tubing, supplied in thermally stabilized Kynar®, PVDF, or medium duty Siltem. Available in 7 colors, standard or slit.



For non-environmental EMI/RFI applications

Annular conduit tubing with braided shield for EMI/RFI protection and additional structural integrity, particularly pull (tensile) strength.



For environmental EMI/RFI applications

Annular conduit tubing with braided shielding for EMI/RFI protection and a ruggedized jacket for environmental protection against dust, dirt, and moisture incursion.



For non-environmental EMI/RFI applications with high dB shielding requirements

Annular conduit tubing with double braided shield for high frequency EMI/RFI protection and mechanical strength.



For environmental EMI/RFI applications with high dB shielding requirements

Annular conduit tubing with double braided shield and jacket for optimum EMI/RFI protection, strength and environmental sealing.

	Tubing Material Choices					
Υ	Kynar®	Flexible, thermally stabilized, resistant to harsh chemicals and radiation. UV resistant, self-extinguishing, nontoxic and resistant to low-temperatures. 166° C temp. rating.				
V	PVDF	Flexible and chemical/radiation resistant. Available in 4 colors plus standard black and natural. 150° C temperature rating.				
S	G-FLEX Siltem	Lightweight, halogen-free, low toxicity, low smoke. Exceptional flexibility and crush resistance. 175°C temperature rating. Ideal for harsh environment applications.				

Material Properties - Kynar® and PVDF							
Material Property	Service Temperature			Elongation		Specific Gravity	
Kynar® and PVDF	-65°F/330°F (-54°C/166°C)*	5000 PSI (34,474 KP)		250%		1.8 Max	
Material Property	Heat Aging	Dielectric Strength		Volume Resistivity		Water Absorption	
Kynar® and PVDF	168 Hrs. @ 347°F (175°C)	10,000V		10 ¹⁶		0.02%	
Material Property	Solvent Resistance		Flammability			Fungus Resistance	
Kynar® and PVDF	No swelling, stickine weight change	ss or	Non-burning		Does not support fungus growth		

*Note: Kynar® and PVDF material properties are identical, with the exception that Kynar® has been irradiated for thermal stability, and thus has a higher temperature rating of 166°C compared to 150°C for non-thermally-stabilized PVDF.

G-FLEX Siltem is Glenair's proprietary annular polymercore convoluted tubing formulation, developed for harsh environment applications that require a lightweight, halogenfree material with exceptional flexibility and crush resistance

Material Properties - G-FLEX Siltem							
	Flexural Modulus	Flexural Strength	Tensile Strength	Elongation			
	168,000 PSI	5590 PSI	5700 PSI	60%			
Material Property	Melt Flow Rate	Dielectric Strength	Volume Resistivity	Water Absorption			
	38.0 G/10 min	422.9 V/mil	>1.E+16 Ohm-cm	0.58%			

SERIES 72 CONVOLUTED TUBING PRODUCT SELECTION GUIDE





Easy-to-Install **Guardian system**

Factory Terminated Assemblies

Sentry system

Helical Polymer-Core Conduit Systems



SERIES 74 / AS81914 **Helical Polymer-Core Conduit Systems**





Seven standard tubing configurations, with and without braided shielding and jacketing

- Lightweight, flexible helical polymer-core materials and easy to install fittings, transitions and adapters
- ETFE, FEP, PFA, PTFE, and PEEK plus AS81914 /1 11 qualified materials and configurations
- Choice of turnkey, factory-terminated assemblies or user-installable configurations
- All popular part numbers in stock and ready for same-day shipment

AS81914 qualified Series 74 high-performance helical convoluted tubing, backshells, fittings and assemblies

Part Number 120-100

Outstanding mechanical wire protection and lubricity for non-environmental and non-EMI/RFI applications

Helical plastic convoluted tubing, available in a choice of 5 materials. Choose standard black or clear color.

Part Number 121-101

Adds EMI/RFI braided shielding for use in non-environmental applications

Helical plastic convoluted tubing, available in a choice of 5 materials, with a single braided shield for EMI/RFI protection.

Part Number 121-102

Adds a second layer of high dB EMI/RFI shielding for use in nonenvironmental applications

Helical plastic convoluted tubing, available in a choice of 5 materials, with double braided shield for high frequency shielding applications.



A jacketed configuration with one EMI/RFI shield for use in environmental applications

Helical plastic convoluted tubing, available in a choice of 5 materials, with braided shielding for EMI/RFI protection and a ruggedized jacket for environmental protection.



Double-braided and jacketed configuration for environmental and high dB EMI/RFI shielding protection

Helical plastic convoluted tubing, available in a choice of 5 materials with double shielding and jacket for optimum EMI/RFI protection and environmental sealing.



For environmental applications without EMI shielding requirements

Helical convoluted tubing in choice of 5 materials with a ruggedized jacket for environmental protection.



Internal braid configuration for harsh chemical environment applications, with EMI/RFI shielding

Chemical- and UV-resistant plastic conduit tubing with internal braid for weight savings and harsh-environment EMI/RFI protection.

	Series 74 Convoluted Tubing Material Choices					
E	ETFE (fluoropolymer) (Series 74 standard)	Highest tensile strength and lubricity. Combines mechanical toughness with outstanding chemical, dielectric and thermal properties, improved radiation resistance. This is our standard material for a reason: ETFE delivers the best performance and best value in high-performance polymer resins.				
F	FEP	Economical with relatively high thermal stability, excellent dielectric properties. Unaffected by virtually all solvents and chemicals, good adhesion resistance.				
Р	PFA (Fluoropolymer)	Outstanding lubricity and resistance to corrosives, -95°F to 500°F temperature rating. Melt-extruded for better cold flow and long-term sealing than PTFE; more economical.				
Т	PTFE (Fluoropolymer)	Outstanding resistance to corrosives, -95°F to 500°F temperature rating. Somewhat better folding endurance than PFA. However, this paste-extruded Fluoropolymer® material is more difficult to process and so costs more than PFA with virtually equal performance.				
К	PEEK	Low-smoke, zero-halogen with high strength and superior crush resistance. Lightest weight of all the tubing polymers, but also the highest material cost.				

		Series 74 Convo	luted Tubing Material Pro	perties			
Material Property	Perfluoroalkoxy (PFA)	Fluorinated Ethylene Propylene (FEP)	Ethylene Tetrafluoroethylene (ETFE)	Polytetrafluoroethylene (PTFE)	Polyether Ketone (PEEK)		
Service Temperature	-95°F/500°F (-71°C/260°C)	-95°F/400°F (-71°C/204°C)	-65°F/310°F (-54°C/154°C)	-95°/500°F (-71°C/260°C)	-76°F/392°F (-60°C/200°C)		
Tensile Strength	3,000 PSI (20,684 KP)	2,500 PSI (17,237 KP)	5,000 PSI (34,474 KP)	2,500 PSI (17,237 KP)	7,000 PSI (48,300 KP)		
Elongation	250%	200%	100%	175%	100%		
Specific Gravity	2.15	2.15	1.70	2.15	1.26		
Heat Aging	2000 Hrs.@ 525°F (274°C)	2000 Hrs.@ 430°F (221°C)	2000 Hrs.@ 350°F (177°C)	2000 Hrs. @ 525°F (274°C)	2,000 Hrs. @ 464°F (240°C)		
Dielectric Strength	12,000V	12,000V	12,000V	12,000V	12,000V		
Volume Resistivity	1018	1018	1016	1018	1016		
Water Absorption	0.03% 0.01%		0.02%	0.01%	0.03%		
Solvent Resistance		No swelling, stickiness or weight change					
Flammability	Non-burning						
Fungus Resistance			Does not support fungus gr	owth			

SERIES 74 CONVOLUTED TUBING PRODUCT SELECTION GUIDE



Convoluted Tubing

Assemblies

Easy Assembly Hat Trick System



Super Durable Internal Braid System



Ultra Lightweight **Composite Hummer Nut System**

Metal-Core Conduit Systems





- Hermetically sealed, flexible metal-core conduit for interconnect applications
- Choice of three materials: Brass, Stainless Steel, and Nickel Iron Alloy
- Turnkey, factory-terminated assemblies for landing gear and other rugged aerospace applications
- All materials deliver superior EMC performance as well as crush resistance and environmental sealing

The ultimate in highly flexible, crush-proof EMI/EMP protection: Series 75 helically-wound metal-core conduit

Part Number 750-190

Superior EMI protection and crush-proof strength for static applications

Highly flexible crush-proof metal conduit, available in Nickel-Iron, Brass, or SST.



Adds braided shielding for additional tensile strength applications

Flexible metal-core conduit tubing with numerous braided shielding options, for additional tensile strength and effective grounding of electromagnetic interference.



Adds a jacket for environmental protection

Flexible metal-core conduit tubing with braided shielding plus a ruggedized jacket for environmental protection against contaminants and moisture.

Part Number 750-193

Adds a second braided shield for high dB EMI/RFI shielding

Flexible metal-core conduit tubing with double braided shield for high frequency EMI/RFI shielding requirements.

Part Number 750-194

A jacketed, double-braided configuration for combined environmental and EMI/RFI applications with high dB shielding requirements

Flexible metal-core conduit tubing with double braided shield and jacket for optimum EMI/RFI protection, strength and environmental sealing.

Part Number

Triple-braided conduit for predictable and reliable grounding of surface-borne/high frequency electromagnetic interference

Flexible metal-core conduit tubing with triple braided shield for optimal tensile strength and enhanced high frequency EMI/RFI protection.



Triple-braided and jacketed conduit for maximum EMI shielding in environmental applications

Flexible metal-core conduit tubing with triple braided shield and jacket for enhanced high-frequency EMI/RFI protection, strength and environmental sealing.

	Conduit Material Choices, Material Properties, and Military Specifications							
Glenair Code	Material	Properties	Applicable Military Specifications					
В	Brass, Per A-A-52440 Type I, Grade B	Optimal EMI shielding when combined with bronze overbraid. Generally specified with bronze overbraid and jacket.	IAW A-A-52440 (Covering shielded, electrical, flexible, metal conduit for use as protection of wiring in military vehicles from mechanical injury and, when properly installed and grounded, to prevent radiation that may cause interference with radio and other electronic equipment.)					
C	Stainless Steel AISI 316	Specified for high-temperature, corrosion, and crush resistance. Nominal shielding value. Typically braided with stainless steel braid for additional pull strength and durability. Available with or without a jacket.	 MIL-C-13909 (Superseded by IAW-A-A-52440 above) MIL-PRF-24758 (Covering the performance requirements for weatherproof flexible conduit systems for use primarily in exposed areas on U.S. Navy ships, to shield against electromagnetic (EM) radiation from own-ship transmitters and emissions external to the ship, electromagnetic pulse 					
N	Nickel Iron Alloy Type 4 ANSI/ASTM-A-753	80% Nickel, 20% Iron. Optimal low-frequency shielding material. Typically braided with stainless steel braid for additional pull strength and durability. Available with or without a jacket.	 (EMP) events, and to minimize corrosion while being field repairable to reduce maintenance.) MIL-DTL-28840 (Covering Connectors, Electrical, Circular, Threaded, High Shock, High Density, Shipboard, Metal Conduit, for EMI Shielding) 					

	EMI/RFI Braided Shielding and Non-Metallic (Fabric) Overbraids					
В	Bronze	Standard for for brass core conduit				
Т	Tin/Copper	150°C temperature rating, 125 lbs. tensile strength, 96 hr. salt spray corrosion resistance				
С	Stainless Steel	Highest tensile strength (225 lbs.), highest temperature—1093°C+				
N	Nickel/Copper	200°C temperature rated, 150 lbs. tensile strength, 500 hrs. salt spray corrosion resistance				
S	SnCuFe	Tin plated iron/copper				
L	ArmorLite™	Microfilament metal-clad ultra lightweight stainless steel braid				
D	Dacron	Yarn with excellent abrasion resistance, good chemical resistance, non-conductive				
M	Nomex	-55°C to 260°C temperature range - will not melt, excellent chemical resistance, non-conductive				
E	AmberStrand® 100%	Expandable, flexible, high-strength conductive metal-clad composite thermoplastic				
F	AmberStrand® 75%/25%	75% Expandable, flexible, high-strength conductive metal-clad composite thermoplastic combined with 25% nickel-plated 36AWG copper wire for additional strength				

SERIES 75 METAL-CORE HELICALLY-WOUND CONDUIT PRODUCT SELECTION GUIDE



Metal-Core Helical-Wound Conduit



Turnkey Factory Terminated Assemblies



Low-Profile **RP Plus** System



Heavy-Duty Environmental Metal System



Heavy-Duty Environmental Conduit System

Navy Shipboard Conduit Systems

Glenair.

and other special-purpose conduit systems








- Qualified to MIL-PRF-24758A(SH)
- User-installable and factory terminated configurations
- Innovative stainless steel fittings with advanced environmental sealing, EMI shield termination and rotatable coupling nut
- Adapters for all shipboard interfaces—fully compatible with legacy MIL-C-24758 conduit system components

Do it once, do it right with Glenair MIL-PRF-24758 and other special purpose wire protection conduit systems



CONVOLUTED POLYMER-CORE TUBING WITH DRAIN HOLES



Reference Part No. (Consult factory for additional materials and configurations)



For aerospace applications where altitude changes can cause moisture condensation within conduit, Glenair produces convoluted polymer-core tubing with drain holes. All major aircraft OEM hole patterns are on file, contact the factory for details on specific configurations.

WIRE-REINFORCED CONVOLUTED POLYMER-CORE TUBING



Reference Part No.(Consult factory for additional materials and configurations)

127 - 009

Glenair has developed a unique configuration where helical polymer-core tubing is reinforced with a stainless steel wire, adding at least 200 lbs. crush strength while maintaining the lightweight, chemical-resistant and environmental protection properties of Polymer-Core tubing.

SLIT POLYMER-CORE TUBING



Reference Part No.(Consult factory for additional

materials and configurations)

120 -

Any of Glenair's regular bulk helical or annular polymer-core tubings can be provided slit, for on-site

installation or addition of wires in open wire loom applications.

Use the Wire Loom Tool for easy wire insertion: simply gather the wires into the tool, insert into the slit conduit, and run the tool through the tubing.

OVAL POLYMER-CORE ANNULAR TUBING



Reference Part No. (Consult factory for additional materials and configurations)

120 <mark>- 140 - 4</mark>0

For specialized wire routing applications, Glenair can fabricate annular tubing with an oval shaped profile. Inhouse manufacturing allows us to design and fabricate non-standard shapes.

"NO-HAL" HALOGEN FREE FLEXIBLE HELICAL PEEK TUBING ASSEMBLY



Reference Part No.(Consult factory for additional materials and configurations)

127 - 130

The Glenair "No Hal" tubing assembly is designed for applications where RoHS compliance or other environmental standards mandate a halogen-free configuration. Halogen-free PEEK tubing (with optional stainless steel wire reinforcement for crush strength) is combined with Glenair halogen-free Duralectric™ jacketing material. Add an optional braided shield for EMI/RFI protection.

DUAL-CORE TUBING



In applications where helical convoluted tubing needs to perform in harsh chemical environments, and weight savings is a concern, dual-core conduit is the answer. Glenair Series 74 Polymer-Core tubing materials are chemical- and UV resistant, and protecting the outside of tubing with a second layer of polymer tubing can save weight over standard jacketing. Consult the factory for Polymer-Core and braided shield material options.

© 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

Backshells and Connector Accessories

For every environmental, mechanical, and EMI requirement



For more information

contact Glenair at **818-247-6000** or

visit our website at www.glenair.com
U.S. CAGE code 06324

Glenair is one of the original military/aerospace manufacturers engaged in the design and production of high-performance backshells, dustcaps, shield termination devices and other connector accessories. In operation since 1956, Glenair has designed and produced more innovative connector accessory products than the rest of our industry combined. Glenair interconnect engineers are responsible for developing literally thousands of innovative connector accessories—from lightweight and corrosion-free composite thermoplastic strain reliefs to innovative fiber optic backshells. Today, the company is able to supply accessory solutions for every requirement, no matter how unique or challenging.

BACKSHELLS

Connector Backshells

and Accessories

Rectangular

Backshells

© 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

lenair.

Connectors and Accessories

QPL AND COMMERCIAL **■** High-performance circular

Circular Connector Backshells and Accessories

Innovation and availability: the Glenair connector accessory product line

- connector accessories for every environmental, mechanical and electromagnetic shielding requirements
- QPL'd AS85049 backshells
- Tens of thousands of popular part numbers in inventory ready for same-day shipment
- Fast turnaround on nonstandard and made-to-order accessories, typically only two to three weeks
- RoHS compliant plating options

PROTECTIVE COVERS AND STOWAGE RECEPTACLES



THE WORLD'S FOREMOST SUPPLIER Circular Connector Backshells and Accessories



BACKSHELL INNOVATION SHOWCASE



TAG-Ring/Qwik-Ty® Feed-Through Fitting



Spring-Loaded "Flop-Lid" **Protective Cover**



Space Grade Quick Clamp Backshell



Ultra Low-Profile Backshell



Series 437-001 Backshell "Connector Saver"



Anti-Decoupling Protective Covers



Ultra small-form-factor **Mighty Mouse** environmental backshell



High-Performance Banding **Backshell**

STARSHIELD "ZERO LENGTH" INDIVIDUAL SHIELD TERMINATION BACKSHELL



- Eliminates "standing antenna" problems common with pigtail shield termination systems
- Utilizes heat shrink termination (HST) sleeve technology for fast and reliable shield termination—even with dissimilar wire types/ gauges
- Available in a standard configuration featuring a threaded compression nut and a tapered split-ring that fits snugly into a conical backshell or a lightweight split banding version.

STANDARD AND PRESSURE BOUNDARY FEED-THRUS



High-performance, weight saving composite feed-thrus



EMI/RFI split-shell metal feed-thru

- High-grade engineering thermoplastic or machined metal
- Six pressure-boundary feed-thru layouts with accommodation for 1 – 6 cables
- Split-shell jam nut versions with EMI/RFI shield termination porch
- O-ring sealed panel and box mounting interface
- Conductive and non-conductive finish options



METAL AND COMPOSITE

Rectangular backshells and accessories

Proven performance backshells and accessories for rectangular connectors

Glenair offers more tested and tooled rectangular interconnect products-including the world's broadest range of rectangular backshells-than any other supplier in the industry. Simply put, from the smallest Micro-D subminiature to the largest ARINC 600, Glenair has an unparalleled range of solutions. Need something light and corrosion free? Glenair is the industry leader in tooled composite thermoplastic connector accessories.





Glenair has developed an extensive range of lightweight OwikSnap™ backshells that completely eliminate assembly hardware in split-shell backshells. QwikSnap™ itilizes innovative composite spring latch technology to reduce weight, FOD, and accelerate assembly.

- All forms of environmental, mechanical and EMC backshells
- Straight, 45° and 90° cable
- High-temp composite thermoplastic and metal shell versions
- To fit all current and legacy rectangular connectors
- Innovative split-shell versions for easy access to wire terminations
- Equally large range of protective covers and caps
- Thousands of part numbers in stock and ready for immediate shipment

METAL AND COMPOSITE Rectangular backshells and accessories The world's largest tooled selection





Composite Micro-D banding backshell



Plastic caps and covers for safe shipment and storage of connectorized



Micro-D backshell with elliptical banding platform



Metal Micro-D banding backshell



Conductive rubber covers

Environmental protective covers for Micro-D connectors

M24308 D-SUB SOLUTIONS: HIGH PERFORMANCE, RUGGEDIZED D-SUBMINIATURE PRODUCTS



Split-shell D-subminiature Split-shell M24308 composite backshell



composite backshell



Composite D-subminiature backshells



Flex-D Composite M24308 Backshell



M24308 EMI/RFI backshell

LARGER FORM FACTOR RECTANGULAR BACKSHELLS

EPX® and EPXB® are registered trademarks of Radiall



Composite EMI/RFI banding backshell for EPXB® connectors



Composite EN4165 fiber optic/electrical backshells





Backshells for EPX® series connectors



ARINC series backshells



Composite airframe banding backshell



ARINC series backshell with



MIL-C-81659



Special Quadrax connector backshell

LIGHTWEIGHT **Composite Backshells** and Accessories High temperature

Corrosion resistance, weight reduction, durability and design innovation







Composite Band-in-a-Can shield termination backshell and strain-relief clamp

- engineered thermoplastics for maximum strength and durability
- Total immunity to galvanic corrosion
- Up to 70% weight reduction compared to standard metal connectors and accessories
- Hundreds of innovative, tooled designs in stock

1000 HOUR GREY™Ni-PTFE NICKEL FLUOROCARBON POLYMER PLATING



The MIL-DTL-38999 Rev L detail specification lists Nickel Fluorocarbon Polymer as a qualified Cadmium free plating alternative. This highly conductive, RoHS compliant plating formula is now available on composite interconnect products from Glenair and offers the following benefits in harsh-environment applications:

- 2000+ hour salt spray
- Cadmium free
- Outstanding mating lubricity
- Hexavalent Chromium free
- 500+ mating cycles
- Non-Magnetic

COMPOSITE Circular and Rectangular Backshells and Accessories



COMPOSITE DESIGN INNOVATION REDUCES CABLE HARNESS ASSEMBLY TIME



Composite QwikSnap™ M24308 Backshell

protective covers



Composite Swing-Arm with **Keyed Drop-In Banding Insert**



"Piggyback" Backshell



Isolated Conductive Ground Path








Non-conductive unplated protective covers

Composite Thermoplastic Vs. Common Metal Materials						
Material	Specific Gravity	Density (lbs. Inch ³)	Salt Spray			
Composite	1.27 - 1.51	.055	2000+ Hrs			
Aluminum	2.55 - 2.80	.098	48-1000 Hrs			
Titanium	4.51 - 4.62	.162	500-1000 Hrs			
Stainless Steel	7.70 - 7.73	.284	500-1000 Hrs			
Brass	8.40 - 8.70	.305	500-1000 Hrs			

Glenair composite interconnect components are principally manufactured from 30% glass fiber polyetherimide (PEI). At room temperature PEI exhibits tensile strength yield of over 15,000 psi. The PEI material meets the most stringent outgassing and flammability requirements.



ULTRA-LIGHTWEIGHT COMPOSITE THERMOPLASTIC SHIELD TERMINATION





Shielded Composite Junction Boxes

Install it and forget it: Glenair corrosion-free EMI/RFI shielded composite junction boxes

Series 316 stainless steel hardware provides long-term durability

Glass reinforced composite thermoplastic material is strong and durable and yet extremely

- Over a dozen different tooled sizes and shapes.
- Extremely durable, corrosion-free, high temperature engineering composite thermoplastic
- Tested and qualified to U.S. Navy, UK MOD and hundreds of commercial aircraft and marine applications

IP67 rated seals and gaskets protect equipment from moisture and dust

- Unlimited corrosion resistance compared to metal junction boxes reduces repair and maintenance costs.
- Low harmonic resonance and inherent attenuating properties reduce loosening and decoupling of feedthrough fittings and accessories.





COMMERCIAL OFF-THE-SHELF AND CUSTOM COMPOSITE THERMOPLASTIC JUNCTION BOXES



	Glenair Composite Box Product	Specifications
Description/Test Report	Requirement	Procedure
Plating Adhesion Glenair #9-44-18/TN94-159	Should not exhibit any blistering, peeling or other separation of the units plating.	Tested IAW MIL-DTL-38999.
Vibration <i>NTS #973-7369-2</i>	Should not exhibit loosening of component parts or evidence of damage.	Tested IAW MIL-STD-167 Type 1 for box units and MIL-STD-1344 Method 2004 Condition II for fittings and accessories.
Shock MOD #BR8470 Grade C and F	There shall be no loosening of parts or evidence of damage.	Tested IAW MOD BR 8470 Grade C and F.
Salt Spray <i>Glenair #9-44-18/TN94-159</i>	Should exhibit no exposure of underplate or base material.	Tested IAW MIL-STD-1344, Method 1001.
Dust NTS #973-7369-1	Should conform to required torque limits and functional requirement within 25%.	Tested IAW MIL-STD-202.
UV Light Resistance GE RDM88050255-6042	No degradation of the mechanical properties defined in the specification after testing.	Tested IAW ASTM D2565.
Impact MIL-STD-1344, Method 2015	No evidence of breaking or cracking of components or other damage that could affect the product performance.	Tested IAW MIL-STD-1344, Method 2015.
Temperature Cycling NTS #575-9249	No cracking, peeling or separation of plating or other functional damage.	Tested IAW MIL-STD-1344, Method 1003 at -65°C to 200°C.
Hydrolytic Stability NTS #878-536	No evidence of increased weight greater than 1% and no evidence of cracking, breaking or loosening of component parts.	Tested IAW ASTM D570-81.
Flammability MIL-STD-1344, Method 1012, Smoke Index, NES 711 Issue 2, NES 713 Issue 3 and ISO 4589	The item flame and after flow extinguishing time shall not exceed the defined limits.	Tested IAW Table II of of MIL-STD-1344, Method 1012, Smoke Index, NES 711 Issue 2, NES 713 Issue 3. Burning behavior by Oxygen Index, ISO 4589.
Water Tightness <i>EA #0C13513-039514</i>	Water tightness and internal pressurization is maintained.	Tested IAW EA #0C13513-039514.
Outgassing JPL #081892	Maximum allowable weight loss is 10%.	Tested IAW ASTME 595.
Electromagnetic Shielding TRW/ABQ-55C-1186-0	Should demonstrate shelding effectiveness and transfer impedance conforming to military industry standards and specific customer requirements.	Tested IAW TRW/ABQ-55C-1186-0.

lightweight.

INDUSTRY STANDARD

Interconnect Assembly Tools

The right tool for every interconnect assembly requirement



Interconnect Assembly Tools Selection Guide

Backshell-to-Connector Assembly Tools

The second secon

BandMaster[™] ATS EMI/RFI Shield Termination System

Glenair offers its connector and connector accessory customers every convenience in the provision of contact termination, shield termination, and backshell-to-connector assembly tooling. We are also proud to offer branded solutions from other well-known tool manufacturers such as Daniels (DMC) crimp tools. From pneumatic Earth-Bond tooling for the rail industry, to fiber optic termination and test equipment, Glenair is your most knowledgeable and reliable source for special-purpose interconnect assembly tooling.

© 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324



For more information contact Glenair at **818-247-6000** or visit our website at **www.glenair.com** U.S. CAGE code 06324

23

EMI/RFI Shield Termination System



The advanced termination system for interconnect cable shielding





- Fast, cost-effective cable shielding termination
- Precision hand-held tool and bands deliver reliable, repeatable performance
- Single piece stainless steel bands in various sizes and lengths
- Clamp both small and large diameters easily and reliably
- Pneumatic banding tool for highspeed mass production
- Qualified for both military and commercial aviation

The Band-Master[™] ATS provides quick, easy, cost-effective and highly reliable termination of braided metallic shielding or fabric braid to connectors and backshells.

Band-Master™ ATS is the advanced termination system for interconnect cable shielding. The unique low profile and smooth inside diameter of the one-piece type 304 austenitic stainless steel clamping band virtually eliminates RFI/EMI/EMP leakage paths. The lock maintains constant tension under extreme environmental conditions. Band-Master™ ATS bands have passed severe shock, vibration and thermal cycle testing with negligible deterioration of shell conductivity.





Glenair Band-Master¹¹ ATS Bands are also AS85049/128 qualified

BAND-MASTER™ ATS ADVANCED TERMINATION SYSTEM



Easy-to-use manual tools with built-in calibration counter



High-volume pneumatic tool for bench use



Save time and tool maintenance costs with the Glenair band tool calibration system

BAND-MASTER™ ATS

EMI/RFI Shield Termination System



The advanced termination system for interconnect cable shielding

Band-Master™ ATS Manual Tool Selection

601-100 Hand Tool for Standard Bands

The 601-100 Standard Band-Master™ ATS Tool weighs 1.18 lbs., and is designed for standard flat .24" width clamping bands (601-005, 601-040 and 601-049) in a tension range from 100 to 180 lbs. Calibrate at 150 lbs. \pm 5 lbs. for most shield terminations. Tool and band should never be lubricated.



601-101 Hand Tool for Micro Bands

The 601-101 Micro Band-Master™ ATS Tool weighs 1.18 lbs., and is designed for micro .120" width clamping bands (601-024, 601-060 and 601-064) in a tension range from 50 to 85 lbs. Calibrate at 80 lbs ± 5 lbs. for most shield terminations. Tool and band should never be lubricated.



601-108 Hand Tool for Nano Bands

The 601-108 Nano Band-Master™ ATS Tool weighs 1.18 lbs., and is designed for nano flat .075" width clamping bands (601-500, 601-504 and 601-508) in a tension range from 20 to 50 lbs. Calibrate at 50 lbs. \pm 3 lbs. for most shield terminations. Tool and band should never be lubricated.



601-109 Hand Tool for Slim Bands

The 601-109 Slim Band-Master™ ATS Tool weighs 1.2 lbs., and is designed for slim standard flat .24" width clamping bands (601-570, 601-571, 601-572 and 601-573) in a tension range from 50 to 100 lbs. Calibrate at 100 lbs. \pm 5 lbs. for most shield terminations. Tool and band should never be lubricated.



3 lengths and 3 widths of EMI braid termination bands plus new slim bands for size and weight savings—50% lighter and lower-profile than standard bands.

		В	and-Master™	" ATS Band Sele	ection	
	Ler	ngth	Part	Number	Fits Diameter	
Bands	in.	mm.	Flat	Pre-Coiled	in.	mm.
Short Standard Band	9.0	228.6	601-005	601-006	1.0	25.4
Medium Standard Band	14.0	355.6	601-040	601-041	1.8	47.8
Long Standard Band	18.0	457.2	601-049	601-050	2.5	63.5
Short Micro Band	5.0	127.0	601-024	601-025	0.5	12.7
Medium Micro Band	8.0	203.2	601-060	601-061	.88	22.4
Long Micro Band	14.0	355.6	601-064	601-065	1.8	47.8
Short Nano Band	6.0	152.4	601-500	601-501	.60	15.2
Medium Nano Band	9.0	228.6	601-504	601-505	.94	23.9
Long Nano Band	14.0	355.6	601-508	601-509	1.8	47.8
Short Slim Standard Band	9.0	228.6	601-570	601-571	.94	25.4
Medium Slim Standard Band	14.25	362.0	601-572	601-573	1.8	47.8

BACKSHELL-TO-CONNECTOR Assembly Tools



Assembly Tools

Glenair offers a complete family of backshell assembly tools for most Mil-Standard circular connectors, as well as connector wrenches, strap wrenches, and universal connector



- Backshell-to-connector holding tools for all cylindrical connectors and accessories in current use
- Special composite thermoplastic coupling nut holding tools
- Discrete tools and complete sets available
- Popular Glenair strap wrenches
- Hand-held and benchmountable digital torque wrenches
- Cutting shears and other special-purpose cable assembly tools
- Instructional videos, installation procedures and manuals available at glenair.com



CONNECTOR HOLDING WRENCHES, PLUG AND RECEPTACLE HOLDING TOOLS AND KITS








Cable Assemblies and Integrated Systems

Customer bespoke cable harnesses and assemblies for mil/aero applications





Clenair has been the go-to cable house for high-performance interconnect cable assemblies for more than 50 years. We specialize in delivering terminated, tested cable harnesses and assemblies with 100% reliability and quality control. We offer complete, turnkey cable assembly services from design engineering to fabrication and test, and are qualified to all military and commercial aerospace standards.





Overmolded and ASAP Cable Assemblies

Wired Conduit Assemblies



Integrated Systems



For more information contact Glenair at 818-247-6000 or visit our website at www.glenair.com U.S. CAGE code 06324 Glenair.






Glenair: *The* Overmold Specialists

Advantages of Overmolding

- **■** Waterproof sealing
- Robust mechanical protection
- Protection of terminations
- Ideally suited for chemical and fuel cell applications
- No induced cold flow stress
- Electrical isolation and insulation
- Reduced wear damage
- Flexible routing/cable entry

Terminated, overmolded, tested, and ready for use. Glenair cable harnesses and assemblies are recognized industry-wide for quality



Point-to-point jumper cables and cordsets for high-speed and high-reliability applications—easy to order and shipped ready for immediate use
















- Glenair can design, build, terminate—and even prewire—turnkey conduit wire routing solutions.
- Certified factory assemblers and calibrated tooling create better-performing systems.


available in Straight, 45°, and 90°

configurations.

■ Simple point-to-point or complex multi-branch.

Reduce package size, weight, and labor with turnkey factory assemblies





Adapter for easy wire

maintenance



BUILD-TO-PRINT Flex circuit assemblies for mission-critical applications


Four reasons to specify flex in your next application




board technology and cabling into a lightweight, integrated package.


Glenair turnkey design, termination and assembly services available worldwide.

- Convenient packaging and integration
- Reliable resistance to Harsh environments





environment.



PURE AIR/NITROGEN **Lightweight Modular Cooling and Actuation Systems**



Solutions built to exact customer

requirements and specifications

Manifold Assembly

Solenoid Valve

Glenair pure gas/nitrogen systems and sub-assemblies provide passage of nitrogen and other pure, pressurized gases through precision-machined components such as pressure regulating valves, solenoids, and Joule-Thompson cryogenic cooling systems. Assemblies feature precision stainless steel pipeworks and tubing which are fabricated using a fluxfree brazing process and are ultrasonically cleaned and packaged in a sealed, dust-free environment. Electromechanical components are also precision-machined with material properties and dimensional attributes per customer specifications.

- Manifold Assemblies including Charging Valves, Relief Valves or **Burst Discs, Pressure Gauges, Control Valves**
- Pipework Sub-Assemblies connecting cylinders to manifolds or components
- Pressure Regulating Valves
- Solenoid Valves manifold or in-line; single or two-stage
- Manifolds to other sub-assemblies

Typical Performance		
Flow Rate	Typical Flow Rate is 5 liters per minute (lpm) @ 150 PSI.	
Operating Temperature	-65°C +175°C for all applicable mechanical requirements.	
Physical Shock	No loosening of parts, cracking or other deleterious results hindering further part operation after 300 G's in each of 3 mutually perpendicular planes.	
High Impact Shock	All components withstand high impact shock per MIL-S-901.	
Vibration	All components withstand high-vibration with no evidence of cracking, breaking or loosening of parts.	



Pressure test rig

Pure air compatibility test equipment



Gas tube helium leak test equipment



Brazing control panel


Pure Air/Nitrogen **Cooling Systems**

Complete systems and ancillaries for IR guided weapons and weapons ejection applications

Glenair high pressure Pure-Air/Nitrogen gas solutions are designed and performance tested for use in a wide variety of Defence, Aerospace and Other applications, including cooling of infrared detectors, missile seekers and all high pressure pneumatic actuation and deployment systems. Products include, Sealed for Life Gas Supply Systems, Re-chargeable Gas Supply Systems, High Pressure Solenoid Valves (miniature & low voltage), Small Bore pipe Assemblies, Relief Valves, Integrated Manifold Assemblies, Charge Valves and High Pressure Vessels. All Systems and Ancillaries are designed for direct incorporation into Joule Thompson (JT) cryogenic systems and all applications which require reliable pressurization, blow down, actuation, and IR Cooling. Glenair Pure-Air and High Pressure Systems and components are designed to exact customer requirements and specifications.



- Brazed stainless steel pipework
- Pure air and nitrogen (DEF STAN 58-96)
- High-pressure cylinders, soleniod valves, manifolds, and complete sub-assemblies



L-8 © 2014 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324

SERIES 06

Hold-Down Release Mechanism **Technology**

Resets in Minutes

Glenair hold-down release mechanism (HDRM) technology is based on a fusable wireactuated separation nut design. Increasingly popular for its reliability and non-pyrotechnic action, fusable wire-actuated nut technology has the added benefit of being partially reusable and refurbishable post-deployment. Glenair HDRM technology is immune to all forms of EMI or ESD, and is capable of easily sustaining launch loads as well as defined preloads—with release deployment times comparable to conventional explosive actuators, but with low-shock and low power input.

A broad range of hold down release mechanism technologies have been historically used to secure and subsequently deploy satellites and other appendages (solar arrays, antenna reflectors, radiators, instruments, doors, sensors, booms, and so on) in space. Most of these technologies relied on non-reusable (explosive/pyrotechnic) designs that suffered from a broad range of deficiencies, including susceptibility to electromagnetic interference, problematic sychronization of release with mission requirements, high-shock release action, and significantly, the inability to reuse or refurbish the device during test. Historically, actuators and release devices of this type have included:


Glenair has taken a different path in the development of a non-explosive HDRM with a consumable initiator which, post-actuation, allows the device to be refurbished and reset on-site, or at the factory. Glenair fusable wire-actuated nut technology solves all of the problems associated with conventional explosive HDRM devices. In addition, the three key components of the Glenair HDRM (preloading assembly, release actuator, and load-carrying structure) may be packaged according to specific customer requirements including the addition of connectors to replace wire leads, cylindrical or rectangular housings, lightweight materials, package size and profile, mounting dimensions and so on. Consult the Glenair

Physical characteristics for ¼ inch unit		
Mass	228 grams nominal weight	
IVIdSS	with 18 inch lead wire included	
Bolt	1/4-28 UNJF-3B*	
Material list	IAW MSFC-STD-3029	
Ероху	Outgassing requirements per GSC19384	

Device features for ¼ inch unit		
Redundant initiation	2 initiation points	
Field refurbishable	Initiator can be replaced in less than 15 minutes by trained	
	personnel	
Reliability prediction	0.9999995	
Packaging	External housing typically supplied with two mounting points. Custom housings and mountings available	
Connectorization	Standard design supplied with wire inputs. Connectorized versions available	
Scalable bolt size	Bolt size determines preload and can be scaled to accommodate a wide range of requirements	

out. Complete test report available upon request





Bolt cutters

Electromechanical

(non-explosive)

electromagnetic

User-serviceable and

Scalable design, up to 40,000 lbs. preload

For more information

contact Glenair at

818-247-6000 or

visit our website at www.glenair.com

technology

interference

■ Ultra-low-shock

■ Immune to

reusable

release

- Separation nuts
- Wire and pyro cable cutters

HDRM team at our Glendale factory for more information.

Physical characteristics for ¼ inch unit		
Mass	228 grams nominal weight	
ividss	with 18 inch lead wire included	
Bolt	1/4-28 UNJF-3B*	
Material list	IAW MSFC-STD-3029	
Ероху	Outgassing requirements per GSC19384	



7/16 inch unit with 35,000 pound preload and connectorized interface



1/4 inch unit wtih 5,000 pound preload and conventional wire lead interface

SERIES 06

Hold-Down Release

electromechanical release mechanism

technology for dependable stowage and

High-reliability, non-explosive

release of deployable

Glenair HDRM device technology is optimized for reliability with built-in mechanical and electrical redundancy. The planned release of the deployable system is activated by a predetermined value of electrical current to a fusewire system which causes the wire to break under

tension and allow the pre-loaded mechanical bolt

defined housing and mounting configurations.

to actuate. Glenair is now positioned to incorporate HDRM technology into a broad range of customer-

space systems

Mechanism Technology

^{*}The size callout is based off the bolt size that is to be used. Metric thread can also be called



Turnkey, precision-machined wired chassis, integrated electronic/photonic systems plus Glenair-built interconnect cabling

Glenair, together with our precision machining partner Dynomax, is able to offer our defense, aerospace and other customers fast, turnkey build-to-print integrated system solutions. From landing gear assemblies to in-flight entertainment platforms, Glenair is uniquely positioned to leverage our component manufacturing, interconnect cable assembly and structural member fabrication capabilities to meet the broadest range of integrated system requirements. Our US-based factories in Glendale, California and Chicago, Illinois are FAA, Mil and ISO 9001 certified, and ready to tackle any integrated system requirement for today's high-performance military and aerospace applications. Our Glenair UK facility is also Mil and ISO 9001 certified and in addition offers ESA and BS certified components and technologies. Glenair Italia is equally credentialed and adds IRIS (International Railway Industry Standard) certification and operates an IEC certified test lab. Our worldwide design and manufacturing teams are ready to provide start-to-finish engineering and assembly support on even the most complex integrated system projects.



Precision-machined, injection molded or stamped-and-formed boxes and structural members

Multibranch interconnect cable harnesses and assemblies terminated, tested, and ready for use

Turnkey integrated system components: Vertically integrated manufacturing, from backplanes to avionic control panels

INTEGRATED SYSTEMS

Turnkey complex cable assemblies • junction box assemblies wired avionic control panels • connectorized backplanes







Integrated systems: all interconnect components, boxes and machined chassis manufactured by Glenair. All cabling and final integration completed by Glenair. Glenair engineering provides extensive design support throughout.

Figure 1: Integrated in-flight entertainment console and cabling

Figure 2: Wired unmanned vehicle control module Figure 3: Rail industry corrosion-resistant junction box assembly

Figure 4: Business-class seat chassis with integrated cabling

Figure 5: Stainless steel vacuum plate with machine-integrated Micro-D connectors and jumpers



For more information contact Glenair at 818-247-6000 or visit our website at www.glenair.com U.S. CAGE code 06324

ervice and



Our high-availability business model puts customer service, support, and convenience first














Every factory operation

machining to molding,

plating, testing

and assembly

controlled by Glenair—from










Backshels and Beyond

Glenair is a full-spectrum interconnect supplier—manufacturing a complete range of solutions in Glendale since 1956



produce a cable clamp,



1965: Glenair's first connector product: the Sav-Con® Connector





1980









1990

NG ARM





acquires Micro-D connector and TwistPin contact manufacturer, Microway Systems

1999: Glenair introduces the composite

3-in-1 Swing-Arm strain-relief



2001: Glenair launches

high-performance fiber optic

2000

2020

2005: Glenair launches its line of

performance

EMI/EMP Filter connectors



Opto-Electronic connector division



More Glenair milestones and innovations:









SuperNine®

Geo-Marine®







Well-Master 260°

Band-Master ATS®







1950

manufactures the


1960

factory specializing in complex cable assemblies and Micro-D flex circuitry




1970

2005: Glenair acquires Italian industrial/rail connector manufacturer,







G lenair.

Engineering Services




Glenair design expertise extends from innovative composite backshells to complex opto-electronic assemblies

The industry's most experienced engineering and design team—in every discipline—from backshells to flex circuit boards



Let us be your design partner: Glenair has the most liberal NRE policy in the industry




Glenair excels in the design of miniaturized components such as this full Gigabit

Ethernet contact



Glenair's engineering team in Glendale is augmented by regional teams worldwide, and we love to travel. Our place or yours? We work at our customers' convenience.

















Glenair. Committed to Quality



How can you be sure Glenair connectors are high-quality and will deliver long-term reliable performance?

How can you be sure they will ship on time and in the correct quantity ordered? Here are seven things to consider:

Mil-Spec Certifications: Glenair is qualified to hundreds of riaorously controlled product and process certifications administered by the US government.



Certified Quality System: Glenair is ISO 9001:2008 and AS9100:2009 Rev. C certified and registered in North America; IRIS (International Railway Industry Standard), AS9100 SAE Aerospace and ISO 9001 certified and registered in Italy, and AS9100 certified and registered in the U.K.



3 Satisfied Customers: Hundreds of worldclass OEMs and system manufacturers have tested and qualified our products. Many conduct independent audits of Glenair quality on an annual basis.










Factory Capacity: Our first-world factories,

the largest in the mil-aero interconnect

and materials/process compliance.

industry, are positioned for ongoing growth








Go-To Supplier: In applications where a single fault can lead to mission failure, Glenair is selected time and

time again—from high-pressure subsea applications to







missions to Mars.







Out of This World INTERCONNECT SOLUTIONS

Glenair, Inc.

1211 Air Way • Glendale, California • 91201-2497 Telephone: 818-247-6000 • Fax: 818-500-9912 • sales@glenair.com www.glenair.com

Glenair Power Products Group

860 N. Main Street Extension Wallingford, CT 06492

Telephone: 203-741-1115

Facsimile: 203-741-0053

sales@glenair.com

Glenair UK Ltd

40 Lower Oakham Way Oakham Business Park P.O. Box 37, Mansfield Notts, NG18 5BY England

Telephone: +44-1623-638100 Facsimile:

+44-1623-638111 sales@glenair.co.uk

Glenair Microway Systems

7000 North Lawndale Avenue Lincolnwood, IL 60712

Telephone: 847-679-8833 Facsimile: 847-679-8849 Glenair Nordic AB

Gustav III: S Boulevard 46 S - 169 27 Solna Sweden

Telephone: +46-8-50550000 Facsimile: +46-8-50550001 sales@glenair.se

Glenair Electric GmbH

Schaberweg 28 61348 Bad Homburg Germany

Telephone: 06172 / 68 16 0 Facsimile: 06172 / 68 16 90 germany@glenair.com

Glenair Iberica

C/La Vega, 16 45612 Velada Spain

Telephone: +34-925-89-29-88 Facsimile:

+34-925-89-29-87 sales@glenair.es

Glenair Italia S.p.A.

Telephone: Via Del Lavoro, 7 +39-051-782811 40057 Ouarto Inferiore -Facsimile: Granarolo dell'Emilia +39-051-782259 Bologna, Italy info@glenair.it

Glenair France SARL

7, Avenue Parmentier Immeuble Central Parc #2 31200 Toulouse France

Telephone: +33-5-34-40-97-40 Facsimile:

+33-5-61-47-86-10 sales@glenair.fr

© 2014 Glenair, Inc.

Printed in U.S.A.