
Final datasheet
CoolSiC™ 1200 V SiC MOSFET G2 : Q-DPAK top-side cooling

Features



- V_{DSS} = 1200 V at T_{vj} = 25°C
- I_{DDC} = 242 A at T_C = 100°C
- $R_{DS(on)}$ = 5 mΩ at V_{GS} = 18 V, T_{vj} = 25°C
- Very low switching losses
- Overload operation up to T_{vj} = 200°C
- Benchmark gate threshold voltage, $V_{GS(th)}$ = 4.2 V
- Robust against parasitic turn on, 0 V turn-off gate voltage can be applied
- Robust body diode for hard commutation
- .XT interconnection technology for best-in-class thermal performance
- Suitable Infineon gate drivers can be found under https://www.infineon.com/gdfinder

Halogen-free
Green
Lead-free
RoHS

Potential applications

- Solid-state circuit breaker / Solid-state relay
- EV Charging
- Online UPS / Industrial UPS
- String inverter
- General purpose drives (GPD)
- CAV
- Servo drives

Product validation

- Qualified for industrial applications according to the relevant tests of JEDEC47/20/22

Description

Pin definition:


• Pin 1 – Gate

• Pin 2 – Kelvin sense contact

• Pin 3-11 – Source

• Pin 12-22, Tab – Drain

Note: the source and sense pins are not exchangeable, their exchange might lead to malfunction



Type	Package	Marking
IMCQ120R005M2H	PG-HDSOP-22-U03	12M2H005

Downloaded from Arrow.com.

Table of contents

Description . . . 1
Features . . . 1
Potential applications . . . 1
Product validation . . . 1
Table of contents . . . 2
1 Package . . . 3
2 MOSFET . . . 3
3 Body diode (MOSFET) . . . 6
4 Characteristics diagrams . . . 8
5 Package outlines . . . 15
6 Testing conditions . . . 16
Revision history . . . 17
Disclaimer . . . 18

Downloaded from Arrow.com.

1 Package

Table 1 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Storage temperature	T_{stg}		-55		150	°C
Soldering temperature	T_{sold}	Reflow soldering (MSL2 according to JEDEC J-STD-020)			260	°C
Thermal resistance, junction-ambient	$R_{th(j-a)}$				62	K/W
MOSFET/body diode thermal resistance, junction-case	$R_{th(j-c)}$			0.08	0.11	K/W
Comparative Tracking Index	*CTI*	IEC 60112 (material group 1 according to IEC 60664-1)	600			V

2 MOSFET

Table 2 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Drain-source voltage	V_{DSS}	$T_{vj} \geq 25$ °C		1200	V
Continuous DC drain current for $R_{th(j-c,max)}$, limited by $T_{vj(max)}$	I_{DDC}	$V_{GS} = 18$ V	$T_c = 25$ °C	342	A
			$T_c = 100$ °C	242	
Peak drain current, t_p limited by $T_{vj(max)}$ [1)]	I_{DM}	$V_{GS} = 18$ V		1210	A
Gate-source voltage, max. transient voltage	V_{GS}	$t_p \leq 0.5$ µs, $D < 0.01$		-10...25	V
Gate-source voltage, max. static voltage [2)]	V_{GS}			-7...23	V
Avalanche energy, single pulse	E_{AS}	$I_D = 69$ A, $V_{DD} = 50$ V, $L = 0.4$ mH, $T_{vj(start)} = 25$ °C		868	mJ
Avalanche energy, repetitive	E_{AR}	$I_D = 69$ A, $V_{DD} = 50$ V, $L = 1.8$ µH, $T_{vj(start)} = 25$ °C		4.34	mJ
Power dissipation, limited by $T_{vj(max)}$	P_{tot}		$T_c = 25$ °C	1364	W
			$T_c = 100$ °C	682	

1) Verified by design.
2) The maximum gate-source voltages in the application design should be in accordance to IPC-9592B.

Downloaded from Arrow.com.

Table 3 Recommended values

Parameter	Symbol	Note or test condition	Values	Unit
Recommended turn-on gate voltage	$V_{GS(on)}$		15...18	V
Recommended turn-off gate voltage	$V_{GS(off)}$		-5...0	V

Table 4 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Drain-source on-state resistance	$R_{DS(on)}$	I_D = 138.2 A	T_{vj} = 25 °C, $V_{GS(on)}$ = 18 V		5		mΩ
			T_{vj} = 150 °C, $V_{GS(on)}$ = 18 V		10.2	13.6	
			T_{vj} = 175 °C, $V_{GS(on)}$ = 18 V		11.9		
			T_{vj} = 25 °C, $V_{GS(on)}$ = 15 V		6.3		
Gate-source threshold voltage	$V_{GS(th)}$	I_D = 43.4 mA, V_{DS} = V_{GS} (tested after 1 ms pulse at V_{GS} = 20 V)	T_{vj} = 25 °C	3.5	4.2	5.1	V
			T_{vj} = 175 °C		3.2		
Zero gate-voltage drain current	I_{DSS}	V_{DS} = 1200 V, V_{GS} = 0 V	T_{vj} = 25 °C			1200	µA
			T_{vj} = 175 °C		20.4		
Gate leakage current	I_{GSS}	V_{DS} = 0 V	V_{GS} = 23 V			120	nA
			V_{GS} = -10 V			-120	
Forward transconductance	g_{fs}	I_D = 138.2 A, V_{DS} = 20 V			91		S
Internal gate resistance	$R_{G,int}$	f = 1 MHz, V_{AC} = 25 mV			2.55		Ω
Input capacitance	C_{iss}	V_{DS} = 800 V, V_{GS} = 0 V, f = 100 kHz, V_{AC} = 25 mV			9.76		nF
Output capacitance	C_{oss}	V_{DS} = 800 V, V_{GS} = 0 V, f = 100 kHz, V_{AC} = 25 mV			428		pF
Reverse transfer capacitance	C_{rss}	V_{DS} = 800 V, V_{GS} = 0 V, f = 100 kHz, V_{AC} = 25 mV			37.3		pF
C_{oss} stored energy	E_{oss}	Calculated based on C_{oss} = f(V_{DD})			181		µJ
Output charge	Q_{oss}	Calculated based on C_{oss} = f(V_{DD})			670		nC
Effective output capacitance, energy related	$C_{o(er)}$	V_{DS} = 0...800 V, V_{GS} = 0 V, Calculated based on E_{oss}			564		pF
Effective output capacitance, time related	$C_{o(tr)}$	I_D = constant, V_{DS} = 0...800 V, V_{GS} = 0 V, Calculated based on Q_{oss}			838		pF
Total gate charge	Q_G	V_{DD} = 800 V, I_D = 138.2 A, V_{GS} = 0/18 V, turn-on pulse			261		nC

(table continues...)

Downloaded from Arrow.com.

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Plateau gate charge	$Q_{GS(pl)}$	V_{DD} = 800 V, I_D = 138.2 A, V_{GS} = 0/18 V, turn-on pulse			57.3		nC
Gate-drain charge	Q_{GD}	V_{DD} = 800 V, I_D = 138.2 A, V_{GS} = 0/18 V, turn-on pulse			64.2		nC
Turn-on delay time	$t_{d(on)}$	V_{DD} = 800 V, I_D = 138.2 A, V_{GS} = 0/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 15 nH, diode: body diode at V_{GS} = 0 V	T_{vj} = 25 °C		32		ns
			T_{vj} = 175 °C		24.4		
Rise time	t_r	V_{DD} = 800 V, I_D = 138.2 A, V_{GS} = 0/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 15 nH, diode: body diode at V_{GS} = 0 V	T_{vj} = 25 °C		21.3		ns
			T_{vj} = 175 °C		19		
Turn-off delay time	$t_{d(off)}$	V_{DD} = 800 V, I_D = 138.2 A, V_{GS} = 0/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 15 nH, diode: body diode at V_{GS} = 0 V	T_{vj} = 25 °C		64.4		ns
			T_{vj} = 175 °C		75.3		
Fall time	t_f	V_{DD} = 800 V, I_D = 138.2 A, V_{GS} = 0/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 15 nH, diode: body diode at V_{GS} = 0 V	T_{vj} = 25 °C		28.2		ns
			T_{vj} = 175 °C		33.3		
Turn-on energy	E_{on}	V_{DD} = 800 V, I_D = 138.2 A, V_{GS} = 0/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 15 nH, diode: body diode at V_{GS} = 0 V	T_{vj} = 25 °C		2.38		mJ
			T_{vj} = 175 °C		3.3		
Turn-off energy	E_{off}	V_{DD} = 800 V, I_D = 138.2 A, V_{GS} = 0/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 15 nH, diode: body diode at V_{GS} = 0 V	T_{vj} = 25 °C		2.53		mJ
			T_{vj} = 175 °C		3.04		
Total switching energy[1)]	E_{tot}	V_{DD} = 800 V, I_D = 138.2 A, V_{GS} = 0/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 15 nH, diode: body diode at V_{GS} = 0 V	T_{vj} = 25 °C		5.52		mJ
			T_{vj} = 175 °C		8.44		

(table continues...)

Downloaded from Arrow.com.

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Turn-on energy at -5 V	E_{on}	V_{DD} = 800 V, I_D = 138.2 A, V_{GS} = -5/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 15 nH, diode: body diode at V_{GS} = -5 V	T_{vj} = 25 °C		2.36		mJ
			T_{vj} = 175 °C		3.27		
Turn-off energy at -5 V	E_{off}	V_{DD} = 800 V, I_D = 138.2 A, V_{GS} = -5/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 15 nH, diode: body diode at V_{GS} = -5 V	T_{vj} = 25 °C		1.46		mJ
			T_{vj} = 175 °C		1.56		
Total switching energy at -5 V[1)]	E_{tot}	V_{DD} = 800 V, I_D = 138.2 A, V_{GS} = -5/18 V, $R_{G,ext}$ = 2.3 Ω, L_σ = 15 nH, diode: body diode at V_{GS} = -5 V	T_{vj} = 25 °C		4.43		µJ
			T_{vj} = 175 °C		6.98		
Virtual junction temperature	T_{vj}			-55		175	°C
Virtual junction temperature	$T_{vj(over)}$	overload, cumulative max. 100 h[2)]				200	°C

1) including E_{fr}
2) up to 5000 cycles. Maximum ΔT limited to 100 K.

***Note**: The chip technology was characterized up to 200 kV/µs. The measured dV/dt was limited by measurement test setup and package.*
Characteristics at T_{vj} = 25°C, unless otherwise specified.

3 Body diode (MOSFET)

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Drain-source voltage	V_{DSS}	T_{vj} ≥ 25 °C		1200	V
Continuous reverse drain current for $R_{th(j-c,max)}$, limited by $T_{vj(max)}$	I_{SDC}	V_{GS} = 0 V	T_c = 25 °C	250	A
			T_c = 100 °C	153.1	
Peak reverse drain current, t_p limited by $T_{vj(max)}$	I_{SM}	V_{GS} = 0 V		725	A

Downloaded from Arrow.com.

Table 6 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Drain-source reverse voltage	V_{SD}	I_{SD} = 138.2 A, V_{GS} = 0 V	T_{vj} = 25 °C		4.2	5.5	V
			T_{vj} = 100 °C		4.1		
			T_{vj} = 175 °C		4		
MOSFET forward recovery charge	Q_{fr}	V_{DD} = 800 V, I_{SD} = 138.2 A, V_{GS} = 0 V, $R_{G,ext}$ = 2.3 Ω, Q_{fr} includes also Q_C	T_{vj} = 25 °C		0.74		µC
			T_{vj} = 175 °C		2.56		
MOSFET peak forward recovery current	I_{frm}	V_{DD} = 800 V, I_{SD} = 138.2 A, V_{GS} = 0 V, $R_{G,ext}$ = 2.3 Ω, Q_{fr} includes also Q_C	T_{vj} = 25 °C		95		A
			T_{vj} = 175 °C		162		
MOSFET forward recovery energy	E_{fr}	V_{DD} = 800 V, I_{SD} = 138.2 A, V_{GS} = 0 V, $R_{G,ext}$ = 2.3 Ω, Q_{fr} includes also Q_C	T_{vj} = 25 °C		0.6		mJ
			T_{vj} = 175 °C		2.1		
MOSFET forward recovery energy at -5 V	E_{fr}	V_{DD} = 800 V, I_{SD} = 138.2 A, V_{GS} = -5 V, $R_{G,ext}$ = 2.3 Ω, Q_{fr} includes also Q_C	T_{vj} = 25 °C		0.61		µJ
			T_{vj} = 175 °C		2.1		
Virtual junction temperature	T_{vj}			-55		175	°C
Virtual junction temperature	$T_{vj(over)}$	overload, cumulative max. 100 h[1)]				200	°C

1) up to 5000 cycles. Maximum ΔT limited to 100 K.


Downloaded from Arrow.com.

4 Characteristics diagrams

Safe operating area (SOA)


$I_D = f(V_{DS})$

$T_{vj} \leq 175\ °C$, $T_c = 25\ °C$




Power dissipation as a function of case temperature

$P_{tot} = f(T_c)$



Maximum DC drain to source current as a function of case temperature limited by bond wire


$I_D = f(T_c)$



Maximum source to drain current as a function of case temperature limited by bond wire

$I_{SD} = f(T_c)$

$V_{GS} = 0\ V$




Downloaded from Arrow.com.

Typical transfer characteristic

$I_D = f(V_{GS})$


V_{DS} = 20 V, t_p = 20 µs



Typical gate-source threshold voltage as a function of junction temperature

$V_{GS(th)} = f(T_{vj})$


I_D = 43.4 mA



Typical output characteristic, V_{GS} as a parameter

$I_D = f(V_{DS})$


T_{vj} = 25 °C, t_p = 20 µs



Typical output characteristic, V_{GS} as a parameter

$I_D = f(V_{DS})$

T_{vj} = 175 °C, t_p = 20 µs




Downloaded from Arrow.com.

Typical on-state resistance as a function of junction temperature

$R_{DS(on)} = f(T_{vj})$


$I_D = 138.2$ A



Typical gate charge

$V_{GS} = f(Q_G)$


$I_D = 138.2$ A, $V_{DS} = 800$ V



Typical capacitance as a function of drain-source voltage

$C = f(V_{DS})$


$f = 100$ kHz, $V_{GS} = 0$ V



Typical reverse drain voltage as a function of junction temperature

$V_{SD} = f(T_{vj})$

$I_{SD} = 138.2$ A, $V_{GS} = 0$ V




Downloaded from Arrow.com.

Typical reverse drain current as a function of reverse drain voltage, V_{GS} as a parameter

$I_{SD} = f(V_{SD})$


$T_{vj} = 25\ °C$, $t_p = 20\ µs$



Typical reverse drain current as a function of reverse drain voltage, V_{GS} as a parameter

$I_{SD} = f(V_{SD})$


$T_{vj} = 175\ °C$, $t_p = 20\ µs$



Typical switching energy as a function of junction temperature, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

$E = f(T_{vj})$


$V_{GS} = 0/18\ V$, $I_D = 138.2\ A$, $R_{G,ext} = 2.3\ Ω$, $V_{DD} = 800\ V$



Typical switching energy as a function of junction temperature, test circuit in Fig. F, 2nd device own body diode: V_{GS} = -5 V

$E = f(T_{vj})$

$V_{GS} = -5/18\ V$, $I_D = 138.2\ A$, $R_{G,ext} = 2.3\ Ω$, $V_{DD} = 800\ V$




Downloaded from Arrow.com.

Typical switching energy as a function of drain current, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

$E = f(I_D)$


V_{GS} = 0/18 V, T_{vj} = 175 °C, $R_{G,ext}$ = 2.3 Ω, V_{DD} = 800 V



Typical switching energy as a function of drain current, test circuit in Fig. F, 2nd device own body diode: V_{GS} = -5 V

$E = f(I_D)$


V_{GS} = -5/18 V, T_{vj} = 175 °C, $R_{G,ext}$ = 2.3 Ω, V_{DD} = 800 V



Typical switching energy as a function of gate resistance, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

$E = f(R_{G,ext})$


V_{GS} = 0/18 V, I_D = 138.2 A, T_{vj} = 175 °C, V_{DD} = 800 V



Typical switching energy as a function of gate resistance, test circuit in Fig. F, 2nd device own body diode: V_{GS} = -5 V

$E = f(R_{G,ext})$

V_{GS} = -5/18 V, I_D = 138.2 A, T_{vj} = 175 °C, V_{DD} = 800 V




Downloaded from Arrow.com.

Typical switching energy as a function of DC link voltage, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

E = f(V_{DD})


V_{GS} = 0/18 V, I_D = 138.2 A, T_{vj} = 175 °C, $R_{G,ext}$ = 2.3 Ω



Typical switching energy as a function of DC link voltage, test circuit in Fig. F, 2nd device own body diode: V_{GS} = -5 V

E = f(V_{DD})


V_{GS} = -5/18 V, I_D = 138.2 A, T_{vj} = 175 °C, $R_{G,ext}$ = 2.3 Ω



Typical switching times as a function of gate resistance, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

t = f($R_{G,ext}$)


V_{GS} = 0/18 V, I_D = 138.2 A, T_{vj} = 175 °C, V_{DD} = 800 V



Typical reverse recovery charge as a function of revere drain current slope, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

Q_{fr} = f(-di_{SD}/dt)

V_{GS} = 0/18 V, I_{SD} = 138.2 A, V_{DD} = 800 V




Downloaded from Arrow.com.

Typical reverse recovery current as a function of reverse drain current slope, test circuit in Fig. F, 2nd device own body diode: V_{GS} = 0 V

$I_{frm} = f(-di_{SD}/dt)$

V_{GS} = 0/18 V, I_{SD} = 138.2 A, V_{DD} = 800 V




Typical switching energy as a function of dead time / blanking time, test circuit in Fig. F, 2nd device own body diode: V_{GS} = -5 V

$E = f(t_{dead})$

V_{GS} = 0/18 V, I_D = 138.2 A, T_{vj} = 175 °C, $R_{G,ext}$ = 2.3 Ω


V_{DD} = 800 V



Max. transient thermal impedance (MOSFET/diode)


$Z_{th(j-c),max} = f(t_p)$

$D = t_p/T$



Downloaded from Arrow.com.

5 Package outlines



PACKAGE - GROUP NUMBER:	PG-HDSOP-22-U03	
DIMENSIONS	**MILLIMETERS**	
	MIN.	MAX.
A	2.25	2.35
A1	0.00	0.15
A2	0.90	
A3	0.50	
b	0.50	0.70
b1	---	0.15
c	0.46	0.58
D	14.90	15.10
D1	12.00	
D2	13.20	
E	20.81	21.11
E1	15.30	15.50
E2	9.83	

DIMENSIONS	**MILLIMETERS**	
	MIN.	MAX.
E3	0.625	
E4	0.45	
E5	0.95	
E6	2.53	
E7	2.40	
E8	0.90	
E9	0.75	
e	1.14	
e1	11.4	
L	1.30	
M	0.60	
N	22	
O	0°	8°
P	0.90	
Q	1.60	
R	1.70	
S	0.631	

NOTES:

ALL METAL SURFACES TIN PLATED EXCEPT AREA OF CUT

DIMENSIONS DO NOT INCLUDE MOLD FLASH, PROTRUSION OR GATE BURRS

Figure 1

Downloaded from Arrow.com.

6 Testing conditions




Figure A. **Definition of switching times**




Figure B. **Definition of body diode switching characteristics**




Figure C. **Definition of switching losses**




Figure D. **Definition of QGD**




Figure E. **Thermal equivalent circuit**




Figure F. **Dynamic test circuit**
Parasitic inductance L_σ,
Parasitic capacitor C_σ,

Figure 2

Downloaded from Arrow.com.

Revision history

Document revision	Date of release	Description of changes
0.10	2024-06-05	Target datasheet
0.20	2024-10-08	Preliminary datasheet
1.00	2025-07-04	Final datasheet
1.10	2025-10-13	Added CTI in Table 1 Increased I_{DM} in Table 2 Added switching information for V_{GS} = -5/18 V in Table 4 and 6 and corresponding diagrams Added I_{SDC} in Table 5 Corrected test conditions and adapt values of the body diode in Table 6 Added SOA diagram on page 8 Added diagram E = f(V_{DD}) @ V_{GS} = 0/18 V Added diagram E = f(V_{DD}) @ V_{GS} = -5/18 V Editorial changes

Downloaded from Arrow.com.

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2025-10-13

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2025 Infineon Technologies AG

All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-ABI270-004

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Downloaded from Arrow.com.