

Film Capacitors

Capacitors for RFI Filtering, Smoothing, General-Purpose

Series/Type: B3256*H/J/T

Date: June 2026

The following products presented in this data sheet are being withdrawn.

Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32561J8683M000		2020-07-17	2020-10-31	2021-01-31
B32561J8683K000		2020-07-17	2020-10-31	2021-01-31
B32561J8683J000		2020-07-17	2020-10-31	2021-01-31

© TDK Electronics AG 2026. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without TDK Electronics' prior express consent is prohibited.



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32561J8473M289		2020-07-17	2020-10-31	2021-01-31
B32561J8473M189		2020-07-17	2020-10-31	2021-01-31
B32561J8473M000		2020-07-17	2020-10-31	2021-01-31
B32561J8473K289		2020-07-17	2020-10-31	2021-01-31
B32561J8473K189		2020-07-17	2020-10-31	2021-01-31
B32561J8473K000		2020-07-17	2020-10-31	2021-01-31
B32561J8473J289		2020-07-17	2020-10-31	2021-01-31
B32561J8473J189		2020-07-17	2020-10-31	2021-01-31
B32561J8473J000		2020-07-17	2020-10-31	2021-01-31
B32561J8333M289		2020-07-17	2020-10-31	2021-01-31
B32561J8333M189		2020-07-17	2020-10-31	2021-01-31
B32561J8333M000		2020-07-17	2020-10-31	2021-01-31
B32561J8333K289		2020-07-17	2020-10-31	2021-01-31
B32561J8333K189		2020-07-17	2020-10-31	2021-01-31
B32561J8333K000		2020-07-17	2020-10-31	2021-01-31
B32561J8333J289		2020-07-17	2020-10-31	2021-01-31
B32561J8333J189		2020-07-17	2020-10-31	2021-01-31
B32561J8333J000		2020-07-17	2020-10-31	2021-01-31
B32561J8223M289		2020-07-17	2020-10-31	2021-01-31
B32561J8223M189		2020-07-17	2020-10-31	2021-01-31
B32561J8223M000		2020-07-17	2020-10-31	2021-01-31
B32561J8223K289		2020-07-17	2020-10-31	2021-01-31
B32561J8223K189		2020-07-17	2020-10-31	2021-01-31
B32561J8223K000		2020-07-17	2020-10-31	2021-01-31
B32561J8223J289		2020-07-17	2020-10-31	2021-01-31
B32561J8223J189		2020-07-17	2020-10-31	2021-01-31
B32561J8223J000		2020-07-17	2020-10-31	2021-01-31
B32561J8154M000		2020-07-17	2020-10-31	2021-01-31
B32561J8154K000		2020-07-17	2020-10-31	2021-01-31
B32561J8154J000		2020-07-17	2020-10-31	2021-01-31
B32561J8153M289		2020-07-17	2020-10-31	2021-01-31
B32561J8153M189		2020-07-17	2020-10-31	2021-01-31
B32561J8153M000		2020-07-17	2020-10-31	2021-01-31
B32561J8153K289		2020-07-17	2020-10-31	2021-01-31
B32561J8153K189		2020-07-17	2020-10-31	2021-01-31
B32561J8153K000		2020-07-17	2020-10-31	2021-01-31
B32561J8153J289		2020-07-17	2020-10-31	2021-01-31
B32561J8153J189		2020-07-17	2020-10-31	2021-01-31



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32561J8153J000		2020-07-17	2020-10-31	2021-01-31
B32561J8104M000		2020-07-17	2020-10-31	2021-01-31
B32561J8104K000		2020-07-17	2020-10-31	2021-01-31
B32561J8104J000		2020-07-17	2020-10-31	2021-01-31
B32561J6683M289		2020-07-17	2020-10-31	2021-01-31
B32561J6683M189		2020-07-17	2020-10-31	2021-01-31
B32561J6683M000		2020-07-17	2020-10-31	2021-01-31
B32561J6683K289		2020-07-17	2020-10-31	2021-01-31
B32561J6683K189		2020-07-17	2020-10-31	2021-01-31
B32561J6683K000		2020-07-17	2020-10-31	2021-01-31
B32561J6683J289		2020-07-17	2020-10-31	2021-01-31
B32561J6683J189		2020-07-17	2020-10-31	2021-01-31
B32561J6683J000		2020-07-17	2020-10-31	2021-01-31
B32561J6474M000		2020-07-17	2020-10-31	2021-01-31
B32561J6474K000		2020-07-17	2020-10-31	2021-01-31
B32561J6474J000		2020-07-17	2020-10-31	2021-01-31
B32561J6473M289		2020-07-17	2020-10-31	2021-01-31
B32561J6473M189		2020-07-17	2020-10-31	2021-01-31
B32561J6473M000		2020-07-17	2020-10-31	2021-01-31
B32561J6473K289		2020-07-17	2020-10-31	2021-01-31
B32561J6473K189		2020-07-17	2020-10-31	2021-01-31
B32561J6473K000		2020-07-17	2020-10-31	2021-01-31
B32561J6473J289		2020-07-17	2020-10-31	2021-01-31
B32561J6473J189		2020-07-17	2020-10-31	2021-01-31
B32561J6473J000		2020-07-17	2020-10-31	2021-01-31
B32561J6334M000		2020-07-17	2020-10-31	2021-01-31
B32561J6334K000		2020-07-17	2020-10-31	2021-01-31
B32561J6334J000		2020-07-17	2020-10-31	2021-01-31
B32561J6333M289		2020-07-17	2020-10-31	2021-01-31
B32561J6333M189		2020-07-17	2020-10-31	2021-01-31
B32561J6333M000		2020-07-17	2020-10-31	2021-01-31
B32561J6333K289		2020-07-17	2020-10-31	2021-01-31
B32561J6333K189		2020-07-17	2020-10-31	2021-01-31
B32561J6333K000		2020-07-17	2020-10-31	2021-01-31
B32561J6333J289		2020-07-17	2020-10-31	2021-01-31
B32561J6333J189		2020-07-17	2020-10-31	2021-01-31
B32561J6333J000		2020-07-17	2020-10-31	2021-01-31
B32561J6224M289		2020-07-17	2020-10-31	2021-01-31



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32561J6224M189		2020-07-17	2020-10-31	2021-01-31
B32561J6224M000		2020-07-17	2020-10-31	2021-01-31
B32561J6224K289		2020-07-17	2020-10-31	2021-01-31
B32561J6224K189		2020-07-17	2020-10-31	2021-01-31
B32561J6224K000		2020-07-17	2020-10-31	2021-01-31
B32561J6224J289		2020-07-17	2020-10-31	2021-01-31
B32561J6224J189		2020-07-17	2020-10-31	2021-01-31
B32561J6224J000		2020-07-17	2020-10-31	2021-01-31
B32561J6154M289		2020-07-17	2020-10-31	2021-01-31
B32561J6154M189		2020-07-17	2020-10-31	2021-01-31
B32561J6154M000		2020-07-17	2020-10-31	2021-01-31
B32561J6154K289		2020-07-17	2020-10-31	2021-01-31
B32561J6154K189		2020-07-17	2020-10-31	2021-01-31
B32561J6154K000		2020-07-17	2020-10-31	2021-01-31
B32561J6154J289		2020-07-17	2020-10-31	2021-01-31
B32561J6154J189		2020-07-17	2020-10-31	2021-01-31
B32561J6154J000		2020-07-17	2020-10-31	2021-01-31
B32561J6104M289		2020-07-17	2020-10-31	2021-01-31
B32561J6104M189		2020-07-17	2020-10-31	2021-01-31
B32561J6104M000		2020-07-17	2020-10-31	2021-01-31
B32561J6104K289		2020-07-17	2020-10-31	2021-01-31
B32561J6104K189		2020-07-17	2020-10-31	2021-01-31
B32561J6104K000		2020-07-17	2020-10-31	2021-01-31
B32561J6104J289		2020-07-17	2020-10-31	2021-01-31
B32561J6104J189		2020-07-17	2020-10-31	2021-01-31
B32561J6104J000		2020-07-17	2020-10-31	2021-01-31
B32561J3684M000		2020-07-17	2020-10-31	2021-01-31
B32561J3684K000		2020-07-17	2020-10-31	2021-01-31
B32561J3684J000		2020-07-17	2020-10-31	2021-01-31
B32561J3474M289		2020-07-17	2020-10-31	2021-01-31
B32561J3474M189		2020-07-17	2020-10-31	2021-01-31
B32561J3474M000		2020-07-17	2020-10-31	2021-01-31
B32561J3474K289		2020-07-17	2020-10-31	2021-01-31
B32561J3474K189		2020-07-17	2020-10-31	2021-01-31
B32561J3474K000		2020-07-17	2020-10-31	2021-01-31
B32561J3474J289		2020-07-17	2020-10-31	2021-01-31
B32561J3474J189		2020-07-17	2020-10-31	2021-01-31
B32561J3474J000		2020-07-17	2020-10-31	2021-01-31



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32561J3334M289		2020-07-17	2020-10-31	2021-01-31
B32561J3334M189		2020-07-17	2020-10-31	2021-01-31
B32561J3334M000		2020-07-17	2020-10-31	2021-01-31
B32561J3334K289		2020-07-17	2020-10-31	2021-01-31
B32561J3334K189		2020-07-17	2020-10-31	2021-01-31
B32561J3334K000		2020-07-17	2020-10-31	2021-01-31
B32561J3334J289		2020-07-17	2020-10-31	2021-01-31
B32561J3334J189		2020-07-17	2020-10-31	2021-01-31
B32561J3334J000		2020-07-17	2020-10-31	2021-01-31
B32561J3224M289		2020-07-17	2020-10-31	2021-01-31
B32561J3224M189		2020-07-17	2020-10-31	2021-01-31
B32561J3224M000		2020-07-17	2020-10-31	2021-01-31
B32561J3224K289		2020-07-17	2020-10-31	2021-01-31
B32561J3224K189		2020-07-17	2020-10-31	2021-01-31
B32561J3224K000		2020-07-17	2020-10-31	2021-01-31
B32561J3224J289		2020-07-17	2020-10-31	2021-01-31
B32561J3224J189		2020-07-17	2020-10-31	2021-01-31
B32561J3224J000		2020-07-17	2020-10-31	2021-01-31
B32561J3154M289		2020-07-17	2020-10-31	2021-01-31
B32561J3154M189		2020-07-17	2020-10-31	2021-01-31
B32561J3154M000		2020-07-17	2020-10-31	2021-01-31
B32561J3154K289		2020-07-17	2020-10-31	2021-01-31
B32561J3154K189		2020-07-17	2020-10-31	2021-01-31
B32561J3154K000		2020-07-17	2020-10-31	2021-01-31
B32561J3154J289		2020-07-17	2020-10-31	2021-01-31
B32561J3154J189		2020-07-17	2020-10-31	2021-01-31
B32561J3154J000		2020-07-17	2020-10-31	2021-01-31
B32561J3105M000		2020-07-17	2020-10-31	2021-01-31
B32561J3105K000		2020-07-17	2020-10-31	2021-01-31
B32561J3105J000		2020-07-17	2020-10-31	2021-01-31
B32561J3104M289		2020-07-17	2020-10-31	2021-01-31
B32561J3104M189		2020-07-17	2020-10-31	2021-01-31
B32561J3104M000		2020-07-17	2020-10-31	2021-01-31
B32561J3104K289		2020-07-17	2020-10-31	2021-01-31
B32561J3104K189		2020-07-17	2020-10-31	2021-01-31
B32561J3104K000		2020-07-17	2020-10-31	2021-01-31
B32561J3104J289		2020-07-17	2020-10-31	2021-01-31
B32561J3104J189		2020-07-17	2020-10-31	2021-01-31



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32561J3104J000		2020-07-17	2020-10-31	2021-01-31
B32561J1684M289		2020-07-17	2020-10-31	2021-01-31
B32561J1684M189		2020-07-17	2020-10-31	2021-01-31
B32561J1684M000		2020-07-17	2020-10-31	2021-01-31
B32561J1684K289		2020-07-17	2020-10-31	2021-01-31
B32561J1684K189		2020-07-17	2020-10-31	2021-01-31
B32561J1684K000		2020-07-17	2020-10-31	2021-01-31
B32561J1684J289		2020-07-17	2020-10-31	2021-01-31
B32561J1684J189		2020-07-17	2020-10-31	2021-01-31
B32561J1684J000		2020-07-17	2020-10-31	2021-01-31
B32561J1335M000		2020-07-17	2020-10-31	2021-01-31
B32561J1335K000		2020-07-17	2020-10-31	2021-01-31
B32561J1335J000		2020-07-17	2020-10-31	2021-01-31
B32561J1225M000		2020-07-17	2020-10-31	2021-01-31
B32561J1225K000		2020-07-17	2020-10-31	2021-01-31
B32561J1225J000		2020-07-17	2020-10-31	2021-01-31
B32561J1155M289		2020-07-17	2020-10-31	2021-01-31
B32561J1155M189		2020-07-17	2020-10-31	2021-01-31
B32561J1155M000		2020-07-17	2020-10-31	2021-01-31
B32561J1155K289		2020-07-17	2020-10-31	2021-01-31
B32561J1155K189		2020-07-17	2020-10-31	2021-01-31
B32561J1155K000		2020-07-17	2020-10-31	2021-01-31
B32561J1155J289		2020-07-17	2020-10-31	2021-01-31
B32561J1155J189		2020-07-17	2020-10-31	2021-01-31
B32561J1155J000		2020-07-17	2020-10-31	2021-01-31
B32561J1105M289		2020-07-17	2020-10-31	2021-01-31
B32561J1105M189		2020-07-17	2020-10-31	2021-01-31
B32561J1105M000		2020-07-17	2020-10-31	2021-01-31
B32561J1105K289		2020-07-17	2020-10-31	2021-01-31
B32561J1105K189		2020-07-17	2020-10-31	2021-01-31
B32561J1105K000		2020-07-17	2020-10-31	2021-01-31
B32561J1105J289		2020-07-17	2020-10-31	2021-01-31
B32561J1105J189		2020-07-17	2020-10-31	2021-01-31
B32561J1105J000		2020-07-17	2020-10-31	2021-01-31
B32561J0685M000		2020-07-17	2020-10-31	2021-01-31
B32561J0685K000		2020-07-17	2020-10-31	2021-01-31
B32561J0685J000		2020-07-17	2020-10-31	2021-01-31
B32561J0475M000		2020-07-17	2020-10-31	2021-01-31



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32561J0475K000		2020-07-17	2020-10-31	2021-01-31
B32561J0475J000		2020-07-17	2020-10-31	2021-01-31
B32561J0335M000		2020-07-17	2020-10-31	2021-01-31
B32561J0335K000		2020-07-17	2020-10-31	2021-01-31
B32561J0335J000		2020-07-17	2020-10-31	2021-01-31
B32561J0225M289		2020-07-17	2020-10-31	2021-01-31
B32561J0225M189		2020-07-17	2020-10-31	2021-01-31
B32561J0225M000		2020-07-17	2020-10-31	2021-01-31
B32561J0225K289		2020-07-17	2020-10-31	2021-01-31
B32561J0225K189		2020-07-17	2020-10-31	2021-01-31
B32561J0225K000		2020-07-17	2020-10-31	2021-01-31
B32561J0225J289		2020-07-17	2020-10-31	2021-01-31
B32561J0225J189		2020-07-17	2020-10-31	2021-01-31
B32561J0225J000		2020-07-17	2020-10-31	2021-01-31
B32561J0155M289		2020-07-17	2020-10-31	2021-01-31
B32561J0155M189		2020-07-17	2020-10-31	2021-01-31
B32561J0155M000		2020-07-17	2020-10-31	2021-01-31
B32561J0155K289		2020-07-17	2020-10-31	2021-01-31
B32561J0155K189		2020-07-17	2020-10-31	2021-01-31
B32561J0155K000		2020-07-17	2020-10-31	2021-01-31
B32561J0155J289		2020-07-17	2020-10-31	2021-01-31
B32561J0155J189		2020-07-17	2020-10-31	2021-01-31
B32561J0155J000		2020-07-17	2020-10-31	2021-01-31
B32561J0105M289		2020-07-17	2020-10-31	2021-01-31
B32561J0105M189		2020-07-17	2020-10-31	2021-01-31
B32561J0105M000		2020-07-17	2020-10-31	2021-01-31
B32561J0105K289		2020-07-17	2020-10-31	2021-01-31
B32561J0105K189		2020-07-17	2020-10-31	2021-01-31
B32561J0105K000		2020-07-17	2020-10-31	2021-01-31
B32561J0105J289		2020-07-17	2020-10-31	2021-01-31
B32561J0105J189		2020-07-17	2020-10-31	2021-01-31
B32561J0105J000		2020-07-17	2020-10-31	2021-01-31

Please contact your nearest TDK sales office if you need support in selecting a suitable substitute. The addresses of our worldwide sales network are presented at www.tdk-electronics.tdk.com/sales.

General purpose (stacked) SilverCap™

Typical applications

- SMPS, converter
- Electronic ballasts
- Compact fluorescent lamps (CFL)
- Ignition

Climatic

- Max. operating temperature: 125 °C
- Climatic category (IEC 60068-1:2013): 55/125/56

Features

- Special dimensions available on request
- High pulse strength
- Small dimensions
- RoHS-compatible

Construction

- Dielectric: polyethylene terephthalate (polyester, PET)
- Stacked-film technology
- Uncoated

Terminals

- Parallel wire leads, lead-free tinned
- Special lead lengths available on request

Marking

Rated capacitance (coded),
rated DC voltage

Delivery mode

Bulk (untaped)

Taped (Ammo pack or reel) for lead spacing ≤15.0 mm.


For notes on taping, refer to chapter "Taping and packing".

Notes on mounting

When mounting these capacitors, take into account creepage distances and clearances to adjacent live parts. The insulating strength of the cut surfaces to other live parts of the circuit is 1.5 times the capacitors rated DC voltage, but is always at least 300 V DC.

Capacitors with 7.5 mm lead spacing are only suitable for use with single-clad printed circuit boards.

Dimensional drawing




Dimensions in mm

Lead spacing $e \pm 0.4$	Lead diameter $d_1 \pm 0.05$	Type
7.5	0.5	B32560
10.0	0.5	B32561
15.0	0.6	B32562J
	0.8	B32562H
22.5	0.8	B32563
27.5	0.8	B32564

Overview of available types

Lead spacing	7.5 mm						10.0 mm						15.0 mm			
Type	B32560						B32561						B32562			
Page	5						7						9			
V _R (V DC)	63	100	250	400	630	1000	63	100	250	400	630	100	250	400	630	
V _{RMS} (V AC)	40	63	160	200	400	500	40	63	160	200	350	63	160	200	350	
C _R (μF)																
0.0010																
0.0015																
0.0022																
0.0033																
0.0047																
0.0068																
0.010																
0.015																
0.022																
0.033																
0.047																
0.068																
0.10																
0.15																
0.22																
0.33																
0.47																
0.68																
1.0																
1.5																
2.2																
3.3																
4.7																
6.8																
10																



B3256*H/J/T


General purpose (stacked) SilverCap™

Overview of available types

Lead spacing	22.5 mm			27.5 mm			
Type	B32563			B32564			
Page	10			11			
V_R (V DC)	100	250	400	100	250	400	420
V_{RMS} (V AC)	63	160	200	63	160	200	200
C_R (μF)							
1.0							
1.5							
2.2							
3.3							
4.7							
6.8							
10							
15							
22							
33							

B32560

General purpose (stacked) SilverCap™



Ordering codes and packing units (lead spacing 7.5 mm)

V_R	V_{RMS} $f \leq 60$ Hz	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Ammo pack pcs./MOQ	Reel pcs./MOQ	Untaped pcs./MOQ
V DC	V AC	μF					
63	40	1.0	$4.0 \times 6.8 \times 9.0$	B32560J0105+***	17600	14400	8000
		1.5	$5.1 \times 7.6 \times 9.0$	B32560J0155+***	13600	11200	4000
		2.2	$6.5 \times 8.2 \times 9.0$	B32560J0225+***	12000	9600	4000
		3.3	$8.5 \times 9.1 \times 9.0$	B32560J0335+000	—	—	2800
		4.7	$9.8 \times 11.0 \times 9.0$	B32560J0475+000	—	—	2000
100	63	0.22	$2.5 \times 5.1 \times 9.0$	B32560J1224+***	24800	20000	15200
		0.33	$2.7 \times 5.7 \times 9.0$	B32560J1334+***	24000	19200	12000
		0.47	$3.4 \times 6.1 \times 9.0$	B32560J1474+***	19200	16000	9600
		0.68	$4.2 \times 6.5 \times 9.0$	B32560J1684+***	16000	12800	7200
		1.0	$5.5 \times 7.0 \times 9.0$	B32560J1105+***	12000	9600	4000
		1.5	$6.7 \times 8.2 \times 9.0$	B32560J1155+***	10000	8000	3200
		2.2	$8.5 \times 9.2 \times 9.0$	B32560J1225+000	—	—	2400
		3.3	$9.5 \times 11.0 \times 9.0$	B32560J1335+000	—	—	1600
250	160	0.047	$2.5 \times 5.2 \times 9.0$	B32560J3473+***	26000	20800	15200
		0.068	$2.6 \times 5.7 \times 9.0$	B32560J3683+***	24800	20000	13600
		0.10	$3.2 \times 6.1 \times 9.0$	B32560J3104+***	24800	16000	9600
		0.15	$3.9 \times 7.0 \times 9.0$	B32560J3154+***	16400	13600	7200
		0.22	$4.9 \times 7.5 \times 9.0$	B32560J3224+***	13600	10400	5200
		0.33	$6.4 \times 8.2 \times 9.0$	B32560J3334+***	10400	8800	3600
		0.47	$7.4 \times 9.8 \times 9.0$	B32560J3474+000	—	—	2400
		0.68	$9.5 \times 11.0 \times 9.0$	B32560J3684+000	—	—	1600

MOQ = Minimum Order Quantity, consisting of 8 packing units.

Further E series and intermediate capacitance values on request.

Special dimensions available on request.

For corresponding design rules, refer to chapter "General technical information", section 1.3.2.

Composition of ordering code

+ = Capacitance tolerance code:

M = $\pm 20\%$

K = $\pm 10\%$


J = $\pm 5\%$

*** = Packaging code:

289 = Ammo pack

189 = Reel

000 = Untaped (lead length 5 – 1 mm)


B32560
General purpose (stacked) SilverCap™
Ordering codes and packing units (lead spacing 7.5 mm)

V_R	V_{RMS} $f \leq 60 \text{ Hz}$	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Ammo pack pcs./MOQ	Reel pcs./MOQ	Untaped pcs./MOQ
V DC	V AC	μF					
400	200	0.0068	$2.5 \times 5.5 \times 9.0$	B32560J6682+***	28000	22400	15200
		0.010	$2.5 \times 5.5 \times 9.0$	B32560J6103+***	25600	20800	14400
		0.015	$2.5 \times 5.5 \times 9.0$	B32560J6153+***	26000	20800	14400
		0.022	$2.5 \times 5.5 \times 9.0$	B32560J6223+***	24800	20000	13600
		0.033	$2.6 \times 6.0 \times 9.0$	B32560J6333+***	24800	20000	12800
		0.047	$3.2 \times 6.5 \times 9.0$	B32560J6473+***	20800	16800	9600
		0.068	$3.8 \times 7.3 \times 9.0$	B32560J6683+***	17200	14400	7200
		0.10	$4.9 \times 7.7 \times 9.0$	B32560J6104+***	13600	11200	4000
		0.15	$6.5 \times 8.2 \times 9.0$	B32560J6154+***	10800	8000	3600
		0.22	$7.7 \times 9.8 \times 9.0$	B32560J6224+000	—	—	2400
630	400	0.0010	$2.5 \times 5.5 \times 9.0$	B32560J8102+***	29600	24000	18400
		0.0015	$2.5 \times 5.5 \times 9.0$	B32560J8152+***	26000	5200	14400
		0.0022	$2.5 \times 5.5 \times 9.0$	B32560J8222+***	26800	21600	14400
		0.0033	$2.5 \times 5.5 \times 9.0$	B32560J8332+***	28000	22400	15200
		0.0047	$2.5 \times 5.5 \times 9.0$	B32560J8472+***	27200	21600	14400
		0.0068	$3.2 \times 6.5 \times 9.0$	B32560J8682+***	30000	18400	10400
		0.010	$3.8 \times 7.5 \times 9.0$	B32560J8103+***	18000	18400	8000
		0.015	$4.6 \times 8.3 \times 9.0$	B32560J8153+000	—	—	4800
		0.022	$5.7 \times 8.6 \times 9.0$	B32560J8223+000	—	—	3200
1000	500	0.0022	$2.5 \times 6.0 \times 9.0$	B32560J9222+***	26000	20800	13600
		0.0033	$3.3 \times 6.5 \times 9.0$	B32560J9332+***	20000	16000	9600
		0.0047	$3.6 \times 7.4 \times 9.0$	B32560J9472+***	18000	15200	7200

MOQ = Minimum Order Quantity, consisting of 8 packing units.

Further E series and intermediate capacitance values on request.

Special dimensions available on request.

For corresponding design rules, refer to chapter "General technical information", section 1.3.2.

Composition of ordering code

+ = Capacitance tolerance code:

M = $\pm 20\%$

K = $\pm 10\%$

J = $\pm 5\%$

*** = Packaging code:


289 = Ammo pack

189 = Reel

000 = Untaped (lead length 5 – 1 mm)

B32561

General purpose (stacked) SilverCap™



Ordering codes and packing units (lead spacing 10 mm)

V_R	V_{RMS} $f \leq 60$ Hz	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Ammo pack pcs./MOQ	Reel pcs./MOQ	Untaped pcs./MOQ
V DC	V AC	μF					
63	40	1.0	$3.5 \times 6.2 \times 11.0$	B32561J0105+***	9920	15200	8000
		1.5	$4.3 \times 6.9 \times 11.0$	B32561J0155+***	8400	12000	5600
		2.2	$5.1 \times 7.9 \times 11.0$	B32561J0225+***	6800	10000	4000
		3.3	$6.4 \times 9.1 \times 11.0$	B32561J0335+000	—	—	2400
		4.7	$7.3 \times 11.0 \times 11.0$	B32561J0475+000	—	—	1600
		6.8	$8.8 \times 12.7 \times 11.0$	B32561J0685+000	—	—	1200
100	63	0.68	$3.6 \times 6.3 \times 11.5$	B32561J1684+***	10080	16000	8000
		1.0	$4.5 \times 6.9 \times 11.5$	B32561J1105+***	8400	12000	4000
		1.5	$5.6 \times 7.8 \times 11.5$	B32561J1155+***	6480	9600	4000
		2.2	$6.9 \times 9.0 \times 11.5$	B32561J1225+000	—	—	2800
		3.3	$7.8 \times 10.5 \times 11.5$	B32561J1335+000	—	—	1600
250	160	0.10	$2.8 \times 5.3 \times 11.5$	B32561J3104+***	12320	18400	10400
		0.15	$3.3 \times 6.0 \times 11.5$	B32561J3154+***	10080	16000	8000
		0.22	$4.2 \times 6.6 \times 11.5$	B32561J3224+***	8320	12000	5600
		0.33	$5.2 \times 7.5 \times 11.5$	B32561J3334+***	6720	10400	4000
		0.47	$6.3 \times 8.5 \times 11.5$	B32561J3474+***	5440	8800	2800
		0.68	$7.5 \times 9.7 \times 11.5$	B32561J3684+000	—	—	1600
		1.0	$9.5 \times 11.0 \times 11.5$	B32561J3105+000	—	—	1200
400	200	0.033	$2.5 \times 5.1 \times 11.5$	B32561J6333+***	12960	18400	12000
		0.047	$2.6 \times 6.0 \times 11.5$	B32561J6473+***	12480	18400	10400
		0.068	$3.2 \times 6.6 \times 11.5$	B32561J6683+***	11120	16800	8000
		0.10	$4.0 \times 6.9 \times 11.5$	B32561J6104+***	8720	13600	5600
		0.15	$5.2 \times 7.7 \times 11.5$	B32561J6154+***	6800	10400	4000
		0.22	$6.6 \times 8.5 \times 11.5$	B32561J6224+***	5440	8000	2800
		0.33	$8.0 \times 9.5 \times 11.5$	B32561J6334+000	—	—	1600
		0.47	$9.8 \times 11.0 \times 11.5$	B32561J6474+000	—	—	1200

MOQ = Minimum Order Quantity, consisting of 8 packing units.
Further E series and intermediate capacitance values on request.

Special dimensions available on request.

For corresponding design rules, refer to chapter "General technical information", section 1.3.2.

Composition of ordering code

+ = Capacitance tolerance code:

M = $\pm 20\%$

K = $\pm 10\%$


J = $\pm 5\%$

*** = Packaging code:

289 = Ammo pack

189 = Reel

000 = Untaped (lead length 5 – 1 mm)


B32561
General purpose (stacked) SilverCap™

Ordering codes and packing units (lead spacing 10 mm)

V_R	V_{RMS} $f \leq 60 \text{ Hz}$	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Ammo pack pcs./MOQ	Reel pcs./MOQ	Untaped pcs./MOQ
V DC	V AC	μF					
630	350	0.015	$2.8 \times 6.3 \times 11.0$	B32561J8153+***	12640	18400	9600
		0.022	$3.4 \times 6.9 \times 11.0$	B32561J8223+***	10400	16000	7200
		0.033	$4.2 \times 7.6 \times 11.0$	B32561J8333+***	8160	12800	4800
		0.047	$5.3 \times 8.0 \times 11.0$	B32561J8473+***	6720	10000	3600
		0.068	$6.3 \times 9.0 \times 11.0$	B32561J8683+000	—	—	2800
		0.10	$7.3 \times 11.4 \times 11.0$	B32561J8104+000	—	—	1600
		0.15	$8.8 \times 13.3 \times 11.0$	B32561J8154+000	—	—	1200

MOQ = Minimum Order Quantity, consisting of 8 packing units.

Further E series and intermediate capacitance values on request.

Special dimensions available on request.

For corresponding design rules, refer to chapter "General technical information", section 1.3.2.

Composition of ordering code

+ = Capacitance tolerance code:

M = $\pm 20\%$

K = $\pm 10\%$

J = $\pm 5\%$

*** = Packaging code:


289 = Ammo pack

189 = Reel

000 = Untaped (lead length 5 – 1 mm)

B32562

General purpose (stacked) SilverCap™



Ordering codes and packing units (lead spacing 15 mm)

V_R	V_{RMS} $f \leq 60$ Hz	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Ammo pack pcs./MOQ	Reel pcs./ MOQ	Untaped pcs./ MOQ
V DC	V AC	μF					
100	63	2.2	$4.9 \times 8.0 \times 16.5$	B32562J1225+***	9520	10400	6400
		3.3	$6.0 \times 9.3 \times 16.5$	B32562J1335+***	7680	8000	4000
		4.7	$7.3 \times 10.6 \times 16.5$	B32562H1475+***	6320	7200	3200
		6.8	$9.0 \times 11.8 \times 16.5$	B32562H1685+***	5120	5600	2320
		10	$11.8 \times 13.0 \times 16.5$	B32562H1106+000	—	—	1600
250	160	0.47	$5.0 \times 6.7 \times 16.5$	B32562J3474+***	9520	10400	7600
		0.68	$6.0 \times 7.8 \times 16.5$	B32562J3684+***	7680	8000	4000
		1.0	$7.0 \times 9.3 \times 16.5$	B32562J3105+***	6640	7200	4000
		1.5	$8.7 \times 11.0 \times 16.5$	B32562H3155+***	5280	5600	2400
		2.2	$10.7 \times 12.8 \times 16.5$	B32562H3225+000	—	—	1600
		3.3	$13.9 \times 14.5 \times 16.5$	B32562H3335+000	—	—	1200
400	200	0.22	$4.7 \times 7.5 \times 16.5$	B32562J6224+***	9920	10400	6800
		0.33	$6.0 \times 8.3 \times 16.5$	B32562J6334+***	7680	8000	4000
		0.47	$7.3 \times 9.3 \times 16.5$	B32562J6474+***	6320	7200	3600
		0.68	$8.9 \times 10.8 \times 16.5$	B32562H6684+***	5120	5600	2400
		1.0	$10.9 \times 12.5 \times 16.5$	B32562H6105+000	—	—	1600
		1.5	$13.7 \times 15.2 \times 16.5$	B32562H6155+000	—	—	800
630	350	0.22	$9.2 \times 12.2 \times 16.5$	B32562H8224+000	—	—	2800
		0.33	$11.2 \times 14.2 \times 16.5$	B32562H8334+000	—	—	2000
		0.47	$13.5 \times 16.3 \times 16.5$	B32562H8474+000	—	—	1440

MOQ = Minimum Order Quantity, consisting of 8 packing units.
Further E series and intermediate capacitance values on request.

Special dimensions available on request.

For corresponding design rules, refer to chapter "General technical information", section 1.3.2.

Composition of ordering code

+ = Capacitance tolerance code:

M = $\pm 20\%$

K = $\pm 10\%$


J = $\pm 5\%$

*** = Packaging code:

289 = Ammo pack

189 = Reel

000 = Untaped (lead length 5 – 1 mm)


B32563
General purpose (stacked) SilverCap™
Ordering codes and packing units (lead spacing 22.5 mm)

V_R	V_{RMS} $f \leq 60 \text{ Hz}$	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Untaped pcs./MOQ
V DC	V AC	μF			
100	63	6.8	$7.0 \times 10.5 \times 24.0$	B32563J1685+000	7360
		10	$8.6 \times 12.2 \times 24.0$	B32563J1106+000	7680
		15	$10.9 \times 14.0 \times 24.0$	B32563J1156+000	4960
		22	$12.8 \times 17.2 \times 24.0$	B32563J1226+000	2880
250	160	2.2	$8.3 \times 11.2 \times 24.0$	B32563J3225+000	5920
		3.3	$10.1 \times 13.5 \times 24.0$	B32563J3335+000	5600
		4.7	$12.2 \times 15.5 \times 24.0$	B32563J3475+000	3120
400	200	1.0	$8.3 \times 11.2 \times 24.0$	B32563J6105+000	6800
		1.5	$10.3 \times 13.2 \times 24.0$	B32563J6155+000	5280
		2.2	$12.6 \times 15.5 \times 24.0$	B32563J6225+000	2880

MOQ = Minimum Order Quantity, consisting of 8 packing units.

Further E series and intermediate capacitance values on request.

Special dimensions available on request.

For corresponding design rules, refer to chapter "General technical information", section 1.3.2.

Composition of ordering code

+ = Capacitance tolerance code:

M = $\pm 20\%$

K = $\pm 10\%$


J = $\pm 5\%$

Packaging code:

000 = Untaped (lead length 5 – 1 mm)

B32564

General purpose (stacked) SilverCap™



Ordering codes and packing units (lead spacing 27.5 mm)

V_R	V_{RMS} $f \leq 60 \text{ Hz}$	C_R	Max. dimensions $w \times h \times l$ mm	Ordering code (composition see below)	Untaped pcs./MOQ
V DC	V AC	μF			
100	63	10	$7.6 \times 11.0 \times 29.0$	B32564J1106+000	5440
		15	$9.1 \times 13.5 \times 29.0$	B32564J1156+000	3440
		22	$11.0 \times 16.0 \times 29.0$	B32564J1226+000	2560
		33	$13.0 \times 19.8 \times 29.0$	B32564J1336+000	2880
250	160	3.3	$7.9 \times 14.0 \times 29.0$	B32564J3335+000	6000
		4.7	$9.6 \times 15.8 \times 29.0$	B32564J3475+000	3200
		6.8	$11.9 \times 18.0 \times 29.0$	B32564J3685+000	2400
		10	$13.8 \times 22.5 \times 29.0$	B32564J3106+000	2240
400	200	1.5	$7.8 \times 14.2 \times 29.0$	B32564J6155+000	6000
		2.2	$9.6 \times 16.4 \times 29.0$	B32564J6225+000	3200
		3.3	$12.2 \times 18.8 \times 29.0$	B32564J6335+000	2640
		4.7	$14.2 \times 22.8 \times 29.0$	B32564J6475+000	2080
420	200	4.7	$16.0 \times 20.0 \times 29.0$	B32564T6475K000	2320
		6.8	$16.0 \times 20.0 \times 29.0$	B32564T6685K000	2320

MOQ = Minimum Order Quantity, consisting of 8 packing units.
Further E series and intermediate capacitance values on request.

Special dimensions available on request.

For corresponding design rules, refer to chapter "General technical information", section 1.3.2.
The technical data given on page 12 do not apply to 420 V series. Please contact your nearest TDK representative if you need further information.

Composition of ordering code

+ = Capacitance tolerance code:


M = $\pm 20\%$

K = $\pm 10\%$

J = $\pm 5\%$

Packaging code:

000 = Untaped (lead length 5 – 1 mm)


B3256*H/J/T
General purpose (stacked) SilverCap™

Technical data

Reference standard: IEC 60384-2:2005. All data given at $T = 20\text{ °C}$, unless otherwise specified.

Operating temperature range	Max. operating temperature $T_{op,max}$ +125 °C Upper category temperature T_{max} +125 °C Lower category temperature T_{min} −55 °C Rated temperature T_R +85 °C			
Dissipation factor $\tan \delta$ (in 10^{-3}) at 20 °C (upper limit values)	at	$C_R \leq 0.1 \mu F$	$0.1 \mu F < C_R \leq 1 \mu F$	$C_R > 1 \mu F$
	1 kHz	8	8	10
	10 kHz	15	15	—
	100 kHz	30	—	—
Insulation resistance R_{ins} or time constant $\tau = C_R \cdot R_{ins}$ at 20 °C, rel. humidity $\leq 65\%$ (minimum as-delivered values)	V_R	$C_R \leq 0.33 \mu F$		$C_R > 0.33 \mu F$
	≤ 100 V DC	3750 M Ω		1250 s
	≥ 250 V DC	7500 M Ω		2500 s
DC test voltage	$1.4 \cdot V_R$, 2 s			
Category voltage V_C (continuous operation with V_{DC} or V_{AC} at $f \leq 60$ Hz)	T_{op} (°C)	DC voltage derating	AC voltage derating	
	$T_{op} \leq 85$	$V_C = V_R$	$V_{C,RMS}=V_{RMS}$	
	$85<T_{op}\leq125$	$V_C = V_R \cdot (165-T_{op})/80$	$V_{C,RMS}=V_{RMS} \cdot (165-T_{op})/80$	
Operating voltage V_{op} for short operating periods (V_{DC} or V_{AC} at $f \leq 60$ Hz)	T_{op} (°C)	DC voltage (max. hours)	AC voltage (max. hours)	
	$T_{op} \leq 100$	$V_{op} = 1.25 \cdot V_C$ (2000 h)	$V_{op} = 1.0 \cdot V_{C,RMS}$ (2000 h)	
	$100<T_{op}\leq125$	$V_{op} = 1.25 \cdot V_C$ (1000 h)	$V_{op} = 1.0 \cdot V_{C,RMS}$ (1000 h)	
Reliability:				
Failure rate λ	2 fit ($\leq 1 \cdot 10^{-9}$ /h) at $0.5 \cdot V_R$, 40 °C			
Service life t_{SL}	100 000 h at $1.0 \cdot V_R$, 85 °C			
	For conversion to other operating conditions and temperatures, refer to chapter "Reliability".			
Failure criteria:				
Total failure	Short circuit or open circuit			
Failure due to variation of parameters	Capacitance change $ \Delta C/C $		> 10%	
	Dissipation factor $\tan \delta$		> 2 · upper limit value	
	Insulation resistance R_{ins}		< 150 M Ω ($C_R \leq 0.33 \mu F$)	
	or time constant $\tau = C_R \cdot R_{ins}$		< 50 s ($C_R > 0.33 \mu F$)	

Pulse handling capability

"dV/dt" represents the maximum permissible voltage change per unit of time for non-sinusoidal voltages, expressed in V/μs.

"k₀" represents the maximum permissible pulse characteristic of the waveform applied to the capacitor, expressed in V²/μs.

Note:


The values of dV/dt and k₀ provided below must not be exceeded in order to avoid damaging the capacitor. These parameters are given for isolated pulses in such a way that the heat generated by one pulse will be completely dissipated before applying the next pulse. For a train of pulses, please refer to the curves of permissible AC voltage-current versus frequency.

dV/dt values

Lead spacing		7.5 mm	10 mm	15 mm	22.5 mm	27.5 mm
V _R V DC	V _{RMS} V AC	dV/dt in V/μs				
63	40	120	60	—	—	—
100	63	150	75	50	50	25
250	160	200	150	100	100	50
400	200	275	175	125	125	60
420	200	—	—	—	—	60
630	350	—	320	150	—	—
630	400	320	—	—	—	—
1000	500	360	—	—	—	—

k₀ values


Lead spacing		7.5 mm	10 mm	15 mm	22.5 mm	27.5 mm
V _R V DC	V _{RMS} V AC	k ₀ in V ² /μs				
63	40	15 000	7500	—	—	—
100	63	30 000	15 000	10 000	10 000	5 000
250	160	100 000	75 000	50 000	50 000	25 000
400	200	220 000	140 000	100 000	100 000	50 000
420	200	—	—	—	—	50 000
630	350	—	400 000	190 000	—	—
630	400	400 000	—	—	—	—
1000	500	720 000	—	—	—	—



B3256*H/J/T


General purpose (stacked) SilverCap™

Impedance Z versus frequency f (typical values)



B32560

General purpose (stacked) SilverCap™




Permissible AC voltage V_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)


For $T_A > 55^\circ\text{C}$, please refer to "General technical information", section 3.2.3.

Lead spacing 7.5 mm


63 V DC/40 V AC




100 V DC/63 V AC




250 V DC/160 V AC



400 V DC/200 V AC





B32560


General purpose (stacked) SilverCap™

Permissible AC voltage V_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)


For $T_A > 55^\circ\text{C}$, please refer to "General technical information", section 3.2.3.

Lead spacing 7.5 mm

630 V DC/400 V AC




1000 V DC/500 V AC



B32561

General purpose (stacked) SilverCap™




Permissible AC voltage V_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)


For $T_A > 55^\circ\text{C}$, please refer to "General technical information", section 3.2.3.

Lead spacing 10 mm


63 V DC/40 V AC




100 V DC/63 V AC




250 V DC/160 V AC



400 V DC/200 V AC





B32561


General purpose (stacked) SilverCap™


Permissible AC voltage V_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)

For $T_A > 55^\circ\text{C}$, please refer to "General technical information", section 3.2.3.

Lead spacing 10 mm

630 V DC/350 V AC






Permissible AC voltage V_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)


For $T_A > 55^\circ\text{C}$, please refer to "General technical information", section 3.2.3.

Lead spacing 15 mm


100 V DC/63 V AC




250 V DC/160 V AC




400 V DC/200 V AC



630 V DC/350 V AC





B32563


General purpose (stacked) SilverCap™

Permissible AC voltage V_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)


For $T_A > 55^\circ\text{C}$, please refer to "General technical information", section 3.2.3.

Lead spacing 22.5 mm


100 V DC/63 V AC



250 V DC/160 V AC




400 V DC/200 V AC



B32564

General purpose (stacked) SilverCap™




Permissible AC voltage V_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)


For $T_A > 55^\circ\text{C}$, please refer to "General technical information", section 3.2.3.

Lead spacing 27.5 mm


100 V DC/63 V AC




250 V DC/160 V AC




400 V DC/200 V AC



420 V DC/200 V AC






B32560

General purpose (stacked) SilverCap™


Permissible current I_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)

Lead spacing 7.5 mm


63 V DC/40 V AC




100 V DC/63 V AC



250 V DC/160 V AC




400 V DC/200 V AC



B32560


General purpose (stacked) SilverCap™




Permissible current I_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)


Lead spacing 7.5 mm

630 V DC/400 V AC



1000 V DC/500 V AC






B32561

General purpose (stacked) SilverCap™


Permissible current I_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ C$)

Lead spacing 10 mm


63 V DC/40 V AC




100 V DC/63 V AC



250 V DC/160 V AC




400 V DC/200 V AC



B32561


General purpose (stacked) SilverCap™




Permissible current I_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)

Lead spacing 10 mm

630 V DC/350 V AC






B32562

General purpose (stacked) SilverCap™


Permissible current I_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)

Lead spacing 15 mm


100 V DC/63 V AC




250 V DC/160 V AC



400 V DC/200 V AC




630 V DC/350 V AC



B32563


General purpose (stacked) SilverCap™




Permissible current I_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)

Lead spacing 22.5 mm


100 V DC/63 V AC




250 V DC/160 V AC



400 V DC/200 V AC






B32564

General purpose (stacked) SilverCap™


Permissible current I_{RMS} versus frequency f (for sinusoidal waveforms, $T_A \leq 55^\circ\text{C}$)

Lead spacing 27.5 mm


100 V DC/63 V AC




250 V DC/160 V AC



400 V DC/200 V AC




420 V DC/200 V AC



Testing and Standards

Test	Reference	Conditions of test	Performance requirements
Electrical parameters	IEC 60384-2:2005	Voltage proof, 1.4 V _R , 1 minute Insulation resistance, R _{ins} Capacitance, C Dissipation factor, tan δ	Within specified limits
Robustness of terminations	IEC 60068-2-21:2006	Tensile strength (test Ua1) Wire diameter Tensile force 0.3 < d ₁ ≤ 0.5 mm 5 N 0.5 < d ₁ ≤ 0.8 mm 10 N	No visible damage Capacitance and tan δ within specified limits
Resistance to soldering heat	IEC 60068-2-20:2008, test Tb, method 1A	Solder bath temperature at 260 ± 5 °C, immersion for 4 seconds (lead spacing ≤ 10mm) 10 seconds (lead spacing > 10mm)	ΔC/C ₀ ≤ 2% Δ tan δ ≤ 0.003 for C ≤ 1 μF Δ tan δ ≤ 0.002 for C > 1 μF
Rapid change of temperature	IEC 60384-2:2005	T _A = lower category temperature T _B = upper category temperature Five cycles, duration t = 30 min.	ΔC/C ₀ ≤ 5% Δ tan δ ≤ 0.003 for C ≤ 1 μF Δ tan δ ≤ 0.002 for C > 1 μF R _{ins} ≥ 50% of initial limit
Vibration	IEC 60384-2:2005	Test Fc: vibration sinusoidal Displacement: 0.75 mm Acceleration: 98 m/s ² Frequency: 10 Hz ... 500 Hz Test duration: 3 orthogonal axes, 2 hours each axe	No visible damage
Bump	IEC 60384-2:2005	Test Eb: Total 4000 bumps with 390 m/s ² mounted on PCB Duration: 6 ms	ΔC/C ₀ ≤ 5% Δ tan δ ≤ 0.003 for C ≤ 1 μF Δ tan δ ≤ 0.002 for C > 1 μF R _{ins} ≥ 50% of initial limit
Climatic sequence	IEC 60384-2:2005	Dry heat Tb / 16 h Damp heat cyclic, 1 st cycle +55 °C / 24 h / 95% ... 100% RH Cold Ta / 2 h Damp heat cyclic, 5 cycles +55 °C / 24 h / 95% ... 100% RH	ΔC/C ₀ ≤ 5% Δ tan δ ≤ 0.005 for C ≤ 1 μF Δ tan δ ≤ 0.003 for C > 1 μF R _{ins} ≥ 50% of initial limit
Damp heat, steady state	IEC 60384-2:2005	Test Ca 40 °C / 93% RH / 56 days	No visible damage ΔC/C ₀ ≤ 5% Δ tan δ ≤ 0.005 R _{ins} ≥ 50% of initial limit



B3256*H/J/T

General purpose (stacked) SilverCap™

Test	Reference	Conditions of test	Performance requirements
Endurance A	IEC 60384-2:2005	85 °C / 1.25 V _R / 2000 hours	No visible damage $ \Delta C/C_0 \leq 5\%$ $ \Delta \tan \delta \leq 0.003$ for $C \leq 1 \mu\text{F}$ $ \Delta \tan \delta \leq 0.002$ for $C > 1 \mu\text{F}$ $R_{\text{ins}} \geq 50\%$ of initial limit
Endurance B	IEC 60384-2:2005	125 °C / 1.25 V _C / 2000 hours	No visible damage $ \Delta C/C_0 \leq 5\%$ $ \Delta \tan \delta \leq 0.003$ for $C \leq 1 \mu\text{F}$ $ \Delta \tan \delta \leq 0.002$ for $C > 1 \mu\text{F}$ $R_{\text{ins}} \geq 50\%$ of initial limit

Mounting guidelines

1 Soldering

1.1 Solderability of leads

The solderability of terminal leads is tested to IEC 60068-2-20, test Ta, method 1.

Before a solderability test is carried out, terminals are subjected to accelerated ageing (to IEC 60068-2-2, test Ba: 4 h exposure to dry heat at 155 °C). Since the ageing temperature is far higher than the upper category temperature of the capacitors, the terminal wires should be cut off from the capacitor before the ageing procedure to prevent the solderability being impaired by the products of any capacitor decomposition that might occur.


Solder bath temperature	235 ±5 °C
Soldering time	2.0 ±0.5 s
Immersion depth	2.0 +0/–0.5 mm from capacitor body or seating plane
Evaluation criteria:	
Visual inspection	Wetting of wire surface by new solder ≥90%, free-flowing solder

1.2 Resistance to soldering heat


Resistance to soldering heat is tested to IEC 60068-2-20, test Tb, method 1.

Conditions:

Series	Solder bath temperature	Soldering time
MKT boxed (except $2.5 \times 6.5 \times 7.2$ mm) coated uncoated (lead spacing >10 mm)	260 ± 5 °C	10 ± 1 s
MFP		
MKP (lead spacing >7.5 mm)		
MKT boxed (case $2.5 \times 6.5 \times 7.2$ mm)		5 ± 1 s
MKP (lead spacing ≤ 7.5 mm)		<4 s
MKT uncoated (lead spacing ≤ 10 mm) insulated (B32559)		recommended soldering profile for MKT uncoated (lead spacing ≤ 10 mm) and insulated (B32559)



Immersion depth	2.0 +0/−0.5 mm from capacitor body or seating plane
Shield	Heat-absorbing board, (1.5 ±0.5) mm thick, between capacitor body and liquid solder
Evaluation criteria:	
Visual inspection	No visible damage
$\Delta C/C_0$	2% for MKT/MKP/MFP 5% for EMI suppression capacitors
$\tan \delta$	As specified in sectional specification



B3256*H/J/T

General purpose (stacked) SilverCap™

1.3 General notes on soldering


Permissible heat exposure loads on film capacitors are primarily characterized by the upper category temperature T_{max} . Long exposure to temperatures above this type-related temperature limit can lead to changes in the plastic dielectric and thus change irreversibly a capacitor's electrical characteristics. For short exposures (as in practical soldering processes) the heat load (and thus the possible effects on a capacitor) will also depend on other factors like:

- Pre-heating temperature and time
- Forced cooling immediately after soldering
- Terminal characteristics:
diameter, length, thermal resistance, special configurations (e.g. crimping)
- Height of capacitor above solder bath
- Shadowing by neighboring components
- Additional heating due to heat dissipation by neighboring components
- Use of solder-resist coatings

The overheating associated with some of these factors can usually be reduced by suitable countermeasures. For example, if a pre-heating step cannot be avoided, an additional or reinforced cooling process may possibly have to be included.

TDK recommendations



As a reference, the recommended wave soldering profile for our film capacitors is as follows:



T_s : Capacitor body maximum temperature at wave soldering

T_p : Capacitor body maximum temperature at pre-heating

KMK1745-A-E



Body temperature should follow the description below:

- MKP capacitor
 - During pre-heating: $T_p \leq 110\text{ }^{\circ}\text{C}$
 - During soldering: $T_s \leq 120\text{ }^{\circ}\text{C}$, $t_s \leq 45\text{ s}$
- MKT capacitor
 - During pre-heating: $T_p \leq 125\text{ }^{\circ}\text{C}$
 - During soldering: $T_s \leq 160\text{ }^{\circ}\text{C}$, $t_s \leq 45\text{ s}$

When SMD components are used together with leaded ones, the film capacitors should not pass into the SMD adhesive curing oven. The leaded components should be assembled after the SMD curing step.

Leaded film capacitors are not suitable for reflow soldering.


In order to ensure proper conditions for manual or selective soldering, the body temperature of the capacitor (T_s) must be $\leq 120\text{ }^{\circ}\text{C}$.

One recommended condition for manual soldering is that the tip of the soldering iron should be $< 360\text{ }^{\circ}\text{C}$ and the soldering contact time should be no longer than 3 seconds.

For uncoated MKT capacitors with lead spacings $\leq 10\text{ mm}$ (B32560/B32561) the following measures are recommended:

- pre-heating to not more than $110\text{ }^{\circ}\text{C}$ in the preheater phase
- rapid cooling after soldering

Please refer to TDK Film Capacitor Data Book in case more details are needed.



B3256*H/J/T

General purpose (stacked) SilverCap™

Cautions and warnings

- Do not exceed the upper category temperature (UCT).
- Do not apply any mechanical stress to the capacitor terminals.
- Avoid any compressive, tensile or flexural stress.
- Do not move the capacitor after it has been soldered to the PC board.
- Do not pick up the PC board by the soldered capacitor.
- Do not place the capacitor on a PC board whose PTH hole spacing differs from the specified lead spacing.
- Do not exceed the specified time or temperature limits during soldering.
- Avoid external energy inputs, such as fire or electricity.
- Avoid overload of the capacitors.
- Consult us if application is with severe temperature and humidity condition.
- There are no serviceable or repairable parts inside the capacitor. Opening the capacitor or any attempts to open or repair the capacitor will void the warranty and liability of TDK.
- Please note that the standards referred to in this publication may have been revised in the meantime.

The table below summarizes the safety instructions that must always be observed. A detailed description can be found in the relevant sections of the chapters "General technical information" and "Mounting guidelines".

Topic	Safety information	Reference chapter "General technical information"
Storage conditions	Make sure that capacitors are stored within the specified range of time, temperature and humidity conditions.	4.5 "Storage conditions"
Flammability	Avoid external energy, such as fire or electricity (passive flammability), avoid overload of the capacitors (active flammability) and consider the flammability of materials.	5.3 "Flammability"
Resistance to vibration	Do not exceed the tested ability to withstand vibration. The capacitors are tested to IEC 60068-2-6:2007. TDK offers film capacitors specially designed for operation under more severe vibration regimes such as those found in automotive applications. Consult our catalog "Film Capacitors for Automotive Electronics".	5.2 "Resistance to vibration"

Topic	Safety information	Reference chapter "Mounting guidelines"
Soldering	Do not exceed the specified time or temperature limits during soldering.	1 "Soldering"
Cleaning	Use only suitable solvents for cleaning capacitors.	2 "Cleaning"

Topic	Safety information	Reference chapter "Mounting guidelines"
Embedding of capacitors in finished assemblies	When embedding finished circuit assemblies in plastic resins, chemical and thermal influences must be taken into account. Caution: Consult us first, if you also wish to embed other uncoated component types!	3 "Embedding of capacitors in finished assemblies"

Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.


Detailed information can be found on the Internet under www.tdk-electronics.tdk.com/orderingcodes.

Correlation of data sheet values and modelling tool outputs

Data sheet values and results of design tools may deviate as they have not been derived in the same context.

While data sheets show individual parameter statements without considering a possible dependency to other parameters. Tools model a complete given scenario as input and processed inside the tool.

Furthermore as we constantly strive to improve our models, the results of tools can change over time and be a non-binding indication only.




B3256*H/J/T

General purpose (stacked) SilverCap™

Symbols and terms

Symbol	English	German
α	Heat transfer coefficient	Wärmeübergangszahl
α_C	Temperature coefficient of capacitance	Temperaturkoeffizient der Kapazität
A	Capacitor surface area	Kondensatoroberfläche
β_C	Humidity coefficient of capacitance	Feuchtekoeffizient der Kapazität
C	Capacitance	Kapazität
C_R	Rated capacitance	Nennkapazität
ΔC	Absolute capacitance change	Absolute Kapazitätsänderung
$\Delta C/C$	Relative capacitance change (relative deviation of actual value)	Relative Kapazitätsänderung (relative Abweichung vom Ist-Wert)
$\Delta C/C_R$	Capacitance tolerance (relative deviation from rated capacitance)	Kapazitätstoleranz (relative Abweichung vom Nennwert)
dt	Time differential	Differentielle Zeit
Δt	Time interval	Zeitintervall
ΔT	Absolute temperature change (self-heating)	Absolute Temperaturänderung (Selbsterwärmung)
$\Delta \tan \delta$	Absolute change of dissipation factor	Absolute Änderung des Verlustfaktors
ΔV	Absolute voltage change	Absolute Spannungsänderung
dV/dt	Time differential of voltage function (rate of voltage rise)	Differentielle Spannungsänderung (Spannungsflankensteilheit)
$\Delta V/\Delta t$	Voltage change per time interval	Spannungsänderung pro Zeitintervall
E	Activation energy for diffusion	Aktivierungsenergie zur Diffusion
ESL	Self-inductance	Eigeninduktivität
ESR	Equivalent series resistance	Ersatz-Serienwiderstand
f	Frequency	Frequenz
f_1	Frequency limit for reducing permissible AC voltage due to thermal limits	Grenzfrequenz für thermisch bedingte Reduzierung der zulässigen Wechselspannung
f_2	Frequency limit for reducing permissible AC voltage due to current limit	Grenzfrequenz für strombedingte Reduzierung der zulässigen Wechselspannung
f_r	Resonant frequency	Resonanzfrequenz
F_D	Thermal acceleration factor for diffusion	Therm. Beschleunigungsfaktor zur Diffusion
F_T	Derating factor	Deratingfaktor
i	Current (peak)	Stromspitze
I_C	Category current (max. continuous current)	Kategoriestrom (max. Dauerstrom)

Symbol	English	German
I_{RMS}	(Sinusoidal) alternating current, root-mean-square value	(Sinusförmiger) Wechselstrom
i_z	Capacitance drift	Inkonstanz der Kapazität
k_0	Pulse characteristic	Impulskennwert
L_S	Series inductance	Serieninduktivität
λ	Failure rate	Ausfallrate
λ_0	Constant failure rate during useful service life	Konstante Ausfallrate in der Nutzungsphase
λ_{test}	Failure rate, determined by tests	Experimentell ermittelte Ausfallrate
P_{diss}	Dissipated power	Abgegebene Verlustleistung
P_{gen}	Generated power	Erzeugte Verlustleistung
Q	Heat energy	Wärmeenergie
ρ	Density of water vapor in air	Dichte von Wasserdampf in Luft
R	Universal molar constant for gases	Allg. Molarkonstante für Gas
R	Ohmic resistance of discharge circuit	Ohmscher Widerstand des Entladekreises
R_i	Internal resistance	Innenwiderstand
R_{ins}	Insulation resistance	Isolationswiderstand
R_P	Parallel resistance	Parallelwiderstand
R_S	Series resistance	Serienwiderstand
S	severity (humidity test)	Schärfegrad (Feuchtetest)
t	Time	Zeit
T	Temperature	Temperatur
τ	Time constant	Zeitkonstante
$\tan \delta$	Dissipation factor	Verlustfaktor
$\tan \delta_D$	Dielectric component of dissipation factor	Dielektrischer Anteil des Verlustfaktors
$\tan \delta_P$	Parallel component of dissipation factor	Parallelanteil des Verlustfaktors
$\tan \delta_S$	Series component of dissipation factor	Serienanteil des Verlustfaktors
T_A	Temperature of the air surrounding the component	Temperatur der Luft, die das Bauteil umgibt
T_{max}	Upper category temperature	Obere Kategorietemperatur
T_{min}	Lower category temperature	Untere Kategorietemperatur
t_{OL}	Operating life at operating temperature and voltage	Betriebszeit bei Betriebstemperatur und -spannung
T_{op}	Operating temperature, $T_A + \Delta T$	Betriebstemperatur, $T_A + \Delta T$
T_R	Rated temperature	Nenntemperatur
T_{ref}	Reference temperature	Referenztemperatur
t_{SL}	Reference service life	Referenz-Lebensdauer



B3256*H/J/T

General purpose (stacked) SilverCap™

Symbol	English	German
V_{AC}	AC voltage	Wechselspannung
V_C	Category voltage	Kategoriespannung
$V_{C,RMS}$	Category AC voltage	(Sinusförmige) Kategorie-Wechselspannung
V_{CD}	Corona-discharge onset voltage	Teilentlade-Einsatzspannung
V_{ch}	Charging voltage	Ladespannung
V_{DC}	DC voltage	Gleichspannung
V_{FB}	Fly-back capacitor voltage	Spannung (Flyback)
V_i	Input voltage	Eingangsspannung
V_o	Output voltage	Ausgangsspannung
V_{op}	Operating voltage	Betriebsspannung
V_p	Peak pulse voltage	Impuls-Spitzenspannung
V_{pp}	Peak-to-peak voltage Impedance	Spannungshub
V_R	Rated voltage	Nennspannung
$\hat{V}_R$	Amplitude of rated AC voltage	Amplitude der Nenn-Wechselspannung
V_{RMS}	(Sinusoidal) alternating voltage, root-mean-square value	(Sinusförmige) Wechselspannung
V_{SC}	S-correction voltage	Spannung bei Anwendung "S-correction"
V_{sn}	Snubber capacitor voltage	Spannung bei Anwendung "Beschaltung"
Z	Impedance	Scheinwiderstand
e	Lead spacing	Rastermaß

Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to our General Terms and Conditions of Supply**.

Important notes

7. **Our manufacturing sites serving the automotive business apply the IATF 16949 standard.** The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that **only requirements mutually agreed upon can and will be implemented in our Quality Management System.** For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
8. The trade names EPCOS, CarXield, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, ModCap, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap, XieldCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2024-02