
MOSFET

650V CoolMOS™ CFD7A SJ Power Device

650V CoolMOS™ CFD7A is Infineon's latest generation of market leading automotive qualified high voltage CoolMOS™ MOSFETs. In addition to the well-known attributes of high quality and reliability required by the automotive industry, the new CoolMOS™ CFD7A series provides for an integrated fast body diode and can be used for PFC and resonant switching topologies like the ZVS phase-shift full-bridge and LLC.

Q-DPAK




Features

- Latest 650V automotive qualified technology with integrated fast body diode on the market featuring ultra low Q_{rr}
- Lowest FOM $R_{DS(on)}$*Q_g and $R_{DS(on)}$*E_{oss}
- 100% avalanche tested
- Best-in-class $R_{DS(on)}$ in SMD and THD packages

Benefits

- Lower switching losses enabling higher switching frequencies
- High quality and reliability
- Advanced controllability due to kelvin source
- Increased efficiency in light load and full load conditions



Potential applications

Suitable for PFC and DC-DC stages for:

- Unidirectional and bidirectional DC-DC converters,
- On-Board battery Chargers

Product validation

Qualified according to Automotive applications.
Product validation according to AEC-Q101.

Please note: For production part approval process (PPAP) release we propose to share application related information during an early design phase to avoid delays in PPAP release. Please contact Infineon sales office. The source and sense source pins are not exchangeable. Their exchange might lead to malfunction. For paralleling 4pin MOSFET devices the placement of the gate resistor is generally recommended to be on the Driver Source instead of the Gate.

Table 1 Key performance parameters

Parameter	Value	Unit
V_{DS}	650	V
$R_{DS(on),max}$	125	mΩ
$Q_{g,typ}$	32	nC
$I_{D,pulse}$	66	A
E_{oss} @ 400V	5.0	µJ
Body diode di_F/dt	1300	A/µs

Part number	Package	Marking	Related links
IPDQ65R125CFD7A	PG-HDSOP-22	65A125F7	see Appendix A

Downloaded from Arrow.com.

Table of contents

Description 1
Maximum ratings 3
Thermal characteristics 4
Electrical characteristics 5
Electrical characteristics diagrams 7
Test circuits 11
Package outlines 12
Appendix A 15
Revision history 16
Trademarks 17
Disclaimer 17

Downloaded from Arrow.com.

1 Maximum ratings

at T_j = 25°C, unless otherwise specified

Table 2 Maximum ratings

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Continuous drain current [1]	I_D	-	-	24	A	T_C=25°C
				15		T_C=100°C
Pulsed drain current [2]	$I_{D,pulse}$	-	-	66	A	T_C=25°C
Avalanche energy, single pulse	E_{AS}	-	-	78	mJ	I_D=4.0A; V_{DD}=50V; see table 10
Avalanche current, single pulse	I_{AS}	-	-	4.0	A	-
MOSFET dv/dt ruggedness	dv/dt	-	-	120	V/ns	V_{DS}=0...400V
Gate source voltage (static)	V_{GS}	-20	-	20	V	static;
Gate source voltage (dynamic)	$V_{GS,pulse}$	-30	-	30	V	$f_{repetition}$≤100kHz, t_{pulse} ≤ 2ns
Power dissipation	P_{tot}	-	-	160	W	T_C=25°C
Storage temperature	T_{stg}	-55	-	150	°C	-
Operating junction temperature	T_j	-40		150	°C	
Mounting torque	-	-		n.a.	Ncm	
Continuous diode forward current	I_S	-	-	24	A	T_C=25°C
Diode pulse current [2]	$I_{S,pulse}$			66		
Reverse diode dv/dt [3]	dv/dt	-	-	70	V/ns	V_{DS}=0...400V, I_{SD}≤7.8A, T_j=25°C see table 8
Maximum diode commutation speed	di_F/dt			1300	A/µs	

[1] Limited by $T_{j\,max}$.

[2] Pulse width t_p limited by $T_{j,max}$

[3] Identical low side and high side switch with identical R_G

Downloaded from Arrow.com.

2 Thermal characteristics

Table 3 Thermal characteristics

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Thermal resistance, junction - case	R_{thJC}	-	-	0.78	°C/W	-
Soldering temperature, reflow soldering allowed	T_{sold}	-	-	260	°C	reflow MSL1

Downloaded from Arrow.com.

3 Electrical characteristics

at T_j=25°C, unless otherwise specified

Table 4 Static characteristics

For applications with applied blocking voltage > 425 V, it is required that the customer evaluates the impact of cosmic radiation effect in early design phase and contacts the Infineon sales office for the necessary technical support by Infineon.

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Drain-source breakdown voltage	$V_{(BR)DSS}$	650	-	-	V	V_{GS}=0V, I_D=1mA
Gate threshold voltage [4]	$V_{(GS)th}$	3.5	4	4.5	V	V_{DS}=V_{GS}, I_D=0.39mA
Zero gate voltage drain current	I_{DSS}	-	-	1	µA	V_{DS}=650V, V_{GS}=0V, T_j=25°C
			30	-		V_{DS}=650V, V_{GS}=0V, T_j=150°C
Gate-source leakage current incl. protection diode	I_{GSS}	-	-	1	µA	V_{GS}=20V, V_{DS}=0V
Drain-source on-state resistance	$R_{DS(on)}$	-	0.108	0.125	Ω	V_{GS}=10V, I_D=7.8A, T_j=25°C
			0.24	-		V_{GS}=10V, I_D=7.8A, T_j=150°C
Gate resistance	R_G	-	6	-	Ω	f=250kHz, open drain

[4] We do not recommend using the CoolMOS™ mentioned in this datasheet to operate in “linear mode”. For assessment of potential “linear mode”, please contact Infineon sales office.

Table 5 Dynamic characteristics

External parasitic elements (PCB layout) influence switching behavior significantly.
Stray inductances and coupling capacitances must be minimized.
For layout recommendations please use provided application notes or contact Infineon sales office.

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Input capacitance	C_{iss}	-	1566	-	pF	V_{GS}=0V, V_{DS}=400V, f=250kHz
Output capacitance	C_{oss}		26			
Effective output capacitance, energy related [5]	$C_{o(er)}$	-	63	-	pF	V_{GS}=0V, V_{DS}=0...400V
Effective output capacitance, time related [6]	$C_{o(tr)}$	-	656	-	pF	I_D=constant, V_{GS}=0V, V_{DS}=0...400V
Turn-on delay time	$t_{d(on)}$	-	20	-	ns	V_{DD}=400V, V_{GS}=13V, I_D=7.8A, R_G=10.2Ω; see table 9
Rise time	t_r		8			
Turn-off delay time	$t_{d(off)}$		95			
Fall time	t_f		5			

[5] $C_{o(er)}$ is a fixed capacitance that gives the same stored energy as C_{oss} while V_{DS} is rising from 0 to 400V

[6] $C_{o(tr)}$ is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to 400V

Downloaded from Arrow.com.

Table 6 Gate charge characteristics

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Gate to source charge	Q_{gs}	-	9	-	nC	V_{DD}=400V, I_D=7.8A, V_{GS}=0 to 10V
Gate to drain charge	Q_{gd}		10		nC	
Gate charge total	Q_g		32		nC	
Gate plateau voltage	$V_{plateau}$		5.7		V	


Table 7 Reverse diode characteristics

Parameter	Symbol	Values			Unit	Note / Test condition
		Min.	Typ.	Max.		
Diode forward voltage	V_{SD}	-	1.0	-	V	V_{GS}=0V, I_F=7.8A, T_j=25°C
Reverse recovery time	t_{rr}	-	105	-	ns	V_R=400V, I_F=7.8A, di_F/dt=100A/µs; see table 8
Reverse recovery charge	Q_{rr}		0.52		µC	
Peak reverse recovery current	I_{rrm}		8.6		A	

Downloaded from Arrow.com.


4 Electrical characteristics diagrams

Diagram 1: Power dissipation




P_{tot}=f(T_C)

Diagram 2: Safe operating area




I_D=f(V_{DS}); T_C=25 °C; D=0; parameter: t_p

Diagram 3: Safe operating area



I_D=f(V_{DS}); T_C=80 °C; D=0; parameter: t_p


Diagram 4: Max. transient thermal impedance



Z_{thJC} =f(t_P); parameter: D=t_p/T


Downloaded from Arrow.com.

Diagram 5: Typ. output characteristics




I_D=f(V_{DS}); T_j=25 °C; parameter: V_{GS}

Diagram 6: Typ. output characteristics




I_D=f(V_{DS}); T_j=125 °C; parameter: V_{GS}

Diagram 7: Typ. drain-source on-state resistance



$R_{DS(on)}$=f(I_D); T_j=125 °C; parameter: V_{GS}

Diagram 8: Drain-source on-state resistance



$R_{DS(on)}$=f(T_j); I_D=7.8 A; V_{GS}=10 V

Downloaded from Arrow.com.






Diagram 9: Typ. transfer characteristics	Diagram 10: Typ. gate charge
	
I_D=f(V_{GS}); V_{DS}=20V; parameter: T_j	V_{GS}=f(Q_{gate}); I_D=7.8 A pulsed; parameter: V_{DD}

Diagram 11: Forward characteristics of reverse diode	Diagram 12: Avalanche energy
	
I_F=f(V_{SD}); parameter: T_j	E_{AS}=f(T_j); I_D=4.0 A; V_{DD}=50 V


Downloaded from Arrow.com.

Diagram 13: Drain-source breakdown voltage




$V_{BR(DSS)}$=f(T_j); I_D=1 mA

Diagram 14: Typ. capacitances



C=f(V_{DS}); V_{GS}=0 V; f=250 kHz

Diagram 15: Typ. Coss stored energy



E_{oss}=f(V_{DS})

Downloaded from Arrow.com.

5 Test circuits

Table 8 Diode characteristics



Test circuit for diode characteristics	Diode recovery waveform
	

Table 9 Switching times (ss)






Switching times test circuit for inductive load	Switching times waveform
	

Table 10 Unclamped inductive load (ss)

Unclamped inductive load test circuit	Unclamped inductive waveform
	

Downloaded from Arrow.com.

6 Package outlines



PACKAGE - GROUP NUMBER:	PG-HDSOP-22-U01	
DIMENSIONS	MILLIMETERS	
	MIN.	MAX.
A	2.25	2.35
A1	0.00	0.15
A2	0.89	1.10
A3	0.5	
b	0.50	0.70
b1	0.50	0.90
c	0.46	0.58
D	15.30	15.50
D1	10.23	10.43
E	14.90	15.10
E1	11.91	12.11
e	1.14	
N	22	
H	20.86	21.06
L	1.20	1.40
O	0°	8°

NOTES:

1. ALL DIMENSIONS REFER TO JEDEC STANDARD TO-252 AND DO NOT INCLUDE MOLD FLASH OR PROTRUSIONS.
2. ALL METAL SUFACES ARE TIN PLATED, EXCEPT AREA OF CUT.

Figure 1 Outline PG-HDSOP-22, dimensions in mm

Downloaded from Arrow.com.




Figure 2 Footprint drawing PG-HDSOP-22, dimensions in mm

Downloaded from Arrow.com.




Figure 3 Packaging variant PG-HDSOP-22, dimensions in mm

Downloaded from Arrow.com.

7 Appendix A

Table 11 Related links

- IFX CoolMOS™ CFD7A Webpage
- IFX CoolMOS™ CFD7A application note
- IFX CoolMOS™ CFD7A simulation model
- IFX Design tools

Downloaded from Arrow.com.

Revision history

IPDQ65R125CFD7A

Revision 2026-03-01, Rev. 2.2

Previous revisions

Revision	Date	Subjects (major changes since last revision)
2.0	2022-08-30	Release of final version
2.1	2022-12-14	Updated Benefits section, Thermal characteristics parameter
2.2	2026-03-01	Implementation of standardized Infineon Umbrella-Templates for package drawings

Downloaded from Arrow.com.

Trademarks
All referenced product or service names and trademarks are the property of their respective owners.

Published by Infineon Technologies AG, Am Campeon 1-15, 85579 Neubiberg, Germany
Copyright (c) 2026 Infineon Technologies AG and its affiliates. All Rights Reserved.

Important notice
Products which may also include samples and may be comprised of hardware or software or both ("Product(s)") are sold or provided and delivered by Infineon Technologies AG and its affiliates ("Infineon") subject to the terms and conditions of the frame supply contract or other written agreement(s) executed by a customer and Infineon or, in the absence of the foregoing, the applicable Sales Conditions of Infineon. General terms and conditions of a customer or deviations from applicable Sales Conditions of Infineon shall only be binding for Infineon if and to the extent Infineon has given its express written consent.

For the avoidance of doubt, Infineon disclaims all warranties of non-infringement of third-party rights and implied warranties such as warranties of fitness for a specific use/purpose or merchantability.

Infineon shall not be responsible for any information with respect to samples, the application or customer's specific use of any Product or for any examples or typical values given in this document.

The data contained in this document is exclusively intended for technically qualified and skilled customer representatives. It is the responsibility of the customer to evaluate the suitability of the Product for the intended application and the customer's specific use and to verify all relevant technical data contained in this document in the intended application and the customer's specific use. The customer is responsible for properly designing, programming, and testing the functionality and safety of the intended application, as well as complying with any legal requirements related to its use.

Unless otherwise explicitly approved by Infineon, Products may not be used in any application where a failure of the Products or any consequences of the use thereof can reasonably be expected to result in personal injury. However, the foregoing shall not prevent the customer from using any Product in such fields of use that Infineon has explicitly designed and sold it for, provided that the overall responsibility for the application lies with the customer.

Infineon expressly reserves the right to use its content for commercial text and data mining (TDM) according to applicable laws, e.g. Section 44b of the German Copyright Act (UrhG).

If the Product includes security features: Because no computing device can be absolutely secure, and despite security measures implemented in the Product, Infineon does not guarantee that the Product will be free from intrusion, data theft or loss, or other breaches ("Security Breaches"), and Infineon shall have no liability arising out of any Security Breaches.

If this document includes or references software:
The software is owned by Infineon under the intellectual property laws and treaties of the United States, Germany, and other countries worldwide. All rights reserved. Therefore, you may use the software only as provided in the software license agreement accompanying the software. If no software license agreement applies, Infineon hereby grants you a personal, non-exclusive, non-transferable license (without the right to sublicense) under its intellectual property rights in the software (a) for software provided in source code form, to modify and reproduce the software solely for use with Infineon hardware products, only internally within your organization, and (b) to distribute the software in binary code form externally to end users, solely for use on Infineon hardware products. Any other use, reproduction, modification, translation, or compilation of the software is prohibited.

For further information on the Product, technology, delivery terms and conditions, and prices, please contact your nearest Infineon office or visit https://www.infineon.com.

Downloaded from Arrow.com.