
finder
RELAYING INNOVATION

62
SERIES

Power relays 16 A

- Road / tunnel lighting
- Industrial furnaces and ovens
- Burners, boilers and furnaces
- Control and management of electric power
- Punches, cleaners, planers and sanders
- Control panels
- Circuit breakers and switches
- Industrial motors







Downloaded from Arrow.com.

Finder reserves the right to make changes to its products and their technical specifications at any time and without prior notice, as part of its policy of continuous improvement.
The information contained in this document is provided for indicative purposes only and does not constitute a contractual obligation; errors and omissions excepted.
In the event of any discrepancy between the printed and online versions, the latter, available at findernet.com, shall prevail.

Downloaded from Arrow.com.

Printed circuit mount
16 A Power relay

- 2 & 3 Pole changeover contacts or NO (≥ 3 mm contact gap)
- AC coils & DC coils
- Reinforced insulation between coil and contacts according to EN 60335-1, with 6 mm clearance & 8 mm creepage distance
- SELV coil-contact separator option

	62.22/62.23	62.22-4300/62.23-4300
		
	• 2 & 3 pole changeover contact • PCB mount	• 2 & 3 pole normally open contact (≥ 3 mm contact gap) • PCB mount
		
		
	62.22 Copper side view	62.23 Copper side view	62.22 - 4300 Copper side view	62.23 - 4300 Copper side view

* Distance between contacts ≥ 3 mm (EN 60730-1).
** Maximum peak current is 120 A - 5 ms (NO contact).

FOR UL RATINGS SEE:
"General technical information" page IX

For outline drawing see page 12









Contact specification					
Contact configuration		2 CO (DPDT)	3 CO (3PDT)	2 NO (DPST-NO), ≥ 3 mm*	3 NO (3PST-NO), ≥ 3 mm*
Rated current/Maximum peak current	A	16/120**		16/120**	
Rated voltage/ Maximum switching voltage	V AC	250/400		250/400	
Rated load AC1	VA	4000		4000	
Rated load AC15 (230 V AC)	VA	750		750	
Motor rating (230/400 V AC)	kW	0.8/—	0.8/1.5	0.8/—	0.8/1.5
Breaking capacity DC1: 24/110/220 V	A	16/0.6/0.4		16/1.1/0.7	
Minimum switching load	mW (V/mA)	1000 (10/10)		1000 (10/10)	
Standard contact material		$AgSnO_2$		$AgSnO_2$	
Coil specification					
Nominal voltage (U_N)	V AC (50/60 Hz)	6 - 12 - 24 - 48 - 60 - 110 - 120 - 230 - 240 - 400			
	V DC	6 - 12 - 24 - 48 - 60 - 110 - 125 - 220			
Rated power AC/DC	VA (50 Hz)/W	2.2/1.3		3/3	
Operating range	AC	(0.8…1.1)U_N		(0.85…1.1)U_N	
	DC	(0.8…1.1)U_N		(0.85…1.1)U_N	
Holding voltage	AC/DC	0.8 U_N / 0.6 U_N		0.8 U_N / 0.6 U_N	
Must drop-out voltage	AC/DC	0.2 U_N / 0.1 U_N		0.2 U_N / 0.1 U_N	
Technical data					
Mechanical life AC/DC	cycles	$10 \cdot 10^6/30 \cdot 10^6$		$10 \cdot 10^6/30 \cdot 10^6$	
Electrical life at rated load AC1	cycles	$100 \cdot 10^3$		$100 \cdot 10^3$	
Operate/release time	ms	11/4		15/3	
Insulation between coil and contacts (1.2/50 µs)	kV	6		6	
Dielectric strength between open contacts	V AC	1500		3000	
Ambient temperature range	°C	–40…+70		–40…+50	
Environmental protection		RT I		RT I	
Approvals (according to type)					

Downloaded from Arrow.com.

A

Plug-in mount/Faston 187
16 A Power relay

- Plug-in (92 series sockets) or Faston 187 (4.8 x 0.5 mm) with optional mounting adaptors
- 2 & 3 Pole changeover contacts or NO (≥ 3 mm contact gap)
- AC coils & DC coils
- UL Listing (certain relay/socket combinations)
- LED, mechanical indicator & test button options
- Reinforced insulation between coil and contacts according to EN 60335-1, with 6 mm clearance & 8 mm creepage distance
- SELV coil-contact separator option
- Sockets and accessories
- European Patent

	62.32/62.33		62.32-4300/62.33-4300	
				
	• 2 & 3 pole changeover contact • Plug-in/Faston 187		• 2 & 3 pole normally open contact (≥ 3 mm contact gap) • Plug-in/Faston 187	
				
				
	62.32	62.33	62.32-4300	62.33-4300

* Distance between contacts ≥ 3 mm (EN 60730-1).
** Maximum peak current is 120 A - 5 ms (NO contact).

For UL ratings see:
"General technical information" page IX

For outline drawing see page 12

Contact specification					
Contact configuration		2 CO (DPDT)	3 CO (3PDT)	2 NO (DPST-NO), ≥ 3 mm*	3 NO (3PST-NO), ≥ 3 mm*
Rated current/Maximum peak current	A	16/120**		16/120**	
Rated voltage/ Maximum switching voltage	V AC	250/400		250/400	
Rated load AC1	VA	4000		4000	
Rated load AC15 (230 V AC)	VA	750		750	
Motor rating (230/400 V AC)	kW	0.8/—	0.8/1.5	0.8/—	0.8/1.5
Breaking capacity DC1: 24/110/220 V	A	16/0.6/0.4		16/1.1/0.7	
Minimum switching load	mW (V/mA)	1000 (10/10)		1000 (10/10)	
Standard contact material		$AgSnO_2$		$AgSnO_2$	
Coil specification					
Nominal voltage (U_N)	V AC (50/60 Hz)	6 - 12 - 24 - 48 - 60 - 110 - 120 - 230 - 240 - 400			
	V DC	6 - 12 - 24 - 48 - 60 - 110 - 125 - 220			
Rated power AC/DC	VA (50 Hz)/W	2.2/1.3		3/3	
Operating range	AC	$(0.8…1.1)U_N$		$(0.85…1.1)U_N$	
	DC	$(0.8…1.1)U_N$		$(0.85…1.1)U_N$	
Holding voltage	AC/DC	0.8 U_N / 0.6 U_N		0.8 U_N / 0.6 U_N	
Must drop-out voltage	AC/DC	0.2 U_N / 0.1 U_N		0.2 U_N / 0.1 U_N	
Technical data					
Mechanical life AC/DC	cycles	$10 \cdot 10^6/30 \cdot 10^6$		$10 \cdot 10^6/30 \cdot 10^6$	
Electrical life at rated load AC1	cycles	$100 \cdot 10^3$		$100 \cdot 10^3$	
Operate/release time	ms	11/4		15/3	
Insulation between coil and contacts (1.2/50 µs)	kV	6		6	
Dielectric strength between open contacts	V AC	1500		3000	
Ambient temperature range	°C	–40…+70		–40…+50	
Environmental protection		RT I		RT I	
Approvals (according to type)					


VII-2026, www.findernet.com


Downloaded from Arrow.com.


Flange mount/Faston 250
16 A Power relay


- Faston 250 (6.3 x 0.8 mm) termination Flange or optional mounting adaptors
- 2 & 3 Pole changeover contacts or NO (≥ 3 mm contact gap)
- AC coils & DC coils
- LED, mechanical indicator & test button options
- Reinforced insulation between coil and contacts according to EN 60335-1, with 6 mm clearance & 8 mm creepage distance
- SELV coil-contact separator option
- European Patent

62.82/62.83	62.82-4300/62.83-4300
	
• 2 & 3 pole changeover contact • Flange mount/Faston 250	• 2 & 3 pole normally open contact (≥ 3 mm contact gap) • Flange mount/Faston 250











* Distance between contacts ≥ 3 mm (EN 60730-1).
** Maximum peak current is 120 A - 5 ms (NO contact).

FOR UL RATINGS SEE:
"General technical information" page IX


For outline drawing see page 13




62.82



62.83



62.82-4300



62.83-4300



Contact specification					
Contact configuration		2 CO (DPDT)	3 CO (3PDT)	2 NO (DPST-NO), ≥ 3 mm*	3 NO (3PST-NO), ≥ 3 mm*
Rated current/Maximum peak current	A	16/120**		16/120**	
Rated voltage/ Maximum switching voltage	V AC	250/400		250/400	
Rated load AC1	VA	4000		4000	
Rated load AC15 (230 V AC)	VA	750		750	
Motor rating (230/400 V AC)	kW	0.8/—	0.8/1.5	0.8/—	0.8/1.5
Breaking capacity DC1: 24/110/220 V	A	16/0.6/0.4		16/1.1/0.7	
Minimum switching load	mW (V/mA)	1000 (10/10)		1000 (10/10)	
Standard contact material		$AgSnO_2$		$AgSnO_2$	
Coil specification					
Nominal voltage (U_N)	V AC (50/60 Hz)	6 - 12 - 24 - 48 - 60 - 110 - 120 - 230 - 240 - 400			
	V DC	6 - 12 - 24 - 48 - 60 - 110 - 125 - 220			
Rated power AC/DC	VA (50 Hz)/W	2.2/1.3		3/3	
Operating range	AC	$(0.8…1.1)U_N$		$(0.85…1.1)U_N$	
	DC	$(0.8…1.1)U_N$		$(0.85…1.1)U_N$	
Holding voltage	AC/DC	0.8 U_N / 0.6 U_N		0.8 U_N / 0.6 U_N	
Must drop-out voltage	AC/DC	0.2 U_N / 0.1 U_N		0.2 U_N / 0.1 U_N	
Technical data					
Mechanical life AC/DC	cycles	$10 \cdot 10^6/30 \cdot 10^6$		$10 \cdot 10^6/30 \cdot 10^6$	
Electrical life at rated load AC1	cycles	$100 \cdot 10^3$		$100 \cdot 10^3$	
Operate/release time	ms	11/4		15/3	
Insulation between coil and contacts (1.2/50 µs)	kV	6		6	
Dielectric strength between open contacts	V AC	1500		3000	
Ambient temperature range	°C	–40…+70		–40…+50	
Environmental protection		RT I		RT I	
Approvals (according to type)					

Downloaded from Arrow.com.

A

Plug-in mount/Faston 187
Magnetic blow power relay

- Plug-in (92 series sockets) or Faston 187 (4.8 x 0.5 mm) with optional mounting adaptors
- 1 & 2 Pole NO contacts
- High DC load (resistive and inductive) switching capability
- DC coils
- Reinforced insulation between coil and contacts according to EN 60335-1, with 6 mm clearance & 8 mm creepage distance
- Cadmium free contact material
- Sockets and accessories

	62.31-4800	62.32-4800
		
	• 1 pole normally open contact (double break, ≥ 4.2 mm contact gap) • Plug-in/Faston 187	• 2 pole normally open contact (≥ 2.1 mm contact gap) • Plug-in/Faston 187
		
* Maximum peak current 120 A - 5 ms.		
For outline drawing see page 13	62.31-4800	62.32-4800
Contact specification		
Contact configuration	1 NO (SPST-NO) double break, ≥ 4.2 mm	2 NO (DPST-NO), ≥ 2.1 mm
Rated current/Maximum peak current A	16/30*	16/30*
Rated voltage/ Maximum switching voltage V AC	250/400	250/400
Rated load AC1 VA	4000	4000
Breaking capacity DC1: 24/125/220 V A	16/16/12	16/12/6
Breaking capacity DC inductive (L/R = 40 ms): 24/125/220 V A	16/5/3	10/2/1.2
Minimum switching load mW (V/mA)	1000 (10/10)	1000 (10/10)
Standard contact material	$AgSnO_2$	$AgSnO_2$
Coil specification		
Nominal voltage (U_N) V DC	6 - 12 - 24 - 48 - 60 - 110 - 125 - 220	
Rated power DC W	1.3	1.3
Operating range DC	$(0.85…1.1)U_N$	$(0.85…1.1)U_N$
Holding voltage DC	0.6 U_N	0.6 U_N
Must drop-out voltage DC	0.1 U_N	0.1 U_N
Technical data		
Mechanical life DC cycles	$10 \cdot 10^6$	$10 \cdot 10^6$
Electrical life at rated load DC1 cycles	$100 \cdot 10^3$	$100 \cdot 10^3$
Operate/release time ms	16/5	16/5
Insulation between coil and contacts (1.2/50 µs) kV	6	6
Dielectric strength between open contacts V AC	3000	2000
Ambient temperature range °C	–40…+70	–40…+70
Environmental protection	RT I	RT I
Approvals (according to type)		

VII-2026, www.findernet.com

Downloaded from Arrow.com.

Ordering information

Example: 62 series power relay + Faston 250 (6.3 x 0.8 mm), rear flange mount, 2 NO (DPST-NO), 12 V DC coil.

6 2	. 8	2	. 9	. 0 1 2	. 4	3	0	0
					A	B	C	D

Series

Type
2 = PCB
3 = Plug-in
8 = Faston 250 (6.3 x 0.8 mm) with rear flange mount

No. of poles
1 = 1 pole (double break)
2 = 2 pole
3 = 3 pole

Coil version
8 = AC (50/60 Hz)
9 = DC

Coil voltage
See coil specifications

A: Contact material
4 = $AgSnO_2$

B: Contact circuit
0 = CO (nPDT)
3 = NO (nPST), ≥ 3 mm contact gap
5 = CO (nPDT) + additional physical separator between coil and contacts (for SELV applications)
6 = NO (nPST), ≥ 3 mm contact gap + additional physical separator between coil and contacts (for SELV applications)
8 = NO (1 pole double break or 2 pole) with magnetic blow


C: Options
0 = None
2 = Mechanical indicator
3 = LED (AC)
4 = Lockable test button + mechanical indicator
5* = Lockable test button + LED (AC)
54* = Lockable test button + LED (AC) + mechanical indicator
6* = LED + diode (DC, polarity positive to pin A/A1)
7* = Lockable test button + LED + diode (DC, polarity positive to pin A/A1)
74* = Lockable test button + LED + diode (DC, polarity positive to pin A/A1) + mechanical indicator
* Options not available for 220 V DC and 400 V AC versions.

D: Special versions
0 = Standard
6 = Rear flange mount
9 = Type 62.82/83 without rear flange mount


Selecting features and options: only combinations in the same row are possible.
Preferred selections for best availability are shown in **bold.**

Type	Coil version	A	B	C	D
62.22/23	AC-DC	4	**0** - 3 - 5 - 6	**0**	**0**
62.32/33	AC-DC	4	0 - 3 - 5 - 6	0	0 - 6
	AC-DC	4	**0** - 5	2 - **4**	**0** - 6
	AC	4	**0**	2 - 3 - **4** - 5	**0** - 6
	AC	4	0 - 3	3	0 - 6
	AC	4	0	54	/
	DC	4	**0**	**4** - 6 - 7	**0** - 6
	DC	4	0 - 3	6	0 - 6
	DC	4	0	74	/
62.31/32	DC	4	**8**	**0**	**0**
62.82/83	AC-DC	4	**0** - 3 - 5 - 6	**0**	**0** - 9
	AC-DC	4	0 - 5	2 - 4	0
	AC	4	0	2 - 3 - 4 - 5	0
	AC	4	0 - 3	3	0
	DC	4	0	4 - 6 - 7	0
	DC	4	0 - 3	6	0


Descriptions: Options and Special versions




C: Option 3, 5, 54
LED (AC)



C: Option 6, 7, 74
LED + diode (DC, polarity positive to pin A/A1)



B: Contact circuit 5, 6
Additional physical separator between coil and contacts (for SELV applications)



B: Contact circuit 8
Magnetic blow





Lockable test button and mechanical flag indicator (0040, 0050, 0054, 0070, 0074)

The dual-purpose Finder test button can be used in two ways:

Case 1) The plastic pip (located directly above the test button) remains intact. In this case, when the test button is pushed, the contacts operate. When the test button is released the contacts return to their former state.

Case 2) The plastic pip is broken-off (using an appropriate cutting tool). In this case, (in addition to the above function), when the test button is pushed and rotated, the contacts are latched in the operating state, and remain so until the test button is rotated back to its former position. In both cases ensure that the test button actuation is swift and decisive.

Downloaded from Arrow.com.

Technical data

A


Insulation according to EN 61810-1							
			2 CO - 3 CO	2 NO - 3 NO	1 NO*	2 NO*	
Nominal voltage of supply system		V AC	230/400	230/400	230/400	230/400	
Rated insulation voltage		V AC	400	400	400	400	
Pollution degree			3	3	3	3	
Insulation between coil and contact set							
Type of insulation			Reinforced	Reinforced	Reinforced	Reinforced	
Overvoltage category			III	III	III	III	
Rated impulse voltage		kV (1.2/50 µs)	6	6	6	6	
Dielectric strength		V AC	4000	4000	4000	4000	
Insulation between adjacent contacts							
Type of insulation			Basic	Basic	—	Basic	
Overvoltage category			III	III	—	III	
Rated impulse voltage		kV (1.2/50 µs)	4	4	—	4	
Dielectric strength		V AC	2500	2500	—	2500	
Insulation between open contacts							
Type of disconnection			Micro-disconnection	Full-disconnection	Full-disconnection	Full-disconnection**	
Overvoltage category			—	III	III	II	
Rated impulse voltage		kV (1.2/50 µs)	—	4	4	2.5	
Dielectric strength		V AC/kV (1.2/50 µs)	1500/2	3000/4	3000/4	2000/2.5	
Insulation between coil terminals							
Rated impulse voltage (according to EN 61180)		kV (1.2/50 µs)	4				
Other data							
Bounce time: NO/NC		ms	1/5 (changeover)	3/— (normally open)	3/— (normally open)	3/— (normally open)	
Vibration resistance (10…150)Hz: NO/NC		g	20/8				
Shock resistance		g	15				
Power lost to the environment			**2 pole (CO)**	**3 pole (CO)**	**2 pole (NO)**	**3 pole (NO)**	**1 pole (NO)***	**2 pole (NO)***
	without contact current	W	1.3	1.3	3	3	1.3	1.3
	with rated current	W	3.3	4.3	5	6	3	3.3
Recommended distance between relays mounted on PCB		mm	≥ 5				—	

* Magnetic blow version
** Only in applications where over voltage category II is permitted. In applications of over voltage category III: Micro-disconnection.


Downloaded from Arrow.com.

Contact specification


F 62 - Electrical life (AC) v contact current



H 62 - Maximum DC1 breaking capacity
Changeover contacts




H 62 - Maximum DC1 breaking capacity
Normally open contacts




- When switching a resistive load (DC1) having voltage and current values under the curve, an electrical life of ≥ 100 · 10^3 can be expected.
- In the case of DC13 loads, the connection of a diode in parallel with the load will permit a similar electrical life as for a DC1 load.
  Note: the release time of the load will be increased.

H 62 - Maximum DC breaking capacity 62.31.9.xxx.4800



H 62 -Maximum DC breaking capacity 62.32.9.xxx.4800



- When switching a resistive load (DC1), or a DC13 load with a diode in parallel to the load, having voltage and current values under the DC1 curve, an electrical life of ≥ 100 · 10^3 can be expected. Note: the release time for the load will be increased.
- When switching a DC13 load without a diode in parallel to the load, the DC13 curve applies and an electrical life of ≥ 80 · 10^3 can be expected.

Downloaded from Arrow.com.

Coil specifications

A

DC version data

Nominal voltage	Coil code	Operating range		Resistance	Rated coil consumption
U_N		U_{min}	U_{max}	R	I at U_N
V		V	V	Ω	mA
6	**9**.006	4.8	6.6	28	214
12	**9**.012	9.6	13.2	110	109
24	**9**.024	19.2	26.4	445	54
48	**9**.048	38.4	52.8	1770	27
60	**9**.060	48	66	2760	21.7
110	**9**.110	88	121	9420	11.7
125	**9**.125	100	138	12000	10.4
220	**9**.220	176	242	37300	5.8

AC version data

Nominal voltage	Coil code	Operating range		Resistance	Rated coil consumption
U_N		U_{min}	U_{max}	R	I at U_N (50Hz)
V		V	V	Ω	mA
6	**8**.006	4.8	6.6	4.6	367
12	**8**.012	9.6	13.2	19	183
24	**8**.024	19.2	26.4	74	90
48	**8**.048	38.4	52.8	290	47
60	**8**.060	48	66	450	37
110	**8**.110	88	121	1600	20
120	**8**.120	96	132	1940	18.6
230	**8**.230	184	253	7250	10.5
240	**8**.240	192	264	8500	9.2
400	**8**.400	320	440	19800	6

DC (NO/nPST-NO) version data - ≥ 3 mm

Nominal voltage	Coil code	Operating range		Resistance	Rated coil consumption
U_N		U_{min}	U_{max}	R	I at U_N
V		V	V	Ω	mA
6	**9**.006	5.1	6.6	12	500
12	**9**.012	10.2	13.2	48	250
24	**9**.024	20.4	26.4	192	125
48	**9**.048	40.8	52.8	770	63
60	**9**.060	51	66	1200	50
110	**9**.110	93.5	121	4200	26
125	**9**.125	106	138	5200	24
220	**9**.220	187	242	17600	12.5

AC (NO/nPST-NO) version data - ≥ 3 mm

Nominal voltage	Coil code	Operating range		Resistance	Rated coil consumption
U_N		U_{min}	U_{max}	R	I at U_N (50Hz)
V		V	V	Ω	mA
6	**8**.006	5.1	6.6	4	540
12	**8**.012	10.2	13.2	14	275
24	**8**.024	20.4	26.4	62	130
48	**8**.048	40.8	52.8	220	70
60	**8**.060	51	66	348	55
110	**8**.110	93.5	121	1200	30
120	**8**.120	106	137	1350	24
230	**8**.230	196	253	5000	14
240	**8**.240	204	264	6300	12.5
400	**8**.400	340	440	14700	7.8

DC (NO/nPST-NO) magnetic blow version - ≥ 2.1 mm or ≥ 4.2 mm


Nominal voltage	Coil code	Operating range		Resistance	Rated coil consumption
U_N		U_{min}	U_{max}	R	I at U_N
V		V	V	Ω	mA
6	**9**.006	5.1	6.6	28	214
12	**9**.012	10.2	13.2	110	109
24	**9**.024	20.4	26.4	445	54
48	**9**.048	40.8	52.8	1770	27
60	**9**.060	51	66	2760	21.7
110	**9**.110	93.5	121	9420	11.7
125	**9**.125	106	138	12000	10.4
220	**9**.220	154*	242	37300	5.8

* Special version with U_{min} = 70% U_N

Downloaded from Arrow.com.


Coil specifications

R 62 - DC coil operating range v ambient temperature
Changeover contacts




1 - Max. permitted coil voltage.
2 - Min. pick-up voltage with coil at ambient temperature.

R 62 - AC coil operating range v ambient temperature
Changeover contacts




1 - Max. permitted coil voltage.
2 - Min. pick-up voltage with coil at ambient temperature.

R 62 - DC coil operating range v ambient temperature
Normally open contacts




1 - Max. permitted coil voltage.
2 - Min. pick-up voltage with coil at ambient temperature.

R 62 - AC coil operating range v ambient temperature
Normally open contacts



1 - Max. permitted coil voltage.
2 - Min. pick-up voltage with coil at ambient temperature.

R 62 - DC coil operating range v ambient temperature
Normally open contacts - magnetic blow version



1 - Max. permitted coil voltage.
2 - Min. pick-up voltage with coil at ambient temperature.


Downloaded from Arrow.com.

Outline drawings

A


Type 62.22

62.22-4300




Type 62.23

62.23-4300




Type 62.32

62.32-4300



Type 62.33

62.33-4300




VII-2026, www.findernet.com

Downloaded from Arrow.com.

Outline drawings


Type 62.82

62.82-4300




Type 62.83


62.83-4300



Type 62.31-4800



Type 62.32-4800



VII-2026, www.findernet.com

Downloaded from Arrow.com.

Accessories




062.10



062.10 with relay

Mounting adaptor for types 62.3x and 62.8x.xxxx.xxx9 (M4)	062.10



062.10 with relay




062.60



062.60 with relay

Flange mounting adaptor for types 62.3x and 62.8x.xxxx.xxx9	062.60



062.60 with relay




062.05



062.05 with relay

Top flange mount for types 62.3x and 62.8x.xxxx.xxx9	062.05



062.05 with relay




062.07



062.07 with relay

Top 35 mm rail (EN 60715) mount for types 62.3x and 62.8x.xxxx.xxx9	062.07



062.07 with relay




062.08




062.08 with relay

Rear 35 mm rail (EN 60715) mount for types 62.3x and 62.8x.xxxx.xxx9	062.08



062.08 with relay




060.48

Sheet of marker tags (CEMBRE Thermal transfer printers) for 62 series relays, plastic, 48 tags, 6 x 12 mm	060.48

VII-2026, www.findernet.com


Downloaded from Arrow.com.





92.03
Approvals
(according to type):

Box clamp socket panel or 35 mm rail (EN 60715) mount		**92.03** **Blue**	**92.03.0** **Black**
For relay type		62.31, 62.32, 62.33	
Accessories			
Metal retaining clip (supplied with socket - packaging code SMA)		092.71	
Identification tag		092.00.2	
Modules (see table below)		99.02	
Timer modules (see table below)		86.00, 86.30	
Technical data			
Rated values		16 A - 250 V	
Dielectric strength		6 kV (1.2/50 µs) between coil and contacts	
Protection category		IP 20	
Ambient temperature	°C	–40…+70 (see diagram L92)	
Screw torque	Nm	0.8	
Wire strip length	mm	10	
Max. wire size for 92.03 socket		solid wire	stranded wire
	mm²	1 x 10 / 2 x 4	1 x 6 / 2 x 4
	AWG	1 x 8 / 2 x 12	1 x 10 / 2 x 12

L 92 - Rated current v ambient temperature









86.00



86.30

86 series timer modules	
Multi-voltage: (12…240)V AC/DC; Multi-functions: AI, DI, SW, BE, CE, DE, EE, FE; (0.05 s…100 h)	86.00.0.240.0000
(12…24)V AC/DC; Bi-function: AI, DI; (0.05 s…100 h)	86.30.0.024.0000
(110…125)V AC; Bi-function: AI, DI; (0.05 s…100 h)	86.30.8.120.0000
(230…240)V AC; Bi-function: AI, DI; (0.05 s…100 h)	86.30.8.240.0000

Approvals
(according to type):



99.02
Approvals
(according to type):

DC Modules with non-standard polarity (+A2) on request.

99.02 coil indication and EMC suppression modules for 92.03 socket		
Diode (+A1, standard polarity)	(6…220)V DC	99.02.3.000.00
LED	(6…24)V DC/AC	99.02.0.024.59
LED	(28…60)V DC/AC	99.02.0.060.59
LED	(110…240)V DC/AC	99.02.0.230.59
LED + Diode (+A1, standard polarity)	(6…24)V DC	99.02.9.024.99
LED + Diode (+A1, standard polarity)	(28…60)V DC	99.02.9.060.99
LED + Diode (+A1, standard polarity)	(110…220)V DC	99.02.9.220.99
LED + Varistor	(6…24)V DC/AC	99.02.0.024.98
LED + Varistor	(28…60)V DC/AC	99.02.0.060.98
LED + Varistor	(110…240)V DC/AC	99.02.0.230.98
RC circuit	(6…24)V DC/AC	99.02.0.024.09
RC circuit	(28…60)V DC/AC	99.02.0.060.09
RC circuit	(110…240)V DC/AC	99.02.0.230.09
Residual current by-pass*	(110…240)V AC	99.02.8.230.07


* Additional 0.9 W power dissipation

Downloaded from Arrow.com.



92.13
Approvals
(according to type):

PCB socket	92.13 Blue	92.13.0 Black
For relay type	62.31, 62.32, 62.33	
Accessories		
Metal retaining clip (supplied with socket - packaging code SMA)	092.54	
Technical data		
Rated values	10 A - 250 V	
Dielectric strength	2.5 kV AC	
Ambient temperature °C	–40…+70	




62.3x plug on 92.13 is 63.3 mm high



92.33
Approvals
(according to type):


Panel mount solder socket mounted with M3 screw	92.33 Blue
For relay type	62.31, 62.32, 62.33
Accessories	
Metal retaining clip (supplied with socket - packaging code SMA)	092.54
Technical data	
Rated values	10 A - 250 V
Dielectric strength	2.5 kV AC
Ambient temperature °C	–40…+70



Packaging codes

How to code and identify retaining clip and packaging options for sockets.

Example:



Please see general technical information

VII-2026, www.findernet.com

Downloaded from Arrow.com.