





600 V, 10 A very fast IGBT



Features

- Low on voltage drop ($V_{CE(sat)}$)
- Low C_{res} / C_{ies} ratio (no cross-conduction susceptibility)
- Very soft ultra-fast recovery antiparallel diode

Applications

- High frequency motor controls
- SMPS and PFC in both hard switch and resonant topologies
- Motor drives

Description

These devices are very fast IGBTs developed using advanced PowerMESH technology. This process guarantees an excellent trade-off between switching performance and low on-state behavior.

Product status links

[STGB10NC60HDT4](#)

[STGP10NC60HD](#)

Product summary

Order code	STGB10NC60HDT4
Marking	GB10NC60HD
Package	D²PAK
Packing	Tape and reel
Order code	STGP10NC60HD
Marking	GP10NC60HD
Package	TO-220
Packing	Tube

1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{CES}	Collector-emitter voltage ($V_{GE} = 0\text{ V}$)	600	V
$I_C^{(1)}$	Continuous collector current at $T_C = 25\text{ °C}$	20	A
	Continuous collector current at $T_C = 100\text{ °C}$	10	
$I_{CL}^{(2)}$	Turn-off latching current	30	A
$I_{CP}^{(3)}$	Pulsed collector current	30	A
V_{GE}	Gate-emitter voltage	±20	V
I_F	Diode RMS forward current at $T_C = 25\text{ °C}$	10	A
I_{FSM}	Surge non repetitive forward current $t_p = 10\text{ ms}$ sinusoidal	20	A
P_{TOT}	Total power dissipation at $T_C = 25\text{ °C}$	65	W
T_{stg}	Storage temperature range	-55 to 150	°C
T_J	Operating junction temperature range		°C

1. Calculated according to the iterative formula: $I_C(T_C) = \frac{T_{J(max)} - T_C}{R_{thJC} \times V_{CE(sat)(max)}(T_{J(max)}, I_C(T_C))}$
2. $V_{clamp} = 80\% V_{CES}$, $T_J = 150\text{ °C}$, $R_G = 10\text{ }\Omega$, $V_{GE} = 15\text{ V}$.
3. Pulse width limited by maximum junction temperature.

Table 2. Thermal data

Symbol	Parameter	Value	Unit
R_{thJC}	Thermal resistance, junction-to-case IGBT	1.9	°C/W
	Thermal resistance, junction-to-case diode	4	
R_{thJA}	Thermal resistance, junction-to-ambient	62.5	°C/W

2 Electrical characteristics

$T_C = 25\text{ °C}$ unless otherwise specified

Table 3. Static

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{(BR)CES}$	Collector-emitter breakdown voltage	$V_{GE} = 0\text{ V}$, $I_C = 1\text{ mA}$	600			V
$V_{CE(sat)}$	Collector-emitter saturation voltage	$V_{GE} = 15\text{ V}$, $I_C = 5\text{ A}$		1.9	2.5	V
		$V_{GE} = 15\text{ V}$, $I_C = 5\text{ A}$, $T_J = 150\text{ °C}$		1.7		
$V_{GE(th)}$	Gate threshold voltage	$V_{CE} = V_{GE}$, $I_C = 250\text{ }\mu\text{A}$	4.5		6.5	V
I_{CES}	Collector cut-off current	$V_{GE} = 0\text{ V}$, $V_{CE} = 600\text{ V}$			0.15	mA
		$V_{GE} = 0\text{ V}$, $V_{CE} = 600\text{ V}$, $T_J = 125\text{ °C}$ ⁽¹⁾			1	
I_{GES}	Gate-emitter leakage current	$V_{CE} = 0\text{ V}$, $V_{GE} = \pm 20\text{ V}$			± 100	nA
g_{fs} ⁽²⁾	Forward transconductance	$V_{CE} = 15\text{ V}$, $I_C = 5\text{ A}$		3.5		S

1. Specified by design, not tested in production.

2. Pulsed: pulse duration = 300 μs , duty cycle 1.5%.

Table 4. Dynamic

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
C_{ies}	Input capacitance	$V_{CE} = 25\text{ V}$, $f = 1\text{ MHz}$, $V_{GE} = 0\text{ V}$	-	365	-	pF
C_{oes}	Output capacitance		-	43	-	pF
C_{res}	Reverse transfer capacitance		-	8.3	-	pF
Q_g	Total gate charge	$V_{CC} = 390\text{ V}$, $I_C = 5\text{ A}$, $V_{GE} = 0\text{ to }15\text{ V}$ (see Figure 18. Gate charge test circuit)	-	19.2	-	nC
Q_{ge}	Gate-emitter charge		-	4.5	-	nC
Q_{gc}	Gate-collector charge		-	7	-	nC

Table 5. Switching on/off (inductive load)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$t_{d(on)}$	Turn-on delay time	$V_{CC} = 390\text{ V}$, $I_C = 5\text{ A}$, $R_G = 10\ \Omega$, $V_{GE} = 15\text{ V}$ (see Figure 16. Test circuit for inductive load switching and Figure 19. Switching waveform)	-	14.2	-	ns
t_r	Current rise time		-	5	-	ns
$(di/dt)_{on}$	Turn-on current slope		-	1000	-	A/ μ s
$t_{d(on)}$	Turn-on delay time	$V_{CC} = 390\text{ V}$, $I_C = 5\text{ A}$, $R_G = 10\ \Omega$, $V_{GE} = 15\text{ V}$, $T_J = 125\text{ }^\circ\text{C}$ (see Figure 16. Test circuit for inductive load switching and Figure 19. Switching waveform)	-	14	-	ns
t_r	Current rise time		-	5	-	ns
$(di/dt)_{on}$	Turn-on current slope		-	920	-	A/ μ s
$t_r(V_{off})$	Off voltage rise time	$V_{CC} = 390\text{ V}$, $I_C = 5\text{ A}$, $R_G = 10\ \Omega$, $V_{GE} = 15\text{ V}$ (see Figure 16. Test circuit for inductive load switching and Figure 19. Switching waveform)	-	27	-	ns
$t_{d(off)}$	Turn-off delay time		-	72	-	ns
t_f	Current fall time		-	85	-	ns
$t_r(V_{off})$	Off voltage rise time	$V_{CC} = 390\text{ V}$, $I_C = 5\text{ A}$, $R_G = 10\ \Omega$, $V_{GE} = 15\text{ V}$, $T_J = 125\text{ }^\circ\text{C}$ (see Figure 16. Test circuit for inductive load switching and Figure 19. Switching waveform)	-	50	-	ns
$t_{d(off)}$	Turn-off delay time		-	108	-	ns
t_f	Current fall time		-	139	-	ns

Table 6. Switching energy (inductive load)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$E_{on}^{(1)}$	Turn-on switching energy	$V_{CE} = 390\text{ V}$, $I_C = 5\text{ A}$, $R_G = 10\ \Omega$, $V_{GE} = 15\text{ V}$ (see Figure 16. Test circuit for inductive load switching)	-	31.8	-	μ J
$E_{off}^{(2)}$	Turn-off switching energy		-	95	-	μ J
E_{ts}	Total switching energy		-	126.8	-	μ J
$E_{on}^{(1)}$	Turn-on switching energy	$V_{CE} = 390\text{ V}$, $I_C = 5\text{ A}$, $R_G = 10\ \Omega$, $V_{GE} = 15\text{ V}$, $T_J = 125\text{ }^\circ\text{C}$ (see Figure 16. Test circuit for inductive load switching)	-	61.8	-	μ J
$E_{off}^{(2)}$	Turn-off switching energy		-	173	-	μ J
E_{ts}	Total switching energy		-	234.8	-	μ J

1. Including the reverse recovery of the diode.

2. Including the tail of the collector current.

Table 7. Diode switching characteristics (inductive load)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
V_F	Forward on-voltage	$I_F = 5\text{ A}$	-	2	2.45	V
		$I_F = 5\text{ A}$, $T_J = 125\text{ }^\circ\text{C}$	-	1.7		
t_{rr}	Reverse recovery time	$I_F = 5\text{ A}$, $V_R = 40\text{ V}$, $di/dt = 100\text{ A}/\mu\text{s}$ (see Figure 17. Diode reverse recovery waveform)	-	22		ns
Q_{rr}	Reverse recovery charge		-	14		nC
I_{rrm}	Reverse recovery current		-	1.3		A
t_{rr}	Reverse recovery time	$I_F = 5\text{ A}$, $V_R = 40\text{ V}$, $di/dt = 100\text{ A}/\mu\text{s}$, $T_J = 125\text{ }^\circ\text{C}$ (see Figure 17. Diode reverse recovery waveform)	-	33		ns
Q_{rr}	Reverse recovery charge		-	30		nC
I_{rr}	Reverse recovery current		-	1.85		A

2.1 Electrical characteristics (curves)

Figure 1. Typical output characteristics




Figure 2. Typical transfer characteristics




Figure 3. Typical transconductance characteristics




Figure 4. Typical collector-emitter on voltage vs temperature




Figure 5. Typical gate charge characteristics




Figure 6. Typical capacitance characteristics




Figure 7. Normalized gate threshold vs temperature




Figure 8. Typical collector-emitter on voltage vs collector current




Figure 9. Normalized breakdown voltage vs temperature




Figure 10. Typical switching energy vs temperature




Figure 11. Typical switching energy vs gate resistance




Figure 12. Typical switching energy vs collector current




Figure 13. Normalized transient thermal impedance




Figure 14. Safe operating area









Figure 15. Emitter-collector diode characteristics



3 Test circuits


Figure 16. Test circuit for inductive load switching

Figure 17. Diode reverse recovery waveform

Figure 18. Gate charge test circuit

Figure 19. Switching waveform


4 Package information

To meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: www.st.com. ECOPACK is an ST trademark.

4.1 D²PAK (TO-263) type B package information


Figure 20. D²PAK (TO-263) type B package outline



0079457_26_B

Table 8. D²PAK (TO-263) type B mechanical data


Dim.	mm		
	Min.	Typ.	Max.
A	4.36		4.56
A1	0		0.25
b	0.70		0.90
b1	0.51		0.89
b2	1.17		1.37
c	0.38		0.694
c1	0.38		0.534
c2	1.19		1.34
D	8.60		9.00
D1	6.90		7.50
E	10.15		10.55
E1	8.10		8.70
e	2.54 BSC		
H	15.00		15.60
L	1.90		2.50
L1			1.65
L2			1.78
L3		0.25	
L4	4.78		5.28

Figure 21. D²PAK (TO-263) recommended footprint (dimensions are in mm)


0079457_Rev27_footprint

4.2 TO-220 type A package information

Figure 22. TO-220 type A package outline




0015988_typeA_Rev_24

Table 9. TO-220 type A package mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	4.40		4.60
b	0.61		0.88
b1	1.14		1.55
c	0.48		0.70
D	15.25		15.75
D1		1.27	
E	10.00		10.40
e	2.40		2.70
e1	4.95		5.15
F	1.23		1.32
H1	6.20		6.60
J1	2.40		2.72
L	13.00		14.00
L1	3.50		3.93
L20		16.40	
L30		28.90	
øP	3.75		3.85
Q	2.65		2.95
Slug flatness		0.03	0.10

4.3 D²PAK packing information

Figure 23. D²PAK tape drawing (dimensions are in mm)



DM01095771_1



Revision history

Table 10. Document revision history

Date	Revision	Changes
30-Jan-2006	1	Initial release
06-Nov-2006	2	Complete version.
08-Feb-2007	3	The document has been reformatted
05-Oct-2007	4	Added TO-220FP, <i>Table 2</i> has been updated
16-Dec-2008	5	Added DPAK package
05-May-2025	6	The part numbers STGD10NC60HD and STGF10NC60HD have been removed and the document has been updated accordingly. Updated Section 4: Package information .



Contents

1	Electrical ratings	2
2	Electrical characteristics.....	3
2.1	Electrical characteristics (curves).....	5
3	Test circuits	8
4	Package information.....	9
4.1	D ² PAK (TO-263) type B package information	9
4.2	TO-220 type A package information	11
4.3	D ² PAK packing information	13
	Revision history	14



IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2025 STMicroelectronics – All rights reserved