

new

VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable



Ruggedized reverse bayonet connectors

Completely intermountable with VG 95234 : the MS 5015 reverse bayonet connectors

Description

This connector series is an enhanced version of the VG 95234 connector standard but remains completely intermountable with VG 95234 : the MS 5015 reverse bayonet connectors.



Features and benefits (see also page 3)

- The insulator is in hard thermoplastic, classified UL94VO. It is also classified I2F3 following NFF 16101-16102 standards.
- An interfacial seal is present on the male inserts to extend the creepage distance and to have a better sealing when the connector is mated.
- The insulator is retained into the plug or receptacle shell by a metallic retaining ring which can be removed with a small screwdriver. Once removed, user can defined insulator orientation.
- Contacts gauge 8, 12 or 16 are machined crimp contacts, removable thanks to a clip on the contact.
- No tools are needed to insert contacts into the insulator. An extraction tool is available to extract the contacts. The tool is engaged by the front face of the connector and the contacts are rear released.
- Contacts are crimped thanks to very common toolings.
- The connector is rated 2 levels of water protection (see page 3):
Dynamic IP67/IP68/IP69K when mated and used with suitable accessories, a grommet or a sealed back shell.
- This connector can be supplied fully assembled or in component form (please consult us).
- Corrosion spray resistance is rated up to 500 hours salt spray
- VGE1 connectors RoHS compliant. Cadmium and lead free materials are used

New VGE1 ruggedized series



New VGE1 series:


- The ruggedized product range in the TRIM TRIO broadband.
- Using size 16 signal and size 12 & 8 power contacts for up to 30 Amps per contact.

VGE1 series major technical features & benefits

• Ruggedized full metal reverse bayonet connector

- Enabling 500 mating-unmating without wear out
- Secure locking device
 - Audible “click” when mating
 - Visible yellow dot to indicate end of mating cycle


Robustness and high reliability
of the locking mechanism



• Dynamic IP68*

Connector will remain IP68 even when:


- Pulling on the cable
- Bending the cable



- * With appropriate back shell and grommet
- * Exists also in IP67 version

• Dynamic IP69K*

Connector withstands high pressure water cleaning.



- * With appropriate back shell and grommet

• Up to 500 hours salt spray resistance

- Can be used in very severe environment

• RoHS compliant

- Cadmium and lead free materials are used

• In accordance with following standards

- Completely intermountable with VG95234: the MS5015 reverse bayonet connectors
- In conformity with the French railway standard NFF 61030

For detailed information on VGE1 series offering see pages 122 to 139

new


VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable




Description

Receptacle



Plug



new

VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable



Technical Features (see also page 3)

Mechanical

- Mechanical endurance : 500 mating and unmating
- Minimum retention force of the contact in the insulator :
 - 70 N for contacts # 16 (1.6 mm)
 - 90 N for contacts # 12 (2.4 mm)
 - 110 N for contacts # 8 (3.6 mm)

Minimum values with a maximum displacement of the contact of 0.3 mm (following NFF 61030)

- Retention of the insulator in the shell : (following MIL-C-26482G Series 2 class L standard)
- Bayonet coupling mechanism - Coupling torque : following VG 95234
- Vibrations : following NFF 61030
Sinus vibrations : 10 - 100 Hz
Acceleration : 2 g
- Shocks : Acceleration = 30 g
Duration = 18 ms following NFF 61030
- Impact strength (free fall of the plug).
The connector plug is subjected to a free fall test. The height of drop is 0.75 m. No mechanical damage.

Electrical

- Contact resistance :
 - 2.5 mΩ maxi for contact # 16
 - 1.3 mΩ maxi for contact # 12
 - 0.9 Z Q maxi for contact # 8 following NFF 61030

Maximum current per contact :

- 15 Amps for contact # 16
- 20 Amps for contact # 12
- 30 Amps for contact # 8

- Withstanding voltage :
 - 2550 Vrms for layouts # 16
 - 3250 Vrms for layouts # 12 and 8

- Insulation resistance :
 - ≥ 5000 MΩ under 500 Vcc
 - ≥ 4000 MΩ under 220 Vcc

- Electrical continuity of the shells : 20 mΩ maximum

- In mated conditions (interfacial seal is compression)
minimum creepage distance = minimum insulation distance in the air :
 - 9 mm minimum for layouts with contacts # 16
 - 12 mm minimum for layouts with contacts # 12 or # 8

Environmental


- Climatic category : -40°C +100°C
Dry heat test : +100°C during 96 h
- Corrosion spray resistance : up to 500 hours salt spray
- Damp heat : 21 days, 40°C, 95% relative humidity
- The connector is rated 2 levels of water protection (see page 3):
Dynamic IP67/IP68/IP69K when mated and used with suitable accessories, a grommet or a sealed back shell.
- Material rated I2F3 following NFF 16101-16102 and UL 94 VO
- Fluid resistance : gas oil, mineral oil, acid bath, basic bath, following NFF 61030
- RoHS compliant. Cadmium and lead free materials are used

Material

- Shell in aluminium alloy with black zinc cobalt plating
- Insulator : hard thermoplastic with glass fiber
- O'ring and interfacial seal in silicone
- Retaining insulator ring in carbon steel

This full product range is qualified by ALSTOM, RATP and SNCF.

Robustness and high reliability of the locking mechanism



new

VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable



Connectors Ordering Information (without contacts and accessories)

Shells, backshells, contacts and accessories have to be ordered separately

VGE1	B	22	– 14	P	N	--
Series						
Shell type						
Rear mounting receptacle	B					
Plug	D					
Rear mounting receptacle for PC tails contact # 16	C					
Shell size : 18 - 20 -22 - 24 - 28 - 32 - 36 - 40						
Layouts						
Contact type : P - Pin S - Socket						
Insert Orientation : N ; W ; X ; Y ; Z or 0 0 = for insulator not installed in the shell						
Modification Code : <i>Please consult us</i>						

For information : connector marking

Example 1 : **VGE1 B 22 - 14 P** Example 2 : **VGE1 D 28 - 21 S**

Nota : Please consult us if you want to order the connector in component form (shell and insert).

new


VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable




Connector Dimensions

Receptacle



Shell size	A Max	B 0/+0.4	C ±0.2	ØD Max	E ±0.3	ØF 0/+0.15	Threading G Class 2A	H ±0.1	ØK -0.15/0
18	45.50	23.05	4.00	25.50	35.00	3.25	1"x20 UNEF	27.00	30.80
20	45.50	23.05	4.00	28.70	38.00	3.25	1 1/8"x18 UNEF	29.40	34.20
22	45.50	23.05	4.00	31.90	41.00	3.25	1 1/4"x18 UNEF	31.80	37.40
24	48.00	23.05	4.00	35.20	44.50	3.75	1 3/8"x18 UNEF	34.90	40.90
28	48.00	24.05	4.00	41.50	50.80	3.75	1 5/8"x18 UNE	39.70	46.70
32	48.00	24.05	4.00	47.90	57.00	4.35	1 7/8"x16 UN	44.50	53.40
36	48.00	24.05	4.00	52.50	63.50	4.35	2 1/16"x16 UNS	49.20	59.60
40	48.00	24.05	4.00	59.00	70.00	4.35	2 5/16"x16 UN	55.50	65.50

Receptacle with PC tails contact # 16




new

VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable



Panel Cutout



Shell size	A ± 0.15	B 0/+0.3	C ± 0.10	Maximum thickness of the panel for rear mounting
18	27	31,2	3,4	3
20	29,4	34,6	3,4	3
22	31,8	37,8	3,4	3
24	34,9	41,3	3,9	3
28	39,7	47,1	3,9	3
32	44,5	53,8	4,5	3
36	49,2	60	4,5	3
40	55,5	66,4	4,5	3

Note : The above panel cut-out enables front mounting of all receptacles.


new

VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable



Plug



Shell size	A Max	B Max	C Max	Threading G Class 2A
18	45.60	37.30	25.50	1" x 20 UNEF
20	45.60	41.50	28.70	1 1/8" x 18 UNEF
22	45.60	44.00	31.90	1 1/4" x 18 UNEF
24	45.60	48.50	35.20	1 3/8" x 18 UNEF
28	48.10	55.30	41.50	1 5/8" x 18 UNEF
32	48.10	62.00	47.90	1 7/8" x 16 UN
36	48.10	66.80	52.50	2 1/6" x 16 UNS
40	48.10	74.50	59.00	2 5/16" x 16 UN






new




VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable





Layouts (marking on front face of female insulator)

18-19	20-15	22-14	24-10	28-21
				
10 contacts # 16	7 contacts # 12	19 contacts # 16	7 contacts # 8	37 contacts # 16

32 A13	36 A22	40 A35	40 A60
			
13 contacts # 12	22 contacts # 12	35 contacts # 12	60 contacts # 16

Note : We will develop other layouts following market demand.

Alternative insert orientation positions

Layouts	Angular displacement of insert					Insulator weight (g)	
	N	W	X	Y	Z	Male	Female
18-19	0	-	120	240	-	10	16
20-15	0	80	-	-	280	13	21
22-14	0	80	-	-	280	16	25
24-10	0	80	110	250	280	19	31
28-21	0	80	110	250	280	27	40
32-A13	0	65	130	230	295	45	75
36-A22	0	80	110	250	280	53	88
40-A35	0	70	130	230	290	61	99
40-A60	0	80	110	250	280	63	100

new

VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable




Contacts

Contacts come from our well known TRIM-TRIO Series.

They are precision solid machined crimp snap-in pins and sockets for heavy duty top performance requirements.

Springs on both contacts are made of spring-tempered, heat treated, beryllium copper.

The socket inner spring supplies high contact pressure to ensure low-resistance contact between pin and socket. The socket contact features closed entry to prevent probe damage. Crimp barrels have insulation grips for vibration support and are provided with a cable stop and inspection hole.



Construction

- Contact body :
High conductive copper alloy
- Outer spring :
Tempered, heat treated, beryllium copper
- Inner spring socket :
Tempered, heat treated, plated beryllium copper

Plating table

Au = Gold plated : minimum of 0.4 μ of Gold all over, over nickel coating
Ag = Silver plated 5 μ of silver all over

Performance characteristics

	Contacts # 16	Contacts # 12	Contacts # 8
Maximum current rating	13 A	26 A	44 A
Contact resistance	$\leq 3 \text{ m}\Omega$	$\leq 5 \text{ m}\Omega$	$\leq 5 \text{ m}\Omega$

new



VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable





Contacts Dimensions



Contacts # 16 (1.6 mm)



Contacts # 12 (2.4 mm)



Contacts # 8 (3.6 mm)



Length L = see table page 12

new

VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable



Contacts Part Numbers

Contact size	Contact type	Contact diameter	Contact Part number	Cable			Protection	Contact dimensions (mm)
				Section of the conductor		Wire insulator diameter (maxi)*		
		mm		mm ²	AWG	mm		L
#16	Male	1.6	RM16M23K	0.52 – 1.50	20-16	3	Au	26.2
#16	Female	1.6	RC16M23K	0.52 – 1.50	20-16	3	Au	18.2
#16	Male	1.6	RM14M30K	2.50	14	3	Au	26.2
#16	Female	1.6	RC14M30K	2.50	14	3	Au	18.2
#12	Male	2.4	8291 1437 NA	0.50	20	4,9	Ag	26.8
#12	Female	2.4	8291 1436 A	0.50	20	4,9	Ag	24.3
#12	Male	2.4	8291 1435 NA	0.75 – 1.00	18	4,9	Ag	26.8
#12	Female	2.4	8291 1434 A	0.75 – 1.00	18	4,9	Ag	24.3
#12	Male	2.4	8291 1463 NA	1.50	16	4,9	Ag	24.8
#12	Female	2.4	8291 1462 A	1.50	16	4,9	Ag	22.3
#12	Male	2.4	8291 1465 NA	2.50	14	4,9	Ag	24.8
#12	Female	2.4	8291 1464 A	2.50	14	4,9	Ag	22.3
#12	Male	2.4	8291 1437 NK	0.50	20	4,9	Au	26.8
#12	Female	2.4	8291 1436 K	0.50	20	4,9	Au	24.3
#12	Male	2.4	8291 1435 NK	0.75 – 1.00	18	4,9	Au	26.8
#12	Female	2.4	8291 1434 K	0.75 – 1.00	18	4,9	Au	24.3
#12	Male	2.4	8291 1463 NK	1.50	16	4,9	Au	24.8
#12	Female	2.4	8291 1462 K	1.50	16	4,9	Au	22.3
#12	Male	2.4	8291 1465 NK	2.50	14	4,9	Au	24.8
#12	Female	2.4	8291 1464 K	2.50	14	4,9	Au	22.3
#8	Male	3.6	8291 3601 A	1.50	16	6.5	Ag	25.5
#8	Female	3.6	8291 3600 A	1.50	16	6.5	Ag	25,5
#8	Male	3.6	8291 3603 A	2.50	14	6.5	Ag	25.5
#8	Female	3.6	8291 3602 A	2.50	14	6.5	Ag	25,5
#8	Male	3.6	8291 3605 A	4.00	12	6.5	Ag	25.5
#8	Female	3.6	8291 3604 A	4.00	12	6.5	Ag	25,5
#8	Male	3.6	8291 3607 A	6.00	10	6.5	Ag	25.5
#8	Female	3.6	8291 3606 A	6.00	10	6.5	Ag	25,5

Note : Dimensions are not contractual and may be subject to modifications.

NB : Other RM/RC contact size 16 are also compatible with VGE1 connector.

* Allowable by the insert

Please consult us

new

VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable



Accessories

Backshells ordering information

Series	VGE1 VGE1	J C	S S	18 22	– 00 – 14	00 00	M
Backnut		R					
Cable clamp		C					
Backshell for PMA tube		S					
Cable clamp with sealing gland		J					
Cable clamp with sealing gland (trumpet)		K					
Cable clamp with sealing gland for shielding		T					
S - Straight backshell E - Elbow backshell							
Shell size : 18 - 20 - 22 - 24 - 28 - 32 - 36 - 40							
Layout (if grommet needed) or 00 (without grommet)							
Adaptor type : 10 - long 00 - short							
Grommet type : M for male or L for female (if grommet needed)							

P/N example : Short backshell with male grommet for shell size 40 connector

VGE1 J S 40 A 35 00 M

VGE1 J S 40 A 60 00 M

P/N example : Long backshell without grommet for shell size 40 connector

VGE1 J S 40-00 10

VGE1 J S 40-00 10

Adaptor ordering information

Series	VGE1	P	S	18	– 00	00
P - Adaptor with PG outlet						
S - Adaptor for straight backshell						
Shell size : 18 - 20 - 22 - 24 - 28 - 32 - 36 - 40						
Adaptor type : 10 - long 00 - short						

new

VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable



Accessories

Grommet

Grommet are delivered with a conical ring

Layout	Grommet type	Part number	Wire insulator diameter (mm)	
			Mini	Maxi *
18-19	male	VGE1M18-1900	1,2	2,95
18-19	female	VGE1L18-1900	1,2	2,95
20-15	male	VGE1M20-1500	1,2	3,6
20-15	female	VGE1L20-1500	1,2	3,6
22-14	male	VGE1M22-1400	1,2	2,95
22-14	female	VGE1L22-1400	1,2	2,95
24-10	male	VGE1M24-1000	4,2	6,2
24-10	female	VGE1L24-1000	4,2	6,2
28-21	male	VGE1M28-2100	1,2	2,95
28-21	female	VGE1L28-2100	1,2	2,95
32A13	male	VGE1M32A1300	1,2	3,6
32A13	female	VGE1L32A1300	1,2	3,6
36A22	male	VGE1M36A2200	1,2	3,6
36A22	female	VGE1L36A2200	1,2	3,6
40A35	male	VGE1M40A3500	1,2	3,6
40A35	female	VGE1L40A3500	1,2	3,6
40A60	male	VGE1M40A6000	1,2	2,95
40A60	female	VGE1L40A6000	1,2	2,95

* Please consult us if your wire has an insulation diameter over these values, we will propose you another grommet.




Grommet filler plug

Contact size	Part number	Color	Photo
# 16 # 12	8500-479	blue	

Panel gasket

Shell size	Part number	Dimensions			
		A ± 0.5	B ± 0.2	C 0/+0.3	Ø D 0/+0.3
20	VGE1G20	38	29.4	34.2	4.2
22	VGE1G22	41	31.8	37.4	4.2
24	VGE1G24	44.5	34.9	40.9	4.2
28	VGE1G28	50.8	39.7	46.7	5.1
32	VGE1G32	57	44.5	53.4	5.1
36	VGE1G36	63.5	49.2	59.6	5.1
40	VGE1G40	69.9	55.5	65.5	5.1



new










VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable





Synoptic of straight backshells (for IP67 applications)



Ref	Description	 +									
		 +									
VGE1 RS****00	Backnut	 +									
VGE1 CS****00	Cable clamp	 +									
VGE1 SS****10	Backshell for PMA tube	 +									
VGE1 SS****00	Backshell for PMA tube	 +									
VGE1 JS****10	Cable clamp with sealing gland	 +									
VGE1 JS****00	Cable clamp with sealing gland	 +									
VGE1 KS****10	Cable clamp with sealing gland (trumpet shape to avoid cable wound)	 +									
VGE1 KS****00	Cable clamp with sealing gland (trumpet shape to avoid cable wound)	 +									
VGE1 TS****10	Cable clamp with sealing gland for shielding	 +									
VGE1 TS****00	Cable clamp with sealing gland for shielding										

Synoptic of adaptors

Ref	Description		
		Long adaptor with PG outlet	Short adaptor with PG outlet
VGE1 PS**0010			VGE1 PS**0000

NB: IP68 backshells are available under request

new

VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable



Dimensions

	Shell 18		Shell 20		Shell 22		Shell 24		Shell 28		Shell 32		Shell 36		Shell 40	
	with grommet	without grommet	with grommet	without grommet	with grommet	without grommet	with grommet	without grommet	with grommet	without grommet	with grommet	without grommet	with grommet	without grommet	with grommet	without grommet
	**** = 18-19	**** = 18-00	**** = 20-15	**** = 20-00	**** = 22-14	**** = 22-00	**** = 24-10	**** = 24-00	**** = 28-21	**** = 28-00	**** = 32A13	**** = 32A00	**** = 36A22	**** = 36A00	**** = 40A35 40A60	**** = 40A00
A	22.5		22.5		22.5		22.5		24		24		24		24	
B	45.6		45.6		45.6		45.6		48.1		48.1		48.1		48.1	
C	18		18		18		18		17		17		17		17	
D	44		44		44		44		47							
E	28,5		28,5		26		26		23							
F	48,6		48,6		48,6		48,6		58		48		48		48	
G	34		34		34		34		33		33		33		33	
H	35,5		35,5		38,5		38,5		38,5		38,5		52		46	
K	PMA 17		PMA 17		PMA23		PMA23		PMA29		PMA29		PMA36		PMA48	
M	23		23		31		31		31.5		31.5		37.5		45	
N	7/12		9/14		10/18		10/18		14/24		14/24		22/30		25/35	
P	30		31,5		38,5		38,5		45		45		51.5		57	
S	33,5		33,5		43		43		52		52					
T	8/12,5		10/14,5		13,5/18		13,5/18		17/24		17/24					
U	4/15,5		7/15,5		9/15,5		8,5/19,5		9,5/19,5							
	PG 13,5		PG 16		PG 21		PG 21		PG 29		PG 29		PG 36		PG 42	

Note : Dimensions are not contractual and may be subject to modifications.

⇒ All backshells are compatible with a grommet and a conical ring.

⇒ For cable or PMA tube diameter not included in the above chart please consult us.

**Example of rear dimensions calculation
of a shell size 18 connector with a sealing gland
cable clamp backshell without grommet and with a long adaptor**

Backshell P/N : VGE1 JS 18 00 10

Rear dimensions receptacle + backshell :

$A + F + M = 94,1 \text{ mm}$






new




VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable



Synoptic of elbow backshells (IP67 applications)

 Receptacle Plug				
	+ + + +			
				
Description	Backshell for PMA tube	Cable clamp with sealing gland	Cable clamp with sealing gland (trumpet shape to avoid cable wound)	Cable clamp with sealing gland for shielding
Part number	VGE1 SE****00	VGE1 JE****00	VGE1 KE****00	VGE1 TE****00

 Receptacle Plug				
	+			
				
Description	Cable clamp			
Part number	VGE1 CE****00			

NB: IP68 backshells are available under request

new

VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable



Dimensions

	Shell 18		Shell 20		Shell 22		Shell 24		Shell 28		Shell 32		Shell 36		Shell 40	
	with grommet	without grommet	with grommet	without grommet	with grommet	without grommet	with grommet	without grommet	with grommet	without grommet	with grommet	without grommet	with grommet	without grommet	with grommet	without grommet
	**** = 18-19	**** = 18-00	**** = 20-15	**** = 20-00	**** = 22-14	**** = 22-00	**** = 24-10	**** = 24-00	**** = 28-21	**** = 28-00	**** = 32A13	**** = 32A00	**** = 36A22	**** = 36A00	**** = 40A35 40A60	**** = 40A40
A	22,5		22,5		22,5		22,5		24		24		24		24	
B	45,6		45,6		45,6		45,6		48,1		48,1		48,1		48,1	
C	44		43,5		43,5		46		41							
D	26		25,5		17,5		20		18							
E	28,5		28,5		26		26		23							
F	43		44		44		49		46		59		60			
H	35,5		35,5		38,5		38,5		38,5		38,5		46			
K	PMA 17		PMA 17		PMA 23		PMA 23		PMA 29		PMA 36		PMA 36			
M	23		23		31		31		31,5		31,5		37,5			
N	7/12		9/14		10/18		10/18		14/24		14/24		22/30			
P	30		31,5		38,5		38,5		45		45		51,5			
S	33,5		33,5		43		43		52		52					
T	8/12,5		10/14,5		13,5/18		13,5/18		17/24		17/24					
U	4/15,5		7/15,5		9/15,5		8,5/19,5		9,5/19,5							
	PG 13,5		PG 16		PG 21		PG 21		PG 29		PG 29		PG 36		PG 42	

Note : Dimensions are not contractual and may be subject to modifications.

⇒ All backshells are compatible with a grommet and a conical ring.

⇒ For cable or PMA tube diameter not included in the above chart please consult us.

new

VGE1

Dynamic IP68 / IP69K
Up to 500 hr salt spray
RoHS compliant
VG95234 intermountable



Tooling Data

Contact size	Contact type	Contact Ø mm	Contact Part number	Contact Size		Crimp tool	Locator	Extraction tool
				mm²	AWG			
# 16	Male	1.6	RM16M23K	0.52 - 1.50	20-16	MH860 (M22520/7-01)	MH86164G	RX2025GE1
# 16	Female	1.6	RC16M23K	0.52 - 1.50	20-16	MH860 (M22520/7-01)	MH86164G	RX2025GE1
# 16	Male	1.6	RM14M30K	2.50	14	AF8 (M22520/3-1)	TP1142 (selector on 8)	RX2025GE1
# 16	Female	1.6	RC14M30K	2.50	14	AF8 (M22520/3-1)	TP1142 (selector on 8)	RX2025GE1
# 12	Male	2.4	8291 1437 NA	0.50	20	M317	VGE10077A	5106.021.09.24
# 12	Female	2.4	8291 1436 A	0.50	20	M317	VGE10077A	5106.021.09.24
# 12	Male	2.4	8291 1435 NA	0.75 - 1.00	18	M317	VGE10077A	5106.021.09.24
# 12	Female	2.4	8291 1434 A	0.75 - 1.00	18	M317	VGE10077A	5106.021.09.24
# 12	Male	2.4	8291 1463 NA	1.50	16	M317	VGE10077A	5106.021.09.24
# 12	Female	2.4	8291 1462 A	1.50	16	M317	VGE10077A	5106.021.09.24
# 12	Male	2.4	8291 1465 NA	2.50	14	M317	VGE10077A	5106.021.09.24
# 12	Female	2.4	8291 1464 A	2.50	14	M317	VGE10077A	5106.021.09.24
# 12	Male	2.4	8291 1437 NK	0.50	20	M317	VGE10077A	5106.021.09.24
# 12	Female	2.4	8291 1436 K	0.50	20	M317	VGE10077A	5106.021.09.24
# 12	Male	2.4	8291 1435 NK	0.75 - 100	18	M317	VGE10077A	5106.021.09.24
# 12	Female	2.4	8291 1434 K	0.75 - 100	18	M317	VGE10077A	5106.021.09.24
# 12	Male	2.4	8291 1463 NK	1.50	16	M317	VGE10077A	5106.021.09.24
# 12	Female	2.4	8291 1462 K	1.50	16	M317	VGE10077A	5106.021.09.24
# 12	Male	2.4	8291 1465 NK	2.50	14	M317	VGE10077A	5106.021.09.24
# 12	Female	2.4	8291 1464 K	2.50	14	M317	VGE10077A	5106.021.09.24
# 8	Male	3.6	8291 3601 A	1.50	16	M317	VGE10078A	5106.021.09.36
# 8	Female	3.6	8291 3600 A	1.50	16	M317	VGE10078A	5106.021.09.36
# 8	Male	3.6	8291 3603 A	2.50	14	M317	VGE10078A	5106.021.09.36
# 8	Female	3.6	8291 3602 A	2.50	14	M317	VGE10078A	5106.021.09.36
# 8	Male	3.6	8291 3605 A	4.00	12	M317	VGE10078A	5106.021.09.36
# 8	Female	3.6	8291 3604 A	4.00	12	M317	VGE10078A	5106.021.09.36
# 8	Male	3.6	8291 3607 A	6.00	10	M317	VGE10078A	5106.021.09.36
# 8	Female	3.6	8291 3606 A	6.00	10	M317	VGE10078A	5106.021.09.36

For detailed information on crimp tooling: see crimp tooling section.