OSRAM SFH 4258B

Datasheet

Published by ams-OSRAM AG
Tobelbader Strasse 30, 8141 Premstaetten, Austria
Phone +43 3136 500-0
ams-osram.com
© All rights reserved

Downloaded from Arrow.com.

Power TOPLED™ Lens

SFH 4258B



Compact. Reliable. Efficient. Automotive-Ready.
Power TOPLED™ with lens, using IR:6 thin-film chip technology for IREDs, delivers outstanding radiant intensity in a compact 3.5 × 2.8 mm package and meets AEC-Q102 standards for automotive-grade reliability. Ideal for driver monitoring, security, and machine vision – engineered for long-term stability in demanding environments.

Applications

- Access control & security
- Authentication
- Factory automation
- Home & building automation
- In-Cabin sensing
- Medical lighting

Features

- Package: Epoxy, diffuse
- Corrosion Robustness Class: 3B
- Qualifications: AEC-Q102 Qualified
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)
- High Power Infrared LED
- High forward current allowed at high temperature
- Short switching times
- UL version available (ordering code & test conditions on request)

Downloaded from Arrow.com.

Ordering Information

Type	Radiant intensity [1)2)] I_F = 100 mA; t_p = 20 ms I_e	Radiant intensity [1)] typ. I_F = 100 mA; t_p = 20 ms I_e	Ordering Code
SFH 4258B	140 ... 280 mW/sr	202 mW/sr	Q65115A0351

Downloaded from Arrow.com.

Maximum Ratings

T_S = 25 °C

Parameter	Symbol		Values
Operating temperature	T_{op}	min. max.	-40 °C 110 °C
Storage temperature	T_{stg}	min. max.	-40 °C 110 °C
Junction temperature	T_j	max.	125 °C
Forward current	I_F	min. max.	1 mA 100 mA
Forward current pulsed $t_p \leq 30$ µs; D ≤ 0.005	$I_{F\ pulse}$	max.	1 A
Reverse voltage [3)]	V_R	max.	5 V
Power consumption	P_{tot}	max.	175 mW
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)	V_{ESD}	max.	2 kV

Downloaded from Arrow.com.

Characteristics

I_F = 100 mA; t_p = 20 ms; T_S = 25 °C

Parameter	Symbol		Values
Peak wavelength	λ_{peak}	typ.	860 nm
Centroid wavelength	$\lambda_{centroid}$	typ.	850 nm
Spectral bandwidth at 50% $I_{rel,max}$ (FWHM)	$\Delta\lambda$	typ.	30 nm
Half angle	φ	typ.	12 °
Rise time (10% / 90%) I_F = 100 mA; R_L = 50 Ω	t_r	typ.	12 ns
Fall time (10% / 90%) I_F = 100 mA; R_L = 50 Ω	t_f	typ.	12 ns
Forward voltage [4] I_F = 100 mA; t_p = 20 ms	V_F	typ. max.	1.45 V 1.75 V
Reverse current [3] V_R = 5 V	I_R	typ. max.	0.01 µA 10 µA
Radiant intensity [1] I_F = 100 mA; t_p = 20 ms	I_e	typ.	202 mW/sr
Total radiant flux [5] I_F = 100 mA; t_p = 20 ms	Φ_e	typ.	84 mW
Thermal resistance junction solder point real [6]	$R_{thJS\ real}$	typ. max.	70 K / W 120 K / W

Downloaded from Arrow.com.

Brightness Groups


Group	Radiant intensity [1)2)] I_F = 100 mA; t_p = 20 ms min. I_e	Radiant intensity [1)2)] I_F = 100 mA; t_p = 20 ms max. I_e
AB	140 mW/sr	180 mW/sr
BA	180 mW/sr	224 mW/sr
BB	224 mW/sr	280 mW/sr

Only one group in one packing unit.

Downloaded from Arrow.com.


Relative Spectral Emission 7), 8)

$I_{e,rel} = f(\lambda)$; I_F = 100 mA; t_p = 20 ms



Radiation Characteristics 7), 8)


$I_{e,rel} = f(\varphi)$



Downloaded from Arrow.com.


Forward current [7], [8]

$I_F = f(V_F)$; single pulse; $t_p = 100\ \mu s$



Relative Radiant Intensity [7], [8]


$I_e/I_e(100mA) = f(I_F)$; single pulse; $t_p = 100\ \mu s$



Downloaded from Arrow.com.


Relative Total Radiant Flux [7)]

$\Phi_{rel} = f(T_S)$; I_F = 100mA; t_p = 20ms




Forward Voltage [7)]

$V_F = f(T_S)$; I_F = 100mA; t_p = 20ms



Centroid Wavelength [7)]


$\lambda_{centroid} = f(T_S)$; I_F = 100mA; t_p = 20ms



Downloaded from Arrow.com.


Max. Permissible Forward Current

$I_F = f(T_S)$; Rth_{js} = 120 K / W




Permissible Pulse Handling Capability

$I_F = f(t_p)$; D = parameter; T_S = 85 °C




Permissible Pulse Handling Capability

$I_F = f(t_p)$; D = parameter; T_S = 110 °C



Downloaded from Arrow.com.

Dimensional Drawing [9)]



Further Information:

Approximate Weight: 37.0 mg


Package marking: Cathode

Corrosion test: Class: 3B
Test condition: 40°C / 90 % RH / 15 ppm H_2S / 14 days (stricter than IEC 60068-2-43)

Pin	Description
1	Cathode
2	Anode
3	Anode
4	Anode

Downloaded from Arrow.com.


Recommended Solder Pad 9)



Downloaded from Arrow.com.

Reflow Soldering Profile

Product complies to MSL Level 2 acc. to JEDEC J-STD-020E




Profile Feature	Symbol	Pb-Free (SnAgCu) Assembly			Unit
		Minimum	Recommendation	Maximum	
Ramp-up rate to preheat*) 25 °C to 150 °C			2	3	K/s
Time t_S T_{Smin} to T_{Smax}	t_S	60	100	120	s
Ramp-up rate to peak*) T_{Smax} to T_P			2	3	K/s
Liquidus temperature	T_L		217		°C
Time above liquidus temperature	t_L		80	100	s
Peak temperature	T_P		245	250	°C
Time within 5 °C of the specified peak temperature T_P - 5 K	t_P	10	20	30	s
Ramp-down rate* T_P to 100 °C			3	4	K/s
Time 25 °C to T_P				480	s

All temperatures refer to the center of the package, measured on the top of the component
* slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range

Downloaded from Arrow.com.


Taping [9)]



C63062-A3856-B1-02

Downloaded from Arrow.com.

Tape and Reel [10)]




Leader: min. 400mm*
Trailer: min. 160mm*
*)Dimensions acc. to IEC 60286-3; EIA 481-E

Reel Dimensions


A	W	N_{min}	W_1	$W_{2\,max}$	Pieces per PU
330 mm	12 + 0.3 / - 0.1 mm	60 mm	12.4 + 2 mm	18.4 mm	2000

Downloaded from Arrow.com.

Barcode-Product-Label (BPL)



Dry Packing Process and Materials [9)]



Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.

Downloaded from Arrow.com.

Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet falls into **exempt risk group - Exempt**.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit https://ams-osram.com/support/application-notes

Downloaded from Arrow.com.

Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics.
Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.
For information on the types in question please contact our Sales Organization.
If printed or downloaded, please find the latest version on our website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.
Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/ applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.

Downloaded from Arrow.com.

Glossary

1) **Radiant intensity:** Measured at a solid angle of Ω = 0.01 sr

2) **Brightness:** The brightness values are measured with a tolerance of ±11%.

3) **Reverse Operation:** This product is intended to be operated applying a forward current within the specified range. Applying any continuous reverse bias or forward bias below the voltage range of light emission shall be avoided because it may cause migration which can change the electro-optical characteristics or damage the LED.

4) **Forward Voltage:** The forward voltages are measured with a tolerance of ±0.1 V.

5) **Total radiant flux:** Measured with integrating sphere.

6) **Thermal resistance:** junction - soldering point, of the device only, mounted on an ideal heatsink (e.g. metal block)

7) **Typical Values:** Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.

8) **Testing temperature:** TA = 25°C (unless otherwise specified)

9) **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.

10) **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.

Downloaded from Arrow.com.

Revision History

Version	Date	Change
1.0	2025-11-06	Derating (Diagrams) Characteristics
1.1	2025-11-28	Maximum Ratings Derating (Diagrams) Product Image Description
1.2	2026-02-13	Derating (Diagrams)
1.3	2026-03-26	Characteristics
1.4	2026-09-01	Features

Downloaded from Arrow.com.

EU RoHS and China RoHS compliant product
此产品符合欧盟 RoHS 指令的要求；
按照中国的相关法规和标准，
不含有毒有害物质或元素。

Published by ams-OSRAM AG
Tobelbader Strasse 30, 8141 Premstaetten, Austria
Phone +43 3136 500-0
ams-osram.com
© All rights reserved

Downloaded from Arrow.com.