



# TAOGLAS®



# Datasheet

## Synergy 4 in 1 Antenna

**Part No:**  
MA1504.AK.001

### Description:

4\*5G/4G MIMO 4-in-1 Antenna with Wideband 600-6000MHz Capabilities

### Features:

- 4 x 5G/4G MIMO Antenna
- IP67 Rated Waterproof Enclosure
- High Efficiency/Peak Gain Outdoor Antenna
- Cable: 300mm RG-174 with 4700mm TGC-200
- Connectors: SMA(M)
- RoHS & REACH Compliant

|                            |    |
|----------------------------|----|
| 1. Introduction            | 3  |
| 2. Specifications          | 4  |
| 3. Antenna Characteristics | 7  |
| 4. Radiation Patterns      | 10 |
| 5. Mechanical Drawing      | 55 |
| 6. Packaging               | 56 |
| Changelog                  | 57 |

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.



# 1. Introduction



The Taoglas Synergy MA1504 is a 4-in-1 next-generation permanent mount antenna for vehicle roof applications. It has a fully IP67 rated waterproof robust PC enclosure and base. The 4 antennas inside support 600-6000MHz 5G/4G. This outstanding patent-pending antenna delivers powerful MIMO antenna technology for 5G/4G. The 5G/4G antennas also include backward compatibility to work at most worldwide 2G and 3G bands.

## Typical Applications:

- Next Generation OEM Automotive Connectivity
- Multimedia, Navigation and Telematics Systems
- V2V, V2X and Fleet Management Applications
- Real-time HD Video Streaming
- First Net Responder Routers

The MA1504 is ideal for applications that require highly sophisticated antennas for real-time streaming applications that demand high-speed video uplink and downlink into the cabin of the vehicle. These challenges are resolved by the highly efficient, high gain MIMO antennas, with high isolation, all of which is necessary to achieve the required signal to noise ratio and throughput.

The MA1504 can also be customized for your particular wireless application and frequency band, subject to NRE and MOQ. All cable lengths and connector types are customizable. The Synergy MA1504 can be supplied with low loss TGC-200 cable extensions for longer cable runs. Contact your regional Taoglas customer services team for details and support.

## 2. Specifications


| 5G/4G MIMO                |                 |       |                |                   |                 |           |              |                   |                  |
|---------------------------|-----------------|-------|----------------|-------------------|-----------------|-----------|--------------|-------------------|------------------|
| Band                      | Frequency (MHz) |       | Efficiency (%) | Average Gain (dB) | Peak Gain (dBi) | Impedance | Polarization | Radiation Pattern | Max. input power |
| 5G NR Band 71             | 617 ~698        | LTE 1 | 16%            | -8.0              | -2.7            | 50 Ω      | Linear       | Omni              | 2W               |
|                           |                 | LTE 2 | 16%            | -8.1              | -4.0            |           |              |                   |                  |
|                           |                 | LTE 3 | 15%            | -8.1              | -3.8            |           |              |                   |                  |
|                           |                 | LTE 4 | 17%            | -7.8              | -3.6            |           |              |                   |                  |
| LTE700                    | 698 ~824        | LTE 1 | 18%            | -7.5              | -2.0            |           |              |                   |                  |
|                           |                 | LTE 2 | 18%            | -7.6              | -1.6            |           |              |                   |                  |
|                           |                 | LTE 3 | 15%            | -8.2              | -3.5            |           |              |                   |                  |
|                           |                 | LTE 4 | 18%            | -7.4              | -2.3            |           |              |                   |                  |
| GSM 850/900               | 824 ~960        | LTE 1 | 22%            | -6.6              | -0.1            |           |              |                   |                  |
|                           |                 | LTE 2 | 27%            | -5.7              | 1.2             |           |              |                   |                  |
|                           |                 | LTE 3 | 22%            | -6.7              | -0.6            |           |              |                   |                  |
|                           |                 | LTE 4 | 28%            | -5.6              | 1.8             |           |              |                   |                  |
| 5G NR Band                | 1427 ~1518      | LTE 1 | 25%            | -6.1              | 1.5             |           |              |                   |                  |
|                           |                 | LTE 2 | 24%            | -6.2              | 2.1             |           |              |                   |                  |
|                           |                 | LTE 3 | 28%            | -5.6              | 2.3             |           |              |                   |                  |
|                           |                 | LTE 4 | 22%            | -6.7              | 1.1             |           |              |                   |                  |
| DCS                       | 1710 ~1880      | LTE 1 | 33%            | -4.8              | 2.7             |           |              |                   |                  |
|                           |                 | LTE 2 | 30%            | -5.2              | 2.4             |           |              |                   |                  |
|                           |                 | LTE 3 | 31%            | -5.0              | 2.3             |           |              |                   |                  |
|                           |                 | LTE 4 | 29%            | -5.3              | 2.6             |           |              |                   |                  |
| PCS                       | 1850 ~1990      | LTE 1 | 32%            | -4.9              | 2.5             |           |              |                   |                  |
|                           |                 | LTE 2 | 30%            | -5.3              | 2.9             |           |              |                   |                  |
|                           |                 | LTE 3 | 31%            | -5.1              | 1.7             |           |              |                   |                  |
|                           |                 | LTE 4 | 28%            | -5.5              | 2.9             |           |              |                   |                  |
| UMTS1                     | 1920 ~2170      | LTE 1 | 34%            | -4.7              | 3.3             |           |              |                   |                  |
|                           |                 | LTE 2 | 26%            | -5.8              | 1.6             |           |              |                   |                  |
|                           |                 | LTE 3 | 32%            | -5.0              | 2.7             |           |              |                   |                  |
|                           |                 | LTE 4 | 26%            | -5.9              | 2.1             |           |              |                   |                  |
| LTE2600                   | 2300 ~2690      | LTE 1 | 33%            | -4.9              | 4.5             |           |              |                   |                  |
|                           |                 | LTE 2 | 24%            | -6.2              | 1.5             |           |              |                   |                  |
|                           |                 | LTE 3 | 32%            | -5.0              | 4.1             |           |              |                   |                  |
|                           |                 | LTE 4 | 25%            | -6.0              | 1.8             |           |              |                   |                  |
| 5G NR Band 48, 77, 78, 79 | 3300 ~5000      | LTE 1 | 21%            | -7.0              | 1.3             |           |              |                   |                  |
|                           |                 | LTE 2 | 20%            | -7.2              | 1.0             |           |              |                   |                  |
|                           |                 | LTE 3 | 21%            | -6.9              | 1.6             |           |              |                   |                  |
|                           |                 | LTE 4 | 15%            | -8.3              | -0.2            |           |              |                   |                  |
| LTE5200/ Wi-Fi 5800       | 5150 ~5925      | LTE 1 | 24%            | -6.2              | 2.3             |           |              |                   |                  |
|                           |                 | LTE 2 | 23%            | -6.5              | 2.0             |           |              |                   |                  |
|                           |                 | LTE 3 | 24%            | -6.1              | 2.3             |           |              |                   |                  |
|                           |                 | LTE 4 | 23%            | -6.4              | 2.4             |           |              |                   |                  |

| Mechanical         |                                                              |
|--------------------|--------------------------------------------------------------|
| Height             | 57.47mm                                                      |
| Planner Dimension  | Ø160mm                                                       |
| Casing             | PC                                                           |
| Cable              | 0.3m RG-174 with 4.7m TGC-200 for 5G/4G – Fully Customizable |
| Connector          | 5G/4G_SMA-Plug – Fully Customizable                          |
| Thread             | 18.23mm                                                      |
| Thread Diameter    | M22                                                          |
| Waterproof         | IP67                                                         |
| Sealant            | Rubber Stopper and O-Ring                                    |
| Weight             | 2Kg                                                          |
| Environmental      |                                                              |
| Ingress Protection | IP67                                                         |
| Temperature Range  | -40°C to 85°C                                                |
| Humidity           | Non-condensing 65°C 95% RH                                   |
| Cable Pull         | RG-174 4 Kg                                                  |


| 5G/4G Bands |                                                                    |                               |         |
|-------------|--------------------------------------------------------------------|-------------------------------|---------|
| Band Number | 5G NR / FR1 / LTE / LTE-Advanced / WCDMA / HSPA / HSPA+ / TD-SCDMA |                               |         |
|             | Uplink                                                             | Downlink                      | Covered |
| 1           | UL: 1920 to 1980                                                   | DL: 2110 to 2170              | ✓       |
| 2           | UL: 1850 to 1910                                                   | DL: 1930 to 1990              | ✓       |
| 3           | UL: 1710 to 1785                                                   | DL: 1805 to 1880              | ✓       |
| 4           | UL: 1710 to 1755                                                   | DL: 2110 to 2155              | ✓       |
| 5           | UL: 824 to 849                                                     | DL: 869 to 894                | ✓       |
| 7           | UL: 2500 to 2570                                                   | DL: 2620 to 2690              | ✓       |
| 8           | UL: 880 to 915                                                     | DL: 925 to 960                | ✓       |
| 9           | UL: 1749.9 to 1784.9                                               | DL: 1844.9 to 1879.9          | ✓       |
| 11          | UL: 1427.9 to 1447.9                                               | DL: 1475.9 to 1495.9          | ✓       |
| 12          | UL: 699 to 716                                                     | DL: 729 to 746                | ✓       |
| 13          | UL: 777 to 787                                                     | DL: 746 to 756                | ✓       |
| 14          | UL: 788 to 798                                                     | DL: 758 to 768                | ✓       |
| 17          | UL: 704 to 716                                                     | DL: 734 to 746 (LTE only)     | ✓       |
| 18          | UL: 815 to 830                                                     | DL: 860 to 875 (LTE only)     | ✓       |
| 19          | UL: 830 to 845                                                     | DL: 875 to 890                | ✓       |
| 20          | UL: 832 to 862                                                     | DL: 791 to 821                | ✓       |
| 21          | UL: 1447.9 to 1462.9                                               | DL: 1495.9 to 1510.9          | ✓       |
| 22          | UL: 3410 to 3490                                                   | DL: 3510 to 3590              | ✓       |
| 23          | UL: 2000 to 2020                                                   | DL: 2180 to 2200 (LTE only)   | ✓       |
| 24          | UL: 1625.5 to 1660.5                                               | DL: 1525 to 1559 (LTE only)   | ✓       |
| 25          | UL: 1850 to 1915                                                   | DL: 1930 to 1995              | ✓       |
| 26          | UL: 814 to 849                                                     | DL: 859 to 894                | ✓       |
| 27          | UL: 807 to 824                                                     | DL: 852 to 869 (LTE only)     | ✓       |
| 28          | UL: 703 to 748                                                     | DL: 758 to 803 (LTE only)     | ✓       |
| 29          | UL: -                                                              | DL: 717 to 728 (LTE only)     | ✓       |
| 30          | UL: 2305 to 2315                                                   | DL: 2350 to 2360 (LTE only)   | ✓       |
| 31          | UL: 452.5 to 457.5                                                 | DL: 462.5 to 467.5 (LTE only) | ✗       |
| 32          | UL: -                                                              | DL: 1452 - 1496               | ✓       |
| 35          |                                                                    | 1850 to 1910                  | ✓       |
| 38          |                                                                    | 2570 to 2620                  | ✓       |
| 39          |                                                                    | 1880 to 1920                  | ✓       |
| 40          |                                                                    | 2300 to 2400                  | ✓       |
| 41          |                                                                    | 2496 to 2690                  | ✓       |
| 42          |                                                                    | 3400 to 3600                  | ✓       |
| 43          |                                                                    | 3600 to 3800                  | ✓       |
| 48          |                                                                    | 3550 to 3700                  | ✓       |
| 66          | UL: 1710-1780                                                      | DL: 2110-2200                 | ✓       |
| 71          |                                                                    | 617 to 698                    | ✓       |
| 74/75/76    |                                                                    | 1427 to 1518                  | ✓       |
| 78          |                                                                    | 3300 to 3800                  | ✓       |
| 79          |                                                                    | 4400 to 5000                  | ✓       |

## 3. Antenna Characteristics


### 3.1 Return Loss




### 3.2 Isolation




### 3.3 Efficiency




### 3.4 Average Gain



### 3.5 Peak Gain




### 3.6 ECC



## 4. Radiation Patterns


### 4.1 Test Setup

Radiation patterns obtained with 300mm of cable.




On 30x30cm Ground Plane


## 4.2 660MHz - MIMO 1 Radiation Patterns




XY Plane




XZ Plane




YZ Plane




750 MHz




XY Plane




XZ Plane




YZ Plane




880MHz




XY Plane




XZ Plane




YZ Plane




1465MHz




XY Plane




XZ Plane




YZ Plane




1805MHz




XY Plane




XZ Plane




YZ Plane




1920MHz




XY Plane




XZ Plane




YZ Plane




2010MHz




XY Plane




XZ Plane




YZ Plane




2500MHz




XY Plane




XZ Plane




YZ Plane




3300MHz




XY Plane




XZ Plane




YZ Plane




3600MHz




XY Plane




XZ Plane




YZ Plane




5550MHz




XY Plane




XZ Plane




YZ Plane




### 4.3 660MHz - MIMO 2 Radiation Patterns




XY Plane




XZ Plane




YZ Plane




750MHz




XY Plane




XZ Plane




YZ Plane




880MHz




XY Plane




XZ Plane




YZ Plane




1465MHz




XY Plane




XZ Plane




YZ Plane




1805MHz




XY Plane




XZ Plane




YZ Plane




1920MHz




XY Plane




XZ Plane




YZ Plane




2010MHz




XY Plane




XZ Plane




YZ Plane




2500MHz




XY Plane




XZ Plane




YZ Plane




3300MHz




XY Plane




XZ Plane




YZ Plane




3600MHz




XY Plane




XZ Plane




YZ Plane




5550MHz




XY Plane




XZ Plane




YZ Plane




## 4.4 660MHz - MIMO 3 Radiation Patterns




XY Plane




XZ Plane




YZ Plane




750MHz




XY Plane




XZ Plane




YZ Plane




880MHz




XY Plane




XZ Plane




YZ Plane




1465MHz




XY Plane




XZ Plane




YZ Plane




1805MHz




XY Plane




XZ Plane




YZ Plane




1920MHz




XY Plane




XZ Plane




YZ Plane




2010MHz




XY Plane




XZ Plane




YZ Plane




2500MHz




XY Plane




XZ Plane




YZ Plane




3300MHz




XY Plane




XZ Plane




YZ Plane




3600MHz




XY Plane




XZ Plane




YZ Plane




5550MHz




XY Plane




XZ Plane




YZ Plane




## 4.5 660MHz - MIMO 4 Radiation Patterns




XY Plane




XZ Plane




YZ Plane




750MHz




XY Plane




XZ Plane




YZ Plane




880MHz




XY Plane




XZ Plane




YZ Plane




1465MHz




XY Plane



XZ Plane




YZ Plane




1805MHz


XY Plane




XZ Plane




YZ Plane




1920MHz




XY Plane




XZ Plane




YZ Plane




2010MHz




XY Plane




XZ Plane




YZ Plane




2500MHz




XY Plane




XZ Plane




YZ Plane




3300MHz




XY Plane




XZ Plane




YZ Plane




3600MHz




XY Plane




XZ Plane




YZ Plane




5550MHz




XY Plane



XZ Plane




YZ Plane








## 6. Packaging



1pc MA1504.AK.001 per PE Bag  
Weight: 2Kg



4pcs MA1509.AK.001 per Carton  
Carton Dimensions: 740\*370\*300mm  
Weight: 8.4Kg



Changelog for the datasheet

SPE-20-8-005 - MA1504.AK.001

| Revision: C (Current Version) |                 |
|-------------------------------|-----------------|
| Date:                         | 2024-07-22      |
| Notes:                        | Updated drawing |
| Author:                       | Conor McGrath   |

Previous Revisions

| Revision: B |              |
|-------------|--------------|
| Date:       | 2022-08-16   |
| Notes:      | Updated data |
| Author:     | Gary West    |

| Revision: A (Original First Release) |                 |
|--------------------------------------|-----------------|
| Date:                                | 2020-01-14      |
| Notes:                               | Initial Release |
| Author:                              | Jack Conroy     |

