300mA LDO
Monolithic IC MM3571 Series

Outline

This IC is a 300mA Low dropout regulator IC with a prevention circuit of rush current.
No load input current is 25μA typ, and it reduce transient drop in voltage with high speed response circuit.
A rush current prevention circuit can control rush current at start up.

Features

1.	Maximum operating voltage	6.5V
2.	Output current	300mA
3.	No load input current	25μA typ.
4.	Input current (OFF)	1μA max.
5.	Output voltage range	1.0~5.0V
6.	Output voltage accuracy	±1%
7.	Dropout voltage	0.62V typ. (I_{OUT}=300mA)
8.	Line regulation	0.1%/V max.
9.	Load regulation	30mV typ.(I_{OUT}=1~300mA)
10.	Ripple rejection	70dB typ. (f=1kHz)
11.	Output Capacitor	0.47μF
12.	ON/OFF control	

Package

SC-82ABB
SOT-25A
SOT89-5A


Applications

1. Mobile phone, Smart phone
2. Digital camera
3. Game equipment
4. Tablet


• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.

Block Diagram




Pin Assignment




SC-82ABB
(TOP VIEW)

1	CE
2	GND
3	VOUT
4	VDD



SOT-25A
(TOP VIEW)

1	VDD
2	GND
3	CE
4	NC
5	VOUT



SOT89-5A
(TOP VIEW)

1	VOUT
2	GND
3	NC
4	CE
5	VDD

Note1 : Heat Spreader Bottom with GND.

• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.

Pin Description

SC-82ABB

Pin No.	Pin name	Functions
1	CE	ON/OFF-Control pin CE: L → OUTPUT: OFF; CE: H → OUTPUT: ON Connect CE pin with V_{DD} pin, when it is not used.
2	GND	GND pin
3	V_{OUT}	Output pin
4	V_{DD}	Voltage-Supply pin

SOT-25A

Pin No.	Pin name	Functions
1	V_{DD}	Voltage-supply pin
2	GND	GND pin
3	CE	ON/OFF-Control pin CE: L → OUTPUT: OFF; CE: H → OUTPUT: ON Connect CE pin with V_{DD} pin, when it is not used.
4	NC	No connection
5	V_{OUT}	Output pin

SOT89-5A

Pin No.	Pin name	Functions
1	V_{OUT}	Output pin
2	GND	GND pin
3	NC	No connection
4	CE	ON/OFF-Control pin CE: L → OUTPUT: OFF; CE: H → OUTPUT: ON Connect CE pin with V_{DD} pin, when it is not used.
5	V_{DD}	Voltage-supply pin

Absolute Maximum Ratings (Except where noted otherwise Ta=25°C)

Item	Symbol	Ratings	Units
Storage Temperature	Tstg	-55~+150	°C
Junction Temperature	T_{jMAX}	150	°C
Supply Voltage	V_{DD}	-0.3~+7.0	V
CE input Voltage	V_{CE}	-0.3~+7.0	V
Output Voltage	V_{OUT}	-0.3~+7.0	V
Output Current	Iomax	500	mA
Power Dissipation 1	Pd1	330(Note2) (SC-82ABB)	mW
		350(Note3) (SOT-25A)	
		690(Note4) (SOT89-5A)	
Power Dissipation 2	Pd2	650(Note5) (SC-82ABB)	mW
		700(Note5) (SOT-25A)	
		1780(Note5) (SOT89-5A)	

Note2 : With PC Board of glass epoxy 100 × 100 × 1.6mm
Note3 : With PC Board of glass epoxy 60 × 40 × 1.6mm
Note4 : With PC Board of glass epoxy 50 × 50 × 1.6mm
Note5 : JEDEC51-7 standard 114.3 × 76.2 × 1.6mm

• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.

Recommended Operating Conditions (Except where noted otherwise Ta=25°C)

Item	Symbol	Ratings	Units
Operating Ambient Temperature	Topr	–40~+85	°C
Operating Voltage	Vop	2.0~6.5	V
Output Current	Iop	0~300	mA

Electrical Characteristics 1 (Except where noted otherwise $V_{DD}=V_{OUT}$(TYP.)+1V, $V_{CE}=V_{DD}$, Ta=25°C)

Item	Symbol	Measurement conditions	Min.	Typ.	Max.	Units
Input Current(OFF)	I_{DDOff}	V_{CE}=0V		0.01	1.0	µA
No-Load Input Current	I_{DD}	I_{OUT}=0mA		25	40	µA
Output Voltage	V_{OUT}	I_{OUT}=10mA (V_{OUT}≧2.0V)	×0.99		×1.01	V
		I_{OUT}=10mA (V_{OUT}≦1.9V)	–0.02		+0.02	V
Line Regulation	V_{LINE}	V_{OUT} (TYP.)+0.5V≦V_{DD}≦6.5V V_{OUT}≧1.1V, I_{OUT}=10mA		0.01	0.10	%/V
		V_{OUT} (TYP.)+1.0V≦V_{DD}≦6.5V V_{OUT}=1.0V, I_{OUT}=10mA				
Load Regulation 1 (Note6)	V_{LOAD1}	1mA≦I_{OUT}≦150mA		10	40	mV
Load Regulation 2 (Note6)	V_{LOAD2}	1mA≦I_{OUT}≦300mA		30	120	mV
Dropout Voltage	Vio	Please refer to another page				V
Ripple Rejection (Note7)	RR	f=1kHz, Vripple=0.5V, I_{OUT}=10mA		70		dB
V_{OUT} Temperature Coefficient (Note7)	$\Delta V_{OUT}/\Delta T$	I_{OUT}=10mA, –40≦Top≦+85°C		±100		ppm/°C
Output Current Limit	Ilim		300	500		mA
Output Short-Circuit Current (Note7)	Ishort	V_{OUT}=0V		50		mA
CE High Threshold Voltage	V_{CEH}		1.5		V_{DD}	V
CE Low Threshold Voltage	V_{CEL}				0.3	V
CE High Threshold Current	I_{CEH}		–1.0		+1.0	µA
CE Low Threshold Current	I_{CEL}		–1.0		+1.0	µA
CL Discharge Resistance (Note7)	Rdisc	V_{CE}=0V, V_{DD}=6V		10		

Note6 : V_{DD}=2.5V at V_{OUT}≦1.5V.

Note7 : The parameter is guaranteed by design.

• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.

Electrical Characteristics 2 (Except where noted otherwise $V_{DD}=V_{OUT}$(TYP.)+1V, $V_{CE}=V_{DD}$, Ta=25°C)

Model No.	Item							
	Output Voltage				Dropout Voltage			
	V_{OUT} (V)				V_{OUT} (V)			
	Measurement Conditions	Min.	Typ.	Max.	Measurement Conditions	Min.	Typ.	Max.
MM3571A10	I_{OUT}=10mA	0.980	1.000	1.020	I_{OUT}=150mA 1.0V≦V_{OUT}<1.9V (Note8)		0.69	0.79
MM3571A11		1.080	1.100	1.120				
MM3571A12		1.180	1.200	1.220				
MM3571A13		1.280	1.300	1.320			0.60	0.70
MM3571A14		1.380	1.400	1.420				
MM3571A15		1.480	1.500	1.520				
MM3571A16		1.580	1.600	1.620			0.51	0.61
MM3571A17		1.680	1.700	1.720				
MM3571A18		1.780	1.800	1.820				
MM3571A19		1.880	1.900	1.920	I_{OUT}=150mA 1.9V≦V_{OUT}≦5.0V $V_{DD}=V_{OUT}$ (TYP.) –0.2V		0.47	0.57
MM3571A20		1.980	2.000	2.020				
MM3571A21		2.079	2.100	2.121				
MM3571A22		2.178	2.200	2.222				
MM3571A23		2.277	2.300	2.323				
MM3571A24		2.376	2.400	2.424				
MM3571A25		2.475	2.500	2.525			0.31	0.41
MM3571A26		2.574	2.600	2.626				
MM3571A27		2.673	2.700	2.727				
MM3571A28		2.772	2.800	2.828				
MM3571A29		2.871	2.900	2.929				
MM3571A30		2.970	3.000	3.030				
MM3571A31		3.069	3.100	3.131				
MM3571A32		3.168	3.200	3.232				
MM3571A33		3.267	3.300	3.333				
MM3571A34		3.366	3.400	3.434				
MM3571A35		3.465	3.500	3.535			0.23	0.33
MM3571A36		3.564	3.600	3.636				
MM3571A37		3.663	3.700	3.737				
MM3571A38		3.762	3.800	3.838				
MM3571A39		3.861	3.900	3.939				
MM3571A40		3.960	4.000	4.040				
MM3571A41		4.059	4.100	4.141				
MM3571A42		4.158	4.200	4.242				
MM3571A43		4.257	4.300	4.343				
MM3571A44		4.356	4.400	4.444				
MM3571A45		4.455	4.500	4.545			0.19	0.28
MM3571A46		4.554	4.600	4.646				
MM3571A47		4.653	4.700	4.747				
MM3571A48		4.752	4.800	4.848				
MM3571A49		4.851	4.900	4.949				
MM3571A50		4.950	5.000	5.050				

Note8 : Dropout voltage maximum value in the input and it is confirmed that there is no output abnormal voltage impression the 150mA in the model less than V_{OUT}<1.9V.

• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.


Model No.	Item							
	Output Voltage				Dropout Voltage			
	V_{OUT} (V)				V_{OUT} (V)			
	Measurement Conditions	Min.	Typ.	Max.	Measurement Conditions	Min.	Typ.	Max.
MM3571A10	I_{OUT}=10mA	0.980	1.000	1.020	I_{OUT}=300mA 1.0V≦V_{OUT}<2.7V (Note9)		1.38	1.50
MM3571A11		1.080	1.100	1.120				
MM3571A12		1.180	1.200	1.220				
MM3571A13		1.280	1.300	1.320			1.20	1.40
MM3571A14		1.380	1.400	1.420				
MM3571A15		1.480	1.500	1.520				
MM3571A16		1.580	1.600	1.620			1.02	1.22
MM3571A17		1.680	1.700	1.720				
MM3571A18		1.780	1.800	1.820				
MM3571A19		1.880	1.900	1.920			0.94	1.14
MM3571A20		1.980	2.000	2.020				
MM3571A21		2.079	2.100	2.121				
MM3571A22		2.178	2.200	2.222				
MM3571A23		2.277	2.300	2.323				
MM3571A24		2.376	2.400	2.424				
MM3571A25		2.475	2.500	2.525			0.62	0.82
MM3571A26		2.574	2.600	2.626				
MM3571A27		2.673	2.700	2.727	I_{OUT}=300mA 2.7V≦V_{OUT}≦5.0V V_{DD}=V_{OUT} (TYP.) –0.2V			
MM3571A28		2.772	2.800	2.828				
MM3571A29		2.871	2.900	2.929				
MM3571A30		2.970	3.000	3.030				
MM3571A31		3.069	3.100	3.131				
MM3571A32		3.168	3.200	3.232				
MM3571A33		3.267	3.300	3.333				
MM3571A34		3.366	3.400	3.434				
MM3571A35		3.465	3.500	3.535			0.46	0.66
MM3571A36		3.564	3.600	3.636				
MM3571A37		3.663	3.700	3.737				
MM3571A38		3.762	3.800	3.838				
MM3571A39		3.861	3.900	3.939				
MM3571A40		3.960	4.000	4.040				
MM3571A41		4.059	4.100	4.141				
MM3571A42		4.158	4.200	4.242				
MM3571A43		4.257	4.300	4.343				
MM3571A44		4.356	4.400	4.444				
MM3571A45		4.455	4.500	4.545			0.38	0.56
MM3571A46		4.554	4.600	4.646				
MM3571A47		4.653	4.700	4.747				
MM3571A48		4.752	4.800	4.848				
MM3571A49		4.851	4.900	4.949				
MM3571A50		4.950	5.000	5.050				

Note9 : Dropout voltage maximum value in the input and it is confirmed that there is no output abnormal voltage impression the 300mA in the model less than V_{OUT}<2.7V.


• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.

Measuring Circuit



Application Circuit



* Temperature Characteristics : B

(Reference example of external parts)

· Output capacitor Ceramic capacitor 0.47µF
· Input capacitor Ceramic capacitor 0.47µF

· We shall not be liable for any trouble or damage caused by using this circuit.

· In the event a problem which may affect industrial property or any other rights of us or a third party is encountered during the use of information described in these circuit, we shall not be liable for any such problem, nor grant a license therefore.

• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.

· Note

1. Please use this IC within the stated absolute maximum ratings.
   The IC is liable to malfunction should the ratings be exceeded.
2. Due to restrictions on the package power dissipation, the output current value may not be satisfied.
   Attention should be paid to the power dissipation of the package when the output current is large or the voltage between Iinput and Output is high.
3. The output capacitor is required between output and GND to prevent oscillation.
4. The ESR of capacitor must be defined in ESR stability area. It is possible to use a ceramic capacitor without ESR resistance for output. The ceramic capacitor must be used more than 0.47μF and B temperature characteristics.
5. The wire of VDD and GND is required to print full ground plane for noise and stability.
6. The input capacitor must be connected a distance of less than 1cm from input pin.
7. It is able to oscillation when you use the capacitor with intense capacitance change such as micro.
   Please evaluate IC in the set.
8. In case the output voltage is above the input voltage, the overcurrent flow by internal parastic diode from output to input.In such application, the external bypass diode must be connected between output and input pin.
9. This IC will limit the output current with the overcurrent protection circuit when the overcurrent and the output do short-circuit.
   However, IC generates heat because of the substrate and use conditions and there is a possibility of destroying it exceeding a permissible loss.
   The characteristic changes depending on the substrate condition. Please evaluate IC in the set.

• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.


Downloaded from Arrow.com.

About Power Dissipation

The Power dissipation change if board to mount IC change because radiative heat fix at board.It is reference data below, Evaluate IC in the set.


MM3571AxxURE

1. PC Board of glass epoxy
   Board size 100mm×100mm t=1.6mm Copper foil area 10%
   Power dissipation 330mW Ta=25°C
2. JEDEC51-7 standard
   Board size 114.3mm×76.2mm t=1.6mm Copper foil area 80%
   Power dissipation 650mW Ta=25°C (It is reference value measured by JEDEC51-7 standard.)



MM3571AxxNRE

1. PC Board of glass epoxy
   Board size 60mm×40mm t=1.6mm Copper foil area 60%
   Power dissipation 350mW Ta=25°C
2. JEDEC51-7 standard
   Board size 114.3mm×76.2mm t=1.6mm Copper foil area 80%
   Power dissipation 700mW Ta=25°C (It is reference value measured by JEDEC51-7 standard.)




• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.

MM3571AxxPRE

1. PC Board of glass epoxy
   Board size 50mm×50mm t=1.6mm Copper foil area 20%
   Power dissipation 690mW Ta=25°C
2. JEDEC51-7 standard
   Board size 114.3mm×76.2mm t=1.6mm Copper foil area 80%
   Power dissipation 1780mW Ta=25°C (It is reference value measured by JEDEC51-7 standard.)




It is recommended to layout the VIA for heat radiation in the GND pattern of reverse (of IC) when there is the GND pattern in the inner layer (in using multiplayer substrate).
By increasing these copper foil pattern area of PCB, Power dissipation improves.

• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.


Downloaded from Arrow.com.

Characteristics (V_{OUT}=1.0V) (Except where noted otherwise V_{DD}=V_{OUT}(TYP.)+1V, V_{CE}=V_{DD}, Ta=25°C)


Input Voltage - Output Voltage




Input Voltage - Input Current




Load Regulation



Line Regulation




Vout Temperature Coefficient




• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.


Ripple Rejection



ESR stable area



Current Limit




• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.


Downloaded from Arrow.com.

Load Transient response
(V_{DD}=2.5V, V_{CE}=V_{DD}, Cin=Cout=0.47µF)


I_{OUT}=1mA⇔100mA




I_{OUT}=1mA⇔300mA




I_{OUT}=10mA⇔300mA




I_{OUT}=100mA⇔200mA



CE Transient
(V_{DD}=2.5V, V_{CE}=0V→V_{DD}, C_O=0.47µF)



CE Transient
(V_{DD}=2.5V, V_{CE}=0V→V_{DD}, C_O=10µF)




• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.


Output Rise Time

(V_{DD}=2.5V, V_{CE}=0V→V_{DD}, Cin=0.47μF)


Output Capacitor – Output Rise Time
(Co=0.47μF – 1000μF)




Output Capacitor – Output Rise Time
(Co=0.47μF – 47μF)



Output Capacitor Co – Rush Current
(Co=0.47μF – 1000μF)



Output Capacitor Co – Rush Current
(Co=0.47μF – 47μF)




• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.


Downloaded from Arrow.com.

Characteristics (V_{OUT}=3.0V) (Except where noted otherwise V_{DD}=V_{OUT}(TYP.)+1V, V_{CE}=V_{DD}, Ta=25°C)


Input Voltage - Output Voltage




Input Voltage - Input Current




Load Regulation




Line Regulation



Dropout Voltage




Vout Temperature Coefficient




• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.


Ripple Rejection



ESR stable area



Current Limit




• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.


Downloaded from Arrow.com.

Load Transient response
(V_{DD}=V_{OUT}+1V, V_{CE}=V_{DD}, Cin=Cout=0.47µF)


I_{OUT}=1mA⇔100mA




I_{OUT}=1mA⇔300mA




I_{OUT}=10mA⇔300mA




I_{OUT}=100mA⇔200mA



CE Transient
(V_{DD}=V_{OUT}+1V, V_{CE}=0V→V_{DD}, C_O=0.47µF)



CE Transient
(V_{DD}=V_{OUT}+1V, V_{CE}=0V→V_{DD}, C_O=10µF)




• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.


Output Rise Time

(V_{DD}=V_{OUT}+1V, V_{CE}=0V→V_{DD}, Cin=0.47μF)


Output Capacitor – Output Rise Time
(Co=0.47μF – 1000μF)




Output Capacitor – Output Rise Time
(Co=0.47μF – 47μF)



Output Capacitor Co – Rush Current
(Co=0.47μF – 1000μF)




Output Capacitor Co – Rush Current
(Co=0.47μF – 47μF)




Downloaded from Arrow.com.

Characteristics (V_{OUT}=5.0V) (Except where noted otherwise V_{DD}=V_{OUT}(TYP.)+1V, V_{CE}=V_{DD}, Ta=25°C)


Input Voltage - Output Voltage




Input Voltage - Input Current




Load Regulation




Line Regulation



Dropout Voltage




Vout Temperature Coefficient




• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.


Ripple Rejection



ESR stable area



Current Limit




• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.


Downloaded from Arrow.com.

Load Transient response
(V_{DD}=V_{OUT}+1V, V_{CE}=V_{DD}, Cin=Cout=0.47µF)


I_{OUT}=1mA⇔100mA




I_{OUT}=1mA⇔300mA




I_{OUT}=10mA⇔300mA




I_{OUT}=100mA⇔200mA



CE Transient
(V_{DD}=V_{OUT}+1V, V_{CE}=0V→V_{DD}, C_O=0.47µF)



CE Transient
(V_{DD}=V_{OUT}+1V, V_{CE}=0V→V_{DD}, C_O=10µF)




• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.


Output Rise Time

(V_{DD}=V_{OUT}+1V, V_{CE}=0V→V_{DD}, Cin=0.47μF)


Output Capacitor – Output Rise Time
(Co=0.47μF – 1000μF)




Output Capacitor – Output Rise Time
(Co=0.47μF – 47μF)



Output Capacitor Co – Rush Current
(Co=0.47μF – 1000μF)



Output Capacitor Co – Rush Current
(Co=0.47μF – 47μF)



• Any products mentioned in this catalog are subject to any modification in their appearance and others for improvements without prior notification.
• The details listed here are not a guarantee of the individual products at the time of ordering. When using the products, you will be asked to check their specifications.

Downloaded from Arrow.com.