

DC–40 GHz GaAs High–Gain MMIC Amplifier

MMA085AA



Product Overview

The MMA085AA is a DC-40 GHz Gallium Arsenide (GaAs) Monolithic Microwave Integrated Circuit (MMIC) Pseudomorphic High–Electron Mobility Transistor (pHEMT) distributed amplifier. It is ideal for test instrumentation, A&D, and space applications. The amplifier provides 16 dB of gain, 20 dBm of P1dB, and -45 dBc of IM3 at 5 dBm per tone with a nominal bias condition of 200 mA from a 7V supply. Noise Figure (NF) is typically 3.5 dB. The amplifier features compact die size with RF I/O's that are internally matched to 50Ω. The MMA085AA can receive up to 29 dBm (CW) of RF input power.

Key Features

- Frequency range: DC to 40 GHz
- Gain: 16 dB
- Positive gain slope
- High IM3: -45 dBc (at 5 dBm per tone)
- Output level detector
- Die input power handling: up to 29dBm (CW)
- Supply voltage: 5V – 9V. Typical voltage: 7V at 200 mA
- ESD Protection on RF and DC ports
- 50 Ohm Matched Input/Output
- Die: 2.05mm × 1. 43 mm × 0.1 mm


Applications

- Test and measurement instrumentation
- Electronic warfare (EW), electronic countermeasures (ECM), and electronic counter-countermeasures (ECCM)
- Military, A&D, space, SATCOM
- Telecom infrastructure
- Wideband microwave radios
- Microwave and millimeter-wave communications systems


Performance Overview

Parameter	Typ.	Units
Operational frequency range	DC–40	GHz
Gain	16	dB
Noise figure	3.5	dB
P1dB	20	dBm
IM3 at 5 dBm per Tone	-45	dBc

Functional Block Diagram



Performance Curves



Export Classification: 3A001.b.2.d

Table of Contents

Product Overview.....	1
1. Electrical Specifications.....	3
1.1. Typical Electrical Performance.....	3
1.2. Absolute Maximum Ratings.....	4
1.3. Typical Performance Curves.....	4
2. Die Specifications.....	15
3. Application Circuit.....	17
4. Ordering, Shipping, and Handling.....	19
4.1. Handling Recommendations.....	19
4.2. Ordering Information.....	19
4.3. Packing Information.....	19
5. Revision History.....	20
Microchip Information.....	21
The Microchip Website.....	21
Product Change Notification Service.....	21
Customer Support.....	21
Product Identification System.....	22
Microchip Devices Code Protection Feature.....	22
Legal Notice.....	22
Trademarks.....	22
Quality Management System.....	23
Worldwide Sales and Service.....	24

1. Electrical Specifications

1.1 Typical Electrical Performance

The following table shows the typical electrical performance of the MMA085AA device at 25 °C, $V_{DD} = 7V$, and $I_{DD} = 200$ mA, unless otherwise specified.

Table 1-1. Typical Electrical Performance

Parameter	Frequency Range	Min	Typ.	Max	Units
Frequency range		0		40	GHz
Gain	DC – 10 GHz	15	16	18	dB
	10 GHz – 30 GHz	15	16	17	
	30 GHz – 40 GHz	12	16	17	
Gain flatness	DC – 10 GHz		±1		dB
	10 GHz – 30 GHz		±0.5		
	30 GHz – 40 GHz		±1.5		
Noise figure	DC – 10 GHz		5	7	dB
	10 GHz – 30 GHz		3.5	5	
	30 GHz – 40 GHz		6	7.5	
Input return loss	DC – 10 GHz	14	17		dB
	10 GHz – 30 GHz	9	12		
	30 GHz – 40 GHz	8	9		
Output return loss	DC – 10 GHz	13	14		dB
	10 GHz – 30 GHz	10	12		
	30 GHz – 40 GHz	8	9		
P1dB	DC – 10 GHz	21	23		dBm
	10 GHz – 30 GHz	18	20		
	30 GHz – 40 GHz	12	16		
P_{sat}	DC – 10 GHz	23	25		dBm
	10 GHz – 30 GHz	19	22		
	30 GHz – 40 GHz	14	18		
IM3, at 5 dBm per tone	DC – 10 GHz		– 48		dBc
	10 GHz – 30 GHz		– 45		
	30 GHz – 40 GHz		– 30		
Input power survivability (CW)	6 GHz – 12 GHz			29	dBm
V_{DD} (drain voltage supply)			7		V
I_{DD} (drain current)			200		mA

1.2 Absolute Maximum Ratings

The following table shows the absolute maximum ratings of the MMA085AA device at 25 °C, unless otherwise specified. Exceeding any of the maximum ratings could cause damage and/or latent defects to the device.

Table 1-2. Absolute Maximum Ratings

Parameters	Rating
Drain bias voltage (V_{DD})	12V
Drain bias current (I_{DD})	300 mA
Gate bias voltage (V_G)	-2V to 0.5V
RF input power (P_{in})	+29 dBm (CW)
Channel temperature	175 °C
Thermal resistance	19 °C/W
Storage temperature	-65 °C to 150 °C
Operating temperature	-55 °C to 85 °C



ESD Sensitive Device

1.3 Typical Performance Curves

1.3.1 Typical Performances vs. Temperature

The graphs shown in figures 1-1 through 1-31 represent the Typical Performance versus Temperature curves of the MMA085AA device under specific bias conditions. All measurements were taken using the test circuit shown in Figure 3-2.

Figure 1-1. Gain vs. Temperature at 6V/150 mA




Figure 1-2. Gain vs. Temperature at 7V/200 mA




Figure 1-3. Gain vs. Temperature at 8V/250 mA




Figure 1-4. S11 vs. Temperature at 6V/150mA




Figure 1-5. S11 vs. Temperature at 7V/200 mA




Figure 1-6. S11 vs. Temperature at 8V/250 mA




Figure 1-7. S22 vs. Temperature at 6V/150 mA




Figure 1-8. S22 vs. Temperature at 7V/200 mA




Figure 1-9. S22 vs. Temperature at 8V/250 mA




Figure 1-10. S12 vs. Temperature at 6V/150 mA




Figure 1-11. S12 vs. Temperature at 7V/200 mA




Figure 1-12. S12 vs. Temperature at 8V/250 mA




Figure 1-13. NF vs. Temperature at 6V/150 mA




Figure 1-14. NF vs. Temperature at 7V/200 mA




Figure 1-15. NF vs. Temperature at 8V/250 mA




Figure 1-16. P1dB vs. Temperature at 5V/120 mA




Figure 1-17. P1dB vs. Temperature at 6V/150 mA




Figure 1-18. P1dB vs. Temperature at 7V/200 mA




Figure 1-19. P1dB vs. Temperature at 8V/250 mA




Figure 1-20. Psat vs. Temperature at 5V/120 mA




Figure 1-21. Psat vs. Temperature at 6V/150 mA




Figure 1-22. Psat vs. Temperature at 7V/200 mA




Figure 1-23. Psat vs. Temperature at 8V/250 mA




Figure 1-24. IM2 (low) vs. Temperature at 5V/120 mA¹




Figure 1-25. IM2 (low) vs. Temperature at 6V/150 mA¹




Figure 1-26. IM2 (low) vs. Temperature at 7V/200 mA¹




Figure 1-27. IM2 (low) vs. Temperature at 8V/250 mA¹




Figure 1-28. IM3 vs. Temperature at 5V/120 mA¹




Figure 1-29. IM3 vs. Temperature at 6V/150 mA¹




Figure 1-30. IM3 vs. Temperature at 7V/200 mA¹





Figure 1-31. IM3 vs. Temperature at 8V/250 mA¹



Note:

1. At 5 dBm per tone.

1.3.2 Typical Performances vs. Bias

The graphs shown in figures 1-32 through 1-44 represent the Typical Performance versus Bias curves of the MMA085AA under constant temperature of 25 °C. All measurements were taken using the test circuit shown in Figure 3-2.

Figure 1-32. Gain vs. V_{DD} at 120 mA




Figure 1-33. Gain vs. V_{DD} at 150 mA




Figure 1-34. Gain vs. V_{DD} at 200 mA




Figure 1-35. Gain vs. V_{DD} at 250 mA




Figure 1-36. NF vs. V_{DD} at 120 mA




Figure 1-37. NF vs. V_{DD} at 150 mA




Figure 1-38. NF vs. V_{DD} at 200 mA




Figure 1-39. NF vs. V_{DD} at 250 mA




Figure 1-40. P1dB Bias




Figure 1-41. P_{sat} vs. Bias




Figure 1-42. OIP3 vs. Bias




Figure 1-43. IM3 vs. Bias at 10 dBm per tone





Figure 1-44. OIP2 (Low at $\Delta = 10$ MHz) vs. Bias


1.3.3 Typical Performances vs. Output Power

The graphs shown in figures 1-45 through 1-56 represent the Typical Performance versus Output power curves of the MMA085AA under constant temperature of 25 °C. All measurements were taken using the test circuit shown in Figure 3-2.



Figure 1-45. IM2 vs. Power at 5V/120 mA

Figure 1-46. IM2 vs. Power at 6V/150 mA


Figure 1-47. IM2 vs. Power at 7V/200 mA




Figure 1-48. IM2 vs. Power at 8V/250 mA




Figure 1-49. IM3 vs. Power at 5V/120 mA




Figure 1-50. IM3 vs. Power at 6V/150 mA




Figure 1-51. IM3 vs. Power at 7V/200 mA




Figure 1-52. IM3 vs. Power at 8V/250 mA




Figure 1-53. 2nd Harmonic vs. Power at 5V/120 mA




Figure 1-54. 2nd Harmonic vs. Power at 6V/150 mA




Figure 1-55. 2nd Harmonic vs. Power at 7V/200 mA





Figure 1-56. 2nd Harmonic vs. Power at 8V/250 mA




2. Die Specifications

Figure 2-1 shows the chip outline of the MMA085AA device. Pad offsets are shown in microns relative to the zero datum location centered on pad 1.

Nominal die dimensions are 2.05 mm × 1.43 mm × 0.1 mm. The minimum bond pad size is 0.1 mm × 0.1 mm. The bond pad surface and the backside metal have 3 μm thick gold. The die thickness is 0.1 mm. The backside is the DC/RF ground. The airbridge keep-out polygon region is shown inside.

Figure 2-1. Die Outline Drawing (μm)



The following table shows the PAD descriptions for the MMA085AA device.

Table 2-1. PAD Description

PAD Number	Description	PAD Size (μm)
1	GND	95 × 95
2	RFIN	95 × 95
3	GND	95 × 95
4	VDA drain termination bypass	95 × 95
5	VDB drain termination bypass	95 × 95
6	GND	95 × 95
7	DC Det. Ref.	95 × 95
8	RF Det	95 × 95
9	GND	95 × 95
10	RFOUT	95 × 140
11	GND	95 × 95
12	VG2	95 × 95
13	VGA gate termination bypass	95 × 95
14	VGB gate termination bypass	95 × 95
15	GND	95 × 95
16	VGC gate termination bypass	95 × 95
17	VGD gate termination bypass	95 × 95
18	VGE gate termination bypass	95 × 95
19	GND	95 × 95

The following table shows the I/O description for the MMA085AA device.

Table 2-2. I/O Description

Pad Number	Pad Name	Pad Description
2	RF _{IN}	This pad RF/DC coupled to the FET gates and matched to 50 Ω .
10	RF _{OUT}	This pad is RF/DC coupled to the FET drains and matched to 50 Ω ; this terminal used for V _{DD} bias
4, 5	V _{DDA} , V _{DDB}	V _{DDA} , V _{DDB} low-frequency termination for drain ballast, DC coupled to the FET drains (this pads ARE NOT designed for V _{DD} bias)
7	V _{DREF}	Detector DC reference
8	V _{DET}	Detector output
12	V _{G2}	Access to gate 2 bias
13, 14	V _{GA} , V _{GB}	First gate low-frequency terminations DC Coupled to the gate 1 and used to set the die bias current
16, 17, 18	V _{GC} , V _{GD} , V _{GE}	Complementary low-frequency terminations for the gate 1, used to control low-frequency response slope
1, 3, 6, 9, 11, 15, 19	Ground	Ground connections used for die test purposes; DC/RF ground is using die backside metal

3. Application Circuit

The following diagram shows the application circuit schematic for the MMA085AA device.

Figure 3-1. Application Circuit Schematic





Figure 3-2. Die Test Circuit: Assembly Drawing

The following table shows the list of materials for the MMA085AA test circuit.

Table 3-1. List of Materials for Test Circuit

Reference	Part Number	Description
E16602B	MMA085AA	MMA085AA amplifier die
C1, C2, C3	160U02A102MT4W	Johnson dielectric, Cer. Cap 1 nF
S1, S2	E57311, E57312	Probe launchers

4. Ordering, Shipping, and Handling

4.1 Handling Recommendations

Gallium Arsenide Integrated Circuits are sensitive to electrostatic discharge (ESD) and can be damaged by static electricity. It is recommended to follow all procedures and guidelines outlined in the Microchip application note AN01: GaAs MMIC Handling and Die Attach Recommendations.

4.2 Ordering Information

For additional ordering information, contact your Microchip sales representative.

Part Number	Package
MMA085AA	Die

4.3 Packing Information

Standard Format
Gel Pack
50 Pieces per Pack

5. Revision History

The revision history describes the changes that were implemented in the document. The changes are listed by revision, starting with the most current publication.

Revision	Date	Description
A	09/2024	Document created.

Microchip Information

The Microchip Website

Microchip provides online support via our website at www.microchip.com/. This website is used to make files and information easily available to customers. Some of the content available includes:

- **Product Support** – Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- **General Technical Support** – Frequently Asked Questions (FAQs), technical support requests, online discussion groups, Microchip design partner program member listing
- **Business of Microchip** – Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

Product Change Notification Service

Microchip's product change notification service helps keep customers current on Microchip products. Subscribers will receive email notification whenever there are changes, updates, revisions or errata related to a specified product family or development tool of interest.

To register, go to www.microchip.com/pcn and follow the registration instructions.

Customer Support

Users of Microchip products can receive assistance through several channels:

- Distributor or Representative
- Local Sales Office
- Embedded Solutions Engineer (ESE)
- Technical Support

Customers should contact their distributor, representative or ESE for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in this document.

Technical support is available through the website at: www.microchip.com/support

Product Identification System

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

Microchip Devices Code Protection Feature

Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is “unbreakable”. Code protection is constantly evolving. Microchip is committed to continuously improving the code protection features of our products.

Legal Notice

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at www.microchip.com/en-us/support/design-help/client-support-services.

THIS INFORMATION IS PROVIDED BY MICROCHIP “AS IS”. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSEQUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP’S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer’s risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, CryptoMemory, CryptoRF, dsPIC, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, ClockWorks, The Embedded Control Solutions Company, EtherSynch, Flashtec, Hyper Speed Control, HyperLight Load, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, TimeCesium, TimeHub, TimePictra, TimeProvider, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, Clockstudio, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, EyeOpen, GridTime, IdealBridge, IGaT, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, IntelliMOS, Inter-Chip Connectivity, JitterBlocker, Knob-on-Display, MarginLink, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, mSiC, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICKit, PICtail, Power MOS IV, Power MOS 7, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SmartHLS, SMART-I.S., storClad, SQL, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, Trusted Time, TSHARC, Turing, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2024, Microchip Technology Incorporated and its subsidiaries. All Rights Reserved.

ISBN: 978-1-6683-0105-0

AMBA, Arm, Arm7, Arm7TDMI, Arm9, Arm11, Artisan, big.LITTLE, Cordio, CoreLink, CoreSight, Cortex, DesignStart, DynamIQ, Jazelle, Keil, Mali, Mbed, Mbed Enabled, NEON, POP, RealView, SecurCore, Socrates, Thumb, TrustZone, ULINK, ULINK2, ULINK-ME, ULINK-PLUS, ULINKpro, μ Vision, Versatile are trademarks or registered trademarks of Arm Limited (or its subsidiaries) in the US and/or elsewhere.

Quality Management System

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.

Worldwide Sales and Service

AMERICAS	ASIA/PACIFIC	ASIA/PACIFIC	EUROPE
Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: www.microchip.com/support Web Address: www.microchip.com	Australia - Sydney Tel: 61-2-9868-6733 China - Beijing Tel: 86-10-8569-7000 China - Chengdu Tel: 86-28-8665-5511 China - Chongqing Tel: 86-23-8980-9588 China - Dongguan Tel: 86-769-8702-9880 China - Guangzhou Tel: 86-20-8755-8029 China - Hangzhou Tel: 86-571-8792-8115 China - Hong Kong SAR Tel: 852-2943-5100 China - Nanjing Tel: 86-25-8473-2460 China - Qingdao Tel: 86-532-8502-7355 China - Shanghai Tel: 86-21-3326-8000 China - Shenyang Tel: 86-24-2334-2829 China - Shenzhen Tel: 86-755-8864-2200 China - Suzhou Tel: 86-186-6233-1526 China - Wuhan Tel: 86-27-5980-5300 China - Xian Tel: 86-29-8833-7252 China - Xiamen Tel: 86-592-2388138 China - Zhuhai Tel: 86-756-3210040	India - Bangalore Tel: 91-80-3090-4444 India - New Delhi Tel: 91-11-4160-8631 India - Pune Tel: 91-20-4121-0141 Japan - Osaka Tel: 81-6-6152-7160 Japan - Tokyo Tel: 81-3-6880-3770 Korea - Daegu Tel: 82-53-744-4301 Korea - Seoul Tel: 82-2-554-7200 Malaysia - Kuala Lumpur Tel: 60-3-7651-7906 Malaysia - Penang Tel: 60-4-227-8870 Philippines - Manila Tel: 63-2-634-9065 Singapore Tel: 65-6334-8870 Taiwan - Hsin Chu Tel: 886-3-577-8366 Taiwan - Kaohsiung Tel: 886-7-213-7830 Taiwan - Taipei Tel: 886-2-2508-8600 Thailand - Bangkok Tel: 66-2-694-1351 Vietnam - Ho Chi Minh Tel: 84-28-5448-2100	Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393 Denmark - Copenhagen Tel: 45-4485-5910 Fax: 45-4485-2829 Finland - Espoo Tel: 358-9-4520-820 France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79 Germany - Garching Tel: 49-8931-9700 Germany - Haan Tel: 49-2129-3766400 Germany - Heilbronn Tel: 49-7131-72400 Germany - Karlsruhe Tel: 49-721-625370 Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44 Germany - Rosenheim Tel: 49-8031-354-560 Israel - Hod Hasharon Tel: 972-9-775-5100 Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781 Italy - Padova Tel: 39-049-7625286 Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340 Norway - Trondheim Tel: 47-72884388 Poland - Warsaw Tel: 48-22-3325737 Romania - Bucharest Tel: 40-21-407-87-50 Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91 Sweden - Gothenberg Tel: 46-31-704-60-40 Sweden - Stockholm Tel: 46-8-5090-4654 UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820