# OSRAM LE A P1MQ

# Datasheet

**Published by ams-OSRAM AG**
Tobelbader Strasse 30, 8141 Premstaetten, Austria
Phone +43 3136 500-0
ams-osram.com
© All rights reserved


Downloaded from Arrow.com.

OSRAM

## OSRAM OSTAR™ Projection Power

# LE A P1MQ

OSRAM OSTAR Projection Power is a high luminance LED for projection applications.



## Applications

- Projection & display
- Visualization

## Features

- Package: OSTAR High Power Projection
- Chip technology: Thinfilm
- Typ. Radiation: 120° (Lambertian emitter)
- Color: $\lambda_{dom}$ = 613 nm (● amber)
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2)

## Ordering Information

| Type | Luminous Flux [1] $I_F$ = 6000 mA $\Phi_V$ | Ordering Code |
|---|---|---|
| LE A P1MQ-SQST-W2 | 1940 ... 2590 lm | Q65113A6957 |



Downloaded from Arrow.com.

## Maximum Ratings

| Parameter | Symbol | | Values |
|---|---|---|---|
| Storage Temperature | $T_{stg}$ | min.<br>max. | -40 °C<br>85 °C |
| Junction Temperature | $T_j$ | max. | 125 °C |
| Forward Current<br>$T_j = T_{j,max}$ | $I_F$ | min.<br>max. | 200 mA<br>8000 mA |
| Forward Current pulsed<br>D = 0.6; f = 240 Hz; $T_j = T_{j,max}$ | $I_{F\ pulse}$ | | 8000 mA |
| Surge Current<br>$t_P \leq 50$ µs; D = 0.1 ; $T_j = T_{j,max}$ | $I_{FS}$ | max. | 10000 mA |
| ESD withstand voltage<br>acc. to ANSI/ESDA/JEDEC JS-001 (HBM, Class 2) | $V_{ESD}$ | | 2 kV |
| Reverse current [2)] | $I_R$ | max. | 200 mA |
| Max. voltage difference anode-board, cathode-board | $\Delta V_{a-b}$, $\Delta V_{c-b}$ | max. | 40 V |



Downloaded from Arrow.com.

## Characteristics

$T_{Board}$ = 25 °C; $I_F$ = 6000 mA

| Parameter | Symbol | | Values |
|---|---|---|---|
| Peak Wavelength | $\lambda_{peak}$ | typ. | 620 nm |
| Dominant Wavelength [3] | $\lambda_{dom}$ | min.<br>typ.<br>max. | 609 nm<br>613 nm<br>618 nm |
| Spectral bandwidth at 50% $I_{rel,max}$ | $\Delta\lambda$ | typ. | 17 nm |
| Viewing angle at 50% $I_V$ | $2\varphi$ | typ. | 120 ° |
| Radiating surface | $A_{color}$ | typ. | 2.6 x 1.55 mm² |
| Partial Flux acc. CIE 127:2007 [4] | $\Phi_{E/V,\ 120°}$ | typ. | 0.77 |
| Forward Voltage [5] | $V_F$ | min.<br>typ.<br>max. | 4.8 V<br>5.8 V<br>7.0 V |
| Reverse voltage (ESD device) | $V_{R\ ESD}$ | min. | 45 V |
| Reverse voltage [2]<br>$I_R$ = 20 mA | $V_R$ | max. | 1.2 V |
| Real thermal resistance junction/board | $R_{thJB\ real}$ | typ. | 1.0 K / W |
| Electrical thermal resistance junction/board with efficiency $\eta_e$ = 22 % | $R_{thJB\ elec.}$ | typ. | 0.78 K / W |



Downloaded from Arrow.com.

## Brightness Groups

| Group | Luminous Flux [1] $I_F$ = 6000 mA min. $\Phi_V$ | Luminous Flux [1] $I_F$ = 6000 mA max. $\Phi_V$ |
|---|---|---|
| SQ | 1940 lm | 2100 lm |
| SR | 2100 lm | 2240 lm |
| SS | 2240 lm | 2400 lm |
| ST | 2400 lm | 2590 lm |

## Wavelength Groups

| Group | Dominant Wavelength [3] min. $\lambda_{dom}$ | Dominant Wavelength [3] max. $\lambda_{dom}$ |
|---|---|---|
| W | 609 nm | 612 nm |
| 2 | 612 nm | 618 nm |

## Group Name on Label

**Example: SQ-2**


| Brightness | Wavelength |
|---|---|
| SQ | 2 |



Downloaded from Arrow.com.


## Relative Spectral Emission [4)]

$\Phi_{rel} = f(\lambda)$; $I_F$ = 6000 mA; $T_J$ = 25 °C




## Radiation Characteristics [4)]

$I_{rel} = f(\varphi)$; $T_J$ = 25 °C







Downloaded from Arrow.com.

## Relative Partial Flux [4)]

$\Phi_v(2\varphi)/\Phi_v(180°) = f(\varphi)$; $T_J$ = 25 °C







Downloaded from Arrow.com.


## Forward current [4)]

$I_F = f(V_F)$; $T_J$ = 25 °C




## Relative Luminous Flux [4)]

$\Phi_v/\Phi_v(6000\ mA) = f(I_F)$; $T_J$ = 25 °C







Downloaded from Arrow.com.


## Forward Voltage [4)]

$\Delta V_F = V_F - V_F(25\ °C) = f(T_j);\ I_F = 6000\ mA$





## Relative Luminous Flux [4)]

$\Phi_v/\Phi_v(25\ °C) = f(T_j);\ I_F = 6000\ mA$




## Dominant Wavelength [4)]


$\Delta\lambda_{dom} = \lambda_{dom} - \lambda_{dom}(25\ °C) = f(T_j);\ I_F = 6000\ mA$






Downloaded from Arrow.com.

## Dimensional Drawing [6)]




## Further Information:

**Approximate Weight:** 5,000.0 mg

**ESD advice:** The device is protected by ESD device which is connected in parallel to the Chip.

**Notes:** For superior solder joint connectivity results we recommend soldering under standard nitrogen atmosphere.
Package not suitable for any kind of wet cleaning or ultrasonic cleaning.


**Connector:** Molex Pico-SPOX™ Wire-to-Board Header, Part Number 87438-1043

**Recommended mating connector:** Molex Pico-SPOX™ Wire-to-Board Housing, Part Number 87439-1000
Crimp Terminal, Part Number 87421-0000



Downloaded from Arrow.com.

## Electrical Internal Circuit





Pins 1a: NTC/Substrate potential, isolated from Cathode and Anode
Pins 1b: NTC
Pins 2: Anode
Pins 3: Cathode



Downloaded from Arrow.com.

## Reflow Soldering Profile

Product complies to MSL Level 2 acc. to JEDEC J-STD-020E




| Profile Feature | Symbol | Pb-Free (SnAgCu) Assembly | | | Unit |
|---|---|---|---|---|---|
| | | Minimum | Recommendation | Maximum | |
| Ramp-up rate to preheat*)<br>25 °C to 150 °C | | | 2 | 3 | K/s |
| Time $t_S$<br>$T_{Smin}$ to $T_{Smax}$ | $t_S$ | 60 | 100 | 120 | s |
| Ramp-up rate to peak*)<br>$T_{Smax}$ to $T_P$ | | | 2 | 3 | K/s |
| Liquidus temperature | $T_L$ | | 217 | | °C |
| Time above liquidus temperature | $t_L$ | | 80 | 100 | s |
| Peak temperature | $T_P$ | | 245 | 260 | °C |
| Time within 5 °C of the specified peak temperature $T_P$ - 5 K | $t_P$ | 10 | 20 | 30 | s |
| Ramp-down rate*<br>$T_P$ to 100 °C | | | 3 | 6 | K/s |
| Time<br>25 °C to $T_P$ | | | | 480 | s |


All temperatures refer to the center of the package, measured on the top of the component
* slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range



Downloaded from Arrow.com.

## Tray [6)]

38 pieces per tray





C63062-A4389-B10-01




Downloaded from Arrow.com.

## Barcode-Product-Label (BPL)




OHA04563

## Barcode-Tray-Label (BTL)





OHA02684_1



Downloaded from Arrow.com.

## Schematic Transportation Box [6)]




## Dimensions of Transportation Box

| Width | Length | Height |
|---|---|---|
| 333 ± 5 mm | 218 ±5 mm | 28 ± 5 mm |
| 337 ± 5 mm | 218 ±5 mm | 63 ± 5 mm |



Downloaded from Arrow.com.

## Data Matrix Code Description

The Data Matrix Code bin information is Laser marked during testing

Content: aaaa@bbbb@ccc@ddddd@eeeee

Data Matrix Code Type: ECC200

| | |
|---|---|
| a = Luminous Flux (Phiv) [lm] or Radiant Flux (Phie) [W] | (example: 3306) |
| b = Forward Voltage (Vf) [V] | (example: 3.46) |
| c = Wavelength (Ldom) [nm] | (example: 618) |
| d = Color Coordinate Cx | (example: 0.321) |
| e = Color Coordinate Cy | (example: 0.641) |

@: Seperator = Blank



Downloaded from Arrow.com.

## Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet fall into the class **exempt group (exposure time 10000 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit https://ams-osram.com/support/application-notes



Downloaded from Arrow.com.

# Disclaimer

### Attention please!

The information describes the type of component and shall not be considered as assured characteristics.
Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.
For information on the types in question please contact our Sales Organization.
If printed or downloaded, please find the latest version on our website.

### Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

### Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.
Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/ applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.



Downloaded from Arrow.com.

## Glossary

1) **Brightness:** Brightness values are measured during a current pulse of typically 1 ms, with an internal reproducibility of ±8 % and an expanded uncertainty of ±11 % (acc. to GUM with a coverage factor of k = 3).

2) **Reverse Operation:** This product is intended to be operated applying a forward current within the specified range. Applying any continuous reverse bias or forward bias below the voltage range of light emission shall be avoided because it may cause migration which can change the electro-optical characteristics or damage the LED.

3) **Wavelength:** The wavelength is measured at a current pulse of typically 1 ms, with an internal reproducibility of ±0.5 nm and an expanded uncertainty of ±1 nm (acc. to GUM with a coverage factor of k = 3).

4) **Typical Values:** Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.

5) **Forward Voltage:** The forward voltage is measured during a current pulse of typically 1 ms, with an internal reproducibility of ±0.05 V and an expanded uncertainty of ±0.1 V (acc. to GUM with a coverage factor of k = 3).

6) **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.



Downloaded from Arrow.com.

## Revision History

| Version | Date | Change |
|---|---|---|
| 1.0 | 2019-09-18 | Initial Version |
| 1.1 | 2019-10-08 | Characteristics |
| 1.2 | 2020-02-18 | Characteristics |
| 1.3 | 2020-07-08 | Ordering Information<br>Brightness Groups |
| 1.4 | 2021-02-15 | Ordering Information<br>Brightness Groups<br>Characteristics<br>Dimensional Drawing<br>Maximum Ratings |
| 1.5 | 2024-07-02 | Ordering Information<br>Characteristics<br>Electro - Optical Characteristics (Diagrams)<br>Dimensional Drawing<br>Electrical Internal Circuit |
| 1.6 | 2025-06-12 | Brand |
| 1.7 | 2026-01-29 | Dimensional Drawing |
| 1.8 | 2026-09-11 | Electro - Optical Characteristics (Diagrams) |



Downloaded from Arrow.com.

EU RoHS and China RoHS compliant product
此产品符合欧盟 RoHS 指令的要求；
按照中国的相关法规和标准，
不含有毒有害物质或元素。

**Published by ams-OSRAM AG**
Tobelbader Strasse 30, 8141 Premstaetten, Austria
Phone +43 3136 500-0
ams-osram.com
© All rights reserved

Downloaded from Arrow.com.