

1194398

https://www.phoenixcontact.com/us/products/1194398

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect universal, Vehicle charging inlet, for charging with alternating current (AC) and with direct current (DC), CCS type 1, IEC 62196-2, IEC 62196-3, 125 A / 1000 V (DC), 48 A / 250 V (AC), Single wires, length: 2 m, locking actuator: 12 V, 4-pos., Front and rear mounting, M6, housing: black, A protective cap is supplied as standard for the DC and AC contacts.

### Product description

Vehicle charging inlet for charging with alternating current (AC) and direct current (DC), compatible with type 1 AC and CCS vehicle charging connectors (EVSE), for installation in electric vehicles (EV).

### Your advantages

- · Complete product range
- · Uniform, space-saving dimensions for the installation space and the screw connection points of all Phoenix Contact vehicle charging inlets
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- · Integrated interlock during charging
- · Manual emergency release of the locking actuator
- · Protected and sealed against dirt and water with a high degree of protection

#### Commercial data

Item number	1194398
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	EM01
Product key	XWCAIB
GTIN	4063151249267
Weight per piece (including packing)	4,170 g
Weight per piece (excluding packing)	4,170 g
Customs tariff number	85444290
Country of origin	PL



1194398

https://www.phoenixcontact.com/us/products/1194398

### Technical data

#### Notes

	General	A protective cap is supplied as standard for the DC and AC contacts.
Pr	oduct properties	
	Product type	Vehicle charging inlet
	Product family	CHARX connect universal
	Application	for charging with alternating current (AC) and with direct current (DC)
		for installation in electric vehicles (EV)
	Technology	Combined Charging System
	Charging standard	CCS type 1
	Charging mode	Mode 2, 3, 4
	Data management status	
	Article revision	05

### Electrical properties

Type of signal transmission	Pulse width modulation with modulated Powerline communication in accordance with ISO/IEC 15118 / DIN SPEC 70121
Note on the connection method	Crimp connection, cannot be disconnected
Insulation resistance	> 200 MΩ
Coding	$2.7~\text{k}\Omega$ (between PE and CS)
Temperature measurement	DC contacts: 2x PT1000 (DIN EN 60751)
Temperature monitoring	AC contacts: PTC chain (DIN EN 60738-1)
Type of charging current	AC single-phase
Charging power	12 kW
Charging current	48 A
Type of charging current	DC
Charging power	125 kW
Charging current	125 A

#### Power contact

Number	5 (L1, N, PE, DC+, DC-)
Rated voltage	250 V AC
	1000 V DC
Rated current	48 A AC
	125 A DC

#### Signal contact

Number	2 (CP, CS)
Rated voltage	30 V AC
Rated current	2 A



1194398

https://www.phoenixcontact.com/us/products/1194398

Temperature	concore	(DTC	chain)
remberature	sensors	(PIC	chain

Sensor type	PTC chain
Standards/regulations	DIN EN 60738-1
Attachment point	Sensor for the AC contacts
Measuring range_resistance	790.00 Ω 1420.00 Ω
Resistance	max. 1200 Ω ±5 K
Ambient temperature	-40 °C 130 °C (Operation)

### Temperature sensors (Pt 1000)

Sensor type	Pt 1000
Standards/regulations	DIN EN 60751
Attachment point	2 sensors for the DC contacts

### Locking actuator

Operating voltage	12 V
Note number of positions	4-pos.
Position of the locking actuator	top center

#### Locking actuator

Operating voltage	12 V
Note number of positions	4-pos.
Position of the locking actuator	top center
Possible power supply range at the motor	9 V 16 V
Maximum voltage for locking detection	12 V
Typical motor current for locking	0.25 A
Reverse current of the motor	max. 1.5 A
Max. dwell time with reverse current	1 s
Recommended adaptation time	600 ms
Pause time after entry or exit path	3 s
Service life insertion cycles	> 10000 load cycles
Lock recognition	available
Mechanical emergency release	available
Ambient temperature (operation)	-40 °C 80 °C

### **Dimensions**

Width	117.6 mm
Height	90 mm
Depth	117.6 mm

### Material specifications

Color (Housing)	black (9005)
Color (Mating face)	black (9005)
Material (Housing)	Plastic
Material (Contact surface)	Silver



1194398

https://www.phoenixcontact.com/us/products/1194398

### Cable/line

Jabic/iiiic	
Cable length	2 m
Cable type	Single wires
Single wire, cross section	35.00 mm²
Single-core wires for AC	
Cable length	2 m
Cable structure	2 x 6 mm²
Single wire, material	Silicone
Single wire, color	OG
External cable diameter	12.60 mm ±0.2 mm
Cable resistance	≤ 3.2 Ω/km
Single-core wires for DC	
Cable length	2 m
Cable structure	2 x 35 mm²
Single wire, material	Silicone
Single wire, color	OG
External cable diameter	14.10 mm ±0.3 mm
Cable resistance	≤ 0.527 Ω/km
Single-core wire for PE	
Cable length	2 m
Cable structure	1 x 25 mm²
Single wire, material	Silicone
Single wire, color	GN/YE
External cable diameter	8.60 mm ±0.1 mm
Cable resistance	≤ 0.743 Ω/km
Single-core wires for locking actuator	
Cable length	1.5 m
Cable structure	4 x 0.5 mm²
Single wire, material	PVC
Single wire, color	BU/RD, BU/GN, BU/YE, BU/BN
External cable diameter	1.60 mm ±0.20 mm
Cable resistance	≤ 37.1 Ω/m
Single-core wires for PTC temperature sensors	
Cable length	1 m
Cable structure	5 x 0,5 mm <sup>2</sup>
Single wire, color	BN/GY
	BN/YE/GN
External cable diameter	
External cable diameter  Cable resistance	1.60 mm ±0.20 mm ≤ 37.1 Ω/m

Oct 16, 2024, 12:27 PM Page 4 (17)

Single-core wires for Pt 1000 temperature sensors



1194398

https://www.phoenixcontact.com/us/products/1194398

Cable length	1 m	
Cable structure	3 x 0.5 mm²	
Single wire, material	PVC	
Single wire, color	BN	
	GN	
	YE	
External cable diameter	1.60 mm ±0.20 mm	
Cable resistance	≤ 37.1 Ω/m	
Single-core wires for communication		
Cable length	1 m	
Cable structure	2 x 0.5 mm²	

**PVC** 

BK WH

1.60 mm ±0.20 mm

≤ 37.1 Ω/m

### Cable resistance Mechanical properties

Single wire, material
Single wire, color

External cable diameter

#### Mechanical data

Insertion/withdrawal cycles	> 10000
Insertion force	< 100 N
Withdrawal force	< 100 N

### Environmental and real-life conditions

#### Ambient conditions

7 Million Continuono	
Degree of protection (Vehicle charging inlet)	IP55 (plugged in; when plugged in and ready to operate, the degree of protection is only ensued if both plug-in components are original products from Phoenix Contact or suitable standard-compliant products)
	IP67 (Inner area of vehicle charging inlet)
Ambient temperature (operation)	-40 °C 40 °C (60°C, maximum (current reduction required, observe the DC contact temperature limit value of 90°C))
Ambient temperature (storage/transport)	-40 °C 85 °C
Altitude	4000 m (above sea level)

### Standards and regulations

#### Standards

Standards/regulations	IEC 62196-2
	IEC 62196-3
	SAE J1772

### Mounting

3	
Mounting type	Front and rear mounting (0 to 90 degree frontal inclination
	possible)



1194398

https://www.phoenixcontact.com/us/products/1194398


Mounting hole diameter	6.70 mm (ø)
Fixing screws	M6
Screws included in the scope of delivery	none




1194398

https://www.phoenixcontact.com/us/products/1194398

### Drawings



Reference points for measuring the line length




The Combined Charging System (CCS) principle - standard-compliant charging system for electric vehicles, which supports both conventional AC charging and fast DC charging. Both Vehicle Connectors fit into the CCS Vehicle Inlet.



1194398

https://www.phoenixcontact.com/us/products/1194398

### Schematic diagram




Operating instructions




1194398

https://www.phoenixcontact.com/us/products/1194398

### Schematic diagram



Temperature sensor technology resistance range at AC contacts




Pt 1000 characteristic curve at an ambient temperature of 25°C for temperature measurement at the DC contacts



1194398

https://www.phoenixcontact.com/us/products/1194398

### Dimensional drawing




Dimensional drawing



1194398

https://www.phoenixcontact.com/us/products/1194398




**Detection for Vehicle Connector** 



1194398

https://www.phoenixcontact.com/us/products/1194398




Locking states of the locking actuator




1194398

https://www.phoenixcontact.com/us/products/1194398



Pin assignment of vehicle charging inlets

### Schematic diagram




Block diagram of the locking actuator



1194398

https://www.phoenixcontact.com/us/products/1194398

### Connection diagram



Installation positions



1194398

https://www.phoenixcontact.com/us/products/1194398

### **Approvals**

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1194398



cULus Recognized

Approval ID: E473195-20210730



1194398

https://www.phoenixcontact.com/us/products/1194398

### Classifications

### **ECLASS**

ECLASS-11.0	27144706
ECLASS-12.0	27144706
ECLASS-13.0	27144706

### **ETIM**

ETIM 9.0	EC002898



1194398

https://www.phoenixcontact.com/us/products/1194398

### Environmental product compliance

#### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-l
China RoHS	
Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	2-ethylhexyl 10-ethyl-4,4-dioctyl-7-oxo-8-oxa-3,5-dithia-4-stannatetradecanoate (DOTE)(CAS: 15571-58-1)
	Lead(CAS: 7439-92-1)
	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	9621e237-0c80-4368-837c-970e0e1e406e

Phoenix Contact 2024 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com