

# COMLINEAR® CLC1001

## Ultra-Low Noise Amplifier

### FEATURES

- 0.6 nV/√Hz input voltage noise
- 1mV maximum input offset voltage
- 2.1GHz gain bandwidth product
- Minimum stable gain of 10
- 410V/μs slew rate
- 130mA output current
- -40°C to +125°C operating temperature range
- Fully specified at 5V and ±5V supplies
- CLC1001: Lead-free SOT23-6, SOIC-8

### APPLICATIONS

- Transimpedance amplifiers
- Pre-amplifier
- Low noise signal processing
- Medical instrumentation
- Probe equipment
- Test equipment
- Ultrasound channel amplifier


### General Description

The COMLINEAR CLC1001(single) is a high-performance, voltage feedback amplifier with ultra-low input voltage noise, 0.6nV/√Hz. The CLC1001 provides 2.1GHz gain bandwidth product and 410V/μs slew rate making it well suited for high-speed data acquisition systems requiring high levels of sensitivity and signal integrity. This COMLINEAR high-performance amplifier also offers low input offset voltage.

The COMLINEAR CLC1001 is designed to operate from 4V to 12V supplies. It consumes only 12.5mA of supply current per channel and offers a power saving disable pin that disables the amplifier and decreases the supply current to below 225μA. The CLC1001 amplifier operates over the extended temperature range of -40°C to +125°C.

If a lower minimum stable gain is required, the CLC1002 offers a minimum stable gain of 5.

### Typical Application - Single Supply Photodiode Amplifier




### Ordering Information

| Part Number  | Package | Pb-Free | RoHS Compliant | Operating Temperature Range | Packaging Method |
|--------------|---------|---------|----------------|-----------------------------|------------------|
| CLC1001IST6X | SOT23-6 | Yes     | Yes            | -40°C to +125°C             | Reel             |
| CLC1001ISO8X | SOIC-8  | Yes     | Yes            | -40°C to +125°C             | Reel             |
| CLC1001ISO8  | SOIC-8  | Yes     | Yes            | -40°C to +125°C             | Rail             |

Moisture sensitivity level for all parts is MSL-1.




SOT23 Pin Configuration



SOT23 Pin Assignments

| Pin No. | Pin Name | Description                                                                                                     |
|---------|----------|-----------------------------------------------------------------------------------------------------------------|
| 1       | OUT      | Output                                                                                                          |
| 2       | -VS      | Negative supply                                                                                                 |
| 3       | +IN      | Positive input                                                                                                  |
| 4       | -IN      | Negative input                                                                                                  |
| 5       | DIS      | Disable. Enabled if pin is left floating or pulled above VON, disabled if pin is grounded or pulled below VOFF. |
| 6       | +VS      | Positive supply                                                                                                 |

SOIC Pin Configuration



SOIC Pin Assignments

| Pin No. | Pin Name | Description                                                                                                     |
|---------|----------|-----------------------------------------------------------------------------------------------------------------|
| 1       | NC       | No connect                                                                                                      |
| 2       | -IN1     | Negative input                                                                                                  |
| 3       | +IN1     | Positive input                                                                                                  |
| 4       | -VS      | Negative supply                                                                                                 |
| 5       | NC       | No connect                                                                                                      |
| 6       | OUT      | Output                                                                                                          |
| 7       | +VS      | Positive supply                                                                                                 |
| 8       | DIS      | Disable. Enabled if pin is left floating or pulled above VON, disabled if pin is grounded or pulled below VOFF. |



## Absolute Maximum Ratings

The safety of the device is not guaranteed when it is operated above the "Absolute Maximum Ratings". The device should not be operated at these "absolute" limits. Adhere to the "Recommended Operating Conditions" for proper device function. The information contained in the Electrical Characteristics tables and Typical Performance plots reflect the operating conditions noted on the tables and plots.

| Parameter           | Min           | Max           | Unit |
|---------------------|---------------|---------------|------|
| Supply Voltage      | 0             | 14            | V    |
| Input Voltage Range | $-V_S - 0.5V$ | $+V_S + 0.5V$ | V    |

## Reliability Information

| Parameter                         | Min | Typ | Max | Unit |
|-----------------------------------|-----|-----|-----|------|
| Junction Temperature              |     |     | 150 | °C   |
| Storage Temperature Range         | -65 |     | 150 | °C   |
| Lead Temperature (Soldering, 10s) |     |     | 260 | °C   |
| Package Thermal Resistance        |     |     |     |      |
| 6-Lead SOT23                      |     | 177 |     | °C/W |
| 8-Lead SOIC                       |     | 100 |     | °C/W |

Notes:

Package thermal resistance ( $\theta_{JA}$ ), JEDEC standard, multi-layer test boards, still air.

## ESD Protection

| Product                    | SOT23-6 |
|----------------------------|---------|
| Human Body Model (HBM)     | 2kV     |
| Charged Device Model (CDM) | 2kV     |

## Recommended Operating Conditions

| Parameter                   | Min | Typ | Max  | Unit |
|-----------------------------|-----|-----|------|------|
| Operating Temperature Range | -40 |     | +125 | °C   |
| Supply Voltage Range        | 4   |     | 12   | V    |



## Electrical Characteristics at +5V

$T_A = 25^\circ\text{C}$ ,  $V_S = +5\text{V}$ ,  $R_f = 200\Omega$ ,  $R_L = 500\Omega$  to  $V_S/2$ ,  $G = 10$ ; unless otherwise noted.

| Symbol                    | Parameter                        | Conditions                                                             | Min                                | Typ        | Max | Units                        |
|---------------------------|----------------------------------|------------------------------------------------------------------------|------------------------------------|------------|-----|------------------------------|
| Frequency Domain Response |                                  |                                                                        |                                    |            |     |                              |
| GBWP                      | -3dB Gain Bandwidth Product      | $G = +40$ , $V_{OUT} = 0.2V_{pp}$                                      |                                    | 2000       |     | MHz                          |
| $BW_{SS}$                 | -3dB Bandwidth                   | $G = +10$ , $V_{OUT} = 0.2V_{pp}$                                      |                                    | 265        |     | MHz                          |
| $BW_{LS}$                 | Large Signal Bandwidth           | $G = +10$ , $V_{OUT} = 2V_{pp}$                                        |                                    | 105        |     | MHz                          |
| $BW_{0.1dBSS}$            | 0.1dB Gain Flatness Small Signal | $G = +10$ , $V_{OUT} = 0.2V_{pp}$                                      |                                    | 37         |     | MHz                          |
| $BW_{0.1dBLS}$            | 0.1dB Gain Flatness Large Signal | $G = +10$ , $V_{OUT} = 2V_{pp}$                                        |                                    | 36         |     | MHz                          |
| Time Domain Response      |                                  |                                                                        |                                    |            |     |                              |
| $t_R, t_F$                | Rise and Fall Time               | $V_{OUT} = 1\text{V}$ step; (10% to 90%)                               |                                    | 2.4        |     | ns                           |
| $t_S$                     | Settling Time to 0.1%            | $V_{OUT} = 1\text{V}$ step                                             |                                    | 11         |     | ns                           |
| OS                        | Overshoot                        | $V_{OUT} = 1\text{V}$ step                                             |                                    | 6          |     | %                            |
| SR                        | Slew Rate                        | 4V step                                                                |                                    | 360        |     | V/ $\mu\text{s}$             |
| Distortion/Noise Response |                                  |                                                                        |                                    |            |     |                              |
| HD2                       | 2nd Harmonic Distortion          | $1V_{pp}$ , 10MHz                                                      |                                    | -80        |     | dBc                          |
| HD3                       | 3rd Harmonic Distortion          | $1V_{pp}$ , 10MHz                                                      |                                    | -83        |     | dBc                          |
| THD                       | Total Harmonic Distortion        | $1V_{pp}$ , 10MHz                                                      |                                    | -79        |     | dB                           |
| $e_n$                     | Input Voltage Noise              | > 100kHz                                                               |                                    | 0.6        |     | nV/ $\sqrt{\text{Hz}}$       |
| $i_n$                     | Input Current Noise              | > 100kHz                                                               |                                    | 4.2        |     | pA/ $\sqrt{\text{Hz}}$       |
| DC Performance            |                                  |                                                                        |                                    |            |     |                              |
| $V_{IO}$                  | Input Offset Voltage             |                                                                        |                                    | 0.1        |     | mV                           |
| $dV_{IO}$                 | Average Drift                    |                                                                        |                                    | 2.7        |     | $\mu\text{V}/^\circ\text{C}$ |
| $I_b$                     | Input Bias Current               |                                                                        |                                    | 28         |     | $\mu\text{A}$                |
| $dI_b$                    | Average Drift                    |                                                                        |                                    | 45         |     | nA/ $^\circ\text{C}$         |
| $I_o$                     | Input Offset Current             |                                                                        |                                    | 0.5        |     | $\mu\text{A}$                |
| PSRR                      | Power Supply Rejection Ratio     | DC                                                                     |                                    | 83         |     | dB                           |
| $A_{OL}$                  | Open-Loop Gain                   | $V_{OUT} = V_S / 2$                                                    |                                    | 82         |     | dB                           |
| $I_S$                     | Supply Current                   | per channel                                                            |                                    | 12         |     | mA                           |
| Disable Characteristics   |                                  |                                                                        |                                    |            |     |                              |
| $t_{ON}$                  | Turn On Time                     | 1V step, 1% settling                                                   |                                    | 100        |     | ns                           |
| $t_{OFF}$                 | Turn Off Time                    |                                                                        |                                    | 900        |     | ns                           |
| $OFF_{ISO}$               | Off Isolation                    | $2V_{pp}$ , 5MHz                                                       |                                    | 80         |     | dB                           |
| $OFFC_{OUT}$              | Off Output Capacitance           |                                                                        |                                    | 5.7        |     | pF                           |
| $V_{OFF}$                 | Power Down Voltage               | Disabled if $\overline{DIS}$ pin is grounded or pulled below $V_{OFF}$ | Disabled if $\overline{DIS} < 1.5$ |            |     | V                            |
| $V_{ON}$                  | Enable Voltage                   | Enabled if $\overline{DIS}$ pin is floating or pulled above $V_{ON}$   | Enabled if $\overline{DIS} > 3$    |            |     | V                            |
| $I_{SD}$                  | Disable Supply Current           | No Load, $\overline{DIS}$ pin tied to ground                           |                                    | 130        |     | $\mu\text{A}$                |
| Input Characteristics     |                                  |                                                                        |                                    |            |     |                              |
| $R_{IN}$                  | Input Resistance                 | Non-inverting                                                          |                                    | 2.6        |     | M $\Omega$                   |
| $C_{IN}$                  | Input Capacitance                |                                                                        |                                    | 1.6        |     | pF                           |
| CMIR                      | Common Mode Input Range          |                                                                        |                                    | 0.8 to 5.1 |     | V                            |
| CMRR                      | Common Mode Rejection Ratio      | DC, $V_{cm} = 1.5\text{V}$ to 4V                                       |                                    | 85         |     | dB                           |
| Output Characteristics    |                                  |                                                                        |                                    |            |     |                              |
| $V_{OUT}$                 | Output Voltage Swing             | $R_L = 500\Omega$                                                      |                                    | 0.93 to 4  |     | V                            |
|                           |                                  | $R_L = 2k\Omega$                                                       |                                    | 0.9 to 4.1 |     | V                            |
| $I_{OUT}$                 | Output Current                   |                                                                        |                                    | $\pm 130$  |     | mA                           |
| $I_{SC}$                  | Short-Circuit Output Current     | $V_{OUT} = V_S / 2$                                                    |                                    | $\pm 150$  |     | mA                           |

### Notes:

- 100% tested at  $25^\circ\text{C}$



## Electrical Characteristics at $\pm 5V$

$T_A = 25^\circ C$ ,  $V_S = \pm 5V$ ,  $R_f = 200\Omega$ ,  $R_L = 500\Omega$ ,  $G = 10$ ; unless otherwise noted.

| Symbol                    | Parameter                                   | Conditions                                                             | Min                                | Typ         | Max | Units            |
|---------------------------|---------------------------------------------|------------------------------------------------------------------------|------------------------------------|-------------|-----|------------------|
| Frequency Domain Response |                                             |                                                                        |                                    |             |     |                  |
| GBWP                      | -3dB Gain Bandwidth Product                 | $G = +40$ , $V_{OUT} = 0.2V_{pp}$                                      |                                    | 2100        |     | MHz              |
| $BW_{SS}$                 | -3dB Bandwidth                              | $G = +10$ , $V_{OUT} = 0.2V_{pp}$                                      |                                    | 284         |     | MHz              |
| $BW_{LS}$                 | Large Signal Bandwidth                      | $G = +10$ , $V_{OUT} = 2V_{pp}$                                        |                                    | 117         |     | MHz              |
| $BW_{0.1dBSS}$            | 0.1dB Gain Flatness Small Signal            | $G = +10$ , $V_{OUT} = 0.2V_{pp}$                                      |                                    | 42          |     | MHz              |
| $BW_{0.1dBLS}$            | 0.1dB Gain Flatness Large Signal            | $G = +10$ , $V_{OUT} = 2V_{pp}$                                        |                                    | 47          |     | MHz              |
| Time Domain Response      |                                             |                                                                        |                                    |             |     |                  |
| $t_R$ , $t_F$             | Rise and Fall Time                          | $V_{OUT} = 1V$ step; (10% to 90%)                                      |                                    | 2.2         |     | ns               |
| $t_S$                     | Settling Time to 0.1%                       | $V_{OUT} = 1V$ step                                                    |                                    | 11          |     | ns               |
| OS                        | Overshoot                                   | $V_{OUT} = 1V$ step                                                    |                                    | 3           |     | %                |
| SR                        | Slew Rate                                   | 4V step                                                                |                                    | 410         |     | V/ $\mu s$       |
| Distortion/Noise Response |                                             |                                                                        |                                    |             |     |                  |
| HD2                       | 2nd Harmonic Distortion                     | $2V_{pp}$ , 10MHz                                                      |                                    | -81         |     | dBc              |
| HD3                       | 3rd Harmonic Distortion                     | $2V_{pp}$ , 10MHz                                                      |                                    | -75         |     | dBc              |
| THD                       | Total Harmonic Distortion                   | $2V_{pp}$ , 5MHz                                                       |                                    | -74         |     | dB               |
| $e_n$                     | Input Voltage Noise                         | > 100kHz                                                               |                                    | 0.6         |     | nV/ $\sqrt{Hz}$  |
| $i_n$                     | Input Current Noise                         | > 100kHz                                                               |                                    | 4.2         |     | pA/ $\sqrt{Hz}$  |
| DC Performance            |                                             |                                                                        |                                    |             |     |                  |
| $V_{IO}$                  | Input Offset Voltage <sup>(1)</sup>         |                                                                        | -1                                 | 0.35        | 1   | mV               |
| $dV_{IO}$                 | Average Drift                               |                                                                        |                                    | 4.4         |     | $\mu V/^\circ C$ |
| $I_b$                     | Input Bias Current <sup>(1)</sup>           |                                                                        | -60                                | 30          | 60  | $\mu A$          |
| $dI_b$                    | Average Drift                               |                                                                        |                                    | 44          |     | nA/ $^\circ C$   |
| $I_o$                     | Input Offset Current                        |                                                                        |                                    | 0.8         | 6   | $\mu A$          |
| PSRR                      | Power Supply Rejection Ratio <sup>(1)</sup> | DC                                                                     | 78                                 | 83          |     | dB               |
| $A_{OL}$                  | Open-Loop Gain <sup>(1)</sup>               | $V_{OUT} = V_S / 2$                                                    | 74                                 | 83          |     | dB               |
| $I_S$                     | Supply Current <sup>(1)</sup>               | per channel                                                            |                                    | 12.5        | 16  | mA               |
| Disable Characteristics   |                                             |                                                                        |                                    |             |     |                  |
| $t_{ON}$                  | Turn On Time                                | 1V step, 1% settling                                                   |                                    | 125         |     | ns               |
| $t_{OFF}$                 | Turn Off Time                               |                                                                        |                                    | 840         |     | ns               |
| $OFF_{ISO}$               | Off Isolation                               | $2V_{pp}$ , 5MHz                                                       |                                    | 80          |     | dB               |
| $OFFC_{OUT}$              | Off Output Capacitance                      |                                                                        |                                    | 5.6         |     | pF               |
| $V_{OFF}$                 | Power Down Voltage                          | Disabled if $\overline{DIS}$ pin is grounded or pulled below $V_{OFF}$ | Disabled if $\overline{DIS} < 1.3$ |             |     | V                |
| $V_{ON}$                  | Enable Voltage                              | Enabled if $\overline{DIS}$ pin is floating or pulled above $V_{ON}$   | Enabled if $\overline{DIS} > 3$    |             |     | V                |
| $I_{SD}$                  | Disable Supply Current <sup>(1)</sup>       | No Load, $\overline{DIS}$ pin tied to ground                           |                                    | 180         | 225 | $\mu A$          |
| Input Characteristics     |                                             |                                                                        |                                    |             |     |                  |
| $R_{IN}$                  | Input Resistance                            | Non-inverting                                                          |                                    | 4           |     | M $\Omega$       |
| $C_{IN}$                  | Input Capacitance                           |                                                                        |                                    | 1.5         |     | pF               |
| CMIR                      | Common Mode Input Range                     |                                                                        |                                    | -4.3 to 5.1 |     | V                |
| CMRR                      | Common Mode Rejection Ratio <sup>(1)</sup>  | DC, $V_{cm} = -3.5V$ to 4V                                             | 75                                 | 90          |     | dB               |
| Output Characteristics    |                                             |                                                                        |                                    |             |     |                  |
| $V_{OUT}$                 | Output Voltage Swing                        | $R_L = 500\Omega$ <sup>(1)</sup>                                       | -3.8                               | $\pm 4$     | 3.8 | V                |
|                           |                                             | $R_L = 2k\Omega$                                                       |                                    | $\pm 4$     |     | V                |
| $I_{OUT}$                 | Output Current                              |                                                                        |                                    | $\pm 130$   |     | mA               |
| $I_{SC}$                  | Short-Circuit Output Current                | $V_{OUT} = V_S / 2$                                                    |                                    | $\pm 160$   |     | mA               |

### Notes:


1. 100% tested at  $25^\circ C$




## Typical Performance Characteristics

$T_A = 25^\circ\text{C}$ ,  $V_S = \pm 5\text{V}$ ,  $R_f = 200\Omega$ ,  $R_L = 500\Omega$ ,  $G = 10$ ; unless otherwise noted.


### Non-Inverting Frequency Response




### Inverting Frequency Response




### Frequency Response vs. $C_L$




### Frequency Response vs. $R_L$



### Frequency Response vs. $V_{OUT}$



### -3dB Bandwidth vs. Output Voltage







## Typical Performance Characteristics

$T_A = 25^\circ\text{C}$ ,  $V_S = \pm 5\text{V}$ ,  $R_f = 200\Omega$ ,  $R_L = 500\Omega$ ,  $G = 10$ ; unless otherwise noted.


Non-Inverting Frequency Response at  $V_S = 5\text{V}$




Inverting Frequency Response at  $V_S = 5\text{V}$




Frequency Response vs.  $C_L$  at  $V_S = 5\text{V}$




Frequency Response vs.  $R_L$  at  $V_S = 5\text{V}$



Frequency Response vs.  $V_{OUT}$  at  $V_S = 5\text{V}$



-3dB Bandwidth vs. Output Voltage at  $V_S = 5\text{V}$







## Typical Performance Characteristics - Continued

$T_A = 25^\circ\text{C}$ ,  $V_S = \pm 5\text{V}$ ,  $R_f = 200\Omega$ ,  $R_L = 500\Omega$ ,  $G = 10$ ; unless otherwise noted.


Input Voltage Noise




Input Voltage Noise at  $V_S = 5\text{V}$




Input Voltage Noise (>10kHz)



Input Voltage Noise at  $V_S = 5\text{V}$  (>10kHz)



$R_{OUT}$  vs. Frequency







## Typical Performance Characteristics - Continued

$T_A = 25^\circ\text{C}$ ,  $V_S = \pm 5\text{V}$ ,  $R_f = 200\Omega$ ,  $R_L = 500\Omega$ ,  $G = 10$ ; unless otherwise noted.


### 2nd Harmonic Distortion vs. $R_L$




### 3rd Harmonic Distortion vs. $R_L$




### 2nd Harmonic Distortion vs. $V_{OUT}$




### 3rd Harmonic Distortion vs. $V_{OUT}$



### 2nd Harmonic Distortion vs. Gain



### 3rd Harmonic Distortion vs. Gain







## Typical Performance Characteristics - Continued

$T_A = 25^\circ\text{C}$ ,  $V_S = \pm 5\text{V}$ ,  $R_f = 200\Omega$ ,  $R_L = 500\Omega$ ,  $G = 10$ ; unless otherwise noted.


2nd Harmonic Distortion vs.  $R_L$  at  $V_S = 5\text{V}$




3rd Harmonic Distortion vs.  $R_L$  at  $V_S = 5\text{V}$




2nd Harmonic Distortion vs.  $V_{OUT}$  at  $V_S = 5\text{V}$




3rd Harmonic Distortion vs.  $V_{OUT}$  at  $V_S = 5\text{V}$



2nd Harmonic Distortion vs. Gain at  $V_S = 5\text{V}$



3rd Harmonic Distortion vs. Gain at  $V_S = 5\text{V}$







## Typical Performance Characteristics - Continued

$T_A = 25^\circ\text{C}$ ,  $V_S = \pm 5\text{V}$ ,  $R_f = 200\Omega$ ,  $R_L = 500\Omega$ ,  $G = 10$ ; unless otherwise noted.


### Small Signal Pulse Response




### Small Signal Pulse Response at $V_S = 5\text{V}$




### Large Signal Pulse Response




### Large Signal Pulse Response at $V_S = 5\text{V}$



### Enable Response



### Disable Response







Typical Performance Characteristics - Continued

T<sub>A</sub> = 25°C, V<sub>S</sub> = ±5V, R<sub>f</sub> = 200Ω, R<sub>L</sub> = 500Ω, G = 10; unless otherwise noted.


Enable Response at V<sub>S</sub> = 5V




Disable Response at V<sub>S</sub> = 5V




Off Isolation




Off Isolation at V<sub>S</sub> = 5V



CMRR vs. Frequency



PSRR vs. Frequency





## Application Information

### Basic Operation

Figures 1 and 2 illustrate typical circuit configurations for non-inverting, inverting, and unity gain topologies for dual supply applications. They show the recommended bypass capacitor values and overall closed loop gain equations.




Figure 1. Typical Non-Inverting Gain Circuit




Figure 2. Typical Inverting Gain Circuit

### Achieving Low Noise in an Application

Making full use of the low noise of the CLC1001 requires careful consideration of resistor values. The feedback and gain set resistors ( $R_f$  and  $R_g$ ) and the non-inverting source impedance ( $R_{source}$ ) all contribute noise to the circuit and can easily dominate the overall noise if their values are too high. The datasheet is specified with an  $R_g$  of  $22.1\Omega$ , at which point the noise from  $R_f$  and  $R_g$  is about equal to the noise from the CLC1001. Lower value resistors could be used at the expense of more distortion. Figure 3 shows

total input voltage noise (amp+resistors) versus  $R_f$  and  $R_g$ . As the value of  $R_f$  increases, the total input referred noise also increases.




Figure 3: Input Referred Voltage Noise vs.  $R_f$  and  $R_g$

The noise caused by a resistor is modeled with either a voltage source in series with the resistance:

$$\sqrt{4kTR}$$

Or a current source in parallel with it:

$$i_R = \sqrt{\frac{4kT}{R}}$$

Op amp noise is modeled with three noise sources,  $e_n$ ,  $i_n$  and  $i_b$ . These three sources are analogous to the DC input voltage and current errors  $V_{os}$ ,  $I_{bn}$  and  $I_{bi}$ .

The noise models must be analyzed in-circuit to determine the effect on the op amp output noise.

Since noise is statistical in nature rather than a continuous signal, the set of noise sources in circuit add in an RMS (root mean square) fashion rather than in a linear fashion. For uncorrelated noise sources, this means you add the squares of the noise voltages. A typical non-inverting application (see figure 1) results in the following noise at the output of the op amp:



$$e_o^2 = e_n^2 \left( 1 + \frac{R_f}{R_g} \right)^2 + i_n^2 R_s^2 \left( 1 + \frac{R_f}{R_g} \right)^2 + i_i^2 R_f^2$$

op amp noise terms  $e_n$ ,  $i_n$  and  $i_i$

$$+ e_{R_s}^2 \left( 1 + \frac{R_f}{R_g} \right)^2 + e_{R_g}^2 \left( \frac{R_f}{R_g} \right)^2 + e_{R_f}^2$$

external resistor noise terms for  $R_s$ ,  $R_g$  and  $R_f$

High source impedances are sometimes unavoidable, but they increase noise from the source impedance and also make the circuit more sensitive to the op amp current noise. Analyze all noise sources in the circuit, not just the op amp itself, to achieve low noise in your application.

### Power Dissipation

Power dissipation should not be a factor when operating under the stated 500Ω load condition. However, applications with low impedance, DC coupled loads should be analyzed to ensure that maximum allowed junction temperature is not exceeded. Guidelines listed below can be used to verify that the particular application will not cause the device to operate beyond its intended operating range.

Maximum power levels are set by the absolute maximum junction rating of 150°C. To calculate the junction temperature, the package thermal resistance value  $\Theta_{JA}$  ( $\Theta_{JA}$ ) is used along with the total die power dissipation.

$$T_{\text{Junction}} = T_{\text{Ambient}} + (\Theta_{JA} \times P_D)$$

Where  $T_{\text{Ambient}}$  is the temperature of the working environment.

In order to determine  $P_D$ , the power dissipated in the load needs to be subtracted from the total power delivered by the supplies.

$$P_D = P_{\text{supply}} - P_{\text{load}}$$

Supply power is calculated by the standard power equation.

$$P_{\text{supply}} = V_{\text{supply}} \times I_{\text{RMS supply}}$$

$$V_{\text{supply}} = V_{S+} - V_{S-}$$

Power delivered to a purely resistive load is:

$$P_{\text{load}} = ((V_{\text{LOAD}})_{\text{RMS}}^2) / R_{\text{load eff}}$$

The effective load resistor ( $R_{\text{load eff}}$ ) will need to include the effect of the feedback network. For instance,

$R_{\text{load eff}}$  in figure 3 would be calculated as:

$$R_L \parallel (R_f + R_g)$$

These measurements are basic and are relatively easy to perform with standard lab equipment. For design purposes however, prior knowledge of actual signal levels and load impedance is needed to determine the dissipated power. Here,  $P_D$  can be found from

$$P_D = P_{\text{Quiescent}} + P_{\text{Dynamic}} - P_{\text{Load}}$$

Quiescent power can be derived from the specified  $I_S$  values along with known supply voltage,  $V_{\text{Supply}}$ . Load power can be calculated as above with the desired signal amplitudes using:

$$(V_{\text{LOAD}})_{\text{RMS}} = V_{\text{PEAK}} / \sqrt{2}$$

$$(I_{\text{LOAD}})_{\text{RMS}} = (V_{\text{LOAD}})_{\text{RMS}} / R_{\text{load eff}}$$

The dynamic power is focused primarily within the output stage driving the load. This value can be calculated as:

$$P_{\text{DYNAMIC}} = (V_{S+} - V_{\text{LOAD}})_{\text{RMS}} \times (I_{\text{LOAD}})_{\text{RMS}}$$

Assuming the load is referenced in the middle of the power rails or  $V_{\text{supply}}/2$ .

Figure 4 shows the maximum safe power dissipation in the package vs. the ambient temperature for the packages available.




Figure 4. Maximum Power Derating



Driving Capacitive Loads

Increased phase delay at the output due to capacitive loading can cause ringing, peaking in the frequency response, and possible unstable behavior. Use a series resistance,  $R_S$ , between the amplifier and the load to help improve stability and settling performance. Refer to Figure 5.




Figure 5. Addition of  $R_S$  for Driving Capacitive Loads

Table 1 provides the recommended  $R_S$  for various capacitive loads. The recommended  $R_S$  values result in  $\leq 1$ dB peaking in the frequency response. The Frequency Response vs.  $C_L$  plots, on page 7, illustrates the response of the CLC1001.

| $C_L$ (pF) | $R_S$ ( $\Omega$ ) | -3dB BW (MHz) |
|------------|--------------------|---------------|
| 10         | 43                 | 266           |
| 22         | 33                 | 228           |
| 47         | 20                 | 192           |
| 100        | 13                 | 155           |
| 470        | 4.3                | 84            |

Table 1: Recommended  $R_S$  vs.  $C_L$

For a given load capacitance, adjust  $R_S$  to optimize the tradeoff between settling time and bandwidth. In general, reducing  $R_S$  will increase bandwidth at the expense of additional overshoot and ringing.

Overdrive Recovery

An overdrive condition is defined as the point when either one of the inputs or the output exceed their specified voltage range. Overdrive recovery is the time needed for the amplifier to return to its normal or linear operating point. The recovery time varies, based on whether the input or output is overdriven and by how much the range is exceeded. The CLC1001 will typically recover in less than 25ns from an overdrive condition. Figure 6 shows the CLC1001 in an overdriven condition.




Figure 6. Overdrive Recovery

Layout Considerations

General layout and supply bypassing play major roles in high frequency performance. has evaluation boards to use as a guide for high frequency layout and as an aid in device testing and characterization. Follow the steps below as a basis for high frequency layout:

- Include 6.8 $\mu$ F and 0.1 $\mu$ F ceramic capacitors for power supply decoupling
- Place the 6.8 $\mu$ F capacitor within 0.75 inches of the power pin
- Place the 0.1 $\mu$ F capacitor within 0.1 inches of the power pin
- Remove the ground plane under and around the part, especially near the input and output pins to reduce parasitic capacitance
- Minimize all trace lengths to reduce series inductances

Refer to the evaluation board layouts below for more information.

Evaluation Board Information

The following evaluation boards are available to aid in the testing and layout of these devices:

| Evaluation Board | Products           |
|------------------|--------------------|
| CEB002           | CLC1001 in SOT23-5 |
| CEB003           | CLC1001 in SOIC-8  |



## Evaluation Board Schematics

Evaluation board schematics and layouts are shown in Figures 7-11. These evaluation boards are built for dual-supply operation. Follow these steps to use the board in a single-supply application:

1. Short  $-V_S$  to ground.
2. Use C3 and C4, if the  $-V_S$  pin of the amplifier is not directly connected to the ground plane.




Figure 7. CEB002/CEB003 Schematic




Figure 8. CEB002 Top View




Figure 9. CEB002 Bottom View




Figure 10. CEB003 Top View





Figure 11. CEB003 Bottom View



## SOT23-6 Package




1. Dimensions and tolerances are as per ANSI Y14.5M-1982.
2. Package surface to be matte finish VDI 11~13.
3. Die is facing up for mold. Die is facing down for trim/form, ie. reverse trim/form.
4. The footlength measuring is based on the gauge plane method.

 Dimension are exclusive of mold flash and gate burr.

 Dimension are exclusive of solder plating.



| SOIC-8     |          |      |
|------------|----------|------|
| SYMBOL     | MIN      | MAX  |
| A1         | 0.10     | 0.25 |
| B          | 0.36     | 0.48 |
| C          | 0.19     | 0.25 |
| D          | 4.80     | 4.98 |
| E          | 3.81     | 3.99 |
| e          | 1.27 BSC |      |
| H          | 5.80     | 6.20 |
| h          | 0.25     | 0.5  |
| L          | 0.41     | 1.27 |
| A          | 1.37     | 1.73 |
| $\theta_1$ | 0°       | 8°   |
| X          | 0.55 ref |      |
| $\theta_2$ | 7° BSC   |      |



1. All dimensions are in millimeters.
2. Lead coplanarity should be 0 to 0.1mm (0.004") max.
3. Package surface finishing: VDI 24~27
4. All dimension excluding mold flashes.
5. The lead width, B to be determined at 0.1905mm from the lead tip.

**Exar Corporation Headquarters and Sales Offices**  
48720 Kato Road Tel.: +1 (510) 668-7000  
Fremont, CA 94538 - USA Fax: +1 (510) 668-7001  
www.exar.com



**NOTICE**

EXAR Corporation reserves the right to make changes to the products contained in this publication in order to improve design, performance or reliability. EXAR Corporation assumes no responsibility for the use of any circuits described herein, conveys no license under any patent or other right, and makes no representation that the circuits are free of patent infringement. Charts and schedules contained here in are only for illustration purposes and may vary depending upon a user's specific application. While the information in this publication has been carefully checked; no responsibility, however, is assumed for inaccuracies.

EXAR Corporation does not recommend the use of any of its products in life support applications where the failure or malfunction of the product can reasonably be expected to cause failure of the life support system or to significantly affect its safety or effectiveness. Products are not authorized for use in such applications unless EXAR Corporation receives, in writing, assurances to its satisfaction that: (a) the risk of injury or damage has been minimized; (b) the user assumes all such risks; (c) potential liability of EXAR Corporation is adequately protected under the circumstances.

Reproduction, in part or whole, without the prior written consent of EXAR Corporation is prohibited.