OSRAM KR EELP41.22

Datasheet

Published by ams-OSRAM AG
Tobelbader Strasse 30, 8141 Premstaetten, Austria
Phone +43 3136 500-0
ams-osram.com
© All rights reserved


Downloaded from Arrow.com.

OSRAM

SMARTLED™ 0603

KR EELP41.22

The SMARTLED™ 0603 is the product of choice for status indication and symbol backlighting in electronics.
The small package size allows compact designs. The improved corrosion robustness and increased junction temperature range makes the devices from this series suitable for professional industrial equipment and applications.



Applications

- Appliances & tools
- Display backlighting
- Factory automation
- Home & building automation
- Projection & display
- Transportation

Features

- Package: SMT package 0603, colorless diffused resin
- Chip technology: Volume emitter (InGaAlP)
- Typ. Radiation: 130° (horizontal = 0°), 130° (vertical = 90°)
- Color: λ_{dom} = 624 nm (● red)
- Corrosion Robustness Class: 3B
- ESD: 2 kV acc. to ANSI/ESDA/JEDEC JS-001 (HBM)

Downloaded from Arrow.com.

Ordering Information

Type	Luminous Intensity [1] I_F = 20 mA I_v	Ordering Code
KR EELP41.22-Q1S1-36-A8J8	71 ... 224 mcd	Q65113A7467

Downloaded from Arrow.com.

Maximum Ratings

Parameter	Symbol		Values
Operating Temperature	T_{op}	min. max.	-40 °C 105 °C
Storage Temperature	T_{stg}	min. max.	-40 °C 105 °C
Junction Temperature	T_j	max.	110 °C
Forward current T_S = 25 °C	I_F	min. max.	0.5 mA 30 mA
Forward Current pulsed D = 0.05 ; T_S = 25 °C	$I_{F\ pulse}$	max.	100 mA
Surge Current t ≤ 10 µs; D = 0.05 ; T_S = 25 °C	I_{FS}	max.	250 mA
Reverse voltage [2)] T_S = 25 °C	V_R	max.	10 V
ESD withstand voltage acc. to ANSI/ESDA/JEDEC JS-001 (HBM)	V_{ESD}		2 kV

Downloaded from Arrow.com.

Characteristics

I_F = 20 mA; T_S = 25 °C

Parameter	Symbol		Values
Peak Wavelength	λ_{peak}	typ.	636 nm
Dominant Wavelength [3]	λ_{dom}	min. typ. max.	616 nm 624 nm 630 nm
Spectral Bandwidth at 50% $I_{rel,max}$	$\Delta\lambda$	typ.	20 nm
Viewing angle at 50% I_V values for 0°, 90°	2φ	typ.	130 ° 130 °
Forward Voltage [4] I_F = 20 mA	V_F	min. typ. max.	1.60 V 1.95 V 2.40 V
Reverse current [2] V_R = 10 V	I_R	typ. max.	0.01 µA 10 µA
Real thermal resistance junction/solderpoint [5]	$R_{thJS\ real}$	typ. max.	550 K / W 670 K / W

Downloaded from Arrow.com.

Brightness Groups

Group	Luminous Intensity [1] I_F = 20 mA min. I_v	Luminous Intensity. [1] I_F = 20 mA max. I_v	Luminous Flux [6] I_F = 20 mA typ. Φ_V
Q1	71 mcd	90 mcd	290 mlm
Q2	90 mcd	112 mcd	360 mlm
R1	112 mcd	140 mcd	450 mlm
R2	140 mcd	180 mcd	580 mlm
S1	180 mcd	224 mcd	730 mlm

Forward Voltage Groups

Group	Forward Voltage [4] I_F = 20 mA min. V_F	Forward Voltage [4] I_F = 20 mA max. V_F
A8	1.60 V	2.00 V
J8	2.00 V	2.40 V

Wavelength Groups

Group	Dominant Wavelength [3] min. λ_{dom}	Dominant Wavelength [3] max. λ_{dom}
3	616 nm	620 nm
4	620 nm	624 nm
5	624 nm	627 nm
6	627 nm	630 nm

Group Name on Label


Example: Q1-3-A8

Brightness	Wavelength	Forward Voltage
Q1	3	A8

Downloaded from Arrow.com.


Relative Spectral Emission [6)]

$I_{rel} = f(\lambda)$; $I_F = 20$ mA; $T_S = 25$ °C



Radiation Characteristics [6)]


$I_{rel} = f(\varphi)$; $T_S = 25$ °C



Downloaded from Arrow.com.


Forward current [6]

$I_F = f(V_F)$; T_S = 25 °C



Relative Luminous Intensity [6], [7]


$I_v/I_v(20\ mA) = f(I_F)$; T_S = 25 °C



Downloaded from Arrow.com.


Forward Voltage [6)]

$\Delta V_F = V_F - V_F(25\ °C) = f(T_j);\ I_F = 20\ mA$




Relative Luminous Intensity [6)]

$I_v/I_v(25\ °C) = f(T_j);\ I_F = 20\ mA$



Dominant Wavelength [6)]


$\Delta\lambda_{dom} = \lambda_{dom} - \lambda_{dom}(25\ °C) = f(T_j);\ I_F = 20\ mA$



Downloaded from Arrow.com.


Max. Permissible Forward Current [5)]

$I_F = f(T)$




Permissible Pulse Handling Capability

$I_F = f(t_p)$; D: Duty cycle; T_S = 25 °C




Permissible Pulse Handling Capability

$I_F = f(t_p)$; D: Duty cycle; T_S = 85 °C



Downloaded from Arrow.com.

Dimensional Drawing [8)]



general tolerance ±0.1

lead finish Au

C67062-A0484-A4-04


Further Information:

Approximate Weight: 1.3 mg


Corrosion test: Class: 3B
Test condition: 40°C / 90 % RH / 15 ppm H_2S / 14 days (stricter than IEC 60068-2-43)

Downloaded from Arrow.com.

Electrical Internal Circuit



Recommended Solder Pad [8)]




For superior solder joint connectivity results we recommend soldering under standard nitrogen atmosphere. Package not suitable for ultra sonic cleaning.

Downloaded from Arrow.com.

Reflow Soldering Profile

Product complies to MSL Level 2 acc. to JEDEC J-STD-020E




Profile Feature	Symbol	Pb-Free (SnAgCu) Assembly			Unit
		Minimum	Recommendation	Maximum	
Ramp-up rate to preheat*) 25 °C to 150 °C			2	3	K/s
Time t_S T_{Smin} to T_{Smax}	t_S	60	100	120	s
Ramp-up rate to peak*) T_{Smax} to T_P			2	3	K/s
Liquidus temperature	T_L		217		°C
Time above liquidus temperature	t_L		80	100	s
Peak temperature	T_P		245	260	°C
Time within 5 °C of the specified peak temperature T_P - 5 K	t_P	10	20	30	s
Ramp-down rate* T_P to 100 °C			3	6	K/s
Time 25 °C to T_P				480	s

All temperatures refer to the center of the package, measured on the top of the component
* slope calculation DT/Dt: Dt max. 5 s; fulfillment for the whole T-range


Downloaded from Arrow.com.

Taping [8)]



Downloaded from Arrow.com.

Tape and Reel [9)]




Leader: min. 400mm*
Trailer: min. 160mm*
*)Dimensions acc. to IEC 60286-3; EIA 481-E

Reel Dimensions


A	W	N_{min}	W_1	$W_{2\,max}$	Pieces per PU
180 mm	8 + 0.3 / - 0.1 mm	58 mm	8.4 + 1,5 mm	14.4 mm	4000

Downloaded from Arrow.com.

Barcode-Product-Label (BPL)




Dry Packing Process and Materials [8)]



Moisture-sensitive product is packed in a dry bag containing desiccant and a humidity card according JEDEC-STD-033.

Downloaded from Arrow.com.

Type Designation System



Downloaded from Arrow.com.

Notes

The evaluation of eye safety occurs according to the standard IEC 62471:2006 (photo biological safety of lamps and lamp systems). Within the risk grouping system of this IEC standard, the device specified in this data sheet fall into the class **exempt group (exposure time 10000 s)**. Under real circumstances (for exposure time, conditions of the eye pupils, observation distance), it is assumed that no endangerment to the eye exists from these devices. As a matter of principle, however, it should be mentioned that intense light sources have a high secondary exposure potential due to their blinding effect. When looking at bright light sources (e.g. headlights), temporary reduction in visual acuity and afterimages can occur, leading to irritation, annoyance, visual impairment, and even accidents, depending on the situation.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit https://ams-osram.com/support/application-notes

Downloaded from Arrow.com.

Disclaimer

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.
For information on the types in question please contact our Sales Organization.
If printed or downloaded, please find the latest version on our website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.
Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/ applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.

Downloaded from Arrow.com.

Glossary

1) **Brightness:** Brightness groups are tested at a current pulse duration of 25 ms and a tolerance of ±11 %.

2) **Reverse Operation:** This product is intended to be operated applying a forward current within the specified range. Applying any continuous reverse bias or forward bias below the voltage range of light emission shall be avoided because it may cause migration which can change the electro-optical characteristics or damage the LED.

3) **Wavelength:** Wavelengths are tested at a current pulse duration of 25 ms and a tolerance of ±1 nm.

4) **Forward Voltage:** Forward voltages are tested at a current pulse duration of 1 ms and a tolerance of ±0.1 V.

5) **Thermal Resistance:** Rth max is based on statistic values (6σ) used for Derating.

6) **Typical Values:** Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.

7) **Characteristic curve:** In the range where the line of the graph is broken, you must expect higher differences between single devices within one packing unit.

8) **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ±0.1 and dimensions are specified in mm.

9) **Tape and Reel:** All dimensions and tolerances are specified acc. IEC 60286-3 and specified in mm.

Downloaded from Arrow.com.

Revision History

Version	Date	Change
1.0	2024-03-22	Initial Version
1.1	2024-08-30	Description
1.2	2025-07-10	Recommended Solder Pad
1.3	2026-08-06	Applications Dimensional Drawing
1.4	2026-08-06	Electro - Optical Characteristics (Diagrams) Derating (Diagrams)

Downloaded from Arrow.com.

EU RoHS and China RoHS compliant product
此产品符合欧盟 RoHS 指令的要求；
按照中国的相关法规和标准，
不含有毒有害物质或元素。

Published by ams-OSRAM AG
Tobelbader Strasse 30, 8141 Premstaetten, Austria
Phone +43 3136 500-0
ams-osram.com
© All rights reserved

Downloaded from Arrow.com.