

Product number **CN14236\_WINNIE-S**

Family	Winnie	FWHM	(simulated) 19
Type	Assembly	Efficiency	(simulated) 92 %
LED	CLL02x/CLU02x (LES10)	cd/lm	(simulated) 4.200
Color	White	Gerber File	Available
Diameter	49.8 mm		
Height	19.3 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	["screw"]		
Status	Production ready		

Product number **CN14237\_WINNIE-M**

Family	Winnie	FWHM	(simulated) 35
Type	Assembly	Efficiency	(simulated) 92 %
LED	CLL02x/CLU02x (LES10)	cd/lm	(simulated) 1.800
Color	White	Gerber File	Available
Diameter	49.8 mm		
Height	19.3 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	["screw"]		
Status	Production ready		

Product number **CN16191\_WINNIE-WW-C**

Family	Winnie	FWHM	(simulated) 68
Type	Assembly	Efficiency	(simulated) 82 %
LED	CLL02x/CLU02x (LES10)	cd/lm	(simulated) 0.000
Color	Clear	Gerber File	Available
Diameter	49.8 mm		
Height	19.3 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	["socket"]		
Status	Production ready		

Product number **CN14236\_WINNIE-S**

Family	Winnie	FWHM	20 degrees
Type	Assembly	Efficiency	88 %
LED	CLL02x/CLU02x (LES10)	cd/lm	3.400
Color	White	Gerber File	Available
Diameter	49.8 mm		
Height	19.3 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	["screw"]		
Status	Production ready		

Product number **CN14236\_WINNIE-S**

Family	Winnie	FWHM	21 degrees
Type	Assembly	Efficiency	87 %
LED	CLL02x/CLU02x (LES10)	cd/lm	3.340
Color	White	Gerber File	Available
Diameter	49.8 mm		
Height	19.3 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	["screw"]		
Status	Production ready		

Product number **CN14237\_WINNIE-M**

Family	Winnie	FWHM	35 degrees
Type	Assembly	Efficiency	87 %
LED	CLL02x/CLU02x (LES10)	cd/lm	2.300
Color	White	Gerber File	Available
Diameter	49.8 mm		
Height	19.3 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	["screw"]		
Status	Production ready		

Product number **CN14237\_WINNIE-M**

Family	Winnie	FWHM	35 degrees
Type	Assembly	Efficiency	86 %
LED	CLL02x/CLU02x (LES10)	cd/lm	1.600
Color	White	Gerber File	Available
Diameter	49.8 mm		
Height	19.3 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	["screw"]		
Status	Production ready		

Product number **CN14238\_WINNIE-W**

Family	Winnie	FWHM	46 degrees
Type	Assembly	Efficiency	87 %
LED	CLL02x/CLU02x (LES10)	cd/lm	1.600
Color	White	Gerber File	Available
Diameter	49.8 mm		
Height	19.3 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	["screw"]		
Status	Production ready		

Product number **CN14238\_WINNIE-W**

Family	Winnie	FWHM	46 degrees
Type	Assembly	Efficiency	87 %
LED	CLL02x/CLU02x (LES10)	cd/lm	1.100
Color	White	Gerber File	Available
Diameter	49.8 mm		
Height	19.3 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	["screw"]		
Status	Production ready		

Product number **CN14811\_WINNIE-O**

Family	Winnie	FWHM	63+22 degrees
Type	Pack	Efficiency	90 %
LED	CLL02x/CLU02x (LES10)	cd/lm	1.600
Color	Clear	Gerber File	Available
Diameter	49.8 mm		
Height	19.3 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	["screw"]		
Status	Production ready		

**NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.**


**GENERAL INFORMATION**

- Product series especially designed & optimized for CLL02x/CLU02x (LES10) series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.


Please find more information about used material from below:

[http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%208N%20UL94\\_Yellow%20Card.pdf](http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%208N%20UL94_Yellow%20Card.pdf)  
<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%208N%20PLEXIGLAS-Datasheet.pdf>

## Relative intensity of CN14237\_WINNIE-M\_(CLL020)



## Relative intensity of CN14238\_WINNIE-W\_(CLL020)




D


C

B


A




Isometric view




Section view A-A



Bottom view



Top view

 $\phi 3.2$ fastening with M3  
pan head screws

## Materials

Lens: PMMA 8N

Holder: PC Makrolon 2407, white

Tolerances if not otherwise shown  
According to DIN ISO 2768-1  
Linear measures:  
Up to 30mm class M, otherwise class C.  
According to DIN ISO 2768-2  
Form and position: class L



Ledil Oy  
Salorankatu 10  
FIN 24240 SALO  
Finland

THIRD ANGLE PROJECTION:



DRAWING TITLE

Datasheet CN14236\_Winnie-S assy

SIZE

A4

PART NUMBER

CN14236

This drawing is the property  
of LEDil Oy. It may not be  
reproduced, copied or  
communicated without a written  
agreement with LEDil Oy.

SCALE


1:1


WEIGHT

SHEET


1/1

Luminaire: Ledil Oy CN14236\_WINNIE-S\_(CLU028)\_SIMULATED  
Lamps: 1 x Citizen CLU028-1204C4-303M2K1







Luminaire: LEDiL Oy CN14236\_WINNIE-S\_(CLU024)\_434-Typ-L5  
Lamps: 1 x CitizenCLU-024\_(CLU024-1204B8-303M1A2)\_434-Typ-L5\_1023.5lm@250mA\_P=8.57963W\_I=0.2498A




Luminaire: Ledil Oy CN14236\_WINNIE-S\_(CLL020) Efficiency=87%  
Lamps: 1 x Citizen CLL020 (CLL020-1202A5-303H1A7) 339lm @ 120mA CCT=3000K P=4.20W I=120mA



Luminaire: LEDiL Oy CN14237\_WINNIE-M\_(CLU024)\_434-Typ-L5  
Lamps: 1 x Citizen\_CLU-024\_(CLU024-1204B8-303M1A2)\_434-Typ-L5\_1023.5lm@250mA\_P=8.57963W\_I=0.2498A




Luminaire: LEDiL Oy CN14238\_WINNIE-W\_(CLU024)\_434-Typ-L5  
Lamps: 1 x CitizenCLU-024\_(CLU024-1204B8-303M1A2)\_434-Typ-L5\_1023.5lm@250mA\_P=8.57963W\_I=0.2498A




## LEDiL Oy CN14811\_WINNIE-O\_(CLU024)\_(434\_Typ\_L5) / LDC (Linear)


Luminaire: LEDiL Oy CN14811\_WINNIE-O\_(CLU024)\_(434\_Typ\_L5)  
Lamps: 1 x Citizen\_CLU024\_(CLU024-1204B8-303M1A2)\_(434\_Typ\_L5)  
\_996.219lm@250mA\_P=8.4851W\_I=0.2499A



Luminaire: Ledil Oy CN14236\_WINNIE-S\_(CLU028)\_SIMULATED  
Lamps: 1 x Citizen CLU028-1204C4-303M2K1




Luminaire: Ledil Oy CN14237\_WINNIE-M\_(CLU028)\_SIMULATED  
Lamps: 1 x Citizen CLU028-1204C4-303M2K1




Luminaire: LEDiL Oy CN14236\_WINNIE-S\_(CLU024)\_434-Typ-L5

Lamps: 1 x Citizen\_CLU-024\_(CLU024-1204B8-303M1A2)\_434-Typ-L5\_1023.5lm@250mA\_P=8.57963W\_I=0.2498A




Luminaire: Ledil Oy CN14236\_WINNIE-S\_(CLL020) Efficiency=87%  
Lamps: 1 x Citizen CLL020 (CLL020-1202A5-303H1A7) 339lm @ 120mA CCT=3000K P=4.20W I=120mA




Luminaire: LEDiL Oy CN14237\_WINNIE-M\_(CLU024)\_434-Typ-L5

Lamps: 1 x Citizen\_CLU-024\_(CLU024-1204B8-303M1A2)\_434-Typ-L5\_1023.5lm@250mA\_P=8.57963W\_I=0.2498A



Luminaire: LEDiL Oy CN14238\_WINNIE-W\_(CLU024)\_434-Typ-L5

Lamps: 1 x Citizen\_CLU-024\_(CLU024-1204B8-303M1A2)\_434-Typ-L5\_1023.5lm@250mA\_P=8.57963W\_I=0.2498A



## LEDiL Oy CN14811\_WINNIE-O\_(CLU024)\_(434\_Typ\_L5) / LDC (Polar)

Luminaire: LEDiL Oy CN14811\_WINNIE-O\_(CLU024)\_(434\_Typ\_L5)  
Lamps: 1 x CitizenCLU024\_(CLU024-1204B8-303M1A2)\_(434\_Typ\_L5)  
\_996.219lm@250mA\_P=8.4851W\_I=0.2499A

