A Product Line of
Diodes Incorporated

74AVC4T245

4 Bit Dual Power Supply Translating Buffer With 3 State Outputs

Description

The 74AVC4T245 device is 4-bit, dual supply transceiver that enables bidirectional level translation, designed for asynchronous communication between two data buses. It features four 2-bit input-output ports (nAn and nBn), a direction control input (nDIR), an output enable input (nOE) and dual supply pins (VCC(A) and VCC(B)). Both VCC(A) and VCC(B) can be supplied at any voltage between 0.8V and 3.6V making the device suitable for translating between any of the low voltage nodes (0.8V, 1.2V, 1.5V, 1.8V, 2.5V and 3.3V). Pins nAn, nOE and nDIR are referenced to VCC(A) and pins nBn are referenced to VCC(B). A HIGH on nDIR allows transmission from nAn to nBn and a LOW on nDIR allows transmission from nBn to nAn. The output enable input (nOE) can be used to disable the outputs so the buses are effectively isolated. The device is fully specified for partial power-down applications using IOFF. The IOFF circuitry disables the output, preventing any damaging back flow current through the device when it is powered down. In suspend mode when either VCC(A) or VCC(B) are at GND level, both nAn and nBn are in the high-impedance OFF-state.

The 74AVC4T245 is available in the packages, and is specified for operation from -40°C to +125°C among all supply voltages. The wide temperature ranges and high ESD tolerance facilitate their use in harsh applications.

Application(s)

- Personal electronics
- Industrial
- Enterprise
- Telecom

Features

- Supply Voltage Range: VCC(A)/ VCC(B): from 0.8V to 3.6V
- Max Data Rates:
  - 380Mbps (1.8V to 3.3V Translation)
  - 200Mbps (<1.8V to 3.3V Translation)
  - 200Mbps (Translate to 2.5V or 1.8V)
  - 150Mbps (Translate to 1.5V)
  - 100Mbps (Translate to 1.2V)
  - 50Mbps (Translate to 0.8V~1.1V)
- High Drive Strength (± 12mA at 3.3V)
- IOFF Supports Partial-Power-Down Mode Operation
- ESD Protection Exceeds JESD 22
  - Exceeds 5000V Human Body Model (A114)
  - Exceeds 1500V Charged Device Model (C101)
- Latch-Up Exceeds 100mA per JESD 78, Class II
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/

Ordering Information

Orderable Part Number	Package Code	Package Description
74AVC4T245T16-13	T16	TSSOP-16
74AVC4T245PB-7	PB	U-QFN1826-16
74AVC4T245PB-7A	PB	U-QFN1826-16 (12*4mm)
74AVC4T245ZSA16-7	ZSA16	VQFN3525-16
74AVC4T245ZD16-7	ZD16	V-QFN4035-16

Notes:

- 7: 7" Tape & Reel, 13: 13" Tape & Reel
- Without A: 8*4mm Reel Size; With A: 12*4 mm Reel Size

Notes:


1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.


Downloaded from Arrow.com.

Pin Configuration


TSSOP (T16) Package




UQFN1826 (PB) Package



VQFN3525 (ZSA16) Package



VQFN4035 (ZD16) Package



Pin Description

Pin Number		Pin Name	Signal Type	Description
TSSOP-16 VQFN3525-16 VQFN4035-16	U-QFN1826-16			
1	3	VCCA	Power	A port supply Voltage
2	4	1DIR	Control Logic Input	Direction Control Pin for Port “1”.
3	5	2DIR	Control Logic Input	Direction Control Pin for Port “2”.
4	6	1A1	I/O	Input/Output 1A1. Referenced to VCCA.
5	7	1A2	I/O	Input/Output 1A2. Referenced to VCCA.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Pin Number		Pin Name	Signal Type	Description
TSSOP-16 VQFN3525-16 VQFN4035-16	U-QFN1826-16			
6	8	2A1	I/O	Input/Output 2A1. Referenced to VCCA.
7	9	2A2	I/O	Input/Output 2A2. Referenced to VCCA.
8	10	GND	Power	Ground
9	11	GND	Power	Ground
10	12	2B2	I/O	Input/Output 2B2. Referenced to VCCB.
11	13	2B1	I/O	Input/Output 2B1. Referenced to VCCB.
12	14	1B2	I/O	Input/Output 1B2. Referenced to VCCB.
13	15	1B1	I/O	Input/Output 1B1. Referenced to VCCB.
14	16	$2\overline{OE}$	Control Logic Input	3-state output-mode enable. Pull to High to place port “2” outputs in high-impedance mode. Referenced to VCCA.
15	1	$1\overline{OE}$	Control Logic Input	3-state output-mode enable. Pull to High to place port “1” outputs in high-impedance mode. Referenced to VCCA.
16	2	VCCB	Power	B port supply Voltage

© 2026 Copyright Diodes Incorporated. All Rights Reserved.


Downloaded from Arrow.com.

Table 1. Function Table

Control Functional		Output Status		Operation
$\overline{OE}$	DIR	A Port	B Port	
L	L	Enabled	Hi-Z	B to A
L	H	Hi-Z	Enabled	A to B
H	X	Hi-Z	Hi-Z	Isolation

*Floating input pin is allowed for this case

Logic Diagram



© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Maximum Ratings

(Above which useful life may be impaired. For user guidelines, not tested.)

Storage Temperature .....–65°C to +150°C
Junction Temperature .....+150°C
Supply Voltage Range ..... –0.5V to +4.6V
Input Voltage Range ..... –0.5V to +4.6V
Voltage Applied to Output in High Impedance or I_{OFF} State.... –0.5V to +4.6V
Voltage Applied to Output in High or Low State..... –0.5V to V_{CCO}+0.5V
Input Clamp Current $V_I < 0$ ..... –50mA
Output Clamp Current ..... –50mA
Continuous Output Current .....±50mA
Continuous Current Through V_{CCA} or GND .....±100mA
ESD: HBM.....5KV
ESD: CDM.....1.5KV

Note:
Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

Thermal Information

Symbol	Parameter	Package	Min.	Typ.	Max.	Units
θJA	Thermal Resistance Junction-to-Ambient	TSSOP-16		100		°C/W
		U-QFN1826-16		140		
		V-QFN3525-16		60		
		V-QFN4035-16		60		
θJC	Thermal Resistance Junction-to-Case	TSSOP-16		43		°C/W
		U-QFN1826-16		80		
		V-QFN3525-16		42		
		V-QFN4035-16		45		

Note: Test condition for each of the 2 package types: Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.

Recommended Operating Conditions

T_A = +25°C

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
V_{CCA}	Operating Voltage		0.8		3.6	V
V_{CCB}	Operating Voltage		0.8		3.6	V
I_{OH}	High-Level Output Current Data Input, nDIR, $\overline{OE}$ Input	V_{CCO} = 1.1V			-3	mA
		V_{CCO} = 1.4V to 1.6V			-6	
		V_{CCO} = 1.65V to 1.95V			-8	
		V_{CCO} = 2.3V to 2.7V			-9	
		V_{CCO} = 3V to 3.6V			-12	

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
I_{OL}	Low-Level Output Current Data Input, nDIR, $\overline{OE}$ Input	V_{CCO} = 1.1V			3	mA
		V_{CCO} = 1.4V to 1.6V			6	
		V_{CCO} = 1.65V to 1.95V			8	
		V_{CCO} = 2.3V to 2.7V			9	
		V_{CCO} = 3V to 3.6V			12	
V_I	Input Voltage		0		3.6	V
V_O	Output Voltage	Active State	0		V_{CCO}	V
		Tri-State	0		3.6	
T_A	Operating Free-Air Temperature		-40		+125	°C

Electrical Characteristics

T_A = +40°C to +125°C, unless otherwise specified.

Symbol	Parameter	Test Conditions		T_A = +25°C			T_A = -40°C to +85°C		T_A = -40°C to +125°C		Units
				Min.	Typ.	Max.	Min.	Max.	Min.	Max.	
V_{IH}	High-level input voltage	Data Input, nDIR, $n\overline{OE}$ Input	V_{CCI} = 0.8V	0.70V_{CCI}			0.70V_{CCI}		0.70V_{CCI}		V
			V_{CCI} = 1.1V to 1.95V	0.65V_{CCI}			0.65V_{CCI}		0.65V_{CCI}		
			V_{CCI} = 1.95V to 2.7V	1.6			1.6		1.6		
			V_{CCI} = 2.7V to 3.6V	2			2		2		
V_{IL}	Low-level input voltage	Data Input, nDIR, $n\overline{OE}$ Input	V_{CCI} = 0.8V			0.3V_{CCI}		0.3V_{CCI}		0.3V_{CCI}	V
			V_{CCI} = 1.1V to 1.95V			0.35V_{CCI}		0.35V_{CCI}		0.35V_{CCI}	
			V_{CCI} = 1.95V to 2.7V			0.7		0.7		0.7	
			V_{CCI} = 2.7V to 3.6V			0.8		0.8		0.8	
V_{OH}	High-Level Output Voltage	I_{OH} = -0.1mA; V_{CCI} & V_{CCO} = 0.8-3.6V					V_{CCO} -0.1		V_{CCO} -0.1		V
		I_{OH} = -3mA; V_{CCI} & V_{CCO} = 1.1V		0.95			0.85		0.85		
		I_{OH} = -6mA; V_{CCI} & V_{CCO} = 1.4V		1.05			1.05		1.05		
		I_{OH} = -8mA; V_{CCI} & V_{CCO} = 1.65V		1.2			1.2		1.2		
		I_{OH} = -9mA; V_{CCI} & V_{CCO} = 2.3V		1.75			1.75		1.75		
		I_{OH} = -12mA; V_{CCI} & V_{CCO} = 3V		2.3			2.3		2.3		

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Symbol	Parameter	Test Conditions		T_A = +25°C			T_A = -40°C to +85°C		T_A = -40°C to +125°C		Units
				Min.	Typ.	Max.	Min.	Max.	Min.	Max.	
V_{OL}	Low-Level Output Voltage	I_{OH} = 0.1mA; V_{CCI} & V_{CCO} = 0.8-3.6V				0.1		0.1		0.1	V
		I_{OH} = 3mA; V_{CCI} & V_{CCO} = 1.1V				0.25		0.25		0.27	
		I_{OH} = 6mA; V_{CCI} & V_{CCO} = 1.4V				0.35		0.35		0.35	
		I_{OH} = 8mA; V_{CCI} & V_{CCO} = 1.65V				0.45		0.45		0.45	
		I_{OH} = 9mA; V_{CCI} & V_{CCO} = 2.3V				0.55		0.55		0.55	
		I_{OH} = 12mA; V_{CCI} & V_{CCO} = 3V				0.7		0.7		0.7	
I_I	Input Current	V_I = V_{CCA} or GND; V_{CCI} & V_{CCO} = 0.8-3.6V				±1		±1.5		±1.5	uA
I_{OFF}	Off State Current	A or B Port; V_I or V_O = 0 to 3.6V	V_{CCI} = 0			±1		±3		±10	uA
			V_{CCI} = 0.8-3.6V			±1		±3		±10	
I_{OZ}	High-Z State Current	A or B Port; V_I or V_O = 0 to 3.6V; V_{CCI} = 3.6V				±1		±2		±10	uA
		A Port; V_I or V_O = 0 to 3.6V; V_{CCI} = 3.6V				±1		±2		±5	
		B Port; V_I or V_O = 0 to 3.6V; V_{CCI} = 0				±1		±2		±5	
I_{CCA}	Supply Current	V_I = V_{CCI} or GND IO = 0	V_{CCI} & V_{CCO} = 0.8-3.6V			±2		±10		±35	uA
			V_{CCI} & V_{CCO} = 0.8-1.1V			±1.5		±8		±25	
			V_{CCI} = 0-3.6V; V_{CCO} = 0			±1.5		±10		±35	
			V_{CCI} = 0; V_{CCO} = 0-3.6V			±1		±1		±1	
I_{CCB}	Supply Current	V_I = V_{CCI} or GND IO = 0	V_{CCI} & V_{CCO} = 0.8-3.6V			±2		±10		±35	uA
			V_{CCI} & V_{CCO} = 0.8-1.1V			±1.5		±8		±25	
			V_{CCI} = 0-3.6V; V_{CCO} = 0			±1		±1		±1	
			V_{CCI} = 0; V_{CCO} = 0-3.6V			±1.5		±10		±35	
I_{CCA} + I_{CCB}	Supply Current	V_I = V_{CCI} or GND IO = 0; V_{CCI} & V_{CCO} = 0.8-3.6V				±4		±20		±70	uA

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Symbol	Parameter	Test Conditions	T_A = +25°C			T_A = -40°C to +85°C		T_A = -40°C to +125°C		Units
			Min.	Typ.	Max.	Min.	Max.	Min.	Max.	
C_I	Control Input Capacitance	nDIR, n$\overline{OE}$ Input; V_I = 3.3V or GND; V_{CCI} = 3.3V		3.5			4.5		4.5	pF
C_O	Input/Output Capacitance	A or B; V_O = 3.3V or GND; V_{CCI} & V_{CCO} = 3.3V		6			7		7	pF

Switching Characteristics

V_{CCA} = 0.8V; T_A = -40°C to +125°C, unless otherwise specified.

Parameter	Test Conditions	Direction	V_{CCB}						Units
			0.8V	1.2V± 0.1V	1.5V ± 0.1V	1.8V± 0.15V	2.5V± 0.2V	3.3V ± 0.3V	
			Typ.	Typ.	Typ.	Typ.	Typ.	Typ.	
tpd	Propagation delay	nAn to nBn	11.0	7.3	6.5	6.2	6.5	7.0	ns
		nBn to nAn	11.0	10.0	12.4	12.3	12.1	12.0	
ten	Enable Time	n$\overline{OE}$ to nAn	18.2	18.2	18.2	18.2	18.2	18.2	
		n$\overline{OE}$ to nBn	19.2	12.7	11.4	10.9	10.7	11.1	
tdis	Disable Time	n$\overline{OE}$ to nAn	14.3	14.3	14.3	14.3	14.3	14.3	
		n$\overline{OE}$ to nBn	12.6	9.9	9.0	9.4	9.0	9.7	

V_{CCB} = 0.8V; T_A = -40°C to +125°C, unless otherwise specified.

Parameter	Test Conditions	Direction	V_{CCA}						Units
			0.8V	1.2V ± 0.1V	1.5V ± 0.1V	1.8V ± 0.15V	2.5V ± 0.2V	3.3V ± 0.3V	
			Typ.	Typ.	Typ.	Typ.	Typ.	Typ.	
tpd	Propagation delay	nAn to nBn	14.5	12.7	12.4	12.3	12.1	12.0	ns
		nBn to nAn	14.5	7.3	6.5	6.2	5.9	6.0	
ten	Enable Time	n$\overline{OE}$ to nAn	18.2	13.0	12.1	9.6	7.3	6.4	
		n$\overline{OE}$ to nBn	19.2	15.8	15.3	15.0	15.0	14.8	
tdis	Disable Time	n$\overline{OE}$ to nAn	14.3	9.6	8.5	7.5	7.7	8.6	
		n$\overline{OE}$ to nBn	17.0	13.8	13.4	13.1	12.9	12.7	

V_{CCA} = 1.2V ±0.1V; T_A = -40°C to +125°C, unless otherwise specified.

Parameter	Test Conditions	Direction	V_{CCB}													Units
			1.2V ± 0.1V			1.5V ± 0.1V			1.8V ± 0.15V			2.5V ± 0.2V			3.3V ± 0.3V			
			Min.	Typ.	Max.	Min.	Typ.	Max.	Min.	Typ.	Max.	Min.	Typ.	Max.	Min.	Typ.	Max.	
tpd	Propagation delay	nAn to nBn	0.5	3	8.3	0.5	2.9	6.3	0.5	2.1	5.5	0.5	2.1	4.6	0.5	2.3	4.6	ns
		nBn to nAn	0.5	3	8.3	0.5	3.1	7.8	0.5	2.8	7.7	0.5	2.1	7.4	0.5	2.2	7.3	
ten	Enable Time	n$\overline{OE}$ to nAn	1.8	3.9	11.7	1.8	4.2	11.7	1.8	4.3	11.7	1.8	3.5	11.7	1.8	3.5	11.7	
		n$\overline{OE}$ to nBn	1.9	4	13.0	1.9	2.5	9.5	1.9	3.3	8.2	1.4	3.6	7.9	1.2	4.5	7.7	
tdis	Disable Time	n$\overline{OE}$ to nAn	1.4	3.2	11.5	1.4	2.3	11.5	1.4	3	11.5	1.4	3	11.5	1.4	3.1	11.5	
		n$\overline{OE}$ to nBn	1.1	3	10.0	1.1	2.2	8.1	1.1	2.9	7.5	1.0	2.5	6.3	1.0	5.5	6.3	

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

V_{CCA} = 1.5V ±0.1V; T_A = -40°C to +125°C, unless otherwise specified.

Parameter	Test Conditions	Direction	V_{CCB}										Units
			1.2V ± 0.1V		1.5V ± 0.1V		1.8V ± 0.15V		2.5V ± 0.2V		3.3V ± 0.3V		
			Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	
tpd	Propagation delay	nAn to nBn	0.3	7.8	0.3	6.3	0.3	5.2	0.4	4.2	0.4	4.2	ns
		nBn to nAn	0.7	6.3	0.7	6.3	0.5	5.9	0.4	5.7	0.3	5.6	
ten	Enable Time	$n\overline{OE}$ to nAn	1.8	10.5	1.4	9.6	1.1	9.5	0.7	9.7	0.4	9.4	
		$n\overline{OE}$ to nBn	1.9	11.0	1.4	9.6	1.1	7.7	0.9	7.1	0.9	6.9	
tdis	Disable Time	$n\overline{OE}$ to nAn	1.1	10.2	1.8	10.2	1.5	10.2	1.3	10.2	1.6	10.2	
		$n\overline{OE}$ to nBn	1.4	10.4	1.9	10.3	1.9	9.1	1.4	7.4	1.2	7.6	

V_{CCA} = 1.8V ±0.15V; T_A = -40°C to +125°C, unless otherwise specified.

Parameter	Test Conditions	Direction	V_{CCB}										Units
			1.2V ± 0.1V		1.5V ± 0.1V		1.8V ± 0.15V		2.5V ± 0.2V		3.3V ± 0.3V		
			Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	
tpd	Propagation delay	nAn to nBn	0.1	7.7	0.1	5.9	0.1	4.9	0.1	3.9	0.3	3.9	ns
		nBn to nAn	0.6	5.5	0.6	5.3	0.5	4.9	0.3	4.6	0.3	4.5	
ten	Enable Time	$n\overline{OE}$ to nAn	1.8	9.0	1	8.6	1	7.3	0.6	7.3	0.4	7.2	
		$n\overline{OE}$ to nBn	1.7	10.5	1.2	9.2	1	7.4	0.8	6.7	0.8	6.5	
tdis	Disable Time	$n\overline{OE}$ to nAn	1.0	8.9	1.6	8.6	1.8	8.7	1.3	8.7	1.6	8.7	
		$n\overline{OE}$ to nBn	1.2	10.0	1.7	9.9	1.6	8.7	1.2	7.4	1	6.9	

V_{CCA} = 2.5V ±0.2V; T_A = -40°C to +125°C, unless otherwise specified.

Parameter	Test Conditions	Direction	V_{CCB}										Units
			1.2V ± 0.1V		1.5V ± 0.1V		1.8V ± 0.15V		2.5V ± 0.2V		3.3V ± 0.3V		
			Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	
tpd	Propagation delay	nAn to nBn	0.1	7.4	0.1	5.7	0.1	4.6	0.2	3.9	0.1	3.6	ns
		nBn to nAn	0.6	4.6	0.6	4.2	0.4	4.1	0.2	3.9	0.2	3.3	
ten	Enable Time	$n\overline{OE}$ to nAn	1.0	8.0	0.7	6.7	0.7	6.5	0.6	5.9	0.4	4.8	
		$n\overline{OE}$ to nBn	1.5	9.8	0.9	8.8	0.8	7.0	0.6	5.8	0.6	4	
tdis	Disable Time	$n\overline{OE}$ to nAn	0.7	9.0	1	8.4	1	8.4	1	6.2	1	6.6	
		$n\overline{OE}$ to nBn	0.9	9.9	1.5	9.4	1.3	8.2	1.1	6.2	0.9	5.2	

V_{CCA} = 3.3V ±0.3V; T_A = -40°C to +125°C, unless otherwise specified.

Parameter	Test Conditions	Direction	V_{CCB}										Units
			1.2V ± 0.1V		1.5V ± 0.1V		1.8V ± 0.15V		2.5V ± 0.2V		3.3V ± 0.3V		
			Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Max.	
tpd	Propagation delay	nAn to nBn	0.1	7.3	0.1	5.6	0.1	4.5	0.1	3.7	0.1	2.9	ns
		nBn to nAn	0.6	4.6	0.6	4.2	0.4	3.9	0.2	3.7	0.1	2.8	
ten	Enable Time	$n\overline{OE}$ to nAn	0.7	9.2	0.6	8.7	0.6	5.9	0.6	5.6	0.4	3.8	
		$n\overline{OE}$ to nBn	1.4	9.5	0.8	8.7	0.6	6.8	0.5	5.7	0.5	3.8	
tdis	Disable Time	$n\overline{OE}$ to nAn	0.6	9.5	0.7	9.3	0.7	8.3	0.7	5.6	0.7	6.6	
		$n\overline{OE}$ to nBn	0.8	9.5	1.4	9.3	1.2	8.1	1	6.4	0.8	6.2	

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Operating Characteristics

$T_A = +25^oC$

Parameter	Test Conditions			0.8V	1.2V	1.5V	1.8V	2.5V	3.3V	Units
CpdA	A to B	Enabled	$C_L = 0$, R_L = Open, f = 10MHz, $t_r = t_f$ = 1ns, $V_{CCA} = V_{CCB}$	0.2	0.2	0.2	0.2	0.3	0.4	pF
		Disabled		0.2	0.2	0.2	0.2	0.3	0.4	
	B to A	Enabled		9.5	9.7	9.8	9.9	10.7	11.9	
		Disabled		0.6	0.6	0.6	0.6	0.7	0.7	
CpdY	A to B	Enabled		9.5	9.7	9.8	9.9	10.7	11.9	
		Disabled		0.6	0.6	0.6	0.6	0.7	0.7	
	B to A	Enabled		0.2	0.2	0.2	0.2	0.3	0.4	
		Disabled		0.2	0.2	0.2	0.2	0.3	0.4	

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Parameter Measurement Information




Figure 1. Voltage Waveform Pulse Duration




Figure 2. Voltage Waveform Propagation Delay Times Inverting and Non Inverting Outputs




Figure 3. The VI Source Waveform




Figure 4. The Enable/Disable ($\overline{EN}$) to Output (Yn) Times




Figure 5. Load Circuit and Voltage Waveforms

Parameter	S1
tpd	Open
ten/ tdis	2*VCCO
ten/ tdis	GND

V_{CC}	R_L	C_L	VTP
0.8V-1.6V	2KΩ	15pF	0.1V
1.65V-2.7V	2KΩ	15pF	0.15V
3.0V-3.6V	2KΩ	15pF	0.3V


Notes:

1. Includes test lead and test apparatus capacitance.
2. f = 1MHz, Δt/ΔV <1ns/V
3. t_{PLH} and t_{PHL} are the same as t_{PD}.
4. t_r, t_f <1ns

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Device Naming Information




Part Marking

TSSOP (T16) Package



Identification Code: AVC4T245
YY: Year: 24, 25, 26~
WW: Workweek: 01~52;
52 represents 52 and 53 week
XX: Internal Code

UQFN (PB) Package




XX: Z3 = Identification Code
Y: Year: 0~9
W: Week: A~Z: week 1~26;
a~z: week 27~52; z represents 52 and 53 week
X: Internal Code

VQFN (ZSA16) Package



XX: 2V = Identification Code
Y: Year: 0~9
W: Week: A~Z: week 1~26;
a~z: week 27~52; z represents 52 and 53 week
X: Internal Code

VQFN (ZD16) Package




XX: Z2 = Identification Code
Y: Year: 0~9
W: Week: A~Z: week 1~26;
a~z: week 27~52; z represents 52 and 53 week
X: Internal Code

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Packaging Mechanical


16-TSSOP (T16)

Package Outline Dimensions



TSSOP-16			
Dim	Min	Max	Typ
A	-	1.08	-
A1	0.05	0.15	-
A2	0.80	0.93	-
b	0.19	0.30	-
c	0.09	0.20	-
D	4.90	5.10	-
E	6.40 BSC		
E1	4.30	4.50	-
e	0.65 BSC		
L	0.45	0.75	-
L1	1.00 REF		
L2	0.25 BSC		
R / R1	0.09	-	-
X	-	-	1.350
Y	-	-	1.050
θ	0°	8°	-
θ1	5°	15°	-
θ2	0°	-	-
All Dimensions in mm			

Suggested Pad Layout



Dimensions	Value (in mm)
C	0.650
X	0.350
X1	4.900
Y	1.400
Y1	6.800

Note: The suggested land pattern dimensions have been provided for reference only, as actual pad layouts may vary depending on application. These dimensions may be modified based on user equipment capability or fabrication criteria. A more robust pattern may be desired for wave soldering and is calculated by adding 0.2 mm to the 'Z' dimension. For further information, please reference document IPC-7351A, Naming Convention for Standard SMT Land Patterns, and for International grid details, please see document IEC, Publication 97.


Note: For high voltage applications, the appropriate industry sector guidelines should be considered with regards to creepage and clearance distances between device Terminals and PCB tracking.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.


16-U-QFN1826 (PB)

Package Outline Dimensions



U-QFN1826-16 (Type A)			
Dim	**Min**	**Max**	**Typ**
A	0.45	0.55	0.50
A1	0.00	0.05	0.02
A3	--	--	0.127
b	0.15	0.25	0.20
b1	0.10	0.20	0.15
D	1.75	1.85	1.80
E	2.55	2.65	2.60
e	--	--	0.40
L	0.35	0.45	0.40
L1	0.45	0.55	0.50
z	--	--	0.20
aaa	0.250		
bbb	0.100		
ccc	0.100		
All Dimensions in mm			

Suggested Pad Layout




Dimensions	Value (in mm)
C	0.400
C1	1.200
X	0.200
X1	0.500
X2	2.250
X3	2.750
Y	0.600
Y1	1.400


© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

16-V-QFN3525 (ZSA16)

Package Outline Dimensions






OPTION A
(Bottom View)

OPTION B
(Bottom View)

V-QFN3525-16 Standard			
Dim	Min	Max	Typ
A	0.75	0.90	--
A1	0.00	0.05	0.02
A3	--	--	0.203
b	0.20	0.30	0.25
D	3.45	3.55	3.50
D2	1.90	2.10	2.00
E	2.45	2.55	2.50
E2	0.90	1.10	1.00
e	0.50 BSC		
k	--	--	0.35
L	0.35	0.45	0.40
aaa	0.250		
bbb	0.100		
ccc	0.100		
All Dimensions in mm			

Suggested Pad Layout




Dimensions	Value (in mm)
C	0.500
G	0.250
X	0.350
X1	2.100
X2	2.850
X3	3.800
Y	0.600
Y1	1.100
Y2	0.850
Y3	2.800

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.


16-V-QFN4035 (ZD16)

Package Outline Dimensions



V-QFN4035-16			
Dim	Min	Max	Typ
A	0.80	1.00	0.90
A1	---	0.05	---
A3	---	---	0.203
b	0.20	0.30	0.25
D	3.95	4.05	4.00
D2	2.45	2.65	2.55
E	3.45	3.55	3.50
E2	1.95	2.15	2.05
e	1.50 BSC		
e1	0.50 BSC		
L	0.35	0.45	0.40
All Dimensions in mm			

Suggested Pad Layout



Dimensions	Value (in mm)
C	0.500
C1	0.150
X	0.600
X1	2.650
X2	4.300
Y	0.300
Y1	2.150
Y2	3.800

For latest package information:
See http://www.diodes.com/design/support/packaging/pericom-packaging/packaging-mechanicals-and-thermal-characteristics/.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Mechanical Data

TSSOP-16 (T16)
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish - Mate Tin Plated Leads. Solderable per MIL-STD-202, Method 208 e3
- Weight: 0.054811 grams (Approximate)

U-QFN1826-16 (PB)
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish - NiPdAu Nickel Palladium Gold. Solderable per MIL-STD-202, Method 208 e4
- Weight: 0.00639 grams (Approximate)

V-QFN3525-16 (ZSA16)
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish - NiPdAu Nickel Palladium Gold, Solderable per MIL-STD-202, Method 208 e4
- Weight: 0.0143 grams (Approximate)

V-QFN4035-16 (ZD16)
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish - NiPdAu Nickel Palladium Gold, Solderable per MIL-STD-202, Method 208 e4
- Weight: 0.03454 grams (Approximate)

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.
All other trademarks are the property of their respective owners.
© 2026 Diodes Incorporated. All Rights Reserved.

www.diodes.com

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.