












Capacitor Ordering Information Guide

KEMET makes it possible.

Electronic Components
KEMET
CHARGED.

Downloaded from Arrow.com.

Electronic Components

KEMET

CHARGED.®

Downloaded from Arrow.com.

Why Choose KEMET

KEMET Electronics Corporation is a leading global supplier of electronic components. We offer our customers the broadest selection of capacitor technologies in the industry, along with an expanding range of electromechanical devices, electromagnetic compatibility solutions and supercapacitors. Our vision is to be the preferred supplier of electronic component solutions for customers demanding the highest standards of quality, delivery and service.

Downloaded from Arrow.com.

Downloaded from Arrow.com.

TABLE OF CONTENTS

Aluminum Capacitors

Axial Leads 9
Radial Crown 10
Screw Terminal 11
Snap-In 13
Solder Pin/Tag 16
Single-Ended 16
Surface Mount 18
Motor Start 20

Ceramic Capacitors

Surface Mount 23
- Commercial Grade 23
- Flex Mitigation 25
- Automotive Grade 28
- High Reliability Commercial Off-The-Shelf (COTS) 33
- SnPb End Metallization 34
- Bulk Capacitance 37
- High Temperature 38
- High Voltage 41
- Aerospace & Defense 44
- RF & Microwave 46

Leaded 47
- Commercial Grade 47
- High Temperature 49
- High Voltage 52
- Aerospace & Defense 53

Disc 56
- Safety 56
- Commercial Grade 59

Film Capacitors

Through-Hole 61
- General Purpose 61
  - Metallized Polyester 61
  - Metallized Paper & Polyphenylene Sulfide 63
- Pulse & AC 64
  - Single Metallized Polypropylene 64
  - Double Metallized Polypropylene 66
  - Film/Foil Polypropylene 66
- Safety/EMI 67
  - X1 Class 67
  - X2 Class 70
  - Y1 Class 73
  - Y2 Class 74
  - Multiple X & Y 76

Downloaded from Arrow.com.

Film Capacitors (cont.)

Surface Mount 78
Polyester (PET) 78
Polyethylene Naphthalate (PEN) 79
Metallized Polyphenylene Sulfide (PPS) 81
Y2 Class 82
Power & Application Optimized 83
Power Film 83
Axial 83
Radial 84
Screw/Faston Terminal 85
Motor Run Applications 87
Screw/Faston Terminal 87
High Voltage Transient Suppression 88
Radial 88
Low Voltage Transient Suppression 90
Radial 90
Capacitive AC Power Supply 91
Radial 91

Supercapacitors

Small Cell 95
Radial 95
Surface Mount 96
Large Cell 97
Snap-In 97
Screw Terminal 97
Bank Module 97

Tantalum Capacitors

Surface Mount 99
Standard Tantalum 99
Polymer Tantalum KEMET Organic Capacitor (KO-CAP) 101
Polymer Aluminum Organic Capacitor (AO-CAP) 104
High Temperature 104
High Reliability Commercial Off-The-Shelf (COTS) 105
MIL–PRF CWR Style 109
Fused 112
Automotive Grade 113
Space Grade 115
Through-Hole 117
Hermetically Sealed Axial 117
Radial Dipped 125
Molded Axial 126
Molded Radial 127

Downloaded from Arrow.com.

Downloaded from Arrow.com.

Aluminum Capacitors

ALUMINUM CAPACITORS							
Axial Leads	**Radial Crown**	**Screw Terminal**	**Snap-In**	**Solder Pin/Tab**	**Single-Ended**	**Surface Mount**	**Motor Start**
PEG124 Very Long Life 105°C & 125°C 10 – 450 VDC	PEH126 High Ripple Current 150°C 25 – 63 VDC	ALS30/31 High CV Value & Long Life 85°C 25 – 500 VDC	ALC10 Long Life 85°C 35 – 550 VDC	ALP/T 20/21 Low ESR 85°C 40 – 450 VDC	ESK General Purpose 85°C 6.3 – 450 VDC	A700 Polymer Aluminum 125°C 2 – 16 VDC	MS/MD 60°C / 70°C 120 – 300 VAC
PEG126 High Ripple Current 150°C 25 – 63 VDC	PEH220 High Ripple Current 150°C 25 – 63 VDC	ALS32/33 High CV Value & Long Life 85°C 350 – 500 VDC	ALC10S Slit Foil Audio 85°C 50 – 100 VDC	ALP/T 22/23 High Ripple 85°C 40 – 450 VDC	ESH High CV 105°C 6.3 – 500 VDC	EDH Gerneral Purpose 105°C 6.3 – 100 VDC	
PEG127 High Ripple Current 150°C 25 – 63 VDC	PEH225 High Ripple Current 125°C & 150°C 25 – 63 VDC	ALS36/37 High Ripple Current 85°C 25 – 500 VDC	ALC40 High Ripple Current 105°C 25 – 500 VDC	ALN20S T-Network 85°C 50 & 100 VDC	ESC Low ESR 105°C 6.3 – 100 VDC	EDK General Purpose 85°C 4 – 450 VDC	
PEG130 Very Long Life 105°C 25 – 63 VDC	PEH226 High Ripple Current 150°C 25 – 63 VDC	ALS40/41 High CV Value 105°C 25 – 500 VDC	PEH506 Low ESR & ESL 85°C 35 – 450 VDC		ESG High Ripple Current 105°C 160 – 450 VDC	EEV Ultra-Low Impedance 105°C 6.3 – 50 VDC	
PEG220 Very High Ripple Current 150°C 25 – 63 VDC		ALS42/43 High CV Value 105°C 350 – 450 VDC	PEH526 Automotive 125°C 25 – 80 VDC		ESY Low Impedance 105°C 6.3 – 100 VDC	EXV Ultra-Low Impedance 105°C 6.3 – 50 VDC	
PEG225 Extremely High Ripple Current 125°C & 150°C 25 – 63 VDC		ALS60/61 High CV Value 85°C 550 VDC	PEH532 Low ESR & ESL 105°C 35 – 450 VDC		ESW Low Impedance 105°C 6.3 – 100 VDC		
PEG226 Extremely High Ripple Current 150°C 25 – 63 VDC		PEH169 Low ESR 85°C 10 – 450 VDC	PEH534 Low ESR & ESL 105°C 35 – 450 VDC		EST Long Life 105°C 6.3 – 63 VDC		
		PEH169 Low ESR & ESL 105°C 10 – 350 VDC	PEH536 Low ESR & ESL 105°C 35 – 450 VDC		EAK Long Life 125°C 10 – 63 VDC		
		PEH200 High CV Value 85°C 25 – 500 VDC	ELH Low Impedance 85°C 6.3 – 450 VDC				
		PEH205 High Ripple 125°C 16 – 100 VDC	ELG General Purpose 105°C 6.3 – 450 VDC				

Downloaded from Arrow.com.

Axial Leads

PEG124 Series Very Long Life 105°C & 125°C, 10 – 450 VDC

Capacitance Range: 1 to 4,700 µF • **Temperature Range:** −40°C to +105°C and −40°C to +125°C • **Lifetime:** 27,500 Hours



PEG124	E		F	410	0	Q	T1
Series	Voltage (VDC)		Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Packaging
Axial Aluminum Electrolytic	E= 10 G = 16 H = 25 K = 4 M = 63	P = 100 R = 200 U = 350 V = 400 Y = 450	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard A-Z = High Performance	Q = -10 +30% M = ±20% T = -10 +50%	See Ordering Options Table

PEG126 Series High Ripple Current 150ºC, 25 – 63 VDC

Capacitance Range: 250 to 4,000 µF • **Temperature Range:** −40°C to +150°C • **Lifetime:** D=16 6,300 Hours, D=20 8,400 Hours



PEG126	H	F	368	E	Q	E1
Series	Voltage (VDC)	Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Packaging
Axial Aluminum Electrolytic	H = 25 K 4 M = 63	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits.	E = Standard	Q = -10 +30% M = ±20%	E1 = Bulk

PEG127 Series High Ripple Current 150ºC, 25 – 63 VDC

Capacitance Range: 33 to 1,300 µF **Tempe ature Range:** −40°C to +150°C • **Lifetime:** 1,600 Hours



PEG127	H	A	318	0	Q	T1
Series	Voltage (VDC)	Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Packaging
Axial Aluminum Electrolytic	H = 25 K = 40 M = 63	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	Q = -10 +30%	See Ordering Options Table

PEG130 Series Very Long Life 105ºC, 25 – 63 VDC

Capacitance Range: 900 to 6,300 µF • **Temperature Range:** −40°C to +150°C • **Lifetime:** 160,000 Hours



PEG130	H	H	436	0	Q	L1
Series	Voltage (VDC)	Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Packaging
Axial Aluminum Electrolytic	H = 25 K = 40 M = 63	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	Q = -10 +30%	See Ordering Options Table

PEG220 Series Very High Ripple Current 150ºC, 25 – 63 VDC

Capacitance Range: 250 to 4,700 µF • **Temperature Range:** −40°C to +150°C • **Lifetime:** 2,000 Hours



PEG220	H	F	415	0	Q	E1
Series	Voltage (VDC)	Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Packaging
Axial Aluminum Electrolytic	H = 25 K = 40 M = 63	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	Q = -10 +30% M = ±20%	E1 = Bulk

Downloaded from Arrow.com.

Axial Leads (cont.)

PEG225 Series Extremely High Ripple Current 125°C & 150°C, 25 – 63 VDC

Capacitance Range: 470 to 6,300 µ • **Temperature Range:** −40°C to +125°C (at U_R) and −40°C to +150°C (at reduced voltage) • **Lifetime:** 2,000 Hours



PEG225	H	F	422	0	M
Series	Voltage (VDC)	Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance
Axial Aluminum Electrolytic	H = 25 K = 40 M = 63	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	Q = -10 +30% M = ±20%

PEG226 Series Extremely High Ripple Current 150°C, 25 – 63 VDC

Capacitance Range: 250 to 4,700 µF • **Temperature Range:** −40°C to +150°C • **Lifetime:** 2,000 Hours



PEG226	H	F	415	0	M
Series	Voltage (VDC)	Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance
Axial Aluminum Electrolytic	H = 25 K = 40 M = 63	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	Q = -10 +30% M = ±20%

Radial Crown

PEH126 High Ripple Current 150°C, 25 – 63 VDC

Capacitance Range: 250 to 4,000 µF • **Temperature Range:** −40°C to +150°C • **Lifetime:** 2,000 Hours



PEH126	H	F	368	E	Q
Series	Voltage (VDC)	Size Code	Capacitance Code (pF)	Version	Capacitance Tolerance
Radial Crown Aluminum Electrolytic with Soldering Star Termination	H = 25 K = 40 M = 63	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits.	E = Standard	Q = -10 +30%

PEH220 High Ripple Current 150°C, 25 – 63 VDC

Capacitance Range: 250 to 4,700 µF • **Temperature Range:** −40°C to +150°C • **Lifetime:** 2,000 Hours



PEH220	H	F	415	0	M
Series	Voltage (VDC)	Size Code	Capacitance Code (pF)	Version	Capacitance Tolerance
Radial Crown Aluminum Electrolytic with Soldering Star Termination	H = 25 K = 40 M = 63	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits	0 = Standard	Q = -10 +30% M = ±20%

PEH225 High Ripple Current 125ºC & 150ºC, 25 – 63 VDC

Capacitance Range: 470 to 6,300 µF • **Temperature Range:** −40°C to +125°C (at U_R) and −40°C to +150°C (at reduced voltage) • **Lifetime:** 2,000 Hours



PEH225	H	F	422	0	M
Series	Voltage (VDC)	Size Code	Capacitance Code (pF)	Version	Capacitance Tolerance
Radial Crown Aluminum Electrolytic with Soldering Star Termination	H = 25 K = 40 M = 63	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	Q = -10 +30% M = ±20%

Downloaded from Arrow.com.

Radial Crown (cont.)

PEH226 High Ripple Current 150ºC, 25 – 63 VDC

Capacitance Range: 250 to 4,700 µF • **Temperature Range:** −40°C to +150°C • **Lifetime:** 2,000 Hours



PEH226	H	F	415	0	M
Series	Voltage (DC)	Size Code	Capacitance Code (pF)	Version	Capacitance Tolerance
Radial Crown Aluminum Electrolytic with Soldering Star Termination	H = 25 K = 40 M = 63	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	Q = -10 +30% M = ±20%

Screw Terminal

ALS30/31 Series High CV Value & Long Life 85°C, 25 – 500 VDC

Capacitance Range: 100 to 680,000 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 40,000 Hours



ALS3	0	A	153	DA	025	
Series	Stud Option	Termination	Capacitance Code (µF)	Size Code	Voltage (VDC)	
Screw Terminal Aluminum Electrolytic	0 = Plain Can 1 = Threaded mounting stud	See Termination Table	First 2 digits equals first 2 significant figures, 3rd digit is the number of additional zeros.	See Dimension Table	025 = 25 040 = 40 063 = 63 100 = 100 200 = 200 250 = 250	350 = 350 400 = 400 415 = 415 450 = 450 500 = 500

ALS32/33 Series High CV Value & Long Life 85°C, 350 – 500 VDC

Capacitance Range: 220 to 18,000 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 40,000 Hours



ALS3	2	A	391	D2C	350
Series	Stud Option	Termination	Capacitance Code (µF)	Size Code	Voltage (VDC)
Screw Terminal Aluminum Electrolytic	2 = Plain Can 3 = Threaded mounting stud	See Termination Table	First 2 digits equals first 2 significant figures, 3rd digit is the number of additional zeros.	See Dimension Table	350 = 350 400 = 400 450 = 450 500 = 500

ALS36/37 Series High Ripple Current 85°C, 25 – 500 VDC

Capacitance Range: 150 to 470,000 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 40,000 Hours



ALS3	6	A	153	D2C	025	
Series	Stud Option	Termination	Capacitance Code (µF)	Size Code	Voltage (VDC)	
Screw Terminal Aluminum Electrolytic	6 = Plain Can 7 = Threaded mounting stud	See Termination Table	First 2 digits equals first 2 significant figures, 3rd digit is the number of additional zeros.	See Dimension Table	025 = 25 040 = 40 050 = 50 063 = 63 075 = 75 100 = 100 160 = 160	200 = 200 250 = 250 350 = 350 400 = 400 450 = 450 500 = 500

Downloaded from Arrow.com.

Screw Terminal (cont.)

ALS40/41 Series High CV Value 105°C, 25 – 500 VDC

Capacitance Range: 150 to 680,000 µF **Temperature Range:** −40°C to +105°C • **Lifetime:** 15,000 Hours



ALS4	0	A	153	DA	025	
Series	Stud Option	Termination	Capacitance Code (µF)	Size Code	Voltage (VDC)	
Screw Terminal Aluminum Electrolytic	0 = Plain Can 1 = Threaded mounting stud	See Termination Table	First 2 digits equals first 2 significant figures, 3rd digit is the number of additional zeros.	See Dimension Table	025 = 25 040 = 40 063 = 63 100 = 100 160 = 160 200 = 200	250 = 250 350 = 350 400 = 400 415 = 415 450 = 450 500 = 500

ALS42/43 Series High CV Value 105°C, 350 – 450 VDC

Capacitance Range: 1,000 to 15,000 µF • **Temperature Range:** −40°C to +105°C • **Lifetime:** 15,000 Hours



ALS4	2	A	102	K3C	350
Series	Stud Option	Termination	Capacitance Code (µF)	Size Code	Voltage (VDC)
Screw Terminal Aluminum Electrolytic	2 = Plain Can 3 = Threaded mounting stud	See Termination Table	First 2 digits equals first 2 significant figures, 3rd digit is the number of additional zeros	See Dimension Table	350 = 350 400 = 400 415 = 415 450 = 450

ALS60/61 Series High CV Value 85°C, 550 VDC

Capacitance Range: 560 to 3,300 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 20,000 Hours



ALS6	0	A	561	KE	550
Series	Stud Option	Termination	Capacitance Code (µF)	Size Code	Voltage (VDC)
Screw Terminal Aluminum Electrolytic	0 = Plain Can 1 = Threaded mounting stud	See Termination Table	First 2 digits equals first 2 significant figures, 3rd digit is the number of additional zeros.	See Dimension Table	550 = 550

PEH169 Series Low ESR 85°C, 10 – 450 VDC

Capacitance Range: 68 to 470,000 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 78,000 Hours



PEH169	E		A	510	V	M	U2
Series	Rated Voltage (VDC)		Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Stud Option
Screw Terminal Aluminum Electrolytic	E = 10 G = 16 H = 25 K = 40 M = 63 P = 100 Q = 160	R = 200 S = 250 U = 350 V = 400 O = 420 Y = 450	See Dimension Table	The second 2 digits indicate the 2 most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	Q = -10 +30% M = ±20%	U2 = Plain Can B2 = Threaded mounting stud

PEH169 Series Low ESR & ESL 105°C, 10 – 350 VDC

Capacitance Range: 100 to 330,000 µF • **Temperature Range:** −40°C to +105°C • **Lifetime:** 25,000 Hours



PEH169	E		A	468	0	Q	U2
Series	Rated Voltage (VDC)		Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Stud Option
Screw Terminal Aluminum Electrolytic	E = 10 G = 16 H = 25 K = 40 M = 63	P = 100 Q = 160 R = 200 S = 250 U = 350	See Dimension Table	The second 2 digits indicate the 2 most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	Q = -10 +30%	U2 = Plain Can B2 = Threaded mounting stud

Downloaded from Arrow.com.

Screw Terminal (cont.)

PEH200 Series High CV Value 85°C, 25 – 500 VDC

Capacitance Range: 100 to 330,000 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 60,000 Hours



PEH200	H		A	515	0	M	U2
Series	Voltage (VDC)		Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Stud Option
Screw Terminal Aluminum Electrolytic	H = 25 K = 40 M = 63 P = 100 S = 250 U = 350	X = 385 V = 400 O = 420 Y = 450 Z = 500	See Dimension table	The second 2 digits indicate the 2 most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	Q = -10 + 30% M = ±20%	U2 = Plain Can B2 = Threaded mounting stud

PEH205 Series High Ripple 125°C, 16 – 100 VDC

Capacitance Range: 1,500 to 390,000 µF • **Temperature Range:** −40°C to +125°C • **Lifetime:** 6,000 Hours



PEH205	G	A	518	0	Q	U3
Series	Voltage (VDC)	Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Stud Option
Screw Terminal Aluminum Electrolytic	G = 16 H = 25 K = 40 L = 55 M = 63 P = 100	See Dimension Table	The second 2 digits indicate the 2 most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	Q = -10 + 30%	U3 = Plain Can B3 = Threaded mounting stud

Snap-In

ALC10 Series Long Life 85°C, 35 – 550 VDC

Capacitance Range: 56 to 82,000 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 29,000 Hours



ALC10	A	392	BB	040	
Series	Termination	Capacitance Code (µF)	Size Code	Rated Voltage (VDC)	
Snap In type Aluminum Electrolytic	See Termination Table	First two digits represent significant figures. Third digit specifies number of zeros.	See Dimension Table	035 = 35 040 = 40 063 = 63 100 = 100 200 = 200 250 = 250	350 = 350 400 = 400 450 = 450 500 = 500 550 = 550

ALC10S Series Slit Foil Audio 85°C, 50 – 100 VDC

Capacitance Range: 10,000 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 29,000 Hours



ALC10	S	110 2	DF
Series	Construction	Unique Sequential Number	Size Code
Snap-In type Aluminum Electrolytic	S = Slit foil		See Dimension Table

Downloaded from Arrow.com.

Snap-In (cont.)

ALC40 Series High Ripple Current 105°C, 25 – 500 VDC

Capacitance Range: 47 to 120,000 µF **Temperature Range:** −40°C to +105°C • **Lifetime:** 14,000 Hours



ALC40	A	822	BB	025	
Series	Termination	Capacitance Code (µF)	Size Code	Voltage (VDC)	
Snap-In type Aluminum Electro ytic	See Termination Table	First two digits equals first two significant figures, third digit is the number of additional zeros.	See Dimension Table	025 = 25 040 = 40 063 = 63 100 = 100 200 = 200	250 = 250 350 = 350 400 = 400 450 = 450 500 = 500

PEH506 Series Low ESR & ESL 85°C, 35 – 450 VDC

Capacitance Range: 68 to 27,000 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 6,000 Hours



PEH506	J	AC	433	0	M	2
Ser es	Voltage (VDC)	Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Termination
Snap-In type Aluminum Electrolytic	J = 35 M = 63 P = 100 R = 200 S = 250 U = 350 V = 400 Y = 450	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	M = ±20%	See Termination Table

PEH526 Series Automotive 125°C, 25 – 63 VDC

Capacitance Range: 820 to 6,800 µF • **Temperature Range:** −40°C to +125°C • **Lifetime:** 20,000 Hours



PEH526	H	AB	427	0	M	3
Series	Voltage (VDC)	Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Termination
Snap-In type Aluminum Electrolytic	H = 25 K = 40 M = 63	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	M = ±20%	3 = 3 Pin

PEH532 Series Low ESR & ESL 105°C, 35 – 450 VDC

Capacitance Range: 68 to 27,000 µF • **Temperature Range:** −40°C to +105°C • **Lifetime:** 2,000 Hours



PEH532	J	AC	433	0	M	2
Series	Voltage (VDC)	Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Termination
Snap-In type Aluminum Electrolytic	J = 35 M = 63 P = 100 R = 200 S = 250 U = 350 V = 400 Y = 450	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	M = ±20%	See Termination Table

Downloaded from Arrow.com.

Snap-In (cont.)

PEH534 Series Low ESR & ESL 105°C, 35 – 450 VDC

Capacitance Range: 150 to 22,000 µF • **Temperature Range:** −40°C to +105°C • **Lifetime:** 4,000 Hours



PEH534	J	BC	456	0	M	2
Series	Voltage (VDC)	Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Termination
Snap-In type Aluminum Electrolytic	J = 35 M = 63 P = 100 R = 200 S = 250 U = 350 V = 400 Y = 450	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value The first digit indicates the total number digits	0 = Standard	M = ±20%	See Termination Table

PEH536 Series Low ESR & ESL 105°C, 35 – 450 VDC

Capacitance Range: 47 to 18,000 µF • **Temperature Range:** −40°C to +105°C • **Lifetime:** 6,000 Hours



PEH536	J	AD	439	0	M	2
Series	V ltage (VDC)	Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Termination
Snap-In type Aluminum Electrolytic	J = 35 M = 63 P = 100 R = 200 S = 250 U = 350 V = 4 0 Y = 450	See Dimension Table	The second two digits indicate the two most significant digits of the capacitance value. The first digit indicates the total number digits.	0 = Standard	M = ±20%	See Termination Table

ELH Series Low Impedance 85°C, 6.3 – 450 VDC

Capacitance Range: 47 to 120,000 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 2,000 Hours



ELH	159	M	6R3		A	Q1	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)		Electrical Parameters	Size Code	Packaging
Snap-In Aluminum Electrolytic	Dig ts 4 – 5 represent the first two digits of the capacitance value. The final digit indicates the number of zeros to be added.	M = ±20%	6R3 = 6.3 010 = 10 016 = 16 025 = 25 035 = 35 050 = 50 063 = 63 080 = 80	100 = 100 160 = 160 180 = 180 200 = 200 250 = 250 350 = 350 400 = 400 450 = 450	A = Standard	See Dimension Table	See Ordering Options Table

ELG Series General Purpose 105°C, 6 3 – 450 VDC

Capacitance Range: 47 to 82,000 µF • **Temperature Range:** −40°C to +105°C • **Lifetime:** 2,000 Hours



ELG	129	M	6R3		A	Q1	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)		Electrical Parameters	Size Code	Packaging
Snap-In Aluminum Electrolytic	Digits 4 – 5 represent the first two digits of the capacitance value. The final digit indicates the number of zeros to be added.	M = ±20%	6R3 = 6.3 010 = 10 016 = 16 025 = 25 035 = 35 050 = 50 063 = 63 080 = 80	100 = 100 160 = 160 180 = 180 200 = 200 250 = 250 350 = 350 400 = 400 450 = 450	A = Standard	See Dimension Table	See Ordering Options Table

Downloaded from Arrow.com.

Solder Pin/Tag

ALP20 and ALT20/21 Series Low ESR 85°C, 40 – 450 VDC

Capacitance Range: 22 to 150,000 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 26,000 Hours



ALP	20A	682	AB	010	
Series	Version	Capacitance Code (µF)	Size Code	Voltage (VDC)	
ALP = Solder pin ALT = Solder tag	20A = Standard 21A = Threaded Mounting Stud (ALT only)	First two digits represent significant figures. Third digit specifies number of zeros.	See Dimension Table	040 = 40 063 = 63 100 = 100 200 = 200	250 = 250 385 = 385 400 = 400 450 = 450

ALP22 and ALT22/23 Series High Ripple 85°C, 40 – 450 VDC

Capacitance Range: 22 to 150,000 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 26,000 Hours



ALP	22A	682	AB	010	
Series	Version	Capacitance Code (µF)	Size Code	Voltage (VDC)	
ALP Solder pin ALT = Solder tag	22A = Standard 23A = Threaded Mounting Stud (ALT only)	First two digits represent significant figures. Third digit specifies number of zeros.	See Dimension Table	040 = 40 063 = 63 100 = 100 200 = 200	250 = 250 385 = 385 400 = 400 450 = 450

ALN20S Series T-Network 85°C, 50 & 100 VDC

Capacitance Range: 10,000 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 18,000 Hours



ALN20	S	1053	DD
Series	Construction	Unique Sequential Number	Size Code
Snap-In type Aluminum Electrolytic	S = Slit foil		See Dimension Table

Single-Ended

ESK Series General Purpose 85°C, 6.3 – 450 VDC

Capacitance Range: 0.1 to 22,000 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 2,000 Hours



ESK	226	M	6R3		A	C3	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)		Electrical Parameters	Size Code	Packaging
Single-Ended Aluminum Electrolytic	Digits 4 – 5 represent the first two digits of the capacitance value. The final digit indicates the number of zeros to be added.	M = ±20%	6R3 = 6.3 010 = 10 016 = 16 025 = 25 035 = 35 050 = 50 063 = 63	100 = 100 160 = 160 200 = 200 250 = 250 350 = 350 400 = 400 450 = 450	A = Standard	See Dimension Table	See Ordering Options Table

Downloaded from Arrow.com.

Single-Ended (cont.)

ESH Series High CV 105°C, 6.3 – 450 VDC

Capacitance Range: 0.47 to 15,000 µ • **Tempera ure Range:** −40°C to +105°C • **Lifetime:** 2,000 Hours



ESH	107	M	6R3		A	C3	AA
Ser es	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)		Electrical Parameters	Size Code	Packaging
Single-Ended Aluminum Electrolytic	Digits 4 – 5 represent the first two digits of the capacitance value. The final digit indicates the number of zeros to be added.	M = ±20%	6R3 = 6.3 010 = 10 016 = 16 025 = 25 035 = 35 050 = 50 063 = 63	100 = 100 160 = 160 200 = 200 250 = 250 350 = 350 400 = 400 450 = 450	A = Standard	See Dimension Table	See Ordering Options Table

ESC Series Low ESR 105°C, 6.3 – 100 VDC

Capacitance Range: 4.7 to 15,000 µF • **Temperature Range:** −40°C to +105°C • **Lifetime:** 3,000 Hours



ESC	157	M	6R3	A	C3	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)	Electrical Parameters	Size Code	Packaging
Single-Ended Aluminum Electrolytic	Digits 4 – 5 represent the first two digits of the capacitance value. The final digit indicates the number of zeros to be added.	M = ±20%	6R3 = 6 3 010 = 10 016 = 16 025 = 25 035 = 35 050 = 50 063 = 63 100 = 100	A = Standard	See Dimension Table	See Ordering Options Table

ESG Series High Ripple Current 105°C, 160 – 450 VDC

Capacitance Range: 4.7 to 330 µF • **Temperature Range:** −40°C to +105°C • **Lifetime:** 5,000 Hours



ESG	336	M	160	A	H4	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)	Electrical Parameters	Size Code	Packaging
Single-Ended Aluminum Electrolytic	Digits 4 – 5 represent the first two digits of the capacitance value. The final digit indicates the number of zeros to be added.	M = ±20%	160 = 160 200 = 200 250 = 250 350 = 350 400 = 400 450 = 450	A = Standard	See Dimension Table	See Ordering Options Table

ESY Series Low Impedance 105°C, 6.3 – 100 VDC

Capacitance Range: 5.6 to 6,800 µF • **Temperature Range:** −40°C to +105°C • **Lifetime:** 5,000 Hours



ESY	396	M	6R3	A	B2	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)	Electrical Parameters	Size Code	Packaging
Single-Ended Aluminum Electrolytic	Digits 4 – 5 represent the first two digits of the capacitance value. The final digit indicates the number of zeros to be added.	M = ±20%	6R3 = 6 3 010 = 10 016 = 16 025 = 25 035 = 35 050 = 50 063 = 63 100 = 100	A = Standard	See Dimension Table	See Ordering Options Table

Downloaded from Arrow.com.

Single-Ended (cont.)

ESW Series Low Impedance 105°C, 6.3 – 100 VDC

Capacitance Range: 6.8 to 15,000 µF • **Temperature Range:** −40°C to +105°C • **Lifetime:** 5,000 Hours



ESW	226	M	6R3	A	C3	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)	Electrical Parameters	Size Code	Packaging
Single-Ended Aluminum Electrolytic	Digits 4 – 5 represent the first two digits of the capacitance value. The final digit indicates the number of zeros to be added.	M = ±20%	6R3 = 6 3 010 = 10 016 = 16 025 = 25 035 = 35 050 = 50 063 = 63 100 = 100	A = Standard	See Dimension Table	See Ordering Options Table

EST Series Long Life 105°C, 6.3 – 63 VDC

Capacitance Range: 6.8 to 15,000 µF • **Tempe ature Range:** −40°C to +105°C • **Lifetime:** 10,000 Hours



EST	157	M	6R3	A	C3	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)	Electrical Parameters	Size Code	Packaging
Single-Ended Aluminum Electrolytic	Digits 4 – 5 represent the first two digits of the capacitance value. The final digit indicates the number of zeros to be added.	M = ±20%	6R3 = 6 3 010 = 10 016 = 16 025 = 25 035 = 35 050 = 50 063 = 63	A = Standard	See Dimension Table	See Ordering Options Table

EAK Series Long Life 125°C, 10 – 63 VDC

Capacitance Range: 47 to 4,700 µF • **Temperature Range:** −40°C to +105°C • **Lifetime:** 5,000 Hours




EAK	227	M	010	A	G3	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)	Electrical Parameters	Size Code	Packaging
Single-Ended Aluminum Electrolytic	Digits 4 – 5 represent the first two digits of the capacitance value. The final digit indicates the number of zeros to be added.	M = ±20%	010 = 10 016 = 16 025 = 25 035 = 35 050 = 50 063 = 63	A = Standard	See Dimension Table	See Ordering Options Table

Surface Mount

A700 Series Polymer Aluminum 125°C, 2 – 16 VDC

Capacitance Range: 6.8 to 560 µF • **Temperature Range:** −55°C to +125°C • **Lifetime:** 2,000 Hours



A	700	V	476	M	006	A	T	E018	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR Code	Packaging (C-Spec)
A = Aluminum	700 = Aluminum Polymer	D, V, X	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	002 = 2 2R5 = 2.5 004 = 4 006 = 6.3 008 = 8 010 = 10 12R = 12.5 016 = 16	A = N/A	T = 100% Matte Tin (Sn) plated	E = ESR Last three digits specify ESR in mΩ (018 = 18 mΩ)	Blank = 7" Reel 7280 = 13" Reel

Downloaded from Arrow.com.

Surface Mount (cont.)

EDH Series General Purpose 105°C, 6.3 – 100 VDC

Capacitance Range: 1.0 to 1,500 µF • **Temperature Range:** −40°C to +105°C • **Lifetime:** 2,000 Hours



EDH	226	M	6R3		A	9B	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)		Electrical Parameters	Size Code	Packaging
Sur ace Mount Aluminum Electrolytic	Dig ts 4 – 5 represent the first two digits of the capacitance value. The final digit indicates the number of zeros to be added	M = ±20%	6R3 = 6.3 010 = 10 016 = 16 025 = 25 035 = 35	050 = 50 063 = 63 100 = 100	A = Standard	See Dimension Table	AA = T&R

EDK Series General Purpose 85°C 4 – 100 VDC

Capacitance Range: 0.1 to 1,000 µF • **Temperature Range:** −40°C to +85°C • **Lifetime:** 2 000 Hours



EDK	226	M	004		A	9B	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)		Electrical Parameters	Size Code	Packaging
Surface Mount Aluminum Electrolytic	Digits 4 – 5 represent the first two digits of the capacitance value. The final digit indicates the number of zeros to be added.	M = ±20%	004 = 4 6R3 = 6.3 010 = 10 016 = 16 025 = 25 035 = 35	050 = 50 063 = 63 100 = 100	A = Standard	See Dimension Table	AA = Tape & Reel

EEV Series Ultra-Low Impedance 105°C, 6.3 – 35 VDC

Capacitance Range: 4.7 to 1,500 µF • **Temperature Range:** −40°C to +105°C • **Lifetime:** 2,000 Hours



EEV	226	M	6R3	A	9B	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)	Electrical Parameters	Size Code	Packaging
Surface Mount Aluminum Electrolytic	Digits 4 – 5 represent the first two digits of the capacitance value. The final digit indicates the number of zeros to be added.	M = ±20%	6R3 = 6.3 010 = 10 016 = 16 025 = 25 035 = 35	A = Standard	See Dimension Table	AA = Tape & Reel

EXV Series Ultra-Low Impedance 105°C, 6.3 – 50 VDC

Capacitance Range: 1 to 1,000 µF • **Temperature Range:** −40°C to +105°C • **Lifetime:** 5,000 Hours



EXV	226	M	6R3	A	9B	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)	Electrical Parameters	Size Code	Packaging
Surface Mount Aluminum Electrolytic	Digits 4 – 5 represent the first two digits of the capacitance value. The final digit indicates the number of zeros to be added.	M = ±20%	6R3 = 6 3 010 = 10 016 = 16 025 = 25 035 = 35 050 = 50	A = Standard	See Dimension Table	AA = Tape & Reel

Downloaded from Arrow.com.

Motor Start

MS/MD Series 60ºC/70°C, 120 – 260 VAC

Capacitance Range: 25 to 750 µF • **Temperature Range:** MS: −20°C to +60°C, MD: −20°C to +70°C • **Lifetime:** 500 Hours



080	MS	12	AA	M	A	1	STD
Capacitance Code (µF)	Rating	Voltage (VAC)	Size Code	Manufacturing Style	Capacitance Tolerance	Terminal Code	Version
Example: 080 = 80 µF 120 = 120 µF	MS = Motor start single rating MD = Motor start dual rating	12 = 120 22 = 220 26 = 260	See Dimension Table	M = Molded case	A = -0% +25% K = ±10%	1 = Double amp tag	STD = Standard

Downloaded from Arrow.com.

Downloaded from Arrow.com.

Ceramic Capacitors

CERAMIC SURFACE MOUNT CAPACITORS

Commercial Grade	Flex Mitigation	Automotive Grade	High Reliability Commercial Off-the-Shelf (COTS)	SnPb End Metallization	Bulk Capacitance	High Temperature (> 125°C)	High Voltage (> 500 V)	Aerospace & Defense	RF & Microwave
C0G 10 – 250 VDC	Open Mode Design X7R 16 – 200 VDC	C0G 10 – 250 VDC	C0G 10 – 250 VDC	C0G 10 – 250 VDC	KPS X7R 10 – 250 VDC	150 C X8R 25 –100 VDC	ArcShield™ Technology X7R 500 – 1,000 VDC	MIL-PRF-123 BP & BX 6.3 – 200 VDC	CBR Series Ultra High Q C0G 6.3 – 500 VDC
X7R 6.3 – 250 VDC	Floating Electrode X7R 6.3 – 250 VDC	X7R 6.3 – 250 VDC	X7R 6.3 – 250 VDC	X7R 6.3 – 250 VDC	KPS High Voltage X7R 500 – 630 VDC	150 C X8L 10 –50 VDC	C0G 500 – 3,000 VDC	GR900 BP & BX 16 – 200 VDC	
X5R 4 – 50 VDC	Flexible Termination C0G 10 – 250 VDC	Capacitor Array C0G 10 – 200 VDC		X5R 4 – 50 VDC	KPS High Temperature 150 C X8L 10 – 50 VDC	200 C C0G 10 – 200 VDC	X7R 500 – 3,000 VDC	MIL-PRF-55681 BP & BX 50 – 100 VDC	
Z5U 50 VDC & 100 VDC	Flexible Termination X7R 6.3 – 250 VDC	Capacitor Array X7R 10 – 200 VDC		COTS C0G 10 – 200 VDC	KPS MIL Series 50 – 1,000 VDC	HV-HT Series 200 C C0G 500 – 2,000 VDC	Flexible Termination C0G 500 – 3,000 VDC	DLA 03028 BR & BX 6.3 – 200 VDC	
Y5V 6.3 – 50 VDC	High Voltage Flexible Termination C0G 500 – 3,000 VDC	Open Mode Design X7R 16 – 200 VDC		COTS X7R 6.3 – 250 VDC		Flexible Termination 150 C X8R 25 – 100 VDC	Flexible Termination X7R 500 – 3,000 VDC	DLA 03029 BR & BX 6.3 – 100 VDC	
Telecom "Tip & Ring" X7R 250 VDC	High Voltage Flexible Termination X7R 500 – 3,000 VDC	Floating Electrode X7R 6.3 – 250 VDC		High Temperature X8R 25 – 100 VDC		175 C X7R 16 – 200 VDC	KPS X7R 500 – 630 VDC	DLA 05006 BP, BR & BX 10 – 200 VDC	
Capacitor Array C0G 10 – 200 VDC	Flexible Termination X8R 25 – 100 VDC	Flexible Termination X7R 6.3 – 250 VDC		High Temperature X8L 10 – 50 VDC		KPS 150 C X8L 10 VDC – 50 VDC	HV-HT Series 200 C C0G 500 – 2,000 VDC	DLA 05007 BP, BR & BX 10 – 200 VDC	
Capacitor Array X7R 10 – 200 VDC	Floating Electrode w/ Flexible Termination X7R 6.3 – 250 VDC	KPS X7R 10 – 250 VDC		Telecom "Tip & Ring" X7R 250 VDC		200 C High Voltage Pulse Discharge C0G 500 – 2,000 VDC	200 C High Voltage Pulse Discharge C0G 500 – 2,000 VDC	DLA 91019 BR 25 – 50 VDC	
	KPS X7R 10 – 250 VDC	High Voltage Flexible Termination X7R 500 – 3,000 VDC		Open Mode Design X7R 16 – 200 VDC			KPS HV Large Case C0G 500 – 10K VDC		
	KPS High Voltage X7R 500 – 630 VDC	KPS High Voltage X7R 500 – 630 VDC		Floating Electrode X7R 6.3 – 250 VDC			KPS HV Large Case X7R 500 – 10K VDC		
	KPS High Temperature 150 C X8L 10 – 50 VDC	KPS High Temperature 150 C X8L 10 – 50 VDC		Flex ble Termination X7R 6.3 – 250 VDC					
		Flexible Termination C0G 10 – 250 VDC		Floating Electrode w/ Flex ble Termination X7R 6.3 – 250 VDC					
		Flexible Termination X8R 25 – 100 VDC							
		Floating Electrode w/ Flexible Termination X7R 6.3 – 250 VDC							
		High Temperature X8R 25 – 100 VDC							
		High Temperature 150 C X8L 10 – 50 VDC							
		High Voltage X7R 500 – 3,000 VDC							
		High Voltage C0G 500 – 3,000 VDC							
		High Voltage Flexible Termination C0G 500 – 3,000 VDC							

CERAMIC DISC CAPACITORS

Safety	Commercial Grade
900 Radial Encapsulated AC Type X1 400 VAC/Y2 250 VAC	KHA X7R 1,000 – 2,000 VDC
900 Radial Encapsulated AC Type X1 440 VAC/Y2 300 VAC	KHB Y5P 1,000 – 2,000 VDC
900 Radial Encapsulated AS Type X1 760 VAC/Y1 500 VAC	KHC SL 1,000 – 2,000 VDC
900 Radial Encapsulated AH Type X1 400 VAC/Y1 250 VAC	
900 Radial Encasulated AH Type X1 400 VAC/Y1 400 VAC	
ERO610 Radial AC Type X1 440 VAC/Y2 250 VAC	
ERK610 Radial AC Type X1 440 VAC/Y2 300 VAC	
ERP610 Radial AC Type X1 760 VAC/Y2 500 VAC	
KJN Y5P, Y5U & Y5V Y1 250/400 VAC/ X1 440 VAC	
KJY Y5P, Y5U & Y5V Y2 250 VAC/ X1 400 VAC	

CERAMIC LEADED CAPACITORS

Commercial Grade	High Temperature (> 125°C)	High Voltage (> 500 V)	Aerospace & Defense
Aximax C0G, X7R & Z5U Axial Conforma ly Coated 25 – 250 VDC	HT 200 C C0G & X7R Radial Molded 50 – 200 VDC	HV 300 Series Goldmax C0G & X7R Radial Conformally Coated 500 – 3,000 VDC	MIL-PRF-123 BP & BX Molded Radial 50 – 100 VDC
300 Series Goldmax C0G, X7R & Z5U Radial Conformally Coated 25 – 250 VDC	HT/HP 200 C C0G & X7R Axial & Radial 25 – 200 VDC	HV 600 Series Goldmax C0G & X7R Radial Conformally Coated 500 – 3,000 VDC	GR900 High Reliability BP & BX Molded Radial 50 – 200 VDC
Molded Axial & Radial C0G & X7R 50 – 200 VDC	HV 200 C C0G & X7R Radial Conformally Coated 500 – 4,000 VDC	HV C0G & X7R Radial Conformally Coated 500 –10,000 VDC	MIL-PRF-20 CG Molded Axial & Radial 50 – 200 VDC
	ACR/ACA 200 C Axial & Radial C0G 50 – 100 VDC		MIL-C-11015/ MIL-PRF-39014 BX & BR Molded Axial 50 – 100 VDC
	ARR/ARA 200 C Axial & Radial X7R 50 – 100 VDC		MIL-C-11015/ MIL-PRF-39014 BX (X7R) Molded Radial 50 – 200 VDC
	TCR/TCA 260 C Axial & Radial C0G 50 – 100 VDC		HV MIL-PRF-46467 Equivalent BP, BR & BZ 500 – 5,000 VDC
	TRR/TRA 260 C Axial & Radial X7R 50 – 100 VDC		HS High Voltage Space Quality C0G & X7R Radial Conformally Coated 500 – 10,000 VDC
	VCR 200 C Axial & Radial C0G 500 – 5,000 VDC		SCR/SCA Standard Axial & Radial C0G 50 – 200 VDC
	VRR 200 C Axial & Radial X7R 500 – 5,000 VDC		SRR/SRA Standard Axial & Radial X7R 50 – 200 VDC
	Aximax 150 C X8L & X8R Molded Axial 25 – 200 VDC		


Downloaded from Arrow.com.

Ceramic Capacitors
Surface Mount

Commercial Grade

C0G Dielectric, 10 – 250 VDC


Capacitance Range: 0.50 pF to 0 47 µF • **Temperature Range:** 55°C to +125°C



C	1206	C	104	J	3	G	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series[1]	Capacitance Code (pF)	Capacitance Tolerance[2]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[3]	Packaging/Grade (C-Spec)
	0201 0402 0603 08 5 1206 1210 1808 1812 1825 2220 2225	C = Standard	2 significant digits + number of zeros. Us 9 for 0 9 9 pF Use 8 for 0 5 99 pF e g , 2 2 pF = 229 e.g., 0.5 pF = 508	B = ±0.10 pF C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	G = C0G	A = N/A	C = 100% Matte Sn	See "Packaging C-Spec Order ng Options Table" below

X7R Dielectric, 6.3 – 250 VDC


Capacitance Range: 10 pF to 47 µF • **Temperature Range:** −55°C to +125°C



C	1206	C	106	M	4	R	A	C	TU
Ceramic	Case Size (L" x W")	Specificatio / Series[1]	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/ Grade (C-Spec)
	0402 0603 0805 1206 1210 1808 1812 1825 2220 2225	C = Standard	Two significant digits + number of zeros.	J = ±5% K = ±10% M = ±20%	9 = 6 3 8 = 10 4 = 16 3 = 25 6 = 35 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	A = N/A	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

X5R Dielectric, 4 – 50 VDC

Capacitance Range: 0.01 µF to 100 µF **Temperature Range:** −55°C to +85°C




C	1206	C	107	M	9	P	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C–Spec)
	0201 0402 0603 0805 1206 1210	C = Standard	Two significant digits + number of zeros.	K = ±10% M = ±20%	7 = 4 9 = 6 3 8 = 10 4 = 16 3 = 25 6 = 35 5 = 50	P = X5R	A = N/A	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

Commercial Grade (cont.)

Z5U Dielectric, 50 & 100 VDC


Capacitance Range: 6,800 pF to 2 2 µF • **Tempe ature Range:** −10°C to +85°C



C	1825	C	225	M	5	U	A	C	TU
Ceramic	Case Size (" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0805 2 6 1210 1812 1825 2225	C = Standard	2 significant di its number of zeros	M = ±20% = 0%/-20	5 = 50 1 = 100	U = Z5U	A = N/A	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

Y5V Dielectric, 6.3 – 50 VDC


Capacitance Range: 0.022 µF o 22 µF **Temperature Range:** −30°C to +85°C



C	1210	C	226	Z	4	V	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish	Packaging/Grade (C-Spec)
	0402 0603 0805 206 1210	C = Standard	significant digits + number of zeros	Z = +80%/-20% M = ±20%	9 = 6 3 8 = 10 4 = 16 3 = 25 5 = 50	V = Y5V	A = N/A	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

Telecom "Tip and Ring" X7R Dielectric, 250 VDC


Capacitance Range: 180 pF to 1.2 µF • **Tempe ature Range:** −55°C to +125°C



C	1825	C	105	K	A	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0805 1206 1210 1812 1825 2220 2225	C = Standard X = Flexible Termination	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	A = 250	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Capacitor Array, C0G Dielectric, 10 – 200 VDC

Capacitance Range: 10 pF to 2,200 pF **Temperature Range:** −55°C to +125°C




CA	06	4	X	104	K	4	G	A	C	TU
Ceramic Array	Case Size (L" x W")[1]	Number of Capacitors	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	05 = 0508 06 = 0612	2 = 2 4 = 4	X = Flexible Termination	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200	G = C0G	A = N/A	C = 100% Matte Sn L = SnPb (5% minimum Pb content)	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

Commercial Grade (cont.)

Capacitor Array, X7R Dielectric, 10 – 200 VDC

Capacitance Range: 330 pF to 0 22 µF **Te pe ature Range:** −55°C to +125°C




CA	06	4	X	104	K	4	R	A	C	TU
Ceramic Array	Case Size (L" x W")[1]	Number of Capacitors	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	05 = 0508 06 = 0612	2 = 2 4 = 4	X = Flexible Termination	2 significant digits + umber of zeros	J = ±5% K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% minimum Pb content)	See "Packaging C-Spec Ordering Options Table" below

Flex Mitigation

Open Mode Design (FO-CAP), X7R Dielectric, 16 – 200 VDC (Commercial & Automotive Grade)


Capacitance Range: 1,000 pF to 6.8 µF • **Temperature Range:** −55°C to +125°C



C	1210	J	685	K	3	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0805 1206 1210 1812	F = Open Mode J = Open Mode with Flexible Termination	Two significant digits + number of zeros	K = ±10% M = ±20%	4 = 16 3 = 25 5 = 50 1 = 100 2 = 200	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Floating Electrode Design (FE-CAP), X7R Dielectric, 6.3 – 250 VDC (Commercial & Automotive Grade)

Capacitance Range: 150 pF to 0.22 µF **Temperature Range:** −55°C to +125°C




C	0805	S	104	K	5	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/ Grade (C-Spec)
	0402 0603 0805 1206 1210 1812	S = Floating Electrode	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	9 = 6.3 8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

Flex Mitigation (cont.)

Flexible Termination System (FT-CAP), C0G Dielectric, 10 – 250 VDC (Commercial & Automotive Grade)


Capacitance Range: 0.5 pF to 0.47 µF • **Temperatu e Range:** −55°C to +125°C



C	1206	X	563	J	3	G	A	C	TU
Ceramic	Case Size (L" x W")	Specifi t o / S ries	Capacit c Code (pF)	Capaci ance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0603 0805 1206 1210 1 12 1825 2220 2225	X = Fl xible Termination	2 sig ifi ant digi s + number of zeros Use 9 for 1.0 – 9.9 pF Use 8 for 0.5 – 99 pF e , 2 pF = 229 e g , 0.5 pF = 508	B = ±0 10 pF C = ±0 25 pF D = ±0 5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	G = C0G	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Flexible Termination System (FT-CAP) X7R Dielectric, 6.3 – 250 VDC (Commercial & Automotive Grade)


Capacitance Range: 180 pF to 22 µF • **Temperature Range:** −55°C to +125°C



C	1206	X	106	K	4	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)[2]
	0603 0805 1206 1210 1808 1812 1825 2220 2225	X = Flexible Termination	2 significant digits + number of zeros	J = ±5% K ±10% M = ±20%	9 = 6.3 8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

High Voltage with Flexible Termination System (HV FT-CAP), C0G Dielectric, 500 – 3,000 VDC (Commercial & Automotive Grade)

Capacitance Range: 1 pF to 0.039 µF • **Tempe ature Range:** −55°C to +125°C




C	2225	X	393	J	C	G	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0805 1206 1210 1808 1812 1825 2220 2225	X= Flexible Termination	Two significant digits + number of zeros.	B = ±0.10 pF C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000 Z = 2,500 H = 3,000	G = C0G	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

Flex Mitigation (cont.)

High Voltage with Flexible Termination System (HV FT-CAP) X7R Dielectric, 500 – 3,000 VDC (Commercial & Automotive Grade)


Capacitance Range: 10 pF to 0.33 µF • **Tempe ature Range:** −55°C to +125°C



C	1210	X	154	K	C	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Die ectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0603 0805 1206 121 1808 1812 1825 2220 2225	X = Flexible Termination	Two significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000 Z = 2,500 H = 3,000	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Flexible Termination System (FT-CAP) Ultra-Stable X8R Dielectric, 25 – 100 VDC (Commercial & Automotive Grade)


Capacitance Range: 430 pF to 0 22 µF **Tempe at re Range:** −55°C to +150°C



C	1206	X	104	J	3	H	A	C	AUTO
Ceramic	Case Size (L" x W")	Specification/ Series	Capacita ce Code (pF)	Capacitance Tolerance	Reated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0603 0805 1206 12 0 1812	X = Flexible Termination	2 significant digits + number of ze os	F = ±1% G = ±2% J = ±5% K = ±10% M ±20%	3 = 25 5 = 50 1 = 100	H = Ultra-Stable X8R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Floating Electrode Design with Flexible Termination System (FF-CAP), X7R Dielectric, 6.3 – 250 VDC (Commercial & Automotive Grade)

Capacitance Range: 180 pF to 0 22 µF **Temperature Range:** −55°C to +125°C



C	0805	Y	104	K	5	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/ Grade (C-Spec)
	0603 0805 1206 1210 1812	Y = Floating Electrode with Flexible Termination	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	9 = 6 3 8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

KPS Series, X7R Dielectric, 10 – 250 VDC (Commercial Grade)

Capacitance Range: 0.1 µF to 47 µF • **Temperature Range:** −55°C to +125°C



C	2220	C	106	M	5	R	2	C	7186
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/Design	Leadframe Finish[2]	Packaging/Grade (C-Spec)
	1210 1812 2220	C = Standard	Two significant digits + number of zeros	K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 A = 250	R = X7R	1 = KPS Single Chip Stack 2 = KPS Double Chip Stack	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

Flex Mitigation (cont)

KPS Series, High Voltage, X7R Dielectric, 500 – 630 VDC (Commercial Grade)

Capacitance Range: 0.047 µF t 1 0 µF • **T p a re Range:** −55°C to +125°C



C	2220	C	105	M	C	R	2	C	7186
Ceramic	Case Size (L x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Lead rame Finish[2]	Packaging/Grade (C-Spec)
	2220	C = Standar	2 signi cant d gi s + number of zeros.	K = ±10% M = ±20%	C = 500 B = 630	R X7R	1 = KPS Single Chip Stack 2 = KPS Double Chip Stack	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

KPS HT Series, High Temperature 150°C, X8L Dielectric, 10 – 50 VDC (Commercial Grade)

Capacitance Range: 0.47 µF to 47 µF • **Temperature Range:** −55°C to +150°C




C	2220	C	476	M	8	N	2	C	7186
Ceramic	Case Size (L"x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Leadframe Finish	Packaging/Grade (C-Spec)
	1210 2220	C = Standa d	2 significant dig ts + number of zer s	K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50	N = X8L	1 = KPS Single Chip Stack 2 = KPS Double Chip Stack	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

Automotive Grade

C0G Dielectric, 10 – 250 VDC


Capacitance Range: 0.5 pF to 0.47 µF • **Temperature Range:** −55°C to +125°C



C	1206	C	104	J	3	G	A	C	AUTO
Ceramic	Case Size (L" x W")	Specification/ Series	Capac tance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0402 0603 0805 1206 1210 1812 2220	C = Standard	2 significant digits + number of zeros Use 9 for 1.0 – 9.9 pF Use 8 for 0 5 – .99 pF ex. 2.2 pF = 229 ex. 0.5 pF = 508	B = ±0.10 pF C = ±0 25 pF D = ±0 5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	G = C0G	A = N/A	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

X7R Dielectric, 6.3 – 250 VDC

Capacitance Range: 10 pF to 22 µF • **Temperature Range:** −55°C to +125°C




C	0805	C	225	M	4	R	A	C	AUTO
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0402 0603 0805 1206 1210 1812 2220	C = Standard	Two significant digits + number of zeros.	J = ±5% K = ±10% M = ±20%	9 = 6.3 8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	A = N/A	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

Automotive Grade (cont.)

Capacitor Array, C0G Dielectric, 10 – 200 VDC


Capacitance Range: 10 pF to 2,200 pF **Temperature Range:** −55°C to +125°C



CA	06	4	X	104	K	4	G	A	C	TU
Ce amic Array	Case Size (L" x W" [1]	Number of Capacitors	Specification/ Series	Capacitance Code (pF)	Capacitance To e ance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	05 = 0508 06 = 12	2 = 2 4 = 4	X = Flexible Te mination	2 significant d gits + number of zeros	J = ±5% K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200	G = C0G	A = N/A	C = 100% Matte Sn L = SnPb (5% minimum Pb content)	See "Packaging C-Spec Ordering Options Table" below

Capacitor Array, X7R Dielectric, 10 – 200 VDC


Capacitance Range: 330 pF to 0 22 µF **Temperature Range:** −55°C to +125°C



CA	06	4	X	104	K	4	R	A	C	TU
Ceramic A ray	Case Size (L" x W")[1]	Number of Capacitors	Specification Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Des gn	Termination Fin sh[2]	Packag ng/Grade (C-Spec)
	05 = 0508 06 = 0612	2 = 2 4 = 4	X = F ex ble Termination	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% minimum Pb content)	See "Packaging C-Spec Ordering Options Table" below

Open Mode Design (FO-CAP), X7R Dielectric, 16 – 200 VDC


Capacitance Range: 1,000 pF to 6.8 µF **Temperature Range:** −55°C to +125°C



C	1210	J	685	K	3	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0805 1206 1210 1812	F = Open Mode J = Open Mode with Flexible Termination	Two significant digits + number of zeros	K = ±10% M = ±20%	4 = 16 3 = 25 5 = 50 1 = 100 2 = 200	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Floating Electrode Design (FE-CAP), X7R Dielectric, 6.3 – 250 VDC

Capacitance Range: 150 pF to 0.22 µF **Temperature Range:** −55°C to +125°C




C	0805	S	104	K	5	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/ Grade (C-Spec)
	0402 0603 0805 1206 1210 1812	S = Floating Electrode	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	9 = 6.3 8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

Automotive Grade (cont.)

Flexible Termination System (FT-CAP) X7R Dielectric, 6.3 – 250 VDC

Capacitance Range: 180 pF to 22 µF • **Temperature Range:** −55°C to +125°C



C	1206	X	106	K	4	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Se ies	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)[2]
	0603 08 5 1206 121 1808 1812 1825 2220 2225	X = F exib e Te m nat n	2 significant di its + number of zeros	J = ±5% K = ±10% M = ±20%	9 = 6.3 8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

KPS Series, X7R Dielectric, 10 – 250 VDC


Capacitance Range: 0.1 µF to 47 µF • **Temperature Range:** −55°C to +125°C



C	2220	C	106	M	5	R	2	C	AUTO
Ceramic	Case Size (L" x W")	Specification/ Ser es	Capacitance Code (pF	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/Design	Leadframe Finish[2]	Packaging/Grade (C-Spec)
	1210 1812 2220	C = Standard	Two significant digits + number of zeros	K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 A = 250	R = X7R	1 = KPS Single Chip Stack 2 = KPS Double Chip Stack	C = 100% Matte Sn	See “Packaging C-Spec Ordering Opt ons Table” below

High Voltage with Flexible Termination System (HV FT-CAP) X7R Dielectric, 500 – 3,000 VDC

Capacitance Range: 10 pF to 0.33 µF • **Temperature Range:** −55°C to +125°C



C	1210	X	154	K	C	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0603 0805 1206 1210 1808 1812 1825 2220 2225	X = Flexible Termination	Two significant digits + number of zeros.	J = ±5% K = ±10% M = ±20%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000 Z = 2,500 H = 3,000	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

KPS Series, High Voltage, X7R Dielectric, 500 – 630 VDC

Capacitance Range: 0.047 µF to 1 µF • **Temperature Range:** −55°C to +125°C



C	2220	C	105	M	C	R	2	C	7186
Ceramic	Case Size (L"x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Leadframe Finish[2]	Packaging/Grade (C-Spec)
	2220	C = Standard	2 significant digits + number of zeros.	K = ±10% M = ±20%	C = 500 B = 630	R = X7R	1 = KPS Single Chip Stack 2 = KPS Double Chip Stack	C = 100% Matte Sn	See “Packaging C-Spec Ordering Options Table” below

Downloaded from Arrow.com.

Automotive Grade (cont.)

KPS HT Series, High Temperature 150°C, X8L Dielectric, 10 – 50 VDC


Capacitance Range: 0.47 µF to 47 µF • **Tempe at re Range:** −55°C to +150°C



C	2220		476	M	8	N	2	C	7186
Cerami	Case Size (L"x W")	Specification/ Series	Capacitance Code (pF)	Capac tance Tolerance[1]	Rated Vo tage (VDC)	Di lectric	Failure Rate/ Design	Leadframe Finish	Packaging/Grade (C-Spec)
	1210 2220	C = Standard	2 significant digits + number o zeros.	K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50	N = X8L	1 = KPS Single Ch p Stack 2 = KPS Double Chip Stack	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" be ow

Flexible Termination System (FT-CAP), C0G Dielectric, 10 – 250 VDC


Capacitance Range: 0.5 pF to 0.47 µF • **Temperature Range:** −55°C to +125°C



C	1206	X	563	J	3	G	A	C	TU
Ceram c	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	D electr c	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0603 0805 1206 1210 1812 1825 2220 2225	X = Flexible Termination	2 significant digits + number of zeros. Use 9 for 1.0 – 9.9 pF Use 8 for 0.5 – 99 pF e g., 2.2 pF = 229 e.g., 0.5 pF = 508	B = ±0.10 pF C = ±0 25 pF D = ±0 5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	G = C0G	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Flexible Termination System (FT-CAP), Ultra-Stable X8R Dielectric, 25 – 100 VDC


Capacitance Range: 430 pF to 0.22 µF • **Temperature Range:** −55°C to +150°C



C	1206	X	104	J	3	H	A	C	AUTO
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Reated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0603 0805 1206 1210 1812	X = Flexible Termination	2 significant dig ts + number of zeros.	F = ±1% G = ±2% J ±5% K = ±10% M = ±20%	3 = 25 5 = 50 1 = 100	H = Ultra-Stable X8R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Floating Electrode Design with Flexible Termination System (FF-CAP), X7R Dielectric, 6.3 – 250 VDC

Capacitance Range: 180 pF to 0.22 µF **Temperature Range:** −55°C to +125°C




C	0805	Y	104	K	5	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/ Grade (C-Spec)
	0603 0805 1206 1210 1812	Y = Floating Electrode with Flexible Termination	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	9 = 6 3 8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

Automotive Grade (cont.)

High Temperature 150°C Ultra-Stable X8R Dielectric, 25 – 100 VDC


Capacitance Range: 100 pF to 0 22 µF **Temperature Range:** −55°C to +150°C



C	1210	C	184	K	3	H	A	C	AUTO
Ceram c	Case Size (L" x W")	Specification/ Series[1]	Capaci ance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	D electric	Failure Rate/ Design	Termination F nish[2]	Packaging/Grade (C-Spec)
	0402 0603 0805 1206 1210 1812	C = Standard	2 significant digits + number of zeros	F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	3 = 25 5 = 50 1 = 100	H = Ultra Stable X8R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

High Temperature 150°C, X8L Dielectric, 10 – 50 VDC


Capacitance Range: 0.012 µF to 10 µF • **Temperature Range:** −55°C to +150°C



C	1210	X	106	K	8	N	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series[1]	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectr c	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0402 0603 0 05 1206 1210	C = Standard X = Flexible Termination	2 significant digits + number of zeros	J = ±5% K = ±10% M ±20%	8 = 10 3 = 25 5 = 50	N = X8L	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

High Voltage X7R Dielectric, 500 – 3,000 VDC


Capacitance Range: 10 pF to 0.56 µF • **Temperature Range:** −55°C to +125°C



C	1210	C	154	K	C	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0603 0805 1206 1210 1808 1812 1825 2220 2225	C = Standard	Two significant digits + number of zeros.	J = ±5% K = ±10% M = ±20%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000 Z = 2,500 H = 3,000	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

High Voltage C0G Dielectric, 500 – 3,000 VDC

Capacitance Range: 1 pF to 0.039 µF • **Temperature Range:** −55°C to +125°C




C	1210	C	332	J	C	G	A	C	AUTO
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0805 1206 1210 1808 1812 1825 2220 2225	C = Standard	Two significant digits + number of zeros.	B = ±0.10 pF C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000 Z = 2,500 H = 3,000	G = C0G	A = N/A	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

Automotive Grade (cont.)

High Voltage with Flexible Termination System (HV FT-CAP), C0G Dielectric, 500 – 3,000 VDC

Capacitance Range: 1 pF to 0.039 µF • **Tempe ature Range:** −55°C to +125°C




C	2225	X	393	J	C	G	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0805 1206 1210 1808 1812 1825 2220 2225	X= Flexible Termination	Two significant digits + number of ze os	B = ±0 10 pF C = ±0 25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ± 0%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000 Z = 2,500 H = 3,000	G = C0G	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

High Reliability Commercial Off-The-Shelf (COTS)

C0G Dielectric, 10 – 250 VDC for Higher Reliability Applications


Capacitance Range: 0.5 pF to 0.47 µF • **Temperature Range:** −55°C to +125°C



C	1206	T	104	K	5	G	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0402 0603 0805 1206 1210 1812 2220	T = COTS	2 significant digits + number of zeros Use 9 for 1.0 – 9 9 pF Use 8 for 0.5 – .99 pF ex. 2 2 pF = 229 ex. 0.5 pF = 508	B = ±0.10 pF C = ±0.25 pF D = ±0 5 pF F = ± 1% G = ±2% J = ±5% K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 6 = 35 5 = 50 1 = 100 2 = 200 A = 250	G = C0G	A = Testing per MIL–PRF–55681 PDA 8% B= Testing per MIL–PRF–55681 PDA 8%, DPA per EIA–469 C = Testing per MIL–PRF–55681 PDA 8%, DPA per EIA–469, Humidity per M L–STD–202, Method 103, Condition A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

X7R Dielectric, 6.3 – 250 VDC for Higher Reliability Applications

Capacitance Range: 10 pF to 22 µF **Temperature Range:** −55°C to +125°C




C	1210	T	104	K	5	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0402 0603 0805 1206 1210 1812 2220	T = COTS	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	9 = 6.3 8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	A = Testing per M L–PRF–55681 PDA 8% B= Testing per MIL–PRF–55681 PDA 8%, DPA per EIA–469 C = Testing per MIL–PRF–55681 PDA 8%, DPA per EIA–469, Humidity per M L–STD–202, Method 103, Condition A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

SnPb End Metallization

C0G Dielectric, 10 – 250 VDC (Commercial Grade)


Capacitance Range: 0.5 pF to 0 47 µF • **Temperature Range:** −55°C to +125°C



C	1206	C	104	J	3	G	A	L	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0402 0603 0805 1206 1210 180 1812 1825 2220 2225	C = Standard	Two significant digits + number of zeros Use 9 for 1 0 – 9.9 pF Use 8 or 0.5 – 99 pF ex. 2 2 pF = 229 ex. 0.5 pF = 508	B = ±0.10 pF C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	G = C0G	A = N/A	L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

X7R Dielectric, 6.3 – 250 VDC (Commercial Grade)


Capacitance Range: 10 pF to 22 µF **Temperature Range:** −55°C to +125°C



C	1210	C	226	K	8	R	A	L	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance olerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0402 0603 0805 1206 1210 1808 1812 1825 2220 2225	C = Standard	2 Significant Dig ts + Number of Zeros	J = ±5% K = ±10% M = ±20%	9 = 6.3 8 = 10 4 = 16 3 = 25 6 = 35 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	A = N/A	L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

C0G Dielectric, 10 – 250 VDC, Commercial Off-The-Shelf (COTS) for Higher Reliability Applications

Capacitance Range: 0.5 pF to 0.47 µF • **Temperature Range:** −55°C to +125°C




C	1206	T	104	K	5	G	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0402 0603 0805 1206 1210 1812 2220	T = COTS	2 significant digits + number of zeros Use 9 for 1.0 – 9.9 pF Use 8 for 0.5 – .99 pF ex. 2.2 pF = 229 ex. 0.5 pF = 508	B = ±0.10 pF C = ±0.25 pF D = ±0 5 pF F = ± 1% G = ±2% J = ±5% K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 6 = 35 5 = 50 1 = 100 2 = 200 A = 250	G = C0G	A = Testing per MIL–PRF–55681 PDA 8% B= Testing per MIL–PRF–55681 PDA 8%, DPA per EIA–469 C = Testing per MIL–PRF–55681 PDA 8%, DPA per EIA–469, Humidity per M L–STD–202, Method 103, Condition A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

SnPb End Metallization (cont.)

X7R Dielectric, 6.3 – 250 VDC, Commercial Off-The-Shelf (COTS) for Higher Reliability Applications


Capacitance Range: 10 pF to 22 µF • **Temperature Range:** −55°C to +125°C



C	1210	T	104	K	5	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Die ectric	Failure Rate/Design	Termination Finish	Packaging/Grade (C-Spec)
	0402 0603 0 05 1206 1210 1812 2220	T = COTS	2 significant digits + number of zeros	J ±5% K = ±10% M = ±20%	9 = 6.3 8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	A = Testing per M L–PRF–55681 PDA 8% B= Testing per MIL–PRF–55681 PDA 8%, DPA per EIA–469 C = Testing per MIL–PRF–55681 PDA 8%, DPA per EIA–469, Humidity per M L–STD–202, Method 103, Condition A	C = 100% Matte Sn L = SnPb (% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

High Temperature 150°C Ultra-Stable X8R Dielectric, 25 – 100 VDC (Commercial & Automotive Grade)


Capacitance Range: 100 pF to 0.22 µF **Temperature Range:** −55°C to +150°C



C	1210	C	184	K	3	H	A	C	AUTO
Ceramic	Case Size (L" x W")	Specificat on/ Series[1]	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0402 0603 0805 1206 1210 1812	C = Standard	2 significant digits + number of zeros	F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	3 = 25 5 = 50 1 = 100	H = Ultra Stable X8R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

High Temperature 150°C, X8L Dielectric, 10 – 50 VDC (Commercial & Automotive Grade)

Capacitance Range: 0.012 µF to 10 µF • **Temperature Range:** −55°C to +150°C




C	1210	X	106	K	8	N	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series[1]	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0402 0603 0805 1206 1210	C = Standard X = Flexible Termination	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	8 = 10 3 = 25 5 = 50	N = X8L	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

SnPb End Metallization (cont)

Telecom "Tip and Ring" X7R Dielectric, 250 VDC (Commercial & Automotive Grade)


Capacitance Range: 180 pF to 1 2 µF • **Tempe ature Range:** −55°C to +125°C



C	1825	C	105	K	A	R	A	C	TU
Ceramic	Cas S e (L" x W")	Specification Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	805 1206 121 1812 8 5 2220 2225	= Standard X = Flexible erm nat on	2 s g fica t digits + number of zeros	J ±5% K = ±10% M = ±20%	A = 250	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Open Mode Design (FO-CAP), X7R Dielectric, 16 – 200 VDC (Commercial & Automotive Grade)


Capacitance Range: 1,000 pF to 6.8 µF • **Temperature Range:** −55°C to +125°C



C	1210	J	685	K	3	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0805 1206 1210 1812	F = Open Mode J = Open Mode w th F exible Termination	Two significant digits + number of zeros	K = ±10% M = ±20%	4 = 16 3 = 25 5 = 50 1 = 100 2 = 200	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Floating Electrode Design (FE-CAP), X7R Dielectric, 6.3 – 250 VDC (Commercial & Automotive Grade)


Capacitance Range: 150 pF to 0.22 µF **Temperature Range:** −55°C to +125°C



C	0805	S	104	K	5	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/ Grade (C-Spec)
	0402 0603 0805 1206 1210 1812	S = Floating Electrode	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	9 = 6.3 8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Flexible Termination System (FT-CAP) X7R Dielectric, 6.3 – 250 VDC (Commercial & Automotive Grade)

Capacitance Range: 180 pF to 22 µF • **Temperature Range:** −55°C to +125°C




C	1206	X	106	K	4	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)[2]
	0603 0805 1206 1210 1808 1812 1825 2220 2225	X = Flexible Termination	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	9 = 6.3 8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

SnPb End Metallization (cont.)

Floating Electrode Design with Flexible Termination System (FF-CAP), X7R Dielectric, 6.3 – 250 VDC (Commercial & Automotive Grade)

Capacitance Range: 180 pF to 0 22 µF **Temperature Range:** −55°C to +125°C



C	0805	Y	104	K	5	R	A	C	TU
Ceramic	Case Si e (L" x W")	Sp ci cation/ Series	Capac tance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/ Grade (C-Spec)
	6 0 05 1206 1210 18 2	Y F at ng Electrode with Flexible Termination	2 s gn ficant digits + numb r of zeros	J = ±5% K = ±10% M = ±20%	9 = 6 3 8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Bulk Capacitance

KPS Series, X7R Dielectric, 10 – 250 VDC (Commercial Grade)

Capacitance Range: 0.1 µF to 47 µF • **Temperature Range:** −55°C to +125°C



C	2220	C	106	M	5	R	2	C	7186
Ceramic	Case Size (L" x W")	Spec fication/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/Design	Leadframe Finish[2]	Packaging/Grade (C-Spec)
	1210 1812 2220	C = Standard	Two s gn ficant digits + number of zeros	K = ±10% M ±20%	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100 A = 250	R = X7R	1 = KPS Sing e Chip Stack 2 = KPS Double Chip Stack	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

KPS Series, High Voltage, X7R Dielectric, 500 – 630 VDC (Commercial Grade)

Capacitance Range: 0.047 µF to 1.0 µF • **Temperature Range:** −55°C to +125°C



C	2220	C	105	M	C	R	2	C	7186
Ceramic	Case Size (L"x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Leadframe Finish[2]	Packaging/Grade (C-Spec)
	2220	C = Standard	2 significant digits + number of zeros.	K = ±10% M = ±20%	C = 500 B = 630	R = X7R	1 = KPS Single Chip Stack 2 = KPS Double Chip Stack	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

KPS HT Series, High Temperature 150°C, X8L Dielectric, 10 – 50 VDC (Commercial & Automotive Grade)

Capacitance Range: 0.47 µF to 47 µF • **Temperature Range:** −55°C to +150°C




C	2220	C	476	M	8	N	2	C	7186
Ceramic	Case Size (L"x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Leadframe Finish	Packaging/Grade (C-Spec)
	1210 2220	C = Standard	2 significant digits + number of zeros.	K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50	N = X8L	1 = KPS Single Chip Stack 2 = KPS Double Chip Stack	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

Bulk Capacitance (cont.)

KPS MIL Series, SMPS Stacked Capacitors, 25 – 1 000 VDC (Commercial, Military, & Space Grades)

Capacitance Range: 0.047 µF to 75 µF • **Temperature Range:** −55°C to +125 C



L1	R	N	30	C	106	K	S	12	
Product Family[1]	Dielectric Classification/ Characterist c[2]	Lead Configuration[3]	Case Size/ Case Code (CC)	Rated Voltage (VDC)	Capacitance Code (pF)	Capacitance Tolerance	Testing Option[4]	Maximum Height Dimension (in.)[5]	
L1 = Unencapsulated L2 = Encapsulated	Q BQ R = BR X = BX W = X7R	N = Stra ght L = Formed "L" M Formed "L" J = Formed "J" K = Formed "J"	30 = CC 3 40 = CC 4 50 = CC 5	3 = 25 5 = 50 1 = 100 2 = 200 C = 500 B = 630 D = 1,000	Two significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	B M49470 "B" Level T = M49470 "T" Level C = DSCC87106 S = Commercial X = Non-Standard (Cus omer Specific Requirements)	Unencapsulated 12 = 0.12" 24 = 0.24" 36 = 0.36" 48 = 0.48" 65 = 0.65"	Encapsulated 27 = 0.27" 39 = 0.39" 53 = 0.53" 66 = 0.66" 80 = 0.80"


MIL–PRF–49470, DSCC 87106

M49470	R	01	474	K	C	N
Performance Specification Indicating M L–PRF–49470[1]	Dielectric Classification/ Characteristic[2]	Performance Specification Sheet Number (ndicating MIL–PRF–49470/1)[3]	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Lead Configuration[4]
M49470 = B level T49470 = T level A T" prefix is used n place of the "M" for T level product.	Q = BQ R = BR X = BX	01 = Unencapsulated 02 = Encapsulated	Two significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	A = 50 B = 100 C = 200 E = 500	N = Straight Pin L = Formed "L" M = Formed "L" J = Formed "J" K = Formed "J"

High Temperature (> 125°C)

High Temperature 150°C, Ultra-Stable X8R Dielectric, 25 – 100 VDC (Commercial & Automotive Grade)


Capacitance Range: 100 pF to 0 22 µF **Temperature Range:** −55°C to +150°C



C	1210	C	184	K	3	H	A	C	AUTO
Ceramic	Case Size (L" x W")	Specification/ Series[1]	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0402 0603 0805 1206 1210 1812	C = Standard	2 significant digits + number of zeros	F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	3 = 25 5 = 50 1 = 100	H = Ultra Stable X8R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

High Temperature 150°C, X8L Dielectric, 10 – 50 VDC (Commercial & Automotive Grade)

Capacitance Range: 0.012 µF to 10 µF **Temperature Range:** −55°C to +150°C




C	1210	X	106	K	8	N	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series[1]	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0402 0603 0805 1206 1210	C = Standard X = Flexible Termination	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	8 = 10 3 = 25 5 = 50	N = X8L	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

High Temperature (> 125°C) (cont.)

High Temperature 200°C, C0G Dielectric, 10 – 200 VDC (Industrial Grade)


Capacitance Range: 0.5 pF to 47 µF **Temperatu e Range:** −55°C to +200°C



C	1210	H	124	J	5	G	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Voltage	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0402 0603 0 05 1206 1210 1812 2220	H = High Temperature (200 C)	2 significant digits + number of zeros. Use 9 for 1.0 – 9 9 pF Use 8 for 0.5 – .99 pF e.g., 2.2 pF = 229 e.g., 0.5 pF = 508	B = ±0 10 pF C = ±0 25 pF D = ±0 5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	8 = 10 V 4 = 16 V 3 = 25 V 5 = 50 V 1 = 100 V 2 = 200 V	G = C0G	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum) E = Gold (Au) 1 97 – 11.8 µin F = Gold (Au) 30 – 50 µin G = Gold (Au) 100 µin minimum	See "Packaging C-Spec Ordering Options Table" below

HV-HT Series, High Voltage, High Temperature 200°C, C0G Dielectric, 500 – 2,000 VDC (Industrial Grade)


Capacitance Range: 1 pF to 0.039 µF • **Temperature Range:** −55°C to +200°C



C	2225	H	393	J	C	G	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0805 1206 1210 1808 1812 1825 2220 2225	H= High Temperature (200 C)	2 significant digits + number of zeros.	B = ±0.10 pF C = ±0.25 pF D = ±0 5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000	G = C0G	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum) E = Gold (Au) 1.97 – 11.8 µin F = Gold (Au) 30 – 50 µin G = Gold (Au) 100 µin minimum	See "Packaging C-Spec Ordering Options Table" below

Flexible Termination System (FT-CAP), Ultra-Stable X8R Dielectric, 25 – 100 VDC (Commercial & Automotive Grade)

Capacitance Range: 430 pF to 0.22 µF • **Temperature Range:** −55°C to +150°C




C	1206	X	104	J	3	H	A	C	AUTO
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Reated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0603 0805 1206 1210 1812	X = Flexible Termination	2 significant digits + number of zeros.	F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	3 = 25 5 = 50 1 = 100	H = Ultra-Stable X8R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

High Temperature (> 125ºC) (cont.)

High Temperature 175ºC, X7R Dielectric, 16 – 200 VDC (Industrial Grade)

Capacitance Range: 2.7 nF to 3.3 µF • **Temperature Range:** −55 C to +175°C



C	1210	R	225	K	3	R	A	C	T050
Ceram c	Case Size[1] (L" x W")	Specification/ Series[1]	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish	Packaging/Grade (C-Spec)[2]
	0402 0603 0805 1206 1210 1812	G = 175 C with standard termination R = 175 C w/ Flexible Termination	First two digits represent significant figu es. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	4 = 16 3 = 25 5 = 50 1 = 100 2 = 200	R = X7R	A = N/A	C = 100% Matte Sn	Blank = Bulk 7292 = Waffle Pack/Tray TU = 7" Reel Unmarked (full reel quantity) T050 = 50 pieces/7" Reel - Unmarked T100 = 100 pieces/7" Reel - Unmarked T250 = 250 pieces/7" Reel - Unmarked T500 = 500 pieces/7" Reel - Unmarked T1K = 1,000 pieces/Reel - Unmarked

KPS HT Series, High Temperature 150°C, X8L Dielectric, 10 – 50 VDC (Commercial & Automotive Grade)


Capacitance Range: 0.47 µF to 47 µF • **Temperature Range:** −55°C to +150°C



C	2220	C	476	M	8	N	2	C	7186
Ceramic	Case Size (L"x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Leadframe Finish	Packaging/Grade (C-Spec)
	1210 2220	C = Standard	2 significant digits + number of zeros.	K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50	N = X8L	1 = KPS Single Chip Stack 2 = KPS Double Chip Stack	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

Pulse Discharge, High Voltage, High Temperature 200°C, C0G Dielectric, 500 – 2,000 VDC (Industrial Grade)

Capacitance Range: 0.5 pF to 0.15 µF • **Temperature Range:** −55°C to +200°C




Contact KEMET for ordering information									
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)[1]	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)[3]
	2824 3040 3640 4540	H= High Temp (200 C)	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000	G = C0G	W = Pulse Discharge	C = 100% Matte Sn	Contact KEMET for packaging availability and details

Downloaded from Arrow.com.

High Voltage (> 500 V)

ArcShield™ Technology, High Voltage, X7R Dielectric, 500 – 1,000 VDC (Commercial & Automotive Grade)


Capacitance Range: 2,200 pF to 0.33 µF • **Temperature Range:** −55°C to +125°C



C	0603	W	392	K	C	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Se es	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/ Grade (C-Spec)[2]
	0603 0805 1206 1210 1808 1812 825 2220 2225	V = ArcShield W = ArcShield with Flexible Termination	Two significant digits + n mber of zeros.	J = ±5% K = ±10% M = ±20%	C = 500 B = 630 D = 1,000	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% PB minimum)	See "Packaging C-Spec Ordering Options Table" below

High Voltage C0G Dielectric, 500 – 3,000 VDC (Commercial & Automotive Grade)


Capacitance Range: 1 pF to 0.039 µF • **Tempe at re Range:** −55°C to +125°C



C	1210	C	332	J	C	G	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0805 1206 1210 1808 1812 1825 2220 2225	C = Standard	Two significant digits + number of zeros.	B = ±0.10 pF C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000 Z = 2,500 H = 3,000	G = C0G	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

High Voltage X7R Dielectric, 500 – 3,000 VDC (Commercial & Automotive Grade)

Capacitance Range: 10 pF to 0.56 µF • **Temperature Range:** −55°C to +125°C




C	1210	C	154	K	C	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0603 0805 1206 1210 1808 1812 1825 2220 2225	C = Standard	Two significant digits + number of zeros.	J = ±5% K = ±10% M = ±20%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000 Z = 2,500 H = 3,000	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

High Voltage (> 500 V) (cont.)

High Voltage with Flexible Termination System (HV FT-CAP), C0G Dielectric, 500 – 3,000 VDC (Commercial & Automotive Grade)


Capacitance Range: 1 pF to 0 039 µF • **Tempe ature Range:** −55°C to +125°C



C	2225	X	393	J	C	G	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0805 1206 1210 1808 1812 1 2 2220 2225	X= Flexible ermination	Two significant digits + number of ze os.	B = ±0 10 pF C ±0 25 pF D = ±0 5 pF F ±1% G = ±2% ±5% K = ±10% M = ±20%	C = 500 B = 630 D = 1,000 F = 500 G = 2,000 Z 2,500 H = 3,000	G = C0G	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

High Voltage with Flexible Termination System (HV FT-CAP) X7R Dielectric, 500 – 3,000 VDC (Commercial & Automotive Grade)

Capacitance Range: 10 pF to 0.56 µF **Temperature Range:** −55°C to +125°C



C	1210	X	154	K	C	R	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[1]	Packaging/Grade (C-Spec)
	0603 0805 1206 1210 1808 1812 1825 2220 2225	X = Flexible Termination	Two significant digits + number of zeros.	J = ±5% K = ±10% M = ±20%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000 Z = 2,500 H = 3,000	R = X7R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

KPS Series, High Voltage, X7R Dielectric, 500 – 630 VDC (Commercial Grade)


Capacitance Range: 0.047 µF to 1.0 µF • **Temperature Range:** −55°C to +125°C



C	2220	C	105	M	C	R	2	C	7186
Ceramic	Case Size (L"x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Leadframe Finish[2]	Packaging/Grade (C-Spec)
	2220	C = Standard	2 significant digits + number of zeros.	K = ±10% M = ±20%	C = 500 B = 630	R = X7R	1 = KPS Single Chip Stack 2 = KPS Double Chip Stack	C = 100% Matte Sn	See "Packaging C-Spec Ordering Options Table" below

HV-HT Series, High Voltage, High Temperature 200°C, C0G Dielectric, 500 – 2,000 VDC (Industrial Grade)

Capacitance Range: 1 pF to 0.039 µF • **Tempe ature Range:** −55°C to +200°C




C	2225	H	393	J	C	G	A	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)
	0805 1206 1210 1808 1812 1825 2220 2225	H= High Temperature (200 C)	2 significant digits + number of zeros.	B = ±0.10 pF C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000	G = C0G	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum) E = Gold (Au) 1.97 – 11.8 µin F = Gold (Au) 30 – 50 µin G = Gold (Au) 100 µin minimum	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

High Voltage (> 500 V) (cont.)

Pulse Discharge, High Voltage, High Temperature 200°C, C0G Dielectric, 500 – 2,000 VDC (Industrial Grade)


Capacitance Range: 0.5 pF to 0.15 µF **Temperature Range:** −55°C to +200°C



Contact KEMET for ordering information									
Ceram c	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)[1]	Dielectric	Failure Rate/ Design	Termination Finish[2]	Packaging/Grade (C-Spec)[3]
	2824 3040 3640 4540	H= High Temp (200 C)	2 significant digits + number of zeros	J = ±5% K ±10% M = ±20%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000	G = C0G	W = Pulse Discharge	C = 100% Matte Sn	Contact KEMET for packaging availability and details

KPS HV, Large Case, SM Series, C0G Dielectric 500 – 10,000 VDC (Industrial Grade)


Capacitance Range: 10 pF to 0.39 µF • **Temperature Range:** −55°C to +125°C



SM20		N	472	J	501	B	M
Style/Size		Dielectric	Capacitance Code (pF)	*Capacitance Tolerance*	Rated Voltage (VDC)	Lead Configuration[1]	Testing/ Inspection Option[2]
SM20 SM21 SM22 SM23 SM24 SM25 SM26	SM30 SM31 SM33 SM34 SM35 SM36	N = C0G	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	501 = 500 102 = 1,000 202 = 2,000 302 = 3,000 402 = 4,000 502 = 5,000 752 = 7,500 103 = 10,000	A = Formed "L" B = Formed "J"	Blank = None M = Group A per MIL–PRF–49467

KPS HV, Large Case, SM Series, X7R Dielectric, 500 – 10,000 VDC (Industrial Grade)

Capacitance Range: 150 pF to 5.6 µF • **Temperature Range:** −55°C to +125°C




SM20		B	153	K	501	B	M
Style/Size		Dielectric	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Lead Configuration[1]	Testing/ Inspection Option[2]
SM20 SM21 SM22 SM23 SM24 SM25 SM26	SM30 SM31 SM33 SM34 SM35 SM36	B = X7R	2 significant digits + number of zeros	K = ±10% M = ±20%	501 = 500 102 = 1,000 202 = 2,000 302 = 3,000 402 = 4,000 502 = 5,000 752 = 7,500 103 = 10,000	A = Formed "L" B = Formed "J"	Blank = None M = Group A per M L–PRF–49467

Downloaded from Arrow.com.

Aerospace & Defense

MIL–PRF–123, BP & BX Dielectric, 6.3 – 200 VDC

Capacitance Range: 1 pF to 1 µF **T mpera ure Range:** −55°C to +125°C




C	0805	Z	101	K	5	G	A	L	A
Ceramic	Style/ Size	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish	Failure Rate
	0805 1206 1210 1808 1812 1825 2225	Z = MIL-PRF-123	Two significant digits + number of zeros Use 9 for 1.0 - 9 9 pF ex. 0.5 pF = 508 ex. 2.2 pF = 229 Use 8 for 0 5 - 0.99 pF	C = ±0.25 pF D = ±0.5 pF F = ±1% J = ±5% K = ±10%	5 = 50 1 = 100	G = BP (Ultra-stable) X = BX (Stable)	A = N/A	H = Nickel guarded, (solder coated) L = 70/30 SnPb plated	A = N/A

MIL PRF–123

M123	A	10	BX	B	472	K	Z
Series	Specification/ Series	Style/Size	Dielectric	Rated Voltage (VDC)	Capacitance Code (pF)	Capacitance Tolerance	Termination Finish
M123 = MIL-PRF	A = Indicates the latest characteristics of the part in the specification sheet.	10 = 0805 11 = 1210 12 = 1808 13 = 2225 21 = 1206 22 = 1812 23 = 1825	BP = G (Ultra-stable) BX = X (Stable)	B = 50 C= 100	Two significant digits + number of zeros Use 9 for 1.0 - 9 9 pF ex. 0.5 pF = 508 ex. 2.2 pF = 229 Use 8 for 0.5 - 0.99 pF	C = ±0.25 pF D = ±0.5 pF F = ±1% J = ±5% K = ±10%	Z = 70/30 SnPb plated S = Nickel guarded, (solder coated)

GR900 High Reliability Series, BP & BX Dielectric, 16 – 200 VDC

Capacitance Range: 1 pF to 1 µF **Temperatu e Range:** −55°C to +125°C




C	0805	A	103	K	5	X	A	C	A
Ceramic	Style/Size	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish	Failure Rate
	0504 0805 1005 1206 1210 1805 1808 1812 1825 2225	A = GR900 Q = Q-Spec	Two significant digits + number of zeros Use 9 for 1.0 - 9.9 pF ex. 0.5 pF = 508 ex. 2.2 pF = 229 Use 8 for 0.5 - 0 99 pF	C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	1 = 100 2 = 200 3 =25 4 = 16 5 = 50	G = BP (Ultra-stable) X = BX (Stable)	A = N/A	C = 100% Tin plated H = 60/40 SnPb coated L = 70/30 SnPb plated G = Gold plated	A = N/A

Downloaded from Arrow.com.

Aerospace & Defense (cont.)

MIL-PRF-55681, BP & BX Dielectric, 50 – 100 VDC

Capacitance Range: 1 pF to 0.47 µF **Temperature Range:** −55°C to +125°C




C	0805	P	101	K	1	G	M	L	A
Ceramic	Style/Size	Specification/ Series	Capacitance Code (pF)	Capaci ance Tolerance	Rated Voltage (VDC)	Dielectric	Failu e Rate/ Design	Termination Finish	Fai u e Rat
	0805 1206 1210 1805 1808 1812 1 25 2225	P = MIL-PRF-55681 (CDR01 – CDR06) N = MIL-PRF-55681 (CDR31 – CDR35)	Two significant digits + number of zeros Use 9 for 1.0 - 9.9 pF ex 0.5 pF = 508 ex. 2.2 pF = 229 Use 8 for 0.5 - 0.99 pF	B = ±0.1 pF C = ±0.25 pF D = ±0.5 pF F = ±1% J = ±5% K = ±10% M = ±20%	5 = 50 1 = 1 0	G = BP (C0G, NP0) X = BX (X7R)	M = 1%/k hours P = 0.1%/k hours R = 0.01%/k hours S = 0.001%/k hours	C = 100% Tin plated H = 60/40 SnPb plated L = 70/30 SnPb plated	A = N/A

MIL-PRF-55681

CDR	01	B	P	101	B	K	Z	M	A
Series	Style/Size	Temperature (C)	Dielectric	Capacitance Code (pF)	Rated Voltage (VDC)	Capacitance Tolerance	Termination Finish	Failure Rate/ Design	Failure Rate
C = Ceramic D = Dielectric, Fixed Chip R = Established Reliability	01 = 0805 02 = 1805 03 = 1808 04 = 1812 05 = 1825 06 = 2225 31 = 0805 32 = 1206 33 = 1210 34 = 1812 35 = 1825	B = -55 to +125	P = G (BP, C0G) X = BX (X7R)	Two significant digits + number of zeros Use 9 for 1.0 - 9.9 pF ex. 0.5 pF = 508 ex. 2 2 pF = 229 Use 8 for 0.5 - 0.99 pF	A = 50 B = 100	B = ±0.1 pF C = ±0.25 pF D = ±0.5 pF F = ±1% J = ±5% K = ±10% M = ±20%	S = Solder coated U = Base metallization, (solder coated) W = Base metaliation, (Tin/Lead alloy) Y = Base metalization, (100% Tin) Z = Base metalization, metal-tinned (Tin/Lead alloy)	M = 1%/k hours P = 0.1%/k hours R = 0.01%/k hours S = 0.001%/k hours	A = N/A

DLA Drawing 03028 BR & BX Dielectric, 6.3 – 200 VDC, 0603 Case Size (1608 Metric)


Capacitance Range: 100 pF to 0.1 µF • **Temperature Range:** −55°C to +125°C



03028	BX	104	Y	J	Z	C	7189
Series	Dielectric	Capacitance Code (pF)	Rated Voltage (VDC)	Capacitance Tolerance	Termination Finish[1]	Screening Option	Packaging/Grade (C-Spec)[2]
03028 = DSCC Drawing Number (0603 case size)	BR BX	2 significant digits + number of zeros Use 9 for 1.0 - 9.9 pF ex. 0.5 pF = 508 ex. 2.2 pF = 229 Use 8 for 0.5 - 0.99 pF	W = 6 3 X = 10 Y = 16 Z = 25 A = 50 B = 100 C = 200	J = ±5% K = ±10% M = ±20%	U = SnPb (4% Pb minimum) Z = SnPb (4% Pb minimum)	Blank = No group C testing C = Full Group C L = 2,000 hour life test only M = 1,000 hour life test only H = Low voltage humidity only	Blank = Bulk bag 7246 = Anti-static bulk bag 7292 = Waffle pack 7189 = 7" Reel marked

DLA Drawing 03029 BR & BX Dielectric, 6.3 – 100 VDC, 0402 Case Size (1005 Metric)

Capacitance Range: 100 pF to 2,200 pF **Temperature Range:** −55°C to +125°C




03029	BX	222	Z	J	Z	C	7189
Series	Dielectric	Capacitance Code (pF)	Rated Voltage (VDC)	Capacitance Tolerance	Termination Finish[1]	Screening Option	Packaging/Grade (C-Spec)[2]
03029 = DSCC Drawing Number (0402 case size)	BR BX	Two significant digits + number of zeros Use 9 for 1.0 - 9.9 pF ex. 0.5 pF = 508 ex. 2.2 pF = 229 Use 8 for 0.5 - 0.99 pF	W = 6 3 X = 10 Y = 16 Z = 25 A = 50 B = 100	J = ±5% K = ±10% M = ±20%	U = SnPb (4% Pb minimum) Z = SnPb (4% Pb minimum)	Blank = No group C testing C = Full Group C L = 2,000 hour life test only M = 1,000 hour life test only H = Low voltage humidity only	Blank = Bulk bag 7246 = Anti-static bulk bag 7292 = Waffle pack 7189 = 7" Reel marked

Downloaded from Arrow.com.

Aerospace & Defense (cont.)

DLA Drawing 05006 BP, BR & BX Dielectric, 10 – 200 VDC, 0805 Case Size (2012 Metric)


Capacitance Range: 0.5 pF to 1,800 pF • **Temperature Range:** −55°C to +125°C



05006	BP	681	Z	F	Z	C	7189
Series	Dielectric	Capacitance Code (pF)	Rated Voltage (VDC)	Capacitance Tolerance	Termination Finish[1]	Screening Option	Packaging/Grade (C-Spec)[2]
05006 = DSCC Drawing Number (0805 case size)	BR BX BP	2 significant digits + number of zeros Use 9 for 1.0 - 9.9 pF ex. 0.5 pF = 508 ex 2 2 pF 229 Use 8 for 0.5 - 0.99 pF	X = 10 Y = 16 Z = 25 A = 50 B = 100 C = 200	C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5%	U = SnPb (4% Pb minimum) Z = SnPb (4% Pb minimum)	Blank = No group C testing C = Full group C L = 2,000 hour life test only M = 1,000 hour life test only H = Low voltage humidity only	Blank = Bulk bag 7246 = Anti-static bulk bag 7292 = Waffle pack 7189 = 7" Reel marked

DLA Drawing 05007 BP, BR & BX Dielectric, 10 – 200 VDC, 1206 Case Size (3216 Metric)


Capacitance Range: 1 pF to 4,700 pF • **Temperature Range:** −55°C to +125°C



05007	BP	222	Z	F	Z	C	7189
Series	Dielectric	Capacitance Code (pF)	Rated Voltage (VDC)	Capacitance Tolerance	Termination Finish[1]	Screening Option	Packaging/Grade (C-Spec)[2]
05007 = DSCC Drawing Number (1206 case size)	BR BX BP	2 significant digits + number of zeros Use 9 for 1.0 - 9.9 pF ex. 0 5 pF = 508 ex 2.2 pF = 229 Use 8 for 0.5 - 0.99 pF	X = 10 Y = 16 Z = 25 A = 50 B = 100 C = 200	C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5%	U = SnPb (4% Pb minimum) Z = SnPb (4% Pb minimum)	Blank = No group C testing C = Full group C L = 2,000 hour life test only M = 1,000 hour life test only H = Low voltage humidity only	Blank = Bulk bag 7246 = Anti-static bulk bag 7292 = Waffle pack 7189 = 7" Reel marked

DLA Drawing 91019, BR Dielectric, 25 – 50 VDC, 2220 Case Size (5650 Metric)

Capacitance Range: 0.56 µF to 1 µF • **Temperature Range:** −55°C to +125°C



91019	01	-	7189
Series	Dash Number	Termination Finish[2]	Packaging/Grade (C-Spec)
91019 = DSCC Drawing Number (2220 case size)	01 02 03 04 05	Blank = "U" termination finish / SnPb (4% Pb minimum) Y = 100% Sn Z = SnPb (4% Pb minimum)	Blank = Bulk bag 7246 = Anti-static bulk bag 7292 = Waffle pack 7189 = 7" Reel marked

RF & Microwave

CBR Series, C0G Dielectric, Ultra High Q, Low ESR, 6.3 – 500 VDC

Capacitance Range: 0.1 pF to 100 pF • **Temperature Range:** −55°C to +125°C



CBR	02	C	330	F	9	G	A	C	
Series	Case Size (L"x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Termination Style	Termination Finish	Packaging/Grade (C-Spec)[1]
CBR	02 = 0201 04 = 0402 06 = 0603 08 = 0805	C = Standard	2 significant digits + number of zeros Use 9 for 1.0 – 9.9 pF Use 8 for 0.1 – .99 pF e.g., 2.2 pF = 229 e.g., 0.5 pF = 508	A = ±0.05 pF B = ±0.1 pF C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5%	9 = 6.3 8 = 10 3 = 25 5 = 50 1 = 100 2 = 200 A = 250 C = 500	G = C0G	A = N/A	C = 100% Matte Sn	Blank = 7" Reel Unmarked

Downloaded from Arrow.com.

Ceramic Capacitors
Leaded

Commercial Grade

Aximax, 400 Series, Axial, Conformally Coated, C0G Dielectric, 50 – 200 VDC

Capacitance Range: 1 pF to 0.015 µF **Temperature Range:** 55°C to +125°C



C	410	C	472	J	5	G	5	T	A	7200
Ceramic	Style/Size	Specification/ Series	Capacitance Code pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging (C-Spec)
	410 412 420 430 440	C = Standard	First two d gits represent significant figures. Third digit specifies number of zeros.	B = ±0.1 pF C = ±0 25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10%	5 = 50 1 = 100 2 = 200	G = C0G	5 = Multilayer	T = 100% Matte Sn H = SnPb (60/40)	A = N/A	Blank = Bulk 7200 = 12" Reel 7293 = Ammo Pack

Aximax, 400 Series, Axial, Conformally Coated, X7R Dielectric, 25 – 250 VDC

Capacitance Range: 10 pF to 4 7 µF • **Temperature Range:** −55°C to +125°C



C	410	C	105	K	3	R	5	T	A	7200
Ceramic	Style/Size	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging (C-Spec)
	410 412 420 430 440	C = Standard	First two digits represent significant figures. Th rd digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	3 = 25 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	5 = Multilayer	T = 100% Matte Sn H = SnPb (60/40)	A = N/A	Blank = Bulk 7200 = 12" Reel 7293 = Ammo Pack

Aximax, 400 Series, Axial, Conformally Coated, Z5U Dielectric, 50 – 100 VDC

Capacitance Range: 1000 pF to 2.2 µF **Temperature Range:** +10°C to +85°C



C	410	C	105	M	3	U	5	T	A	7200
Ceramic	Style/Size	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging (C-Spec)
	410 412 420 430 440	C = Standard	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20% Z =+80%, -20%	3 = 25 5 = 50 1 = 100 2 = 200 A = 250	U = Z5U	5 = Multilayer	T = 100% Matte Sn H = SnPb (60/40)	A = N/A	Blank = Bulk 7200 = 12" Reel 7293 = Ammo Pack

Goldmax, 300 Series, Radial, Conformally Coated, C0G Dielectric, 50 – 200 VDC

Capacitance Range: 1 pF to 0.15 µF • **Temperature Range:** −55°C to +125°C



C	320			C	153	J	5	G	5	T	A	7301
Ceramic	Style/Size			Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging (C-Spec)[3]
	315 316 317 318 320 321 322 323	324 325 326 327 328 330 331 333	335 336 340 346 350 356	C = Standard	First two digits represent significant figures. Third digit specifies number of zeros.	B = ±0.1 pF C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10%	5 = 50 1 = 100 2 = 200	G = C0G	5 = Multilayer	T = 100% Matte Sn H = SnPb (60/40)	A = N/A	Blank = Bulk 7301 = 12" Reel 7303 = 12" Reel 7293 = Ammo Pack

Downloaded from Arrow.com.

Commercial Grade (cont.)

Goldmax, 300 Series, Radial, Conformally Coated, X7R Dielectric, 25 250 VDC

Capacitance Range: 100 pF to 10 µF • **Temperatu e Range:** −55°C to +125°C



C	320			C	106	K	3	R	5	T	A	7301
Ceramic	Style/Size			Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging (C-Spec)[3]
	315 316 317 318 320 321 322 323	324 325 326 327 328 330 331 333	335 336 340 346 350 356	C = Standard	First two digits represent significant figures. Th rd digit specifi s number of zeros.	J = ±5% K = ±10% M = ±20%	3 = 25 5 = 50 1 = 100 2 = 200 A = 250	R = X7R	5 = Multilayer	T = 100% Matte Sn H = SnPb (60/40)	A = N/A	Blank = Bulk 7301 = 12" Reel 7303 = 12" Reel 7293 = Ammo Pack

Goldmax, 300 Series, Radial Conformally Coated, Z5U Dielectric, 50 – 200 VDC

Capacitance Range: 100 pF to 10 µF • **Temperature Range:** +10°C to +85°C



C	335			C	225	M	5	U	5	T	A	7303
Ceramic	Style/Size			Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging (C-Spec)[3]
	315 316 317 318 320 321 322 323	324 325 326 327 328 330 331 333	335 336 340 346 350 356	C = Standard	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20% Z = +80%, -20%	3 = 25 5 = 50 1 = 100 2 = 200 A = 250	U = Z5U	5 = Multilayer	T = 100% Matte Sn H = SnPb (60/40)	A = N/A	Blank = Bulk 7301 = 12" Reel 7303 = 12" Reel 7293 = Ammo Pack

Radial, Molded, C0G Dielectric, 100 – 200 VDC

Capacitance Range: 1 pF to 0 18 µF • **Temperature Range:** −55°C to +125°C



C	052	C	272	F	2	G	5	T	A	7303
Ceramic	Style/Size	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging/Grade (C-Spec)[3]
	052 062 512 522	C = Standard	2 significant digits + number of zeros Use 9 for 1.0 – 9.9 pF Use 8 for 0.5 – .99 pF ex. 2 2 pF = 229 ex. 0.5 pF = 508	D = ±0 5 pF F = ±1% G = ±2% J = ±5% K = ±10%	1 = 100 2 = 200	G = C0G	5 = Multilayer	T = 100% Matte Sn C = SnPb (60/40)	A = N/A	Blank = Bulk 7301 = 12" Reel 7303 = 12" Reel 7293 = Ammo Pack

Radial, Molded, X7R Dielectric, 50 – 200 VDC

Capacitance Range: 10 pF to 3.3 µF • **Temperature Range:** −55°C to +125°C




C	062	C	105	K	1	R	5	T	A	7301
Ceramic	Style/Size	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging/Grade (C-Spec)[3]
	052 062 512 522	C = Standard	2 significant digits + number of zeros	K = ±10% M = ±20%	5 = 50 1 = 100 2 = 200	R = X7R	5 = Multilayer	T = 100% Matte Sn C = SnPb (60/40)	A = N/A	Blank = Bulk 7301 = 12" Reel 7303 = 12" Reel 7293 = Ammo Pack

Downloaded from Arrow.com.

Commercial Grade (cont.)

Axial, Molded, C0G Dielectric, 100 – 200 VDC


Capacitance Range: 1 pF to 0.1 µF • **Temperature Range:** −55°C to +125 C



C	114	C	681	F	1	G	5	C	A	7200
Ceramic	Style/ Size	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging/Grade (C-Spec)
	114 124 192 202 222	= Standard	2 significant digits + number of zeros Use 9 for 1.0 – 9 9 pF Use 8 for 0.5 – 99 pF ex. 2.2 pF = 229 ex 0.5 pF = 508	D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10%	1 = 100 2 = 200	G = C0G	5 = Multilayer	C = SnPb (60/40)	A = N/A	Blank = Bulk 7200 = 12" Reel 7293 = Ammo Pack

Axial, Molded, X7R Dielectric, 50 – 100 VDC

Capacitance Range: 10 pF to 3.3 µF • **Temperature Range:** −55°C to +125°C



C	114	C	472	M	1	R	5	C	A	7200
Ceramic	Style/Size	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging/Grade (C-Spec)
	114 124 192 202 222	C = Standard	2 significant digits + number of zeros	K = ±10% M = ±20%	5 = 50 1 = 100	R = X7R	5 = Multilayer	C = SnPb (60/40)	A = N/A	Blank = Bulk 7200 = 12" Reel 7293 = Ammo Pack

High Temperature (> 125°C)

High Temperature 200°C, Radial, Molded, C0G Dielectric, 50 – 200 VDC (Industrial Grade)

Capacitance Range: 1 pF up to 0.22 µF • **Temperature Range:** −55°C to +200°C



C	052	H	272	F	2	G	5	G	A	7301
Ceramic	Style/Size	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging C-Spec[3]
	052 062	H = High Temp 200°C	2 significant digits + number of zeros Use 9 for 1.0 – 9.9 pF ex. 2.2 pF = 229	B = ±0.1 pF C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10%	5 = 50 1 = 100 2 = 200	G = C0G	5 = Multilayer	G = Gold (Au)	A = N/A	Blank = Bulk Bag T250 = 250 pcs / 12" Reel T500 = 500 pcs / 12" Reel T1K0 = 1,000 pcs / 12" Reel 7301 = Full Reel Qty / 12" Reel 7303 = Full Reel Qty / 12" Reel 7061 = Bulk Tray

Downloaded from Arrow.com.

High Temperature (> 125°C) (cont.)

High Temperature 200°C, Radial, Molded, X7R Dielectric, 50 – 200 VDC (Industrial Grade)

Capacitance Range: 1,000 pF up to 1 µF • **Temperature Range:** −55°C to +200°C



C	062	H	105	K	5	R	5	G	A	7303
Ceramic	Style/Size	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging C-Spec[3]
	052 062	H = High Temp 200°C	2 significant digits + number of zeros Use 9 for 1.0 – 9.9 pF ex. 2.2 pF = 229	J = ±5% K = ±10% M = ±20%	5 = 50 1 = 100 2 = 200	R = X7R	5 = Multilayer	G = Gold (Au)	A = N/A	Blank = Bulk Bag T250 = 250 pcs / 12" Reel T500 = 500 pcs / 12" Reel T1K0 = 1,000 pcs / 12" Reel 7301 = Full Reel Qty / 12" Reel 7303 = Full Reel Qty / 12" Reel 7061 = Bulk Tray

HT/HP Series, 200°C, C0G & X7R Dielectric, Axial & Radial, 25 – 200 VDC

Capacitance Range: 5.6 pF to 2.7 µF • **Temperature Range:** −55°C to +200°C



HT06	A	W	472	K	N
Style/Size	Rated Voltage (VDC)	Dielectric	Capacitance Code (pF)	Capacitance Tolerance	Lead Finish
HT05 – HT16 HP05 – HP16	A = 25 B = 50 C = 100 D = 200	N = C0G (NP0) W = X7R	Two significant digits plus number of zeros	J = ±5% K = ±10% M = ±20%	N = Nickel (Standard) C = Solder Coated Clad Steel

HV Series, 200°C, C0G & X7R Dielectric, Radial Conformally Coated, 500 – 4,000 VDC

Capacitance Range: 10 pF to 1.0 µF **Temperature Range:** −55°C to +200°C



10	HV12	W	472	K	N	M
Rated Voltage (VDC)	Style/Size	Dielectric	Capacitance Code (pF)	Capacitance Tolerance	Lead Finish	Group A Screening
05 = 500 10 = 1,000 20 = 2,000 30 = 3,000 40 = 4,000	HV10 – HV16	N = C0G (NP0) W = X7R	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	N = Nickel (Standard) C = Solder Coated Clad Steel	MIL-PRF-49467 (Subgroup 1) except Corona

ACR/ACA/ARR/ARA Series, 200°C, C0G & X7R Dielectric, Axial & Radial, 50 – 100 VDC

Capacitance Range: 10 pF to 5.6 µF **Temperature Range:** −55°C to +200°C



A	C	R	06	B	103	K	G	S
Series	Dielectric	Lead Configuration	Case Size	Rated Voltage (VDC)	Capacitance Code (pF)	Capacitance Tolerance	Lead Finish	Grade/ Test Level
A = High Temperature Axial and Radial Capacitors	C = C0G (NP0)/BP R = X7R (BX)	A = Axial R = Radial	05 – 09 = Radial 16 – 69 = Axial	B = 50 D = 100 S = Special	Two significant digits plus the number of zeros	J = ±5% K = ±10% M = ±20%	W = Solder Coated Copper Clad Steel G = Gold Plated Copper Clad Steel	S = Standard A = M L-PRF-39014, Group A Test A = M L-PRF-20 (C0G) X = Special

Downloaded from Arrow.com.

High Temperature (> 125°C) (cont.)

TCR/TRR/TCA/TRA Series, 260°C, C0G & X7R Dielectric, Axial & Radial, 50 – 100 VDC

Capacitance Range: 10 pF to 5 6 µF **Temperature Range:** −55°C to +200°C



T	C	R	06	B	103	K	G	S
Series	Dielectric	Lead Configuration	Case Size	Rated Voltage (VDC)	Capacitance Code (pF)	Capacitance Tolerance	Lead Finish	Grade/ Test Level
T = High Temperature Axial and Radial Capacitors	C C0G (NP0)/BP R = X7R (BX)	A = Axial R = Radial	05 – 09 = Radial 1 – 69 = Axial	B = 5 D = 100	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	W = Solder Coated Copper Clad Steel G = Gold Plated Copper Clad Steel	S = Standard A = M L-PRF-20, Group A Test (C0G) A = M L-PRF-39014 (X7R) X = Special

VCR/VRR Series, 200°C, C0G & X7R Dielectric, Radial, 500 – 5,000 VDC

Capacitance Range: 10 pF to 1.5 µF **Temperature Range:** −55°C to +200°C



V	C	R	40	M	102	K	W	A
Series	Dielectric	Lead Con guratio	Case S ze	Rated Voltage (VDC)	Capacitance Code (pF)	Capacitance Tolerance	Lead Finish	Grade/ Test Level
V = High Voltage Radial Capacitors	C = C0G (NP0)/BP R = X7R (BX)	R = Radial	07 40 50 60 70 80	L = 500 M = 1,000 T = 2,000 V = 3,000 W = 4,000 X = 5,000	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	W = Solder Coated Copper Clad Steel G = Gold Plated Copper Clad Steel	S = Standard A = MIL-PRF-20, Group A Test X = Special

Aximax, 400 Series, Axial, Conformally Coated, X8L Dielectric, 25 – 50 VDC (Commercial & Automotive Grade)

Capacitance Range: 0.1 µF to 2.2 µF • **Temperature Range:** −55°C to +150°C



C	410	C	105	K	3	N	5	T	A	7200
Ceramic	Style/Size	Specification/ Se ies	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging/Grade (C-Spec)
	410 430	C = Standard	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	3 = 25 V 5 = 50 V	N = X8L	5 = Multilayer	T = 100% Matte Sn H = SnPb (60/40)	A = N/A	Blank = Bulk 7200 = 12" Reel 7293 = Ammo pack AUTO = Automotive grade

Aximax, 400 Series, Axial, Conformally Coated, X8R Dielectric, 50 – 200 VDC (Commercial & Automotive Grade)

Capacitance Range: 100 pF to 0.082 µF **Temperature Range:** −55°C to +150°C



C	410	C	472	J	5	H	5	T	A	7200
Ceramic	Style/Size	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging/Grade (C-Spec)
	410 430	C = Standard	2 significant digits + number of zeros	F = ±1% G = ±2% J = ±5% K = ±10%	5 = 50 1 = 100 2 = 200	H = Ultra-Stable X8R	5 = Multilayer	T = 100% Matte Sn H = SnPb (60/40)	A = N/A	Blank = Bulk 7200 = 12" Reel 7293 = Ammo pack AUTO = Automotive grade

Downloaded from Arrow.com.

High Voltage (> 500 V)

High Voltage Goldmax, 300 Series, Radial, Conformally Coated, C0G Dielectric, 500 – 3,000 VDC (Commercial Grade)

Capacitance Range: 1 pF to 0 039 µF • **Temperature Range:** −55°C to +125°C



C	320			C	332	J	C	G	5	T	A	7301
Ceramic	Style/Size			Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packag ng (C-Spec)[3]
	315 316 317 318 320 321 322 323	324 325 326 327 328 3 331 333	335 336 340 346 350 3 6	C Standard	F rst two dig ts represent significant figures Third digit specifies number of zeros.	B = ±0.1 pF C = ±0.25 pF D = ±0 5 pF F = ±1% G = ±2% J = ±5% K = ±10%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2, 00 Z = 2,500 H = 3 000	G = C0G	5 = Multilayer	T = 100% Matte Sn H = SnPb (60/40)	A = N/A	Blank = Bulk 7301 = 12" Reel 7303 = 12" Reel

High Voltage Goldmax, 300 Series, Radial, Conformally Coated, X7R Dielectric, 500 – 3,000 VDC (Commercial Grade)


Capacitance Range: 10 pF to 0.56 µF • **Temperature Range:** −55°C to +125°C



C	320			C	473	K	C	R	5	T	A	7301
Ceram c	St le/Size			Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	D electric	Design	Lead Finish[2]	Failure Rate	Packaging (C-Spec)[3]
	315 316 317 318 320 321 322 323	324 325 326 327 328 330 331 333	335 336 340 346 350 356	C = Standard	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000 Z = 2,500 H = 3,000	R = X7R	5 = Multilayer	T = 100% Matte Sn H = SnPb (60/40)	A = N/A	Blank = Bulk 7301 = 12" Reel 7303 = 12" Reel 7293 = Ammo Pack

High Voltage Goldmax, 600 Series, Radial, Conformally Coated, C0G Dielectric, 500 – 3,000 VDC (Commercial Grade)


Capacitance Range: 12 pF to 0.1 µF • **Temperature Range:** −55°C to +125°C



C	627			C	224	K	C	G	5	T	A	7301
Ceramic	Style/Size			Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging (C-Spec)
	617 622 623 627 628 630 631	637 638 640 641 642 643 647	648 657 658 667 668	C = Standard	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20% Z = +80%, -20%	C = 500 D = 1,000 F = 1,500 G = 2,000 Z = 2,500 H = 3,000	G = C0G	5 = Multilayer	T = 100% Matte Sn H = SnPb (60/40)	A = N/A	See "Packaging C-Spec Ordering Options Table" below

High Voltage Goldmax, 600 Series, Radial, Conformally Coated, X7R Dielectric, 500 – 3,000 VDC (Commercial Grade)

Capacitance Range: 150 pF to 2 9 µF • **Tempe atu e Range:** −55°C to +125°C



C	627			C	224	K	C	R	5	T	A	7301
Ceramic	Style/Size			Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance[1]	Rated Voltage (VDC)	Dielectric	Design	Lead Finish[2]	Failure Rate	Packaging (C-Spec)
	617 622 623 627 628 630 631	637 638 640 641 642 643 647	648 657 658 667 668	C = Standard	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20% Z = +80%, -20%	C = 500 D = 1,000 F = 1,500 G = 2,000 Z = 2,500 H = 3,000	R = X7R	5 = Multilayer	T = 100% Matte Sn H = SnPb (60/40)	A = N/A	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

High Voltage (> 500 V) (cont.)

HV Series, C0G and X7R, Radial Conformally Coated, 500 – 10,000 VDC

Capacitance Range: 12 pF to 5 6 µF • **Temperature Range:** −55°C to +125°C



10	HV23	N	102	K	N	M
Rated Voltage (VDC)	Style/Size	Dielectric	Capacitance Code (pF)	Capacitance Tolerance	Lead Finish	Group A Screening
05 = 500 10 = 1, 00 20 = 2,000 3,0 40 = 4,000 50 5,0 0 75 = 7,500 100 = 10,000	HV20 – HV36	N = C0G (NP0) B = X7R	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	N = Nickel C = Solder Coated Clad Steel (Standard)	MIL-PRF-49467 (Subgroup 1) except Corona

Aerospace & Defense

MIL–PRF–123, BP & BX Dielectric, Molded Radial, 50 – 100 VDC

Capacitance Range: 4.7 pF to 1 µF • **Temperature Range:** −55°C to +125°C



C	052	Z	102	K	5	G	5	C	A
Ceramic	Style/Size	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Design	Lead Finish	Failure Rate
	052 062 512	Z = MIL-PRF-123	Two significant digits + number of zeros Use 9 for 1.0 - 9 9 pF ex. 0.5 pF = 508 ex. 2.2 pF = 229 Use 8 for 0 5 - 0.99 pF	C = ±0.25 pF D = ±0.5 pF F = ±1% J = ±5% K = ±10%	5 = 50 1= 100	G = BP (Ultra-stable) X = BX (Stable)	5 = Standard	C = Solder coated copper (standard)	A = N/A

MIL–PRF–123

M123	A	01	BX	B	103	K	C
Series	Specification/ Series	Style/Size	Dielectric	Rated Voltage (VDC)	Capacitance Code (pF)	Capacitance Tolerance	Lead Finish
M123 = MIL-PRF	A = Indicates the latest characteristics of the part in the specification sheet.	01 = 052 02 = 062 03 = 512	BP = G (Ultra-stable) BX = X (Stable)	B = 50 C= 100	Two significant digits + number of zeros Use 9 for 1.0 - 9.9 pF ex. 0 5 pF = 508 ex. 2 2 pF = 229 Use 8 for 0 5 - 0.99 pF	C = ±0 25 pF D = ±0 5 pF F = ±1% J = ±5% K = ±10%	C = Solder coated copper

GR900 High Reliability, BP & BX Dielectric, Molded Radial, 50 – 200 VDC

Capacitance Range: 1 pF to 3.3 µF • **Temperature Range:** −55°C to +125°C



C	052	B	223	K	1	X	5	C	A
Ceramic	Style/Size	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Design	Lead Finish	Failure Rate
	052 062 512	B = Leaded devices	Two significant digits + number of zeros Use 9 for 1.0 - 9 9 pF ex. 0.5 pF = 508 ex. 2.2 pF = 229 Use 8 for 0.5 - 0.99 pF	C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	1 = 100 2 = 200 5 = 50	G = C0G (CG, BP) X = X7R (BX)	5 = Standard	C = Solder coated copper (standard)	A = N/A

Downloaded from Arrow.com.

Aerospace & Defense

MIL-PRF-20, CG, Molded Axial & Radial, 50 – 200 VDC

Capacitance Range: 1 pF to 0.1 µF • **Temperature Range:** −55°C to +125°C



C	052	G	102	J	1	G	5	C	A
Ceramic	Style/Size	Specification	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Design	Lead Finish	Failure Rate
	C052 – C522 (Radial) C114 – C222 (Axial)	G – MIL-PRF-20	2 significant digits + number of zeros	C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10%	1 = 100 2 = 200 5 = 50	G = C0G, CG	5 = Standard	C = 60/40 Tin/ Lead (SnPb)	A = N/A M = 1.0% P = 0.1% R = 0.01% S = 0.001%

MIL–C–11015/MIL–PRF–39014, BX & BR, Molded Axial & Radial, 50 – 200 VDC

Capacitance Range: Axial: 10 pF to 3.3 µF, Radial: 10 pF to 0.1 µF • **Temperature Range:** −55°C to +125°C



C	052	K	102	K	2	X	5	C	A
Ceramic	Style/Size	Specification	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Design	Lead Finish	Failure Rate
	C052 – C066 (Radial) C114 – C222 (Axial)	Military T – MIL-PRF-39014 K – MIL-C-11015	2 significant digits + number of zeros	K = ±10% M = ±20%	1 = 100 V 2 = 200 V 5 = 50 V	X = BX (X7R) R = BR	5 = Multilayer	C = 60/40 Tin/ Lead (SnPb)	A = N/A M = 1.0% P = 0.1% R = 0.01% S = 0.001%

HV Series, MIL–PRF–49467 Equivalent, BP BR & BZ, 500 – 5,000 VDC

Capacitance Range: 15 pF to 1.0 µF • **Temperature Range:** −55°C to +125°C



10	HV60	R	102	K	C
Rated Voltage (VDC)	Style/Size	Dielectric	Capacitance Code (pF)	Capacitance Tolerance	Grade/ Test Level
05 = 500 06 = 600 10 = 1,000 20 = 2,000 30 = 3,000 40 = 4,000 50 = 5,000	HV60 – HV69	P = BP C0G (NP0) R = BR (X7R) Z = BZ (X7R)	Two significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	C = CSAM

HS Series High Voltage Space Quality, C0G & X7R, Radial, 500 – 10,000 VDC

Capacitance Range: 12 pF to 5.6 µF • **Temperature Range:** −55°C to +125°C



10	HS24	B	103	K	C	F
Rated Voltage (VDC)	Style/Size	Dielectric	Capacitance Code (pF)	Capacitance Tolerance	Grade/ Test Level	Lead Finish
05 = 500 10 = 1,000 20 = 2,000 30 = 3,000 40 = 4,000 50 = 5,000 75 = 7,500 100 = 10,000	HS20 – HS36	B = X7R N = BP C0G (NP0)	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20% P = 0/+100% Z = -20%/+80%	C = CSAM	INERT LIQU D (BURN-IN) Standard for > 2kV; Add “F” if required for 500 V or 1 kV parts

Downloaded from Arrow.com.

Aerospace & Defense (cont.)

SCA Series, Axial, C³ Technology, C0G Dielectric, 50 – 200 VDC (Commercial Grade)

Capacitance Range: 10 pF to 0.1 µF **Temperature Range:** −55°C to +125°C



S	C	A	69	B	104	J	W	S	
Spec fication/ Series	Dielectric	Lead Configuration	Style/Size	Rated Voltage (VDC)	Capacitance Code (pF)	Capacitance Tolerance[1]	Lead Finish[2]	Screening Option	Packaging/Grade (C-Spec)
S=Standard	C = C0G	A = Axial	16 25 39 69	B = 50 D = 100 F = 200	2 significant digits + number of zeros Use 9 for 1.0 – 9 9 pF Use 8 for 0.5 – .99 pF ex. 2.2 pF = 229 ex. 0.5 pF = 508	J = ±5% K = ±1 % M = ±20%	W = SnPb (60/40) G = Au	S = Standard A = Group A (MIL PRF–20)	Blank = Tray

SCR Series, Radial, C³ Technology, C0G Dielectric, 50 – 200 VDC (Commercial Grade)

Capacitance Range: 12 pF to 0.15 µF • **Temperature Range:** −55°C to +125°C



S	C	R	09	D	184	J	W	S	
Specification/ Series	Dielectric	Lead Configuration	Style/Size	Rated Voltage (VDC)	Capacitance Code (pF)	Capacitance Tolerance	Lead Finish[2]	Screening Option	Packaging/Grade (C-Spec)
S=Standard	C = C0G	R =Radial	05 06 07 08 09	B = 50 D = 100 F = 200	2 significant digits + number of zeros Use 9 for 1 0 – 9 9 pF Use 8 for 0.5 – .99 pF ex. 2.2 pF = 229 ex. 0.5 pF = 508	J = ±5% K = ±10% M = ±20%	W = SnPb (60/4) G = Au	S = Standard A = Group A (MIL–PRF–20)	Blank = Tray

SRA Series, Axial, C³ Technology, X7R Dielectric, 50 – 200 VDC (Commercial Grade)

Capacitance Range: 1,000 pF to 5.6 µF **Temperature Range:** −55°C to +125°C



S	R	A	69	B	475	J	W	S	
Specification/ Series	Dielectric	Lead Configuration	Style/Size	Rated Voltage (VDC)	Capacitance Code (pF)	Capacitance Tolerance[1]	Lead Finish[2]	Screening Option	Packaging/Grade (C-Spec)
S=Standard	R = X7R	A = Axial	16 25 39 50 69	B = 50 D = 100 F = 200	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	W = SnPb (60/40) G = Au	S = Standard A = Group A (MIL–PRF–39014)	Blank = Tray

SRR Series, Radial, C³ Technology, X7R Dielectric, 50 – 200 VDC (Commercial Grade)

Capacitance Range: 680 pF to 4.7 µF • **Temperature Range:** −55°C to +125°C



S	R	R	09	D	475	J	W	S	
Specification/ Series	Dielectric	Lead Configuration	Style/Size	Rated Voltage (VDC)	Capacitance Code (pF)	Capacitance Tolerance[1]	Lead Finish[2]	Screening Option	Packaging/ Grade (C-Spec)
S=Standard	R = X7R	R =Radial	05 06 07 08 09	B = 50 V D = 100 V F = 200 V	2 significant digits + number of zeros	J = ±5% K = ±10% M = ±20%	W = SnPb (60/40) G = Au	S = Standard A = Group A (M L–PRF–39014)	Blank = Tray

Downloaded from Arrow.com.

Safety

Safety Standard Recognized, 900 Series, Radial Disc, Encapsulated, AC Type, X1 400 VAC/Y2 250 VAC (Industrial Grade)

Capacitance Range: 2 pF to 10,000 pF • **Temperature Range:** −40°C to +125°C



C9	8	1	U	103	M	Y	V	D	A	A	7317
Ceramic Seri s	Body Diameter	Lead Spacing[1 2 4]	Spec.	Capacitance Code (pF	Capacitance Tolerance	Rated Voltage	Dielectric/ Temp Char	Design	Lead Config [1 3 4]	Failure Rate	Packaging (C-Spec)
C9 = Ceramic 900 Series	0 = 7.0 mm 1 = 8.0 mm 2 = 9.0 mm 3 = 10.0 mm 4 = 11.0 mm 6 = 13.0 mm 8 = 15.0 mm	5 = 5 0 mm 7 = 7.5 mm 1 = 10.0 mm	U = Safety	2 significant digits + number of zeroes	J = ±5% K = ±10% M = ±20%	Y = X1 40 VAC /Y2 250 VAC	S = SL Y = Y5P W = Y5U V = Y5V	D = Disc	A = Straight B = Vertical Kink C = Outside Kink D = Inside Kink	A = N/A	See "Packaging C-Spec Ordering Options Table" below

Safety Standard Recognized, 900 Series, Radial Disc, Encapsulated, AC Type, X1 440 VAC/Y2 300 VAC (Industrial Grade)

Capacitance Range: 2 pF to 10,000 pF • **Temperature Range:** −40°C to +125°C



C9	7	1	U	472	M	Z	W	D	A	A	7317
Ceramic Series	Body Diameter	Lead Spacing[1 3]	Spec.	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage	Dielectric/ Temp. Char.	Design	Lead Config.[2 3]	Failure Rate	Packaging (C-Spec)
C9 = Ceramic 900 Series	0 = 7.0 mm 1 = 8.0 mm 2 = 9 0 mm 3 = 10.0 mm 4 = 11.0 mm 6 = 13.0 mm 8 = 15.0 mm	7 = 7.5 mm 1 = 10.0 mm	U = Safety	2 significant digits + number of zeroes	J = ±5% K = ±10% M = ±20%	Z = X1 440 VAC /Y2 300 VAC	S = SL Y = Y5P W = Y5U V = Y5V	D = Disc	A = Straight B = Vertical Kink C = Outside Kink D = Inside Kink	A = N/A	See "Packaging C-Spec Ordering Options Table" below

Safety Standard Recognized, 900 Series, Radial Disc, Encapsulated, AS Type, X1 760 VAC/Y1 500 VAC (Industrial Grade)

Capacitance Range: 2,200 pF • **Temperature Range:** −25°C to +125°C



C9	6	1	U	222	M	W	W	D	A	A	7317
Ceramic Series	Body Diameter	Lead Spacing[1]	Spec.	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage	Dielectric/ Temp. Char.	Design	Lead Config.[1]	Failure Rate	Packaging (C-Spec)
C9 = Ceramic 900 Series	6 = 13.0 mm	1 = 10.0 mm	U = Safety	2 significant digits + number of zeroes	M = ±20%	W = X1 760 VAC /Y1 500 VAC	W = Y5U	D = Disc	A = Straight B = Vertical Kink C = Outside Kink	A = N/A	See "Packaging C-Spec Ordering Options Table" below

Downloaded from Arrow.com.

Safety (cont.)

Safety Standard Recognized, 900 Series, Radial Disc, Encapsulated, AH Type, X1 400 VAC/Y1 250 VAC (Industrial Grade)

Capacitance Range: 2.0 pF to 4,700 pF • **Temperature Range:** −25°C to +125°C



C9	1	1	U	620	J	U	S	D	A	A	7317
Ceramic Se ies	Body Diameter	Lead Spacing[1]	Spec	Capacitance Code (pF)	Capacitance To erance	Rated Voltage	Dielectric/ Temp Char.	Design	Lead Config.[2]	Failure Rate	Packaging (C-Spec)
C9 = Ceramic 900 Series	0 = 7.0 mm 1 = 8.0 mm 2 = 9 0 mm 3 = 10.0 mm 4 = 11 0 mm 5 = 12.0 mm 7 = 14.0 mm	1 = 10.0 mm	U = Safety	2 significant digits + n mber of zeroes	J = ±5% K = ±10% M = ±10%	U = X1 400 VAC /Y1 250 VAC	S = SL Y = Y5P W = Y5U V = Y5V	D = Disc	A = Straight B = Vertical Kink C = Outside Kink	A = N/A	See "Packaging C-Spec Ordering Options Table" below

Safety Standard Recognized, 900 Series, Radial Disc, Encapsulated, AH Type, X1 400 VAC/Y1 400 VAC (Industrial Grade)

Capacitance Range: 2.0 pF to 4,700 pF • **Temperature Range:** −25°C to +125°C



C9	3	1	U	101	J	V	S	D	A	A	7317
Ceramic Series	Body Diameter	Lead Spacing[1]	Spec.	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage	Dielectric/ Temp. Char.	Design	Lead Config.[2]	Failure Rate	Packaging (C-Spec)
C9 = Ceramic 900 Series	0 = 7.0 mm 1 = 8.0 mm 2 = 9.0 mm 3 = 10.0 mm 4 = 11.0 mm 5 = 12.0 mm 6 = 13.0 mm 7 = 14.0 mm	1 = 10.0 mm	U = Safety	2 significant digits + number of zeroes	J = ±5% K = ±10% M = ±20%	V = X1 400 VAC /Y1 400 VAC	S = SL Y = Y5P W = Y5U V = Y5V	D = Disc	A = Straight B = Vertical Kink C = Outside Kink	A = N/A	See "Packaging C-Spec Ordering Options Table" below

ERO610 Series, Radial AC Type, X1 440 VAC/Y2 250 VAC

Capacitance Range: 1,000 pF to 12,000 pF • **Temperature Range:** −40°C to +125°C



ERO610	R	J	4250	K	BF0
Series	Safety Class/Sub-Class	Lead Spacing	Capacitance Code (pF)	Capacitance Tolerance	Lead Configuration & Packaging
ERO610	R = X1/Y2	J = 5.0 mm K = 7.5 mm	Digits 2 – 4 indicate the first three significant figures of capacitance in pF. The first digit indicates the total number of significant figures of capacitance. Example: 12,000 pF = 5120 1,800 pF = 4180 150 pF = 3150	K = ±10% M = ±20%	Please refer to datasheet

Downloaded from Arrow.com.

Safety (cont.)

ERK610 Series, Radial AC Type, X1 440 VAC/Y2 300 VAC

Capacitance Range: 33 pF to 4,700 pF • **Temperature Range:** −40°C to +125°C



ERK610	R	K	4470	K	CF0
Series	Safety Class/Sub-Class	Lead Spacing	Capacitance Code (pF)	Capacitance Tolerance	Lead Configuration & Packaging
ERK610	R = X1/Y2	K = 7.5 mm	Digits 2 – 4 indicate the first three significant figures of capacitance in pF. The first digit indicates the total number of significant figures of capacitance. Example: 12,000 pF = 5120 1,800 pF = 4180 150 pF = 3150	K = ±10% M = ±20%	Please refer to datasheet

ERP610 Series, Radial AC Type, X1 760 VAC/Y2 500 VAC

Capacitance Range: 33 pF to 4,700 pF • **Temperature Range:** −40°C to +125°C



ERP610	V	H	4470	K	EF0
Series	Safety Class/Sub-Class	Lead Spacing	Capacitance Code (pF)	Capacitance Tolerance	Lead Configuration & Packaging
ERP610	V = X1 / Y1	H = 12.5 mm	Digits 2 – 4 indicate the first three significant figures of capacitance in pF. The first digit indicates the total number of significant figures of capacitance. Example: 12,000 pF = 5120 1,800 pF = 4180 150 pF = 3150	K = ±10% M = ±20%	Please refer to datasheet

KJN Series, Y5P, Y5U & Y5V Dielectric, Y1 250/400 VAC/X1 440 VAC

Capacitance Range: 100 pF to 4,700 pF **Temperature Range:** −25°C to +125°C



KJN	331	K	Q	35		F	G
Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage	Size (mm)		Lead Spacing (mm)	Temperature Code
	2 significant digits + number of zeros	K = ±10% M = ±20%	Q = 440 VDC/X1, 250 VAC/Y1	28 = 7 31 = 8 35 = 9 39 = 10 43 = 11 47 = 12 51 = 13	55 = 14 59 = 15 63 = 16 67 = 17 71 = 18 79 = 20 87 = 22	F = 10 G = 12.5	A = Y5U or better B = Y5V G = Y5P

KJY Series, Y5P, Y5U & Y5V Dielectric, Y2 250 VAC/X1 400 VAC

Capacitance Range: 100 pF to 10,000 pF • **Temperature Range:** −25°C to +125°C



KJY	102	M	R	31		F	A
Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage	Size (mm)		Lead Spacing (mm)	Temperature Code
	2 significant digits + number of zeros	K = ±10% M = ±20%	R = 400 VAC/X1, 250 VAC/Y2	28 = 7 31 = 8 35 = 9 39 = 10 43 = 11 47 = 12 51 = 13	55 = 14 59 = 15 63 = 16 67 = 17 71 = 18 79 = 20 87 = 22	F = 10 G = 12.5	A = Y5U or better B = Y5V G = Y5P

Downloaded from Arrow.com.

Commercial Grade

KHA Series, X7R Dielectric, 1,000 – 2,000 VDC

Capacitance Range: 100 pF to 4,700 pF **Temperature Range:** −55°C to +125°C



KHA	152	K	N	35		C	H
Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage	Size (mm)		Lead Spacing (mm)	Temperature Code
	2 significant digits + number of zeros	K = ±10% M = ±20%	N = 1,000 VDC P = 2,000 VDC	28 = 7 31 = 8 35 = 9 39 = 10 43 = 11 47 = 12 51 = 13	55 = 14 59 = 15 63 = 16 67 = 17 71 = 18 79 = 20 87 = 22	C = 5 D = 7.5	H = X7R

KHB Series, Y5P Dielectric, 1,000 – 2,000 VDC

Capacitance Range: 100 pF to 10,000 pF • **Temperature Range:** −25°C to +85°C



KHB	122	K	N	31		D	G
Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage	Size (mm)		Lead Spacing (mm)	Temperature Code
	2 significant digits + number of zeros	K = ±10% M = ±20%	N = 1,000 VDC P = 2,000 VDC	28 = 7 31 = 8 35 = 9 39 = 10 43 = 11 47 = 12 51 = 13	55 = 14 59 = 15 63 = 16 67 = 17 71 = 18 79 = 20 87 = 22	C = 5 D = 7.5	G = Y5P

KHC Series, SL Dielectric, 1,000 – 2,000 VDC

Capacitance Range: 15 pF to 560 pF • **Temperature Range:** −55°C to +125°C



KHC	820	K	N	28		D	C
Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage	Size (mm)		Lead Spacing (mm)	Temperature Code
	2 significant digits + number of zeros	K = ±10% M = ±20%	N = 1,000 VDC P = 2,000 VDC	28 = 7 31 = 8 35 = 9 39 = 10 43 = 11 47 = 12 51 = 13	55 = 14 59 = 15 63 = 16 67 = 17 71 = 18 79 = 20 87 = 22	C = 5 D = 7.5	C = SL

Downloaded from Arrow.com.

Film Capacitors

THROUGH-HOLE FILM CAPACITORS

General Purpose

Metallized Polyester	Metallized Paper & Polyphenylene Sulfide
F611 & F612 5 – 37.5 mm 50 – 1,000 VDC	PME261 (P561) Impregnated Paper 400 – 1,000 VDC
F622 – 125 C Halogen Free 5 mm (Stacked) 50 – 630 VDC	SMR (F211) Polyphenylene Sulfide 150 C 50 – 400 VDC
R60 10 – 37.5 mm 50 – 1,000 VDC	
R66 7.5 mm Lead Spacing 50 – 630 VDC	
R82 5 mm Lead Spacing 50 – 400 VDC	
RSB – 125 C 5 mm (Stacked) 50 – 630 VDC	
A50 Axial 50 – 1,000 VDC	
MDK (F683/4/5/7/8) Dual In-Line High Current 50 – 630 VDC	

Pulse & AC

Single Metallized Polypropylene	Double Metallized Polypropylene	Film/Foil Polypropylene
F461 – 464 Halogen Free 160 – ,500 VDC	PHE450 (F450) DC Applications 250 – 3,000 VAC	R73 Radial 100 – 2,000 VDC
R79 5 mm Lead Spacing 160 – 630 VDC	R76 DC & Pulse Applications 250 – 2,000 VDC	PFR (F411) Radial 63 – 1,000 VDC
R75 160 – 2,000 VDC		A72 Axial 100 – 2,000 VDC
R74 AC Applications 250 – 900 VDC		
R74 – 125 C AC Applications 500 – 700 VDC		
R71 SMPS PFC Applications 420 – 1,000 VDC		
A70 Axial 160 – 630 VDC		

Safety/EMI

X1 Class	X2 Class	Y1 Class	Y2 Class	Multiple X & Y
F871 – F873 Halogen Free Metallized Polypropylene 330/480/760 VAC	F861 Metallized Polypropylene 310 VAC	P295 Metallized Impregnated Paper 500 VA	F881 Halogen Free Metalized Polypropylene 3 0 VAC	PHZ9004 (9004) Metalized Polypropylene 300 VAC (3x X2)
R49 Metallized Polypropylene 310 VAC/330 VAC	F 62 Metallized Polypropylene 310 VAC	PME295 (P295) Metallized Impregnated Paper 440 VAC/480 VAC	R4 Metalized Polypropylene 300 VAC	PMZ2074 (P 74) Metallized Impregnated Paper 275 VAC (2x X2)
R47 Metallized Polypropylene 440 VAC	R 7 Metallized Polypropylene 440 VAC/5 0 VAC		PME271Y A E (P272) Impregnated Paper 00 VAC	PZB300 (P300) Metallized Impregnated Paper 275 VAC (X2 2x Y2)
P278 Metallized Impregnated Paper 480 VAC	R46 Metallized Polypropylene 31 AC		PME271Y (P271) Impregnated Paper 250 VAC	
P410 Metallized Impregnated Paper 300 VAC	R46 (Miniature) Metallized Polypropylene 275 VAC			
PME271E (P277) Metallized Impregnated Paper 300 VAC	R46 – 125 C Metallized Polypropylene 275 VAC			
PHE844 (F844) Metallized Polypropylene 440/480 VAC	PME264 (P264) Metallized Impregnated Paper 660 VAC			
PHE845 (F845) Metallized Polypropylene 760 VAC	P409 Metallized Impregnated Paper 275 VAC			
	PME271M (P276) Metallized Impregnated Paper 275 VAC			

POWER & APPLICATION OPTIMIZED FILM CAPACITORS

Power Film

Axial	Radial	Screw/Faston Terminal
C4C Axial Round 850 – 3,000 VDC/ 450 – 750 VAC	C4AE 2 or 4 Leads DC Link 450 – 1,100 VDC	C4DE Low Inductance DC Link 400 – 1,000 VDC
C4DC GTO Snubbing 850 – 1,400 VDC/ 500 – 700 VAC	C4AS 2 or 4 Leads 850 – 3,000 VDC/ 500 – 750 VAC	C44A General Purpose & Snubbing 400 – 1,500 VDC/ 250 – 630 VAC
C4DR GTO Clamping 400 – 3,000 VDC/ 160 – 1,500 VAC	C4AT 2 or 4 Leads 250 – 850 VDC/ 160 – 450 VAC	C44B General Purpose & Snubbing 1,200 – 2,400 VDC/ 500 – 1,000 VAC
C4G Axial Round 250 – 850 VDC/ 160 – 450 VAC	C4BS IGBT Direct Mount 850 – 3,000 VDC/ 550 – 750 VAC	C44H PFC & AC Filter 330 – 440 VAC/ 700 – 1,000 VDC
	C4BT IGBT Direct Mount 400 – 850 VDC/ 250 – 450 VAC	C44P/C20A PFC & AC Filter 330 – 1,000 VAC/ 700 – 2,300 VDC
		C44U DC Link 700 – 1,300 VDC
		C93 Filter Applications 400 – 600 VDC
		C9T PFC & AC Filter 415 – 690 VAC

Motor Run Applications

Screw/Faston Terminal
C27 Plastic Case 425 – 450 VAC
C87 Aluminum Case 470 VAC

High Voltage Transient Suppression

Radial
F43 Integrated Resistor Metallized Polypropylene 250 – 630 VDC
PMR205 (P405) Integrated Resistor Metallized Impregnated Paper 125 VAC/250 VDC
P409 Integrated Resistor Metallized Impregnated Paper 275 VAC
P410 Integrated 100 Ω Resistor Metallized Impregnated Paper 300 VAC
PMZ2035 (P435) Integrated 100 Ω Resistor Metallized Impregnated Paper 300 VDC

Low Voltage Transient Suppression

Radial
F5A Integrated Varistor 18 – 63 VDC
F5B Integrated Suppression Diode 18– 63 VDC
F5D Integrated Ceramic Capacitor 63 – 100 VDC

Capacitive AC Power Supply

Radial
F862 Metallized Polypropylene 310 VAC
R47 X1 – X2 Metallized Polypropylene 440 VAC
R75 2/L Metallized Polypropylene 230 VAC / 250 VAC
PME271E (P277) Metalized Impregnated Paper 300 VAC
PME271M X2 (P276) Metalized Impregnated Paper 275 VAC

SURFACE MOUNT FILM CAPACITORS

Polyester (PET)	Polyethylene Naphthalate (PEN)	Metallized Polyphenylene Sulfide (PPS)	Y2 Class
F161 Encapsulated Stacked 50 – 400 VDC	LDE Unencapsulated Stacked 50 – 1,000 VDC	LDB Unencapsulated Stacked 16 VDC & 50 VDC	SMP253 (P101) Metallized Impregnated Paper 250 VAC
MDC (F153/4/5/7/8) Dual In-Line High Current 50 – 630 VDC	GMC (F115) Encapsulated Stacked Size 2220 – 6560 50 – 630 VDC	SMC (F125) Encapsulated Stacked 50 – 400 VDC	
MDS (F173/4/5) Dual In-Line High Current 50 – 630 VDC	GPC (F117) Encapsulated Double Metalized 63 – 1,000 VDC	SPC (F127) Encapsulated Double Metallized 100 – 630 VDC	


Downloaded from Arrow.com.

Film Capacitors
Through-Hole – General Purpose

Metallized Polyester

F611 & F612 Series Metallized Polyester Film, 5 – 37.5 mm Lead Spacing, 50 – 1,000 VDC


Capacitance Range: 0.001 to 180 µF • **Temperature Range:** −55°C to +105°C



F	611	J	F	104	M	050	C
Capacitor C ass	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Packaging
F = Film	Metallized Polyester 611 = Wound 612 = Stacked	J = 5 K = 7 5 A 10 0 B = 15 0 D = 22.5 F = 27.5 R = 37 5	See Dimension Table	First two digits represent significant figures Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	050 = 50 063 = 63 100 = 100 160 = 160 250 = 250 400 = 400 630 = 630 1K0 = 1,000	See Ordering Options Table

F622 Series, 125ºC, Halogen Free, 5 mm (Stacked), 50 – 630 VDC

Capacitance Range: 0.001 to 2 2 µF • **Temperatu e Range:** −55°C to +125°C



F	622	J	F	104	M	050	C
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capac tance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Packaging
F = Film	Metallized Polyester	J = 5	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	050 = 50 063 = 63 100 = 100 250 = 250 400 = 400 500 = 500 630 = 630	See Ordering Options Table

R60 Series, Radial, 10 – 37.5 mm Lead Spacing, 50 – 1,000 VDC (Automotive Grade)

Capacitance Range: 0.001 to 220 µF • **Temperature Range:** −55°C to +105°C



R60	M	F	2470	AA	60	K
Series	Rated Voltage (VDC)	Length (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Meta ized Polyester	C = 50 D = 63 E = 100 G = 160 I = 250 M = 400 P = 630 Q = 1000	F = 10 I = 15 N = 22 5 R = 27.5 W = 37.5	The last three digits represent significant figures. First digit specifies the number of zeros to be added.	See Ordering Options Table	00 01 30 40 50 6A L0 L1	J = ±5% K = ±10% M = ±20%

R66 Series, Radial, 7.5 mm Lead Spacing, 50 – 630 VDC (Automotive Grade)

Capacitance Range: 0.001 to 4.7 µF • **Temperature Range:** −55°C to +105°C




R66	E	D	3100	AA	7A	J
Series	Rated Voltage (VDC)	Length (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Metallized Polyester	C = 50 D = 63 E = 100 I = 250 M = 400 P = 630	D = 7.5	The last three digits represent significant figures. First digit specifies the number of zeros to be added.	See Ordering Options Table	10 6A 7A	J = ±5% K = ±10% M = ±20%

Downloaded from Arrow.com.

Metallized Polyester (cont.)

R82 Series, 5 mm Lead Spacing, 50 – 400 VDC (Automotive Grade)


Capacitance Range: 0.001 to 4.7 µF • **Temperature Range:** −55°C to +105°C



R82	D	C	3470	AA	60	J
Series	Rated Voltage (VDC)	Length (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Metallized Polyester	C = 50 D = 63 E = 100 I = 250 M = 400	C = 5.0	The last three digits represent significant figures. First digit specifies the number of zeros to be added.	See Ordering Options Table	30 50 60 70	J = ±5% K = ±10% M = ±20%

RSB Series, 125ºC, 5 mm (Stacked), 50 – 630 VDC (Automotive Grade)

Capacitance Range: 0.001 to 2. µF **Tempe ture Range:** 55°C to +125°C



RSB	D	C	3100	AA	00	J
Series	Rated Voltage (VDC)	Length (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Metallized Polyester	C = 50 D = 63 E = 100 I = 250 M = 400 W = 500 P = 630	C = 5.0	The last three digits represent signi ca t figures. First digit specifies the number of zeros to be added.	See Ordering pt ons Tab e	30 50 60 70	J = ±5% K = ±10% M = ±20%

A50 Series Axial Pulse DC Transient, 50 – 1,000 VDC (Automotive Grade)


Capacitance Range: 0.001 to 10 µF • **Temperature Range:** −55°C to +105°C



A50	C	F	3470	AA	00	J
Se ies	Rated Voltage (VDC)	Length (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Metallized Polyester	C = 5 D = 63 E = 100 I = 250 M = 400 P = 630 Q = 1000	F = 11 H= 14 K = 20.5 Q = 28 T = 33	The last three digits represent significant figures. First digit specifies the number of zeros to be added.	See Ordering Options Table	00, 60 (Standard)	J = ±5% K = ±10% M = ±20%

MDK Series, Dual In-Line, High Current, 50 – 630 VDC

Capacitance Range: 0.033 to 15 µF • **Temperature Range:** −55°C to +125°C



Legacy Part Number System

MDK	10	333	K	50	A52	P3	TUBE
Series	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Size Code	Number of Leads per Side	Packaging
Dual In-Line, Metallized Polyester	10 15	First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros.	J = ±5 K = ±10% Other tolerances on request	50 100 250 400 630	See Dimension Table	P3 = 3 leads P4 = 4 leads P5 = 5 leads P7 = 7 leads P8 = 8 leads	See Ordering Options Table

New KEMET Part Number System

F	68	3	A	A	333	K	050	T
Capacitor Class	Series	Number of Leads per Side	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Packaging
F = Film	Dual In-Line, Metallized Polyester	3 = 3 leads 4 = 4 leads 5 = 5 leads 7 = 7 leads 8 = 8 leads	A = 10 B = 15	A = Standard box size	First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros.	J = ±5 K = ±10% Other tolerances on request	050 = 50 100 = 100 250 = 250 400 = 400 630 = 630	See Ordering Options Table

Downloaded from Arrow.com.

Metallized Paper & Polyphenylene Sulfide

PME261 Series Impregnated Paper, 10.2 – 25 4 mm Lead Spacing, 400 – 1,000 VDC

Capacitance Range: 0.001 to 1 µF • **Temperature Range:** −40°C to +70°C AC app & −40°C to +100°C DC app



Legacy Part Number System


PME261	K	A	5100	K	R30
Series	Rated Voltage (VAC)	Lead Spac ng (mm)	Capacitance Code (pF)	Capacitance Tolerance	Packaging
Meta ized Paper	K = 220 E = 300 J = 500	A = 10 2 B = 15 2 C = 20.3 E = 25.4	The ast three digits represent significant figures. First digit specifies the total number of digits in the capacitiance value.	J = ±5% K = ±10% M = ±20%	See Order ng Options Table

New KEMET Part Number System

P	561	H	E	103	K	220	A
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging
P = Paper	Metallized Paper General Purpose	H = 10 2 Q = 15.2 C = 20 3 E = 25 4	See Dimension Table	First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeroes.	J = ±5% K = ±10% M = ±20%	220 = 220 300 = 300 500 = 500	See Ordering Options Table

SMR Series Polyphenylene Sulfide Film, +150°C, 5.0 – 27.5 mm Lead Spacing, 50 – 400 VDC

Capacitance Range: 0.001 to 22 µF • **Temperature Range:** −55°C to +150°C



Legacy Part Number System

SMR	5	104	K	50	J01	L4	BULK
Series	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Size Code	Lead Length	Packaging
Metallized PPS	5 = 5 0 7.5 = 7.5 10 = 10.0 15 = 15.0 22 5 = 22 5 27 5 = 27 5	First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros.	H = ±2 5% J = ±5% K = ±10% M = ±20%	50 = 50 63 = 63 100 = 100 250 = 250 400 = 400	See Dimension Table	Letter "L" followed by lead length in mm	See Ordering Options Table

New KEMET Part Number System


F	211	J	F	104	K	050	C
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Packaging
F = Film	Metallized PPS	J = 5.0 K = 7.5 A = 10.0 B = 15.0 D = 22 5 F = 27.5	See Dimension Table	First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros.	R = ±2.5% J = ±5% K = ±10% M = ±20%	050 = 50 063 = 63 100 = 100 250 = 250 400 = 400	See Ordering Options Table

Downloaded from Arrow.com.

Single Metallized Polypropylene

F461 – 464 Series Halogen Free, 160 – 2,500 VDC


Capacitance Range: 0.001 to 56 µF • **Temperature Range:** −55°C to +105°C



F	46x	K	E	223	J	160	C
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Packaging
F Fi m	Metallized Polypropy ene x = s ct ons in construction	J = 5 K 7 5 A = 10 B = 15 D = 22.5 F = 27 5 R = 37.5	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% On Request: F = ±1% G = ±2% M = ±20%	160 = 160 250 = 250 400 = 400 630 = 630 1K0 = 1000 1L2 = 1250 1K6 = 1600 2K0 = 2000 2K5 = 2500	See Ordering Options Table

R79 Series Radial, 5 mm Lead Spacing, 160 – 630 VDC


Capacitance Range: 0.001 to 0 22 µF **Temperature Range:** −55°C to +105°C



R79	G	C	2390	AA	40	K
Series	Rated Voltage (VDC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Metallized Polypropylene	G = 160 I = 250 M = 400 P = 630	C = 5	The last three digits represent significant figures. The first digit specifies the total number of zeros to be added.	See Ordering Options Table	40 45	H = 2.5% J = ±5% K = ±10%

R75 Series Radial, DC & Pulse Applications 160 – 2,000 VDC (Automotive Grade)


Capacitance Range: 220 pF to 33 µF • **Temperature Range:** −55°C to +105°C



R75	P	N	2820	AA	30	K
Series	Rated Voltage (VDC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Metallized Polypropylene	G = 160 I = 250 M = 400 P = 630 Q = 1,000 R = 1,250 T = 1,600 U = 2 000	D = 7.5 F = 10 I = 15 N = 22 5 R = 27 5 W = 37.5	The last three digits represent significant figures. The first digit specifies the total number of zeros to be added.	See Ordering Options Table	00 10 30 40 50 60 70 80	J = ±5% K = ±10% M = ±20%

R74 Series Radial, AC Applications 250 – 900 VAC (Automotive Grade)

Capacitance Range: 470 pF to 3.3 µF • **Temperature Range:** −55°C to +105°C




R74	5	N	2180	AA	00	J
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Metallized Polypropylene	L = 250 N = 400 5 = 500 6 = 600 7 = 700 9 = 900	F = 10 I = 15 N = 22.5 R = 27 5 W = 37.5	The last three digits represent significant figures. The first digit specifies the total number of zeros to be added.	See Ordering Options Table	00 30 60	J = ±5% K = ±10%

Downloaded from Arrow.com.

Single Metallized Polypropylene (cont.)

R74 Series 125°C Radial, AC Applications 500 – 700 VAC (Automotive Grade)


Capacitance Range: 470 pF to 0.018 µF • **Temperature Range:** −55°C to +125°C



R74	5	F	1100	AA	H0	J
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Metallized Polypropylene	5 = 500 7 = 700	F = 10 I = 15 N = 22.5	The last three digits represent significant figures. The first digit specifies the total number of zeros to be added.	See Ordering Options Table	H0 H1 H3 (Hx = 125 C)	J = ±5% K = ±10%

R71 Series Radial, SMPS PFC Applications 420 – 1,000 VDC

Capacitance Range: 0.01 to 22 µF • **Temperature Range:** −55°C to +105°C



R71	M	F	2100	AA	00	J
Series	Rated Voltage (VDC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Metallized Polypropylene	M = 420 V = 520 P = 630 Q = 1,000	F = 10 0 I = 15.0 N = 22.5 R = 27 5 W = 37.5	The last three digits represent significant figures. The first digit specifies the total number of zeros to be added.	See Ordering Options Table	00, 10, 20, 30, 40 (Standard)	J = ±5% K = ±10% M = ±20%

A70 Series Axial 160 – 630 VDC

Capacitance Range: 0.001 to 4.7 µF • **Temperature Range:** −55°C to +105°C




A70	G	F	2220	AA	00	J
Series	Rated Voltage (VDC)	Length (mm)	Capacitance Code (pF)	Lead and Packaging Code	Internal Use	Capacitance Tolerance
Metallized Polypropylene	G = 160 I = 250 M = 400 P = 630	F = 11 H= 14 K = 20.5 Q = 28 T = 33	The last three digits represent significant figures. The first digit specifies the total number of zeros to be added.	See Ordering Options Table	00 (Standard)	J = ±5% K = ±10% M = ±20%

Downloaded from Arrow.com.

Double Metallized Polypropylene

PHE450 Series Radial, 250 – 3,000 VAC

Capacitance Range: 0.00033 to 10 µF • **Temperature Range:** −55°C to +105°C



Legacy Part Number System


PHE450	P	B	5180	J	B04	R06
Series	Rated Voltage (VDC)	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Optional Box Code	Packaging
Metall zed Polypropylene	H = 250 K = 400 M P = 1000 R = 1 00 S = 2000 T = 2500 X = 3000	K = 7 5 A = 10.0 B 5 0 D = 22 5 F = 27.5 R = 37 5	The last three digits represent significant figu es Fi st dig t specifies the number of zeros to be added.	J = ±5% On request: F = ±1% G = ±2% H = ±2 5% K = ±10% M = ±20%	See Dimension Table	See Ordering Options Table

New KEMET Part Number System

F	450	B	D	183	J	1K0	C
Capac tor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Packaging
F = Film	Metallized Polypropylene	K = 7 5 A = 10.0 B = 15 0 D = 22.5 F = 27 5 R = 37 5	See Dimension Table	First two digits represent s gnificant figures Third digit specifies number of zeros.	J = ±5% On request: F = ±1% G = ±2% H = ±2.5% K = ±10% M = ±20%	250 = 250 400 = 400 630 = 630 1K0 = 1000 1K6 = 1600 2K0 = 2000 2K5 = 2500 3K0 = 3000	See Ordering Options Table

R76 Series Radial, DC & Pulse Applications 250 – 2,000 VDC (Automotive Grade)

Capacitance Range: 100 pF to 15 µF • **Temperature Range:** −55°C to +105°C




R76	I	D	1680	SE	30	K
Series	Rated Voltage (VDC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Double Metallized Polypropylene	I = 250 M = 400 P = 630 Q = 1,000 T = 1,600 U = 2,000	D = 7.5 F = 10 I = 15 N = 22.5 R = 27 5 W = 37 5	The last three digits represent significant figures. The first digit specifies the total number of zeros to be added.	See Ordering Options Table	00 10 30 40 50 60 70 80	H = 2.5% J = ±5% K = ±10%

Film/Foil Polypropylene

R73 Series Radial 100 – 2,000 VDC (Automotive Grade)

Capacitance Range: 100 pF to 2.2 µF **Temperature Range:** −55°C to +105°C




R73	E	I	2470	AA	00	H
Series	Rated Voltage (VDC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Polypropylene Film/ Foil	E = 100 G = 160 I = 250 M = 400 P = 630 Q = 1000 R = 1250 T = 1600 U = 2000	I = 15.0 N = 22.5 R = 27 5 W = 37.5	The last three digits represent significant figures. The first digit specifies the total number of zeros to be added.	See Ordering Options Table	00, 10, 30, 40 (Standard)	H = ±2.5% (for 2-section construction only) J = ±5% K = ±10%

Downloaded from Arrow.com.

Film/Foil Polypropylene (cont.)

PFR Series Radial 63 – 1,000 VDC

Capacitance Range: 100 pF to 0 022 µF **T pe ature Range:** −55°C to +100 C



Legacy Part Number System

PFR	5	101	J	63	J11	L4	BULK
Ser es	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Size Code	Lead Length	Packaging
Polypropylene Film/Foil	5 (Standard)	First two digits represent significant figures Third digit specifies number of zeros.	F = ±1% G = ±2% H = ±2 5% J = ±5% K = ±10%	63 = 63 100 = 100 250 = 250 400 = 400 630 = 630 1000 = 1000	See Dimension Table	Letter "L" followed by lead length in mm	See Ordering Options Table

New KEMET Part Number System

F	411	J	H	101	J	063	C
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Packaging
F = Film	Polypropylene Film/Foil	J = 5.0	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	F = ±1% G = ±2% H = ±2.5% J = ±5% K = ±10%	063 = 63 100 = 100 250 = 250 400 = 400 630 = 630 1K0 = 1000	See Ordering Options Table

A72 Series Axial 100 – 2,000 VDC

Capacitance Range: 47 pF to 0.33 µF **Temperatu e Range:** −55°C to +105°C




A72	E	F	1470	AA	00	J
Series	Rated Voltage (VDC)	Length (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Polypropylene Film/ Foil	E = 100 I = 250 M = 400 P = 630 Q = 1000 S = 1500 U = 2000	F = 11 H= 14 K = 20.5 Q = 28 T = 33	The last three digits represent significant figures. The first digit specifies the total number of zeros to be added.	See Ordering Options Table	00, 02 (Standard)	J = ±5% K = ±10% M = ±20%

X1 Class

F871 – F873 Series, Halogen Free, Metallized Polypropylene, 330/480/760 VAC

Capacitance Range: 0.001 to 8.2 µF • **Temperature Range:** −40°C to +110°C



F	871	B	K	104	M	330	C
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Voltage (VAC)	Packaging
F = Film	X1, Metallized Polypropylene	A = 10 B = 15 D = 22.5 F = 27 5 R = 37.5	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	330	See Ordering Options Table

Downloaded from Arrow.com.

X1 Class (cont.)

R49 Series, Metallized Polypropylene, 310 VAC

Capacitance Range: 0.01 to 2 2 µF **T mperature Range:** −40°C to +110°C



R49	A	I	3100	00	01	M
Se ies	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
X1, Metallized Polyp opylene	A = 310	F = 10.0 = 15.0 N = 22.5 R = 27 5	The last th ee digits represent significant figures. The first digit specifies number of zeros to be added.	See Ordering Options Table	01 M1	K = ±10% M = ±20%

R49 Series, Metallized Polypropylene, 330 VAC

Capacitance Range: 0.047 to 6 8 µF • **Temperatu e Range:** −40°C to +110°C



R49	A	N	3150	00	B1	M
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Lead and Packaging Code	Internal Use	Capacitance Tolerance
X1, Metallized Polypropylene	A = 330	I = 15.0 N = 22.5 R = 27 5 W = 37.5	The last three digits represent significant figures. The first digit specifies number of zeros to be added.	See Ordering Options Table	A1 A2 A3 B1 B2	K = ±10% M = ±20%

R47 Series, Metallized Polypropylene, 440 VAC (Automotive Grade)

Capacitance Range: 0.0047 to 2.2 µF **Temperature Range:** −40°C to +110°C



R47	4	I	2100	00	A1	M
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
X1, Metallized Polypropylene	4 = 440	F = 10 0 I = 15.0 N = 22.5 R = 27 5 W = 37.5	The last three digits represent significant figures. The first digit specifies number of zeros to be added.	See Ordering Options Table	A1 A2 A3	K = ±10% M = ±20%

P278 Series, Metallized Impregnated Paper, 480 VAC

Capacitance Range: 0.001 to 0.15 µF **Temperature Range:** −40°C to +110°C



P	278	H	E	102	M	480	A
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging
P = Paper	X1, Metallized Paper	H = 10 2 Q = 15.2 C = 20.3 S = 22 5 E = 25.4	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	480 = 480	See Ordering Options Table

Downloaded from Arrow.com.

X1 Class (cont.)

P410 Series, Metallized Impregnated Paper 300 VAC

Capacitance Range: 0.022 to 0 1 µF • **Temperature Range:** 40°C to +85°C



P	410	Q	M	223	M	300	A	H101
Capacitor Class	r es	Lead Spacing (mm)	S ze Code	Capac tance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging	Res stance (Ω)
P= Metallized Paper	RC Snubber	Q = 15.2 C = 20.3 E = 25.4	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	300 = 300	See Ordering Options Table	H plus first two digits represent significant figures. Third digit specifies number of zeros.

PME271E Series, Metallized Impregnated Paper, 300 VAC


Capacitance Range: 0.01 to 0.22 µF • **Tempe atu e Range:** −40°C to +110°C



P	277	Q	E	103	M	300	A
Capacit Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging
P = Paper	X1 Metallized Paper	Q = 15 2 C = 20 3 S = 22 5 E = 25.4	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20% (for C ≤ 0.1 µF) K = ±10% (for C > 0.1 µF)	300 = 300	See Ordering Options Table

PHE844 Series, Metallized Polypropylene, 440/480 VAC

Capacitance Range: 0.1 to 2.2 µF • **Temperature Range:** −40°C to +105°C



Legacy Part Number System

PHE844	R	D	6100	M	R06L2
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Packaging
X1, Metallized Polypropylene	R = 440	D = 22.5 F = 27 5 R = 37.5	The last three digits represent significant figures. The first digit specifies the total number of digits.	K = ±10% M = ±20%	See Ordering Options Table

New KEMET Part Number System


F	844	D	H	104	M	440	C
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging
F = Film	X1, Metallized Polypropylene	D = 22.5 F = 27.5 R = 37 5	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	440 = 440	See Ordering Options Table

Downloaded from Arrow.com.

X1 Class (cont.)

PHE845 Series, Metallized Polypropylene, 760 VAC

Capacitance Range: 0.01 to 1 0 µF • **Temperatu e Range:** −40°C to +105°C



Legacy Part Number System

PHE845	V	D	5100	M	R06L2
Series	Rated Voltage (VAC)	Lead Spac ng (mm)	Capa tance Code (pF)	Capacitance Tolerance	Packaging
X1, Metallized Polypropylene	V = 760	D = 22.5 F = 27 5 R = 37.5	The ast three digits represent significant figures. The first digit specifies the total number of digits.	K = ±10% M = ±20%	See Ordering Options Table


New KEMET Part Number System

F	845	D	D	103	M	760	C
Capacitor Class	Ser es	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging
F = Film	X1, Metallized Polypropylene	D = 22.5 F = 27.5 R = 37.5	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	760 = 760	See Ordering Options Table

X2 Class

F861 Series Metallized Polypropylene Film, 310 VAC


Capacitance Range: 0.01 – 4.7 µF • **Temperature Range:** −40°C to +110°C



F	861	B	C	104	M	310	C
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Voltage (VAC)	Packaging
F = Film	X2, Metallized Polypropylene	K = 7 5 A = 10 B = 15 D = 22.5 F = 27 5 R = 37.5	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	310	See Ordering Options Table

F862 Series, Metallized Polypropylene for Harsh Environmental Conditions, 310 VAC (Automotive Grade)

Capacitance Range: 0.047 to 4.7 µF • **Temperature Range:** −40°C to +110°C



F	862	B	C	104	M	310	C
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Voltage (VAC)	Packaging
F = Film	X2, Metallized Polypropylene	B = 15 D = 22.5 F = 27 5	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	310	See Ordering Options Table

Downloaded from Arrow.com.

X2 Class (cont.)

R47 Series, Metallized Polypropylene, 440 VAC (Automotive Grade)

Capacitance Range: 0.0047 to 2 2 F **Temperat re Range:** −40°C to +110°C



R47	4	F	1470	00	01	M
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
X2, Metal ized Polypropylene	4 = 440	F = 10.0 I = 15 0 N = 22.5 R 27 5 W = 37.5	The last three digits represent significant figures. The first digit specifies number of zeros to be added	See Ordering Options Table	01 02 03	K = ±10% M = ±20%

R47 Series, Metallized Polypropylene, 520 VAC, 85ºC (Automotive Grade)

Capacitance Range: 0.0047 to 2.2 µF **Temperature Range:** −40°C to +85°C



R47	5	I	2100	00	01	M
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
X2, Metallized Polyp opylene	5 = 520	F = 10.0 = 15.0 N = 22.5 R = 27 5 W = 37.5	The last three digits represent significant figures. The first digit specifies number of zeros to be added.	See Ordering Options Table	01 02 03	K = ±10% M = ±20%

R46 Series, Metallized Polypropylene, 310 VAC


Capacitance Range: 0.01 to 10 µF • **Temperature Range:** −40°C to +110°C



R46	3	N	3150	00	01	M
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
X2, Metallized Polypropylene	3 = 310	F = 10.0 I = 15.0 N = 22.5 R = 27 5 W = 37.5	The last three digits represent significant figures. The first digit specifies number of zeros to be added.	See Ordering Options Table	01 02 L2 M1 M2 N0 N1 N2	K = ±10% M = ±20%

R46 (Miniature) Series, Metallized Polypropylene, 275 VAC

Capacitance Range: 0.033 to 10 µF • **Temperature Range:** −40°C to +110°C



R46	K	I	3470	00	P0	M
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
X2, Metallized Polypropylene	K = 275	F = 10.0 I = 15.0 N = 22.5 R = 27 5 W = 37.5	The last three digits represent significant figures. The first digit specifies number of zeros to be added.	See Ordering Options Table	P0 P1 P2 P3	K = ±10% M = ±20%

Downloaded from Arrow.com.

X2 Class (cont.)

R46 Series, Metallized Polypropylene, 275 VAC, 125ºC


Capacitance Range: 0.01 to 1 µF **Temperature Range:** −40°C to +125°C



R46	K	N	3220	00	H1	M
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
X2, Metallized Polypropylene	K = 275	F = 10.0 I = 15.0 N = 22.5	The last three digits represent significant figures. The first digit specifies number of zeros to be added.	See Ordering Options Table	H = High Temperature H1 H2 H3 H4	K = ±10% M = ±20%

PME264 Series Metallized Impregnated Paper, 660 VAC

Capacitance Range: 0.001 to 0.1 µF • **Temperature Range:** −40°C to +85°C



Legacy Part Number System

PME264	N	B	5100	M	R30
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Packaging
X2, Metallized Paper	N = 660	B = 15.2 C = 20.3 E = 25.4	The last three digits represent significant figures. The first digit specifies the total number of digits.	M = ±20%	See Ordering Options Table

New KEMET Part Number System

P	264	Q	E	103	M	660	A
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging
P = Paper	X2, Metallized Paper	Q = 15.2 C = 20.3 E = 25.4	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	660 = 660	See Ordering Options Table

P409 Series Metallized Polypropylene, 275 VAC

Capacitance Range: 0.047 to 0.47 µF **Temperature Range:** −40°C to +85°C



P	409	Q	M	473	M	275	A	H470
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging	Resistance (Ω)
P= Metallized Paper	RC Snubber	Q = 15.2 C = 20.3 E = 25.4	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	275 = 275	See Ordering Options Table	H plus first two digits represent significant figures. Third digit specifies number of zeros.

Downloaded from Arrow.com.

X2 Class (cont.)

PME271M Series Metallized Impregnated Paper, 275 VAC

Capacitance Range: 0.001 to 0.6 µF • **Temperature Range:** −40°C to +110°C



L acy Part Number System

PME271	M	(B)	610(0)	M	R30
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Packaging
X2, Metallized Paper	M = 275	Blank = Standard A = 10.2 B = 15.2 D = 22.5	The last three digits represent significant figures. The first digit specifies the total number of digits.	M = ±20% (for C ≤ 0.1 µF) K = ±10% (for C > 0.1 µF)	See Ordering Options Table


New KEMET Part Number System

P	276	Q	E	104	M	275	A
Capacitor C ass	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging
P = Paper	X2, Metallized Pape	H = 10.2 Q = 15 2 C = 20.3 S = 22.5 E = 25.4	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20% (for C ≤ 0.1 µF) K = ±10% (for C > 0.1 µF)	275 = 275	See Ordering Options Table

Y1 Class

P295 Series Metallized Impregnated Paper, 500 VAC

Capacitance Range: 470 to 4,700 pF • **Temperature Range:** −40°C to +115°C



P	295	B	E	471	M	500	A
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging
P = Paper	Y1, Metallized Paper	B = 15.0	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	500 = 500	See Ordering Options Table

Downloaded from Arrow.com.

Y1 Class (cont.)

PME295 Series Metallized Impregnated Paper, 440 VAC/480 VAC

Capacitance Range: 470 to 4,700 pF • **Temperature Range:** −40°C to +115°C



Legacy Part Number System

PME295	R	B	3470	M	R30
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Packaging
Y1, Metallized Paper	R = 440	B = 15.0	The last h ee digits present signific n fi u The st digit specifies the total number of digits.	M = ±20%	See Orde ng Options Table


New KEMET Part Number System

P	295	B	E	471	M	440	A
Capacitor Class	Ser es	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging
P = Paper	Y1, Metallized Paper	B = 15.0	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	440 = 440	See Ordering Options Table

Y2 Class

F881 Series, Halogen Free, Metallized Polypropylene, 300 VAC

Capacitance Range: 0.01 to 1 0 µF **Temperature Range:** −40°C to +110°C



F	881	B	C	103	M	300	C
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Voltage (VAC)	Packaging
F = Film	Y2, Metallized Polypropylene	K = 7 5 A = 10 B = 15 D = 22.5 F = 27 5 R = 37 5	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	300	See Ordering Options Table

R41 Series, Metallized Polypropylene, 300 VAC (Automotive Grade)

Capacitance Range: 0.001 to 1 µF • **Temperature Range:** −40°C to +110°C



R41	3	I	2330	00	M1	M
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Y2, Metallized Polypropylene	3 = 300	F = 10.0 I = 15.0 N = 22.5 R = 27 5 W = 37.5	The last three digits represent significant figures. The first digit specifies number of zeros to be added.	See Ordering Options Table	00 M1	K = ±10% M = ±20%

Downloaded from Arrow.com.

Y2 Class (cont.)

PME271Y A–E Series Metallized Impregnated Paper, 300 VAC

Capacitance Range: 0.001 to 0.15 µF • **Temperature Range:** −40°C to +115°C



Legacy Part Number System

PME271	Y	A	4100	M	R30
Series	Rated V ltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Packaging
Y2, Metallized Paper	Y = 300	A = 10.2 B = 15.2 C = 20 3 D = 22 5 E = 25.4	The last three digits represent significant figures. The first digit specifies the total number of digits.	M = ±20% (for C ≤ 0 1 µF) K = ±10% (for C > 0.1 µF)	See Ordering Options Table

N w KEMET Part Number System

P	272	H	E	102	M	300	A
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging
P = Paper	Y2, Metallized Paper	H = 10 2 Q = 15.2 C = 20 3 D = 22.5 E = 25.4	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20% (for C ≤ 0.1 µF) K = ±10% (for C > 0.1 µF)	300 = 300	See Ordering Options Table

PME271Y Series Metallized Impregnated Paper, 250 VAC

Capacitance Range: 0.001 to 0 1 µF • **Temperature Range:** −40°C to +100°C



Legacy Part Number System

PME271	Y	410	M	R30
Series	Rated Voltage (VAC)	Capacitance Code (pF)	Capacitance Tolerance	Packaging
Y2, Metallized Paper	Y = 250	The last two digits represent significant figures. The first digit specifies the total number of digits.	M = ±20%	See Ordering Options Table

N w KEMET Part Number System

P	271	H	E	102	M	250	A
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Lead and Packaging Code
P = Paper	Y2, Metallized Paper	H = 10 2 Q = 15.2 C = 20.3 E = 25.4	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	250 = 250	See Ordering Options Table

Downloaded from Arrow.com.

Multiple X & Y

PHZ9004 Series Metallized Polypropylene Film, 300 VAC 3x X2 with Separate Terminals for Three-Phase Filtering

Capacitance Range: 3 x 1.0 µF • **Temperatu e Ra g :** 55 C to +105°C



Legacy Part Number System

PHZ9004	E	F	7100	M	R06L2
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capac tance Co e pF)	Capacitance Tolerance	Packaging
ip Capacit r X2, Metallized Polypropylene	E = 300	F = 27 5	h la t r e d g s represent significant figures The first digit specifies the total number of digits.	M ±20%	See rder ng Options Table

New KEMET Part Number System

9004	AA	105	M	300	C	DECT	V680
Capacitor Class	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging	C-Spec	V-Spec
Triple Capacitor X2, Metallized Polypropylene	See Dimension Table	First tw di its represent significant figures. Third digit specifies number of zeros.	M = ±20%	300 = 300	See Ordering Options Table	Optional additional characters at KEMET's option.	Part Number specific version code

PMZ2074 Series Metallized Impregnated Paper, 275 VAC 2x X2 with One Common Terminal

Capacitance Range: 0.15 µF + 0.033 µF, 0 15 µF + 0.047 µF, 0.15 µF + 0.068 µF, 0.22 µF + 0.082 µF, 0.22 µF + 0.1 µF
Temperature Range: −40°C to +110°C



Legacy Part Number System

PMZ2074	M	C	615	M	533	M	R30
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Capacitance Code (pF)	Internal Use	Packaging
Double Capacitor X2, Metallized Paper	M = 275	C = 20 3	The last two digits represent significant figures. The first digit specifies the total number of digits.	K = ±10% M = ±20%	The last two digits represent significant figures. The first digit specifies the total number of digits.	M (Standard)	See Ordering Options Table

New KEMET Part Number System


P	374	C	L	154	M	275	A	C333
Capacitor Class	Series	Lead Spacing (mm)	Size Code	X Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging	Y Capacitance Code
P = Paper	Double Capacitor X2, Metallized Paper	C = 20.3	See Dimension Table	First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros.	M = ±20%	275 = 275	See Ordering Options Table	C plus first two digits represent significant figures. Third digit specifies number of zeros.

Downloaded from Arrow.com.

Multiple X & Y (cont.)

PZB300 Series Metallized Impregnated Paper, 275 VAC Delta Configuration X2 + 2x Y2

Capacitance Range: X Value 0 1 µF and 0.15 µF Y Value 0.0022 µF, 0.0033 µF and 0.0047 µF • **Temperature Range:** −40°C to +100°C



Legacy Part Number System

PZB300	M	C	11	R30
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging
Delta EMI, X2 + 2x Y2, Metallized Paper	M = 275	C = 20.0	The first digit indicates the value of the X capacitor: 1 = 0.10 µF 2 = 0.15 µF The second digit indicates the value of the Y capacitor: 1 = 0.0022 µF 2 = 0.0033 µF 3 = 0.0047 µF	See Ordering Options Table

N w KEMET Part Number System

P	300	P	L	104	M	275	A	C222
Capacitor Class	Series	Lead Spacing (mm)	Size Code	X Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging	Y Capacitance Code
P = Paper	Delta EMI, X2 + 2x Y2, Metallized Paper	P = 20	See Dimension Table	First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros.	M = ±20%	275 = 275	See Ordering Options Table	C plus first two digits represent significant figures. Third digit specifies number of zeros.

Downloaded from Arrow.com.

Polyester (PET)

F161 Series Encapsulated Stacked, Size 2220 – 6560, 50 – 400 VDC

Capacitance Range: 0.01 to 12 µF • **Temperature Range:** −55°C to +125°C




F	161	P	P	103	K	050	V
Capacito Class	Series	Chip Size	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Packaging Code
F = Film	Metallized Polyester Stacked Technology	P = 2220 S = 2824 W = 4036 Y = 5045 Z = 6560	See Dimension Table	First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros.	J = ±5 K = ±10% M = ±20% Other tolerances on request.	050 = 50 063 = 63 100 = 100 250 = 250 400 = 400 630 = 630	See Ordering Options Table

MDC Series Dual In-Line, High Current, 50 – 630 VDC

Capacitance Range: 0.033 to 15 µF • **Tempe ature Range:** −55°C to +125°C

Legacy Part Number System



MDC	10	333	K	50	A52	P3	TUBE
Se ies	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Size Code	Number of Leads per Side	Packaging
Dual In-Line, Metallized Polyester	10 15	First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros.	J = ±5 K = ±10% Other tolerances on request.	50 100 250 400 630	See Dimension Table	P3 = 3 leads P4 = 4 leads P5 = 5 leads P7 = 7 leads P8 = 8 leads	See Ordering Options Table

New KEMET Part Number System

F	15	3	A	A	333	K	050	T
Capacitor Class	Series	Number of Leads per Side	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Packaging
F = Film	Dual In-Line, Metallized Polyester	3 = 3 leads 4 = 4 leads 5 = 5 leads 7 = 7 leads 8 = 8 leads	A = 10 B = 15	A = Standard box size	First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros.	J = ±5 K = ±10% Other tolerances on request	050 = 50 100 = 100 250 = 250 400 = 400 630 = 630	See Ordering Options Table

Downloaded from Arrow.com.

Polyester (PET) (cont.)

MDS Series Dual In-Line Low Profile, High Current, 50 – 630 VDC

Capacitance Range: 0.033 to 6 8 µF • **Tempe ature Range:** −55°C to +125°C



Legacy Part Number System

MDS	10	333	K	50	A52	P3	TUBE
Series	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Size Code	Number of Leads per Side	Packaging
Dual In-Line, Metallized Polyester	10 15	First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros.	J ±5 K = ±10% Other tolerances on request.	050 = 50 100 = 100 250 = 250 400 = 400 630 = 630	See Dimension Table	P3 = 3 leads P4 = 4 leads P5 = 5 leads	See Ordering Options Table

New KEMET Part Number System

F	17	3	A	A	333	K	050	T
Capacitor Class	Series	Number of Leads per Side	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Packaging
F = Film	Dual In-Line, Metallized Polyester	3 = 3 leads 4 = 4 leads 5 = 5 leads	A = 10 B = 15	A = Standard box size	First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros.	J = ±5 K = ±10% Other tolerances on request	050 = 50 100 = 100 250 = 250 400 = 400 630 = 630	See Ordering Options Table

Polyethylene Naphthalate (PEN)

LDE Series Unencapsulated Stacked Chip, Size 1206 – 6054, 50 – 1,000 VDC (Automotive Grade)

Capacitance Range: 0.001 to 4.7 µF **Temperature Range:** −55°C to +125°C



LDE	C	C	2560	M	A	5	N	00
Series	Rated Voltage (VDC)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Dielectric	Version	Packaging	Internal Use
Metallized PEN	C = 50 D = 63 E = 100 I = 250 M = 400 P = 630 Q = 1000	See Dimension Table	Digits 2-4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	K = ±10% M = ±20% J = ±5% on request	A = PEN	5 = Standard 0 = Miniature	See Ordering Options Table	00 (Standard)

Downloaded from Arrow.com.

Polyethylene Naphthalate (PEN) (cont.)

GMC Series Encapsulated Stacked, Size 2220 – 6560, 50 – 630 VDC

Capacitance Range: 0.001 to 5 6 µF • **Tempe ature Range** 55°C to +125°C



egacy Part Number System

GMC	5.7	102	K	50	J31	TR12
Series	Chip Length (mm)	Capacitance Code (pF)	Capacitance Tole anc	Rated Voltage (VDC)	Size Code	Packaging
Metallized PEN	5.7 7 3 0.2 12. 16.5	First two digits indicate the two most significant digits of the capacitance alue in p cofarads The third digit is the n mber of following zeros.	J = ±5% K = ±10% Other tolerances on request.	50 63 100 250 400 630	See Dimension Table	See Ordering Options Table

New KEMET Part Number System

F	115	P	L	102	K	050	V
Capacitor Class	Series	Chip Size	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Packaging
F = Film	Metallized PEN	P = 2220 S = 2824 W = 4036 Y = 5045 Z = 6560	See Dimension Table	First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros.	J = ±5% K = ±10% Other tolerances on request.	050 = 50 063 = 63 100 = 100 250 = 250 400 = 400 630 = 630	See Ordering Options Table

GPC Series Encapsulated Double Metallized, Size 2824 – 6560, 63 – 1,000 VDC

Capacitance Range: 470 pF to 1.0 µF • **Temperature Range:** −55°C to +125°C



Legacy Part Number System

GPC	7.3	471	K	63	K31	TR12
Series	Chip Length (mm)	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Size Code	Packaging
Double Metallized PEN	7.3 10.2 12.7 16.5	First two digits indicate the two most significant digits of the capacitance value in picofarads The third digit is the number of following zeros.	K = ±10% M = ±20% Other tolerances on request.	63 100 160 250 400 630 1,000	See Dimension Table	See Ordering Options Table

New KEMET Part Number System


F	117	S	G	471	K	063	V
Capacitor Class	Series	Chip Size	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Packaging
F = Film	Double Metallized PEN	S = 2824 W = 4036 Y = 5045 Z = 6560	See Dimension Table	First two digits indicate the two most significant digits of the capacitance value in picofarads. The third digit is the number of following zeros.	K = ±10% M = ±20% Other tolerances on request.	063 = 63 100 = 100 160 = 160 250 = 250 400 = 400 630 = 630 1K0 = 1,000	See Ordering Options Table

Downloaded from Arrow.com.

Metallized Polyphenylene Sulfide (PPS)

LDB Series Unencapsulated Stacked Chip, Size 1206 – 1812, 16 & 50 VDC

Capacitance Range: 0.0033 to 0 1 µF • **Temperature Range:** −55°C to +125°C



LDB	A	A	2120	G	C	5	N	0
Series	Rated Voltage (VDC)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Dielectric	Version	Packaging	Internal Use
Metallized PPS	A = 16 C = 50	See Dimension Table	Digits 2-4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	G = ±2% J = ±5%	C = PPS	5 = Standard	See Ordering Options Table	0 (Standard)

SMC Series Encapsulated Stacked, Size 2220 – 6560, 50 – 400 VDC

Capacitance Range: 0.001 to 3 3 µF • **Tempe ature Range:** −55°C to +125°C

Le acy Part Number System



SMC	5 7	102	J	50	J31	TR12
Series	Chip Length (mm)	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Siz Code	Packagi g
Metallized PPS	5.7 7.3 10.2 12.7 16.5	First two digits represent significant figures. The third digit specifies number of zeros.	G = ±2% H = ±2.5% J = ±5%	50 100 250 400	See Dimension Table	See Ordering Options Table

New KEMET Part Number System

F	125	P	L	102	J	050	V
Capacitor Class	Series	Chip Size	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Packaging
F = Film	Metallized PPS	P = 2220 S = 2820 W = 4036 Y = 5045 Z = 6560	See Dimension Table	First two digits represent significant figures. The third digit specifies number of zeros.	G = ±2% R = ±2.5% J = ±5%	050 = 50 100 = 100 250 = 250 400 = 400	See Ordering Options Table

Downloaded from Arrow.com.

Metallized Polyphenylene Sulfide (PPS) (cont.)

SPC Series Encapsulated Double Metallized, Size 2824 – 6560, 100 – 630 VDC

Capacitance Range: 470 pF to 0.68 µF • **Temperature Range:** −55°C to +125°C



Le acy Part Number System

SPC	7.3	471	K	100	K31	TR12
Series	Chip Length (mm)	Capacitance Code (pF)	Capacitanc Tolerance	Rated Voltage (VDC)	Size Code	Packaging
Double Metallized PPS	7.3 10 2 12 7 16.5	First two digits represent significant figures. The third digit specifies number of zeros.	G = ±2% H = ±2.5% J = ±5% K = ±10%	10 250 400 630	See Dimension Table	See Ordering Options Table

New KEMET Part Number System

F	127	S	G	471	K	100	V
Capacitor Class	Series	Chip Size	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Packaging
F = Film	Double Metallized PPS	S = 2824 W = 4036 Y = 5045 Z = 6560	See Dimension Table	First two digits represent significant figures. The third digit specifi s mber of zeros	G = ±2% R = ±2.5% J = ±5% K = ±10%	100 250 400 630	See Ordering Options Table

Y2 Class

SMP253 Series Metallized Impregnated Paper, 250 VAC

Capacitance Range: 1,000 to 4,700 pF • **Temperature Range:** −40°C to +100°C



Legacy Part Number System

SMP253	M	A	4100	M	TR24
Series	Rated Voltage (VAC)	Chip Length (mm)	Capacitance Code (pF)	Capacitance Tolerance	Packaging
Y2, Metallized Paper	M = 250	A = 12.7	The last three digits represent significant figures. The first digit specifies the total number of digits.	M = ±20%	See Ordering Options Table

New KEMET Part Number System

P	101	AA	102	M	250	V
Capacitor Class	Series	Chip Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging
P = Paper	Y2, Metallized Paper	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	250 = 250	See Ordering Options Table

Downloaded from Arrow.com.

Axial

C4C Series, Axial Round, 850 – 3,000 VDC/450 – 750 VAC

Capacitance Range: 0.0068 to 2 5 µF **Temperature Range:** −40°C to +85°C



C4	C	A	M	U	B	3100	AA	0	J
Series	Type	Fire Protection	Rated Voltage (VDC)	Insulation	Lead Diameter (mm)	Capacitance Code (pF)	Lead and Packaging Code	Capacitor Length (mm)	Tolerance
C4 = MKP capacitors	C = Round body, snubber application	A = No fire retardant S = Fire retardant (on request)	M = 850 P = 1,200 W = 2,000 Y = 3 000	U = Polyester tape & resin protection 0 = Uninsulated (on request)	B = 0.8 C = 1.0 D = 1.2	Digits 2 – 4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	AA (Standard)	0 = 33 1 = 44 3 = 58	J = 5% K = 10%

C4DC Series, GTO Snubbing, 850 – 1,400 VDC/500 – 700 VAC

Capacitance Range: 0.5 to 6 µF • **Temperature Range:** −40°C to +85°C



C4DC	M	A	Q	4150	AA0	J
Series	Rated Voltage (VDC)	Case	Terminal Style	Capacitance Code (pF)	Internal Code	Tolerance
C4DC = MKP, GTO Application	M = 850 N = 1000 R = 1400	A = Axial plastic case	Q = M8 Threaded Inserts	Digits 2 – 4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	AA0 = Standard	J = 5% K = 10%

C4DR Series, GTO Clamping, 400 – 3,000 VDC/160 – 1,000 VAC

Capacitance Range: 1 to 220 µF • **Temperature Range:** −40°C to +85°C



C4DR	F	A	Q	5250	AA0	J
Series	Rated Voltage (VDC)	Case	Terminal Style	Capacitance Code (pF)	Internal Code	Tolerance
C4DR = MKP, Clamping Application	F = 400 H = 600 J = 700 M = 850 P = 1,200 S = 1,500 Y = 3,000	A = Axial plastic case	Q = M8 threaded inserts	Digits 2-4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	AA0 = Standard	J = 5% K = 10%

C4G Series, Axial Round, 250 – 850 VDC/160 – 450 VAC

Capacitance Range: 0.15 to 40 µF • **Temperature Range:** −40°C to +85°C



C4	G	A	D	U	B	4100	AA	4	J
Series	Type	Fire Protection	Rated Voltage (VDC)	Insulation	Lead Diameter (mm)	Capacitance Code (pF)	Lead and Packaging Code	Capacitor Length (mm)	Tolerance
C4 = MKP capacitors	G = Round body, switching application	A = No fire retardant S = Fire retardant (on request)	D = 250 F = 400 H = 600 J = 700 M = 850	U = Polyester tape & resin protection 0 = Uninsulated (on request)	B = 0.8 C = 1.0 D = 1 2	Digits 2 – 4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	AA (Standard)	4 = 20.5 5 = 28 0 = 33 1 = 44 3 = 58	J = 5% K = 10%

Downloaded from Arrow.com.

Radial

C4AE Series, Radial, 2 or 4 Leads, 450 – 1,100 VDC, for DC Link

Capacitance Range: 1 to 100 µF **Temperature Range:** −40°C to +105°C



C4	A	E	G	B	W	4 4 5 0	A	1	W	J
Series			DC Voltage	Case Code	Terminals Code	Capacitance Code (pF)	Variants	Terminals Diameter (mm)	Case Letter[2]	Tolerance
C4 = MKP Capacitors	A = Box Wire Terminals	E = DC Link	E = 300 V G = 450 V H = 600 V I = 80 V J = 700 V K = 750 V L = 500 V M = 850 V N = 1000 V O = 900 V Q = 1100 V U = 1300 V	B = Box plastic case	U = Single copper wire W = Double coppe wire Z = Special wire	Digits 9, 10, & 11 indicate the first 3 digits of capacitance value. Digit 8 indicates the number of zeroes that must be added t obtain rated capacitance in pF.	A = Standard B = Special H[1] = 100 C	1 = 0.8 2 = 1 3 = 1.2	0, A, B, C, D, E, F, G, H, J, L, M, N, W, X, Y, 1, 2	J = 5% K = 10%

C4AS Series, 2 or 4 Leads, 850 – 3,000 VDC/500 – 750 VAC

Capacitance Range: 0.022 to 5 µF • **Temperature Range:** −40°C to +85°C



C4	AS	M	B	U	3150	A3	A	J
Series	Type	Rated Voltage (VDC)	Case	Number of Leads	Capacitance Code (pF)	Lead Diameter (mm)	Size Code	Tolerance
C4 = MKP Capacitors	AS = Radial box, snubber application	M = 850 N = 1,000 P = 1,200 W = 2,000 Y = 3,000	B = Plastic box with epoxy resin sealing	U = 2 lead W = 4 lead	Digits 2-4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	A1 = 0.8 A3 = 1.2	See Dimension Table	J = 5% K = 10%

C4AT Series, 2 or 4 Leads, 250 – 850 VDC/160 – 450 VAC

Capacitance Range: 0.22 to 60 µF • **Temperature Range:** −40°C to +85°C



C4	AT	D	B	U	4100	A3	0	J
Series	Type	Rated Voltage (VDC)	Case	Number of Leads	Capacitance Code (pF)	Lead Diameter (mm)	Size Code	Tolerance
C4 = MKP Capacitors	AT = Radial box, switching application	D = 250 F = 400 G = 450 H = 600 J = 700 M = 850	B = Plastic box with epoxy resin sealing	U = 2 lead W = 4 lead	Digits 2-4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	A1 = 0.8 A3 = 1.2	See Dimension Table	J = 5% K = 10%

C4BS Series, IGBT Box, 850 – 3,000 VDC/550 – 750 VAC

Capacitance Range: 0.047 to 5 µF • **Temperature Range:** −40°C to +85°C



C4	BS	M	B	X	3470	Z	E	E	J
Series	Type	Rated Voltage (VDC)	Case	Number of Leads	Capacitance Code (pF)	Internal Code	Termination Style	Size Code	Tolerance
C4 = MKP Capacitors for Power Applications	BS = Radial box with tab terminals, IGBT application	M = 850 N = 1,000 P = 1,200 W = 2,000 Y = 3,000	B = Plastic box with epoxy resin sealing	X = Standard	Digits 2-4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	Z = Standard	A = Style A B = Style B E = Style E F = Style F G = Style G	See Dimension Table	J = 5% K = 10%

Downloaded from Arrow.com.

Film Capacitors
Power & Application Optimized – Power Film

Radial (cont.)

C4BT Series, IGBT Box, 400 – 850 VDC/250 – 450 VAC
Capacitance Range: 1 to 60 µF • **Temperature Range:** −40°C to +85°C



C4	BT	F	B	X	4330	Z	E	E	J
Series	Type	Rated Voltage (VDC)	Case	Number of Leads	Capacitance Code (pF)	Internal Code	Termination Style	Size Code	Tolerance
C4 = MKP Capac tors for Power Applications	BT = Radial box w th tab terminals, switching application	F = 400 M = 850	B = Plastic box with epoxy resin sealing	X = Standard	Digits 2 – 4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added	Z = Standard	A = Style A E = Style E	See Dimension Table	J = 5% K = 10%

Screw/Faston Terminal

C4DE Series, Low Inductance DC Link, 400 – 1,000 VDC
Capacitance Range: 47 to 380 µF • **Temperature Range:** −40°C to +85°C



C4DE	F	P	Q	6175	A8T	K
Series	Rated Voltage (VDC)	Case & Fixing Bolt Code	Terminal Style	Capacitance Code (pF)	Internal Code	Tolerance
C4DE = MKP, DC Link Application	F = 400 H = 600 I = 800 N = 1,000	P = Cylindrical plastic case with fixing feet	Q = M8 threaded inserts	Digits 2-4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	A8T = Standard	K = 10%

C44A Series, Aluminum Case, 400 – 1,500 VDC
Capacitance Range: 1 to 330 µF • **mperature Range:** −40°C to +85°C



C44A	F	F	P	5150	ZA0	J
Series	Rated Voltage (VDC)	Case & Fixing Bolt Code	Terminal Style	Capacitance Code (pF)	Internal Code	Tolerance
C44A = MKP, General Purpose	F = 400 H = 600 J = 700 M = 850 P = 1,200 S = 1,500	F = Cylindrical aluminum case with M8 bolt G = Cylindrical aluminum case with M12 bolt	P = M6 Threaded posts R = M10 Threaded posts Q = M8 Threaded posts (on request) 2 = Simple faston 6.3 x 0.8 mm (on request) 3 = Double faston 6.3 x 0.8 mm (on request)	Digits 2-4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	ZA0, ZB0, ZC0, ZD0, ZE0, ZF0, ZG0, ZH0 = Standard	J = 5% K = 10%

C44B Series, Aluminum Case, Snubber Applications, 1,200 – 2,400 VDC
Capacitance Range: 0.047 to 4 µF • **Temperature Range:** −40°C to +85°C



C44B	P	F	001	3100	ZB0	J
Series	Rated Voltage (VDC)	Case & Fixing Bolt Code	Terminal Style	Capacitance Code (pF)	Internal Code	Tolerance
C44B = MKP, Snubber Application	P = 1,200 W = 2,000 X = 2,400	F = Cylindrical aluminum case with M8 bolt G = Cylindrical aluminum case with M12 bolt	P = M6 Threaded posts 1 = Single fasten 2.8 x 0.8 mm	Digits 2-4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	ZA0, ZB0, ZC0 = Standard	J = 5% K = 10%

Downloaded from Arrow.com.

Screw/Faston Terminal (cont.)

C44H Series, 330 – 440 VAC, 700 – 1,000 VDC, for PFC and AC Filter

Capacitance Range: 100 to 600 µF • **Temperature Range:** −40°C to +75°C



C44H	L	G	P	6100	A	A	S	J
Series	Rated Voltage	Case & Fixing Bolt Code	Terminal Style	Capacitance Code (pF)	Internal Code	Internal Code		Tolerance
C44H = MKP Capacitors for AC filtering	L = 330 V_{rms} K = 440 V_{rms}	G = Cylindrical aluminum case with M12 bolt	P = M6 Threaded Posts R = M10 Threaded Posts	Digits 9-11 indicate the first three digits of the capacitance value. Digit 8 indicates the number of zeros to be added.	A = Standard Z = Special			J = 5% K = 10%

C44P/C20A Series, for PFC & AC Filter, 330 – 1,000 VAC/700 – 2,300 VDC

Capacitance Range: 10 to 600 µF **emperature Range:** −40°C to +80°C



C	44	P	L		G	R	6	1	0	0	A	A	S	J
Series		Application	Rated Voltage (VAC)		Case Type	Terminal Style	Capacitance Code (pF)				Internal Code	Internal Codes		Tolerance
MKP Capacitors for Power Applications	44 = 330 – 440 VAC 20 = 550 – 1,000 VAC	AC Filter P = C44 A = C20	For C44P: L = 330 K = 440	For C20A: K = 550 L = 640 Q = 780 Z = 1000	G = M12 bolt	R = Male M10	Digits 9 – 11 indicate the first 3 digits of capacitance value. Digit 8 indicates the number of zeros that must be added to obtain rated capacitance in pF.				A = Standard Z = Special			J = 5% K = 10%

C44U Series, for DC Link, 700 – 1,300 VDC

Capacitance Range: 50 to 600 µF **Temperature Range:** −40°C to +85°C



C4	4	U	Q	G	T	6	5	0	0	F	8	S	K
Series			DC Voltage	Case & Fixing	Terminals Code	Capacitance Code (pF)				Variants	Case Diameter	Film Type	Tolerance
MKP Capacitors for Power Applications	Cylindrical types	DC-Link	J = 700 V O = 900 V Q = 1100 V U = 1300 V	G = Cylindrical case with threaded bolt M12 E = Cylindrical case without threaded bolt	T = M6 female terminals Q = M8 male terminals Y = M8 female terminals	Digits 9, 10, & 11 indicate the first 3 digits of capacitance value. Digit 8 indicates the number of zeroes that must be added in order to obtain rated capacitance in pF.				A = 85 C Hot Spot temperature series F = 70 C Hot Spot temperature series	7 = 76 mm 8 = 85 mm	T = Standard film S = Segmented film	J = 5% K = 10%

C93 Series, Aluminum Case, Filter Applications, 400 – 600 VDC

Capacitance Range: 10 to 100 µF • **Temperature Range:** −25°C to +55°C



C93	0	Z	G	3	5500	ZA0	X
Series	Rated Voltage (VAC)	Internal Code	Case & Mounting	Terminal Style	Capacitance Code (pF)	Internal Code	Tolerance
C93 = Single Phase Power Factor Correction Capacitors	0 = 320 1 = 415 3 = 460	Z = Standard	G = Cylindrical aluminum case with M12 bolt	3 = Double fasten	Digits 2-4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	ZA0, RA0 & RS0 = Standard	X = -5/+15%

Downloaded from Arrow.com.

Screw/Faston Terminal (cont.)

C9T Series, Aluminum Case, PFC & AC Filter, 415 – 690 VAC

Capacitance Range: 19.2 to 184.8 µF • **Temperature Range:** −25°C to +55°C



C9T	S	5	A	D	5308	AA0	X
Series	Type	Rated Voltage (VAC)	Terminal Style	Internal Connection	Capacitance Code (pF)	Internal Code	Tolerance
C9T = Cylindrical Three-Phase Capacitors	S = Slim	A = 525 D = 690 5 = 415 6 = 450	A = Single quick connect B = Double quick connect M = Screw Terminal	D = Delta Y = Star	Digits 2-4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	AA0 = Standard	X = -5% / +15%

C27 Series, Plastic Case, 250 – 470 VAC

Capacitance Range: 1 to 100 µF • **Temperature Range:** −25°C to +100°C



C27	4	A	C	2	4100	AA	4	J
Series		Marking	Case & Fixing Bolt Code	Terminal Style	Capacitance Code (pF)	Packaging	Internal Use	Tolerance
C27 Motor Run Capacitors	4 = 30,000 hours/420 VAC (Class A) or 10,000 hours/470 VAC (Class B) 6 = 10,000 hours/420 VAC (Class B) or 3,000 hours/470 VAC (Class C) 7 = 10,000 hours/275 VAC (Class C) or 1,000 hours/425 VAC (Class D)	A = C274 C = C276 L = C277	C = Cylindrical plastic case with M8 bolt	2 = Single fasten 6.3 x 0.8 3 = Double fasten 6 3 x 0.8 A = Polar cable (tinned end) B = Polar cable (untinned end) F = Bipolar cable (40 mm unsheathed, 8 mm exposed end)	Digits 2 – 4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	AA, AF, AL, LG = Standard	0, 1, 2, 5 = Standard	J = 5%

C87 Series, Aluminum Case, 470 VAC

Capacitance Range: 1 to 80 µF • **Temperature Range:** −25°C to +85°C




C87	0	C	F	2	4300	AA	4	J
Series		Marking	Case & Fixing Bolt Code	Terminal Style	Capacitance Code (pF)	Packaging	Internal Use	Tolerance
C87 = Motor Run Capacitors	0 = 10,000 hours/420 VAC (Class B) or 3,000 hours/470 VAC (Class C) 8 = 30,000 hours/420 VAC (Class A) or 10,000 hours/470 VAC (Class B) 1 = Legacy (not for new design) 5 = Legacy (not for new design)	A, C, W = Standard	F = Cylindrical aluminum can with M8 bolt G = Cylindrical aluminum can with M12 bolt	2 = Single fasten 6.3 x 0.8 3 = Double fasten 6.3 x 0.8	Digits 2 – 4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	AA= Standard	0, 1, 2, 4, 5 = Standard	J = 5% K = 10%

Downloaded from Arrow.com.

Radial

F43 Series, Integrated Resistor Metallized Polypropylene, 250 – 630 VDC

Capacitance Range: 0.01 to 1 0 µF • **emperature Range:** −55°C to +100°C



F	43	K	N	3100	XX	01	M
Capac tor C ass	Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
Legacy PN: F New KEMET PN: Om t this character	RC Snubber, Metallized Polyp opylene	I = 160 M = 200 P = 220 K = 275 (X2)	I = 15.0 N = 22.5 R = 27.5	The last three digits represent sign ficant figures. The first digit specifies number of zeros to be added.	Contact KEMET for packaging availability and details	00, 01, 04 (Standard)	K = ±10% M = ±20%

PMR205 Series Integrated Resistor Metallized Impregnated Paper, 125 VAC/250 VDC

Capacitance Range: 0.1 to 1.0 µF • **Temperature Range:** −40°C to +85°C

Legacy Part Number System



PMR205	A	B	6100	M	033	R30
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Resistance (Ω)	Packaging
RC Snubbe , Metallized Paper	A = 125	B 15 2 C = 20.3 E = 25.4	The last h ee digits epresent significant figures. The first digit spec fies the total number of digits.	M = ±20%	Resistance Value in Ω	See Orde ng Options Table

New KEMET Part Number System

P	405	Q	E	104	M	125	A	H330
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging	Resistance (Ω)
P = Metallized Paper	RC Snubber	Q = 15.2 C = 20.3 E = 25.4	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	125 = 125	See Ordering Options Table	H plus first two digits represent significant figures. Third digit specifies number of zeros.

P409 Series Integrated Resistor Metallized Impregnated Paper, Class X2, 275 VAC

Capacitance Range: 0.047 to 0.47 µF • **Temperature Range:** −40°C to +85°C



P	409	Q	M	473	M	275	A	H470
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging	Resistance (Ω)
P= Metallized Paper	RC Snubber	Q = 15.2 C = 20 3 E = 25.4	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	275 = 275	See Ordering Options Table	H plus first two digits represent significant figures. Third digit specifies number of zeros.

Downloaded from Arrow.com.

Radial (cont.)

P410 Series, Integrated 100 Ω Resistor Metallized Impregnated Paper, 300 VAC

Capacitance Range: 0.022 to 0.1 µF • **Temperature Range:** −40°C to +85°C



P	410	Q	M	223	M	300	A	H101
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging	Resistance (Ω)
P= M tallized Paper	RC Snubber	Q = 15.2 C = 20.3 E = 25.4	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	300 = 300	See Ordering Options Table	H plus first two digits represent significant figures. Third digit specifies number of zeros.

PMZ2035 Series, Integrated 100 Ω Resistor Metallized Impregnated Paper, 440 VAC/1,000 VDC

Capacitance Range: 0.1 µF • **Temperature Range:** −40°C to +85°C



Legacy Part Number System

PMZ2035	R	E	6100	K	150	R30
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Resistance (Ω)	Packaging
RC Snubber, Metallized Paper	R = 440	E = 25.4	The last three digits represent s gnificant figu es. The fir t dig t specifies the total number of digits.	K = ±10% M 2	Resistance Value in Ω	See Ordering Options Table

N w KEMET Part Number System

P	435	E	J	104	K	440	A	H151
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging	Resistance (Ω)
P = Metallized Paper	RC Snubber	E = 25.4	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	440 = 440	See Ordering Options Table	H plus first two digits represent significant figures. Third digit specifies number of zeros.

Downloaded from Arrow.com.

Radial

F5A Series Metallized Polyester Film with Integrated Varistor, 18 – 63 VDC

Capacitance Range: 0.1 to 2.2 µF **Temperature Range:** −55°C to +125°C



F5A	H	C	4100	DQ	A	6	K
Series	Rated Voltage (VDC)	Lead Spacing (mm)	Capacitance Code (pF)	Lead and Packaging Code	Varistor Voltage V_v @ 1 mA	S ze Code	Capacitance Tolerance
Film Capac to Ceramic Varistor Unit	B = 1 H = 25 J 30 N = 45 C = 50 D = 63	C = 5 F = 10	Digits 2 – 4 indicate the first three dig ts of the capacitance value. First digit indicates the number of zeros to be added.	See Ordering Options Table	See Varistor Voltage Table	See Dimension Table	K = ±10% M = ±20%

F5B Series Metallized Polyester Film with Integrated Suppression Diode, 18 – 63 VDC


Capacitance Range: 0.1 to 2.2 µF **Temperature Range:** −55°C to +125°C



F5B	H	C	4100	DQ	A	7	K
Series	Rated Voltage (VDC)	Lead Spacing (mm)	Capacitance Code (pF)	Lead and Packaging Code	Diode Breakdown Voltage V_{BR} @ 1 mA	Size Code	Capacitance Tolerance
F lm Capacitor/ Diode Unit	B = 18 H = 25 J = 30 N = 45 C = 50 D = 63	C = 5	Digits 2 – 4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	See Ordering Options Table	See Diode Breakdown Voltage Table	See Dimension Table	K = ±10% M = ±20%

F5D Series Metallized Polyester Film with Integrated Ceramic Capacitor, 63 – 100 VDC

Capacitance Range: 0.1 to 2.2 µF **Temperature Range:** −55°C to +125°C




F5D	D	C	3100	DQ	W	5	M
Series	Rated Voltage (VDC)	Lead Spacing (mm)	Capacitance Code (pF)	Lead and Packaging Code	Ceramic Capacitor Value	Size Code	Capacitance Tolerance
Film Capacitor/ Ceramic Capacitor Unit	D = 63 E = 100	C = 5 mm F= 10 mm	Digits 2 – 4 indicate the first three digits of the capacitance value. First digit indicates the number of zeros to be added.	See Ordering Options Table	See Ceramic Capacitor Table	See Dimension Table	K = ±10% M = ±20%

Downloaded from Arrow.com.

Film Capacitors
Power & Application Optimized – Capacitive AC Power Supply


Radial

F862 Series, Metallized Polypropylene, 310 VAC (Automotive Grade)
Capacitance Range: 0.1 to 4.7 µF • **Temperature Range:** −40°C to +110°C




F	862	B	C	104	M	310	C
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Voltage (VAC)	Packaging
F = Film	X2, Metallized Polypropylene	B = 15 D = 22.5 F = 27.5	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	310	See Ordering Options Table

R47 Series, Metallized Polypropylene, 440 VAC (Automotive Grade)
Capacitance Range: 0.0047 to 2.2 µF **Temperature Range:** −40°C to +110°C



R47	4	F	1470	00	01	M
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Packaging	Internal Use	Capacitance Tolerance
X2, Metallized Polypropylene	4 = 440	F = 10.0 I = 15.0 N = 22.5 R = 27.5 W = 37.5	The last three digits represent significant figures. The first digit specifies number of zeros to be added.	See Ordering Options Table	01 02 03	K = ±10% M = ±20%

R75 2/L Series Metallized Polypropylene, 230 VAC/250 VAC
Capacitance Range: 0.01 to 10 µF • **Temperature Range:** −55°C to +105°C



R75	2/L	R	3680	DQ	3	–	K
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Ordering Code	Electrical Characteristics	Internal use	Capacitance Tolerance
	2 = 230 L = 250	I = 15 N = 22.5 R = 27.5 W = 37.5	Two significant digits + number of zeros	DQ GY CK AA 40 50	Dimensions and electrical characteristics (0 – 9)		J = ±5% K = ±10% M = ±20%

Downloaded from Arrow.com.

Radial (cont.)

PME271E Series Metallized Impregnated Paper, Class X1, 300 VAC

Capacitance Range: 0.01 to 0.22 µF • **Temperature Range:** −40°C to +110°C

acy Part Number System



PME271	E	(D)	510(0)	M	R30
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capac tance Code (pF)	Capacitance Tolerance	Packaging
X1, Metallized Paper	E = 300	Blank = Standard D = 22.5	The last three digits represent significant figures. The first digit specifies the total number of digits.	M = ±20% (for C ≤ 0.1 µF) K = ±10% (for C > 0.1 µF)	See Ordering Options Table

New KEMET Part Number System

P	277	Q	E	103	M	300	A
Capacitor C ass	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging
P Paper	X1, Metallized Paper	Q = 15.2 C = 20.3 S = 22 5 E = 25 4	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20% (for C ≤ 0.1 µF) K = ±10% (for C > 0.1 µF)	300 = 300	See Ordering Options Table

PME271M Series Metallized Impregnated Paper, Class X2, 275 VAC

Capacitance Range: 0.001 to 0 6 µF • **Temperature Range:** −40°C to +110°C

Legacy Part Number System



PME271	M	(B)	610(0)	M	R30
Series	Rated Voltage (VAC)	Lead Spacing (mm)	Capacitance Code (pF)	Capacitance Tolerance	Packaging
X2, Metallized Paper	M = 275	Blank = Standard A = 10.2 B = 15.2 D = 22.5	The last three digits represent significant figures. The first digit specifies the total number of digits.	M = ±20% (for C ≤ 0.1 µF) K = ±10% (for C > 0.1 µF)	See Ordering Options Table

N w KEMET Part Number System

P	276	Q	E	104	M	275	A
Capacitor Class	Series	Lead Spacing (mm)	Size Code	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VAC)	Packaging
P = Paper	X2, Metallized Paper	H = 10.2 Q = 15.2 C = 20.3 S = 22.5 E = 25.4	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20% (for C ≤ 0.1 µF) K = ±10% (for C > 0.1 µF)	275 = 275	See Ordering Options Table

Downloaded from Arrow.com.

Downloaded from Arrow.com.

Supercapacitors

SUPERCAPACITORS				
Small Cell		Large Cell		
Radial	Surface Mount	Snap-In	Screw Terminal	Bank Module
FA 5.5 V & 11 V 70°C	FC 3.5 V – 5.5 V 70°C	S501 2.7 V 65°C	S301 2.7 V 65°C	S02 16 V – 48 V 65°C
FE 5.5 V 70°C			S301 Development Balancing Kit	
FG 3.5 V & 5.5 V 70°C & 85°C				
FM 3.5 V, 5.5 V & 6.5 V 70°C & 85°C				
FR 5.5 V 85°C				
FS 5.5 V, 11 V & 12 V 70°C				
FT 5.5 V 85°C				
FY 5.5 V 70°C				
HV 2.5 V & 2.7 V 60°C & 70°C				

Downloaded from Arrow.com.

Radial

FA Series, 5.5 V – 11 V, 70ºC

Capacitance Range: 0.022 to 1 F • **Temperature Range:** −25°C to +70°C



FA	0H	104	Z	F
Series	Maximum Operating Voltage	Capacitance Code (F)	Capacitance Tolerance	Environmental
FA	0H = 5.5 VDC 1A = 11.0 VDC	First two digits represent s gnificant figures Third digit specifies number of zeros	Z = -20/+80%	F = Lead-free

FE Series, 5.5 V, 70ºC

Capacitance Range: 0.047 to 1 5 F • **Temperature Range:** −40°C to +70°C



FE	0H	104	Z	F
Series	Maximum Operating Voltage	Capacitance Code (F)	Capacitance Tolerance	Environmental
FE	0H = 5.5 VDC	First two digits ep ese t significant figures. Third digit specifies number of zeros.	Z = -20/+80%	F = Lead-free

FG Series, 3.5 V – 5.5 V, 70ºC & 85ºC

Capacitance Range: 0.01 to 4.7 F • **Temperature Range:** −25°C to +70°C (FG, FGH) and −40°C to +85°C (FGR)



FG	0H	104	Z	F
Series	Maximum Operating Voltage	Capacitance Code (F)	Capacitance Tolerance	Environmental
FG FGH FGR	0V = 3.5 VDC 0H = 5.5 VDC	First two digits represent significant figures. Third digit specifies number of zeros.	Z = -20/+80%	F = Lead-free

FM Series, 3.5 V – 6.5 V, 70ºC & 85ºC

Capacitance Range: 0.01 to 0.22 F • **Temperature Range:** −25°C to +70°C (all types except FMR) and −40°C to +85°C (FMR)



FM	0H	223	Z	F	TP	16
Series	Maximum Operating Voltage	Capacitance Code (F)	Capacitance Tolerance	Environmental	Tape Type	Height (excluding lead)
FM FME FML FMR FMC	0V = 3.5 VDC 0H = 5.5 VDC 0J = 6.5 VDC	First two digits represent significant figures. Third digit specifies number of zeros.	Z = -20/+80%	F = Lead-free	TP = AMMO -L1 = Transverse mounting Blank = Bulk	16 = 16 mm 18 = 18 mm Blank = Bulk

FR Series, 5.5 V, 85ºC

Capacitance Range: 0.022 to 1 F • **Temperature Range:** −40°C to +85°C



FR	0H	104	Z	F
Series	Maximum Operating Voltage	Capacitance Code (F)	Capacitance Tolerance	Environmental
FR	0H = 5.5 VDC	First two digits represent significant figures. Third digit specifies number of zeros.	Z = -20/+80%	F = Lead-free

Downloaded from Arrow.com.

Radial (cont.)

FS Series, 5.5 V – 12 V, 70ºC

Capacitance Range: 0.022 o 5 F • **Temperature Range:** −25°C to +70°C



FS	0H	104	Z	F
Series	Maximum Operating Voltage	Capacitance Code F)	Capacitance Tolerance	Environmental
FS	0H = 5.5 VDC 1A = 11.0 VDC 1B = 12.0 VDC	First two digits represent significant figures. Third digit specifies number of zeros.	Z = -20/+80%	F = Lead-free

FT Series, 5.5 V, 85ºC

Capacitance Range: 0.1 to 5.6 F • **Temperature Range:** −40°C to +85°C



FT	0H	104	Z	F
Series	Maximum Operating Voltage	Capacitance Code (F)	Capacitance Tolerance	Environmental
FT FTW	0H = 5.5 VDC	First two digits represent significant figures. Third digit specifies number of zeros.	Z = -20/+80%	F = Lead-free

FY Series, 5.5 V, 70ºC

Capacitance Range: 0.01 to 2 2 F • **Temperature Range:** −25°C to +70°C



FY	0H	104	Z	F
Series	Maximum Operating Voltage	Capacitance Code (F)	Capacitance Tolerance	Environmental
FYD FYH FYL	0H = 5.5 VDC	First two digits represent significant figures. Third digit specifies number of zeros.	Z = -20/+80%	F = Lead-free

HV Series, 2.5 V – 2.7 V, 60ºC & 70ºC

Capacitance Range: 1 to 200 F • **Temperature Range:** −25°C to +60°C and −25°C to +70°C



HVZ	0E	105	N	F	-LT
Series	Maximum Operating Voltage	Capacitance Code (F)	Capacitance Tolerance	Environmental	Terminal
HVZ	0E = 2.7 VDC (50 F type has 2.5 VDC)	First two digits represent significant figures. Third digit specifies number of zeros.	N = ±30%	F = Lead-free	-LT = Snap-in Blank = Standard

Surface Mount

FC Series, 3.5 V – 5.5 V, 70ºC

Capacitance Range: 0.1 to 1 F • **Temperature Range:** −25°C to +70°C



FC	0H	104	Z	F	TB	R	24	-SS
Series Surface Mount	Maximum Operating Voltage	Capacitance Code (F)	Capacitance Tolerance	Environmental	Tape Type	Orientation	Tape Width	C-Spec
FCS FC	0V = 3.5 VDC 0H = 5.5 VDC	First two digits represent significant figures. Third digit specifies number of zeros.	Z = -20/+80%	F = Lead-free	TB = Embossed	R = Positive electrode forward	24 = 24 mm 32 = 32 mm 44 = 44 mm	-SS = 3 digit serial number marked on top Blank = No serial number marking

Downloaded from Arrow.com.

Snap-In

S501 Series, 2.7 V, 65ºC

Capacitance Range: 100 to 350 F **Temperature Range:** −40°C to +65°C



S501	DC	107	V	2R7	A
Series	Size Code (D x L)	Capacitance Code (µF)	Capacitance Tolerance	Rated Voltage (VDC)	Termination Code
Supercapacitor, Snap-In Termination	DC = 22 x 45 LF = 35 x 60 L = 5 x 9 LR = 35 x 89	First two digits represent significant figures. Third digit specifies number of zeros.	V = -5/+10% W = -0/+20%	2R7 = 2.7	A = 2 pin, 10 mm lead spacing, 5.9 mm terminal length U = 4 pin standard snap-in style

Screw Terminal

S301 Series, 2.7 V, 65ºC

Capacitance Range: 1,200 to 3,000 F • **Temperature Range:** −40°C to +65°C



S301	RV	308	T	2R7	W
Series	Size Code (D x L)	Capacitance Code (µF)	Capacitance Tolerance	Rated Voltage (VDC)	Termination Code
Supercapacitor, Screw Termination	RP = 60.5 x 80.5 RS = 60.5 x 108.5 RV = 60.5 x 144	First two digits represent significant figures. Third digit specifies number of zeros.	R = -0%	2R7 = 2.7	2 threaded inserts per end, 20 mm lead spacing, M6

S301 Development Balancing Kit

Capacitance Range: 1,200 to 3,000 F • **Temperature Range:** −40°C to +105°C




S0K	MOD	0001
Series	Configuration	Model
Supercapacitor Development Balancing Kit	Module	Additional Hardware Required: Six (6) KEMET S301 Screw Terminal Supercapacitors, 60 mm cell diameter only

Bank Module

S02 Series, Modules with Cells in Extruded Metal Holder, 16 V – 48 V, 65ºC

Capacitance Range: 165 to 500 F • **Temperature Range:** −40°C to +65°C



S02	A	T	5006	R	016	A	U808
Series	Configuration Code Balancing	Configuration Code Capacitor Type	Capacitance Code (µF)	Capacitance Tolerance	Rated Voltage (VDC)	Termination Code	C-Spec
Supercapacitor, Bank Modules with cells in extruded metal holder	A = Analog with clamping	T =Array, 2 dimensions D = Array, 3 dimensions	First three digits represent significant figures. Fourth digit specifies number of zeros.	R = -0%	016 = 16 V 048 = 48 V	A = The first mechanical configuration of a particular part number B = Refers only to part number S02AT1656R048BU808	Blank = No monitor U808 = Digital Overvoltage and analog over temperature monitor

Downloaded from Arrow.com.

Tantalum Capacitors

TANTALUM SURFACE MOUNT CAPACITORS

Standard Tantalum	Polymer Tantalum KEMET Organic Capacitor (KO-CAP)	Polymer Aluminum Organic Capacitor (AO-CAP)	High Temperature	High Reliability Commercial Off-The-Shelf (COTS)	MIL-PRF CWR Series	Fused	Automotive Grade	Space Grade
T489 Low DC Leakage MnO_2	T520 105°C Rated	A700 125°C Rated	T498 150°C Rated MnO_2	T428 High Volumetric Efficiency Facedown MnO_2	T409 (CWR09) MIL-PRF-55365/4	T496 MnO_2	T489 Low DC Leakage MnO_2	T493 COTS MnO_2 (CWR11)
T490 High CV MnO_2	T521 High Voltage		T499 175°C Rated MnO_2	T493 MnO_2 (CWR11)	T419 (CWR19) MIL-PRF-55365/11		T491 MnO_2	T496 COTS Fail-Safe Fused MnO_2
T491 Industrial Grade MnO_2	T522 Reduced Leakage		T500 200°C Rated MnO_2	T495 Surge Robust MnO_2 DLA 95158	T429 (CWR29) MIL-PRF-55365/11		T494 Low ESR MnO_2	T497 COTS MnO_2 (CWR09/19/29)
T494 Industrial Grade Low ESR MnO_2	T525 125°C Rated			T497 MnO_2 (CWR09/19/29)	T492 (CWR11) MIL-PRF-55365/8		T495 Surge Robust MnO_2	T510 Multiple Anode MnO_2
T495 Surge Robust MnO_2	T527 Facedown Terminal			T496 Fused MnO_2			T498 150°C Rated MnO_2	
T510 Multiple Anode MnO_2	T528 Low ESL/Facedown Terminal			T513 Multiple Anode MnO_2			T499 175°C Rated MnO_2	
TSM Tantalum Stack MnO_2	T529 Small Case Size Substrate Terminal			T540 Single Anode Polymer			T510 Multiple Anode MnO_2	
	T530 High Capacitance 125°C Rated			T541 Multiple Anode Polymer			T591 High Performance Polymer	
	T545 High Energy			T543 Polymer				
	TSP Tantalum Stack Polymer							

TANTALUM THROUGH-HOLE CAPACITORS

Hermetically Sealed Axial		Radial Dipped	Molded Axial	Molded Radial
T110 MIL-PRF-39003 Polar & T212 (CSR13)	T225 High Temperature Solder (CSR09)	T35X Polar	T322/T323 (CX01/CX05) MIL-PRF-49137/1 & 5	T330 Precision Molded Polar
T111 MIL-PRF-39003 Non-Polar & T213 (CSR91)	T245 High Temperature Solder (CSR23)	T363 (CX02) & T369 (CX12) MIL-PRF-49137/2		T340 Precision Molded Polar
T140 MIL-PRF-39003 Polar & T242 (CSR23)	T252 MIL-PRF-39003 (CSR33)	T368 High Capacitance		T370 & T378 (CX06) MIL-PRF-49137/6
T210/T240/GR500 High Reliability	T255 High Temperature Solder (CSR33)	T396 & T398 3 Leaded		
T215 High Temperature Solder (CSR13)	T262 MIL-PRF-30093 (CSR21)			
T216 MIL-PRF-39003 (CSS13) & T256 (CSS33)	T550 Polymer 105°C Rated			
T222 MIL-PRF-39003 Polar Miniature (CSR09)	T551 Polymer 125°C Rated			

Downloaded from Arrow.com.

Standard Tantalum

T489 Series Low DC Leakage MnO_2


Capacitance Range: 0.1 to 470 µF • **Temperature Range:** −55°C to +125°C



T	489	B	156	M	16	A	T	E800
Capacitor Class	Se ies	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR
T = Tantalum	Low DC Leakage Series	A, B, C, D, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	006 = 6.3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% Matte Tin (Sn) Plated H = Standard Solder Coated (SnPb 5% Pb minimum) G = Gold Plated	Last three digits specify ESR in mΩ. (800 = 800 mΩ)

T490 Series Commercial Grade High CV MnO_2


Capacitance Range: 47 to 470 µF • **Temperature Range:** −55°C to +40°C



T	490	B	227	M	006	A	T	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Packaging (C-Spec)
T = Tantalum	Industrial	A, B, T	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	004 = 4 006 = 6.3 010 = 10	A = N/A	T = 100% Matte Tin (Sn) plated H = Standard solder coated (SnPb 5% Pb minimum) G = Gold plated (A, B on y)	Blank = 7" Reel 7280 = 13" Reel

T491 Series Industrial Grade MnO_2

Capacitance Range: 0.1 to 1,000 µF • **Temperature Range:** −55°C to +125°C



T	491	X	157	K	020	A	T	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Packaging (C-Spec)
T = Tantalum	Industrial	A, B, C, D, E, M, S, T, U, V, W, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	2R5 = 2 5 003 = 3 004 = 4 006 = 6.3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% Matte Tin (Sn) plated H = Standard solder coated (SnPb 5% Pb minimum) G = Gold plated (A, B, C, D, X only) N = Non-magnetic 100% Tin (Sn) M = Non-magnetic (SnPb)	Blank = 7" Reel 7280 = 13" Reel

Downloaded from Arrow.com.

Standard Tantalum (cont.)

T494 Series Industrial Grade Low ESR MnO_2

Capacitance Range: 0.1 to 1,000 µF • **Temperature Range:** −55°C to +125°C



T	494	T	336	M	004	A	T	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Packaging (C-Spec)
T = Tantalum	Industrial - Low ESR	A, B, C, D, E, S, T, U, V, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	2R5 = 2.5 003 = 3 004 = 4 006 = 6 3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% Matte Tin (Sn) plated H = Standard solder coated (SnPb 5% Pb minimum) G = Gold plated (A, B, C, D, X only) N = Non-magnetic 100% Tin (Sn) M = Non-magnetic (SnPb)	Blank = 7" Reel 7280 = 13" Reel

T495 Series Surge Robust MnO_2

Capacitance Range: 0.47 to 1,000 µF • **Temperature Range:** −55°C to +125°C



T	495	X	107	M	010	A	T	E045	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR	Packaging (C-Spec)
T = Tantalum	Surge Robust Low ESR	A, B, C, D, E, M, T, U, V, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	2R5 = 2.5 004 = 4 006 = 6 3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% Matte Tin (Sn) plated H = Standard solder coated (SnPb 5% Pb minimum) G = Gold plated (A, B, C, D, X only)	Last three digits specify ESR in mΩ. (45 = 45 mΩ)	Blank = 7" Reel 7280 = 13" Reel

T510 Series Multiple Anode MnO_2

Capacitance Range: 10 to 1,000 µF • **Temperature Range:** −55°C to +125°C



T	510	X	477	M	006	A	T	E800	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR	Packaging (C-Spec)
T = Tantalum	Multiple Anode Low ESR	E, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	004 = 4 006 = 6.3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A Z = N/A	T = 100% Matte Tin (Sn) Plated H = Standard Solder Coated (SnPb 5% Pb minimum) G = Gold Plated (A, B, C, D, X only)	Last three digits specify ESR in mΩ. (800 = 800 mΩ)	Blank = 7" Reel 7280 = 13" Reel

Downloaded from Arrow.com.

Standard Tantalum (cont.)

Tantalum Stack MnO_2 (TSM) Series

Capacitance Range: 9.4 to 2,000 µF • **Temperature Range:** −55°C to +125°C



T	SM	2D	447	K	10	A	H	61	20	D493
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Surge	ESR	C-Spec 2
T = Tantalum	Stacks MnO_2 Cathode	2C, 3C, 4C, 6C, 2D, 3D, 4D, 6D, 2X, 3X, 4X, 6X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	006 = 6 3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A B = 0.1%/1,000 hours C = 0.01%/1,000 hours	H = Standard Solder Coated (SnPb 5% Pb minimum) C = Hot Solder Dipped B = Gold Plated T = 100% Tin	61 = None 62 = 10 Cycles 25 C After Weibull 63 = 10 cycles, -55 C and 85 C After Weibull 64 = 10 cycles, -55 C and 85 C Before Weibull	10 = ESR-Standard 20 = ESR-Low 30 = ESR-Ultra-low	Designates discrete component series. D493 = T493

Polymer Tantalum KEMET Organic Capacitor (KO-CAP)

T520 Series Polymer Tantalum


Capacitance Range: 10 to 1,500 µF **Temperature Range:** −55°C to +105°C



T	520	V	157	M	006	A	T	E045	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR Code	Packaging (C-Spec)
T = Tantalum	520 = Polymer	A, B, C, D, H, L, M, Q, T, U, V, W, X, Y	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	2R5 = 2 5 003 = 3 004 = 4 006 = 6.3 008 = 8 010 = 10 011 = 11 12R = 12.5 016 = 16 020 = 20 025 = 25	A = N/A	T = 100% Matte Tin (Sn) plated H = Tin/Lead (SnPb) solder coated (5% Pb minimum) P* = Ni-Pd-Au plated N = Non-magnetic 100% Tin (Sn) M = Non-magnetic (SnPb)	E = ESR Last three digits specify ESR in mΩ. (045 = 45 mΩ)	Blank = 7" Reel 7280 = 13" Reel

T521 Series High Voltage Polymer Tantalum

Capacitance Range: 15 to 330 µF **Temperature Range:** −55°C to +105°C and −55°C to +125°C




T	521	V	226	M	025	A	T	E060	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR Code	Packaging (C-Spec)
T = Tantalum	521 = High Voltage Polymer	B, T, D, Q, V, W, X	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	016 = 16 020 = 20 025 = 25 035 = 35 050 = 50 063 = 63	A = N/A	T = 100% Matte Tin (Sn) plated H = Tin/Lead (SnPb) solder coated (5% Pb minimum) P = Ni/Pd/Au plated	E = ESR Last three digits specify ESR in mΩ. (060 = 60 mΩ)	Blank = 7" Reel 7280 = 13" Reel

Downloaded from Arrow.com.

Polymer Tantalum KEMET Organic Capacitor (KO-CAP) (cont.)

T522 Series Reduced Leakage Polymer Tantalum

Capacitance Range: 150 to 470 µF • **Temperature Range:** −55°C to +105°C



T	522	V	157	M	006	A	T	E025	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR Code	Packaging (C-Spec)
T = Tantalum	522 = Reduced Leakage Polymer	V, Y	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	006 = 6.3	A = N/A	T = 100% Matte Tin (Sn) plated H = Tin/Lead (SnPb) solder coated (5% Pb minimum)	E = ESR Last three digits specify ESR in mΩ. (025 = 25 mΩ)	Blank = 7" Reel 7280 = 13" Reel

T525 Series Polymer Tantalum 125ºC


Capacitance Range: 10 to 680 µF **Temperature Range:** −55°C to +125°C



T	525	D	337	M	006	A	T	E025	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR	Packaging (C-Spec)
T = Tantalum	525 = 125 C Rated Polymer	A, B, D, T, Y	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	2R5 = 2 5 003 = 3 004 = 4 006 = 6.3 008 = 8 010 = 10 016 = 16	A = N/A	T = 100% Matte Tin (Sn) Plated H = Tin/Lead (SnPb) Solder Coated (5% Pb minimum)	Last three digits specify ESR in mΩ. (025 = 25 mΩ)	Blank = 7" Reel 7280 = 13" Reel

T527 Series Facedown Terminal Polymer Tantalum


Capacitance Range: 22 to 100 µF • **Temperature Range:** −55°C to +105°C



T	527	I	476	M	006	A	T	E200
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR Code
T = Tantalum	527 = Facedown Terminal Polymer	I = 3216	First two digits represent significant figures. Third digit specifies number of zeros. ex. 476 = 47 µF	M = ±20%	004 = 4 006 = 6.3 010 = 10	A = N/A	T = 100% Tin (Sn)	E = ESR Last three digits specify ESR in mΩ (200 = 200 mΩ)

T528 Series Low ESL Facedown Terminal Polymer Tantalum

Capacitance Range: 33 to 470 µF **Temperature Range:** −55°C to +105°C




T	528	Z	337	M	2R5	A	T	E009	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR Code	Packaging (C-Spec)
T = Tantalum	528 = Low ESL Facedown Terminal Polymer	B = 3528-21 W = 7343-15 Z = 7343-17	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	002 = 2 2R5 = 2 5 004 = 4 006 = 6.3	A = N/A	T = 100% Matte Tin (Sn) plated P = Ni-Pd-Au plated	E = ESR Last three digits specify ESR in mΩ (009 = 9 mΩ)	Blank = 7" Reel 7280 = 13" Reel

Downloaded from Arrow.com.

Polymer Tantalum KEMET Organic Capacitor (KO-CAP) (cont.)

T529 Series Small Case Size Substrate Terminal Polymer Tantalum

Capacitance Range: 22 to 150 µF **Temperature Range:** −55°C to +105°C



T	529	P	476	M	006	A	A	E200
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR Code
T = Tantalum	529 = Substrate Terminal Polymer	P = 2012-10 I = 3216-10	First two digits represent significant figures. Third digit specifies number of zeros. ex. 476 = 47 µF	M = ±20%	006 = 6.3 010 = 10	A = N/A	A = Ni - Au	E = ESR Last three digits specify ESR in mΩ (200 200 mΩ)

T530 Series High Capacitance Polymer Tantalum 125ºC


Capacitance Range: 150 to 1,500 µF • **Temperature Range:** −55°C to +125°C



T	530	X	337	M	010	A	T	E005	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR Code	Packaging (C-Spec)
T = Tantalum	530 = High Capacitance 125 C Rated Polymer	D, X, Y	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	2R5 = 2.5 003 = 3 004 = 4 006 = 6.3 010 = 10 016 = 16	A = N/A	T = 100% Matte Tin (Sn) plated* H = Standard solder Coated (SnPb 5% Pb minimum)	E = ESR Last three digits specify ESR in mΩ (005 = 5 mΩ)	Blank = 7" Reel 7280 = 13" Reel

T545 Series High Energy Polymer Tantalum

Capacitance Range: 33 to 1,500 µF **Temperature Range:** −55°C to +125°C



T	545	H	108	M	006	A	T	E055	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR	Packaging (C-Spec)
T = Tantalum	High Energy Polymer Tantalum	H, V, W, X, Y	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20% K = ±10 %	006 = 6.3 008 = 8 010 = 10 016 = 16 020 = 20	A = N/A	T = 100% Tin (Sn)	ESR in mΩ	Blank = 7" Reel 7280 = 13" Reel

Tantalum Stack Polymer (TSP) Series

Capacitance Range: 66 to 4,080 µF **Temperature Range:** −55°C to +125°C




T	SP	2D	207	M	010	A	H	65	20	D540
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Surge	ESR	C-Spec 2
T = Tantalum	Stacks Polymer Cathode	2B, 3B, 4B, 6B, 2D, 3D, 4D, 6D	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	003 = 3 004 = 4 006 = 6 3 010 = 10 016 = 16	A = N/A	H = Standard Solder Coated (SnPb 5% Pb minimum)	65 = No Surge 66 = 10 cycles at 25 C 67 = 10 cycles at -55 C and 85 C	10 = ESR - Standard 20 = ESR-Low	Designates discrete component series. D540 = T540

Downloaded from Arrow.com.

Polymer Aluminum Organic Capacitor (AO-CAP)

A700 Series Polymer Aluminum

Capacitance Range: 6.8 to 560 µF • **Temperature Range:** −55°C to +125°C




A	700	V	476	M	006	A	T	E018	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR Code	Packaging (C-Spec)
A = Aluminum	700 = Aluminum Polymer	D, V, X	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	002 = 2 2R5 = 2.5 004 = 4 006 = 6.3 008 = 8 010 = 10 12R = 12.5 016 = 16	A = N/A	T = 100% Matte Tin (Sn) plated	E = ESR Last three digits specify ESR in mΩ (018 = 18 mΩ)	Blank = 7" Reel 7280 = 13" Reel

High Temperature

T498 Series Automotive Grade MnO_2 150ºC


Capacitance Range: 0.1 to 220 µF • **Temperature Range:** −55°C to +150°C



T	498	X	227	M	010	A	T	E500	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR	Packaging (C-Spec)
T = Tantalum	High Temperature 150ºC	A, B, C, D, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	004 = 4 006 = 6.3 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% Matte Tin (Sn) plated* G = Gold plated H = Standard solder coated (SnPb 5% Pb minimum)	E = ESR Last three digits specify ESR in mΩ (500 = 500 mΩ)	Blank = 7" Reel 7280 = 13" Reel

T499 Series Automotive Grade MnO_2 175ºC


Capacitance Range: 0.15 to 220 µF • **Temperature Range:** −55°C to +175°C



T	499	X	227	M	010	A	T	E500	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR	Packaging (C-Spec)
T = Tantalum	High Temperature 175ºC	A, B, C, D, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	006 = 6 3 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% Matte Tin (Sn) plated G = Gold plated H = Standard solder coated (SnPb 5% Pb minimum)	E = ESR Last three digits specify ESR in mΩ (500 = 500 mΩ)	Blank = 7" Reel 7280 = 13" Reel

T500 Series MnO_2 200ºC

Capacitance Range: 10 to 220 µF **Temperature Range:** −55°C to +200°C



T	500	X	227	M	010	A	G	61	10
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Performance	ESR
T = Tantalum	High Temperature 200 C	X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	010 = 10 016 = 16 035 = 35	A = N/A B= 0.1%/1,000 hours	G = Gold plated	61 = Surge None 62 = Surge at 25 C after Weibull 63 = Surge -55 C and +85 C after Weibull	10 = Standard ESR

Downloaded from Arrow.com.

High Reliability Commercial Off-The-Shelf (COTS)

T428 Series High Volumetric Efficiency Facedown COTS MnO_2

Capacitance Range: 15 to 470 µF **Temperature Range:** −55°C to +125°C



	428	P	227	K	006	A	H	61	10
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Surge	ESR
T = Tantalum	High Volumetric Efficiency Facedown Hi-Rel MnO_2 COTS	P	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	004 = 4 006 = 6 3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A B = 0.1%/1,000 hours	H = Standard solder coated (SnPb 5% Pb) T = 100% tin (Sn)	61 = None 62 = 10 cycles, 25 C 63 = 10 cycles, -55 C and 85 C	10 = Standard 20 = Low 30 = Ultra-low

T493 Series COTS MnO_2 (CWR11 Style)

Capacitance Range: 0.1 µF to 470 µF • **Temperature Range:** −55°C to +125°C



T	493	D	227	K	006	C	H	61	20
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Surge	ESR
T = Tantalum	Military COTS	A, B, C, D, E, X	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	004 = 4 006 = 6 3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50 063 = 63	A = N/A B = 0.1%/1,000 hours C = 0.01%/1,000 hours	C = Hot solder dipped H = Standard solder coated (SnPb 5% Pb minimum) B = Gold plated K = Solder fused T = 100% Tin N = Non-magnetic 100% Tin (Sn) M = Non-magnetic (SnPb)	61 = None 62 = 10 Cycles after Weibull, 25°C 63 = 10 cycles after Weibull, -55°C and 85°C after Weibull 64 = 10 cycles before Weibull,-55 and +85 C	10 = ESR – Standard 20 = ESR – Low 30 = ESR – Ultra low

DLA Drawing 07016

07016-	001	K	B	H	A
Drawing Number	Dash Number	Capacitance Tolerance	Reliability Grade	Termination Finish	Surge
	See Part Number Table	J = ±5% K = ±10% M = ±20%	B = 0.1%/1,000 hours C = 0.01%/1,000 hours	C = Hot solder dipped H = Standard solder coated (SnPb 5% Pb minimum) B = Gold plated	A = + 25°C after Weibull B = -55°C and +85°C after Weibull C = -55°C and + 85°C before Weibull Z or no option= No test required

F-Tech & Simulated Breakdown Screening (SBDS)


T	493	D	226	K	020	C	H	61	20
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Surge	Screening/ESR
T = Tantalum	Military COTS	A, B, C, D, E, X	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	020 = 20 025 = 25 035 = 35 050 = 50 063 = 63	A = N/A B = 0.1%/1,000 hours C = 0.01%/1,000 hours	C = Hot solder dipped H = Standard solder coated (SnPb 5% Pb minimum) B = Gold plated K = Solder fused K = Solder fused T = 100% Tin N = Non-magnetic 100% Tin (Sn) M = Non-magnetic (SnPb)	61 = None 62 = 10 Cycles after Weibull, 25°C 63 = 10 cycles after Weibull, -55°C and 85°C after Weibull 64 = 10 cycles before Weibull,-55 and +85 C	11 = F-Tech + SBDS * 12 = SBDS 13 = F-Tech * 21 = Low ESR + 11 22= Low ESR + 12 23 = Low ESR + 13 31= Ultra Low ESR + 11 32 = Ultra Low ESR + 12 33 = Ultra Low ESR + 13

Downloaded from Arrow.com.

High Reliability Commercial Off-The-Shelf (COTS) (cont)

T495 Series Surge Robust COTS MnO_2

Capacitance Range: 4.7 to 220 µF • **Temperature Range:** −55°C to +125°C



T	495	X	107	M	010	A	H	4095	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Customer Specification	Packaging (C-Spec)
T = Tantalum	Surge Robust Low ESR	C, D, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	006 = 6.3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	H = Standard Solder Coated (SnPb 5% Pb minimum) B = Gold Plated	Tested to meet the Established Reliability	Blank = 7" Reel 7280 = 13" Reel

DLA Drawing 95158

95158-	07	M	H
Drawing Number	Dash Number	Capacitance Tolerance	Termination Finish
Capacitor, Fixed, Tantalum Chip, Low ESR	See Part Number List	K = ±10% M = ±20%	H = Solder Plated B= Gold Plated

T496 Series Fused COTS MnO_2

Capacitance Range: 0.15 to 470 µF • **Temperature Range:** −55°C to +125°C



T	496	X	227	M	010	B	T	61	10	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Performance	ESR	Packaging (C-Spec)
T Tantalum	Fail Safe	B, C, D, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	004 = 4 006 = 6.3 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35 050 = 50	B = 0.1%/1,000 hours C = 0.01%/1,000 hours D = 0.001%/ 1,000 hours A = Non-Weibull Graded	T = 100% Matte Tin (Sn) plated H = Standard solder coated (SnPb 5% Pb minimum) C = Hot solder dipped K = Solder Fused	61 = Surge None 62 = Surge at 25 C after Weibull 63 = Surge 55 C and +85 C after Weibull 64 = Surge -55 C and +85 C before Weibull	10 Standard 20 = Low	Blank = 7" Reel 7280 = 13" Reel

DLA Drawing 04053

04053-	001	B
Drawing Number	Dash Number	Reliability Grade
	See Part Number List	B = 0.1%/1,000 hours C = 0.01%/1,000 hours D = 0.001%/1,000 hours Z = Non-Weibull Graded

Downloaded from Arrow.com.

High Reliability Commercial Off-The-Shelf (COTS) (cont.)

T497 Series COTS MnO_2 (CWR09/19/29 Style)

Capacitance Range: 0.1 to 150 µF • **Temperature Range:** −55°C to +125°C



T	497	G	226	K	020	A	H	61	10
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Surge	X-ray
T = Tantalum	High Grade COTS	A, B, C, D, E, F, G, H, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	004 = 4 006 = 6.3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A B = 0.1%/1,000 hours C = 0.01%/1,000 hours	T = 100% Matte Tin (Sn) Plated H = Standard Solder Coated (SnPb 5% Pb minimum) B = Gold Plated	61 = Standard (in-process) 62 = 10 Cycles After Weibull, 25 C 63 = 10 Cycles After Weibull, -55 and 85 C 64 = 10 Cycles Before Weibull, -55 and 85 C	10 = None 15 = 100%

F-Tech & Simulated Breakdown Screening (SBDS)

T	497	H	226	K	020	A	H	61	10
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Surge	Design/Screening
T = Tantalum	High Grade COTS	H	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	020 = 20 025 = 25 035 = 35 050 = 50	A = N/A B=0.1%/1,000 hours C=.01%/1,000 hours	T = 100% Matte Tin (Sn) Plated H = Standard Solder Coated (SnPb 5% Pb minimum) B = Gold Plated	61 = Standard (in-process) 62 = 10 Cycles After Weibull, 25 C 63 = 10 Cycles After Weibull, -55 and 85 C 64 = 10 Cycles Before Weibull, -55 and 85 C	10 = Standard 11 = F-Tech & SBDS * 12 = SBDS 13 = F-Tech * 15 = 100% X-ray 16 = F-Tech & SBDS & 100% X-ray * 17 = SBDS & 100% X-ray 18 = F-Tech & 100% X-ray *

T513 Series COTS Multiple Anode MnO_2

Capacitance Range: 15 to 1,000 µF • **Temperature Range:** −55°C to +125°C




T	513	X	108	K	004	B	H	61	10
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Surge	ESR
T = Tantalum	Multiple Anode COTS	D, E, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	004 = 4 006 = 6.3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35	A = N/A B = 0.1%/1,000 hours	C = Hot Solder Dipped H = Standard Solder Coated (SnPb 5% Pb minimum) B = Gold Plated K = Solder Fused T = 100% Tin	61 = None 62 = 10 cycles, 25 C after Weibull 63 = 10 cycles, -55 C & 85 C after Weibull 64 = 10 cycles, -55 C & 85 C before Weibull	10 = Standard ESR 20 = Low ESR 30 = Ultra Low ESR

Downloaded from Arrow.com.

High Reliability Commercial Off-The-Shelf (COTS) (cont.)

T540 Series COTS Single Anode Polymer Tantalum

Capacitance Range: 4.7 to 680 µF **Temperature Range:** −55°C to +125°C



T	540	D	107	M	10	A	H	65	10	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Surge Option	ESR	Packaging (C-Spec)
T = Tantalum	540 = Polymer COTS	B, C, D	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	2R5 = 2.5 003 = 3 004 = 4 006 = 6 3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50 063 = 63	A = N/A B** = 0.1%/1,000 hours C** = 0.01%/1,000 hours D** = 0.001%/1,000 hours	H = Standard Solder Coated (SnPb 5% Pb minimum)	65 = 4 cycles at 25 C * 66 = 10 cycles at 25 C * 67 = 10 cycles at -55 C and 85 C *	10 = ESR - Standard 20 = ESR - Low	Blank = 7" Reel 7280 = 13" Reel

DLA Drawing 04051

04051-	001	A
Drawing Number	Dash Number	Surge Current Option
04051	See Part Number List	Blank = 4 cycles +25 C ±5 C Before Voltage Aging A = 10 cycles +25 C ±5 C After Voltage Aging B = 10 cycl s 55 C ±5 C, +0 C ±5 C, and +85 C ±5 C After Voltage Aging

T541 Series COTS Multiple Anode Polymer Tantalum

Capacitance Range: 10 to 1,500 µF **Temperature Range:** −55°C to +125°C



T	541	D	157	M	10	A	H	65	10	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Fail re Rate/ Design	Terminat on Finish	Surge Option	ESR	Packaging (C-Spec)
T = Tantalum	541 = Polymer COTS Multiple Anode	D, X, Y	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	2R5 = 2 5 003 = 3 004 = 4 006 = 6.3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50 063 = 63	A = N/A B** = 0.1%/1,000 hours C** = 0 01%/1,000 hours D** = 0.001%/1,000 hours	H = Standard Solder Coated (SnPb 5% Pb minimum)	65 = 4 cycles at 25 C * 66 = 10 cycles at 25 C * 67 = 10 cycles at -55 C and 85 C	10 = ESR - Standard 20 = ESR - Low 30 = ESR - Ultra Low ESR	Blank = 7" Reel 7280 = 13" Reel

DLA Drawing 04052

04052-	001	A
Drawing Number	Dash Number	Surge Current Option
04052	See Part Number List	Blank = 4 cycles +25 C ±5 C Before Voltage Aging A = 10 cycles +25 C ±5 C After Voltage Aging B = 10 cycles -55 C ±5 C, +0 C ±5 C, and +85 C ±5 C After Voltage Aging

Downloaded from Arrow.com.

High Reliability Commercial Off-The-Shelf (COTS) (cont.)

T543 Series COTS Polymer Tantalum

Capacitance Range: 4.7 to 1,500 µF • **Temperature Range:** −55°C to +105°C




T	543	D	156	K	035	A	H	E	100	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Surge	ESR	Packaging (C-Spec)
T = Tantalum	Polymer Tantalum COTS	A, B, C, D, H, L, M, T, U, V, W, X, Y	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	2R5 = 2.5 003 = 3 004 = 4 006 = 6 3 010 = 10 12R = 12.5 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50 063 =63	A = N/A	H = Standard Solder Coated (SnPb 5% Pb minimum) T = 100% Tin (Sn)	E = None S = 10 cycles 25 C W = 10 cycles -55 C and 85 C	ESR in mΩ	Blank = 7" Reel 7280 = 13" Reel

MIL–PRF CWR Style

T409 Series MIL–PRF–55365/4 (CWR09 Style)

Capacitance Range: 0.1 to 100 µF • **Temperature Range:** −55°C to +125°C



T	409	A	225	K	004	A	H	4252	7280
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Design	Termination Finish	Surge	Packaging (C-Spec)
T = Tantalum	CWR 09 Established Reliability	A, B, C, D, E, F, G, H	First two digits represent significant figures Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	004 = 4 006 = 6.3 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35 050 = 50	Weibull A = non-ER B = (0.1%/1 000 hours) C = (0 01%/1,000 hours) D = (0 001%/1,000 hours) T = (0.01%/1,000 hours) Exponential M = (1 0%/1,000 hours) P = (0 1%/1,000 hours) R = (0.01%/1,000 hours) S =(0.001%/1,000 hours)	C = Hot Solder Dipped H = Standard Solder Coated (SnPb 5% Pb minimum) B = Gold Plated K = Solder Fused	4250= 25°C after Weibull 4251 = -55°C and 85°C after Weibull 4252 = -55°C and 85°C before Weibull TLVL = Weibull Grade Level "T"	Blank = 7" Reel 7280 = 13" Reel 7610 = Bag 7005 = Moisture bags

MIL–PRF–55365/4


CWR09	J	H	105	K	C	A
Capacitor Style	Rated Voltage (VDC)	Termination Finish	Capacitance Code (pF)	Capacitance Tolerance	Reliability Level	Surge Current Option
Per M L–PRF–55365/4	C = 4 D = 6 F = 10 H = 15 J = 20 K = 25 M = 35 N = 50	B = Gold Plated C = Hot solder dipped H = Solder Plated K = Solder fused	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	Weibull A = non-ER B = (0.1%/1,000 hours) C = (0.01%/1,000 hours) D =(0.001%/1,000 hours) T= T Level* (0.01%/1,000 hours) Exponential M = (1.0%/1,000 hours) P = (0.1%/1,000 hours) R = (0.01%/1,000 hours) S =(0.001%/1,000 hours)	A = +25 C after Weibull B = -55 C +85 C after Weibull C = -55 C +85 C before Weibull Blank = No Surge

Downloaded from Arrow.com.

MIL–PRF CWR Style (cont.)

T419 Series MIL–PRF–55365/11 (CWR19 Style)

Capacitance Range: 0.33 to 330 µF • **Temperature Range:** −55°C to +125°C



T	419	A	225	K	004	A	H	4251	7280
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Design	Termination Finish	Surge	Packaging (C-Spec)
T = Tantalum	CWR19 Established Reliability	A, B, C, D, E, F, G, H, X	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	004 = 4 006 = 6 3 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35	Weibull A = non-ER B = (0.1%/1,000 hours) C = (0 01%/1,000 hours) D = (0.001%/1,000 hours) T = (0.01%/1,000 hours) Exponential M = (1.0%/1,000 hours) P = (0.1%/1,000 hours) R = (0.01%/1,000 hours) S =(0.001%/1,000 hours)	C = Hot Solder Dipped H = Standard Solder Coated (SnPb 5% Pb minimum) B = Gold Plated K = Solder Fused	Blank = No Surge 4250= 25ºC after Weibull 4251 = -55ºC and 85ºC after Weibull 4252 = -55ºC and 85ºC before Weibull TLVL = Weibull Grade Level "T"	Blank = 7" Reel 7280 = 13" Reel 7610 = Bag 7005 = Moisture bags

MIL–PRF–55365/11


CWR19	K	H	225	K	C	D	A
Capacitor Style	Rated Voltage (VDC)	Termination Finish	Capacitance Code (pF)	Capacitance Tolerance	Reliability Level	Case Code	Surge Current Option
Per MIL–PRF–55365/11	C = 4 D = 6 F = 10 H = 15 J = 20 K = 25 M = 35	B = Gold Plated C = Hot solder dipped H = Solder Plated K = Solder fused	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	Weibull A = non-ER B = (0.1%/1,000 hours) C = (0.01%/1,000 hours) D =(0.001%/1,000 hours) T= T Level* (0.01%/1,000 hours) Exponential M = (1.0%/1,000 hours) P = (0.1%/1,000 hours) R = (0.01%/1,000 hours) S =(0.001%/1,000 hours)	A, B, C, D, E, F, G, H, X	A = +25 C after Weibull B = -55 C +85 C after Weibull C = -55 C +85 C before Weibull Z = None

Downloaded from Arrow.com.

MIL–PRF CWR Style (cont.)

T429 Series MIL–PRF–55365/11 (CWR29 Style)

Capacitance Range: 0.1 to 330 µF • **Temperature Range:** −55°C to +125°C



T	429	A	225	K	004	A	H	4251	7280
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Fail e Rate/Design	Terminat on F nish	Su ge	Packaging (C-Spec)
T = Tantalum	CWR29 Established Reliability	A, B, C, D, E F, G, H, X	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	004 = 4 006 = 6.3 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35 050 = 50	Weibull A = non-ER B = (0 1%/1,000 hours) C = (0 01%/1,000 hours) D =(0 001%/1,000 hours) T = (0.01%/1,000 hours) Exponential M = (1.0%/1,000 hours) P = (0 1%/1,000 hours) R = (0.01%/1,000 hours) S =(0.001%/1,000 hours)	C = Hot Solder Dipped H = Standard Solder Coated (SnPb 5% Pb minimum) B = Gold Plated K = Solder Fused	Blank = No surge 4250= 25ºC after Weibull 4251 = -55ºC and 85ºC after Weibull 4252 = -55ºC and 85ºC before Weibull TLVL= Weibull Grade Level "T"	Blank = 7" Reel 7280 = 13" Reel 7610 = Bag 7005 = Moisture bags

MIL–PRF–55365/11


CWR29	K	H	225	K	C	D	A
Capacitor Style	Rated Voltage (VDC)	Termination Finish	Capacitance Code (pF)	Capacitance Tolerance	Reliability Level	Case Code	Surge Current Option
Per MIL–PRF–55365/11	C = 4 D = 6 F = 10 H = 15 J = 20 K = 25 M = 35 N = 50	B = Gold Plated C = Hot solder dipped H = Solder Plated K = Solder fused	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	Weibull A = non-ER B = (0.1%/1,000 hours) C = (0.01%/1,000 hours) D =(0.001%/1,000 hours) T = T Level* (0.01%/1,000 hours) Exponential M = (1.0%/1,000 hours) P = (0.1%/1,000 hours) R = (0.01%/1,000 hours) S =(0.001%/1,000 hours)	A, B, C, D, E, F, G, H, X	A = +25 C after Weibull B = -55 C +85 C after Weibull C = -55 C +85 C before Weibull Z = None

Downloaded from Arrow.com.

MIL–PRF CWR Style (cont)

T492 Series MIL–PRF–55365/8 (CWR11 Style)

Capacitance Range: 0.1 to 100 µF • **Temperature Range:** −55°C to +125°C



T	492	D	156	K	020	A	C	4251
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Design	Termination Finish	Surge (C-Spec)
T = Tantalum	CWR11 Established Reliability	A, B, C, D	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	004 = 4 006 = 6.3 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35 050 = 50	Weibull A = non-ER B = (0.1%/1,000 hours) C = (0.01%/1,000 hours) D = (0.001%/1,000 hours) T = (0.01%/1,000 hours) Exponential M = (1.0%/1,000 hours) P = (0.1%/1,000 hours) R = (0.01%/1,000 hours) S =(0.001%/1,000 hours	C = Hot Solder Dipped H = Standard Solder Coated (SnPb 5% Pb minimum) B = Gold Plated K = Solder Fused	4250= 25°C after Weibull 4251 = -55°C and 85°C after Weibull 4252 = -55°C and 85°C before Weibull TLVL= Weibull Grade Level "T"

MIL–PRF–55365/8

CWR11	M	H	105	K	B	A
Capacitor Style	Rated Voltage (VDC)	Termination Finish	Capacitance Code (pF)	Capacitance Tolerance	Reliability Level	Surge Current Option
Per MIL–PRF–55365/8	C = 4 D = 6 F = 10 H = 15 J = 20 K = 25 M = 35 N = 50	B = Gold Plated C = Hot solder dipped H = Solder Plated K = Solder fused	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	Weibull A = non-ER B = (0.1%/1,000 hours) C = (0.01%/1,000 hours) D =(0.001%/1,000 hours) T= T Level* (0.01%/1,000 hours) Exponential M = (1.0%/1,000 hours) P = (0.1%/1,000 hours) R = (0.01%/1,000 hours) S =(0.001%/1,000 hours	A = +25 C after Weibull B = -55 C +85 C after Weibull C = -55 C +85 C before Weibull Blank = None

Fused

T496 Series Fused MnO_2

Capacitance Range: 0.15 to 477 µF • **Temperature Range:** −55°C to +125°C



T	496	X	227	M	010	A	T	E500	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR	Packaging (C-Spec)
T = Tantalum	Fail Safe	B, C, D, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	004 = 4 006 = 6.3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% Matte Tin (Sn) plated H = Standard solder coated (SnPb 5% Pb minimum)	E = ESR Last three digits specify ESR in mΩ (500 = 500 mΩ)	Blank = 7" Reel 7280 = 13" Reel

Downloaded from Arrow.com.

Automotive Grade

T489 Series Automotive Grade Low DC Leakage MnO_2


Capacitance Range: 0.10 to 470 µF • **Temperature Range:** −55°C to +125°C



T	489	B	156	M	16	A	T	A800	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	C-Spec	Packaging (C-Spec)
T = Tantalum	Low DC Leakage Series	A, B, C, D, X	First two digits represent significant figures. Third digit specifies number of zeros	K = ±10% M = ±20%	006 = 6.3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% matte tin (Sn) plated H = Standard solder coated (SnPb 5% Pb minimum) G = Gold plated	A = Automotive grade 800 = ESR value (800 = 800 mΩ)	Blank = 7" Reel 7280 = 13" Reel

T491 Series Automotive/Industrial Grade MnO_2


Capacitance Range: 0.1 to 470 µF • **Temperature Range:** −55°C to +125°C



T	491	X	157	K	020	A	T	AUTO	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	C-Spec 1	Packaging (C-Spec)
T = Tantalum	Industrial	A, B, C, D, E, S, T, U, V, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	2R5 = 2 5 003 = 3 004 = 4 006 = 6.3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% Matte Tin (Sn) plated* H = Standard solder coated (SnPb 5% Pb minimum) G = Gold plated (A, B, C, D, X only) N = Non-magnetic 100% Tin (Sn) M = Non-magnetic (SnPb)	AUTO = Automotive Grade (AUTO = AEC–Q200 Certification)	Blank = 7" Reel 7280 = 13" Reel

T494 Series Automotive/Industrial Grade MnO_2

Capacitance Range: 0.1 to 1,000 µF • **Temperature Range:** −55°C to +125°C



T	494	T	336	M	004	A	T	AUTO	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	C-Spec 1	Packaging (C-Spec)
T = Tantalum	Industrial - Low ESR	A, B, C, D, E, S, T, U, V, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	2R5 = 2.5 003 = 3 004 = 4 006 = 6 3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% Matte Tin (Sn) plated H = Standard solder coated (SnPb 5% Pb minimum) G = Gold plated (A, B, C, D, X only)	AUTO = Automotive Grade (AUTO = AEC–Q200 Certification)	Blank = 7" Reel 7280 = 13" Reel

Downloaded from Arrow.com.

Automotive Grade (cont.)

T495 Series Automotive Grade Surge Robust MnO_2


Capacitance Range: 0.1 to 1,000 µF • **Temperature Range:** −55°C to +125°C



T	495	X	107	M	010	A	T	A080	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR	Packaging (C-Spec)
T = Tantalum	Surge Robust Low ESR	A, B, C, D, E, T, V, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	2R5 = 2.5 004 = 4 006 = 6 3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% Matte Tin (Sn) plated H = Standard solder coated (SnPb 5% Pb minimum) G = Gold plated (A, B, C, D, X only) N = Non-magnetic 100% Tin (Sn) M = Non-magnetic (SnPb)	A = AUTO grade product 080 = Maximum ESR in mΩ at room temperature (80 mΩ)	Blank = 7" Reel 7280 = 13" Reel

T498 Series Automotive Grade MnO_2 150ºC


Capacitance Range: 0.1 to 220 µF • **Temperature Range:** −55°C to +150°C



T	498	X	227	M	010	A	T	E500	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR	Packaging (C-Spec)
T = Tantalum	High Temperature 150°C	A, B, C, D, X	First two digits represent significant figures. Third digit specifies number of zeros	K = ±10% M = ±20%	004 = 4 006 = 6.3 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% Matte Tin (Sn) plated* G = Gold plated H = Standard solder coated (SnPb 5% Pb minimum)	E = ESR Last three digits specify ESR in mΩ (500 = 500 mΩ)	Blank = 7" Reel 7280 = 13" Reel

T499 Series Automotive Grade MnO_2 175ºC

Capacitance Range: 0.15 to 220 µF • **Temperature Range:** −55°C to +175°C



T	499	X	227	M	010	A	T	E500	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR	Packaging (C-Spec)
T = Tantalum	High Temperature 175°C	A, B, C, D, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	006 = 6 3 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% Matte Tin (Sn) plated G = Gold plated H = Standard solder coated (SnPb 5% Pb minimum)	E = ESR Last three digits specify ESR in mΩ (500 = 500 mΩ)	Blank = 7" Reel 7280 = 13" Reel

T510 Series Automotive Grade Multiple Anode MnO_2

Capacitance Range: 10 to 1,000 µF • **Temperature Range:** −55°C to +125°C



T	510	X	477	M	006	A	T	A030	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR	Packaging (C-Spec)
T = Tantalum	Multiple Anode Low ESR	E, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	004 = 4 006 = 6.3 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% Matte Tin (Sn) Plated* H = Standard Solder Coated (SnPb 5% Pb minimum) G = Gold Plated (A, B, C, D, X only)	A = AUTO grade product 030 = Maximum ESR in mΩ at room temperature (30mΩ)	Blank = 7" Reel 7280 = 13" Reel

Downloaded from Arrow.com.

Automotive Grade (cont.)

T59x High Humidity/High Temperature Automotive Grade Polymer Electrolytic

Capacitance Range: 10 to 330 µF • **Temperat re Range:** −55°C to +105°C & −55°C to +125°C



T	598	D	107	M	010	A	T	E025
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR
T = Tantalum	591 = High Performance 598 = High Humidity/High Temperature	B, D, V	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	2R5 = 2 5 006 = 6.3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A	T = 100% Tin (Sn)	Maximum ESR in mΩ, 025 = 25 mΩ

Space Grade

T493 Series Space Grade (COTS) MnO_2 (CWR11 Style)


Capacitance Range: 0.1 to 330 µF • **Temperature Range:** −55°C to +125°C



T	493	D	227	K	006	C	H	61	2	A
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Voltage	Failure Rate/ Design	Lead Material	Surge	ESR	Testing
T = Tantalum	CRW11 Style Space Grade	A, B, C, D, X	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	004 = 4 V 006 = 6 3 V 010 = 10 V 016 = 16 V 020 = 20 V 025 = 25 V 035 = 35 V 050 = 50 V	C = .01%/1,000 hours	C = Hot Solder Dipped H = Standard Solder Coated (SnPb 5% Pb minimum) B = Gold Plated K = Solder Fused T = 100% Tin	61 = None 62 = 10 Cycles after Weibull,25 C 63 = 10 Cycles, after Weibull,-55 C and 85 C 64 = 10 Cycles before Weibull, -55 C and 85 C 65 = 10 Cycles Before and After Weibull, -55 C and 85 C	1 = ESR - Standard 2 = ESR - Low	A = Option A B = Option B C = Option C

T496 Series Space Grade Fail-Safe Fused MnO_2

Capacitance Range: 0.15 to 470 µF • **Temperature Range:** −55°C to +125°C




T	496	X	227	M	010	C	T	61	2	A
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Voltage	Failure Rate/ Design	Lead Material	Surge	ESR	Testing
T = Tantalum	Fail Safe - Space Grade	B, C, D, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	004 = 4 V 006 = 6.3 V 010 = 10 V 016 = 16 V 020 = 20 V 025 = 25 V 035 = 35 V 050 = 50 V	C = 0.01%/1,000 hours	C = Hot Solder Dipped T = 100% Matte Tin (Sn) Plated H = Standard Solder Coated (SnPb 5% Pb minimum)	61 = None 62 = 10 Cycles after Weibull,25 C 63 = 10 Cycles, after Weibull,-55 C and 85 C 64 = 10 Cycles before Weibull, -55 C and 85 C 65 = 10 Cycles Before and After Weibull, -55 C and 85 C	1 = ESR - Standard 2 = ESR - Low	A = Option A B = Option B C = Option C

Downloaded from Arrow.com.

Space Grade (cont.)

T497 Series Space Grade (COTS) MnO_2 (CWR09/19/29 Style)

Capacitance Range: 0.1 to 150 µF **Temperature Range:** −55°C to +125°C



T	497	G	226	K	020	C	H	61	2	A
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Voltage	Failure Rate/ Design	Lead Material	Surge	ESR	Testing
T = Tantalum	High Grade - Space Grade	A, B, C, D, E, F, G, H, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	004 = 4 V 006 = 6 3 V 010 = 10 V 015 = 15 V 020 = 20 V 025 = 25 V 035 = 35 V 050 = 50 V	C = 0.01%/1,000 hours	C = Hot Solder Dipped T = 100% Matte Tin (Sn) Plated H = Standard Solder Coated (SnPb 5% Pb minimum) B = Gold Plated	61 = None 62 = 10 Cycles after Weibull,25 C 63 = 10 Cycles, after Weibull,-55 C and 85 C 64 = 10 Cycles before Weibull, -55 C and 85 C 65 = 10 Cycles Before and After Weibull, -55 C and 85 C	1 = ESR - Standard 2 = ESR - Low	A = Option A B = Option B C = Option C

T510 Series Space Grade Multiple Anode MnO_2

Capacitance Range: 10 to 1,000 µF • **Temperature Range:** −55°C to +125°C



T	510	X	477	M	006	C	T	61	1	A
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Voltage	Failure Rate/ Design	Lead Material	Surge	ESR	Testing
T = Tantalum	Ultra Low ESR - Space Grade	E, X	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	004 = 4 V 006 = 6.3 V 010 = 10 V	C = 0.01%/1,000 hours	C = Hot Solder Dipped T = 100% Matte Tin (Sn) Plated H = Standard Solder Coated (SnPb 5% Pb minimum)	61 = None 62 = 10 Cycles after Weibull,25 C 63 = 10 Cycles, after Weibull,-55 C and 85 C 64 = 10 Cycles before Weibull, -55 C and 85 C 65 = 10 Cycles Before and After Weibull, -55 C and 85 C	1 = ESR - Standard	A = Option A B = Option B C = Option C

Downloaded from Arrow.com.

Electronic Components
KEMET
CHARGED.

Hermetically Sealed Axial

T110 Series MIL–PRF–39003 Polar Type & T212 (CSR13 Style)

Capacitance Range: 0.0047 to 330 µF • **Temperature Range:** −55°C to +125°C



T	110	A	105	K	050	A	T	7200
Capacitor Class	Series	Case Size	Capa i nc C de (pF	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Military Product Only	Termination Finish	Specification
T = Tantalum	Hermetically Sealed Axial capacitor	A, B, C, D	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	006 = 6 010 = 10 015 = 15 020 = 20 035 = 35 050 = 50 060 = 60 075 = 75 100 = 100 125 = 125	A = N/A	T = 100% Tin S= Standard (Sn/Pb)	All capacitors are sleeved unless specified. 0100 = Without sleeve 7200 = Tape & Reel 7293 & 7443 = Ammo

T212 (CSR13 Style)

T	212	A	105	K	050	B	S	7200
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Military Product Only	Termination Finish	Specification
T = Tantalum	Hermetically Sealed Axial Military grade capacitor	A, B, C, D	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	006 = 6 010 = 10 015 = 15 020 = 20 035 = 35 050 = 50 075 = 75 100 = 100	Graded: B = 0.1%/k hours C = 0 01%/k hours D = 0 001%/k hours G= 1 0 %/k hours Expone tial: M = 1%/k hours P = 0.1%/k hours R = 0 01%/k hours S = 0.001%/k hours	S = Standard (Sn/Pb)	All capacitors are sleeved unless specified 0100 = Without sleeve 7200 = Tape & Reel 7293 & 7443 = Ammo 4250 = "A" surge current 4251 = "B" surge current 4252 = "C" surge current

MIL–PRF–39003

M39003	/01	6003	A
Capacitor Class	Slash	Dash Number	Surge Option
Military Specification Number	Specification Sheet Number	Failure Rate Level	A = C-4250 B = C-4251 C = C-4252 Blank - No surge

Downloaded from Arrow.com.

Hermetically Sealed Axial (cont.)

T111 Series MIL–PRF–39003 Non-Polar & T213 (CSR91 Style)

Capacitance Range: 0.0023 to 160 µF **Temperatu e Range:** −55°C to +125°C



T	111	A	105	K	050	A	S	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Military Product Only	Termination Finish	Specification
T = Tantalum	Hermetically Sealed Axial capacitor	A, B, C, D	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	006 = 6 010 = 10 015 = 15 020 = 20 035 = 35 050 = 50 075 = 75 100 = 100	A = N/A	S= Standard (Sn/Pb)	All capacitors are sleeved unless specified.

T213 (CSR91 Style)

T	213	A	115	K	020	B	S	7200
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Military Product Only	Termination Finish	Specification
T Tantalum	Hermetically Sealed Axial Military grade capacitor	A, B, C, D	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	006 = 6 010 = 10 015 = 15 020 = 20 035 = 35 050 = 50 075 75 100 = 100	Graded: B = 0.1%/k hours C = 0.01%/k hours D = 0.001%/k hours G= 1.0 %/k hours Exponential: M = 1%/k hours P = 0.1%/k hours R = 0.01%/k hours S = 0.001%/k hours	S = Standard (Sn/Pb)	All capacitors are sleeved unless specified. 0100 = Without sleeve 7200 = Tape & Reel 7293 & 7443 Ammo 4250 = "A" surge current 1 B" rg cu n 4252 = "C" surge current

MIL–PRF–39003

M39003	/04	3007	A
Capacitor Class	Slash	Dash Number	Surge Option
Military Specification Number	Specification Sheet Number	Failure Rate Level	A = C-4250 B = C-4251 C = C-4252 Blank - No surge

Downloaded from Arrow.com.

Hermetically Sealed Axial (cont)

T140 Series MIL–PRF–39003 Polar Type & T242 (CSR23 Style)

Capacitance Range: 0.82 to 1,200 µF • **Temperature Range:** −55°C to +125°C



T	140	A	105	K	050	A	S	7200
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Military Product Only	Termination F nish	Specification
T = Tantalum	Hermetically Sealed Axial Capacitor	A, B, C, D	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	00 = 6 010 10 015 = 15 20 = 20 030 30 0 5 = 5 060 = 60 050 = 50 060 = 60	A = N/A	S = Standard (Sn/Pb) T = 100% Tin	All apacitors are sleeved unless specified. 0100 = Without sleeve 7200 Tape & R el 7293 & 744 = Ammo 4250 = 0 cycles, 25 C after We bull 4251 = 10 cycles, 55 & 85 C after Weibull 4252 = 10 cycles, -55 & 85 C before Weibull

T242 (CSR23 Style)

T	242	A	105	K	050	A	S	C
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Military Product Only	Termination Finish	Specification
T = Tantalum	T242 = CSR23	A, B, C, D	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	006 = 6 010 = 10 015 = 15 020 = 20 030 = 30 035 = 35 060 = 60 050 = 50 060 = 60	Graded: B = 0.1%/k hours C = 0.01%/k hours D = 0.001%/k hours G = 1.0%/k hours Exponential: M = 1%/k hours P = 0.1%/k hours R = 0.01%/k hours S = 0.001%/k hours	S = Standard	All capacitors are sleeved unless specified. 0100 = Without sleeve 7200 = Tape & Reel 7293 & 7443= Ammo 4250 = 10 cycles, 25 C after Weibull 4251 = 10 cycles, -55 & 85 C after Weibull 4252 = 10 cycles, -55 & 85 C before Weibull

MIL–PRF–39003

M39003	/03	3075	A
Capacitor Class	Slash	Dash Number	Surge Option
Military Specification Number	Specification Sheet Number	Failure Rate Level	A = C-4250 B = C-4251 C = C-4252 Blank - No surge

T210/T240/GR500 Series High Reliability

Capacitance Range: 0.0047 to 330 µF **Temperature Range:** −55°C to +125°C



T	210	A	105	K	050	R	S
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate	Termination Finish
T = Tantalum	210 = GR500/J (KEMET) High Reliability, Solid Electrolyte, Graded, Hermetic Seal, Axial Lead, Polar	A, B, C, D	First two digits represent significant figures. Third digit specifies number of zeros to follow.	J = ±5% K = ±10% M = ±20%	006 = 6.3 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35 050 = 50 075 = 75 100 = 100	M = 1%/k hours P = 0.1/k hours R = 0.01%/k hours S = 0.001%/k hours	S = Standard (Solder-coated nickel)

Downloaded from Arrow.com.

Hermetically Sealed Axial (cont.)

T215 Series High Temperature Solder (CSR13 Style)

Capacitance Range: 0.0047 to 330 µF **Temperature Range:** −55°C to +125°C



T	215	A	105	K	050	B	S	7200
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Military Product Only	Termination Finish	Specification
T Tantalum	Hermetically Sealed Axial High Temperature Solder	A, B, C, D	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	006 = 6 010 = 10 015 = 15 020 = 20 035 = 35 050 = 50 075 = 75 100 = 100	Graded: B = 0.1%/k hours C = 0.01%/k hours D = 0.001%/k hours G= 1.0 %/k hours Exponential: M = 1%/k hours P = 0.1%/k hours R = 0.01%/k hours S = 0.001%/k hours	S = Standard (Sn/Pb)	All capacitors are sleeved unless specified. 0100 = Wi hout sleeve 7200 = Tape & Reel 7293 & 7443 = Ammo 4250 = 10 cycles, 25 C after Weibull 4251 = 10 cycles, 55 & 85 C after Weibull 4252 = 10 cycles, 55 & 85 C before Weibull

CSR13 Style

M39003	/01	6003	E
Capacitor Class	Slash	Dash Number	Surge Option
Military Specification Number	Specification Sheet Number	Failure Rate Level	D = C-4250 E C-4251 F = C-4252 H = No C-Spec

T216 Series MIL–PRF–39003 (CSS13 Style) & T256 (CSS33 Style)

Capacitance Range: CSS13: 0.12 to 330 µF, CSS33: 1.2 to 1,000 µF • **Temperature Range:** −55°C to +125°C



T	216	A	106	K	050	C	S	
Capacitor Class	Series	Case Size	Capac tan e Code (pF)	Capacitance Tolerance	Ra ed Voltage (VDC)	Failure Rate	Termination Finish	C-Spec
T = Tantalum	216 (MIL–C–39003/10, CSS13) 256 (MIL–C–39003/10, CSS33)	A, B, C, D	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10%	006 = 6 010 = 10 015 = 15 020 = 20 035 = 35 050 = 50 075 = 75	Graded: B = 0.1%/k hours C = 0.01%/k hours	S = Standard (Solder-coated nickel)	Blank = Sleeved 0100 = Unsleeved 7200 = Tape & Reel 7200 = Tape & Reel 7293 & 7443 = Ammo

CSS13 Style

M39003	/10	2049	S
Capacitor Class	Slash	Dash Number	Sleeve
Military Specification Number	Specification Sheet Number	Failure Rate Level	S = Sleeved U = Unsleeved use C - 0100

CSS33 Style

M39003	/10	2549	S
Capacitor Class	Slash	Dash Number	Sleeve
Military Specification Number	Specification Sheet Number	Failure Rate Level	S = Sleeved U = Unsleeved use C - 0100

Downloaded from Arrow.com.

Hermetically Sealed Axial (cont.)

T222 Series MIL–PRF–39003 Polar Miniature (CSR09 Style)

Capacitance Range: 0.047 to 18 µF • **Temperature Range:** −55°C to +125°C



T	222	A	225	K	010	B	S	C
Capacitor Class	Series	Case Size	Capacitanc Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Military Produ t Only	Termination Finish	Specification
T = Tantalum	T222 (CSR09)	A, B	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10%	006 = 6 010 = 10 015 = 15 020 = 20 035 = 35 050 = 50 075 = 75	Graded: B = 0.1%/k hours C = 0.01%/k hours D = 0 001% k hours G = 1.0%/k hours Exponential: M = 1%/k h urs P = 0.1%/k hours R = 0.01%/k hours S = 0.001%/k hours	S = Standard Positive: Alloy 52 (solder-coated) Negative: Solder-coated nickel	All capacitors are sleeved unless specified. 7200 = Tape & Reel 7293 & 7443 = Ammo

CSR09 Style

M39003	/02	2061	D
Capacitor Class	Slash	Dash Number	Surge Option
Military Specification Number	Specification Sheet Number	Failure Rate Level	D = C-4250 E = C-4251 F = C-4252 H = No C-Spec

T225 Series High Temperature Solder (CSR09 Style)

Capacitance Range: 0.047 to 18 µF • **Temperature Range:** −55°C to +125°C



T	225	A	225	K	010	B	S	7200
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Military Product Only	Termination Finish	Specification
T = Tantalum	Hermetically Sealed Axial High Temperature Solder	A, B	First two digits represent significant figures. Third digit specifies number of zeros to follow.	J = ±5% K = ±10%	006 = 6 010 = 10 015 = 15 020 = 20 035 = 35 050 = 50 075 = 75	Graded: B = 0.1%/k hours C = 0.01%/k hours D = 0.001%/k hours G = 1.0%/k hours Exponential: M = 1%/k hours P = 0.1%/k hours R = 0.01%/k hours S = 0.001%/k hours	S = Standard	All capacitors are sleeved unless specified. 0100 = Without sleeve 7200 = Tape & Reel 7293 & 7443 = Ammo 4250 = 10 cycles, 25 C after Weibull 4251 = 10 cycles, -55 & 85 C after Weibull 4252 = 10 cycles, -55 & 85 C before Weibull

CSR09 Style

M39003	/02	3036	A
Capacitor Class	Slash	Dash Number	Surge Option
Military Specification Number	Specification Sheet Number	Failure Rate Level	A = C-4250 B = C-4251 C = C-4252 Blank - No surge

Downloaded from Arrow.com.

Hermetically Sealed Axial (cont.)

T245 Series High Temperature Solder (CSR23 Style)

Capacitance Range: 1.2 to 1,000 µF • **Temperature Range:** −55°C to +125°C



T	245	A	105	K	050	A	S	7200
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Military Product Only	Termination Finish	Specification
T = Tantalum	Hermetically Sealed Axial High Temperature Solder	A, B, C, D	First two digits represent significant figures Third digit specifies number of zeros.	K = ±10% M = ±20%	006 = 6 010 = 10 015 = 15 020 = 20 035 = 35 050 = 50	Graded: B = 0.1%/k hours C = 0.01%/k hours D = 0 001% k hours G = 1.0%/k hours Exponential: M = 1%/k h urs P = 0.1%/k hours R = 0.01%/k hours S = 0.001%/k hours	S = Standard	All capacitors are sleeved unless specified 0100 = Without sleeve 7200 = Tape & Reel 7293 & 7443 = Ammo 4250 = 10 cycles, 25 C after Weibull 4251 = 10 cycles, -55 & 85 C after Weibull 4252 = 10 cycles, -55 & 85 C before Weibull

CSR23 Style

M39003	/03	3075	E
Capacitor Class	Slash	Dash Number	Surge Option
Military Specification Number	Specification Sheet Number	Failure Rate Level	D = C-4250 E = C-4251 F = C-4252 H = No C-Spec

T252 Series MIL–PRF–39003 (CSR33 Style)

Capacitance Range: 1.2 to 1,000 µF • **Temperature Range:** −55°C to +125°C



T	252	A	125	K	050	M	S	C
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate Military Product Only	Termination Finish	Specification
T = Tantalum	252 (CSR33)	A, B, C, D	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	006 6 010 = 10 015 = 15 020 = 20 035 = 35 050 = 50	Graded: B = 0 1% k hours C = 0.01%/k hours D = 0 001%/k hours Exponentia : M = 1%/k hours P = 0.1%/k hours R = 0.01%/k hours S = 0.001%/k hours	S = Standard	All capacit rs are sleeved unless specified 0100 = Without sleeve 7200 = Tape & Reel 7293 & 7443 = Ammo 4250 = 0 cycles, 25 C after Weibull 4251 = 10 cycles, -55 & 85 C after Weibull 4252 = 10 cycles, -55 & 85 C before Weibull

CSR33 Style

M39003	/06	4073	B
Capacitor Class	Slash	Dash Number	Surge Option
Military Specification Number	Specification Sheet Number	Failure Rate Level	B = C-4251 C = C-4252

Downloaded from Arrow.com.

Hermetically Sealed Axial (cont.)

T255 Series High Temperature Solder (CSR33 Style)

Capacitance Range: 1.2 to 1,000 µF • **Temperature Range:** −55°C to +125°C



T	255	A	125	K	050	M	S	C
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Military Product Only	Termination Finish	Specification
T = Tantalum	Hermetically Sealed Axial High Temperature Solder	A, B, C, D	First two digits represent significant figures. Third digit specifies number of zeros to follow.	K = ±10% M = ±20%	006 = 6 010 = 10 015 = 15 020 = 20 035 = 35 050 = 50	Graded: B = 0.1%/k hours C = 0.01%/k hours D = 0.001%/k hours G = 1.0%/k hours Exponential: M = 1%/k hours P = 0.1%/k hours R = 0.01%/k hours S = 0.001%/k hours	S = Standard	4251 = 10 cycles, -55 & 85 C after Weibull 4252 = 10 cycles, -55 & 85 C before Weibull 7200 = Tape & Reel 7293 & 7443 = Ammo

CSR33 Style

M39003	/06	4073	H
Capacitor Class	Slash	Dash Number	Surge Option
Military Specification Number	Specification Sheet Number	Failure Rate Level	E = C-4251 F = C-4252 H = Hi Temp Solder Only

T262 Series MIL–PRF–39003 (CSR21 Style)

Capacitance Range: 5.6 to 330 µF • **Temperature Range:** −55°C to +125°C



T	262	C	106	K	050	C	C
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate	Termination Finish
T = Tantalum	Hermetically Sealed Axial Capacitor	C, D	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	006 = 6 010 = 10 015 = 15 020 = 20 035 = 35 050 = 50	Graded: B = 0.1%/k hours C = 0.01%/k hours D = 0.001%/k hours Exponential: M = 1%/k hours P = 0.1%/k hours R = 0.01%/k hours S = 0.001%/k hours	All capacitors are sleeved unless specified. 0100 = Without sleeve 7200 = Tape & Reel 7293 & 7443 = Ammo 4251 = 10 cycles, 55 & 85 C after Weibull 4252 = 10 cycles, -55 & 85 C before Weibull

CSR21 Style

M39003	/09	3074	B
Capacitor Class	Slash	Dash Number	Surge Option
Military Specification Number	Specification Sheet Number	Failure Rate Level	B = C-4251 C = C-4252

Downloaded from Arrow.com.

Hermetically Sealed Axial (cont.)

T550 Series Polymer Hermetic Seal (PHS) 105ºC & DLA Series

Capacitance Range: 20 to 820 µF • **Temperature Range:** −55°C to +105°C



T	550	B	107	M	025	A	T	4251	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	P oduct Level	Termination Finish	Surge Option	Sleeve Option
T = Tantalum	550 = Polymer Hermetic Seal	B	First two digits represent sig ificant figures Third digit specifies number of zeros.	K = ±10% M = ±20%	006 = 6.3 008 = 8 015 = 15 025 = 25 040 = 40 050 = 5 060 = 60 075 = 75 100 = 100	A = N/A B* = DLA 13030 Standard reliability T* = DLA 13030 High reliability	T = 100% tin (Sn) plated H = Tin/lead (SnPb) solder coated (5% Pb minimum)	Blank 25 C ±5 C, 10 cycles, after constant voltage c nditioning (KEMET standard) 4251 = 10 cycles, 55 C and +85 C after voltage aging 4252 = 10 cycles, -55 C and +85 C before voltage aging	Blank = Sleeved 0100 = Unsleeved 7200 = Tape & Reel 7293 & 7443 = Ammo

DLA Series

13030	-01	K	A	S	L	B
Drawing Number	Dash Number	Capacitance Tolerance	Surge Current Testing	Insulation	Lead Length	Product Level
	See Part Number Table	K = ±10% M = ±20%	A = +25 C ± 5 C, 10 cycles, after constant voltage conditioning (KEMET standard) B = -55 C -5 C, +0 C and +85 C ± 5 C; after constant voltage conditioning. C = -55 C -5 C, +0 C and +85 C ± 5 C; before constant voltage conditioning.	S = Sleeved U = Unsleeved	L = 1.50 inches (standard)	B = Standard reliability T = High reliability

T551 Series Polymer Hermetic Seal (PHS) 125ºC

Capacitance Range: 20 to 820 µF • **Temperature Range:** −55°C to +125°C



T	551	B	107	M	025	A	T	4251	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Product Level	Termination Finish	Surge Option	Sleeve Option
T = Tantalum	551 = Polymer Hermetic Seal	B	First two digits represent significant figures. Third digit specifies number of zeros.	K = ±10% M = ±20%	006 = 6.3 V 008 = 8 V 015 = 15 V 025 = 25 V 040 = 40 V 050 = 50 V 060 = 60 V	A = N/A	T = 100% tin (Sn) plated H = Tin/lead (SnPb) solder coated (5% Pb minimum)	4251 = Surge current, 10 cycles, -55 C and +85 C	Blank = Sleeved 0100 = Unsleeved 7200 = Tape & Reel 7293 & 7443 = Ammo

Downloaded from Arrow.com.

Radial Dipped

T350, T351, T352, T353, T354, T355 and T356 Series UltraDip II Polar

Capacitance Range: 0.1 to 680 µF • **Temperature Range:** −55°C to +125°C



T	35X	A	105	M	035	A	S	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate	Termination Finish	Specification
T = Tantalum	350 351 352 353 354 355 356	A, B, C, D, E, F, G, H, J, K, L, M	First two digits represent significant figures. Third digit specifies number of zeros to follow.	M = ±20% K = ±10% J = ±5% (Available on special order)	003 = 3 006 = 6 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	Not Applicable	S = Standard	7301 & 7303 = Tape & Reel 7305 & 7317 = Ammo

T363 and T369 Series MIL-PRF-49137/2 (CX02 and CX12 Style)

Capacitance Range: 0.1 to 330 µF **Temperatu e Range:** −55°C to +85°C



T	35X	A	105	M	035	A	S	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate	Termination Finish	Specification
T = Tantalum	363 369	A, B, C, D	First two digits represent significant figures. Third digit specifies number of zeros to follow.	M = ±20% K = ±10%	006 = 6 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35 050 = 50	Not Applicable	S = Standard	7301 & 7303 = Tape & Reel 7305 & 7317 = Ammo

MIL–PRF–49137/2 (CX02 & CX12 Style)

CX	02	D	225	K
Capacitor Class	Series	Voltage	Capacitance Code (pF)	Capacitance Tolerance
CX = MIL-PRF	02 = T363 12 = T369	D = 6 V F = 10 V H = 15 V J = 20 V K = 25 V M = 35 V N = 50 V	First two digits represent significant figures. Third digit specifies number of zeros to follow.	K = ±10% M = ±20%

T368 Series UltraDip II

Capacitance Range: 5.6 to 330 µF • **Temperature Range:** −55°C to +85°C



T	368	C	106	M	035	A	S	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate	Termination Finish	Specification
T = Tantalum	T368	C, D	First two digits represent significant figures. Third digit specifies number of zeros to follow.	M = ±20% K = ±10%	006 = 6 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35 050 = 50	Not Applicable	S = Standard	7301 & 7303= Tape & Reel 7305 & 7317 = Ammo

Downloaded from Arrow.com.

Radial Dipped (cont.)

T396 and T398 Series UltraDip III (3 Leaded)

Capacitance Range: 0.1 to 680 µF • **Temperature Range:** −55°C to +125°C



T	39X	A	105	M	035	A	S	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate	Termination Finish	Specification
T = Tantalum	T396 Straight Leads T398 Straight Leads	A, B, C, D, E, F, G, H, J, K, L, M	First two digits represent significant figures. Third digit specifies number of zeros to follow.	M = ±20% K = ±10% (Special order only)	003 = 3 006 = 6 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	Not Applicable	S = Standard	7301 & 7303 = Tape & Reel 7305 & 7317 = Ammo

Molded Axial

T322 & T323 Series MIL–PRF–49137/1 and 5 (CX01 & CX05 Style)

Capacitance Range: 0.1 to 330 µF • **Temperature Range:** −55°C to +85°C



T	32X	A	474	M	035	A	T	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/Military Product	Termination Finish	Packaging
T = Tantalum	Axial Molded Polar Solid Tantalum. Insert appropriate number to replace letter ""X"" = 322 or 323 (CX01 or CX05).	A, B, C, D, E, F	First two digits represent significant figures. Third digit specifies number of zeros to follow.	J = ±5% K = ±10% M = ±20%	002 = 2 004 = 4 006 = 6 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35 050 = 50	Not Applicable	T = 100% tin S = standard (solder-coated nickel)	(When necessary) Reeling per EIA Specification RS-296 Blank = Bulk 7200 = Reel

MIL PRF 49137/1/5 (CX01 & CX05 Style)

CX	05	D	225	K
Capacitor Class	Series	Rated Voltage (VDC)	Capacitance Code (pF)	Capacitance Tolerance
CX = MIL-PRF	01 = T322 05 = T323	D = 6 F = 10 H = 15 J = 20 K = 25 M = 35 N = 50	First two digits represent significant figures. Third digit specifies number of zeros to follow.	K = ±10% M = ±20%

Downloaded from Arrow.com.

Molded Radial

T330 Series Precision Molded Polar

Capacitance Range: 0.1 to 220 µF **Temperature Range:** −55°C to +125°C



T	330	B	104	M	035	A	S	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate	Termination Finish	Specification
T = Tantalum	Radial Lead Precision Molded Polar Solid Tantalum	A B C, D	F rs wo digits represent significant figures. Third digit specifies number of zeros to follow.	K = ± % M = ±20% J = ±5% (available on request)	6 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35 050 = 50	Not A p cab e	S = Standard (Solder-coated nickel) T = 100% tin (Sn) plated	7301 = Tape & Reel 7305 & 7317 = Ammo

T340 Series Precision Molded Radial Lead

Capacitance Range: 0.1 to 330 µF • **Temperature Range:** −55°C to +125°C



T	340	A	105	M	035	A	S	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate	Termination Finish	Specification
T = Tantalum	Radial Lead Precision Molded Polar Solid Tantalum	A, B, C, D, E, F	First two digits represent significant figures. Third digit specifies number of zeros to follow.	M = ±20% (standard) K = ±10% J = ±5% (available on request)	003 = 3 006 = 6 010 = 10 015 = 15/16 020 = 20 025 = 25 035 = 35 040 = 40 050 = 50	Not Applicable	S = Standard (Solder-coated copperweld)	7301 = Tape & Reel 7305 & 7317 = Ammo

T370 and T378 Series Micron MIL-PRF-4913716 (CX06 Style)

Capacitance Range: T370: 0 68 to 220 µF, T378 2 2 to 220 µF • **Temperature Range:** −55°C to +125°C



T	37X	D	475	M	035	A	S	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate	Termination Finish	Specification
T = Tantalum	370 378	C, D, E, F	First two digits represent significant figures. Third digit specifies number of zeros to follow.	M = ±20% K = ±10% J = ±5% L = 40%, -20%	003 = 3 004 = 4 006 = 6.3 010 = 10 015 = 15 020 = 20 025 = 25 035 = 35	Not Applicable	S = Standard (Solder coated nickel)	7301 = Tape & Reel 7305 & 7317 = Ammo

MIL-PRF-49137/6 (CX06 Style)

CX	06	D	225	K
Capacitor Class	Series	Voltage	Capacitance Code (pF)	Capacitance Tolerance
CX = MIL-PRF	06 = T378	A = 2 V B = 3 V C = 4 V D = 6 V F = 10 V H = 15 V J = 20 V K = 25 V M = 35 V	First two digits represent significant figures. Third digit specifies number of zeros to follow.	K = ±10% M = ±20%

Downloaded from Arrow.com.

Downloaded from Arrow.com.

Electronic Components

KEMET

CHARGED.®

Downloaded from Arrow.com.



Corporate Headquarters

KEMET Corporation
2835 KEMET Way
Simpsonville, SC 29681
USA
864.963.6300
www.kemet.com

Countries and Areas listed below represent KEMET operations throughout the world.

Bulgaria	Indonesia	Singapore
China	Italy	South Korea
Finland	Japan	Sweden
France	Macedonia	Taiwan
Germany	Malaysia	United Kingdom
Hong Kong	Mexico	USA
India	Portugal	

©2015 KEMET. All rights reserved.
COIG1015

Electronic Components
KEMET
CHARGED.®

Downloaded from Arrow.com.