

# NXU0304

## 4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

Rev. 2 — 2 December 2024

Product data sheet

### 1. General description


The NXU0304 is a 4-bit, dual-supply level translating buffer with Schmitt-trigger inputs and 3-state outputs. It features four data inputs (A<sub>n</sub> and B<sub>4</sub>), four data outputs (YB<sub>n</sub> and YA<sub>4</sub>) and an output enable input (OE).

Both V<sub>CCA</sub> and V<sub>CCB</sub> can be supplied at any voltage between 0.9 V and 5.5 V making the device suitable for translating between any of the voltage nodes (1.2 V, 1.5 V, 1.8 V, 2.5 V, 3.3 V and 5.0 V).

This device facilitates asynchronous communication between data buses. Transmit data with a fixed direction (unidirectionally) from the A bus to the B bus on three channels and from the B bus to the A bus for on one channel. The OE pin can be referenced to V<sub>CCA</sub> and V<sub>CCB</sub> domain and when OE pin is set LOW the outputs are disabled and enter a high-impedance OFF-state which isolates the buses. The OE pin can be left floating or externally pulled down to ground to ensure the high-impedance state of the outputs during power up or power down.

This device ensures low static and dynamic power consumption across the entire supply range and is fully specified for partial power down applications using I<sub>OFF</sub>. The I<sub>OFF</sub> circuitry prevents potentially damaging backflow current through the device when it is powered down or if one of the power supplies is disconnected (floating).

No power supply sequencing is required and output glitches during power supply transitions are prevented. As a result, glitches will not appear on the outputs for supply transitions during power-up/down.



### 2. Features and benefits

- Wide supply voltage range:
  - V<sub>CCA</sub>: 0.9 V to 5.5 V
  - V<sub>CCB</sub>: 0.9 V to 5.5 V
- Low power consumption for supply voltage range 1.1 V to 5.5 V
  - 3  $\mu$ A (T<sub>amb</sub> = 25 °C)
  - 5  $\mu$ A (T<sub>amb</sub> = -40 °C to +125 °C)
- Schmitt-trigger inputs with integrated static high ohmic pull-down resistor on the input
- Maximum data rates:
  - 250 Mbps ( $\geq$  1.8 V to 5 V translation)
- High output drive 12 mA at 5 V
- Output enable (OE) allows connection to V<sub>CCA</sub> or V<sub>CCB</sub> domain
- Suspend mode when either one of the supply voltages is below 100 mV or disconnected (floating)
- Low noise overshoot and undershoot <10% of V<sub>CCO</sub>
- I<sub>OFF</sub> circuitry provides partial power-down mode operation
- Latch-up performance exceeds 100 mA per JESD78D Class II
- Complies with JEDEC standard:
  - JESD8-12 (0.9 V to 1.3 V)
  - JESD8-11 (1.4 V to 1.6 V)
  - JESD8-7 (1.65 V to 1.95 V)
  - JESD8-5 (2.3 V to 2.7 V)
  - JESD8C (2.7 V to 3.6 V)
  - JESD12-6 (4.5 V to 5.5 V)
- ESD protection:
  - HBM: ANSI/ESDA/JEDEC JS-001 class 2 exceeds 2500 V
  - CDM: ANSI/ESDA/JEDEC JS-002 class C3 exceeds 1500 V
- Specified from -40 °C to +85 °C and -40 °C to +125 °C
- Similar functions: NXU0104 and NXU0204

### 3. Applications

- General purpose I/O level translation
- Noisy environments or slow input signals
- Supports push-pull voltage translation as UART, SPI and JTAG protocols
- Consumer

nexperia

4. Ordering information

Table 1. Ordering information

| Type number                 | Package           |          |                                                                                                                                                             |                           |
|-----------------------------|-------------------|----------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|
|                             | Temperature range | Name     | Description                                                                                                                                                 | Version                   |
| <a href="#">NXU0304PW</a>   | -40 °C to +125 °C | TSSOP14  | plastic thin shrink small outline package; 14 leads; body width 4.4 mm                                                                                      | <a href="#">SOT402-1</a>  |
| <a href="#">NXU0304BQ</a>   | -40 °C to +125 °C | DHVQFN14 | plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads; 14 terminals; body 2.5 × 3 × 0.85 mm                                | <a href="#">SOT762-1</a>  |
| <a href="#">NXU0304BZ</a>   | -40 °C to +125 °C | DHXQFN14 | plastic, leadless dual in-line compatible thermal enhanced extreme thin quad flat package; no leads; 14 terminals; 0.4 mm pitch; body 2 mm × 2 mm × 0.48 mm | <a href="#">SOT8014-1</a> |
| <a href="#">NXU0304GU12</a> | -40 °C to +125 °C | XQFN12   | plastic, extremely thin quad flat package; no leads; 12 terminals; body 1.70 × 2.0 × 0.50 mm                                                                | <a href="#">SOT1174-1</a> |


5. Marking

Table 2. Marking

| Type number | Marking code[1] |
|-------------|-----------------|
| NXU0304PW   | NXU0304         |
| NXU0304BQ   | U0304           |
| NXU0304BZ   | L03             |
| NXU0304GU12 | L6              |


[1] The pin 1 indicator is located on the lower left corner of the device, below the marking code.

6. Functional diagram



7. Pinning information

7.1. Pinning



7.2. Pin description

Table 3. Pin description

| Symbol             | Pin                           |             | I/O | Description                                                                                                     |
|--------------------|-------------------------------|-------------|-----|-----------------------------------------------------------------------------------------------------------------|
|                    | SOT402-1, SOT762-1, SOT8014-1 | SOT1174-1   |     |                                                                                                                 |
| V <sub>CCA</sub>   | 1                             | 1           | -   | supply voltage A-side (A1, A2, A3, YA4)                                                                         |
| A1, A2, A3, B4     | 2, 3, 4, 10                   | 2, 3, 4, 7  | I   | data inputs A-side and referenced to V <sub>CCA</sub><br>data input B-side and referenced to V <sub>CCB</sub>   |
| n.c.               | 6, 9                          | -           | -   | not connected                                                                                                   |
| GND                | 7                             | 6           | -   | ground (0 V)                                                                                                    |
| YB1, YB2, YB3, YA4 | 13, 12, 11, 5                 | 10, 9, 8, 5 | O   | data outputs B-side and referenced to V <sub>CCB</sub><br>data output A-side and referenced to V <sub>CCA</sub> |
| OE                 | 8                             | 12          | I   | output enable input (active HIGH)                                                                               |
| V <sub>CCB</sub>   | 14                            | 11          | -   | supply voltage B-side (YB1, YB2, YB3, B4)                                                                       |

8. Functional description

Table 4. Function table

H = HIGH voltage level; L = LOW voltage level; X = don't care; Z = high-impedance OFF-state.

| Supply voltage                      | Input | Input  | Output   |
|-------------------------------------|-------|--------|----------|
| V <sub>CCA</sub> , V <sub>CCB</sub> | OE    | An, B4 | YBn, YA4 |
| 0.9 V to 5.5 V                      | H     | L      | L        |
| 0.9 V to 5.5 V                      | H     | H      | H        |
| 0.9 V to 5.5 V                      | L     | X      | Z        |
| GND [1]                             | X     | X      | Z        |
| Floating [2]                        | X     | X      | Z        |

[1] If either V<sub>CCA</sub> or V<sub>CCB</sub> is below 100 mV or GND, the device goes into suspend mode (Hi-Z).  
[2] If either V<sub>CCA</sub> or V<sub>CCB</sub> disconnected (floating), the device goes into suspend mode (Hi-Z).

8.1. Overview

The NXU0304 is a 4-bit, dual-supply level translating buffer with Schmitt-trigger inputs and 3-state outputs. It features four data inputs (An and B4), four data outputs (YBn and YA4) and an output enable input (OE). Both V<sub>CCA</sub> and V<sub>CCB</sub> can be supplied at any voltage between 0.9 V and 5.5 V.

8.2. Inputs



The inputs have integrated pull-down resistors of 6.5 MΩ (typical) which prevent an undefined state at the Schmitt-trigger input and the output. If an external pull-up is required, it should be no larger than 1 MΩ to avoid contention with the 6.5 MΩ internal pull-down.

Additionally, each input is provided with a through Schmitt-trigger which makes this device tolerant for slow and noisy input signals. Prolonged input slopes at a slow rate may lead to increased dynamic current consumption.

The output-enable input (OE) can be referenced to V<sub>CCA</sub> and V<sub>CCB</sub> domain by making use of the developed V<sub>CC(MIN)</sub> circuitry. When the OE pin is set LOW, the output is disabled and enters high-impedance OFF-state which isolates the output. The OE pin can be left floating or externally pulled down to ground to ensure outputs remain in the high-impedance state during power up or power down.

The input signals can be safely driven above the supply voltage, as long as the maximum input voltage value specified in the Recommended Operating Conditions is not exceeded.

Input transfer characteristics



8.3. Outputs

Balanced output enables the device to both sink and source similar currents. The high drive capability of this device creates fast edges and capable of driving larger currents.

Output transfer characteristics




Fig. 6. Typical LOW-level output voltage ( $V_{OL}$ ) versus LOW-level output current ( $I_{OL}$ ) for data outputs YBn, YA4




Fig. 7. Typical HIGH-level output voltage ( $V_{OH}$ ) versus HIGH-level output current ( $I_{OH}$ ) for data outputs YBn, YA4

8.4. Suspend mode and I<sub>OFF</sub> protection circuitry

When either V<sub>CCA</sub> or V<sub>CCB</sub> drops below 100 mV or becomes disconnected (floating) the product enters suspend mode (Hi-Z). All outputs are disabled and in transition to a high-impedance OFF-state. The I<sub>OFF</sub> circuitry prevents potentially damaging backflow current through the device when it is powered down or if one of the power supplies is disconnected (floating). It is advisable to keep the inputs in low state before disconnecting (floating) either supply.

Below a graphical explanation:




Fig. 8. Suspend mode and I<sub>OFF</sub> protection circuitry

9. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

| Symbol           | Parameter               | Conditions                                                     | Min  | Max                    | Unit |
|------------------|-------------------------|----------------------------------------------------------------|------|------------------------|------|
| V <sub>CCA</sub> | supply voltage A        |                                                                | -0.5 | +6.5                   | V    |
| V <sub>CCB</sub> | supply voltage B        |                                                                | -0.5 | +6.5                   | V    |
| I <sub>IK</sub>  | input clamping current  | V <sub>I</sub> < 0 V                                           | -50  | -                      | mA   |
| V <sub>I</sub>   | input voltage           | [1]                                                            | -0.5 | +6.5                   | V    |
| I <sub>OK</sub>  | output clamping current | V <sub>O</sub> < 0 V                                           | -50  | -                      | mA   |
| V <sub>O</sub>   | output voltage          | Active mode [1][2][3]                                          | -0.5 | V <sub>CCO</sub> + 0.5 | V    |
|                  |                         | Suspend or 3-state mode [1]                                    | -0.5 | +6.5                   | V    |
| I <sub>O</sub>   | output current          | V <sub>O</sub> = 0 V to V <sub>CCO</sub> [2]                   | -    | ±25                    | mA   |
| I <sub>CC</sub>  | supply current          | I <sub>CCA</sub> or I <sub>CCB</sub> ; per V <sub>CC</sub> pin | -    | 100                    | mA   |
| I <sub>GND</sub> | ground current          | per GND pin                                                    | -100 | -                      | mA   |
| T <sub>stg</sub> | storage temperature     |                                                                | -65  | +150                   | °C   |

4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

| Symbol           | Parameter               | Conditions                                     | Min | Max | Unit |
|------------------|-------------------------|------------------------------------------------|-----|-----|------|
| P <sub>tot</sub> | total power dissipation | SOT402-1 (TSSOP14) [4]<br>SOT762-1 (DHVQFN14)  | -   | 500 | mW   |
|                  |                         | SOT8014-1 (DHXQFN14) [5]<br>SOT1174-1 (XQFN12) | -   | 250 | mW   |

- [1] The minimum input voltage ratings and output voltage ratings may be exceeded if the input and output current ratings are observed.
- [2] V<sub>CCO</sub> is the supply voltage associated with the outputs (YBn, YA4).
- [3] V<sub>CCO</sub> + 0.5 V should not exceed 6.5 V.
- [4] For SOT402-1 (TSSOP14) package: P<sub>tot</sub> derates linearly with 7.3 mW/K above 81 °C.  
For SOT762-1 (DHVQFN14) package: P<sub>tot</sub> derates linearly with 9.6 mW/K above 98 °C.
- [5] For SOT8014-1 (DHXQFN14) package: P<sub>tot</sub> derates linearly with 8.7 mW/K above 121 °C.  
For SOT1174-1 (XQFN12) package: P<sub>tot</sub> derates linearly with 5.6 mW/K above 105 °C.

10. ESD ratings

Table 6. ESD ratings

| Symbol           | Parameter                       | Conditions                           | Value  | Unit |
|------------------|---------------------------------|--------------------------------------|--------|------|
| V <sub>ESD</sub> | electrostatic discharge voltage | HBM: ANSI/ESDA/JEDEC JS-001 class 2  | ± 2500 | V    |
|                  |                                 | CDM: ANSI/ESDA/JEDEC JS-002 class C3 | ± 1500 | V    |

11. Recommended operating conditions

Table 7. Recommended operating conditions

| Symbol           | Parameter           | Conditions              | Min | Max              | Unit |
|------------------|---------------------|-------------------------|-----|------------------|------|
| V <sub>CCA</sub> | supply voltage A    |                         | 0.9 | 5.5              | V    |
| V <sub>CCB</sub> | supply voltage B    |                         | 0.9 | 5.5              | V    |
| V <sub>I</sub>   | input voltage       |                         | 0   | 5.5              | V    |
| V <sub>O</sub>   | output voltage      | Active mode [1]         | 0   | V <sub>CCO</sub> | V    |
|                  |                     | Suspend or 3-state mode | 0   | 5.5              | V    |
| T <sub>amb</sub> | ambient temperature |                         | -40 | +125             | °C   |

- [1] V<sub>CCO</sub> is the supply voltage associated with the outputs (YBn, YA4).

12. Thermal characteristics

Table 8. Thermal characteristics

| Symbol               | Parameter                                                          | Condition                        | SOT402-1 | SOT762-1 | SOT8014-1 | SOT1174-1 | Unit |
|----------------------|--------------------------------------------------------------------|----------------------------------|----------|----------|-----------|-----------|------|
| R <sub>th(j-a)</sub> | thermal resistance from junction to ambient                        | in free air;<br>JEDEC test board | 134      | 98       | 98        | 172       | °C/W |
| R <sub>th(j-c)</sub> | thermal resistance from case (top) of package                      | in free air;<br>JEDEC test board | 59       | 65       | 71        | 82        | °C/W |
| Ψ <sub>j-top</sub>   | thermal characterization parameter from junction to top of package | in free air;<br>JEDEC test board | 5.4      | 14       | 3.4       | 3.3       | °C/W |

13. Static characteristics

Table 9. Static characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

| Symbol          | Parameter                        | Conditions                                                     | +25 °C |      |     | -40 °C to +85 °C |      | -40 °C to +125 °C |      | Unit |
|-----------------|----------------------------------|----------------------------------------------------------------|--------|------|-----|------------------|------|-------------------|------|------|
|                 |                                  |                                                                | Min    | Typ  | Max | Min              | Max  | Min               | Max  |      |
| V <sub>T+</sub> | positive-going threshold voltage | An, B4 inputs                                                  |        |      |     |                  |      |                   |      |      |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 0.9 V                    | -      | 0.58 | -   | -                | -    | -                 | -    | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.1 V                    | -      | 0.71 | -   | 0.44             | 0.88 | 0.44              | 0.88 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.4 V                    | -      | 0.89 | -   | 0.60             | 0.98 | 0.60              | 0.98 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.65 V                   | -      | 1.05 | -   | 0.76             | 1.13 | 0.76              | 1.13 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 2.3 V                    | -      | 1.39 | -   | 1.08             | 1.56 | 1.08              | 1.56 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 3.0 V                    | -      | 1.75 | -   | 1.48             | 1.92 | 1.48              | 1.92 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 4.5 V                    | -      | 2.50 | -   | 2.19             | 2.74 | 2.19              | 2.74 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 5.5 V                    | -      | 3.02 | -   | 2.65             | 3.33 | 2.65              | 3.33 | V    |
|                 |                                  | OE input (referenced to V <sub>CCA</sub> or V <sub>CCB</sub> ) |        |      |     |                  |      |                   |      |      |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 0.9 V                    | -      | 0.58 | -   | -                | -    | -                 | -    | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.1 V                    | -      | 0.70 | -   | 0.44             | 0.88 | 0.44              | 0.88 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.4 V                    | -      | 0.89 | -   | 0.60             | 0.98 | 0.60              | 0.98 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.65 V                   | -      | 1.04 | -   | 0.76             | 1.13 | 0.76              | 1.13 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 2.3 V                    | -      | 1.38 | -   | 1.08             | 1.56 | 1.08              | 1.56 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 3.0 V                    | -      | 1.74 | -   | 1.48             | 1.92 | 1.48              | 1.92 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 4.5 V                    | -      | 2.50 | -   | 2.19             | 2.74 | 2.19              | 2.74 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 5.5 V                    | -      | 3.03 | -   | 2.65             | 3.33 | 2.65              | 3.33 | V    |

4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

| Symbol          | Parameter                        | Conditions                                                     | +25 °C |      |     | -40 °C to +85 °C |      | -40 °C to +125 °C |      | Unit |
|-----------------|----------------------------------|----------------------------------------------------------------|--------|------|-----|------------------|------|-------------------|------|------|
|                 |                                  |                                                                | Min    | Typ  | Max | Min              | Max  | Min               | Max  |      |
| V <sub>T-</sub> | negative-going threshold voltage | An, B4 inputs                                                  |        |      |     |                  |      |                   |      |      |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 0.9 V                    | -      | 0.33 | -   | -                | -    | -                 | -    | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.1 V                    | -      | 0.40 | -   | 0.17             | 0.48 | 0.17              | 0.48 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.4 V                    | -      | 0.50 | -   | 0.28             | 0.59 | 0.28              | 0.59 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.65 V                   | -      | 0.59 | -   | 0.35             | 0.69 | 0.35              | 0.69 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 2.3 V                    | -      | 0.84 | -   | 0.56             | 0.97 | 0.56              | 0.97 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 3.0 V                    | -      | 1.12 | -   | 0.89             | 1.5  | 0.89              | 1.5  | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 4.5 V                    | -      | 1.71 | -   | 1.51             | 1.97 | 1.51              | 1.97 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 5.5 V                    | -      | 2.10 | -   | 1.88             | 2.4  | 1.88              | 2.4  | V    |
|                 |                                  | OE input (referenced to V <sub>CCA</sub> or V <sub>CCB</sub> ) |        |      |     |                  |      |                   |      |      |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 0.9 V                    | -      | 0.33 | -   | -                | -    | -                 | -    | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.1 V                    | -      | 0.41 | -   | 0.17             | 0.48 | 0.17              | 0.48 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.4 V                    | -      | 0.51 | -   | 0.28             | 0.59 | 0.28              | 0.59 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.65 V                   | -      | 0.59 | -   | 0.35             | 0.69 | 0.35              | 0.69 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 2.3 V                    | -      | 0.84 | -   | 0.56             | 0.97 | 0.56              | 0.97 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 3.0 V                    | -      | 1.12 | -   | 0.89             | 1.5  | 0.89              | 1.5  | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 4.5 V                    | -      | 1.69 | -   | 1.51             | 1.97 | 1.51              | 1.97 | V    |
|                 |                                  | V <sub>CCA</sub> = V <sub>CCB</sub> = 5.5 V                    | -      | 2.07 | -   | 1.88             | 2.46 | 1.88              | 2.46 | V    |

## 4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

| Symbol          | Parameter                 | Conditions                                                     | +25 °C                 |      |     | -40 °C to +85 °C       |      | -40 °C to +125 °C      |      | Unit |
|-----------------|---------------------------|----------------------------------------------------------------|------------------------|------|-----|------------------------|------|------------------------|------|------|
|                 |                           |                                                                | Min                    | Typ  | Max | Min                    | Max  | Min                    | Max  |      |
| V <sub>H</sub>  | hysteresis voltage        | An, B4 inputs                                                  |                        |      |     |                        |      |                        |      |      |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 0.9 V                    | -                      | 0.25 | -   | -                      | -    | -                      | -    | V    |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.1 V                    | -                      | 0.31 | -   | 0.2                    | 0.4  | 0.2                    | 0.4  | V    |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.4 V                    | -                      | 0.39 | -   | 0.25                   | 0.5  | 0.25                   | 0.5  | V    |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.65 V                   | -                      | 0.46 | -   | 0.3                    | 0.55 | 0.3                    | 0.55 | V    |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 2.3 V                    | -                      | 0.59 | -   | 0.38                   | 0.65 | 0.38                   | 0.65 | V    |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 3.0 V                    | -                      | 0.63 | -   | 0.46                   | 0.72 | 0.46                   | 0.72 | V    |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 4.5 V                    | -                      | 0.79 | -   | 0.58                   | 0.93 | 0.58                   | 0.93 | V    |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 5.5 V                    | -                      | 0.93 | -   | 0.69                   | 1.06 | 0.69                   | 1.06 | V    |
|                 |                           | OE input (referenced to V <sub>CCA</sub> or V <sub>CCB</sub> ) |                        |      |     |                        |      |                        |      |      |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 0.9 V                    | -                      | 0.25 | -   | -                      | -    | -                      | -    | V    |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.1 V                    | -                      | 0.30 | -   | 0.15                   | 0.41 | 0.15                   | 0.41 | V    |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.4 V                    | -                      | 0.39 | -   | 0.2                    | 0.5  | 0.2                    | 0.5  | V    |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 1.65 V                   | -                      | 0.44 | -   | 0.23                   | 0.55 | 0.23                   | 0.55 | V    |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 2.3 V                    | -                      | 0.54 | -   | 0.32                   | 0.65 | 0.32                   | 0.65 | V    |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 3.0 V                    | -                      | 0.62 | -   | 0.39                   | 0.72 | 0.39                   | 0.72 | V    |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 4.5 V                    | -                      | 0.81 | -   | 0.57                   | 0.97 | 0.57                   | 0.97 | V    |
|                 |                           | V <sub>CCA</sub> = V <sub>CCB</sub> = 5.5 V                    | -                      | 0.96 | -   | 0.69                   | 1.18 | 0.69                   | 1.18 | V    |
| V <sub>OH</sub> | HIGH-level output voltage | V <sub>I</sub> = V <sub>T+(MAX)</sub> [1][2]                   |                        |      |     |                        |      |                        |      |      |
|                 |                           | I <sub>O</sub> = -0.1 mA; V <sub>CCO</sub> = 0.9 V to 5.5 V    | V <sub>CCO</sub> - 0.1 | 0.9  | -   | V <sub>CCO</sub> - 0.1 | -    | V <sub>CCO</sub> - 0.1 | -    | V    |
|                 |                           | I <sub>O</sub> = -1.5 mA; V <sub>CCO</sub> = 1.1 V             | 0.825                  | 1.0  | -   | 0.825                  | -    | 0.825                  | -    | V    |
|                 |                           | I <sub>O</sub> = -3 mA; V <sub>CCO</sub> = 1.4 V               | 1.05                   | 1.2  | -   | 1.05                   | -    | 1.05                   | -    | V    |
|                 |                           | I <sub>O</sub> = -4.5 mA; V <sub>CCO</sub> = 1.65 V            | 1.2                    | 1.4  | -   | 1.2                    | -    | 1.2                    | -    | V    |
|                 |                           | I <sub>O</sub> = -8 mA; V <sub>CCO</sub> = 2.3 V               | 1.7                    | 1.94 | -   | 1.7                    | -    | 1.7                    | -    | V    |
|                 |                           | I <sub>O</sub> = -10 mA; V <sub>CCO</sub> = 3.0 V              | 2.2                    | 2.6  | -   | 2.2                    | -    | 2.2                    | -    | V    |
|                 |                           | I <sub>O</sub> = -12 mA; V <sub>CCO</sub> = 4.5 V              | 3.7                    | 4.1  | -   | 3.7                    | -    | 3.7                    | -    | V    |

## 4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

| Symbol           | Parameter                 | Conditions                                                                                                                                                                             | +25 °C |      |       | -40 °C to +85 °C |       | -40 °C to +125 °C |       | Unit |
|------------------|---------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|------|-------|------------------|-------|-------------------|-------|------|
|                  |                           |                                                                                                                                                                                        | Min    | Typ  | Max   | Min              | Max   | Min               | Max   |      |
| V <sub>OL</sub>  | LOW-level output voltage  | V <sub>I</sub> = V <sub>T-(MIN)</sub> [1][2]                                                                                                                                           |        |      |       |                  |       |                   |       |      |
|                  |                           | I <sub>O</sub> = 0.1 mA; V <sub>CCO</sub> = 0.9 V to 5.5 V                                                                                                                             | -      | 0    | 0.1   | -                | 0.1   | -                 | 0.1   | V    |
|                  |                           | I <sub>O</sub> = 1.5 mA; V <sub>CCO</sub> = 1.1 V                                                                                                                                      | -      | 0.12 | 0.275 | -                | 0.275 | -                 | 0.275 | V    |
|                  |                           | I <sub>O</sub> = 3 mA; V <sub>CCO</sub> = 1.4 V                                                                                                                                        | -      | 0.17 | 0.35  | -                | 0.35  | -                 | 0.35  | V    |
|                  |                           | I <sub>O</sub> = 4.5 mA; V <sub>CCO</sub> = 1.65 V                                                                                                                                     | -      | 0.23 | 0.45  | -                | 0.45  | -                 | 0.45  | V    |
|                  |                           | I <sub>O</sub> = 8 mA; V <sub>CCO</sub> = 2.3 V                                                                                                                                        | -      | 0.35 | 0.7   | -                | 0.7   | -                 | 0.7   | V    |
|                  |                           | I <sub>O</sub> = 10 mA; V <sub>CCO</sub> = 3.0 V                                                                                                                                       | -      | 0.39 | 0.8   | -                | 0.8   | -                 | 0.8   | V    |
|                  |                           | I <sub>O</sub> = 8 mA; V <sub>CCO</sub> = 4.5 V                                                                                                                                        | -      | 0.28 | 0.5   | -                | 0.5   | -                 | 0.5   | V    |
|                  |                           | I <sub>O</sub> = 12 mA; V <sub>CCO</sub> = 4.5 V                                                                                                                                       | -      | 0.43 | 0.8   | -                | 0.8   | -                 | 0.8   | V    |
| I <sub>I</sub>   | input leakage current     | An, B4 inputs; V <sub>I</sub> = 0 V to 5.5 V; V <sub>CCI</sub> = 0.9 V to 5.5 V [3]                                                                                                    | -0.1   | 1    | 1.5   | -0.1             | 1.85  | -0.1              | 2     | μA   |
|                  |                           | OE input; V <sub>I</sub> = 0 V to 5.5 V; V <sub>CCI</sub> = 0.9 V to 5.5 V [3]                                                                                                         | -0.1   | 1    | 1.5   | -0.1             | 1.85  | -0.1              | 2     | μA   |
| I <sub>OZ</sub>  | OFF-state output current  | suspend mode YBn, YA4 output; V <sub>CCA</sub> = V <sub>CCB</sub> = 0.9 V to 5.5 V; V <sub>I</sub> = 0 V or V <sub>CCI</sub> ; V <sub>O</sub> = 0 V or V <sub>CCO</sub> ; OE = GND [1] | -0.1   | -    | 0.1   | -0.5             | 0.5   | -2                | 2     | μA   |
| I <sub>OFF</sub> | power-off leakage current | YBn, YA4 output; V <sub>I</sub> or V <sub>O</sub> = 0 V to 5.5 V; V <sub>CCA</sub> = 0 V; V <sub>CCB</sub> = 0.9 V to 5.5 V                                                            | -1.5   | -    | 1.5   | -1.85            | 1.85  | -2                | 2     | μA   |
|                  |                           | YBn, YA4 output; V <sub>I</sub> or V <sub>O</sub> = 0 V to 5.5 V; V <sub>CCB</sub> = 0 V; V <sub>CCA</sub> = 0.9 V to 5.5 V                                                            | -1.5   | -    | 1.5   | -1.85            | 1.85  | -2                | 2     | μA   |
|                  |                           | YBn, YA4 output; V <sub>I</sub> or V <sub>O</sub> = GND; V <sub>CCA</sub> = floating; V <sub>CCB</sub> = 0.9 V to 5.5 V [4]                                                            | -1.5   | -    | 1.5   | -1.85            | 1.85  | -2                | 2     | μA   |
|                  |                           | YBn, YA4 output; V <sub>I</sub> or V <sub>O</sub> = GND; V <sub>CCB</sub> = floating; V <sub>CCA</sub> = 0.9 V to 5.5 V [4]                                                            | -1.5   | -    | 1.5   | -1.85            | 1.85  | -2                | 2     | μA   |

4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

| Symbol          | Parameter      | Conditions                                                                                                                                                              | +25 °C |     |     | -40 °C to +85 °C |     | -40 °C to +125 °C |     | Unit |
|-----------------|----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|-----|-----|------------------|-----|-------------------|-----|------|
|                 |                |                                                                                                                                                                         | Min    | Typ | Max | Min              | Max | Min               | Max |      |
| I <sub>CC</sub> | supply current | I <sub>CCA</sub> ; V <sub>I</sub> = 0 V or V <sub>CCI</sub> ; I <sub>O</sub> = 0 A [3]                                                                                  |        |     |     |                  |     |                   |     |      |
|                 |                | V <sub>CCA</sub> , V <sub>CCB</sub> = 0.9 V to 5.5 V                                                                                                                    | -      | 1   | 1.8 | -                | 2.5 | -                 | 3   | µA   |
|                 |                | V <sub>CCA</sub> = 5.5 V; V <sub>CCB</sub> = 0 V                                                                                                                        | -      | 1   | 1.8 | -                | 2.5 | -                 | 3   | µA   |
|                 |                | V <sub>CCA</sub> = 0 V; V <sub>CCB</sub> = 5.5 V                                                                                                                        | -0.1   | -   | 0.1 | -0.4             | 0.4 | -1                | 1   | µA   |
|                 |                | I <sub>CCB</sub> ; V <sub>I</sub> = 0 V or V <sub>CCI</sub> ; I <sub>O</sub> = 0 A [3]                                                                                  |        |     |     |                  |     |                   |     |      |
|                 |                | V <sub>CCA</sub> , V <sub>CCB</sub> = 0.9 V to 5.5 V                                                                                                                    | -      | 1   | 1.8 | -                | 2.5 | -                 | 3   | µA   |
|                 |                | V <sub>CCB</sub> = 5.5 V; V <sub>CCA</sub> = 0 V                                                                                                                        | -      | 1   | 1.8 | -                | 2.5 | -                 | 3   | µA   |
|                 |                | V <sub>CCB</sub> = 0 V; V <sub>CCA</sub> = 5.5 V                                                                                                                        | -0.1   | -   | 0.1 | -0.4             | 0.4 | -1                | 1   | µA   |
|                 |                | I <sub>CCA</sub> or I <sub>CCB</sub> ; V <sub>I</sub> or V <sub>O</sub> = GND; I <sub>O</sub> = 0 A                                                                     |        |     |     |                  |     |                   |     |      |
|                 |                | I <sub>CCA</sub> ; V <sub>CCB</sub> = floating; V <sub>CCA</sub> = 5.5 V [4]                                                                                            | -      | 1   | 1.5 | -                | 2.5 | -                 | 3   | µA   |
|                 |                | I <sub>CCB</sub> ; V <sub>CCA</sub> = floating; V <sub>CCB</sub> = 5.5 V [4]                                                                                            | -      | 1   | 1.5 | -                | 2.5 | -                 | 3   | µA   |
|                 |                | I <sub>CCA</sub> + I <sub>CCB</sub> combined; V <sub>I</sub> = 0 V or V <sub>CCI</sub> ; I <sub>O</sub> = 0 A; V <sub>CCA</sub> = V <sub>CCB</sub> = 0.9 V to 5.5 V [3] | -      | 2   | 3   | -                | 4.5 | -                 | 5   | µA   |

[1] V<sub>CCO</sub> is the supply voltage associated with the outputs (YBn, YA4).  
[2] Typical values for V<sub>OL</sub> and V<sub>OH</sub> are measured at V<sub>CCO</sub> is 0.9 V.  
[3] V<sub>CCI</sub> is the supply voltage associated with the inputs (An, B4).  
[4] Floating is defined, if one of the supply pins is not actively driven externally and has a leakage not exceeding 10 nA

4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

Table 10. Typical total supply current  $I_{CCA}$  at  $T_{amb} = 25\text{ }^{\circ}\text{C}$   
Voltages are referenced to GND (ground = 0 V).

| V <sub>CCA</sub> | V <sub>CCB</sub> |       |       |       |       |       |       |       | Unit |
|------------------|------------------|-------|-------|-------|-------|-------|-------|-------|------|
|                  | 0 V              | 0.9 V | 1.2 V | 1.5 V | 1.8 V | 2.5 V | 3.3 V | 5.0 V |      |
| 0 V              | 0.00             | 0.01  | 0.01  | 0.01  | 0.01  | 0.01  | 0.01  | 0.01  | μA   |
| 0.9 V            | 0.2              | 0.2   | 0.2   | 0.2   | 0.2   | 0.2   | 0.2   | 0.2   | μA   |
| 1.2 V            | 0.3              | 0.3   | 0.3   | 0.3   | 0.3   | 0.3   | 0.3   | 0.3   | μA   |
| 1.5 V            | 0.4              | 0.4   | 0.4   | 0.4   | 0.4   | 0.4   | 0.4   | 0.4   | μA   |
| 1.8 V            | 0.4              | 0.4   | 0.4   | 0.4   | 0.4   | 0.4   | 0.4   | 0.4   | μA   |
| 2.5 V            | 0.4              | 0.4   | 0.4   | 0.4   | 0.4   | 0.4   | 0.4   | 0.4   | μA   |
| 3.3 V            | 0.5              | 0.5   | 0.5   | 0.5   | 0.5   | 0.5   | 0.5   | 0.5   | μA   |
| 5.0 V            | 0.9              | 0.9   | 0.9   | 0.9   | 0.9   | 0.9   | 0.9   | 0.9   | μA   |

Table 11. Typical total supply current  $I_{CCB}$  at  $T_{amb} = 25\text{ }^{\circ}\text{C}$   
Voltages are referenced to GND (ground = 0 V).

| V <sub>CCA</sub> | V <sub>CCB</sub> |       |       |       |       |       |       |       | Unit |
|------------------|------------------|-------|-------|-------|-------|-------|-------|-------|------|
|                  | 0 V              | 0.9 V | 1.2 V | 1.5 V | 1.8 V | 2.5 V | 3.3 V | 5.0 V |      |
| 0 V              | 0.00             | 0.01  | 0.01  | 0.01  | 0.01  | 0.01  | 0.01  | 0.01  | μA   |
| 0.9 V            | 0.01             | 0.2   | 0.25  | 0.3   | 0.4   | 0.45  | 0.5   | 0.7   | μA   |
| 1.2 V            | 0.01             | 0.2   | 0.25  | 0.3   | 0.4   | 0.45  | 0.5   | 0.7   | μA   |
| 1.5 V            | 0.01             | 0.2   | 0.25  | 0.3   | 0.4   | 0.45  | 0.5   | 0.7   | μA   |
| 1.8 V            | 0.01             | 0.2   | 0.25  | 0.3   | 0.4   | 0.45  | 0.5   | 0.7   | μA   |
| 2.5 V            | 0.01             | 0.2   | 0.25  | 0.3   | 0.4   | 0.45  | 0.5   | 0.7   | μA   |
| 3.3 V            | 0.01             | 0.2   | 0.25  | 0.3   | 0.4   | 0.45  | 0.5   | 0.7   | μA   |
| 5.0 V            | 0.01             | 0.2   | 0.25  | 0.3   | 0.4   | 0.45  | 0.5   | 0.9   | μA   |

14. Dynamic characteristics

Table 12. Maximum data rate and output skew  
Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 12.

| Symbol             | Parameter        | Conditions                                                                                                                 | T <sub>amb</sub> = -40 °C to +125 °C |      |     | Unit |
|--------------------|------------------|----------------------------------------------------------------------------------------------------------------------------|--------------------------------------|------|-----|------|
|                    |                  |                                                                                                                            | Min                                  | Typ  | Max |      |
| f <sub>data</sub>  | data rate        | 50% duty cycle input; one channel switching; 20% of pulse > 0.7xV <sub>CCO</sub> ; 20% of pulse < 0.3xV <sub>CCO</sub> [1] |                                      |      |     |      |
|                    |                  | Up translation [1][2]                                                                                                      |                                      |      |     |      |
|                    |                  | V <sub>CCI</sub> = 3.0 V to 3.6 V; V <sub>CCO</sub> = 4.5 V to 5.5 V                                                       | -                                    | 350  | 250 | Mbps |
|                    |                  | V <sub>CCI</sub> = 1.65 V to 1.95 V; V <sub>CCO</sub> = 4.5 V to 5.5 V                                                     | -                                    | 350  | 250 | Mbps |
|                    |                  | V <sub>CCI</sub> = 1.1 V to 1.3 V; V <sub>CCO</sub> = 4.5 V to 5.5 V                                                       | -                                    | 220  | 100 | Mbps |
|                    |                  | V <sub>CCI</sub> = 1.65 V to 1.95 V; V <sub>CCO</sub> = 3.0 V to 3.6 V                                                     | -                                    | 230  | 150 | Mbps |
|                    |                  | V <sub>CCI</sub> = 1.1 V to 1.3 V; V <sub>CCO</sub> = 3.0 V to 3.6 V                                                       | -                                    | 300  | 140 | Mbps |
|                    |                  | V <sub>CCI</sub> = 1.1 V to 1.3 V; V <sub>CCO</sub> = 1.65 V to 1.95 V                                                     | -                                    | 100  | 40  | Mbps |
|                    |                  | Down translation [1][2]                                                                                                    |                                      |      |     |      |
|                    |                  | V <sub>CCI</sub> = 4.5 V to 5.5 V; V <sub>CCO</sub> = 3.0 V to 3.6 V                                                       | -                                    | 250  | 170 | Mbps |
|                    |                  | V <sub>CCI</sub> = 4.5 V to 5.5 V; V <sub>CCO</sub> = 1.65 V to 1.95 V                                                     | -                                    | 150  | 60  | Mbps |
|                    |                  | V <sub>CCI</sub> = 4.5 V to 5.5 V; V <sub>CCO</sub> = 1.1 V to 1.3 V                                                       | -                                    | 80   | 30  | Mbps |
|                    |                  | V <sub>CCI</sub> = 3.0 V to 3.6 V; V <sub>CCO</sub> = 1.65 V to 1.95 V                                                     | -                                    | 150  | 60  | Mbps |
|                    |                  | V <sub>CCI</sub> = 3.0 V to 3.6 V; V <sub>CCO</sub> = 1.1 V to 1.3 V                                                       | -                                    | 80   | 30  | Mbps |
|                    |                  | V <sub>CCI</sub> = 1.65 V to 1.95 V; V <sub>CCO</sub> = 1.1 V to 1.3 V                                                     | -                                    | 70   | 30  | Mbps |
| t <sub>sk(o)</sub> | output skew time | Timing skew between any switching outputs on the rising or falling edge                                                    |                                      |      |     |      |
|                    |                  | Up translation [1][2]                                                                                                      |                                      |      |     |      |
|                    |                  | V <sub>CCI</sub> = 3.0 V to 3.6 V; V <sub>CCO</sub> = 4.5 V to 5.5 V                                                       | -                                    | 0.15 | 0.7 | ns   |
|                    |                  | V <sub>CCI</sub> = 1.65 V to 1.95 V; V <sub>CCO</sub> = 4.5 V to 5.5 V                                                     | -                                    | 0.25 | 1   | ns   |
|                    |                  | V <sub>CCI</sub> = 1.1 V to 1.3 V; V <sub>CCO</sub> = 4.5 V to 5.5 V                                                       | -                                    | 0.5  | 2.1 | ns   |
|                    |                  | V <sub>CCI</sub> = 1.65 V to 1.95 V; V <sub>CCO</sub> = 3.0 V to 3.6 V                                                     | -                                    | 0.25 | 1   | ns   |
|                    |                  | V <sub>CCI</sub> = 1.1 V to 1.3 V; V <sub>CCO</sub> = 3.0 V to 3.6 V                                                       | -                                    | 0.5  | 2.1 | ns   |
|                    |                  | V <sub>CCI</sub> = 1.1 V to 1.3 V; V <sub>CCO</sub> = 1.65 V to 1.95 V                                                     | -                                    | 0.5  | 2.1 | ns   |
|                    |                  | Down translation [1][2]                                                                                                    |                                      |      |     |      |
|                    |                  | V <sub>CCI</sub> = 4.5 V to 5.5 V; V <sub>CCO</sub> = 3.0 V to 3.6 V                                                       | -                                    | 0.15 | 0.8 | ns   |
|                    |                  | V <sub>CCI</sub> = 4.5 V to 5.5 V; V <sub>CCO</sub> = 1.65 V to 1.95 V                                                     | -                                    | 0.25 | 1.1 | ns   |
|                    |                  | V <sub>CCI</sub> = 4.5 V to 5.5 V; V <sub>CCO</sub> = 1.1 V to 1.3 V                                                       | -                                    | 0.6  | 2.5 | ns   |
|                    |                  | V <sub>CCI</sub> = 3.0 V to 3.6 V; V <sub>CCO</sub> = 1.65 V to 1.95 V                                                     | -                                    | 0.25 | 2.5 | ns   |
|                    |                  | V <sub>CCI</sub> = 3.0 V to 3.6 V; V <sub>CCO</sub> = 1.1 V to 1.3 V                                                       | -                                    | 0.6  | 2.5 | ns   |
|                    |                  | V <sub>CCI</sub> = 1.65 V to 1.95 V; V <sub>CCO</sub> = 1.1 V to 1.3 V                                                     | -                                    | 0.6  | 2.5 | ns   |

[1] V<sub>CCO</sub> is the supply voltage associated with the outputs (YBn, YA4).  
[2] V<sub>CCI</sub> is the supply voltage associated with the inputs (An, B4).

4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

Table 13. Typical dynamic characteristics at  $V_{CCA} = 0.9\text{ V}$  and  $T_{amb} = 25\text{ }^{\circ}\text{C}$

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 12; for waveforms see Fig. 9, Fig. 11 and Fig. 10.

| Symbol    | Parameter         | Conditions    | $V_{CCB}$ |       |       |       |       |       |       | Unit |
|-----------|-------------------|---------------|-----------|-------|-------|-------|-------|-------|-------|------|
|           |                   |               | 0.9 V     | 1.2 V | 1.5 V | 1.8 V | 2.5 V | 3.3 V | 5.0 V |      |
| $t_{pd}$  | propagation delay | An to YBn [1] | 61        | 44    | 41    | 39.5  | 38.5  | 38.5  | 39.4  | ns   |
|           |                   | B4 to YA4 [1] | 55.4      | 34.1  | 29.8  | 28.1  | 27.1  | 26.5  | 27.5  | ns   |
| $t_{dis}$ | disable time      | OE to YA4 [1] | 65        | 67    | 68    | 70    | 74    | 79    | 92    | ns   |
|           |                   | OE to YBn [1] | 67        | 51    | 47    | 47    | 44    | 44    | 42    | ns   |
| $t_{en}$  | enable time       | OE to YA4 [1] | 70        | 58    | 58    | 58    | 58    | 58.2  | 58.2  | ns   |
|           |                   | OE to YBn [1] | 67        | 51    | 47    | 47    | 44    | 44    | 42    | ns   |

[1]  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ ;  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ ;  $t_{en}$  is the same as  $t_{PZL}$  and  $t_{PZH}$ .

Table 14. Typical dynamic characteristics at  $V_{CCB} = 0.9\text{ V}$  and  $T_{amb} = 25\text{ }^{\circ}\text{C}$

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 12; for waveforms see Fig. 9, Fig. 11 and Fig. 10.

| Symbol    | Parameter         | Conditions    | $V_{CCA}$ |       |       |       |       |       |       | Unit |
|-----------|-------------------|---------------|-----------|-------|-------|-------|-------|-------|-------|------|
|           |                   |               | 0.9 V     | 1.2 V | 1.5 V | 1.8 V | 2.5 V | 3.3 V | 5.0 V |      |
| $t_{pd}$  | propagation delay | An to YBn [1] | 61        | 44    | 41    | 39.5  | 38.5  | 38.5  | 39.4  | ns   |
|           |                   | B4 to YA4 [1] | 54.5      | 43.7  | 40.3  | 39.2  | 38.5  | 38.6  | 39.5  | ns   |
| $t_{dis}$ | disable time      | OE to A4 [1]  | 65        | 51    | 47    | 47    | 44    | 45    | 44    | ns   |
|           |                   | OE to YBn [1] | 67        | 68    | 70    | 72    | 76    | 81    | 94    | ns   |
| $t_{en}$  | enable time       | OE to YA4 [1] | 60        | 52    | 52    | 52    | 52    | 50    | 70    | ns   |
|           |                   | OE to YBn [1] | 70        | 60    | 52    | 52    | 52    | 50    | 50    | ns   |

[1]  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ ;  $t_{dis}$  is the same as  $t_{PLZ}$  and  $t_{PHZ}$ ;  $t_{en}$  is the same as  $t_{PZL}$  and  $t_{PZH}$ .

## 4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

Table 15. Typical dynamic characteristics at  $T_{amb} = 25\text{ }^{\circ}\text{C}$ 

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 12.

| Symbol   | Parameter                     | Conditions                                                                                                                                                     | Supply voltage ( $V_{CCA} = V_{CCB}$ ) |       |       |       |       |       |       | Unit |
|----------|-------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------|-------|-------|-------|-------|-------|-------|------|
|          |                               |                                                                                                                                                                | 0.9 V                                  | 1.2 V | 1.5 V | 1.8 V | 2.5 V | 3.3 V | 5.0 V |      |
| $C_{PD}$ | power dissipation capacitance | $V_{CCA}$ [1][2][3]<br>$f_i = 10\text{ MHz}$ ; $V_i = \text{GND to } V_{CCI}$ ; $t_r = t_f = 1\text{ ns}$ ; $C_L = 0\text{ pF}$ ; $R_L = \infty\text{ }\Omega$ |                                        |       |       |       |       |       |       |      |
|          |                               | An to YBn; outputs disabled                                                                                                                                    | 1.5                                    | 1.6   | 1.7   | 1.7   | 1.9   | 2.1   | 2.7   | pF   |
|          |                               | B4 to YA4; outputs disabled                                                                                                                                    | 1.5                                    | 1.6   | 1.7   | 1.7   | 1.9   | 2.1   | 2.7   | pF   |
|          |                               | An to YBn; outputs enabled                                                                                                                                     | 1.5                                    | 1.6   | 1.7   | 1.7   | 1.9   | 2.1   | 2.7   | pF   |
|          |                               | B4 to YA4; outputs enabled                                                                                                                                     | 10                                     | 10.4  | 10.6  | 10.7  | 10.9  | 11.3  | 12.1  | pF   |
|          |                               | $V_{CCB}$ [1][2][3]<br>$f_i = 10\text{ MHz}$ ; $V_i = \text{GND to } V_{CCI}$ ; $t_r = t_f = 1\text{ ns}$ ; $C_L = 0\text{ pF}$ ; $R_L = \infty\text{ }\Omega$ |                                        |       |       |       |       |       |       |      |
|          |                               | An to YBn; outputs disabled                                                                                                                                    | 1.5                                    | 1.6   | 1.7   | 1.7   | 1.9   | 2.1   | 2.7   | pF   |
|          |                               | B4 to YA4; outputs disabled                                                                                                                                    | 1.5                                    | 1.6   | 1.7   | 1.7   | 1.9   | 2.1   | 2.7   | pF   |
|          |                               | An to YBn; outputs enabled                                                                                                                                     | 10                                     | 10.4  | 10.6  | 10.7  | 10.9  | 11.3  | 12.1  | pF   |
|          |                               | B4 to YA4; outputs enabled                                                                                                                                     | 1.5                                    | 1.6   | 1.7   | 1.7   | 1.9   | 2.1   | 2.7   | pF   |
| $C_i$    | input capacitance             | $V_i = 0\text{ V or } V_{CCI}$ [2]                                                                                                                             | 1.9                                    | 1.9   | 1.9   | 1.9   | 1.9   | 1.9   | 1.9   | pF   |
| $C_o$    | output capacitance            | $OE = \text{GND}$ ; $V_{CCA} = 3.3\text{ V}$ ;<br>$V_{CCB} = 3.3\text{ V}$ ; $V_o = 0\text{ V or } V_{CCI}$                                                    | 3.2                                    | 3.2   | 3.2   | 3.2   | 3.2   | 3.2   | 3.2   | pF   |

[1]  $C_{PD}$  per channel is used to determine the dynamic power dissipation ( $P_{DYN}$  in  $\mu\text{W}$ ). $P_{DYN} = N \times (C_{PD} \times V_{CCI}^2 \times f_i) + N \times (C_L \times V_{CCO}^2 \times f_o)$  where: $f_i$  = input frequency in MHz; $f_o$  = output frequency in MHz; $C_L$  = load capacitance in pF; $V_{CCI}$  = the supply voltage associated with the input pins in V; $V_{CCO}$  = the supply voltage associated with the output pins in V; $N$  = total number of inputs or outputs switching.[2]  $V_{CCI}$  is the supply voltage associated with the inputs (An, B4).[3]  $V_{CCO}$  is the supply voltage associated with the outputs (YBn, YA4).

4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

Table 16. Dynamic characteristics for temperature range -40 °C to +85 °C  
Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 12; for waveforms see Fig. 9, Fig. 11 and Fig. 10.

| Symbol          | Parameter         | Conditions                        | V <sub>CCB</sub> |      |               |      |                |      |               |      |               |      |               |      | Unit |
|-----------------|-------------------|-----------------------------------|------------------|------|---------------|------|----------------|------|---------------|------|---------------|------|---------------|------|------|
|                 |                   |                                   | 1.2 V ± 0.1 V    |      | 1.5 V ± 0.1 V |      | 1.8 V ± 0.15 V |      | 2.5 V ± 0.2 V |      | 3.3 V ± 0.3 V |      | 5.0 V ± 0.5 V |      |      |
|                 |                   |                                   | Min              | Max  | Min           | Max  | Min            | Max  | Min           | Max  | Min           | Max  | Min           | Max  |      |
| t <sub>pd</sub> | propagation delay | An to YBn [1]                     |                  |      |               |      |                |      |               |      |               |      |               |      |      |
|                 |                   | V <sub>CCA</sub> = 1.2 V ± 0.1 V  | 6.0              | 42.1 | 5.3           | 30.1 | 5.0            | 26.5 | 4.7           | 22.8 | 4.7           | 21.5 | 4.7           | 21.9 | ns   |
|                 |                   | V <sub>CCA</sub> = 1.5 V ± 0.1 V  | 5.3              | 33.4 | 4.6           | 21.4 | 4.2            | 18.1 | 3.8           | 14.6 | 3.8           | 13.3 | 3.8           | 12.7 | ns   |
|                 |                   | V <sub>CCA</sub> = 1.8 V ± 0.15 V | 5.0              | 31.3 | 4.3           | 19.2 | 3.5            | 15.6 | 3.4           | 12.4 | 3.4           | 11.2 | 3.4           | 10.1 | ns   |
|                 |                   | V <sub>CCA</sub> = 2.5 V ± 0.2 V  | 4.6              | 29.5 | 3.7           | 17.3 | 3.4            | 13.6 | 3.0           | 10.1 | 2.9           | 8.8  | 2.9           | 7.7  | ns   |
|                 |                   | V <sub>CCA</sub> = 3.3 V ± 0.3 V  | 4.6              | 29.1 | 3.8           | 16.6 | 3.5            | 12.9 | 3.1           | 9.4  | 2.9           | 7.9  | 2.8           | 6.8  | ns   |
|                 |                   | V <sub>CCA</sub> = 5.0 V ± 0.5 V  | 4.8              | 29.6 | 4.1           | 16.3 | 3.7            | 12.5 | 3.2           | 8.7  | 2.9           | 7.3  | 2.6           | 6.1  | ns   |
|                 |                   | B4 to YA4                         |                  |      |               |      |                |      |               |      |               |      |               |      |      |
|                 |                   | V <sub>CCA</sub> = 1.2 V ± 0.1 V  | 6.7              | 42.1 | 5.9           | 34.4 | 5.5            | 32.3 | 5.1           | 30.4 | 5.1           | 29.8 | 5.1           | 30.3 | ns   |
|                 |                   | V <sub>CCA</sub> = 1.5 V ± 0.1 V  | 6.1              | 30.6 | 5.2           | 22.5 | 4.5            | 20.3 | 4.1           | 18.2 | 4.1           | 17.4 | 4.1           | 17.1 | ns   |
|                 |                   | V <sub>CCA</sub> = 1.8 V ± 0.15 V | 5.7              | 27.4 | 4.7           | 19.1 | 4.0            | 16.4 | 3.5           | 14.1 | 3.5           | 13.3 | 3.5           | 12.8 | ns   |
|                 |                   | V <sub>CCA</sub> = 2.5 V ± 0.2 V  | 5.4              | 23.7 | 4.4           | 15.3 | 3.6            | 12.7 | 3.2           | 10.3 | 3.2           | 9.6  | 3.3           | 8.9  | ns   |
|                 |                   | V <sub>CCA</sub> = 3.3 V ± 0.3 V  | 5.3              | 22.3 | 4.3           | 13.9 | 3.5            | 11.3 | 3.0           | 9.1  | 3.1           | 8.1  | 3.1           | 7.4  | ns   |
|                 |                   | V <sub>CCA</sub> = 5.0 V ± 0.5 V  | 5.1              | 22.7 | 4.1           | 13.3 | 3.5            | 10.4 | 3.0           | 7.9  | 2.8           | 6.9  | 2.7           | 6.2  | ns   |

4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

| Symbol          | Parameter   | Conditions                        | V <sub>CCB</sub> |      |               |      |                |      |               |      |               |      |               |      | Unit |
|-----------------|-------------|-----------------------------------|------------------|------|---------------|------|----------------|------|---------------|------|---------------|------|---------------|------|------|
|                 |             |                                   | 1.2 V ± 0.1 V    |      | 1.5 V ± 0.1 V |      | 1.8 V ± 0.15 V |      | 2.5 V ± 0.2 V |      | 3.3 V ± 0.3 V |      | 5.0 V ± 0.5 V |      |      |
|                 |             |                                   | Min              | Max  | Min           | Max  | Min            | Max  | Min           | Max  | Min           | Max  | Min           | Max  |      |
| t <sub>en</sub> | enable time | OE to YBn [1]                     |                  |      |               |      |                |      |               |      |               |      |               |      |      |
|                 |             | V <sub>CCA</sub> = 1.2 V ± 0.1 V  | 8.5              | 42.8 | 7.7           | 31.8 | 7.4            | 28.5 | 7.2           | 25.5 | 7.2           | 24.6 | 7.2           | 24.2 | ns   |
|                 |             | V <sub>CCA</sub> = 1.5 V ± 0.1 V  | 7.9              | 39.4 | 6.4           | 23.1 | 5.8            | 19.8 | 5.6           | 16.7 | 5.6           | 15.7 | 5.6           | 15.2 | ns   |
|                 |             | V <sub>CCA</sub> = 1.8 V ± 0.15 V | 7.5              | 38.5 | 6.1           | 22.2 | 5.2            | 17.2 | 4.7           | 13.7 | 4.6           | 12.5 | 4.6           | 11.8 | ns   |
|                 |             | V <sub>CCA</sub> = 2.5 V ± 0.2 V  | 7.1              | 37.5 | 5.3           | 21.3 | 4.4            | 16.1 | 3.9           | 10.7 | 3.7           | 9.5  | 3.7           | 8.6  | ns   |
|                 |             | V <sub>CCA</sub> = 3.3 V ± 0.3 V  | 6.6              | 37.1 | 5.1           | 20.8 | 4.1            | 15.5 | 3.4           | 10.1 | 3.3           | 8.2  | 3.2           | 7.3  | ns   |
|                 |             | V <sub>CCA</sub> = 5.0 V ± 0.5 V  | 6.2              | 36.5 | 4.5           | 20.2 | 3.6            | 15.1 | 2.9           | 9.4  | 2.6           | 7.4  | 2.6           | 6.2  | ns   |
|                 |             | OE to YA4                         |                  |      |               |      |                |      |               |      |               |      |               |      |      |
|                 |             | V <sub>CCA</sub> = 1.2 V ± 0.1 V  | 8.5              | 42.8 | 8.7           | 42.7 | 8.7            | 42.7 | 8.7           | 42.7 | 8.5           | 42.7 | 8.5           | 42.7 | ns   |
|                 |             | V <sub>CCA</sub> = 1.5 V ± 0.1 V  | 7.4              | 38.6 | 6.4           | 28.2 | 6.5            | 28.2 | 6.5           | 28.2 | 6.4           | 28.2 | 6.4           | 28.2 | ns   |
|                 |             | V <sub>CCA</sub> = 1.8 V ± 0.15 V | 6.5              | 33.3 | 5.6           | 23.8 | 5.2            | 23.8 | 5.2           | 23.8 | 5.2           | 23.8 | 5.2           | 23.8 | ns   |
|                 |             | V <sub>CCA</sub> = 2.5 V ± 0.2 V  | 5.6              | 28.6 | 4.7           | 19.6 | 4.3            | 17.7 | 4.1           | 15.8 | 4.1           | 15.8 | 3.4           | 15.8 | ns   |
|                 |             | V <sub>CCA</sub> = 3.3 V ± 0.3 V  | 5.2              | 27.8 | 4.2           | 18.2 | 3.7            | 16.1 | 3.4           | 9.2  | 3.4           | 8.3  | 3.0           | 8.3  | ns   |
|                 |             | V <sub>CCA</sub> = 5.0 V ± 0.5 V  | 4.8              | 25.7 | 3.8           | 16.0 | 3.3            | 9.7  | 2.8           | 7.4  | 2.7           | 6.6  | 2.7           | 6.2  | ns   |

4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

| Symbol           | Parameter    | Conditions                        | V <sub>CCB</sub> |      |               |      |                |      |               |      |               |      |               |      | Unit |
|------------------|--------------|-----------------------------------|------------------|------|---------------|------|----------------|------|---------------|------|---------------|------|---------------|------|------|
|                  |              |                                   | 1.2 V ± 0.1 V    |      | 1.5 V ± 0.1 V |      | 1.8 V ± 0.15 V |      | 2.5 V ± 0.2 V |      | 3.3 V ± 0.3 V |      | 5.0 V ± 0.5 V |      |      |
|                  |              |                                   | Min              | Max  | Min           | Max  | Min            | Max  | Min           | Max  | Min           | Max  | Min           | Max  |      |
| t <sub>dis</sub> | disable time | OE to YBn [1]                     |                  |      |               |      |                |      |               |      |               |      |               |      |      |
|                  |              | V <sub>CCA</sub> = 1.2 V ± 0.1 V  | 11.7             | 44.1 | 10.9          | 37.2 | 11.5           | 36.2 | 10.6          | 32.9 | 10.8          | 33.7 | 9.9           | 32.2 | ns   |
|                  |              | V <sub>CCA</sub> = 1.5 V ± 0.1 V  | 11.6             | 44.2 | 8.5           | 26.4 | 8.9            | 25.1 | 7.4           | 21.6 | 7.4           | 22.1 | 7.4           | 20.2 | ns   |
|                  |              | V <sub>CCA</sub> = 1.8 V ± 0.15 V | 11.6             | 44.4 | 8.4           | 26.3 | 6.9            | 21.3 | 5.3           | 18.1 | 5.3           | 18.4 | 6.3           | 16.3 | ns   |
|                  |              | V <sub>CCA</sub> = 2.5 V ± 0.2 V  | 11.6             | 44.9 | 8.3           | 26.4 | 7.1            | 21.3 | 4.7           | 17.9 | 6.0           | 15.3 | 4.6           | 13.7 | ns   |
|                  |              | V <sub>CCA</sub> = 3.3 V ± 0.3 V  | 11.3             | 45.6 | 8.2           | 26.6 | 6.7            | 21.4 | 4.1           | 15.1 | 4.9           | 14.6 | 4.1           | 12.2 | ns   |
|                  |              | V <sub>CCA</sub> = 5.0 V ± 0.5 V  | 11.3             | 47.1 | 8.4           | 27.2 | 6.4            | 24.6 | 3.4           | 16.7 | 4.9           | 17.1 | 3.1           | 12.7 | ns   |
|                  |              | OE to YA4                         |                  |      |               |      |                |      |               |      |               |      |               |      |      |
|                  |              | V <sub>CCA</sub> = 1.2 V ± 0.1 V  | 11.6             | 58.7 | 11.6          | 58.7 | 11.6           | 58.7 | 11.6          | 58.7 | 11.6          | 58.7 | 11.6          | 58.7 | ns   |
|                  |              | V <sub>CCA</sub> = 1.5 V ± 0.1 V  | 10.8             | 50.5 | 8.5           | 39.4 | 8.5            | 39.4 | 8.5           | 39.4 | 8.7           | 39.4 | 8.7           | 39.4 | ns   |
|                  |              | V <sub>CCA</sub> = 1.8 V ± 0.15 V | 7.5              | 49.5 | 7.5           | 37.9 | 7.5            | 34.3 | 5.0           | 34.3 | 5.0           | 34.3 | 4.0           | 27.0 | ns   |
|                  |              | V <sub>CCA</sub> = 2.5 V ± 0.2 V  | 7.5              | 44.5 | 7.5           | 32.5 | 5.0            | 28.9 | 5.0           | 25.1 | 5.0           | 16.1 | 2.6           | 19.5 | ns   |
|                  |              | V <sub>CCA</sub> = 3.3 V ± 0.3 V  | 7.5              | 39.6 | 7.5           | 27.2 | 5.0            | 22.4 | 5.0           | 15.0 | 5.0           | 14.9 | 4.7           | 18.1 | ns   |
|                  |              | V <sub>CCA</sub> = 5.0 V ± 0.5 V  | 7.5              | 33.7 | 7.5           | 20.4 | 4.9            | 16.5 | 4.9           | 12.3 | 4.9           | 11.9 | 3.6           | 12.3 | ns   |

[1] t<sub>pd</sub> is the same as t<sub>PLH</sub> and t<sub>PHL</sub>; t<sub>dis</sub> is the same as t<sub>PLZ</sub> and t<sub>PHZ</sub>; t<sub>en</sub> is the same as t<sub>PZL</sub> and t<sub>PZH</sub>.

4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

Table 17. Dynamic characteristics for temperature range -40 °C to +125 °C  
Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 12; for waveforms see Fig. 9, Fig. 11 and Fig. 10.

| Symbol          | Parameter         | Conditions                        | V <sub>CCB</sub> |      |               |      |                |      |               |      |               |      |               |      | Unit |
|-----------------|-------------------|-----------------------------------|------------------|------|---------------|------|----------------|------|---------------|------|---------------|------|---------------|------|------|
|                 |                   |                                   | 1.2 V ± 0.1 V    |      | 1.5 V ± 0.1 V |      | 1.8 V ± 0.15 V |      | 2.5 V ± 0.2 V |      | 3.3 V ± 0.3 V |      | 5.0 V ± 0.5 V |      |      |
|                 |                   |                                   | Min              | Max  | Min           | Max  | Min            | Max  | Min           | Max  | Min           | Max  | Min           | Max  |      |
| t <sub>pd</sub> | propagation delay | An to YBn [1]                     |                  |      |               |      |                |      |               |      |               |      |               |      |      |
|                 |                   | V <sub>CCA</sub> = 1.2 V ± 0.1 V  | 6.0              | 42.1 | 5.3           | 31.1 | 5.0            | 27.4 | 4.7           | 23.6 | 4.7           | 22.2 | 4.7           | 22.3 | ns   |
|                 |                   | V <sub>CCA</sub> = 1.5 V ± 0.1 V  | 5.3              | 34.1 | 4.6           | 22.6 | 4.2            | 19.2 | 3.8           | 15.7 | 3.8           | 14.2 | 3.8           | 13.4 | ns   |
|                 |                   | V <sub>CCA</sub> = 1.8 V ± 0.15 V | 5.0              | 31.8 | 4.3           | 20.4 | 3.5            | 16.6 | 3.4           | 13.3 | 3.4           | 12.1 | 3.4           | 10.7 | ns   |
|                 |                   | V <sub>CCA</sub> = 2.5 V ± 0.2 V  | 4.6              | 29.9 | 3.7           | 18.3 | 3.4            | 14.5 | 3.0           | 10.9 | 2.9           | 9.4  | 2.9           | 8.2  | ns   |
|                 |                   | V <sub>CCA</sub> = 3.3 V ± 0.3 V  | 4.6              | 29.5 | 3.8           | 17.6 | 3.5            | 13.7 | 3.1           | 10.1 | 2.9           | 8.5  | 2.8           | 7.2  | ns   |
|                 |                   | V <sub>CCA</sub> = 5.0 V ± 0.5 V  | 4.8              | 29.9 | 4.1           | 17.2 | 3.7            | 13.2 | 3.2           | 9.3  | 2.9           | 7.7  | 2.6           | 6.4  | ns   |
|                 |                   | B4 to YA4                         |                  |      |               |      |                |      |               |      |               |      |               |      |      |
|                 |                   | V <sub>CCA</sub> = 1.2 V ± 0.1 V  | 6.7              | 42.7 | 5.9           | 35.2 | 5.5            | 32.7 | 5.1           | 30.6 | 5.1           | 30.1 | 5.1           | 30.7 | ns   |
|                 |                   | V <sub>CCA</sub> = 1.5 V ± 0.1 V  | 6.1              | 31.9 | 5.2           | 24.2 | 4.5            | 21.5 | 4.1           | 19.1 | 4.1           | 18.3 | 4.1           | 17.8 | ns   |
|                 |                   | V <sub>CCA</sub> = 1.8 V ± 0.15 V | 5.7              | 28.6 | 4.7           | 20.3 | 4.0            | 17.5 | 3.5           | 15.1 | 3.5           | 14.2 | 3.5           | 13.6 | ns   |
|                 |                   | V <sub>CCA</sub> = 2.5 V ± 0.2 V  | 5.4              | 24.6 | 4.4           | 16.3 | 3.6            | 13.6 | 3.2           | 11.2 | 3.2           | 10.2 | 3.3           | 9.6  | ns   |
|                 |                   | V <sub>CCA</sub> = 3.3 V ± 0.3 V  | 5.3              | 23.2 | 4.3           | 14.9 | 3.5            | 12.2 | 3.0           | 9.6  | 3.1           | 8.6  | 3.1           | 7.9  | ns   |
|                 |                   | V <sub>CCA</sub> = 5.0 V ± 0.5 V  | 5.1              | 23.2 | 4.1           | 14.2 | 3.5            | 11.1 | 3.0           | 8.4  | 2.8           | 7.4  | 2.7           | 6.6  | ns   |

4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

| Symbol          | Parameter   | Conditions                        | V <sub>CCB</sub> |      |               |      |                |      |               |      |               |      |               |      | Unit |
|-----------------|-------------|-----------------------------------|------------------|------|---------------|------|----------------|------|---------------|------|---------------|------|---------------|------|------|
|                 |             |                                   | 1.2 V ± 0.1 V    |      | 1.5 V ± 0.1 V |      | 1.8 V ± 0.15 V |      | 2.5 V ± 0.2 V |      | 3.3 V ± 0.3 V |      | 5.0 V ± 0.5 V |      |      |
|                 |             |                                   | Min              | Max  | Min           | Max  | Min            | Max  | Min           | Max  | Min           | Max  | Min           | Max  |      |
| t <sub>en</sub> | enable time | OE to YBn [1]                     |                  |      |               |      |                |      |               |      |               |      |               |      |      |
|                 |             | V <sub>CCA</sub> = 1.2 V ± 0.1 V  | 8.5              | 43.3 | 7.7           | 32.7 | 7.4            | 29.4 | 7.2           | 26.2 | 7.2           | 25.3 | 7.2           | 24.8 | ns   |
|                 |             | V <sub>CCA</sub> = 1.5 V ± 0.1 V  | 7.9              | 39.8 | 6.4           | 24.3 | 6.1            | 21.1 | 5.6           | 17.6 | 5.6           | 16.5 | 5.6           | 15.9 | ns   |
|                 |             | V <sub>CCA</sub> = 1.8 V ± 0.15 V | 7.5              | 38.9 | 6.1           | 23.4 | 5.2            | 18.2 | 4.7           | 14.6 | 4.6           | 13.3 | 4.6           | 12.6 | ns   |
|                 |             | V <sub>CCA</sub> = 2.5 V ± 0.2 V  | 7.1              | 37.9 | 5.3           | 22.4 | 4.4            | 17.2 | 3.9           | 11.5 | 3.7           | 10.2 | 3.7           | 9.2  | ns   |
|                 |             | V <sub>CCA</sub> = 3.3 V ± 0.3 V  | 6.6              | 37.4 | 5.1           | 21.9 | 4.1            | 16.5 | 3.4           | 10.8 | 3.3           | 8.8  | 3.2           | 7.7  | ns   |
|                 |             | V <sub>CCA</sub> = 5.0 V ± 0.5 V  | 6.2              | 36.9 | 4.5           | 21.4 | 3.6            | 16.1 | 2.9           | 10.2 | 2.6           | 8.1  | 2.6           | 6.5  | ns   |
|                 |             | OE to YA4                         |                  |      |               |      |                |      |               |      |               |      |               |      |      |
|                 |             | V <sub>CCA</sub> = 1.2 V ± 0.1 V  | 8.5              | 43.2 | 8.7           | 43.2 | 8.7            | 43.2 | 8.7           | 43.2 | 8.5           | 43.2 | 8.5           | 43.2 | ns   |
|                 |             | V <sub>CCA</sub> = 1.5 V ± 0.1 V  | 7.4              | 39.7 | 6.4           | 29.4 | 6.5            | 29.4 | 6.5           | 29.4 | 6.4           | 29.4 | 6.4           | 29.4 | ns   |
|                 |             | V <sub>CCA</sub> = 1.8 V ± 0.15 V | 6.5              | 34.3 | 5.6           | 24.9 | 5.2            | 23.2 | 5.2           | 23.2 | 5.2           | 23.2 | 5.2           | 23.2 | ns   |
|                 |             | V <sub>CCA</sub> = 2.5 V ± 0.2 V  | 5.6              | 29.0 | 4.7           | 20.5 | 4.3            | 18.6 | 4.1           | 16.6 | 4.1           | 16.6 | 3.4           | 16.6 | ns   |
|                 |             | V <sub>CCA</sub> = 3.3 V ± 0.3 V  | 5.2              | 28.0 | 4.2           | 19.1 | 3.7            | 16.7 | 3.4           | 9.6  | 3.4           | 8.9  | 3.0           | 8.9  | ns   |
|                 |             | V <sub>CCA</sub> = 5.0 V ± 0.5 V  | 4.8              | 28.4 | 3.8           | 16.6 | 3.3            | 10.4 | 2.8           | 7.9  | 2.7           | 7.2  | 2.7           | 6.5  | ns   |

4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state

| Symbol           | Parameter    | Conditions                        | V <sub>CCB</sub> |      |               |      |                |      |               |      |               |      |               |      | Unit |
|------------------|--------------|-----------------------------------|------------------|------|---------------|------|----------------|------|---------------|------|---------------|------|---------------|------|------|
|                  |              |                                   | 1.2 V ± 0.1 V    |      | 1.5 V ± 0.1 V |      | 1.8 V ± 0.15 V |      | 2.5 V ± 0.2 V |      | 3.3 V ± 0.3 V |      | 5.0 V ± 0.5 V |      |      |
|                  |              |                                   | Min              | Max  | Min           | Max  | Min            | Max  | Min           | Max  | Min           | Max  | Min           | Max  |      |
| t <sub>dis</sub> | disable time | OE to YBn [1]                     |                  |      |               |      |                |      |               |      |               |      |               |      |      |
|                  |              | V <sub>CCA</sub> = 1.2 V ± 0.1 V  | 11.7             | 45.2 | 10.9          | 38.2 | 11.5           | 36.8 | 10.6          | 33.2 | 10.8          | 33.9 | 9.9           | 33.4 | ns   |
|                  |              | V <sub>CCA</sub> = 1.5 V ± 0.1 V  | 11.6             | 45.2 | 8.5           | 27.8 | 8.9            | 26.3 | 7.4           | 22.6 | 7.4           | 23.2 | 7.4           | 21.2 | ns   |
|                  |              | V <sub>CCA</sub> = 1.8 V ± 0.15 V | 11.6             | 45.4 | 8.4           | 27.8 | 6.9            | 22.6 | 5.3           | 19.2 | 5.3           | 19.5 | 6.3           | 17.3 | ns   |
|                  |              | V <sub>CCA</sub> = 2.5 V ± 0.2 V  | 11.6             | 45.8 | 8.3           | 27.9 | 7.1            | 22.6 | 4.7           | 18.9 | 6.0           | 16.0 | 4.6           | 14.1 | ns   |
|                  |              | V <sub>CCA</sub> = 3.3 V ± 0.3 V  | 11.3             | 46.4 | 8.4           | 28.2 | 6.7            | 22.7 | 4.1           | 15.5 | 4.9           | 15.0 | 4.1           | 12.8 | ns   |
|                  |              | V <sub>CCA</sub> = 5.0 V ± 0.5 V  | 11.3             | 59.2 | 8.4           | 28.8 | 6.4            | 25.6 | 3.4           | 16.9 | 4.9           | 17.1 | 3.1           | 13.3 | ns   |
|                  |              | OE to YA4                         |                  |      |               |      |                |      |               |      |               |      |               |      |      |
|                  |              | V <sub>CCA</sub> = 1.2 V ± 0.1 V  | 11.6             | 59.6 | 11.6          | 59.6 | 11.6           | 59.6 | 11.6          | 59.6 | 11.6          | 59.6 | 11.6          | 58.9 | ns   |
|                  |              | V <sub>CCA</sub> = 1.5 V ± 0.1 V  | 10.8             | 51.3 | 8.5           | 40.8 | 8.5            | 40.8 | 8.5           | 40.8 | 8.7           | 40.8 | 8.7           | 40.8 | ns   |
|                  |              | V <sub>CCA</sub> = 1.8 V ± 0.15 V | 7.5              | 50.3 | 7.5           | 40.8 | 7.5            | 39.4 | 5.0           | 39.4 | 5.0           | 39.4 | 4.0           | 39.4 | ns   |
|                  |              | V <sub>CCA</sub> = 2.5 V ± 0.2 V  | 7.5              | 44.8 | 7.5           | 33.7 | 5.0            | 30.1 | 5.0           | 25.9 | 5.0           | 25.9 | 2.6           | 19.2 | ns   |
|                  |              | V <sub>CCA</sub> = 3.3 V ± 0.3 V  | 7.5              | 39.9 | 7.5           | 28.3 | 5.0            | 23.5 | 5.0           | 16.2 | 5.0           | 15.0 | 4.7           | 17.1 | ns   |
|                  |              | V <sub>CCA</sub> = 5.0 V ± 0.5 V  | 7.5              | 34.2 | 7.5           | 21.5 | 4.9            | 17.5 | 4.9           | 12.9 | 4.9           | 11.6 | 3.6           | 11.9 | ns   |

[1] t<sub>pd</sub> is the same as t<sub>PLH</sub> and t<sub>PHL</sub>; t<sub>dis</sub> is the same as t<sub>PLZ</sub> and t<sub>PHZ</sub>; t<sub>en</sub> is the same as t<sub>PZL</sub> and t<sub>PZH</sub>.

14.1. Waveforms and test circuit





Table 18. Measurement points

| Supply voltage     | Input[1]             | Output[2]            |                           |                           |
|--------------------|----------------------|----------------------|---------------------------|---------------------------|
| $V_{CCA}, V_{CCB}$ | $V_M$                | $V_M$                | $V_X$                     | $V_Y$                     |
| 0.9 V to 1.6 V     | $0.5 \times V_{CCI}$ | $0.5 \times V_{CCO}$ | $V_{OL} + 0.1 \text{ V}$  | $V_{OH} - 0.1 \text{ V}$  |
| 1.65 V to 2.7 V    | $0.5 \times V_{CCI}$ | $0.5 \times V_{CCO}$ | $V_{OL} + 0.15 \text{ V}$ | $V_{OH} - 0.15 \text{ V}$ |
| 3.0 V to 5.5 V     | $0.5 \times V_{CCI}$ | $0.5 \times V_{CCO}$ | $V_{OL} + 0.3 \text{ V}$  | $V_{OH} - 0.3 \text{ V}$  |

[1]  $V_{CCI}$  is the supply voltage associated with the inputs (An, B4).  
[2]  $V_{CCO}$  is the supply voltage associated with the outputs (YBn, YA4).

4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state









Table 19. Test data

| Supply voltage     | Load  |       | Input                   |           | $V_{EXT}$          |                    |                        |
|--------------------|-------|-------|-------------------------|-----------|--------------------|--------------------|------------------------|
| $V_{CCA}, V_{CCB}$ | $C_L$ | $R_L$ | $t_r, t_f$              | $V_I$ [1] | $t_{PLH}, t_{PHL}$ | $t_{PZH}, t_{PHZ}$ | $t_{PZL}, t_{PLZ}$ [2] |
| 0.9 V to 5.5 V     | 5 pF  | 10 kΩ | $\leq 1.0 \text{ ns/V}$ | $V_{CCI}$ | open               | GND                | $2 \times V_{CCO}$     |

[1]  $V_{CCI}$  is the supply voltage associated with the inputs (An, B4).  
[2]  $V_{CCO}$  is the supply voltage associated with the outputs (YBn, YA4).

14.2. Additional propagation delay versus load capacitance graphs



4-bit dual-supply voltage level translating buffer with Schmitt-trigger; 3-state




Fig. 17. Additional propagation delay versus load capacitance




Fig. 18. Additional propagation delay versus load capacitance




Fig. 19. Additional propagation delay versus load capacitance

15. Application information

The NXU0304 is a 4-bit level-shifting transceiver suitable for level-translation purposes. This device is ideal in any application requiring level-shifting between two voltage domains and especially designed for applications where push-pull drivers are utilized to the data inputs pins. Below an example of possible SPI application.

Typical application schematic (SPI interface)




Fig. 20. SPI interface application

16. Package outline

TSSOP14: plastic thin shrink small outline package; 14 leads; body width 4.4 mm

SOT402-1




Fig. 21. Package outline SOT402-1 (TSSOP14)

DHVQFN14: plastic dual in-line compatible thermal enhanced very thin quad flat package; no leads;  
14 terminals; body 2.5 x 3 x 0.85 mm

SOT762-1




Fig. 22. Package outline SOT762-1 (DHVQFN14)

DHXQFN14: plastic, leadless dual in-line compatible thermal enhanced extreme thin quad flat package;  
no leads; 14 terminals; 0.4 mm pitch; body 2 mm x 2 mm x 0.48 mm

SOT8014-1




Fig. 23. Package outline SOT8014-1 (DHXQFN14)

XQFN12: plastic, extremely thin quad flat package; no leads;  
12 terminals; body 1.70 x 2.00 x 0.50 mm

SOT1174-1




Fig. 24. Package outline SOT1174-1 (XQFN12)

17. Abbreviations

Table 20. Abbreviations

| Acronym | Description             |
|---------|-------------------------|
| CDM     | Charged Device Model    |
| DUT     | Device Under Test       |
| ESD     | ElectroStatic Discharge |
| HBM     | Human Body Model        |

18. Revision history

Table 21. Revision history

| Document ID   | Release date                                                                                                                                                                                                                                  | Data sheet status  | Change notice | Supersedes  |
|---------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|---------------|-------------|
| NXU0304 v.2   | 20241202                                                                                                                                                                                                                                      | Product data sheet | -             | NXU0304 v.1 |
| Modifications | <ul style="list-style-type: none"><li><a href="#">Fig. 5</a>: input waveform at <math>V_{CC} = 1.8\text{ V}</math> corrected (errata).<br/><a href="#">Section 1</a> and <a href="#">Section 8.1</a>: "Schmitt-trigger" text added.</li></ul> |                    |               |             |
| NXU0304 v.1   | 20240819                                                                                                                                                                                                                                      | Product data sheet | -             | -           |

## 19. Legal information

### Data sheet status

| Document status [1][2]         | Product status [3] | Definition                                                                            |
|--------------------------------|--------------------|---------------------------------------------------------------------------------------|
| Objective [short] data sheet   | Development        | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet | Qualification      | This document contains data from the preliminary specification.                       |
| Product [short] data sheet     | Production         | This document contains the product specification.                                     |

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the internet at <https://www.nexperia.com>.

### Definitions

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

**Short data sheet** — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

### Disclaimers

**Limited warranty and liability** — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia.

In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

**Right to make changes** — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal

injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

**Limiting values** — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

**Terms and conditions of commercial sale** — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nexperia.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

**Non-automotive qualified products** — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

**Trademarks**

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Contents

|                                                                        |    |
|------------------------------------------------------------------------|----|
| 1. General description.....                                            | 1  |
| 2. Features and benefits.....                                          | 1  |
| 3. Applications.....                                                   | 1  |
| 4. Ordering information.....                                           | 2  |
| 5. Marking.....                                                        | 2  |
| 6. Functional diagram.....                                             | 3  |
| 7. Pinning information.....                                            | 4  |
| 7.1. Pinning.....                                                      | 4  |
| 7.2. Pin description.....                                              | 5  |
| 8. Functional description.....                                         | 5  |
| 8.1. Overview.....                                                     | 5  |
| 8.2. Inputs.....                                                       | 5  |
| 8.3. Outputs.....                                                      | 7  |
| 8.4. Suspend mode and I <sub>OFF</sub> protection circuitry.....       | 8  |
| 9. Limiting values.....                                                | 8  |
| 10. ESD ratings.....                                                   | 9  |
| 11. Recommended operating conditions.....                              | 9  |
| 12. Thermal characteristics.....                                       | 9  |
| 13. Static characteristics.....                                        | 10 |
| 14. Dynamic characteristics.....                                       | 16 |
| 14.1. Waveforms and test circuit.....                                  | 25 |
| 14.2. Additional propagation delay versus load capacitance graphs..... | 27 |
| 15. Application information.....                                       | 29 |
| 16. Package outline.....                                               | 30 |
| 17. Abbreviations.....                                                 | 34 |
| 18. Revision history.....                                              | 34 |
| 19. Legal information.....                                             | 35 |

© Nexperia B.V. 2024. All rights reserved

For more information, please visit: <http://www.nexperia.com>  
For sales office addresses, please send an email to: [salesaddresses@nexperia.com](mailto:salesaddresses@nexperia.com)  
Date of release: 2 December 2024