

Product Overview


Description

The MHP series are non-isolated point-of-load switching regulators for high reliability military and space distributed power applications (MIL-PRF-38534 certified facility). Fully integrated, these include a buck controller, inductor, and input/output capacitors combined in a single package. They operate from an input voltage of +4.5V to +12V, providing step down power conversion to output voltages as low as 0.5V or lower. Operating features include output voltage adjust, output current limit, and output enable/disable. Careful design and layout ensure excellent stability, transient response, and low noise operation. Packaged in a compact metal case, it operates over the full -55 °C to +125 °C temperature range.

Features

- Now available as SMD: 5962R1323601xxx
- Single 3 amp product
- Efficiencies to 87%, see [Figure 6-7](#)
- Radiation hard to 100K rad TID
- Single-event results show no significant output transients through an LET of 58 MeV/(mg/cm²).
- Optimized for 5V input. Consult factory for higher input voltages.
- Operates down to 4.5 volts input
- Current mode control
- Adjustable output voltage between 0.5V and 4V (depends on model, see [Table 3-1](#))
- Enable function available
- Operates at a nominal frequency of 500 KHz

Figure 1. MO-078 (MHP8565)



Levels Available
COTS
Military
Space

Applications/Benefits

- More efficient than competitive POLs (See [Figure 6-6](#)).
- FPGA power supply - satellite
- ASIC power supply - satellite

Table of Contents

Product Overview.....	1
1. Absolute Maximum Ratings.....	3
1.1. Mechanical Packaging.....	3
2. Electrical Characteristics.....	4
3. Model Number Functionality Chart.....	5
4. Screening Options.....	7
5. Application Circuits, 3 Amp Product.....	8
6. Package Outlines, 3 Amp Product (8565A).....	9
7. Revision History.....	14
Microchip Information.....	15
The Microchip Website.....	15
Product Change Notification Service.....	15
Customer Support.....	15
Microchip Devices Code Protection Feature.....	15
Legal Notice.....	15
Trademarks.....	16
Quality Management System.....	17
Worldwide Sales and Service.....	18

1. Absolute Maximum Ratings

Table 1-1. Absolute Maximum Ratings ($T_c = +25^\circ\text{C}$ unless otherwise note)

Parameters / Test Conditions	Symbol	Value	Unit
Input voltage ¹	V_{in}	16	Vdc
Output current ²	I_o	4	A
Enable input voltage	V_{en}	7	Vdc
Approximate weight	MO-078	10	Grams
Operating temperature range, base of package	T_c	-55 to +125	°C
Storage temperature range	T_{stg}	-65 to +150	°C

Table 1-2. Thermal Characteristics

Parameters / Test Conditions	Symbol	Value	Unit
Series switch Thermal resistance, junction-to-case, MO-78 package	$R_{\theta JC}$	2.5	°C/W

Notes:

1. Most internal components are rated at +16 volts maximum and are therefore properly de-rated for operation at a nominal input of +5 volts. Operation at +12V will decrease that de-rating.
2. Internal series switch is self-protected and is rated to conduct 4.0 amps minimum. However, limitations on internal components plus the characteristics of PWM operation conspire to reduce further the minimum available output current, especially at output voltages above $V_{in}/2$. Minimum available output current is guaranteed to be as specified at output voltage of 2.5V down to 1.21V, assuming a clean layout. At output voltages below 1.21V, maximum output current may reduce by up to 1 amp, depending on actual output voltage, and load regulation may degrade slightly (up to 1%). At 3.3V output with a 5V input, output current reduces by 0.5A from the value specified at 2.5V out.

1.1 Mechanical Packaging

See [Figure 6-1](#), [Figure 6-2](#), [Figure 6-3](#), [Figure 6-4](#), and [Table 6-1](#).

2. Electrical Characteristics

Table 2-1. Electrical Characteristics¹ (TA = -55 °C to +125 °C unless otherwise noted)

Parameters / Test Conditions	Symbol	Value			Unit
		Min.	Nom.	Max.	
Minimum input voltage ²	Vin(min)	4.5	—	—	V
Output voltage accuracy Vo = 1.21V	Vout	1.19	—	1.23	V
	Vout	1.17	—	1.24	V
Post 100K irradiation, 25 °C					
Line regulation 4.5V < Vin < 5.5V Vo = 1.21V	Kvi	-0.5	—	+0.5	%
	Kvo	-1	—	+1	%
Load regulation 1A < Iout < 2A	ICL	3.5	5	—	A
	ICL	3.0	—	—	
Current limit Vo = 2.5V					
Post 100K irradiation, 25 °C	Vshdn	0.13	0.40	0.60	V
Input voltage on enable pin to guarantee shutdown ^{3, 4} Io = 0A					

Notes:

1. Testing is accomplished at an output load of 1A, and at an output voltage of 2.5V and an input of 5V unless otherwise specified. Only the specifications with post irradiation limits are tested after radiation exposure.
2. Minimum input voltage is guaranteed by line regulation test.
3. If not used, or when on, the enable pin should be pulled up to a logic one (2.5V min, 7V max) through a resistor of no more than 5K ohms. Voltage on this pin to disable operation needs to be less than 0.13V.
4. Not tested in production. Parameters are for reference only.

3. Model Number Functionality Chart

Table 3-1. Model Number Functionality Chart

Model Number ¹	Notes	Package Type	Output Type	Other Functionality					Former P/N
		MO-078	Adj	Enable Pin	Parallelable	Note A	Output Voltage Range ^{2, 3}	Package Body	Internal Compensation
MHP8565A\$&*	3 amp series	✓	✓	✓	No	0.5 - 4V	Isolated	✓	SAT8565A-3\$T-ADJ

Replace “\$” with letter to denote required screening level

- C = COTS
- M = MIL-PRF-38534, Class H
- S = MIL-PRF-38534, Class K

Replace “&” with lead lend option

- Blank = No lead-bend
- -1 = SMT lead-bend
- -2 = lead-bend down
- -3 = lead-bend up

Replace “*” with lead finish option

- C = Gold plate
- A = Solder dipped

Notes:

1. See DS CC SMD 5962-13236 for DS CC part number options.
2. Internal series switch is self-protected and is rated to conduct 4.0 amps minimum. However, limitations on internal components plus the characteristics of PWM operation conspire to reduce further the minimum available output current, especially at output Voltages above Vin/2. Minimum available output current is guaranteed to be as specified at output voltage of 2.5V down to 1.21V, assuming a clean layout. At output voltages below 1.21V, maximum output current may reduce by up to 1 amp, depending on actual output voltage, and load regulation may degrade slightly (up to 1%). At 3.3V output with a 5V input, output current reduces by 0.5A from the value specified at 2.5V out.
3. Minimum input voltage is guaranteed by line regulation test.

Table 3-2. Example SMD Part Numbers

Standard Microcircuit Drawing	Microchip Similar Part ¹
5962R1323601KUC	MHP8565ASC
5962R1323601KUA	MHP8565ASA
5962R1323601KXC	MHP8565AS-1C
5962R1323601KXA	MHP8565AS-1A
5962R1323601KYC	MHP8565AS-2C
5962R1323601KYA	MHP8565AS-2A

.....continued

Standard Microcircuit Drawing	Microchip Similar Part ¹
5962R1323601KZC	MHP8565AS-3C
5962R1323601KZA	MHP8565AS-3A

The SMD number shown is for Class K screening and radiation hardness level R. See the SMD 13236 for the numbers for other screening and radiation levels. For exact specifications for an SMD product, refer to the SMD drawing. SMD's can be downloaded from the DLA Land and Maritime website.

Note:

1. Do not use the Microchip similar part number to order the SMD device.

4. Screening Options

Table 4-1. Screening Options

Test	Commercial	Military = Class H	Space = Class K	MIL-STD-883 Method
	COTS	MIL-PRF-38534		
Element evaluation	N/A	Military	Space	Note 1
Non-destruct wirebond pull	N/A	Sample	100%	2023
Pre-cap visual	N/A	100%	100%	2017
Temperature cycle	N/A	100%	100%	1010
Constant acceleration	N/A	100%	100%	2001
PIND	N/A	N/A	100%	2020
Pre-burn-in electrical	N/A	100%	100%	—
Burn-in	N/A	100% (160 hours)	100% (320 hours)	1015
Final electrical tests	100% (25 °C)	100%	100%	Note 1
Hermeticity (fine and gross leak)	100%	100%	100%	1014
X-ray ²	N/A	N/A	Yes	2012
External visual	Sample	100%	100%	2009

NOTES:

1. Microchip is a DLA approved facility. Testing is performed per MIL-PRF-38534.
2. Maximum solder reflow temperature = 180 °C. Do not exceed.

5. Application Circuits, 3 Amp Product

Figure 5-1. 3A Adjustable Configuration

$V_{out} = V_{ref} \times (1 + R_{adj} / 2490)$, with $V_{ref} \sim 1.21$ Volts





Table 5-1. Commonly Available 1% Resistor Values for Various Output Voltage for 3A Product

V_{out} (V)	R_{adj} (Ω)	V_{out} (V)	R_{adj} (Ω)
1.21	0	2.8	3240
1.5	590	3.0	3650
1.8	1210	3.3	4320
2.0	1620	3.5	4750
2.2	2050	3.8	5360
2.5	2670	4.0	5760


6. Package Outlines, 3 Amp Product (8565A)

Figure 6-1. Standard Straight Package




Dimensions are in inches
Tolerances .XXX = $\pm .005"$
.XX = $\pm .010"$

Figure 6-2. Surface Mount Lead-Bend (-1 Option)



Dimensions are in inches
Tolerances .XXX=±.005'
.XX=±.010'

Figure 6-3. Right Angle Lead-Bend (-2 Option Lead-Bend Down)



Dimensions are in inches
Tolerances .XXX = $\pm .005"$
.XX = $\pm .010"$

Figure 6-4. -3 Option Lead-Bend Up





Table 6-1. Pin Assignments for 3 Amp Product

Pin No	8565A	
	Pin Name	Pin Description
1	Vin	Input voltage
2	GND	Current ground
3	Vout	Output voltage

.....continued

Pin No	8565A	
	Pin Name	Pin Description
4	Enable	Enable output
5	Adjust	Output voltage adjust
Case	N/C	Isolated

Figure 6-5. Circuit for Creating Regulated Output Voltages Below 1.21 Volts



$$V_{OUT} = 1.21 - R \text{ (K-Ohms)}$$

Example: If $R = 0.21$ K Ohms (210 Ohms), $V_{OUT} = 1.21 - 0.21 = 1.0$ V, within the limits of the tolerances of the components used.

Note:

** RAD Hard Zener or other fixed voltage > 2 V may be used. For any voltage other than 2.5V, resistor values would have to be adjusted accordingly.

Figure 6-6. MHP8565 Typical Efficiency Vs. Typical Competitive POL (Vin = 5V, Vout = 3.3V)





Figure 6-7. Typical Efficiency Curves (Vin = 5V)



7. Revision History

The revision history describes the changes that were implemented in the document. The changes are listed by revision, starting with the most current publication.

Revision	Date	Description
A	09/2023	Initial revision.

Microchip Information

The Microchip Website

Microchip provides online support via our website at www.microchip.com/. This website is used to make files and information easily available to customers. Some of the content available includes:

- **Product Support** – Data sheets and errata, application notes and sample programs, design resources, user's guides and hardware support documents, latest software releases and archived software
- **General Technical Support** – Frequently Asked Questions (FAQs), technical support requests, online discussion groups, Microchip design partner program member listing
- **Business of Microchip** – Product selector and ordering guides, latest Microchip press releases, listing of seminars and events, listings of Microchip sales offices, distributors and factory representatives

Product Change Notification Service

Microchip's product change notification service helps keep customers current on Microchip products. Subscribers will receive email notification whenever there are changes, updates, revisions or errata related to a specified product family or development tool of interest.

To register, go to www.microchip.com/pcn and follow the registration instructions.

Customer Support

Users of Microchip products can receive assistance through several channels:

- Distributor or Representative
- Local Sales Office
- Embedded Solutions Engineer (ESE)
- Technical Support

Customers should contact their distributor, representative or ESE for support. Local sales offices are also available to help customers. A listing of sales offices and locations is included in this document.

Technical support is available through the website at: www.microchip.com/support

Microchip Devices Code Protection Feature

Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is "unbreakable". Code protection is constantly evolving. Microchip is committed to continuously improving the code protection features of our products.

Legal Notice

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure

that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at www.microchip.com/en-us/support/design-help/client-support-services.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSEQUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Trademarks

The Microchip name and logo, the Microchip logo, Adaptec, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, CryptoMemory, CryptoRF, dsPIC, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AgileSwitch, ClockWorks, The Embedded Control Solutions Company, EtherSynch, Flashtec, Hyper Speed Control, HyperLight Load, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, TimeCesium, TimeHub, TimePictra, TimeProvider, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, Augmented Switching, BlueSky, BodyCom, Clockstudio, CodeGuard, CryptoAuthentication, CryptoAutomotive, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, Espresso T1S, EtherGREEN, EyeOpen, GridTime, IdealBridge, IGaT, In-Circuit Serial Programming, ICSP, INICnet, Intelligent Paralleling, IntelliMOS, Inter-Chip Connectivity, JitterBlocker, Knob-on-Display, MarginLink, maxCrypto, maxView, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, mSiC, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, Power MOS IV, Power MOS 7, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, RTAX, RTG4, SAM-ICE, Serial Quad I/O, simpleMAP, SimpliPHY, SmartBuffer, SmartHLS, SMART-I.S., storClad, SQI, SuperSwitcher, SuperSwitcher II, Switchtec, SynchroPHY, Total Endurance, Trusted Time, TSHARC, Turing, USBCheck, VariSense, VectorBlox, VeriPHY, ViewSpan, WiperLock, XpressConnect, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2016-2023, Microchip Technology Incorporated and its subsidiaries. All Rights Reserved.

ISBN: 978-1-6683-3081-4

Quality Management System

For information regarding Microchip's Quality Management Systems, please visit
www.microchip.com/quality.

Worldwide Sales and Service

AMERICAS	ASIA/PACIFIC	ASIA/PACIFIC	EUROPE
Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support: www.microchip.com/support Web Address: www.microchip.com	Australia - Sydney Tel: 61-2-9868-6733 China - Beijing Tel: 86-10-8569-7000 China - Chengdu Tel: 86-28-8665-5511 China - Chongqing Tel: 86-23-8980-9588 China - Dongguan Tel: 86-769-8702-9880 China - Guangzhou Tel: 86-20-8755-8029 China - Hangzhou Tel: 86-571-8792-8115 China - Hong Kong SAR Tel: 852-2943-5100 China - Nanjing Tel: 86-25-8473-2460 China - Qingdao Tel: 86-532-8502-7355 China - Shanghai Tel: 86-21-3326-8000 China - Shenyang Tel: 86-24-2334-2829 China - Shenzhen Tel: 86-755-8864-2200 China - Suzhou Tel: 86-186-6233-1526 China - Wuhan Tel: 86-27-5980-5300 China - Xian Tel: 86-29-8833-7252 China - Xiamen Tel: 86-592-2388138 China - Zhuhai Tel: 86-756-3210040	India - Bangalore Tel: 91-80-3090-4444 India - New Delhi Tel: 91-11-4160-8631 India - Pune Tel: 91-20-4121-0141 Japan - Osaka Tel: 81-6-6152-7160 Japan - Tokyo Tel: 81-3-6880-3770 Korea - Daegu Tel: 82-53-744-4301 Korea - Seoul Tel: 82-2-554-7200 Malaysia - Kuala Lumpur Tel: 60-3-7651-7906 Malaysia - Penang Tel: 60-4-227-8870 Philippines - Manila Tel: 63-2-634-9065 Singapore Tel: 65-6334-8870 Taiwan - Hsin Chu Tel: 886-3-577-8366 Taiwan - Kaohsiung Tel: 886-7-213-7830 Taiwan - Taipei Tel: 886-2-2508-8600 Thailand - Bangkok Tel: 66-2-694-1351 Vietnam - Ho Chi Minh Tel: 84-28-5448-2100	Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393 Denmark - Copenhagen Tel: 45-4485-5910 Fax: 45-4485-2829 Finland - Espoo Tel: 358-9-4520-820 France - Paris Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79 Germany - Garching Tel: 49-8931-9700 Germany - Haan Tel: 49-2129-3766400 Germany - Heilbronn Tel: 49-7131-72400 Germany - Karlsruhe Tel: 49-721-625370 Germany - Munich Tel: 49-89-627-144-0 Fax: 49-89-627-144-44 Germany - Rosenheim Tel: 49-8031-354-560 Israel - Ra'anana Tel: 972-9-744-7705 Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781 Italy - Padova Tel: 39-049-7625286 Netherlands - Drunen Tel: 31-416-690399 Fax: 31-416-690340 Norway - Trondheim Tel: 47-72884388 Poland - Warsaw Tel: 48-22-3325737 Romania - Bucharest Tel: 40-21-407-87-50 Spain - Madrid Tel: 34-91-708-08-90 Fax: 34-91-708-08-91 Sweden - Gothenberg Tel: 46-31-704-60-40 Sweden - Stockholm Tel: 46-8-5090-4654 UK - Wokingham Tel: 44-118-921-5800 Fax: 44-118-921-5820
Atlanta Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455 Austin, TX Tel: 512-257-3370 Boston Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088 Chicago Itasca, IL Tel: 630-285-0071 Fax: 630-285-0075 Dallas Addison, TX Tel: 972-818-7423 Fax: 972-818-2924 Detroit Novi, MI Tel: 248-848-4000 Houston, TX Tel: 281-894-5983 Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380 Los Angeles Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800 Raleigh, NC Tel: 919-844-7510 New York, NY Tel: 631-435-6000 San Jose, CA Tel: 408-735-9110 Tel: 408-436-4270 Canada - Toronto Tel: 905-695-1980 Fax: 905-695-2078			