# SCT4036KE


**N-channel SiC power MOSFET**

Datasheet

| | |
|---|---|
| $V_{DSS}$ | 1200V |
| $R_{DS(on)}$ (Typ.) | 36mΩ |
| $I_D$ *1 | 43A |
| $P_D$ | 176W |

## ●Outline


TO-247N




## ● Features

1) Low on-resistance
2) Fast switching speed
3) Fast reverse recovery
4) Easy to parallel
5) Simple to drive
6) Pb-free lead plating ; RoHS compliant

## ●Inner circuit




## ● Application

・Solar inverters
・DC/DC converters
・Switch mode power supplies
・Induction heating

## ●Packaging specifications

| | | |
|---|---|---|
| Type | Packing | Tube |
| | Reel size (mm) | - |
| | Tape width (mm) | - |
| | Basic ordering unit (pcs) | 30 |
| | Taping code | C11 |
| | Marking | SCT4036KE |

## ●Absolute maximum ratings ($T_{vj}$ = 25°C unless otherwise specified)

| Parameter | | | Symbol | Value | Unit |
|---|---|---|---|---|---|
| Drain - source voltage | | | $V_{DSS}$ | 1200 | V |
| Continuous drain and source current | $V_{GS}$ = $V_{GS_on}$ | $T_c$ = 25°C | $I_D$, $I_S$ *1 | 43 | A |
| | | $T_c$ = 100°C | | 30 | A |
| Pulsed drain current | $V_{GS}$ = $V_{GS_on}$ | $T_c$ = 25°C | $I_{D,pulse}$ *2 | 84 | A |
| Body diode pulsed forward current | | $T_c$ = 25°C, $V_{GS}$ = 0 V | $I_{S,pulse}$ *1,*3 | 43 | A |
| Body diode surge forward current | | | $I_{S,pulse}$ *1,*4 | 84 | A |
| Gate - source voltage (DC) | | | $V_{GSS_DC}$ | -4 to +21 | V |
| Gate - source surge voltage ($t_{surge}$ < 300ns) | | | $V_{GSS_surge}$ *5 | -4 to +23 | V |
| Recommended turn-on gate - source drive voltage | | | $V_{GS_on}$ *6 | +15 to +18 | V |
| Recommended turn-off gate - source drive voltage | | | $V_{GS_off}$ | 0 | V |
| Virtual junction temperature | | | $T_{vj}$ | 175 | °C |
| Range of storage temperature | | | $T_{stg}$ | -40 to +175 | °C |



©2024 ROHM Co., Ltd. All rights reserved.



Downloaded from Arrow.com.

## ●Electrical characteristics ($T_{vj}$ = 25°C unless otherwise specified)

| Parameter | Symbol | Conditions | Values | | | Unit |
|---|---|---|---|---|---|---|
| | | | Min. | Typ. | Max. | |
| Drain - Source breakdown voltage | $V_{(BR)DSS}$ | $V_{GS}$ = 0 V, $I_D$ = 9.2mA<br>$T_{vj}$ = 25°C | 1200 | - | - | V |
| Zero Gate voltage Drain current | $I_{DSS}$ | $V_{GS}$ = 0 V, $V_{DS}$ =1200V<br>$T_{vj}$ = 25°C<br>$T_{vj}$ = 150°C | -<br>- | 1<br>10 | 80<br>- | μA |
| Gate - Source leakage current | $I_{GSS+}$ | $V_{GS}$ = +21V , $V_{DS}$ = 0V | - | - | 100 | nA |
| Gate - Source leakage current | $I_{GSS-}$ | $V_{GS}$ = -4V , $V_{DS}$ = 0V | - | - | -100 | nA |
| Gate threshold voltage | $V_{GS(th)}$ *7 | $V_{DS}$ = 10V, $I_D$ = 11.1mA | 2.8 | - | 4.8 | V |
| Static Drain - Source on - state resistance | $R_{DS(on)}$ *8 | $V_{GS}$ = 18V, $I_D$ = 21A<br>$T_{vj}$ = 25°C<br>$T_{vj}$ = 150°C | -<br>- | 36<br>72 | 47<br>- | mΩ |
| Gate input resistance | $R_G$ | f = 1MHz, open drain | - | 1 | - | Ω |


## ●Thermal resistance

| Parameter | Symbol | Values | | | Unit |
|---|---|---|---|---|---|
| | | Min. | Typ. | Max. | |
| Thermal resistance, junction - case | $R_{thJC}$ *9 | - | 0.65 | 0.85 | K/W |

## ●Typical Transient Thermal Characteristics

| Symbol | Value | Unit |
|---|---|---|
| $R_{th1}$ | $4.9 \times 10^{-2}$ | K/W |
| $R_{th2}$ | $3.0 \times 10^{-1}$ | |
| $R_{th3}$ | $3.0 \times 10^{-1}$ | |

| Symbol | Value | Unit |
|---|---|---|
| $C_{th1}$ | $8.7 \times 10^{-4}$ | Ws/K |
| $C_{th2}$ | $4.0 \times 10^{-3}$ | |
| $C_{th3}$ | $5.2 \times 10^{-2}$ | |





©2024 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

●**Electrical characteristics** ($T_{vj}$ = 25°C unless otherwise specified)

| Parameter | | Symbol | Conditions | Values | | | Unit |
|---|---|---|---|---|---|---|---|
| | | | | Min. | Typ. | Max. | |
| Transconductance | | $g_{fs}$ *8 | $V_{DS}$ = 10V, $I_D$ = 21A | - | 11 | - | S |
| Input capacitance | | $C_{iss}$ | $V_{GS}$ = 0V | - | 2335 | - | pF |
| Output capacitance | | $C_{oss}$ | $V_{DS}$ = 800V | - | 70 | - | |
| Reverse transfer capacitance | | $C_{rss}$ | f = 1MHz | - | 5 | - | |
| Effective output capacitance, energy related | | $C_{o(er)}$ | $V_{GS}$ = 0V<br>$V_{DS}$ = 0V to 800V | - | 84 | - | pF |
| Total Gate charge | | $Q_g$ *8 | $V_{DS}$ = 800V<br>$I_D$ = 21A<br>$V_{GS}$ = 18V<br>See Fig. 1-1, 1-2. | - | 91 | - | nC |
| Gate - Source charge | | $Q_{gs}$ *8 | | - | 20 | - | |
| Gate - Drain charge | | $Q_{gd}$ *8 | | - | 24 | - | |
| Turn - on delay time | | $t_{d(on)}$ *8 | $V_{DS}$ = 800V<br>$I_D$ = 21A<br>$V_{GS}$ = +18V / 0V<br>$R_G$ = 3.3Ω, L = 250μH<br>$E_{on}$ includes diode reverse recovery<br>$L_\sigma$ = 50nH, $C_\sigma$ = 10pF<br>See Fig. 2-1, 2-2, 2-3. | - | 10 | - | ns |
| Rise time | | $t_r$ *8 | | - | 28 | - | |
| Turn - off delay time | | $t_{d(off)}$ *8 | | - | 31 | - | |
| Fall time | | $t_f$ *8 | | - | 12 | - | |
| Turn - on switching loss | | $E_{on}$ *8 | | - | 480 | - | μJ |
| Turn - off switching loss | | $E_{off}$ *8 | | - | 57 | - | |
| Short-circuit withstand time | $V_{GS(on)}$ = +15V | $t_{sc}$ *10 | $V_{DS} \leq$ 800V<br>$V_{DS,peak} \leq$ 1200V<br>$T_{vj(start)}$ = 25°C<br>$R_G$ = 2.2Ω | - | 4.5 | - | μs |
| | $V_{GS(on)}$ = +18V | | | - | 4.0 | - | μs |


©2024 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

●**Body diode electrical characteristics** (Source-Drain) ($T_{vj}$ = 25°C unless otherwise specified)

| Parameter | Symbol | Conditions | Values | | | Unit |
|---|---|---|---|---|---|---|
| | | | Min. | Typ. | Max. | |
| Forward voltage | $V_{SD}$ *8 | $V_{GS}$ = 0V, $I_S$ = 21A | - | 3.3 | - | V |
| Reverse recovery time | $t_{rr}$ *8 | $I_F$ = 21A<br>$V_R$ = 800V<br>di/dt = 2400A/μs<br>$L_\sigma$ = 50nH, $C_\sigma$ = 10pF<br>See Fig. 3-1, 3-2. | - | 20 | - | ns |
| Reverse recovery charge | $Q_{rr}$ *8 | | - | 130 | - | nC |
| Peak reverse recovery current | $I_{rrm}$ *8 | | - | 12 | - | A |


*1 Limited by maximum $T_{vj}$ and for Max. $R_{thJC}$.

*2 Pulse width and duty cycle are limited by $T_{vj,max}$.

*3 Only for body-diode, Repetitive pulse, PW ≤ 1.5μs, Duty cycle ≤ 5%

*4 When used as a protective function, PW ≤ 10μs

*5 Example of acceptable $V_{GS}$ waveform




*6 Please be advised not to use SiC-MOSFETs with $V_{GS}$ below 10V as doing so may cause thermal runaway.

*7 Tested after applying $V_{GS}$ = 21V for 100ms.

*8 Pulsed

*9 Measured conformable to JESD51-14.

See the application note "rthjc_measurement_and_usage_an-e.pdf". Link

URL: https://fscdn.rohm.com/en/products/databook/applinote/discrete/common/rthjc_measurement_and_usage_an-e.pdf

*10 Single Pulsed.


©2024 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

## ●Electrical characteristic curves

Fig.1 Power Dissipation Derating Curve





Fig.2 Maximum Safe Operating Area






Fig.3 Typical Transient Thermal Impedance vs. Pulse Width





©2024 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

## ●Electrical characteristic curves

Fig.4 $T_{vj}$ = 25ºC Typical Output Characteristics






Fig.5 $T_{vj}$ = 25ºC 3rd Quadrant Characteristics





©2024 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

## ●Electrical characteristic curves

Fig.6 $T_{vj}$ = 150ºC Typical Output Characteristics





Fig.7 $T_{vj}$ = 150ºC 3rd Quadrant Characteristics






Fig.8 Body Diode Forward Voltage vs. Gate - Source Voltage





©2024 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

## ●Electrical characteristic curves

Fig.9 Typical Transfer Characteristics (I)





Fig.10 Typical Transfer Characteristics (II)





Fig.11 Gate Threshold Voltage vs. Virtual Junction Temperature






Fig.12 Transconductance vs. Drain Current





©2024 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

## ●Electrical characteristic curves

Fig.13 Static Drain - Source On - State Resistance vs. Gate - Source Voltage





Fig.14 Static Drain - Source On - State Resistance vs. Virtual Junction Temperature





Fig.15 Static Drain - Source On - State Resistance vs. Drain Current






Fig.16 Normalized Drain - Source Breakdown Voltage vs. Virtual Junction Temperature





©2024 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

## ●Electrical characteristic curves

Fig.17 Typical Capacitance vs. Drain - Source Voltage





Fig.18 $C_{oss}$ Stored Energy vs. Drain - Source Voltage






Fig.19 Dynamic Input Characteristics





©2024 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

## ●Electrical characteristic curves

Fig.20 Typical Switching Time vs. External Gate Resistance





Fig.21 Typical Switching Loss vs. Drain - Source Voltage





Fig.22 Typical Switching Loss vs. Drain Current






Fig.23 Typical Switching Loss vs. External Gate Resistance





©2024 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

## ●Measurement circuits and waveforms

Fig.1-1 Gate Charge Measurement Circuit





Fig.1-2 Gate Charge Waveform





Fig.2-1 Switching Characteristics Measurement Circuit





Fig.2-2 Waveforms for Switching Time





Fig.2-3 Waveforms for Switching Energy Loss





Fig.3-1 Reverse Recovery Time Measurement Circuit






Fig.3-2 Reverse Recovery Waveform






©2024 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.


## ●Package Dimensions




Unit: mm


©2024 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.





Unit: mm


©2024 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

## ●Die Bonding Layout




・Front view of the packaging.

・Dimensions are design values.

・If the heat sink is to be installed, it should be in contact with the die bonding point.

Unit: mm


©2024 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.

## Notes

1) The information contained herein is subject to change without notice.

2) Before you use our Products, please contact our sales representative and verify the latest specifications.

3) Although ROHM is continuously working to improve product reliability and quality, semiconductors can break down and malfunction due to various factors.
Therefore, in order to prevent personal injury or fire arising from failure, please take safety measures such as complying with the derating characteristics, implementing redundant and fire prevention designs, and utilizing backups and fail-safe procedures. ROHM shall have no responsibility for any damages arising out of the use of our Poducts beyond the rating specified by ROHM.

4) Examples of application circuits, circuit constants and any other information contained herein are provided only to illustrate the standard usage and operations of the Products. The peripheral conditions must be taken into account when designing circuits for mass production.

5) The technical information specified herein is intended only to show the typical functions of and examples of application circuits for the Products. ROHM does not grant you, explicitly or implicitly, any license to use or exercise intellectual property or other rights held by ROHM or any other parties. ROHM shall have no responsibility whatsoever for any dispute arising out of the use of such technical information.

6) The Products specified in this document are not designed to be radiation tolerant.

7) For use of our Products in applications requiring a high degree of reliability (as exemplified below), please contact and consult with a ROHM representative : transportation equipment (i.e. cars, ships, trains), primary communication equipment, traffic lights, fire/crime prevention, safety equipment, medical systems, and power transmission systems.

8) Do not use our Products in applications requiring extremely high reliability, such as aerospace equipment, nuclear power control systems, and submarine repeaters.

9) ROHM shall have no responsibility for any damages or injury arising from non-compliance with the recommended usage conditions and specifications contained herein.

10) ROHM has used reasonable care to ensure the accuracy of the information contained in this document. However, ROHM does not warrants that such information is error-free, and ROHM shall have no responsibility for any damages arising from any inaccuracy or misprint of such information.

11) Please use the Products in accordance with any applicable environmental laws and regulations, such as the RoHS Directive. For more details, including RoHS compatibility, please contact a ROHM sales office. ROHM shall have no responsibility for any damages or losses resulting non-compliance with any applicable laws or regulations.

12) When providing our Products and technologies contained in this document to other countries, you must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the US Export Administration Regulations and the Foreign Exchange and Foreign Trade Act.

13) This document, in part or in whole, may not be reprinted or reproduced without prior consent of ROHM.

ROHM SEMICONDUCTOR

Thank you for your accessing to ROHM product informations.
More detail product informations and catalogs are available, please contact us.

ROHM Customer Support System

http://www.rohm.com/contact/


© 2012 ROHM Co., Ltd. All rights reserved.


Downloaded from Arrow.com.

## General Precaution

1. Before you use our Products, you are requested to carefully read this document and fully understand its contents. ROHM shall not be in any way responsible or liable for failure, malfunction or accident arising from the use of any ROHM's Products against warning, caution or note contained in this document.

2. All information contained in this document is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sales representative.

3. The information contained in this document is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate and/or error-free. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.


© 2015 ROHM Co., Ltd. All rights reserved.

Downloaded from Arrow.com.