


Low voltage 16-bit constant current LED sink driver with auto power-saving



Maturity status link

[STP16CPPS05](#)

Features

- Low voltage power supply down to 3 V
- 16 constant current output channels
- Adjustable output current through external resistor
- Serial data IN/parallel data OUT
- Auto power-saving
- 3.3 V MCU-driving capability
- Output current: 3 to 40 mA
- 30 MHz clock frequency
- Available in high thermal efficiency TSSOP exposed pad
- ESD protection: 2 kV HBM, 200 V MM

Description

The STP16CPPS05 is a monolithic, low voltage, low current power 16-bit shift register designed for LED panel displays. The device features a 16-bit serial-in, parallel-out shift register that feeds a 16-bit D-type storage register. In the output stage, sixteen regulated current sources are designed to provide 3 to 40 mA of constant current to drive the LEDs.

The STP16CPPS05 output current can be adjusted through an external resistor to control the light intensity of the LEDs. LED brightness is adjustable from 0% to 100% via the OE pin.

The auto power-shutdown and auto power-ON feature allows the device to save power with no external intervention.

The STP16CPPS05 guarantees a 20 V output driving capability, allowing users to connect more LEDs in series. The high 30 MHz clock frequency makes the device suitable for high data rate transmission. The 3.3 V supply is well suited for applications which interface a 3.3 V MCU. Compared to a standard TSSOP package, the TSSOP with exposed pad increases heat dissipation capability by a factor of 2.5.


1 Summary description

Table 1. Typical current accuracy

Output voltage	Current accuracy		Output current	V _{DD}	Temperature
	Between bits	Between ICs			
≥ 1.3 V	± 1%	± 2%	5 to 40 mA	3.3 V to 5 V	25 °C

1.1 Pin connection and description

Figure 1. Pin connection



GIPD180320161202MT

Note: The exposed pad should be electrically connected to a metal land electrically isolated or connected to ground.

Table 2. Pin description

Pin n°	Symbol	Name and function
1	GND	Ground terminal
2	SDI	Serial data input terminal
3	CLK	Clock input terminal
4	LE	Latch input terminal - detect mode 1 (see operation principle)
5-20	OUT 0-15	Output terminal
21	$\overline{OE}$	Input terminal of output enable (active low) - detect mode 1 (see operation principle)
22	SDO	Serial data out terminal
23	R-EXT	Input terminal for an external resistor for constant current programming
24	V _{DD}	Supply voltage terminal

2 Electrical ratings

2.1 Absolute maximum ratings

Stressing the device above the ratings listed in the “absolute maximum ratings” table may cause permanent damage to the device. These are stress ratings only and operation of the device at these or any other condition above those indicated in the operating sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Table 3. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{DD}	Supply voltage	0 to 7	V
V_O	Output voltage	-0.5 to 20	V
I_O	Output current	50	mA
V_I	Input voltage	-0.4 to V_{DD}	V
I_{GND}	GND terminal current	800	mA
f_{CLK}	Clock frequency	50	MHz
T_J	Junction temperature range ⁽¹⁾	-40 to +170	°C

1. Such absolute value is based on the thermal shutdown protection.

2.2 Thermal data

Table 4. Thermal data

Symbol	Parameter		Value	Unit
T _A	Operating free-air temperature range		-40 to +125	°C
T _{J-OPR}	Operating thermal junction temperature range		-40 to +150	°C
T _{STG}	Storage temperature range		-55 to +150	°C
R _{thJA}	Thermal resistance junction-ambient ⁽¹⁾	SO-24	42.7	°C/W
		TSSOP24	55	°C/W
		TSSOP24 ⁽²⁾ exposed pad	37.5	°C/W
		QSOP-24	55	°C/W

1. According with JEDEC standard 51-7B.

2. The exposed pad should be soldered directly to the PCB to realize the thermal benefits.

2.3 Recommended operating conditions

Table 5. Recommended operating conditions

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
V_{DD}	Supply voltage		3.0		5.5	V
V_O	Output voltage				20	V
I_O	Output current	OUTn	3		40	mA
I_{OH}	Output current	SERIAL-OUT			+1	mA

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
I_{OL}	Output current	SERIAL-OUT			-1	mA
V_{IH}	Input voltage		$0.7 V_{DD}$		V_{DD}	V
V_{IL}	Input voltage		-0.3		$0.3 V_{DD}$	V
t_{wLAT}	LE pulse width	$V_{DD} = 3.0 \text{ V to } 5.0 \text{ V}$	20			ns
t_{wCLK}	CLK pulse width		10			ns
t_{wEN}	$\overline{OE}$ pulse width		100			ns
$t_{SETUP(D)}$	Setup time for DATA		8			ns
$t_{HOLD(D)}$	Hold time for DATA		5			ns
$t_{SETUP(L)}$	Setup time for LATCH		8			ns
f_{CLK}	Clock frequency	Cascade operation ⁽¹⁾			30	MHz

1. If the device is connected in cascade, it may not be possible to achieve the maximum data transfer. Please consider the timings carefully.

3 Electrical characteristics

$V_{DD} = 3.3 \text{ V to } 5 \text{ V}$, $T_A = 25 \text{ }^\circ\text{C}$, unless otherwise specified.

Table 6. Electrical characteristics

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
V_{IH}	Input voltage high level		$0.7 V_{DD}$		V_{DD}	V
V_{IL}	Input voltage low level		GND		$0.3 V_{DD}$	V
I_{OH}	Output leakage current	$V_{OH} = 20 \text{ V}$			1	μA
V_{OL}	Output voltage (serial-OUT)	$I_{OL} = 1 \text{ mA}$			0.4	V
V_{OH}	Output voltage (serial-OUT)	$I_{OH} = -1 \text{ mA}$	$V_{DD}-0.4 \text{ V}$			V
I_{OL1}	Output current	$V_O = 0.3 \text{ V}$, $R_{ext} = 4 \text{ k}\Omega$	4.75	5	5.25	mA
I_{OL2}		$V_O = 0.3 \text{ V}$, $R_{ext} = 1 \text{ k}\Omega$	19	20	20	
I_{OL3}		$V_O = 1.3 \text{ V}$, $R_{ext} = 497 \text{ }\Omega$	38	40	42	
ΔI_{OL1}	Output current error between bit (all output ON)	$V_O = 0.3 \text{ V}$, $I_O = 5 \text{ mA}$, $R_{ext} = 4 \text{ k}\Omega$		± 1	± 5	%
ΔI_{OL2}		$V_O = 0.3 \text{ V}$, $I_O = 20 \text{ mA}$, $R_{ext} = 980 \text{ }\Omega$		± 0.5	± 3	
ΔI_{OL3}		$V_O = 1.3 \text{ V}$, $I_O = 40 \text{ mA}$, $R_{ext} = 490 \text{ }\Omega$		± 0.5	± 3	
$R_{SIN(up)}$	Pull-up resistor		150	300	600	k Ω
$R_{SIN(down)}$	Pull-down resistor		100	200	400	k Ω
$I_{DD(OFF1)}$	Supply current (OFF)	$R_{EXT} = 1 \text{ k}\Omega$, $I_{OUT} = 20 \text{ mA}$, OUT 0 to 15 = OFF		5.4	7.5	mA
$I_{DD(OFF2)}$		$R_{EXT} = 497 \text{ }\Omega$, $I_{OUT} = 40 \text{ mA}$, OUT 0 to 15 = OFF		8.0	9.5	
$I_{DD(ON1)}$	Supply current (ON)	$R_{EXT} = 1 \text{ k}\Omega$, $I_{OUT} = 20 \text{ mA}$, OUT 0 to 15 = ON		5.5	7.5	
$I_{DD(ON2)}$		$R_{EXT} = 497 \text{ }\Omega$, $I_{OUT} = 40 \text{ mA}$, OUT 0 to 15 = ON		8.1	9.5	
$I_{DD(SH)}$	Shut-down current all latched data = L	$V_{DD} = 3.3 \text{ V}$		160	200	μA
		$V_{DD} = 5 \text{ V}$		190	240	
Thermal	Thermal protection			170		$^\circ\text{C}$

$V_{DD} = 3.3 \text{ V to } 5 \text{ V}$, $T_A = 25 \text{ }^\circ\text{C}$, unless otherwise specified.


Table 7. Switching characteristics

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
t_{PLH1}	Propagation delay time, CLK- $\overline{\text{OUTn}}$, LE = H, $\overline{\text{OE}} = \text{L}$	$V_{DD} = 3.3 \text{ V}$	-	53.5	86.5	ns
		$V_{DD} = 5 \text{ V}$	-	32	46.5	
t_{PLH2}	Propagation delay time, LE- $\overline{\text{OUTn}}$, $\overline{\text{OE}} = \text{L}$	$V_{DD} = 3.3 \text{ V}$	-	48	75.5	ns
		$V_{DD} = 5 \text{ V}$	-	30	43	
t_{PLH3}	$\overline{\text{OE}} - \overline{\text{OUTn}}$, LE = H Propagation delay time,	$V_{DD} = 3.3 \text{ V}$	-	71.5	118	ns
		$V_{DD} = 5 \text{ V}$	-	43	62	
t_{PLH}	CLK-SDO Propagation delay time,	$V_{DD} = 3.3 \text{ V}$	15	21	31	ns
		$V_{DD} = 5 \text{ V}$	11	15	21	
t_{PHL1}	CLK- $\overline{\text{OUTn}}$, LE = H, $\overline{\text{OE}} = \text{L}$ Propagation delay time,	$V_{DD} = 3.3 \text{ V}$	-	27.5	39	ns
		$V_{DD} = 5 \text{ V}$	-	22	30.5	
t_{PHL2}	LE- $\overline{\text{OUTn}}$, $\overline{\text{OE}} = \text{L}$ Propagation delay time,	$V_{DD} = 3.3 \text{ V}$	-	11.5	17.5	ns
		$V_{DD} = 5 \text{ V}$	-	8	11.5	
t_{PHL3}	$\overline{\text{OE}} - \overline{\text{OUTn}}$, LE = H Propagation delay time,	$V_{DD} = 3.3 \text{ V}$	-	24	33.5	ns
		$V_{DD} = 5 \text{ V}$	-	21	28.5	
t_{PHL}	CLK-SDO Propagation delay time,	$V_{DD} = 3.3 \text{ V}$	17.5	24	36	ns
		$V_{DD} = 5 \text{ V}$	12.5	17	25	
t_{ON}	10~90% of voltage waveform Output rise time	$V_{DD} = 3.3 \text{ V}$	-	29	54	ns
		$V_{DD} = 5 \text{ V}$	-	10	17	
t_{OFF}	90~10% of voltage waveform Output fall time	$V_{DD} = 3.3 \text{ V}$	-	4.5	6	ns
		$V_{DD} = 5 \text{ V}$	-	3.5	5	
t_r	CLK rise time ⁽¹⁾		-		5000	ns
t_f	CLK fall time ⁽¹⁾		-		5000	ns

1. In order to achieve high cascade data transfer, please consider t_r/t_f timings carefully.


4 Equivalent circuit of inputs and outputs

Figure 2. $\overline{OE}$ terminal




GIPD021120150913MT

Figure 3. LE terminal




GIPD021120150914MT

Figure 4. CLK, SDI terminal




GIPD290920151407MT

Figure 5. SDO terminal



AMG130220170700MT

Figure 6. Block diagram




GIPD180320161206MT

5 Timing diagrams

Table 8. Truth table

CLOCK	LE	$\overline{OE}$	SERIAL-IN	$\overline{OUT_0}$ $\overline{OUT_7}$ $\overline{OUT_{15}}$	SDO
	H	L	Dn	Dn Dn - 7 Dn -15	Dn - 15
	L	L	Dn + 1	No change	Dn - 14
	H	L	Dn + 2	Dn + 2 Dn - 5 Dn -13	Dn - 13
	X	L	Dn + 3	Dn + 2 Dn - 5 Dn -13	Dn - 13
	X	H	Dn + 3	OFF	Dn - 13

Note: $OUTn = ON$ when $Dn = H$ $OUTn = OFF$ when $Dn = L$.

Figure 7. Timing diagram


Note: 1 Latch and output enable terminals are level-sensitive and are not synchronized with rising or falling edge of CLK signal. 2 When LE terminal is low level, the latch circuit holds previous set of data. 3 When LE terminal is high level, the latch circuit refreshes new set of data from SDI chain. 4 When $\overline{OE}$ terminal is at low level, the output terminals Out 0 to Out 15 respond to data in the latch circuits, either '1' for ON or '0' for OFF. 5 When $\overline{OE}$ terminal is at high level, all output terminals are switched OFF.


Table 9. Enable IO: shutdown truth table

CLOCK	LE	SDI ₀ SDI ₇ SDI ₁₅	SH	Auto power-up	OUTn
	H	All = L	Active	Not active ⁽¹⁾	OFF
	L	No change	No change	No change	No change
	H	One or more = H	Not active	Active	X ⁽²⁾


1. At power-up, the device starts in shutdown mode.

2. Undefined.

Figure 8. Clock, serial-in, serial-out




AMG130220170701MT

Figure 9. Clock, serial-in, latch, enable, outputs


CS17060

* Only for detection feature.

AMG130220170702MT


Figure 10. Outputs


CS17070

GIPD300920151146MT

6 Typical characteristics

Figure 11. Output current vs. R-EXT resistor




GIPD150320161209MT

Table 10. Output current vs. R-EXT resistor

R-EXT (Ω)	Output current (mA)
23700	1
11730	2
6930	3
4090	5
2025	10
1000	20
667	30
497	40
331	60

Conditions:

Temperature = 25 °C, V_{DD} = 3.3 V; 5.0 V, I_{SET} = 3 mA; 5 mA; 10 mA; 20 mA; 50 mA; 60 mA.

Figure 12. I_{SET} vs drop out voltage (V_{drop})



GIPD150320161228MT

Table 11. I_{SET} vs drop out voltage (V_{drop})

I_{out} (mA)	Avg (mV) @ 3.3 V	Avg (mV)@ 5.0 V
3	36	37
5	71	72
10	163	163
20	346	347
40	724	724
60	1080	1110


 $T_A = 25\text{ }^{\circ}\text{C}$, $V_{dd} = 3.3\text{ V}; 5\text{ V}$

Figure 13. Output current vs. $\pm \Delta I_{OL}(\%)$




GIPD210320161330MT

Figure 14. Idd ON/OFF




GIPD210320161334MT

Figure 15. Power dissipation vs. package temperature


GIPD210320161340MT

Note: The exposed pad should be soldered to the PCB to obtain the thermal benefits.

Figure 16. Turn ON output current characteristics


GIPD210320161342MT

Figure 17. Turn OFF output current characteristics


GIPD210320161343MT

1. The reference level for the T_{ON} characteristics is 50% of $\overline{OE}$ signal and 90% of output current.
2. The reference level for the T_{OFF} characteristics is 50% of $\overline{OE}$ signal and 10% of output current.

Electrical conditions:

 $V_{DD} = 3.3\text{ V}$, $V_{IN} = V_{DD}$, $V_{LED} = 3.0\text{ V}$, $R_L = 60\ \Omega$, $C_L = 10\text{ pF}$
 $\text{Ch1 (Yellow)} = \overline{OE}$, $\text{Ch2 (Blue)} = \text{CLK}$, $\text{Ch3 (Purple)} = \text{VOUT}$, $\text{Ch4 (Green)} = \text{OUT}$

7 Auto power-saving

The auto power-saving feature minimizes the quiescent current if no active data is detected on the latches and auto powers-up the device as the first active data is latched.

Figure 18. Auto power-saving feature



GIPD210320161354MT

Electrical conditions:

Temp. = 25 °C, Vdd = 3.3 V, Vin = Vdd, Vled = 3.0 V, RL = 60 Ω, CL = 10 pF

Ch1 (Yellow) = $\overline{OE}$, Ch2 (Blue) = CLK, Ch3 (Purple) = LE, Ch4 (Green) = idd

Idd consumption:

Idd (normal operation) = 4.2 mA

Idd (shut down condition) = 190 μA

Figure 19. First output ON after switching from auto power saving to normal operating condition



GIPD210320161355MT

Electrical conditions:

temp. = 25 °C, Vdd = 3.3 V, Vin = Vdd, Vled = 3.0 V, Iset = 20 mA

Ch1 (Yellow) = SDI, Ch2 (Blue) = CLK, Ch3 (Purple) = LE, Ch4 (Green) = first output ON

Note: *When the device goes from AUTO power saving to normal operative condition, the first output that switch ON shows TON condition as seen in the plot above.*

8 Package information


In order to meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

Table 12. QSOP-24 mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	1.54	1.62	1.73
A1	0.10	0.15	0.25
A2		1.47	
b	0.20		0.31
c	0.17		0.254
D	8.56	8.66	8.76
E	5.80	6.00	6.20
E1	3.80	3.91	4.01
e		0.635	
L	0.40	0.635	0.89
h	0.25	0.33	0.41
<	0°		8°

8.2 SO-24 0070769 package information

Figure 21. SO-24 package outline



0070769


Table 13. SO-24 mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	2.35		2.65
A1	0.10		0.30
B	0.33		0.51

Dim.	mm		
	Min.	Typ.	Max.
C	0.23		0.32
D	15.20		15.60
E	7.40		7.60
e		1.27	
H	10.00		10.65
h	0.25		0.75
L	0.40		1.27
k	0		8
ddd			0.10

8.3 TSSOP24 package information

Figure 22. TSSOP24 package outline



7047476B

Table 14. TSSOP24 mechanical data


Dim.	mm		
	Min.	Typ.	Max.
A			1.1
A1	0.05		0.15
A2		0.9	
b	0.19		0.30
c	0.09		0.20
D	7.7		7.9
E	4.3		4.5
e		0.65 BSC	



Dim.	mm		
	Min.	Typ.	Max.
H	6.25		6.5
K	0°		8°
L	0.50		0.70

8.4 TSSOP24 exposed pad package information

Figure 23. TSSOP24 exposed pad package outline



7100778_D

Table 15. TSSOP24 exposed pad mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A			1.20
A1			0.15
A2	0.80	1.00	1.05
b	0.19		0.30
c	0.09		0.20
D	7.70	7.80	7.90
D1	4.80	5.00	5.2
E	6.20	6.40	6.60
E1	4.30	4.40	4.50
E2	3.00	3.20	3.40
e		0.65	
L	0.45	0.60	0.75
L1		1.00	
k	0°		8°
aaa			0.10

8.5 TSSOP24, TSSOP24 exposed pad and SO-24 packing information

Figure 24. TSSOP24, TSSOP24 exposed pad and SO-24 reel outline




Table 16. TSSOP24 and TSSOP24 exposed pad tape and reel mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	330	-	331
C	13.0	-	14.0
D	18.7	-	
N	100	-	
T	16.5	-	18.5
Ao	6.85	-	7.05
Bo	8.20	-	8.40
Ko	1.5	-	1.7
Po	3.9	-	4.1
P	7.9	-	8.1

Table 17. SO-24 tape and reel mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A		-	330
C	12.8	-	13.2
D	20.2	-	
N	60	-	
T		-	30.4
Ao	10.8	-	11.0
Bo	15.7	-	15.9
Ko	2.9	-	3.1
Po	3.9	-	4.1
P	11.9	-	12.1

9 Device Summary

Table 18. Order codes

Order code	Package	Packing
STP16CPPS05TTR	TSSOP24	2500 parts per reel
STP16CPPS05XTTR	TSSOP24 exposed pad	2500 parts per reel
STP16CPPS05PTR	QSOP-24	2500 parts per reel

Revision history

Table 19. Document revision history

Date	Revision	Changes
23-Oct-2009	1	First release.
16-Jun-2014	2	Updated Section 7: Package mechanical data. Added Section 8: Packaging mechanical data. Minor text changes.
08-Apr-2016	3	Updated <i>Section 8.1: "QSOP-24 package information"</i> . Minor text changes.
09-Mar-2017	4	Updated Figure 5. SDO terminal, Figure 8. Clock, serial-in, serial-out and Figure 9. Clock, serial-in, latch, enable, outputs. Minor text changes.
18-Jun-2024	5	Updated Table 18

Contents

1	Summary description	2
1.1	Pin connection and description	2
2	Electrical ratings	3
2.1	Absolute maximum ratings	3
2.2	Thermal data	3
2.3	Recommended operating conditions	3
3	Electrical characteristics	5
4	Equivalent circuit of inputs and outputs	7
5	Timing diagrams	10
6	Typical characteristics	13
7	Auto power-saving	17
8	Package information	19
8.1	QSOP-24 package information	20
8.2	SO-24 0070769 package information	22
8.3	TSSOP24 package information	23
8.4	TSSOP24 exposed pad package information	25
8.5	TSSOP24, TSSOP24 exposed pad and SO-24 packing information	27
9	Device Summary	29
	Revision history	30

List of tables

Table 1.	Typical current accuracy	2
Table 2.	Pin description	2
Table 3.	Absolute maximum ratings	3
Table 4.	Thermal data	3
Table 5.	Recommended operating conditions	3
Table 6.	Electrical characteristics	5
Table 7.	Switching characteristics	6
Table 8.	Truth table	10
Table 9.	Enable IO: shutdown truth table	10
Table 10.	Output current vs. R-EXT resistor	13
Table 11.	I _{SET} vs drop out voltage (V _{drop})	14
Table 12.	QSOP-24 mechanical data	21
Table 13.	SO-24 mechanical data	22
Table 14.	TSSOP24 mechanical data	23
Table 15.	TSSOP24 exposed pad mechanical data	26
Table 16.	TSSOP24 and TSSOP24 exposed pad tape and reel mechanical data	27
Table 17.	SO-24 tape and reel mechanical data	28
Table 18.	Order codes	29
Table 19.	Document revision history	30

List of figures

Figure 1.	Pin connection	2
Figure 2.	$\overline{\text{OE}}$ terminal	7
Figure 3.	LE terminal	7
Figure 4.	CLK, SDI terminal	8
Figure 5.	SDO terminal	8
Figure 6.	Block diagram	9
Figure 7.	Timing diagram	10
Figure 8.	Clock, serial-in, serial-out	11
Figure 9.	Clock, serial-in, latch, enable, outputs	12
Figure 10.	Outputs	12
Figure 11.	Output current vs. R-EXT resistor	13
Figure 12.	I_{SET} vs drop out voltage (V_{drop})	14
Figure 13.	Output current vs. $\pm \Delta I_{\text{OL}}(\%)$	15
Figure 14.	I_{dd} ON/OFF	15
Figure 15.	Power dissipation vs. package temperature	16
Figure 16.	Turn ON output current characteristics	16
Figure 17.	Turn OFF output current characteristics	16
Figure 18.	Auto power-saving feature	17
Figure 19.	First output ON after switching from auto power saving to normal operating condition	18
Figure 20.	QSOP-24 package outline	20
Figure 21.	SO-24 package outline	22
Figure 22.	TSSOP24 package outline	23
Figure 23.	TSSOP24 exposed pad package outline	25
Figure 24.	TSSOP24, TSSOP24 exposed pad and SO-24 reel outline	27

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2024 STMicroelectronics – All rights reserved