3x3 MIMO

The Frontline 802.11
Protocol Analyzer includes
powerful Frontline software and
the 802.11 a/b/g/n hardware
interface.

Key Features and Benefits

- 3x3 MIMO (3 streams)
- Get the Data You Need
 Fewer dropped packets with our built-in ~250GB buffer
- Trust the Data You Get
 Get exact timing information
 for each packet the Frontline
 802.11 provides reliable and
 accurate timestamps for all
 packets
- Coexistence Packets in Lock-Step

In tandem with the Frontline Sodera or BPA 600, the coexistence window combines 802.11 and Bluetooth 4.0+HS packets into one view with precise timestamp synchronization using Frontline's ProbeSync technology

Up-to-the-Minute Decodes
 Means Thorough Analysis
 Analyze devices using the
 spectrum of 802.11 protocols 802.11 a/b/g/n support means
 you don't have to wonder if an
 802.11 protocol is supported



frontline **802.11**

802.11 a/b/g/n Protocol Analyzer

The Frontline 802.11 protocol analyzer lets you passively capture wireless traffic like never before, and stands as the **first 3x3 MIMO Bluetooth® coexistence solution on the market**. No other device available today provides the precision, reliability, or capacity to gather wireless data better than the Frontline 802.11 protocol analyzer.


The sheer volume of 802.11 data flowing between devices can be staggering, but gone are the days when you missed or dropped large numbers of packets because your analyzer simply couldn't keep up with the amount of data flowing through the air. Frontline has met the challenge head-on by building into the Frontline 802.11 analyzer a staggering ~250GB data buffer.

Bluetooth Coexistence


The analysis of 802.11 and Bluetooth data packets in one view is possibly one of the most challenging tasks for wireless device developers. Capturing the precise timing, size, and frequency of each and every packet is essential to successfully developing and debugging devices using both technologies, and until now has been, at best, an elusive objective.

- Massive buffer fewer dropped packets
- 3x3 MIMO (3 streams)
- Precise packet synchronization with Bluetooth data with the Frontline Sodera
- Improved coexistence view
- Spectrum analysis

Either as a stand-alone 802.11 or in combination with the Frontline Sodera or BPA 600, the Frontline 802.11 is the precise and comprehensive analysis tool you need for 802.11 and Bluetooth over 802.11 wireless communications.



energy packets in a single view



Specifications

- Supports IEEE 802.11 a/b/g/n specifications
- Features 3x3 MIMO technology
- Supports WEP and AES-CCN (i.e. WPA2 PSK) decryption
- Supports 2.4 and 5.0 GHz bands
- 802.11n (High Throughput) MCS: 0 to 15
- 20 and 40 MHz channel widths
- Short guard interval support for both 20 MHz and 40 MHz channels
- Supports data rates of up to 216.7 Mbps for 20 MHz channels and 450 Mbps for 40 MHz channels
- Frame encoding: BCC (Default for 802.11), LDPC (Option for 802.11n)
- Max AMPDU size: 65,535 bytes

• Bus Type:

USB 2.0 Type B, compatible with USB1.1

• Operating Frequencies:

2.412GHz – 2.4835 GHz 5.15 - 5.85 GHz

• Power:

AC Adapter supplied. The output of the adapter is 12Vdc, 2.5A

• Dimensions:

6.563" X 4.055" X 2.087" 167mm X 103mm X 53mm

• Temperature:

0° to 30° Celsius 32° to 86° Fahrenheit

• Humidity:

Operating: 10% to 90% RH (noncondensing)

Receive Sensitivity

802.11a: -68dBm ±2dBm@54Mbps 802.11b: -85dBm ±2dBm@11Mbps 802.11g: -68dBm ±2dBm@54Mbps 802.11gn HT20: -68dBm ±2dBm@MCS7 802.11gn HT40: -68dBm ±2dBm@MCS7 802.11an HT20: -68dBm ±2dBm@MCS7 802.11an HT40: -68dBm ±2dBm@MCS7

Modulation

802.11a: OFDM (BPSK, QPSK, 16-QAM, 64-QAM) 802.11b: DSSS (DBPSK, DQPSK, CCK) 802.11g: OFDM (BPSK, QPSK, 16-QAM, 64-QAM)

802.11n: OFDM (BPSK, QPSK, 16-QAM,

64-QAM)

The Frontline 802.11 Hardware Interface

The Frontline 802.11 Protocol Analyzer includes the portable and robust 802.11 3x3 a/b/g/n hardware interface, which supports connectivity to 802.11 wireless communications.

The 802.11 a/b/g/n hardware interface is one member of an extensive arsenal of technology-specific hardware interfaces, all functioning with the powerful Frontline software. This modular approach allows greater flexibility in protocol analysis and debugging, and provides comprehensive views over virtually any combination of protocols.

Supported Configurations

• OS Supported: Windows 7, 8 and 10


• USB Port: USB 2.0 or USB 3.0 High-Speed

Minimum System Requirements

Processor: Core i5 processor at 2.7 GHz

RAM: 4 GB

• Free Hard Disk Space: 20 GB



The Frontline Modular Approach

Frontline software is at the core of Frontline protocol analysis, allowing technology-specific hardware interfaces to work individually or in combination with other hardware interfaces. This modular approach gives the developer or analyst the widest possible range of scenarios for debugging complex communications.

To order or for more information:

www.fte.com frontline_onlinesales@teledyne.com 1.800.359.8570 US & Canada +1.434.984.4500

Fax: 434.984.4505



© Copyright 2018. All rights reserved. BPA, Sodera and the Frontline logo are trademarks and Frontline is registered trademark. The Bluetooth word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks is under license. Other trademarks and trade names are those of their respective owners.