




## DYNAMIC D1000 SLIM CONNECTOR

Dynamic D1000 slim small wire-to-board and wire-to-wire connector is suitable for narrow and Robotic applications spaces in small industrial equipment, small machinery applications.

The size of the D1000 Slim is 50% smaller than the D1200 series with low interference risk and streamlined design.

Dynamic D-1000 slim Series provide gold plated contacts to maintain its high reliability and also tin plated contacts for economical market needs. Customers can choose their own contacts according to specifications, applications and cost.

Keying and the locking feature provides reliability and reduces unexpected unmating and lever breakage in narrow spaces such as robotic arms and other customer applications.

### BENEFITS

- Smaller size increases the connectivity per used space
- Reducing risk of connector breakage by interference in narrow space
- Reliability increased as the user can hear when connector is properly locked
- Easy mating and crimping process to speed up installation time

## DYNAMIC D1000 SLIM CONNECTOR

### APPLICATIONS

- Robotics
  - Small industrial robot
  - Collaborative robot
  - Scala robot
- Automatic-guided vehicle (AGV)
- Servo motor
- Sensors

### ELECTRICAL

- **Current rating:** 4.5A/pos  
(at 4pos AWG #22 **Temperature rising:** 30°C max)
- **Voltage rating:** AC/DC 250V max
- **Withstand voltage:** AC 1,500 V/1 minutes

### MECHANICAL

- **Mating times:** 30

### MATERIALS

- **HSG:** Thermo plastic, UL 94V-0, black
- **Contact:** Copper alloy

### SPECIFICATIONS

- **Applicable wire size:** AWG #22 to #30
- **Applicable temperature:** -55°C to +125°C

### PART NUMBER LIST

| Part Type         | Part Description          | Black                       | Natural | Blue |
|-------------------|---------------------------|-----------------------------|---------|------|
| HDR Au<br>Plating | D1SLIM HDR V ASSY Au X 2P | <a href="#">1-2498846-2</a> | -       | -    |
|                   | D1SLIM HDR V ASSY Au Y 2P | <a href="#">2-2498846-2</a> | -       | -    |
|                   | D1SLIM HDR V ASSY Au X 3P | <a href="#">1-2498846-3</a> | -       | -    |
|                   | D1SLIM HDR V ASSY Au Y 3P | <a href="#">2-2498846-3</a> | -       | -    |
|                   | D1SLIM HDR V ASSY Au X 4P | <a href="#">1-2498846-4</a> | -       | -    |
|                   | D1SLIM HDR V ASSY Au Y 4P | <a href="#">2-2498846-4</a> | -       | -    |
|                   | D1SLIM HDR V ASSY Au X 6P | <a href="#">1-2498846-6</a> | -       | -    |
|                   | D1SLIM HDR V ASSY Au Y 6P | <a href="#">2-2498846-6</a> | -       | -    |
|                   | D1SLIM HDR V ASSY Au X 8P | <a href="#">1-2498846-8</a> | -       | -    |
|                   | D1SLIM HDR V ASSY Au Y 8P | <a href="#">2-2498846-8</a> | -       | -    |

## DYNAMIC D1000 SLIM CONNECTOR

| Part Type       | Part Description           | Black                       | Natural                     | Blue                        |
|-----------------|----------------------------|-----------------------------|-----------------------------|-----------------------------|
| HDR Tin Plating | D1SLIM HDR V ASSY Tin X 2P | <a href="#">1-2499863-2</a> | -                           | -                           |
|                 | D1SLIM HDR V ASSY Tin Y 2P | <a href="#">2-2499863-2</a> | -                           | -                           |
|                 | D1SLIM HDR V ASSY Tin X 3P | <a href="#">1-2499863-3</a> | -                           | -                           |
|                 | D1SLIM HDR V ASSY Tin Y 3P | <a href="#">2-2499863-3</a> | -                           | -                           |
|                 | D1SLIM HDR V ASSY Tin X 4P | <a href="#">1-2499863-4</a> | -                           | -                           |
|                 | D1SLIM HDR V ASSY Tin Y 4P | <a href="#">2-2499863-4</a> | -                           | -                           |
|                 | D1SLIM HDR V ASSY Tin X 6P | <a href="#">1-2499863-6</a> | -                           | -                           |
|                 | D1SLIM HDR V ASSY Tin Y 6P | <a href="#">2-2499863-6</a> | -                           | -                           |
|                 | D1SLIM HDR V ASSY Tin X 8P | <a href="#">1-2499863-8</a> | -                           | -                           |
|                 | D1SLIM HDR V ASSY Tin Y 8P | <a href="#">2-2499863-8</a> | -                           | -                           |
| REC Housing     | REC HSG 2P X KEY           | <a href="#">1-2375948-2</a> | <a href="#">5-2375948-2</a> | <a href="#">7-2375948-2</a> |
|                 | REC HSG 2P Y KEY           | <a href="#">2-2375948-2</a> | <a href="#">6-2375948-2</a> | <a href="#">8-2375948-2</a> |
|                 | REC HSG 3P X KEY           | <a href="#">1-2375948-3</a> | <a href="#">5-2375948-3</a> | <a href="#">7-2375948-3</a> |
|                 | REC HSG 3P Y KEY           | <a href="#">2-2375948-3</a> | <a href="#">6-2375948-3</a> | <a href="#">8-2375948-3</a> |
|                 | REC HSG 4P X KEY           | <a href="#">1-2366515-4</a> | <a href="#">5-2366515-4</a> | <a href="#">7-2366515-4</a> |
|                 | REC HSG 4P Y KEY           | <a href="#">2-2366515-4</a> | <a href="#">6-2366515-4</a> | <a href="#">8-2366515-4</a> |
|                 | REC HSG 5P X KEY           | <a href="#">1-2375948-5</a> | <a href="#">5-2375948-5</a> | <a href="#">7-2375948-5</a> |
|                 | REC HSG 5P Y KEY           | <a href="#">2-2375948-5</a> | <a href="#">6-2375948-5</a> | <a href="#">8-2375948-5</a> |
|                 | REC HSG 6P X KEY           | <a href="#">1-2366515-6</a> | <a href="#">5-2366515-6</a> | <a href="#">7-2366515-6</a> |
|                 | REC HSG 6P Y KEY           | <a href="#">2-2366515-6</a> | <a href="#">6-2366515-6</a> | <a href="#">8-2366515-6</a> |
|                 | REC HSG 7P X KEY           | <a href="#">1-2375948-7</a> | <a href="#">5-2375948-7</a> | <a href="#">7-2375948-7</a> |
|                 | REC HSG 7P Y KEY           | <a href="#">2-2375948-7</a> | <a href="#">6-2375948-7</a> | <a href="#">8-2375948-7</a> |
|                 | REC HSG 8P X KEY           | <a href="#">1-2366515-8</a> | <a href="#">5-2366515-8</a> | <a href="#">7-2366515-8</a> |
|                 | REC HSG 8P Y KEY           | <a href="#">2-2366515-8</a> | <a href="#">6-2366515-8</a> | <a href="#">8-2366515-8</a> |
|                 | REC HSG 9P X KEY           | <a href="#">1-2375948-9</a> | <a href="#">5-2375948-9</a> | <a href="#">7-2375948-9</a> |
|                 | REC HSG 9P Y KEY           | <a href="#">2-2375948-9</a> | <a href="#">6-2375948-9</a> | <a href="#">8-2375948-9</a> |

## DYNAMIC D1000 SLIM CONNECTOR

| Part Type   | Part Description  | Black                       | Natural                     | Blue                        |
|-------------|-------------------|-----------------------------|-----------------------------|-----------------------------|
| REC Housing | REC HSG 12P X KEY | <a href="#">3-2366515-2</a> | <a href="#">5-2366515-2</a> | <a href="#">7-2366515-2</a> |
|             | REC HSG 12P Y KEY | <a href="#">4-2366515-2</a> | <a href="#">6-2366515-2</a> | <a href="#">8-2366515-2</a> |
|             | REC HSG 18P X KEY | <a href="#">1-2423582-8</a> | <a href="#">5-2423582-8</a> | <a href="#">7-2423582-8</a> |
|             | REC HSG 18P Y KEY | <a href="#">2-2423582-8</a> | <a href="#">6-2423582-8</a> | <a href="#">8-2423582-8</a> |
|             | REC HSG 24P X KEY | <a href="#">1-2420333-4</a> | <a href="#">5-2420333-4</a> | <a href="#">7-2420333-4</a> |
|             | REC HSG 24P Y KEY | <a href="#">2-2420333-4</a> | <a href="#">6-2420333-4</a> | <a href="#">8-2420333-4</a> |
| TAB Housing | TAB HSG 2P X KEY  | <a href="#">1-2375951-2</a> | <a href="#">5-2375951-2</a> | <a href="#">7-2375951-2</a> |
|             | TAB HSG 2P Y KEY  | <a href="#">2-2375951-2</a> | <a href="#">6-2375951-2</a> | <a href="#">8-2375951-2</a> |
|             | TAB HSG 3P X KEY  | <a href="#">1-2375951-3</a> | <a href="#">5-2375951-3</a> | <a href="#">7-2375951-3</a> |
|             | TAB HSG 3P Y KEY  | <a href="#">2-2375951-3</a> | <a href="#">6-2375951-3</a> | <a href="#">8-2375951-3</a> |
|             | TAB HSG 4P X KEY  | <a href="#">1-2366600-4</a> | <a href="#">5-2366600-4</a> | <a href="#">7-2366600-4</a> |
|             | TAB HSG 4P Y KEY  | <a href="#">2-2366600-4</a> | <a href="#">6-2366600-4</a> | <a href="#">8-2366600-4</a> |
|             | TAB HSG 5P X KEY  | <a href="#">1-2375951-5</a> | <a href="#">5-2375951-5</a> | <a href="#">7-2375951-5</a> |
|             | TAB HSG 5P Y KEY  | <a href="#">2-2375951-5</a> | <a href="#">6-2375951-5</a> | <a href="#">8-2375951-5</a> |
|             | TAB HSG 6P X KEY  | <a href="#">1-2366600-6</a> | <a href="#">5-2366600-6</a> | <a href="#">7-2366600-6</a> |
|             | TAB HSG 6P Y KEY  | <a href="#">2-2366600-6</a> | <a href="#">6-2366600-6</a> | <a href="#">8-2366600-6</a> |
|             | TAB HSG 7P X KEY  | <a href="#">1-2375951-7</a> | <a href="#">5-2375951-7</a> | <a href="#">7-2375951-7</a> |
|             | TAB HSG 7P Y KEY  | <a href="#">2-2375951-7</a> | <a href="#">6-2375951-7</a> | <a href="#">8-2375951-7</a> |
|             | TAB HSG 8P X KEY  | <a href="#">1-2366600-8</a> | <a href="#">5-2366600-8</a> | <a href="#">7-2366600-8</a> |
|             | TAB HSG 8P Y KEY  | <a href="#">2-2366600-8</a> | <a href="#">6-2366600-8</a> | <a href="#">8-2366600-8</a> |
|             | TAB HSG 9P X KEY  | <a href="#">1-2375951-9</a> | <a href="#">5-2375951-9</a> | <a href="#">7-2375951-9</a> |
|             | TAB HSG 9P Y KEY  | <a href="#">2-2375951-9</a> | <a href="#">6-2375951-9</a> | <a href="#">8-2375951-9</a> |
|             | TAB HSG 12P X KEY | <a href="#">3-2366600-2</a> | <a href="#">5-2366600-2</a> | <a href="#">7-2366600-2</a> |
|             | TAB HSG 12P Y KEY | <a href="#">4-2366600-2</a> | <a href="#">6-2366600-2</a> | <a href="#">8-2366600-2</a> |
|             | TAB HSG 18P X KEY | <a href="#">1-2423584-8</a> | <a href="#">5-2423584-8</a> | <a href="#">7-2423584-8</a> |
|             | TAB HSG 18P Y KEY | <a href="#">2-2423584-8</a> | <a href="#">6-2423584-8</a> | <a href="#">8-2423584-8</a> |
|             | TAB HSG 24P X KEY | <a href="#">1-2420334-4</a> | <a href="#">5-2420334-4</a> | <a href="#">7-2420334-4</a> |
|             | TAB HSG 24P Y KEY | <a href="#">2-2420334-4</a> | <a href="#">6-2420334-4</a> | <a href="#">8-2420334-4</a> |

DYNAMIC D1000 SLIM CONNECTOR

| Part Type                                          | Part Description       | Part Number        |
|----------------------------------------------------|------------------------|--------------------|
| <u>REC</u><br><u>Contact</u><br><u>Au Plating</u>  | REC Cont M size Au     | <u>2367817-2</u>   |
|                                                    | REC Cont M size Au L/P | <u>2367818-2</u>   |
|                                                    | REC Cont S size Au     | <u>2367817-1</u>   |
|                                                    | REC Cont S size Au L/P | <u>2367818-1</u>   |
| <u>TAB</u><br><u>Contact</u><br><u>Au Plating</u>  | TAB Cont M size Au     | <u>2367819-2</u>   |
|                                                    | TAB Cont M size Au L/P | <u>2367820-2</u>   |
|                                                    | TAB Cont S size Au     | <u>2367819-1</u>   |
|                                                    | TAB Cont S size Au L/P | <u>2367820-1</u>   |
| <u>REC</u><br><u>Contact</u><br><u>Tin Plating</u> | REC Cont M Size Tin    | <u>3-2367817-2</u> |
|                                                    | REC Cont S Size Tin    | <u>3-2367817-1</u> |
| <u>TAB</u><br><u>Contact</u><br><u>Tin Plating</u> | TAB Cont M Size Tin    | <u>3-2367819-2</u> |
|                                                    | TAB Cont S Size Tin    | <u>3-2367819-1</u> |

Connect With Us

We make it easy to connect with our experts and are ready to provide all the support you need.  
Visit [te.com/support](https://te.com/support) to chat with a Product Information Specialist.

te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2026 TE Connectivity. All Rights Reserved.

04/26

