


CG2H80015D

15 W, 8.0 GHz, GaN HEMT Die

Description

Wolfspeed's CG2H80015D is a gallium nitride (GaN) High Electron Mobility Transistor (HEMT). GaN has superior properties compared to silicon or gallium arsenide, including higher breakdown voltage, higher saturated electron drift velocity, and higher thermal conductivity. GaN HEMTs offer greater power density and wider bandwidths compared to Si and GaAs transistors.



PNs: CG2H80015D


Features

- 17 dB Typical Small Signal Gain at 4 GHz
- 12 dB Typical Small Signal Gain at 8 GHz
- 15 W Typical P_{SAT}
- 28 V Operation
- High Breakdown Voltage
- High Temperature Operation
- Up to 8 GHz Operation
- High Efficiency

Applications

- 2-Way Private Radio
- Broadband Amplifiers
- Cellular infrastructure
- Test Instrumentation
- Class A, AB, Linear amplifiers suitable for OFDM, W-CDMA, EDGE, CDMA waveforms

Packaging Information



- Bare die are shipped in Gel-Pak® containers
- Non-adhesive tacky membrane immobilizes die during shipment



Large Signal Models Available for ADS and MWO





Absolute Maximum Ratings (not simultaneous) at 25°C Case Temperature

Parameter	Symbol	Rating	Units	Conditions
Drain-Source Voltage	V_{DS}	120	V	25°C
Gate-to-Source Voltage	V_{GS}	-10, +2		
Storage Temperature	T_{STG}	-65, +150	°C	
Operating Junction Temperature	T_J	225		
Maximum Forward Gate Current	I_{GMAX}	4.0	mA	25°C
Maximum Drain Current ¹	I_{DMAX}	1.5	A	
Thermal Resistance, Junction to Case (packaged) ²	$R_{\theta JC}$	8.0	°C/W	
Thermal Resistance, Junction to Case (die only)		5.1		
Mounting Temperature (30 seconds)	T_s	300	°C	30 seconds

Notes:

¹ Current limit for long term, reliable operation

² Eutectic die attach using 80/20 AuSn mounted to a 40 mil thick CuMoCu carrier

Electrical Characteristics (Frequency = 4 GHz unless otherwise stated; $T_c = 25^\circ\text{C}$)

Characteristics	Symbol	Min.	Typ.	Max.	Units	Conditions
DC Characteristics						
Gate Threshold Voltage	$V_{GS(th)}$	-3.8	-3.0	-2.3	V_{DC}	$V_{DS} = 10\text{ V}, I_D = 3.6\text{ mA}$
Gate Quiescent Voltage	$V_{GS(Q)}$	—	-2.7	—		$V_{DD} = 28\text{ V}, I_{DQ} = 100\text{ mA}$
Saturated Drain Current	I_{DS}	2.9	3.5	—	A	$V_{DS} = 6.0\text{ V}, V_{GS} = 2.0\text{ V}$
Drain-Source Breakdown Voltage	V_{BD}	84	—	—	V_{DC}	$V_{GS} = -8\text{ V}, I_D = 3.6\text{ mA}$
On Resistance	R_{ON}	—	0.67	—	Ω	$V_{DS} = 0.1\text{ V}$
Gate Forward Voltage	V_{G-ON}	—	1.9	—	V	$I_{GS} = 3.6\text{ mA}$
RF Characteristics						
Small Signal Gain	G_{SS}	—	17	—	dB	$V_{DD} = 28\text{ V}, I_{DQ} = 100\text{ mA}$
Output Power ¹	P_{SAT}	—	15	—	W	
Drain Efficiency ²	η	—	65	—	%	$V_{DD} = 28\text{ V}, I_{DQ} = 100\text{ mA}, P_{SAT} = 15\text{ W}$
Intermodulation Distortion	IM3	—	-30	—	dBc	$V_{DD} = 28\text{ V}, I_{DQ} = 100\text{ mA}, P_{OUT} = 15\text{ W PEP}$
Output Mismatch Stress ³	VSWR	—	—	10 : 1	Y	$V_{DD} = 28\text{ V}, I_{DQ} = 100\text{ mA}, P_{OUT} = 15\text{ W CW}$
Dynamic Characteristics						
Input Capacitance	C_{GS}	—	3.7	—	pF	$V_{DS} = 28\text{ V}, V_{GS} = -8\text{ V}, f = 1\text{ MHz}$
Output Capacitance	C_{DS}	—	1.1	—		
Feedback Capacitance	C_{GD}	—	0.2	—		

Notes:

¹ P_{SAT} is defined as $I_G = 0.4\text{ mA}$

² Drain Efficiency = P_{OUT} / P_{DC}

³ No damage at all phase angles



Electrostatic Discharge (ESD) Classifications

Parameter	Symbol	Class	Classification Level	Test Methodology
Human Body Model	HBM	TBD	ANSI/ESDA/JEDEC JS-001 Table 3	JEDEC JESD22 A114-D

Typical Performance




Figure 1. Simulated Maximum Available Gain and K-Factor
 $V_{DD} = 28\text{ V}$, $I_{DQ} = 200\text{ mA}$





Figure 2. Simulated Minimum Noise Figure and Noise Resistance vs. Frequency
 $V_{DD} = 28\text{ V}$, $I_{DQ} = 200\text{ mA}$

Intrinsic die parameters - reference planes at centers of gate and drain bonding pads. No wire bonds assumed.

Die Dimensions (units in microns)



Assembly Notes:

- Recommended solder is AuSn (80/20) solder. Refer to Wolfspeed's website for the Eutectic Die Bond Procedure application note at <https://www.wolfspeed.com/rf/document-library>
- Vacuum collet is the preferred method of pick-up.
- The backside of the die is the Source (ground) contact.
- Die back side gold plating is 5 microns thick minimum.
- Thermosonic ball or wedge bonding are the preferred connection methods.
- Gold wire must be used for connections.
- Use the die label (XX-YY) for correct orientation.



Typical Package S-Parameters for CG2H80015D
(Small Signal, $V_{DS} = 28\text{ V}$, $I_{DQ} = 100\text{ mA}$, magnitude / angle)

Frequency	Mag S11	Ang S11	Mag S21	Ang S21	Mag S12	Ang S12	Mag S22	Ang S22
0.5	0.909	-110.59	21.66	117.76	0.030	28.48	0.437	-96.69
0.6	0.900	-120.05	18.90	112.17	0.031	23.04	0.426	-105.26
0.7	0.893	-127.43	16.69	107.63	0.032	18.63	0.419	-111.87
0.8	0.889	-133.31	14.89	103.82	0.033	14.98	0.414	-117.03
0.9	0.885	-138.08	13.41	100.56	0.033	11.86	0.412	-121.10
1.0	0.883	-142.02	12.18	97.71	0.034	9.15	0.412	-124.36
1.1	0.881	-145.32	11.15	95.16	0.034	6.75	0.413	-126.99
1.2	0.880	-148.13	10.26	92.86	0.034	4.59	0.415	-129.14
1.3	0.879	-150.55	9.50	90.74	0.034	2.62	0.418	-130.90
1.4	0.879	-152.65	8.83	88.79	0.034	0.80	0.421	-132.37
1.5	0.879	-154.49	8.25	86.95	0.034	-0.89	0.425	-133.61
1.6	0.878	-156.12	7.73	85.23	0.034	-2.47	0.430	-134.65
1.8	0.879	-158.88	6.86	82.02	0.034	-5.38	0.440	-136.33
2.0	0.879	-161.14	6.15	79.08	0.034	-8.03	0.451	-137.62
2.2	0.880	-163.03	5.57	76.35	0.034	-10.48	0.463	-138.66
2.4	0.881	-164.63	5.07	73.77	0.033	-12.77	0.476	-139.54
2.6	0.883	-166.03	4.65	71.32	0.033	-14.93	0.489	-140.32
2.8	0.884	-167.26	4.28	68.98	0.033	-16.98	0.502	-141.04
3.0	0.886	-168.35	3.97	66.73	0.032	-18.94	0.516	-141.72
3.2	0.887	-169.34	3.69	64.57	0.032	-20.81	0.530	-142.39
3.4	0.889	-170.24	3.44	62.48	0.032	-22.61	0.543	-143.05
3.6	0.891	-171.07	3.21	60.45	0.031	-24.34	0.556	-143.71
3.8	0.893	-171.84	3.01	58.49	0.031	-26.01	0.570	-144.37
4.0	0.895	-172.57	2.83	56.59	0.030	-27.62	0.583	-145.03
4.2	0.896	-173.25	2.67	54.74	0.030	-29.17	0.595	-145.70
4.4	0.898	-173.90	2.52	52.94	0.030	-30.68	0.608	-146.37
4.6	0.900	-174.51	2.38	51.18	0.029	-32.14	0.620	-147.05
4.8	0.902	-175.11	2.26	49.48	0.029	-33.55	0.632	-147.73
5.0	0.904	-175.68	2.14	47.81	0.028	-34.91	0.643	-148.41
5.2	0.905	-176.23	2.04	46.19	0.028	-36.24	0.654	-149.09
5.4	0.907	-176.76	1.94	44.60	0.027	-37.52	0.665	-149.77
5.6	0.909	-177.28	1.85	43.06	0.027	-38.77	0.675	-150.45
5.8	0.910	-177.79	1.76	41.54	0.027	-39.98	0.685	-151.13
6.0	0.912	-178.29	1.68	40.07	0.026	-41.15	0.695	-151.81
6.2	0.914	-178.77	1.61	38.63	0.026	-42.29	0.704	-152.48
6.4	0.915	-179.25	1.54	37.21	0.025	-43.40	0.713	-153.14
6.6	0.917	-179.72	1.48	35.83	0.025	-44.47	0.722	-153.80
6.8	0.918	-179.82	1.42	34.48	0.024	-45.52	0.730	-154.46
7.0	0.919	-179.36	1.36	33.16	0.024	-46.53	0.738	-155.11
7.2	0.921	-178.91	1.31	31.87	0.024	-47.51	0.745	-155.75
7.4	0.922	-178.46	1.26	30.60	0.023	-48.47	0.753	-156.38
7.6	0.923	-178.02	1.21	29.36	0.023	-49.40	0.760	-157.01
7.8	0.925	-177.58	1.17	28.14	0.022	-50.30	0.767	-157.63
8.0	0.926	-177.15	1.12	26.94	0.022	-51.18	0.773	-158.24

To download the s-parameters in s2p format, go to the [CG2H80015D](#) product page and click on the documentation tab.



Typical Package S-Parameters for CG2H80015D
(Small Signal, $V_{DS} = 28\text{ V}$, $I_{DQ} = 200\text{ mA}$, magnitude / angle)

Frequency	Mag S11	Ang S11	Mag S21	Ang S21	Mag S12	Ang S12	Mag S22	Ang S22
0.5	0.914	-119.76	23.66	114.12	0.025	24.92	0.414	-115.65
0.6	0.908	-128.48	20.44	109.01	0.026	19.96	0.414	-123.32
0.7	0.903	-135.16	17.92	104.91	0.026	16.02	0.414	-128.96
0.8	0.900	-140.41	15.92	101.51	0.027	12.78	0.415	-133.20
0.9	0.898	-144.63	14.29	98.61	0.027	10.04	0.417	-136.45
1.0	0.896	-148.09	12.95	96.08	0.027	7.66	0.419	-138.97
1.1	0.895	-150.98	11.83	93.82	0.027	5.56	0.422	-140.95
1.2	0.894	-153.43	10.87	91.77	0.027	3.68	0.425	-142.52
1.3	0.894	-155.54	10.06	89.90	0.027	1.96	0.428	-143.78
1.4	0.893	-157.37	9.35	88.16	0.027	0.38	0.432	-144.79
1.5	0.893	-158.97	8.73	86.52	0.027	-1.09	0.436	-145.61
1.6	0.893	-160.39	8.18	84.98	0.027	-2.47	0.440	-146.29
1.8	0.893	-162.80	7.26	82.12	0.027	-5.02	0.448	-147.30
2.0	0.894	-164.77	6.51	79.48	0.027	-7.34	0.458	-148.00
2.2	0.894	-166.42	5.90	77.01	0.027	-9.49	0.468	-148.51
2.4	0.895	-167.84	5.38	74.67	0.027	-11.51	0.478	-148.89
2.6	0.896	-169.07	4.94	72.45	0.026	-13.41	0.489	-149.21
2.8	0.897	-170.15	4.56	70.31	0.026	-15.23	0.500	-149.49
3.0	0.898	-171.13	4.23	68.25	0.026	-16.97	0.511	-149.76
3.2	0.899	-172.01	3.93	66.25	0.026	-18.64	0.523	-150.03
3.4	0.900	-172.81	3.68	64.32	0.026	-20.24	0.534	-150.30
3.6	0.902	-173.55	3.44	62.44	0.025	-21.80	0.545	-150.59
3.8	0.903	-174.25	3.24	60.62	0.025	-23.30	0.557	-150.90
4.0	0.904	-174.90	3.05	58.83	0.025	-24.75	0.568	-151.23
4.2	0.906	-175.51	2.88	57.09	0.024	-26.16	0.579	-151.57
4.4	0.907	-176.09	2.72	55.40	0.024	-27.53	0.590	-151.94
4.6	0.908	-176.65	2.58	53.74	0.024	-28.86	0.601	-152.33
4.8	0.910	-177.19	2.45	52.11	0.023	-30.15	0.612	-152.73
5.0	0.911	-177.71	2.33	50.53	0.023	-31.40	0.622	-153.15
5.2	0.912	-178.21	2.22	48.97	0.023	-32.62	0.632	-153.59
5.4	0.913	-178.69	2.11	47.45	0.023	-33.81	0.642	-154.03
5.6	0.915	-179.17	2.02	45.96	0.022	-34.96	0.652	-154.49
5.8	0.916	-179.63	1.93	44.50	0.022	-36.08	0.661	-154.96
6.0	0.917	-179.92	1.85	43.07	0.022	-37.17	0.670	-155.43
6.2	0.918	-179.47	1.77	41.67	0.021	-38.22	0.679	-155.92
6.4	0.920	-179.03	1.70	40.29	0.021	-39.25	0.688	-156.41
6.6	0.921	-178.60	1.63	38.94	0.021	-40.25	0.696	-156.90
6.8	0.922	-178.17	1.56	37.62	0.020	-41.22	0.704	-157.39
7.0	0.923	-177.75	1.50	36.32	0.020	-42.17	0.712	-157.89
7.2	0.924	-177.33	1.45	35.04	0.020	-43.09	0.720	-158.39
7.4	0.925	-176.92	1.39	33.79	0.019	-43.98	0.727	-158.90
7.6	0.926	-176.51	1.34	32.56	0.019	-44.85	0.734	-159.40
7.8	0.927	-176.10	1.30	31.35	0.019	-45.69	0.741	-159.90
8.0	0.928	-175.69	1.25	30.16	0.018	-46.51	0.747	-160.40

To download the s-parameters in s2p format, go to the [CG2H80015D](#) product page and click on the documentation tab.




Typical Package S-Parameters for CG2H80015D
(Small Signal, $V_{DS} = 28\text{ V}$, $I_{DQ} = 500\text{ mA}$, magnitude / angle)

Frequency	Mag S11	Ang S11	Mag S21	Ang S21	Mag S12	Ang S12	Mag S22	Ang S22
0.5	0.925	-129.48	24.00	109.96	0.020	20.87	0.401	-131.97
0.6	0.920	-137.20	20.52	105.38	0.020	16.47	0.406	-137.90
0.7	0.918	-143.01	17.88	101.74	0.021	13.01	0.411	-142.09
0.8	0.916	-147.53	15.81	98.73	0.021	10.18	0.414	-145.14
0.9	0.914	-151.13	14.15	96.16	0.021	7.79	0.418	-147.40
1.0	0.914	-154.07	12.79	93.91	0.021	5.73	0.421	-149.10
1.1	0.913	-156.52	11.66	91.90	0.021	3.90	0.424	-150.39
1.2	0.913	-158.60	10.71	90.08	0.021	2.26	0.428	-151.38
1.3	0.912	-160.38	9.89	88.39	0.021	0.76	0.431	-152.14
1.4	0.912	-161.93	9.19	86.83	0.021	-0.63	0.435	-152.72
1.5	0.912	-163.29	8.58	85.35	0.021	-1.92	0.439	-153.16
1.6	0.912	-164.49	8.04	83.95	0.021	-3.14	0.443	-153.50
1.8	0.912	-166.54	7.13	81.34	0.021	-5.38	0.451	-153.93
2.0	0.913	-168.23	6.40	78.92	0.021	-7.44	0.459	-154.16
2.2	0.913	-169.65	5.79	76.63	0.021	-9.36	0.468	-154.27
2.4	0.914	-170.87	5.29	74.46	0.021	-11.16	0.478	-154.31
2.6	0.914	-171.94	4.85	72.38	0.021	-12.87	0.488	-154.32
2.8	0.915	-172.89	4.48	70.38	0.020	-14.50	0.498	-154.32
3.0	0.916	-173.74	4.16	68.44	0.020	-16.07	0.508	-154.33
3.2	0.916	-174.52	3.87	66.56	0.020	-17.58	0.519	-154.36
3.4	0.917	-175.24	3.62	64.72	0.020	-19.03	0.529	-154.41
3.6	0.918	-175.91	3.39	62.94	0.020	-20.44	0.540	-154.49
3.8	0.919	-176.53	3.19	61.19	0.019	-21.80	0.550	-154.60
4.0	0.920	-177.12	3.01	59.49	0.019	-23.12	0.561	-154.75
4.2	0.921	-177.68	2.84	57.82	0.019	-24.41	0.571	-154.92
4.4	0.922	-178.21	2.69	56.19	0.019	-25.65	0.582	-155.12
4.6	0.923	-178.72	2.55	54.59	0.018	-26.86	0.592	-155.35
4.8	0.923	-179.21	2.43	53.03	0.018	-28.04	0.602	-155.61
5.0	0.924	-179.69	2.31	51.49	0.018	-29.18	0.612	-155.89
5.2	0.925	-179.85	2.20	49.99	0.018	-30.29	0.622	-156.19
5.4	0.926	-179.40	2.10	48.51	0.018	-31.37	0.631	-156.51
5.6	0.927	-178.96	2.01	47.06	0.017	-32.41	0.640	-156.85
5.8	0.928	-178.53	1.92	45.64	0.017	-33.43	0.649	-157.21
6.0	0.929	-178.10	1.84	44.24	0.017	-34.42	0.658	-157.57
6.2	0.930	-177.69	1.76	42.87	0.017	-35.37	0.667	-157.96
6.4	0.931	-177.28	1.69	41.52	0.016	-36.30	0.675	-158.35
6.6	0.931	-176.87	1.63	40.20	0.016	-37.21	0.683	-158.75
6.8	0.932	-176.47	1.56	38.90	0.016	-38.08	0.691	-159.16
7.0	0.933	-176.07	1.50	37.62	0.015	-38.93	0.699	-159.58
7.2	0.934	-175.68	1.45	36.36	0.015	-39.75	0.707	-160.00
7.4	0.934	-175.29	1.40	35.13	0.015	-40.54	0.714	-160.43
7.6	0.935	-174.90	1.35	33.91	0.015	-41.31	0.721	-160.86
7.8	0.936	-174.51	1.30	32.72	0.014	-42.05	0.728	-161.30
8.0	0.937	-174.13	1.26	31.54	0.014	-42.77	0.734	-161.73

To download the s-parameters in s2p format, go to the [CG2H80015D](#) product page and click on the documentation tab.



Product Ordering Information

Order Number	Description	Unit of Measure	Image
CG2H80015D	GaN HEMT Bare Die	Each	

**For more information, please contact:**

4600 Silicon Drive
Durham, NC 27703 USA
Tel: +1.919.313.5300
www.wolfspeed.com/RF

Sales Contact
RFSales@wolfspeed.com

RF Product Marketing Contact
RFMarketing@wolfspeed.com

Notes & Disclaimer

Specifications are subject to change without notice. “Typical” parameters are the average values expected by Wolfspeed in large quantities and are provided for information purposes only. Wolfspeed products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

© 2017 - 2022 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc.
PATENT: <https://www.wolfspeed.com/legal/patents>

The information in this document is subject to change without notice.