




# Heatsinks HS-01, HS-02 and HS-03

The advantages of adding a heatsink are to help heat dissipation and increase the stability and reliability of the DC/DC converters at high operating temperatures. Refer to the derating curves below to upgrade the operating temperatures of various ConTech models.





· Aluminum with Black Anodic Treatment

#### HS-01 (2 x 1 Case Size)



Fits 2 x 1 Cases Aluminum with Black Anodic Finish Weight: 2 gms 1.89 x 0.82 x 0.25






Dimensions are inches (mm) unless noted


Tolerance: Inches Millimeters


X.XX ±0.02 X.X ±0.5


X.XXX ±0.01 X.XX ±0.25


### Derating Curves with heastsink HS-01 attached














#### HS-02 (2 x 1.6 Case Size)




Fits 2 x 1.6 Cases Aluminum with Black Anodic Finish Weight: 2 gms 1.89 x 1.47 x 0.25


Dimensions are inches (mm) unless noted

Tolerance: Inches Millimeters


X.XX ±0.02 X.X ±0.5 X.XXX ±0.01 X.XX ±0.25

#### Derating Curves with heastsink HS-02 attached





## HS-03 (1 x 1 Case Size)




Fits 1 x 1 Cases Aluminum with Black Anodic Finish Weight: 2.9 gms 0.83 x 0.83 x 0.25 Dimensions are inches (mm) unless noted

Tolerance: Inches Millimeters  $X.XX \pm 0.02 \qquad X.X \pm 0.5$ 

X.XXX ±0.01 X.XX ±0.25

## Derating Curves with heastsink HS-03 attached



www.ConTech-us.com