

## PolySwitch® PTC Devices

**Overcurrent Protection Device** 

PRODUCT: miniSMDC110F/24

DOCUMENT: SCD25813 REV LETTER: K

**REV DATE: JULY 26, 2016** 

PAGE NO.: 1 OF 2

### **Specification Status: Released**

#### **Maximum Electrical Rating**


Voltage: 24V<sub>DC</sub>


**Short Circuit Current: 20A** 

#### Notes

- 1. All terminations are tin plated.
- 2. Drawing not to scale

#### Marking:





#### **TABLE I. DIMENSIONS:**

	Α		В		С		D		Е
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN
mm:	4.37	4.83	0.81	1.46	3.07	3.41	0.25	0.95	0.20
in:	(0.172)	(0.190)	(0.032)	(0.057)	(0.121)	(0.134)	(0.010)	(0.040)	(800.0)

#### TABLE IL PERFORMANCE RATINGS:

TABLE II. PERFORMANCE RATINGS.									
CURRENT RATINGS**						TIME TO	RESISTANCE		TRIPPED-STATE
						TRIP**	VALUES		POWER
							DISSIPATION**		
AMPERES		AMPERES		AMPERES		SECONDS	OHMS		WATTS AT
AT 0°C		AT 20°C		AT 60°C		AT 20°C, 8.0A	AT 20°C		20°C, 24V
HOLD	TRIP	HOLD	TRIP	HOLD	TRIP	MAX	MIN	MAX*	MAX
1.4	2.8	1.1	2.2	0.8	1.6	0.5	0.060	0.180	0.8

<sup>\*</sup> Maximum resistance is measured 1 hour after reflow.

Agency Recognition: UL, CSA, TÜV Reference Document: PS300

Precedence: This specification takes precedence over documents referenced herein.

Effectivity: Reference documents shall be the issue in effect on the date of invitation for bid.

CAUTION: Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

#### **Materials Information**

**ROHS Compliant** 

**ELV Compliant** 

Pb-Free

Halogen Free\*



Directive 2000/53/EC

\* Halogen Free refers to: Br≤900ppm, Cl≤900ppm, Br+Cl≤1500ppm.

© 2016 Littelfuse,Inc Specifications are subject to change without notice. Revised July 26, 2016 Littelfuse.com

<sup>\*\*</sup> Values Specified were determined using PCB's with 0.030"X1.5 ounce copper traces.

Directive 2002/95/EC Compliant



# PolySwitch® PTC Devices

**Overcurrent Protection Device** 

PRODUCT: miniSMDC110F/24

DOCUMENT: SCD25813

REV LETTER: K REV DATE: JULY 26, 2016

PAGE NO.: 2 OF 2

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, military, aerospace, medical, lifesaving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.